

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332305-935

Luminaire Tested: **S123RDIP-S775D365U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332305-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D365U935-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3643.2 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69
1	102	98	94	91	97	93	90	87	83	81	78	74	72	70	66	64	63	59
2	94	86	80	75	88	82	76	72	73	69	66	66	62	60	58	56	54	50
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	52	49	46	43
4	79	68	60	54	74	65	57	52	58	52	48	52	48	44	47	43	40	37
5	73	61	53	47	68	58	50	45	52	46	42	47	42	38	42	38	35	33
6	67	55	47	41	63	52	45	39	47	41	37	43	38	34	39	35	31	29
7	62	50	42	36	59	47	40	35	43	37	33	39	34	30	35	31	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	2.9
10°-20°	290.4	8.0
20°-30°	418.2	11.5
30°-40°	471.1	12.9
40°-50°	450.7	12.4
50°-60°	369.0	10.1
60°-70°	249.0	6.8
70°-80°	125.3	3.4
80°-90°	34.3	0.9
90°-100°	83.7	2.3
100°-110°	236.9	6.5
110°-120°	233.0	6.4
120°-130°	185.8	5.1
130°-140°	146.5	4.0
140°-150°	109.4	3.0
150°-160°	76.2	2.1
160°-170°	44.8	1.2
170°-180°	14.6	0.4
0°-30°	813.0	22.3
0°-40°	1284.1	35.2
0°-60°	2103.8	57.7
0°-90°	2512.3	69.0
90°-120°	553.5	15.2
90°-150°	995.3	27.3
90°-180°	1131.0	31.0
0°-180°	3643.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	4	8	8	9	3
95°	10	34	180	53	35	11
105°	35	52	245	428	387	38
115°	62	78	187	410	471	62
125°	87	102	175	316	371	77
135°	102	121	172	261	301	79
145°	116	133	170	214	235	73
155°	132	142	165	187	195	61
165°	144	148	158	167	170	41
175°	150	150	151	153	153	14
180°	150	150	150	150	150	



TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.4	15.8	14.1	12.6	10.9	10.2	10.3	10.5	10.7	10.9	10.7
90°	0.6	1.2	1.8	2.8	3.4	4.0	4.9	5.8	6.7	7.6	7.3
92.5°	3.8	5.6	8.2	10.5	13.1	17.6	25.6	38.7	51.5	46.8	35.3
95°	10.3	11.3	14.6	19.8	27.7	39.5	65.4	110.7	160.7	180.5	146.4
97.5°	17.7	17.9	20.6	25.1	32.9	45.7	70.4	121.5	204.7	279.7	299.1
100°	22.6	22.8	25.0	29.2	36.5	48.4	69.7	114.7	194.8	288.2	348.1
102.5°	27.6	28.2	30.0	34.1	40.6	51.6	70.7	108.8	180.1	272.3	350.5
105°	35.3	36.2	38.1	41.7	47.4	56.9	73.4	104.7	162.2	244.6	331.9
107.5°	43.5	44.3	46.1	49.7	55.1	63.9	78.4	104.4	150.8	220.2	299.5
110°	49.2	50.2	51.7	55.1	60.3	68.8	82.5	105.6	146.4	206.3	279.1



TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	54.7	55.5	57.1	60.4	65.6	73.9	86.6	108.1	143.9	197.0	261.2
115°	62.3	63.6	65.4	68.4	73.6	81.9	93.4	111.9	143.0	187.1	239.8
117.5°	70.1	71.5	73.0	75.9	81.6	89.2	100.7	117.2	143.5	181.2	226.8
120°	75.4	76.4	77.9	80.9	86.7	94.3	105.3	121.1	144.6	178.6	220.0
122.5°	80.1	81.0	82.5	85.8	91.4	99.4	110.1	124.8	146.2	176.9	214.4
125°	86.7	87.3	89.1	92.5	98.2	106.5	117.2	130.5	148.8	174.6	207.2
127.5°	91.8	92.6	95.0	98.3	104.7	113.0	123.2	135.3	151.7	173.6	200.9
130°	95.0	95.8	98.6	102.2	108.7	116.8	126.9	138.4	153.7	172.8	197.4
132.5°	97.4	98.5	101.5	105.9	112.3	120.3	130.0	141.4	155.2	172.5	194.3
135°	101.6	102.8	106.2	110.7	117.2	125.4	134.7	145.2	157.3	172.2	190.2
137.5°	105.6	106.9	110.2	115.0	121.4	129.0	138.1	147.9	158.8	171.5	186.6
140°	108.3	109.9	112.9	117.8	123.8	131.5	140.3	149.4	159.7	171.3	184.3
142.5°	111.2	112.5	115.8	120.2	126.3	133.4	142.0	150.8	160.5	170.8	182.4
145°	115.9	116.8	119.6	124.2	129.3	136.3	144.2	152.4	160.9	170.0	179.8
147.5°	120.7	121.2	123.9	127.9	132.9	138.8	146.0	153.4	160.9	168.9	177.3
150°	123.8	124.2	126.6	130.5	134.7	140.3	147.2	153.7	160.9	168.0	175.6
152.5°	127.0	127.1	129.5	132.9	136.7	142.0	148.0	154.1	160.2	166.8	173.6
155°	131.7	131.7	133.5	136.6	140.0	144.2	149.4	154.3	159.5	164.6	170.7
157.5°	135.5	135.8	137.2	139.9	142.8	146.0	150.2	154.5	158.4	162.7	167.4
160°	138.4	138.4	139.7	142.1	144.2	147.2	150.9	154.5	157.9	161.3	165.2
162.5°	140.6	140.6	141.6	143.5	145.4	148.0	151.2	154.3	157.0	159.8	163.0
165°	143.9	143.6	144.2	145.8	147.0	149.1	151.5	153.7	155.5	157.6	160.1
167.5°	146.4	146.0	146.4	147.5	148.4	149.7	151.4	153.2	154.0	155.4	157.2
170°	147.8	147.2	147.6	148.4	149.1	149.7	151.2	152.4	153.1	153.9	155.5
172.5°	148.9	148.4	148.5	149.2	149.6	149.9	151.2	152.2	152.3	152.7	153.8
175°	150.0	149.7	149.4	150.0	150.0	150.3	150.9	151.5	151.2	151.2	151.8
177.5°	150.6	150.3	150.1	150.3	150.3	150.3	150.6	151.0	150.6	150.3	150.6
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3



TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	10.6	10.5	10.4	10.3	10.2	10.0	9.9	9.7
90°	7.6	7.9	8.2	8.8	8.5	8.8	9.1	8.8
92.5°	25.7	20.3	17.9	16.4	15.8	14.9	15.2	14.6
95°	109.5	74.2	58.1	47.2	41.4	38.7	36.5	35.3
97.5°	273.0	218.7	179.4	143.1	120.6	106.9	98.7	96.1
100°	358.7	334.1	298.5	255.3	224.5	202.3	190.5	190.8
102.5°	387.2	386.4	365.7	338.3	314.4	296.8	286.9	279.8
105°	395.5	425.9	431.7	423.9	409.8	398.3	388.6	387.0
107.5°	371.5	420.9	447.6	458.5	458.7	454.8	451.5	448.8
110°	348.7	404.7	443.0	464.3	472.9	475.3	474.7	474.1



TEST NUMBER: P332305-935

CATALOG NUMBER: S123RDIP-S775D365U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	326.1	383.2	426.2	453.6	469.2	476.7	479.1	479.1
115°	296.0	349.0	393.7	426.9	449.7	463.0	469.2	470.7
117.5°	274.3	320.0	360.2	393.8	417.7	433.0	441.7	443.8
120°	262.9	303.9	340.4	371.2	395.2	412.2	419.6	421.4
122.5°	253.9	291.0	324.9	353.4	374.8	390.1	398.1	400.5
125°	241.9	275.1	304.3	328.6	348.1	361.4	369.1	371.2
127.5°	231.4	261.0	287.3	309.5	326.8	338.3	345.2	347.1
130°	224.8	252.3	276.9	297.6	313.7	324.7	331.1	333.5
132.5°	218.8	243.9	266.9	286.6	301.8	312.7	318.4	320.1
135°	210.5	232.1	251.9	269.2	284.2	293.3	298.8	300.9
137.5°	203.0	220.8	237.8	252.9	265.4	274.7	279.2	280.7
140°	198.7	214.2	228.8	241.9	253.5	262.0	266.8	266.6
142.5°	194.6	207.8	220.5	231.9	241.8	249.3	253.7	253.4
145°	189.6	199.6	209.3	218.2	225.8	232.1	234.6	235.2
147.5°	185.5	193.5	201.3	207.6	213.4	217.7	220.0	220.2
150°	182.5	189.6	196.0	201.7	206.3	209.7	211.5	211.5
152.5°	179.9	185.9	191.6	196.4	199.9	203.0	204.1	204.1
155°	175.9	180.7	185.3	188.9	191.7	194.2	194.8	195.0
157.5°	171.6	175.6	179.2	182.1	184.4	186.2	186.8	186.7
160°	169.2	172.5	175.6	177.7	179.8	181.7	181.7	181.3
162.5°	166.3	169.1	171.9	173.8	175.2	176.8	176.8	176.5
165°	162.5	164.3	166.4	168.0	169.2	170.4	170.0	170.0
167.5°	159.2	160.6	161.8	162.9	163.4	164.3	164.0	164.0
170°	157.0	157.9	159.1	159.7	160.1	160.7	160.3	160.3
172.5°	155.1	155.8	156.7	157.0	157.1	157.7	157.2	157.0
175°	152.4	152.7	153.3	153.3	153.3	153.7	153.3	153.1
177.5°	150.8	151.0	151.3	151.3	151.0	151.3	150.8	150.8
180°	150.3	150.3	150.3	150.3	150.3	150.3	150.3	150.3

(END OF REPORT)