

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P832404

Luminaire Tested: S123RDIP-S775D585U935-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P832404  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-2, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D585U935-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4866.2 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 1.17 / 0.8  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 41.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59		
1	101	97	93	90	94	90	87	84	79	76	74	68	66	65	58	57	56	51		
2	92	86	80	75	86	80	75	71	70	66	63	61	58	56	52	50	49	44		
3	85	76	69	64	79	72	65	61	63	58	54	55	51	48	47	45	43	39		
4	78	68	61	55	73	64	58	52	57	51	47	50	46	42	43	40	38	34		
5	73	61	54	48	68	58	51	46	51	46	42	45	41	38	39	36	34	31		
6	67	56	48	43	63	53	46	41	47	41	37	41	37	34	36	33	30	28		
7	63	51	43	38	59	48	41	36	43	37	33	38	34	30	34	30	28	25		
8	58	47	39	34	55	44	38	33	40	34	30	35	31	28	31	28	25	23		
9	55	43	36	31	51	41	34	30	37	31	28	33	28	25	29	26	23	21		
10	51	40	33	28	48	38	32	27	34	29	25	31	26	23	27	24	21	20		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	23137	23137	23137	23137	23137
5°	27472	26596	23282	18821	17474
10°	24890	27015	23166	15080	12937
15°	17137	23162	22921	12325	10233
20°	11922	17833	22462	10393	8994
25°	9086	13592	21791	9236	8290
30°	7909	10866	20954	8576	7679
35°	7261	9165	19768	8020	7122
40°	6625	8185	18216	7474	6613
45°	5984	7486	16541	6955	6104
50°	5431	6906	14565	6449	5476
55°	4911	6343	12669	5955	4697
60°	4402	5767	11003	5408	4439
65°	4062	5117	9472	4860	4197
70°	3301	4425	8264	4397	3412
75°	2895	3518	6999	3647	3007
80°	2622	2975	5734	3062	2839
85°	2396	2618	4360	2779	2618

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 17454 cd/sqm



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.9	4.0
10°-20°	453.4	9.3
20°-30°	520.2	10.7
30°-40°	512.7	10.5
40°-50°	452.1	9.3
50°-60°	347.8	7.1
60°-70°	228.7	4.7
70°-80°	111.1	2.3
80°-90°	29.3	0.6
90°-100°	23.3	0.5
100°-110°	112.7	2.3
110°-120°	276.1	5.7
120°-130°	350.6	7.2
130°-140°	374.5	7.7
140°-150°	350.2	7.2
150°-160°	282.5	5.8
160°-170°	182.3	3.7
170°-180°	62.8	1.3
0°-30°	1169.4	24.0
0°-40°	1682.1	34.6
0°-60°	2482.1	51.0
0°-90°	2851.2	58.6
90°-120°	412.1	8.5
90°-150°	1487.4	30.6
90°-180°	2015.0	41.4
0°-180°	4866.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2150	2150	2150	2150	2150	
5°	2542	2461	2155	1742	1617	232
15°	1538	2078	2057	1106	918	434
25°	765	1144	1835	778	698	361
35°	553	698	1504	610	542	344
45°	393	492	1087	457	401	305
55°	262	338	675	317	250	235
65°	160	201	372	191	165	156
75°	70	85	168	88	72	75
85°	19	21	35	22	21	21
90°	15	12	0	12	15	8
95°	19	15	30	15	19	16
105°	22	108	146	108	22	45
115°	289	282	274	282	289	272
125°	395	393	387	393	395	353
135°	487	487	482	487	487	375
145°	561	560	556	560	561	351
155°	611	612	612	612	611	282
165°	644	644	646	644	644	182
175°	658	659	661	659	658	63
180°	661	661	661	661	661	



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5
2.5°	2382.1	2374.6	2367.1	2364.9	2362.7	2355.7	2348.6	2332.8	2316.9	2300.6	2284.3
5°	2542.5	2543.4	2544.3	2542.1	2539.9	2530.6	2521.4	2502.0	2482.6	2461.4	2440.3
7.5°	2493.2	2507.3	2521.4	2524.0	2526.6	2533.7	2540.7	2536.3	2531.9	2524.0	2516.1
10°	2277.2	2276.4	2275.5	2291.3	2307.2	2354.4	2401.5	2425.7	2450.0	2471.6	2493.2
12.5°	1924.7	1926.1	1927.4	1979.4	2031.4	2075.9	2120.4	2182.1	2243.8	2310.3	2376.8
15°	1537.8	1559.4	1581.0	1627.3	1673.6	1740.5	1807.5	1890.4	1973.2	2078.5	2183.8
17.5°	1262.9	1272.1	1281.4	1325.9	1370.4	1433.9	1497.3	1591.2	1685.0	1820.7	1956.5
20°	1040.8	1049.2	1057.5	1089.7	1121.9	1182.7	1243.5	1332.9	1422.4	1556.8	1691.2
22.5°	868.9	885.3	901.6	923.1	944.7	988.8	1032.9	1124.1	1215.3	1337.8	1460.3
25°	765.0	772.4	779.9	798.4	817.0	859.3	901.6	961.9	1022.3	1144.4	1266.4
27.5°	694.5	696.7	698.9	712.5	726.2	753.5	780.8	836.8	892.7	993.2	1093.7
30°	636.3	640.3	644.2	654.8	665.4	685.2	705.0	744.7	784.3	874.2	964.1
32.5°	591.3	593.5	595.7	604.6	613.4	627.9	642.5	673.7	705.0	773.8	842.5
35°	552.6	553.0	553.4	560.1	566.7	580.8	594.9	620.9	646.9	697.5	748.2
37.5°	508.5	511.6	514.7	519.5	524.4	536.7	549.0	570.2	591.3	633.2	675.1
40°	471.5	474.1	476.8	482.5	488.2	497.9	507.6	527.0	546.4	582.5	618.7
42.5°	434.5	436.2	438.0	443.7	449.5	461.4	473.3	488.7	504.1	534.1	564.0
45°	393.1	397.5	401.9	408.0	414.2	424.3	434.5	450.3	466.2	491.8	517.3
47.5°	358.7	360.9	363.1	368.4	373.7	386.0	398.3	412.4	426.5	450.3	474.1
50°	324.3	325.2	326.1	330.9	335.8	346.8	357.8	374.1	390.4	412.4	434.5
52.5°	291.7	293.9	296.1	301.0	305.8	313.3	320.8	337.5	354.3	375.9	397.5
55°	261.7	263.1	264.4	267.9	271.4	280.2	289.1	303.6	318.1	338.0	357.8
57.5°	233.5	235.3	237.1	239.7	242.4	250.3	258.2	271.0	283.8	303.6	323.4
60°	204.5	206.7	208.9	211.9	215.0	221.2	227.4	238.8	250.3	267.9	285.5
62.5°	183.3	183.7	184.2	186.8	189.5	193.9	198.3	207.5	216.8	234.4	252.0
65°	159.5	160.8	162.2	163.5	164.8	168.3	171.9	179.8	187.7	200.9	214.2
67.5°	134.8	136.2	137.5	139.7	141.9	145.0	148.1	153.3	158.6	171.0	183.3
70°	104.9	104.9	104.9	108.4	111.9	117.2	122.5	126.5	130.4	140.6	150.7
72.5°	85.5	85.9	86.4	86.8	87.2	90.3	93.4	100.0	106.6	112.8	119.0
75°	69.6	70.1	70.5	70.9	71.4	72.3	73.1	75.3	77.6	84.6	91.7
77.5°	55.5	56.0	56.4	56.8	57.3	58.2	59.0	59.9	60.8	63.5	66.1
80°	42.3	42.7	43.2	43.6	44.1	44.5	44.9	45.8	46.7	48.0	49.4
82.5°	30.8	30.8	30.8	30.8	30.8	31.7	32.6	32.6	32.6	33.5	34.4
85°	19.4	19.4	19.4	19.8	20.3	20.3	20.3	20.7	21.2	21.2	21.2
87.5°	8.8	8.4	7.9	8.4	8.8	8.8	8.8	9.3	9.7	9.7	9.7
90°	14.7	14.5	14.3	14.1	13.9	13.5	13.1	12.7	12.2	11.8	10.4
92.5°	16.7	16.6	16.5	16.4	16.3	15.8	15.1	14.3	13.5	12.8	11.8
95°	18.7	18.7	18.7	18.7	18.7	18.3	17.5	16.8	16.0	15.2	14.0
97.5°	20.1	20.0	19.9	19.8	19.7	19.2	18.3	17.5	16.6	15.7	21.3
100°	20.6	20.5	20.4	20.3	20.2	19.7	18.8	18.0	17.1	16.2	33.2
102.5°	21.1	20.9	20.7	20.5	20.2	21.9	25.5	29.1	32.7	36.3	55.3
105°	21.6	21.4	21.2	21.0	20.7	30.3	49.6	68.9	88.2	107.5	117.4
107.5°	51.1	65.4	79.7	94.0	108.3	123.8	140.6	157.4	174.2	191.0	189.4
110°	135.0	150.7	166.3	181.9	197.5	207.1	210.7	214.3	217.9	221.5	220.3



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	255.9	256.1	256.3	256.5	256.7	256.3	255.4	254.4	253.4	252.4	251.2
115°	288.8	288.3	287.9	287.4	287.0	286.2	285.2	284.1	283.0	281.9	280.9
117.5°	315.3	315.2	315.1	314.9	314.8	314.3	313.5	312.6	311.7	310.9	310.3
120°	342.8	342.8	342.8	342.8	342.8	342.3	341.5	340.6	339.7	338.8	338.5
122.5°	369.8	369.7	369.6	369.5	369.3	369.0	368.5	367.9	367.4	366.8	366.4
125°	394.8	394.6	394.4	394.2	394.0	393.7	393.5	393.3	393.1	392.9	392.4
127.5°	419.4	419.6	419.8	420.0	420.3	420.2	419.9	419.5	419.2	418.9	418.3
130°	442.9	443.2	443.4	443.6	443.8	443.7	443.3	442.8	442.4	442.0	441.5
132.5°	464.6	464.9	465.2	465.5	465.9	465.8	465.4	464.9	464.5	464.1	463.7
135°	486.7	487.0	487.3	487.6	488.0	488.0	487.6	487.3	487.0	486.7	486.2
137.5°	507.8	508.0	508.2	508.4	508.6	508.5	507.9	507.4	506.8	506.3	506.1
140°	526.4	526.7	526.9	527.1	527.3	527.2	526.8	526.3	525.9	525.5	525.1
142.5°	543.6	543.9	544.3	544.6	544.9	544.9	544.6	544.3	543.9	543.6	543.3
145°	561.3	561.3	561.3	561.3	561.3	561.2	561.0	560.8	560.5	560.3	560.1
147.5°	574.1	574.6	575.2	575.7	576.2	576.4	576.2	576.0	575.8	575.5	575.3
150°	588.8	589.1	589.5	589.8	590.1	590.2	589.9	589.7	589.5	589.3	589.1
152.5°	600.6	601.1	601.7	602.2	602.8	602.8	602.4	601.9	601.5	601.1	601.0
155°	611.4	612.0	612.7	613.4	614.0	614.1	613.5	613.0	612.4	611.9	611.8
157.5°	620.7	621.6	622.5	623.3	624.2	624.3	623.7	623.0	622.4	621.7	621.8
160°	629.6	630.3	631.1	631.8	632.6	632.7	632.0	631.4	630.7	630.0	630.2
162.5°	637.9	638.6	639.2	639.9	640.5	640.5	639.7	638.9	638.2	637.4	637.5
165°	644.3	645.1	645.8	646.6	647.3	647.3	646.4	645.5	644.7	643.8	643.9
167.5°	649.2	650.1	650.9	651.8	652.7	652.7	651.8	650.9	650.1	649.2	649.2
170°	653.6	654.5	655.4	656.2	657.1	657.1	656.2	655.4	654.5	653.6	653.6
172.5°	656.1	657.1	658.0	659.0	660.0	660.1	659.2	658.3	657.4	656.6	656.5
175°	658.5	659.4	660.3	661.2	662.0	662.1	661.3	660.6	659.8	659.0	658.9
177.5°	659.0	660.1	661.2	662.3	663.4	663.5	662.6	661.8	660.9	660.0	659.9
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5
2.5°	2282.1	2279.9	2258.7	2237.6	2216.9	2196.2	2180.7	2165.3	2139.3	2113.3	2097.0
5°	2423.5	2406.8	2373.3	2339.8	2289.6	2239.3	2197.0	2154.7	2101.0	2047.2	2002.3
7.5°	2502.4	2488.8	2448.2	2407.7	2341.1	2274.6	2208.5	2142.4	2063.1	1983.8	1915.9
10°	2504.6	2516.1	2482.6	2449.1	2374.2	2299.3	2209.4	2119.5	2012.9	1906.2	1818.5
12.5°	2426.2	2475.5	2468.5	2461.4	2385.2	2309.0	2199.7	2090.4	1959.5	1828.7	1718.9
15°	2279.4	2375.1	2403.3	2431.5	2368.5	2305.4	2181.2	2056.9	1903.1	1749.4	1623.3
17.5°	2090.4	2224.4	2298.8	2373.3	2327.5	2281.7	2145.5	2009.3	1836.2	1663.0	1525.9
20°	1866.6	2041.9	2158.7	2275.5	2258.7	2242.0	2101.4	1960.9	1774.0	1587.2	1438.7
22.5°	1645.4	1830.4	1991.7	2153.0	2170.2	2187.4	2045.5	1903.6	1699.1	1494.7	1343.5
25°	1454.6	1642.7	1834.8	2027.0	2065.7	2104.5	1969.7	1834.8	1622.9	1410.9	1260.7
27.5°	1272.6	1451.5	1663.0	1874.5	1945.0	2015.5	1892.1	1768.7	1548.0	1327.2	1177.4
30°	1124.1	1284.0	1499.9	1715.9	1814.1	1912.4	1799.1	1685.9	1466.9	1247.9	1101.2
32.5°	985.7	1128.9	1345.7	1562.5	1676.6	1790.8	1693.0	1595.1	1384.5	1173.9	1028.9
35°	876.4	1004.7	1206.9	1409.2	1537.0	1664.7	1584.6	1504.4	1298.6	1092.8	955.8
37.5°	782.6	890.1	1080.0	1269.9	1405.7	1541.4	1474.4	1407.4	1214.0	1020.5	891.0
40°	705.0	791.4	968.1	1144.8	1277.9	1410.9	1353.7	1296.4	1123.2	950.0	828.8
42.5°	638.5	713.0	871.6	1030.2	1152.3	1274.3	1236.4	1198.5	1041.7	884.8	772.4
45°	579.9	642.5	782.1	921.8	1034.2	1146.6	1116.6	1086.6	951.3	816.1	713.0
47.5°	527.9	581.6	706.4	831.1	932.0	1032.9	1005.1	977.3	865.4	753.5	659.6
50°	480.3	526.1	630.1	734.1	824.9	915.7	892.7	869.8	777.3	684.8	603.7
52.5°	435.4	473.3	566.7	660.1	733.2	806.4	788.8	771.1	699.7	628.4	554.8
55°	392.6	427.4	506.3	585.2	647.7	710.3	692.7	675.1	619.5	564.0	499.2
57.5°	353.8	384.2	448.1	512.0	561.8	611.6	603.2	594.9	548.6	502.3	449.0
60°	312.9	340.2	395.3	450.3	490.4	530.5	520.8	511.1	478.1	445.0	399.2
62.5°	276.3	300.5	344.6	388.6	421.3	453.9	446.8	439.8	414.6	389.5	351.6
65°	237.9	261.7	297.4	333.1	358.7	384.2	378.1	371.9	353.0	334.0	303.6
67.5°	203.1	223.0	253.8	284.7	301.8	319.0	315.5	312.0	297.4	282.9	259.1
70°	167.9	185.1	210.6	236.2	248.1	260.0	261.3	262.6	249.4	236.2	218.6
72.5°	132.6	146.3	170.1	193.9	203.1	212.4	211.9	211.5	203.6	195.6	179.8
75°	101.8	111.9	130.4	148.9	156.9	164.8	166.6	168.3	160.8	153.3	144.5
77.5°	73.1	80.2	94.3	108.4	117.2	126.0	126.9	127.8	124.3	120.7	112.4
80°	51.6	53.8	62.6	71.4	80.6	89.9	91.2	92.5	89.0	85.5	80.2
82.5°	35.7	37.0	40.1	43.2	50.7	58.2	59.9	61.7	59.9	58.2	52.4
85°	21.6	22.0	23.4	24.7	28.2	31.7	33.5	35.3	34.4	33.5	30.4
87.5°	9.7	9.7	10.1	10.6	11.5	12.3	14.5	16.7	15.4	14.1	12.8
90°	8.9	7.5	6.1	4.9	3.8	2.7	1.6	0.5	1.6	2.7	3.8
92.5°	10.8	9.8	8.8	8.7	9.3	10.0	10.6	11.3	10.6	10.0	9.3
95°	12.8	11.6	10.4	12.1	16.5	21.0	25.5	30.0	25.5	21.0	16.5
97.5°	26.8	32.4	38.0	42.3	45.3	48.4	51.5	54.5	51.5	48.4	45.3
100°	50.3	67.3	84.3	91.7	89.5	87.4	85.2	83.0	85.2	87.4	89.5
102.5°	74.3	93.3	112.3	121.1	119.7	118.2	116.8	115.4	116.8	118.2	119.7
105°	127.2	137.0	146.8	151.1	149.9	148.7	147.5	146.3	147.5	148.7	149.9
107.5°	187.8	186.1	184.5	183.2	182.2	181.2	180.2	179.2	180.2	181.2	182.2
110°	219.1	217.9	216.7	215.6	214.8	213.9	213.0	212.1	213.0	213.9	214.8





TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	250.0	248.8	247.6	246.6	245.9	245.1	244.3	243.6	244.3	245.1	245.9
115°	279.9	278.9	277.9	277.1	276.5	275.8	275.2	274.5	275.2	275.8	276.5
117.5°	309.8	309.2	308.7	308.0	307.2	306.5	305.7	305.0	305.7	306.5	307.2
120°	338.2	337.9	337.5	336.9	335.9	334.9	333.9	332.9	333.9	334.9	335.9
122.5°	366.0	365.5	365.1	364.5	363.7	363.0	362.2	361.4	362.2	363.0	363.7
125°	392.0	391.6	391.1	390.5	389.6	388.7	387.8	387.0	387.8	388.7	389.6
127.5°	417.8	417.3	416.7	416.0	415.1	414.2	413.4	412.5	413.4	414.2	415.1
130°	441.1	440.7	440.2	439.6	438.7	437.8	436.9	436.1	436.9	437.8	438.7
132.5°	463.4	463.1	462.8	462.2	461.3	460.4	459.5	458.7	459.5	460.4	461.3
135°	485.8	485.3	484.9	484.4	483.7	483.1	482.4	481.7	482.4	483.1	483.7
137.5°	505.9	505.6	505.4	504.9	504.0	503.1	502.3	501.4	502.3	503.1	504.0
140°	524.8	524.5	524.1	523.6	523.0	522.3	521.7	521.0	521.7	522.3	523.0
142.5°	543.0	542.6	542.3	541.8	541.2	540.5	539.9	539.2	539.9	540.5	541.2
145°	559.9	559.7	559.4	559.0	558.2	557.4	556.7	555.9	556.7	557.4	558.2
147.5°	575.1	574.9	574.7	574.3	573.7	573.2	572.6	572.1	572.6	573.2	573.7
150°	588.9	588.6	588.4	588.1	587.8	587.5	587.2	586.8	587.2	587.5	587.8
152.5°	600.9	600.7	600.6	600.5	600.4	600.3	600.2	600.1	600.2	600.3	600.4
155°	611.7	611.6	611.4	611.5	611.7	611.9	612.2	612.4	612.2	611.9	611.7
157.5°	621.9	622.0	622.1	622.2	622.2	622.2	622.2	622.2	622.2	622.2	622.2
160°	630.3	630.4	630.5	630.6	630.7	630.8	630.9	631.0	630.9	630.8	630.7
162.5°	637.6	637.7	637.9	638.1	638.4	638.7	639.1	639.4	639.1	638.7	638.4
165°	644.0	644.1	644.2	644.5	644.8	645.1	645.4	645.8	645.4	645.1	644.8
167.5°	649.2	649.2	649.2	649.4	649.9	650.3	650.7	651.2	650.7	650.3	649.9
170°	653.6	653.6	653.6	653.8	654.3	654.7	655.1	655.6	655.1	654.7	654.3
172.5°	656.3	656.2	656.1	656.3	656.9	657.4	658.0	658.5	658.0	657.4	656.9
175°	658.8	658.7	658.6	658.8	659.3	659.9	660.4	661.0	660.4	659.9	659.3
177.5°	659.8	659.7	659.6	659.8	660.3	660.9	661.4	662.0	661.4	660.9	660.3
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5	2149.5
2.5°	2080.7	2055.6	2030.5	2012.4	1994.4	1971.9	1949.4	1948.5	1947.6	1930.9	1914.2
5°	1957.3	1913.7	1870.1	1827.3	1784.6	1741.9	1699.1	1689.4	1679.7	1665.2	1650.6
7.5°	1848.1	1778.4	1708.8	1654.2	1599.5	1556.8	1514.0	1485.0	1455.9	1433.4	1410.9
10°	1730.8	1644.5	1558.1	1492.0	1425.9	1379.7	1333.4	1299.9	1266.4	1250.5	1234.7
12.5°	1609.2	1515.4	1421.5	1356.7	1292.0	1236.4	1180.9	1150.5	1120.1	1098.1	1076.1
15°	1497.3	1396.4	1295.5	1226.8	1158.0	1106.0	1054.0	1023.6	993.2	971.2	949.1
17.5°	1388.9	1287.1	1185.3	1115.7	1046.1	998.9	951.8	922.3	892.7	879.1	865.4
20°	1290.2	1187.5	1084.9	1019.2	953.6	907.3	861.0	845.2	829.3	816.5	803.7
22.5°	1192.4	1093.7	995.0	932.0	868.9	835.5	802.0	789.2	776.4	766.7	757.0
25°	1110.4	1012.2	913.9	858.8	803.7	777.7	751.7	743.4	735.0	725.3	715.6
27.5°	1027.6	934.2	840.7	796.7	752.6	731.5	710.3	699.7	689.2	681.2	673.3
30°	954.4	868.1	781.7	745.1	708.6	690.0	671.5	660.1	648.6	641.1	633.6
32.5°	883.9	807.3	730.6	699.3	668.0	649.9	631.9	620.9	609.9	601.0	592.2
35°	818.7	752.2	685.6	657.0	628.4	610.3	592.2	581.2	570.2	561.4	552.6
37.5°	761.4	701.1	640.7	613.8	586.9	571.1	555.2	543.8	532.3	523.0	513.8
40°	707.7	654.4	601.0	575.0	549.0	531.9	514.7	504.5	494.4	486.0	477.7
42.5°	660.1	611.2	562.3	536.7	511.1	494.8	478.5	466.6	454.7	449.9	445.0
45°	609.9	566.7	523.5	498.8	474.1	456.9	439.8	429.6	419.5	415.1	410.7
47.5°	565.8	525.7	485.6	461.4	437.1	421.7	406.3	398.3	390.4	384.2	378.1
50°	522.6	483.8	445.0	421.7	398.3	385.1	371.9	362.2	352.5	348.1	343.7
52.5°	481.2	445.9	410.7	386.9	363.1	350.3	337.5	329.2	320.8	311.5	302.3
55°	434.5	403.6	372.8	351.6	330.5	317.3	304.0	294.3	284.7	275.0	265.3
57.5°	395.7	365.3	334.9	315.9	297.0	284.2	271.4	260.9	250.3	242.4	234.4
60°	353.4	327.0	300.5	282.0	263.5	251.2	238.8	228.7	218.6	214.6	210.6
62.5°	313.7	289.1	264.4	248.1	231.8	219.9	208.0	201.4	194.8	192.1	189.5
65°	273.2	252.0	230.9	215.9	200.9	190.8	180.7	177.6	174.5	172.3	170.1
67.5°	235.3	217.2	199.2	186.0	172.7	165.7	158.6	155.1	151.6	148.9	146.3
70°	200.9	185.1	169.2	157.8	146.3	139.7	133.1	130.0	126.9	122.1	117.2
72.5°	163.9	151.6	139.2	130.4	121.6	115.9	110.2	104.0	97.8	93.4	89.0
75°	135.7	123.4	111.0	102.7	94.3	87.7	81.1	78.9	76.7	75.3	74.0
77.5°	104.0	93.4	82.8	76.2	69.6	66.5	63.5	62.1	60.8	60.4	59.9
80°	74.9	66.1	57.3	53.8	50.2	49.4	48.5	47.6	46.7	46.3	45.8
82.5°	46.7	42.3	37.9	37.0	36.1	35.7	35.3	34.8	34.4	33.9	33.5
85°	27.3	25.6	23.8	23.4	22.9	22.5	22.0	22.0	22.0	22.0	22.0
87.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.0	10.6
90°	4.9	6.1	7.5	8.9	10.4	11.8	12.2	12.7	13.1	13.5	13.9
92.5°	8.7	8.8	9.8	10.8	11.8	12.8	13.5	14.3	15.1	15.8	16.3
95°	12.1	10.4	11.6	12.8	14.0	15.2	16.0	16.8	17.5	18.3	18.7
97.5°	42.3	38.0	32.4	26.8	21.3	15.7	16.6	17.5	18.3	19.2	19.7
100°	91.7	84.3	67.3	50.3	33.2	16.2	17.1	18.0	18.8	19.7	20.2
102.5°	121.1	112.3	93.3	74.3	55.3	36.3	32.7	29.1	25.5	21.9	20.2
105°	151.1	146.8	137.0	127.2	117.4	107.5	88.2	68.9	49.6	30.3	20.7
107.5°	183.2	184.5	186.1	187.8	189.4	191.0	174.2	157.4	140.6	123.8	108.3
110°	215.6	216.7	217.9	219.1	220.3	221.5	217.9	214.3	210.7	207.1	197.5



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	246.6	247.6	248.8	250.0	251.2	252.4	253.4	254.4	255.4	256.3	256.7
115°	277.1	277.9	278.9	279.9	280.9	281.9	283.0	284.1	285.2	286.2	287.0
117.5°	308.0	308.7	309.2	309.8	310.3	310.9	311.7	312.6	313.5	314.3	314.8
120°	336.9	337.5	337.9	338.2	338.5	338.8	339.7	340.6	341.5	342.3	342.8
122.5°	364.5	365.1	365.5	366.0	366.4	366.8	367.4	367.9	368.5	369.0	369.3
125°	390.5	391.1	391.6	392.0	392.4	392.9	393.1	393.3	393.5	393.7	394.0
127.5°	416.0	416.7	417.3	417.8	418.3	418.9	419.2	419.5	419.9	420.2	420.3
130°	439.6	440.2	440.7	441.1	441.5	442.0	442.4	442.8	443.3	443.7	443.8
132.5°	462.2	462.8	463.1	463.4	463.7	464.1	464.5	464.9	465.4	465.8	465.9
135°	484.4	484.9	485.3	485.8	486.2	486.7	487.0	487.3	487.6	488.0	488.0
137.5°	504.9	505.4	505.6	505.9	506.1	506.3	506.8	507.4	507.9	508.5	508.6
140°	523.6	524.1	524.5	524.8	525.1	525.5	525.9	526.3	526.8	527.2	527.3
142.5°	541.8	542.3	542.6	543.0	543.3	543.6	543.9	544.3	544.6	544.9	544.9
145°	559.0	559.4	559.7	559.9	560.1	560.3	560.5	560.8	561.0	561.2	561.3
147.5°	574.3	574.7	574.9	575.1	575.3	575.5	575.8	576.0	576.2	576.4	576.2
150°	588.1	588.4	588.6	588.9	589.1	589.3	589.5	589.7	589.9	590.2	590.1
152.5°	600.5	600.6	600.7	600.9	601.0	601.1	601.5	601.9	602.4	602.8	602.8
155°	611.5	611.4	611.6	611.7	611.8	611.9	612.4	613.0	613.5	614.1	614.0
157.5°	622.2	622.1	622.0	621.9	621.8	621.7	622.4	623.0	623.7	624.3	624.2
160°	630.6	630.5	630.4	630.3	630.2	630.0	630.7	631.4	632.0	632.7	632.6
162.5°	638.1	637.9	637.7	637.6	637.5	637.4	638.2	638.9	639.7	640.5	640.5
165°	644.5	644.2	644.1	644.0	643.9	643.8	644.7	645.5	646.4	647.3	647.3
167.5°	649.4	649.2	649.2	649.2	649.2	649.2	650.1	650.9	651.8	652.7	652.7
170°	653.8	653.6	653.6	653.6	653.6	653.6	654.5	655.4	656.2	657.1	657.1
172.5°	656.3	656.1	656.2	656.3	656.5	656.6	657.4	658.3	659.2	660.1	660.0
175°	658.8	658.6	658.7	658.8	658.9	659.0	659.8	660.6	661.3	662.1	662.0
177.5°	659.8	659.6	659.7	659.8	659.9	660.0	660.9	661.8	662.6	663.5	663.4
180°	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0	661.0

TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2149.5	2149.5	2149.5	2149.5
2.5°	1909.7	1905.3	1903.6	1901.8
5°	1637.0	1623.3	1620.2	1617.2
7.5°	1405.2	1399.5	1380.5	1361.6
10°	1217.1	1199.4	1191.5	1183.6
12.5°	1059.7	1043.4	1040.8	1038.2
15°	937.7	926.2	922.3	918.3
17.5°	857.5	849.6	844.7	839.9
20°	798.0	792.3	788.8	785.2
22.5°	752.6	748.2	745.6	742.9
25°	709.0	702.4	700.2	698.0
27.5°	667.6	661.8	659.6	657.4
30°	628.8	624.0	620.9	617.8
32.5°	586.5	580.8	579.0	577.2
35°	549.0	545.5	543.8	542.0
37.5°	509.4	505.0	502.3	499.7
40°	475.5	473.3	471.9	470.6
42.5°	441.1	437.1	436.7	436.2
45°	406.7	402.7	401.9	401.0
47.5°	374.5	371.0	370.6	370.1
50°	338.9	334.0	330.5	327.0
52.5°	297.9	293.5	290.4	287.3
55°	260.4	255.6	252.9	250.3
57.5°	232.2	230.0	228.7	227.4
60°	209.3	208.0	207.1	206.2
62.5°	188.2	186.8	186.8	186.8
65°	168.8	167.4	166.1	164.8
67.5°	143.6	141.0	140.6	140.1
70°	113.2	109.3	108.8	108.4
72.5°	88.6	88.1	87.2	86.4
75°	73.1	72.3	72.3	72.3
77.5°	59.0	58.2	58.2	58.2
80°	45.4	44.9	45.4	45.8
82.5°	33.5	33.5	33.0	32.6
85°	21.6	21.2	21.2	21.2
87.5°	10.6	10.6	10.6	10.6
90°	14.1	14.3	14.5	14.7
92.5°	16.4	16.5	16.6	16.7
95°	18.7	18.7	18.7	18.7
97.5°	19.8	19.9	20.0	20.1
100°	20.3	20.4	20.5	20.6
102.5°	20.5	20.7	20.9	21.1
105°	21.0	21.2	21.4	21.6
107.5°	94.0	79.7	65.4	51.1
110°	181.9	166.3	150.7	135.0



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	256.5	256.3	256.1	255.9
115°	287.4	287.9	288.3	288.8
117.5°	314.9	315.1	315.2	315.3
120°	342.8	342.8	342.8	342.8
122.5°	369.5	369.6	369.7	369.8
125°	394.2	394.4	394.6	394.8
127.5°	420.0	419.8	419.6	419.4
130°	443.6	443.4	443.2	442.9
132.5°	465.5	465.2	464.9	464.6
135°	487.6	487.3	487.0	486.7
137.5°	508.4	508.2	508.0	507.8
140°	527.1	526.9	526.7	526.4
142.5°	544.6	544.3	543.9	543.6
145°	561.3	561.3	561.3	561.3
147.5°	575.7	575.2	574.6	574.1
150°	589.8	589.5	589.1	588.8
152.5°	602.2	601.7	601.1	600.6
155°	613.4	612.7	612.0	611.4
157.5°	623.3	622.5	621.6	620.7
160°	631.8	631.1	630.3	629.6
162.5°	639.9	639.2	638.6	637.9
165°	646.6	645.8	645.1	644.3
167.5°	651.8	650.9	650.1	649.2
170°	656.2	655.4	654.5	653.6
172.5°	659.0	658.0	657.1	656.1
175°	661.2	660.3	659.4	658.5
177.5°	662.3	661.2	660.1	659.0
180°	661.0	661.0	661.0	661.0



TEST NUMBER: P832404

CATALOG NUMBER: S123RDIP-S775D585U935-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.43	13.31	13.33	14.21	15.36	17.10	17.97	17.99	18.88	20.03
	3H	13.66	14.44	14.56	15.35	16.53	18.60	19.38	19.50	20.30	21.47
	4H	14.04	14.78	14.96	15.70	16.88	19.09	19.83	20.01	20.75	21.93
	6H	14.33	15.01	15.26	15.93	17.13	19.41	20.09	20.34	21.01	22.21
	8H	14.41	15.06	15.35	16.00	17.20	19.49	20.13	20.42	21.07	22.27
	12H	14.47	15.08	15.41	16.02	17.24	19.52	20.14	20.46	21.07	22.29
4H	2H	13.16	13.90	14.09	14.82	16.00	17.10	17.84	18.02	18.76	19.94
	3H	14.54	15.15	15.47	16.10	17.30	18.76	19.37	19.69	20.32	21.52
	4H	14.99	15.55	15.94	16.50	17.72	19.37	19.93	20.31	20.87	22.10
	6H	15.36	15.84	16.32	16.81	18.03	19.81	20.29	20.77	21.26	22.48
	8H	15.49	15.94	16.45	16.90	18.13	19.94	20.39	20.90	21.35	22.59
	12H	15.57	15.97	16.54	16.95	18.19	20.00	20.41	20.98	21.39	22.63
8H	4H	15.31	15.76	16.27	16.72	17.96	19.34	19.79	20.30	20.75	21.98
	6H	15.77	16.14	16.76	17.15	18.38	19.84	20.21	20.82	21.21	22.44
	8H	15.97	16.29	16.96	17.29	18.54	20.02	20.35	21.02	21.34	22.59
	12H	16.11	16.40	17.10	17.38	18.68	20.14	20.43	21.14	21.41	22.71
12H	4H	15.32	15.73	16.30	16.70	17.95	19.29	19.69	20.27	20.67	21.91
	6H	15.83	16.16	16.83	17.15	18.40	19.81	20.14	20.80	21.13	22.38
	8H	16.05	16.34	17.05	17.33	18.63	20.01	20.29	21.00	21.28	22.58