

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332019

Luminaire Tested: **S123DIP-S1000D805U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332019
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6999.7 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	62	56	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15118	15118	15118	15118
5°	18029	15183	13456	15183
10°	22566	15106	12153	15106
15°	27679	14985	11314	14985
20°	32972	14795	10772	14795
25°	35011	14563	10652	14563
30°	30009	14395	10708	14395
35°	20871	14155	10820	14155
40°	15719	13874	10786	13874
45°	13052	13457	10648	13457
50°	11692	12603	10551	12603
55°	10931	11684	10421	11684
60°	10254	10723	10314	10723
65°	9638	9775	9984	9775
70°	9039	8696	9508	8696
75°	8093	7615	8717	7615
80°	7085	6242	7507	6242
85°	5545	4533	5039	4533



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	2.0
10°-20°	443.6	6.3
20°-30°	744.6	10.6
30°-40°	843.1	12.0
40°-50°	756.1	10.8
50°-60°	610.1	8.7
60°-70°	425.2	6.1
70°-80°	223.5	3.2
80°-90°	57.6	0.8
90°-100°	64.8	0.9
100°-110°	194.1	2.8
110°-120°	330.1	4.7
120°-130°	434.2	6.2
130°-140°	488.0	7.0
140°-150°	479.7	6.9
150°-160°	403.8	5.8
160°-170°	268.8	3.8
170°-180°	94.1	1.3
0°-30°	1326.6	19.0
0°-40°	2169.7	31.0
0°-60°	3535.9	50.5
0°-90°	4242.1	60.6
90°-120°	589.0	8.4
90°-150°	1990.8	28.4
90°-180°	2758.0	39.4
0°-180°	6999.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1404	1404	1404	1404	1404	
5°	1669	1405	1245	1405	1669	173
15°	2484	1345	1015	1345	2484	717
25°	2948	1226	897	1226	2948	1293
35°	1588	1077	823	1077	1588	1032
45°	857	884	700	884	857	678
55°	582	623	555	623	582	523
65°	378	384	392	384	378	377
75°	195	183	210	183	195	208
85°	45	37	41	37	45	54
90°	24	1	24	1	24	14
95°	61	46	61	46	61	63
105°	186	176	186	176	186	197
115°	333	332	333	332	333	330
125°	481	486	481	486	481	430
135°	630	631	630	631	630	484
145°	765	765	765	765	765	478
155°	875	876	875	876	875	403
165°	952	955	952	955	952	268
175°	989	993	989	993	989	94
180°	995	995	995	995	995	



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1490.5	1489.5	1486.7	1488.9	1484.6	1478.6	1478.0	1472.6	1456.8	1455.7	1451.4
5°	1668.6	1663.1	1662.4	1661.8	1652.2	1639.3	1614.8	1612.8	1580.1	1563.8	1544.0
7.5°	1899.1	1902.0	1892.0	1883.3	1854.2	1835.0	1808.7	1775.1	1735.0	1694.3	1667.2
10°	2064.6	2087.1	2059.2	2040.1	2022.4	1989.1	1950.3	1902.0	1853.7	1797.2	1754.3
12.5°	2242.1	2253.1	2247.5	2229.6	2202.1	2151.3	2082.6	2029.4	1984.9	1890.8	1852.8
15°	2483.8	2525.3	2498.8	2437.5	2438.9	2390.6	2300.7	2202.1	2149.7	2067.3	1955.1
17.5°	2741.3	2746.5	2735.2	2684.1	2650.1	2583.7	2500.8	2406.2	2300.1	2200.4	2081.4
20°	2878.5	2874.4	2850.6	2824.0	2765.5	2713.8	2623.3	2517.8	2381.7	2283.7	2153.8
22.5°	2954.7	2947.9	2936.6	2914.4	2865.7	2810.2	2728.9	2613.6	2484.1	2349.1	2198.9
25°	2947.9	2956.7	2958.1	2952.0	2935.0	2901.6	2837.6	2745.8	2616.5	2443.0	2286.5
27.5°	2681.1	2693.7	2730.0	2762.3	2798.3	2835.1	2830.2	2784.6	2688.9	2539.0	2347.7
30°	2414.4	2387.2	2454.5	2539.6	2597.4	2699.5	2756.7	2760.1	2706.3	2577.7	2391.2
32.5°	2044.2	2074.1	2103.9	2208.6	2335.0	2449.6	2563.4	2655.0	2665.5	2579.9	2416.8
35°	1588.3	1625.7	1680.1	1734.6	1870.7	1987.7	2187.8	2362.0	2500.8	2519.2	2419.1
37.5°	1279.9	1298.4	1332.8	1387.4	1476.4	1615.2	1770.0	1990.2	2191.3	2340.9	2347.4
40°	1118.7	1124.2	1163.0	1204.5	1276.6	1390.9	1530.4	1725.0	1965.9	2174.9	2262.0
42.5°	997.9	1009.8	1026.3	1066.2	1123.6	1209.6	1339.3	1500.2	1721.0	1961.4	2131.8
45°	857.4	871.0	881.2	907.8	948.6	1006.4	1097.0	1243.9	1412.0	1660.4	1889.7
47.5°	764.6	765.7	773.3	793.3	821.1	864.5	928.5	1022.9	1177.2	1378.7	1614.1
50°	698.2	709.1	711.8	727.4	749.2	781.2	834.3	914.6	1041.2	1218.1	1434.5
52.5°	651.4	654.6	662.3	673.6	692.6	717.5	763.5	826.4	925.7	1076.5	1275.5
55°	582.5	582.5	590.0	598.8	609.7	632.2	662.8	709.1	784.6	901.7	1066.3
57.5°	518.8	522.2	527.5	530.2	539.5	554.3	579.9	615.0	671.4	761.5	892.4
60°	476.3	482.5	481.8	487.2	495.4	507.0	528.7	557.3	607.7	679.8	790.1
62.5°	439.3	438.9	438.8	445.3	453.5	464.5	478.7	503.4	546.2	610.1	704.0
65°	378.4	377.0	381.8	385.8	388.6	396.7	407.6	429.4	458.0	505.6	578.4
67.5°	324.2	320.2	322.8	324.2	328.8	335.2	345.4	358.9	381.6	419.9	474.7
70°	287.2	283.8	283.1	284.4	288.5	293.3	300.8	313.7	334.8	365.4	405.6
72.5°	249.1	246.7	246.6	249.6	251.5	254.6	259.9	271.8	288.5	311.5	349.0
75°	194.6	194.6	194.6	195.3	197.3	200.1	204.1	210.3	223.2	239.5	264.7
77.5°	145.9	145.8	144.9	144.8	147.8	149.0	150.0	155.7	162.9	173.9	192.3
80°	114.3	110.9	112.3	114.3	115.7	116.4	118.4	119.8	125.9	132.0	144.9
82.5°	84.9	82.1	82.3	85.5	85.7	86.4	88.5	90.4	92.7	98.3	105.2
85°	44.9	44.9	45.6	45.6	46.3	45.6	47.6	48.3	48.3	51.7	55.8
87.5°	21.0	19.9	20.3	20.8	20.2	20.6	21.0	21.5	21.9	22.3	22.4
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	31.6	31.8	32.0	32.2	32.4	32.2	31.7	31.1	30.6	30.0	28.7
95°	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2	58.6	57.9	56.5
97.5°	93.8	93.9	94.0	94.0	94.1	93.7	92.9	92.1	91.3	90.5	89.5
100°	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0	115.5	114.9	114.1
102.5°	144.5	144.6	144.6	144.7	144.8	144.5	144.0	143.5	143.0	142.5	141.3
105°	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5	184.5	184.5	183.0
107.5°	229.4	229.6	229.8	230.0	230.2	230.1	229.5	228.9	228.4	227.8	227.2
110°	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6	257.9	257.2	256.9



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	290.1	290.1	290.2	290.3	290.3	290.0	289.1	288.3	287.5	286.6	286.6
115°	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1	333.4
117.5°	376.7	377.2	377.7	378.2	378.6	378.9	378.9	379.0	379.0	379.0	379.5
120°	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3	409.5	409.7	410.6
122.5°	436.7	437.2	437.7	438.2	438.7	439.2	439.6	440.1	440.5	441.0	441.4
125°	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7	486.4	487.1	487.4
127.5°	524.8	525.6	526.4	527.2	528.0	528.9	529.8	530.8	531.8	532.7	533.1
130°	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8	561.4	562.1	562.7
132.5°	583.6	584.5	585.4	586.4	587.3	588.2	589.0	589.9	590.7	591.5	591.9
135°	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5	634.2	634.9	635.0
137.5°	671.3	672.0	672.6	673.3	673.9	674.6	675.4	676.1	676.8	677.5	677.1
140°	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.7	726.6	727.6	728.5	729.5	730.0	730.2	730.4	730.5	730.7	730.4
145°	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0	769.2	769.3	768.8
147.5°	800.8	801.8	802.8	803.9	804.9	805.5	805.5	805.5	805.5	805.5	805.0
150°	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0	828.0	828.0	827.6
152.5°	845.2	846.1	847.0	847.9	848.8	849.1	848.8	848.5	848.3	848.0	847.8
155°	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6	877.9	877.2	877.1
157.5°	901.9	902.9	903.9	904.9	905.8	905.9	905.2	904.5	903.8	903.0	902.9
160°	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4	919.5	918.7	918.7
162.5°	932.6	933.7	934.8	935.9	937.0	937.2	936.3	935.4	934.5	933.7	933.5
165°	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4	953.3	952.3	952.3
167.5°	967.6	968.7	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6	967.5
170°	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7	975.7
172.5°	982.0	983.2	984.4	985.6	986.9	986.9	985.9	984.8	983.7	982.6	982.6
175°	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9	990.9	989.8	989.8
177.5°	992.8	993.8	994.7	995.7	996.7	996.7	995.9	995.1	994.2	993.4	993.4
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1448.1	1443.7	1439.4	1431.8	1425.2	1416.0	1413.2	1410.0	1400.2	1391.5	1384.9
5°	1536.5	1520.2	1496.4	1474.6	1456.9	1433.1	1419.5	1405.2	1384.8	1366.4	1351.5
7.5°	1629.1	1597.0	1560.0	1519.9	1482.7	1446.7	1417.7	1391.9	1363.3	1336.2	1315.1
10°	1702.6	1656.3	1604.6	1548.8	1501.2	1454.9	1416.1	1382.1	1345.3	1313.3	1286.8
12.5°	1786.4	1717.8	1646.5	1578.7	1522.4	1458.2	1411.2	1367.9	1326.3	1287.8	1258.0
15°	1885.6	1798.5	1714.2	1620.9	1535.2	1454.9	1399.1	1344.7	1296.3	1256.9	1218.8
17.5°	1976.0	1877.3	1766.1	1652.8	1549.3	1454.1	1376.0	1314.4	1254.0	1205.7	1167.7
20°	2027.2	1914.9	1789.0	1671.3	1557.0	1450.8	1365.1	1291.6	1226.2	1175.2	1132.3
22.5°	2071.3	1939.9	1809.7	1683.8	1556.4	1442.1	1344.9	1269.3	1198.5	1148.5	1102.9
25°	2117.0	1959.8	1829.2	1681.5	1539.3	1420.9	1312.0	1226.2	1155.5	1097.0	1050.0
27.5°	2156.2	1958.5	1803.4	1644.6	1512.3	1393.6	1277.4	1185.4	1110.3	1046.7	999.1
30°	2182.3	1961.2	1776.8	1619.6	1486.2	1363.7	1250.7	1158.2	1079.3	1014.6	969.7
32.5°	2198.7	1959.5	1752.3	1584.7	1444.8	1336.5	1221.9	1126.1	1045.0	981.4	938.1
35°	2208.2	1947.6	1710.1	1512.7	1378.0	1272.5	1176.6	1077.2	992.2	933.0	884.0
37.5°	2189.1	1922.4	1661.1	1443.3	1295.8	1191.9	1111.2	1026.6	945.2	880.0	837.8
40°	2159.2	1906.1	1623.0	1394.3	1239.2	1139.1	1070.4	987.4	907.1	845.2	805.7
42.5°	2102.0	1872.8	1581.1	1339.9	1180.4	1080.3	1017.1	947.7	871.7	813.6	774.1
45°	1962.5	1800.6	1518.2	1258.2	1093.5	990.1	934.3	884.0	815.2	758.7	724.7
47.5°	1769.0	1691.8	1427.3	1172.1	1002.9	903.4	845.4	804.9	754.7	709.1	676.4
50°	1634.5	1602.6	1365.7	1113.3	942.5	845.2	789.4	752.6	716.6	671.0	641.0
52.5°	1479.4	1499.1	1293.9	1052.3	881.0	785.3	732.8	703.6	670.8	633.4	607.3
55°	1261.0	1332.4	1169.8	950.0	789.4	698.2	648.5	622.6	603.6	575.7	553.2
57.5°	1056.4	1147.3	1035.6	844.5	699.4	620.7	573.1	544.9	532.7	518.1	500.4
60°	935.0	1024.8	939.8	773.7	639.0	564.1	521.9	498.1	485.9	475.7	460.7
62.5°	826.7	917.6	846.1	701.9	579.6	510.2	473.5	450.2	440.7	435.4	422.6
65°	677.8	756.0	708.4	590.0	494.7	433.5	400.1	383.8	375.0	372.9	364.7
67.5°	551.6	611.2	576.5	489.4	414.4	361.5	333.2	319.3	312.5	311.8	305.7
70°	468.9	524.7	498.1	419.2	354.5	313.0	288.5	276.3	272.2	271.5	268.1
72.5°	404.6	443.5	422.4	356.6	306.6	268.9	251.0	238.2	233.5	234.5	232.2
75°	299.4	328.7	316.4	270.8	230.7	206.2	191.2	183.1	179.0	181.0	178.3
77.5°	215.4	234.0	222.9	191.4	166.6	148.9	137.9	132.8	129.2	129.0	127.8
80°	162.6	173.5	167.4	148.3	127.9	113.0	104.1	100.7	98.7	98.0	97.3
82.5°	115.8	125.1	117.9	104.8	90.9	81.9	76.9	72.4	70.9	71.3	70.6
85°	58.5	61.9	59.2	51.0	45.6	41.5	38.8	36.7	35.4	36.1	34.7
87.5°	23.0	23.1	21.0	18.4	17.0	15.0	14.7	13.2	12.5	12.8	12.6
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	27.5	26.2	24.9	23.6	22.5	21.3	20.1	18.9	20.1	21.3	22.5
95°	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1	47.3	48.6	49.8
97.5°	88.5	87.5	86.5	85.6	84.6	83.7	82.8	81.9	82.8	83.7	84.6
100°	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3	107.4	108.4	109.5
102.5°	140.2	139.0	137.9	137.0	136.4	135.7	135.1	134.5	135.1	135.7	136.4
105°	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9	176.3	176.6	177.0
107.5°	226.6	226.0	225.3	224.9	224.7	224.5	224.3	224.1	224.3	224.5	224.7
110°	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1	254.4	254.8	255.1



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	286.5	286.4	286.3	286.2	286.0	285.8	285.6	285.4	285.6	285.8	286.0
115°	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3	332.8	333.3	333.8
117.5°	379.9	380.4	380.8	380.9	380.5	380.2	379.9	379.5	379.9	380.2	380.5
120°	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9	409.9	411.0	412.0
122.5°	441.9	442.3	442.8	442.6	441.8	441.1	440.3	439.6	440.3	441.1	441.8
125°	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3	486.8	487.3	487.9
127.5°	533.5	533.9	534.3	533.9	532.8	531.7	530.6	529.5	530.6	531.7	532.8
130°	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2	559.6	561.0	562.4
132.5°	592.3	592.7	593.1	592.6	591.2	589.8	588.4	587.0	588.4	589.8	591.2
135°	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9	632.0	633.0	634.1
137.5°	676.6	676.2	675.7	675.1	674.2	673.3	672.5	671.6	672.5	673.3	674.2
140°	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7	700.6	701.5	702.4
142.5°	730.1	729.8	729.5	728.9	728.0	727.1	726.3	725.4	726.3	727.1	728.0
145°	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4	765.8	766.1	766.5
147.5°	804.5	804.0	803.5	803.0	802.3	801.7	801.1	800.5	801.1	801.7	802.3
150°	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8	825.2	825.5	825.9
152.5°	847.6	847.4	847.2	846.8	846.3	845.8	845.3	844.9	845.3	845.8	846.3
155°	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4	876.4	876.4	876.4
157.5°	902.8	902.6	902.5	902.5	902.7	902.9	903.1	903.3	903.1	902.9	902.7
160°	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2	919.9	919.5	919.2
162.5°	933.4	933.3	933.1	933.3	933.8	934.3	934.8	935.2	934.8	934.3	933.8
165°	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6	954.1	953.6	953.1
167.5°	967.3	967.2	967.1	967.3	968.0	968.7	969.4	970.1	969.4	968.7	968.0
170°	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9	978.2	977.5	976.8
172.5°	982.6	982.6	982.6	983.0	983.7	984.4	985.1	985.7	985.1	984.4	983.7
175°	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9	992.2	991.6	990.9
177.5°	993.4	993.4	993.4	993.7	994.2	994.8	995.4	995.9	995.4	994.8	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1381.1	1377.3	1371.9	1363.7	1357.2	1346.8	1346.8	1348.5	1348.5	1347.9	1346.8
5°	1339.2	1329.0	1316.8	1302.5	1287.5	1272.5	1269.8	1264.4	1260.3	1257.5	1254.1
7.5°	1295.0	1276.9	1259.0	1239.0	1220.8	1205.7	1195.2	1186.5	1180.9	1174.9	1170.6
10°	1265.0	1242.6	1221.5	1200.4	1177.2	1158.9	1147.3	1139.1	1133.0	1127.6	1124.9
12.5°	1229.6	1203.9	1180.7	1160.6	1135.3	1116.4	1105.4	1101.6	1094.4	1082.9	1076.9
15°	1177.9	1154.1	1126.2	1095.6	1083.3	1060.2	1047.3	1041.2	1037.1	1028.2	1025.5
17.5°	1133.7	1102.5	1071.2	1048.4	1025.6	1006.9	999.6	992.0	986.6	979.4	977.2
20°	1098.3	1070.4	1041.8	1017.3	993.5	973.1	967.0	961.5	956.1	952.7	950.0
22.5°	1062.4	1034.5	1010.8	987.9	962.5	949.1	942.5	936.5	932.7	930.4	927.6
25°	1011.9	987.4	960.9	940.4	920.0	911.2	907.1	903.7	901.0	897.6	896.9
27.5°	966.7	940.0	918.5	899.5	884.8	877.4	873.5	871.8	872.4	873.6	874.4
30°	933.0	908.5	890.8	874.4	860.8	854.0	853.3	853.3	856.1	856.7	858.1
32.5°	901.9	881.8	864.1	848.3	838.0	833.3	835.9	835.9	838.1	839.9	842.3
35°	856.7	839.0	825.4	811.8	803.0	805.0	806.4	807.7	811.1	815.2	818.0
37.5°	813.6	798.2	784.1	773.4	769.4	773.0	776.3	779.2	783.1	786.2	789.0
40°	782.6	771.0	757.4	747.9	749.2	751.3	754.0	757.4	760.8	762.8	765.6
42.5°	753.7	741.6	731.3	723.4	725.3	727.9	729.5	731.3	735.2	738.9	740.5
45°	709.8	700.2	690.7	685.9	687.3	688.7	690.0	692.1	695.5	698.2	698.9
47.5°	660.3	653.7	647.3	642.7	644.8	644.3	646.1	650.4	651.5	653.1	656.9
50°	628.8	622.6	615.2	613.8	613.8	613.8	614.5	619.9	619.9	622.6	625.4
52.5°	593.9	590.0	585.2	582.8	581.7	581.7	584.5	587.3	588.4	592.2	594.9
55°	542.4	538.3	534.2	532.1	530.8	532.1	537.6	538.9	542.4	544.4	546.4
57.5°	488.6	485.5	482.2	481.1	480.8	482.6	485.6	489.7	490.5	496.8	499.9
60°	453.2	448.4	445.7	445.7	444.4	450.5	449.1	455.9	457.3	461.4	466.1
62.5°	416.7	410.3	409.2	409.2	411.2	412.9	414.8	417.8	421.4	426.5	430.2
65°	357.9	354.5	359.3	358.6	357.3	361.3	361.3	364.7	368.8	373.6	381.1
67.5°	302.3	300.5	300.9	300.9	303.0	305.3	307.2	310.2	315.1	320.1	325.0
70°	264.7	266.8	263.4	266.1	268.1	268.8	270.2	274.2	279.7	283.1	288.5
72.5°	228.2	228.1	228.5	229.6	231.6	232.9	234.2	238.9	244.8	247.7	252.1
75°	175.6	174.9	176.9	176.9	180.3	181.7	183.1	185.1	190.5	194.6	198.0
77.5°	128.2	129.0	128.6	130.9	130.0	130.2	134.5	136.5	137.1	145.1	146.9
80°	96.6	98.0	98.7	99.4	100.0	98.7	103.4	105.5	105.5	110.2	113.6
82.5°	69.4	70.2	72.0	72.7	72.8	74.2	74.6	76.1	77.7	79.8	84.2
85°	34.7	36.7	37.4	36.7	37.4	36.1	38.1	38.8	39.5	39.5	39.5
87.5°	12.4	13.4	13.3	14.3	14.2	15.2	15.3	14.4	14.5	16.3	14.2
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	23.6	24.9	26.2	27.5	28.7	30.0	30.6	31.1	31.7	32.2	32.4
95°	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2	59.9	60.6	61.0
97.5°	85.6	86.5	87.5	88.5	89.5	90.5	91.3	92.1	92.9	93.7	94.1
100°	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0	116.5	117.0	117.5
102.5°	137.0	137.9	139.0	140.2	141.3	142.5	143.0	143.5	144.0	144.5	144.8
105°	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5	184.5	184.5	184.7
107.5°	224.9	225.3	226.0	226.6	227.2	227.8	228.4	228.9	229.5	230.1	230.2
110°	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6	259.3	260.0	260.2



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	286.2	286.3	286.4	286.5	286.6	286.6	287.5	288.3	289.1	290.0	290.3
115°	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4	333.6	333.8	333.8
117.5°	380.9	380.8	380.4	379.9	379.5	379.0	379.0	379.0	378.9	378.9	378.6
120°	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3	409.2	409.0	408.7
122.5°	442.6	442.8	442.3	441.9	441.4	441.0	440.5	440.1	439.6	439.2	438.7
125°	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7	485.0	484.3	483.6
127.5°	533.9	534.3	533.9	533.5	533.1	532.7	531.8	530.8	529.8	528.9	528.0
130°	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8	560.1	559.4	558.4
132.5°	592.6	593.1	592.7	592.3	591.9	591.5	590.7	589.9	589.0	588.2	587.3
135°	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5	632.8	632.1	631.6
137.5°	675.1	675.7	676.2	676.6	677.1	677.5	676.8	676.1	675.4	674.6	673.9
140°	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1	703.9	703.7	703.1
142.5°	728.9	729.5	729.8	730.1	730.4	730.7	730.5	730.4	730.2	730.0	729.5
145°	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0	768.8	768.6	768.2
147.5°	803.0	803.5	804.0	804.5	805.0	805.5	805.5	805.5	805.5	805.5	804.9
150°	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0	828.0	828.0	827.5
152.5°	846.8	847.2	847.4	847.6	847.8	848.0	848.3	848.5	848.8	849.1	848.8
155°	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6	879.3	880.0	879.7
157.5°	902.5	902.5	902.6	902.8	902.9	903.0	903.8	904.5	905.2	905.9	905.8
160°	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4	921.3	922.1	922.2
162.5°	933.3	933.1	933.3	933.4	933.5	933.7	934.5	935.4	936.3	937.2	937.0
165°	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4	955.4	956.5	956.4
167.5°	967.3	967.1	967.2	967.3	967.5	967.6	968.7	969.8	970.8	971.9	971.9
170°	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2	979.4	980.6	980.6
172.5°	983.0	982.6	982.6	982.6	982.6	982.6	983.7	984.8	985.9	986.9	986.9
175°	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9	992.9	994.0	993.9
177.5°	993.7	993.4	993.4	993.4	993.4	993.4	994.2	995.1	995.9	996.7	996.7
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1343.0	1342.5	1346.3	1343.6	1346.3	1342.5	1343.0	1346.8	1347.9	1348.5	1348.5
5°	1250.1	1252.1	1245.3	1245.3	1245.3	1252.1	1250.1	1254.1	1257.5	1260.3	1264.4
7.5°	1167.3	1164.3	1164.6	1160.9	1164.6	1164.3	1167.3	1170.6	1174.9	1180.9	1186.5
10°	1116.7	1112.6	1111.2	1111.9	1111.2	1112.6	1116.7	1124.9	1127.6	1133.0	1139.1
12.5°	1074.8	1074.0	1065.0	1065.1	1065.0	1074.0	1074.8	1076.9	1082.9	1094.4	1101.6
15°	1025.5	1012.6	1011.2	1015.3	1011.2	1012.6	1025.5	1025.5	1028.2	1037.1	1041.2
17.5°	976.1	969.3	969.7	967.7	969.7	969.3	976.1	977.2	979.4	986.6	992.0
20°	950.0	945.9	945.2	940.4	945.2	945.9	950.0	950.0	952.7	956.1	961.5
22.5°	926.0	924.7	925.1	919.8	925.1	924.7	926.0	927.6	930.4	932.7	936.5
25°	896.2	899.6	896.9	896.9	896.9	899.6	896.2	896.9	897.6	901.0	903.7
27.5°	876.1	875.9	874.6	874.6	874.6	875.9	876.1	874.4	873.6	872.4	871.8
30°	860.8	860.1	861.5	861.5	861.5	860.1	860.8	858.1	856.7	856.1	853.3
32.5°	845.6	846.5	846.8	847.3	846.8	846.5	845.6	842.3	839.9	838.1	835.9
35°	822.0	822.7	824.8	823.4	824.8	822.7	822.0	818.0	815.2	811.1	807.7
37.5°	790.2	793.3	792.6	793.7	792.6	793.3	790.2	789.0	786.2	783.1	779.2
40°	766.2	768.3	767.6	767.6	767.6	768.3	766.2	765.6	762.8	760.8	757.4
42.5°	741.7	743.2	741.5	740.4	741.5	743.2	741.7	740.5	738.9	735.2	731.3
45°	701.6	700.2	702.3	699.5	702.3	700.2	701.6	698.9	698.2	695.5	692.1
47.5°	656.7	658.0	658.6	660.6	658.6	658.0	656.7	656.9	653.1	651.5	650.4
50°	626.7	630.8	630.8	630.1	630.8	630.8	626.7	625.4	622.6	619.9	619.9
52.5°	597.3	599.2	602.0	601.8	602.0	599.2	597.3	594.9	592.2	588.4	587.3
55°	551.9	553.2	554.6	555.3	554.6	553.2	551.9	546.4	544.4	542.4	538.9
57.5°	504.8	504.2	507.5	508.5	507.5	504.2	504.8	499.9	496.8	490.5	489.7
60°	471.6	471.6	477.0	479.1	477.0	471.6	471.6	466.1	461.4	457.3	455.9
62.5°	436.2	438.4	443.8	441.0	443.8	438.4	436.2	430.2	426.5	421.4	417.8
65°	384.5	389.9	389.2	392.0	389.2	389.9	384.5	381.1	373.6	368.8	364.7
67.5°	330.4	333.8	338.7	339.2	338.7	333.8	330.4	325.0	320.1	315.1	310.2
70°	294.0	297.4	300.1	302.1	300.1	297.4	294.0	288.5	283.1	279.7	274.2
72.5°	258.6	260.4	266.9	264.0	266.9	260.4	258.6	252.1	247.7	244.8	238.9
75°	202.8	207.5	211.6	209.6	211.6	207.5	202.8	198.0	194.6	190.5	185.1
77.5°	150.0	154.7	156.6	154.9	156.6	154.7	150.0	146.9	145.1	137.1	136.5
80°	118.4	117.7	121.8	121.1	121.8	117.7	118.4	113.6	110.2	105.5	105.5
82.5°	86.8	86.2	88.1	88.5	88.1	86.2	86.8	84.2	79.8	77.7	76.1
85°	42.2	44.2	41.5	40.8	41.5	44.2	42.2	39.5	39.5	39.5	38.8
87.5°	14.3	14.4	13.9	13.4	13.9	14.4	14.3	14.2	16.3	14.5	14.4
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	32.2	32.0	31.8	31.6	31.8	32.0	32.2	32.4	32.2	31.7	31.1
95°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2
97.5°	94.0	94.0	93.9	93.8	93.9	94.0	94.0	94.1	93.7	92.9	92.1
100°	117.8	118.1	118.5	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0
102.5°	144.7	144.6	144.6	144.5	144.6	144.6	144.7	144.8	144.5	144.0	143.5
105°	185.0	185.4	185.7	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5
107.5°	230.0	229.8	229.6	229.4	229.6	229.8	230.0	230.2	230.1	229.5	228.9
110°	259.8	259.5	259.1	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	290.3	290.2	290.1	290.1	290.1	290.2	290.3	290.3	290.0	289.1	288.3
115°	333.6	333.4	333.2	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4
117.5°	378.2	377.7	377.2	376.7	377.2	377.7	378.2	378.6	378.9	378.9	379.0
120°	408.4	408.0	407.7	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3
122.5°	438.2	437.7	437.2	436.7	437.2	437.7	438.2	438.7	439.2	439.6	440.1
125°	482.9	482.2	481.5	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7
127.5°	527.2	526.4	525.6	524.8	525.6	526.4	527.2	528.0	528.9	529.8	530.8
130°	557.2	556.0	554.8	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8
132.5°	586.4	585.4	584.5	583.6	584.5	585.4	586.4	587.3	588.2	589.0	589.9
135°	631.2	630.9	630.5	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5
137.5°	673.3	672.6	672.0	671.3	672.0	672.6	673.3	673.9	674.6	675.4	676.1
140°	701.8	700.6	699.4	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1
142.5°	728.5	727.6	726.6	725.7	726.6	727.6	728.5	729.5	730.0	730.2	730.4
145°	767.5	766.8	766.1	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0
147.5°	803.9	802.8	801.8	800.8	801.8	802.8	803.9	804.9	805.5	805.5	805.5
150°	826.4	825.4	824.3	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0
152.5°	847.9	847.0	846.1	845.2	846.1	847.0	847.9	848.8	849.1	848.8	848.5
155°	878.5	877.3	876.1	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6
157.5°	904.9	903.9	902.9	901.9	902.9	903.9	904.9	905.8	905.9	905.2	904.5
160°	921.5	920.8	920.1	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4
162.5°	935.9	934.8	933.7	932.6	933.7	934.8	935.9	937.0	937.2	936.3	935.4
165°	955.2	953.9	952.7	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4
167.5°	970.8	969.8	968.7	967.6	968.7	969.8	970.8	971.9	971.9	970.8	969.8
170°	979.4	978.2	977.0	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2
172.5°	985.6	984.4	983.2	982.0	983.2	984.4	985.6	986.9	986.9	985.9	984.8
175°	992.7	991.5	990.2	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9
177.5°	995.7	994.7	993.8	992.8	993.8	994.7	995.7	996.7	996.7	995.9	995.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1346.8	1346.8	1357.2	1363.7	1371.9	1377.3	1381.1	1384.9	1391.5	1400.2	1410.0
5°	1269.8	1272.5	1287.5	1302.5	1316.8	1329.0	1339.2	1351.5	1366.4	1384.8	1405.2
7.5°	1195.2	1205.7	1220.8	1239.0	1259.0	1276.9	1295.0	1315.1	1336.2	1363.3	1391.9
10°	1147.3	1158.9	1177.2	1200.4	1221.5	1242.6	1265.0	1286.8	1313.3	1345.3	1382.1
12.5°	1105.4	1116.4	1135.3	1160.6	1180.7	1203.9	1229.6	1258.0	1287.8	1326.3	1367.9
15°	1047.3	1060.2	1083.3	1095.6	1126.2	1154.1	1177.9	1218.8	1256.9	1296.3	1344.7
17.5°	999.6	1006.9	1025.6	1048.4	1071.2	1102.5	1133.7	1167.7	1205.7	1254.0	1314.4
20°	967.0	973.1	993.5	1017.3	1041.8	1070.4	1098.3	1132.3	1175.2	1226.2	1291.6
22.5°	942.5	949.1	962.5	987.9	1010.8	1034.5	1062.4	1102.9	1148.5	1198.5	1269.3
25°	907.1	911.2	920.0	940.4	960.9	987.4	1011.9	1050.0	1097.0	1155.5	1226.2
27.5°	873.5	877.4	884.8	899.5	918.5	940.0	966.7	999.1	1046.7	1110.3	1185.4
30°	853.3	854.0	860.8	874.4	890.8	908.5	933.0	969.7	1014.6	1079.3	1158.2
32.5°	835.9	833.3	838.0	848.3	864.1	881.8	901.9	938.1	981.4	1045.0	1126.1
35°	806.4	805.0	803.0	811.8	825.4	839.0	856.7	884.0	933.0	992.2	1077.2
37.5°	776.3	773.0	769.4	773.4	784.1	798.2	813.6	837.8	880.0	945.2	1026.6
40°	754.0	751.3	749.2	747.9	757.4	771.0	782.6	805.7	845.2	907.1	987.4
42.5°	729.5	727.9	725.3	723.4	731.3	741.6	753.7	774.1	813.6	871.7	947.7
45°	690.0	688.7	687.3	685.9	690.7	700.2	709.8	724.7	758.7	815.2	884.0
47.5°	646.1	644.3	644.8	642.7	647.3	653.7	660.3	676.4	709.1	754.7	804.9
50°	614.5	613.8	613.8	613.8	615.2	622.6	628.8	641.0	671.0	716.6	752.6
52.5°	584.5	581.7	581.7	582.8	585.2	590.0	593.9	607.3	633.4	670.8	703.6
55°	537.6	532.1	530.8	532.1	534.2	538.3	542.4	553.2	575.7	603.6	622.6
57.5°	485.6	482.6	480.8	481.1	482.2	485.5	488.6	500.4	518.1	532.7	544.9
60°	449.1	450.5	444.4	445.7	445.7	448.4	453.2	460.7	475.7	485.9	498.1
62.5°	414.8	412.9	411.2	409.2	409.2	410.3	416.7	422.6	435.4	440.7	450.2
65°	361.3	361.3	357.3	358.6	359.3	354.5	357.9	364.7	372.9	375.0	383.8
67.5°	307.2	305.3	303.0	300.9	300.9	300.5	302.3	305.7	311.8	312.5	319.3
70°	270.2	268.8	268.1	266.1	263.4	266.8	264.7	268.1	271.5	272.2	276.3
72.5°	234.2	232.9	231.6	229.6	228.5	228.1	228.2	232.2	234.5	233.5	238.2
75°	183.1	181.7	180.3	176.9	176.9	174.9	175.6	178.3	181.0	179.0	183.1
77.5°	134.5	130.2	130.0	130.9	128.6	129.0	128.2	127.8	129.0	129.2	132.8
80°	103.4	98.7	100.0	99.4	98.7	98.0	96.6	97.3	98.0	98.7	100.7
82.5°	74.6	74.2	72.8	72.7	72.0	70.2	69.4	70.6	71.3	70.9	72.4
85°	38.1	36.1	37.4	36.7	37.4	36.7	34.7	34.7	36.1	35.4	36.7
87.5°	15.3	15.2	14.2	14.3	13.3	13.4	12.4	12.6	12.8	12.5	13.2
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	30.6	30.0	28.7	27.5	26.2	24.9	23.6	22.5	21.3	20.1	18.9
95°	58.6	57.9	56.5	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1
97.5°	91.3	90.5	89.5	88.5	87.5	86.5	85.6	84.6	83.7	82.8	81.9
100°	115.5	114.9	114.1	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3
102.5°	143.0	142.5	141.3	140.2	139.0	137.9	137.0	136.4	135.7	135.1	134.5
105°	184.5	184.5	183.0	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9
107.5°	228.4	227.8	227.2	226.6	226.0	225.3	224.9	224.7	224.5	224.3	224.1
110°	257.9	257.2	256.9	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	287.5	286.6	286.6	286.5	286.4	286.3	286.2	286.0	285.8	285.6	285.4
115°	333.2	333.1	333.4	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3
117.5°	379.0	379.0	379.5	379.9	380.4	380.8	380.9	380.5	380.2	379.9	379.5
120°	409.5	409.7	410.6	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9
122.5°	440.5	441.0	441.4	441.9	442.3	442.8	442.6	441.8	441.1	440.3	439.6
125°	486.4	487.1	487.4	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3
127.5°	531.8	532.7	533.1	533.5	533.9	534.3	533.9	532.8	531.7	530.6	529.5
130°	561.4	562.1	562.7	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2
132.5°	590.7	591.5	591.9	592.3	592.7	593.1	592.6	591.2	589.8	588.4	587.0
135°	634.2	634.9	635.0	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9
137.5°	676.8	677.5	677.1	676.6	676.2	675.7	675.1	674.2	673.3	672.5	671.6
140°	704.3	704.4	704.3	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7
142.5°	730.5	730.7	730.4	730.1	729.8	729.5	728.9	728.0	727.1	726.3	725.4
145°	769.2	769.3	768.8	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4
147.5°	805.5	805.5	805.0	804.5	804.0	803.5	803.0	802.3	801.7	801.1	800.5
150°	828.0	828.0	827.6	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8
152.5°	848.3	848.0	847.8	847.6	847.4	847.2	846.8	846.3	845.8	845.3	844.9
155°	877.9	877.2	877.1	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4
157.5°	903.8	903.0	902.9	902.8	902.6	902.5	902.5	902.7	902.9	903.1	903.3
160°	919.5	918.7	918.7	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2
162.5°	934.5	933.7	933.5	933.4	933.3	933.1	933.3	933.8	934.3	934.8	935.2
165°	953.3	952.3	952.3	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6
167.5°	968.7	967.6	967.5	967.3	967.2	967.1	967.3	968.0	968.7	969.4	970.1
170°	977.0	975.7	975.7	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9
172.5°	983.7	982.6	982.6	982.6	982.6	982.6	983.0	983.7	984.4	985.1	985.7
175°	990.9	989.8	989.8	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9
177.5°	994.2	993.4	993.4	993.4	993.4	993.4	993.7	994.2	994.8	995.4	995.9
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1413.2	1416.0	1425.2	1431.8	1439.4	1443.7	1448.1	1451.4	1455.7	1456.8	1472.6
5°	1419.5	1433.1	1456.9	1474.6	1496.4	1520.2	1536.5	1544.0	1563.8	1580.1	1612.8
7.5°	1417.7	1446.7	1482.7	1519.9	1560.0	1597.0	1629.1	1667.2	1694.3	1735.0	1775.1
10°	1416.1	1454.9	1501.2	1548.8	1604.6	1656.3	1702.6	1754.3	1797.2	1853.7	1902.0
12.5°	1411.2	1458.2	1522.4	1578.7	1646.5	1717.8	1786.4	1852.8	1890.8	1984.9	2029.4
15°	1399.1	1454.9	1535.2	1620.9	1714.2	1798.5	1885.6	1955.1	2067.3	2149.7	2202.1
17.5°	1376.0	1454.1	1549.3	1652.8	1766.1	1877.3	1976.0	2081.4	2200.4	2300.1	2406.2
20°	1365.1	1450.8	1557.0	1671.3	1789.0	1914.9	2027.2	2153.8	2283.7	2381.7	2517.8
22.5°	1344.9	1442.1	1556.4	1683.8	1809.7	1939.9	2071.3	2198.9	2349.1	2484.1	2613.6
25°	1312.0	1420.9	1539.3	1681.5	1829.2	1959.8	2117.0	2286.5	2443.0	2616.5	2745.8
27.5°	1277.4	1393.6	1512.3	1644.6	1803.4	1958.5	2156.2	2347.7	2539.0	2688.9	2784.6
30°	1250.7	1363.7	1486.2	1619.6	1776.8	1961.2	2182.3	2391.2	2577.7	2706.3	2760.1
32.5°	1221.9	1336.5	1444.8	1584.7	1752.3	1959.5	2198.7	2416.8	2579.9	2665.5	2655.0
35°	1176.6	1272.5	1378.0	1512.7	1710.1	1947.6	2208.2	2419.1	2519.2	2500.8	2362.0
37.5°	1111.2	1191.9	1295.8	1443.3	1661.1	1922.4	2189.1	2347.4	2340.9	2191.3	1990.2
40°	1070.4	1139.1	1239.2	1394.3	1623.0	1906.1	2159.2	2262.0	2174.9	1965.9	1725.0
42.5°	1017.1	1080.3	1180.4	1339.9	1581.1	1872.8	2102.0	2131.8	1961.4	1721.0	1500.2
45°	934.3	990.1	1093.5	1258.2	1518.2	1800.6	1962.5	1889.7	1660.4	1412.0	1243.9
47.5°	845.4	903.4	1002.9	1172.1	1427.3	1691.8	1769.0	1614.1	1378.7	1177.2	1022.9
50°	789.4	845.2	942.5	1113.3	1365.7	1602.6	1634.5	1434.5	1218.1	1041.2	914.6
52.5°	732.8	785.3	881.0	1052.3	1293.9	1499.1	1479.4	1275.5	1076.5	925.7	826.4
55°	648.5	698.2	789.4	950.0	1169.8	1332.4	1261.0	1066.3	901.7	784.6	709.1
57.5°	573.1	620.7	699.4	844.5	1035.6	1147.3	1056.4	892.4	761.5	671.4	615.0
60°	521.9	564.1	639.0	773.7	939.8	1024.8	935.0	790.1	679.8	607.7	557.3
62.5°	473.5	510.2	579.6	701.9	846.1	917.6	826.7	704.0	610.1	546.2	503.4
65°	400.1	433.5	494.7	590.0	708.4	756.0	677.8	578.4	505.6	458.0	429.4
67.5°	333.2	361.5	414.4	489.4	576.5	611.2	551.6	474.7	419.9	381.6	358.9
70°	288.5	313.0	354.5	419.2	498.1	524.7	468.9	405.6	365.4	334.8	313.7
72.5°	251.0	268.9	306.6	356.6	422.4	443.5	404.6	349.0	311.5	288.5	271.8
75°	191.2	206.2	230.7	270.8	316.4	328.7	299.4	264.7	239.5	223.2	210.3
77.5°	137.9	148.9	166.6	191.4	222.9	234.0	215.4	192.3	173.9	162.9	155.7
80°	104.1	113.0	127.9	148.3	167.4	173.5	162.6	144.9	132.0	125.9	119.8
82.5°	76.9	81.9	90.9	104.8	117.9	125.1	115.8	105.2	98.3	92.7	90.4
85°	38.8	41.5	45.6	51.0	59.2	61.9	58.5	55.8	51.7	48.3	48.3
87.5°	14.7	15.0	17.0	18.4	21.0	23.1	23.0	22.4	22.3	21.9	21.5
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6	31.1
95°	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2
97.5°	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3	92.1
100°	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0
102.5°	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0	143.5
105°	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5
107.5°	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4	228.9
110°	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5	288.3
115°	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4
117.5°	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0	379.0
120°	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3
122.5°	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5	440.1
125°	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7
127.5°	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8	530.8
130°	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8
132.5°	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7	589.9
135°	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5
137.5°	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8	676.1
140°	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1
142.5°	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5	730.4
145°	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0
147.5°	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5	805.5
150°	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0
152.5°	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3	848.5
155°	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6
157.5°	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8	904.5
160°	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4
162.5°	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5	935.4
165°	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4
167.5°	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7	969.8
170°	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2
172.5°	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7	984.8
175°	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9
177.5°	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2	995.1
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1478.0	1478.6	1484.6	1488.9	1486.7	1489.5	1490.5
5°	1614.8	1639.3	1652.2	1661.8	1662.4	1663.1	1668.6
7.5°	1808.7	1835.0	1854.2	1883.3	1892.0	1902.0	1899.1
10°	1950.3	1989.1	2022.4	2040.1	2059.2	2087.1	2064.6
12.5°	2082.6	2151.3	2202.1	2229.6	2247.5	2253.1	2242.1
15°	2300.7	2390.6	2438.9	2437.5	2498.8	2525.3	2483.8
17.5°	2500.8	2583.7	2650.1	2684.1	2735.2	2746.5	2741.3
20°	2623.3	2713.8	2765.5	2824.0	2850.6	2874.4	2878.5
22.5°	2728.9	2810.2	2865.7	2914.4	2936.6	2947.9	2954.7
25°	2837.6	2901.6	2935.0	2952.0	2958.1	2956.7	2947.9
27.5°	2830.2	2835.1	2798.3	2762.3	2730.0	2693.7	2681.1
30°	2756.7	2699.5	2597.4	2539.6	2454.5	2387.2	2414.4
32.5°	2563.4	2449.6	2335.0	2208.6	2103.9	2074.1	2044.2
35°	2187.8	1987.7	1870.7	1734.6	1680.1	1625.7	1588.3
37.5°	1770.0	1615.2	1476.4	1387.4	1332.8	1298.4	1279.9
40°	1530.4	1390.9	1276.6	1204.5	1163.0	1124.2	1118.7
42.5°	1339.3	1209.6	1123.6	1066.2	1026.3	1009.8	997.9
45°	1097.0	1006.4	948.6	907.8	881.2	871.0	857.4
47.5°	928.5	864.5	821.1	793.3	773.3	765.7	764.6
50°	834.3	781.2	749.2	727.4	711.8	709.1	698.2
52.5°	763.5	717.5	692.6	673.6	662.3	654.6	651.4
55°	662.8	632.2	609.7	598.8	590.0	582.5	582.5
57.5°	579.9	554.3	539.5	530.2	527.5	522.2	518.8
60°	528.7	507.0	495.4	487.2	481.8	482.5	476.3
62.5°	478.7	464.5	453.5	445.3	438.8	438.9	439.3
65°	407.6	396.7	388.6	385.8	381.8	377.0	378.4
67.5°	345.4	335.2	328.8	324.2	322.8	320.2	324.2
70°	300.8	293.3	288.5	284.4	283.1	283.8	287.2
72.5°	259.9	254.6	251.5	249.6	246.6	246.7	249.1
75°	204.1	200.1	197.3	195.3	194.6	194.6	194.6
77.5°	150.0	149.0	147.8	144.8	144.9	145.8	145.9
80°	118.4	116.4	115.7	114.3	112.3	110.9	114.3
82.5°	88.5	86.4	85.7	85.5	82.3	82.1	84.9
85°	47.6	45.6	46.3	45.6	45.6	44.9	44.9
87.5°	21.0	20.6	20.2	20.8	20.3	19.9	21.0
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	259.3	260.0	260.2	259.8	259.5	259.1	258.8



TEST NUMBER: P332019

CATALOG NUMBER: S123DIP-S1000D805U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)