

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332315-935

Luminaire Tested: **S123RDIP-S775D805U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332315-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D805U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5276.7 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82		67	67	67		54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68		60	58	57		48	47	46	41
2	89	82	76	71	82	76	70	66	64	60	57		53	50	48		43	41	39	35
3	81	72	65	59	75	67	61	56	56	52	48		47	44	41		38	36	34	30
4	75	64	56	50	68	59	53	47	50	45	41		42	38	35		34	32	29	26
5	69	57	49	43	63	53	46	41	45	40	36		38	34	31		31	28	26	22
6	63	51	43	38	58	48	41	36	41	35	31		34	30	27		28	25	23	20
7	59	46	39	33	54	43	36	31	37	32	28		31	27	24		26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25		29	24	21		24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22		26	22	19		22	19	17	14
10	47	35	28	24	44	33	27	22	29	23	20		24	20	18		20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11965	11965	11965
5°	12011	11846	11914
10°	11943	11696	11657
15°	11814	11422	11303
20°	11639	11080	10822
25°	11457	10696	10354
30°	11216	10253	9692
35°	10970	9809	9087
40°	10742	9285	8335
45°	10443	8770	7658
50°	10114	8182	6899
55°	9779	7512	6191
60°	9472	6794	5414
65°	9070	6016	4638
70°	8567	5051	3745
75°	7835	3976	3523
80°	6986	3521	3242
85°	5903	3112	2890



TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	2.0
10°-20°	290.4	5.5
20°-30°	418.2	7.9
30°-40°	471.1	8.9
40°-50°	450.7	8.5
50°-60°	369.0	7.0
60°-70°	249.0	4.7
70°-80°	125.3	2.4
80°-90°	35.7	0.7
90°-100°	32.9	0.6
100°-110°	157.0	3.0
110°-120°	377.1	7.1
120°-130°	480.2	9.1
130°-140°	513.1	9.7
140°-150°	479.8	9.1
150°-160°	387.0	7.3
160°-170°	249.8	4.7
170°-180°	86.1	1.6
0°-30°	813.0	15.4
0°-40°	1284.1	24.3
0°-60°	2103.8	39.9
0°-90°	2513.7	47.6
90°-120°	567.0	10.7
90°-150°	2040.1	38.7
90°-180°	2763.0	52.4
0°-180°	5276.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1112	1112	1112	1112	1112	
5°	1112	1107	1096	1104	1103	105
15°	1060	1049	1025	1020	1014	299
25°	965	941	901	882	872	443
35°	835	801	746	709	692	522
45°	686	644	576	526	503	529
55°	521	475	400	350	330	467
65°	356	305	236	194	182	352
75°	188	145	96	87	85	201
85°	48	29	25	24	23	54
90°	1	8	16	19	20	4
95°	41	15	21	25	26	51
105°	201	204	147	35	30	213
115°	376	380	386	393	396	371
125°	530	536	538	540	541	474
135°	660	664	667	669	667	508
145°	762	766	768	769	769	477
155°	839	838	839	842	838	387
165°	885	883	882	887	883	250
175°	906	903	903	907	903	86
180°	906	906	906	906	906	



TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1115.2	1114.6	1113.9	1113.3	1112.7	1111.4	1109.4	1107.5	1105.6	1103.6	1105.4
5°	1111.6	1110.6	1109.6	1108.6	1107.6	1105.9	1103.5	1101.0	1098.6	1096.3	1098.0
7.5°	1101.3	1100.3	1099.2	1098.0	1097.0	1094.8	1091.7	1088.6	1085.5	1082.4	1083.4
10°	1092.7	1091.2	1089.9	1088.5	1087.0	1084.5	1080.9	1077.4	1073.8	1070.1	1070.3
12.5°	1080.4	1078.8	1077.3	1075.7	1074.2	1071.2	1066.8	1062.4	1057.9	1053.5	1053.4
15°	1060.2	1058.0	1055.8	1053.6	1051.4	1047.5	1041.9	1036.3	1030.6	1025.0	1024.1
17.5°	1034.7	1032.3	1029.7	1027.1	1024.5	1019.7	1012.5	1005.4	998.2	991.2	989.0
20°	1016.1	1012.8	1009.6	1006.4	1003.2	997.8	990.2	982.6	975.0	967.3	964.8
22.5°	995.1	991.4	987.7	984.0	980.3	974.5	966.4	958.3	950.2	942.1	938.8
25°	964.7	959.7	954.6	949.6	944.6	937.5	928.2	919.0	909.8	900.6	896.4
27.5°	927.6	922.1	916.6	911.1	905.6	897.7	887.4	877.2	866.9	856.6	850.8
30°	902.4	896.4	890.4	884.4	878.4	869.8	858.6	847.3	836.1	824.9	818.1
32.5°	877.2	870.4	863.6	856.8	850.0	840.6	828.7	816.9	805.0	793.2	785.7
35°	834.8	827.6	820.4	813.2	806.0	796.2	783.8	771.3	758.9	746.5	737.9
37.5°	791.9	783.9	775.8	767.8	759.8	749.2	736.0	722.7	709.5	696.2	686.4
40°	764.5	755.7	746.8	738.0	729.3	717.7	703.5	689.3	675.0	660.8	650.4
42.5°	733.5	724.7	715.8	707.1	698.3	686.5	671.8	657.0	642.4	627.7	616.3
45°	686.0	677.1	668.0	659.0	650.0	637.8	622.3	606.9	591.5	576.1	564.6
47.5°	638.7	628.8	618.9	609.0	599.1	586.4	571.0	555.5	540.1	524.7	512.3
50°	604.0	594.6	585.2	575.8	566.4	553.5	537.4	521.1	504.9	488.6	476.2
52.5°	573.0	562.8	552.6	542.3	532.2	519.0	502.9	486.9	470.8	454.7	441.9
55°	521.1	511.3	501.4	491.6	481.8	468.4	451.3	434.4	417.3	400.3	388.7
57.5°	473.1	462.4	451.8	441.0	430.3	416.5	399.3	382.2	365.1	348.0	337.0
60°	440.0	429.0	417.9	406.9	395.9	382.0	365.4	348.8	332.2	315.6	304.7
62.5°	406.7	395.7	384.7	373.7	362.7	348.9	332.3	315.6	299.0	282.3	272.2
65°	356.1	345.1	334.1	323.0	312.0	298.7	283.1	267.4	251.8	236.2	226.4
67.5°	305.5	294.3	283.2	272.0	260.9	247.8	232.8	217.8	202.9	187.9	180.6
70°	272.2	261.5	250.6	239.8	229.0	216.5	202.5	188.6	174.5	160.5	153.4
72.5°	239.1	228.4	217.7	207.1	196.5	184.8	172.0	159.3	146.5	133.8	128.0
75°	188.4	178.8	169.2	159.5	150.0	139.7	128.6	117.6	106.6	95.6	93.6
77.5°	142.2	133.5	124.8	116.1	107.5	99.6	92.5	85.4	78.4	71.2	70.2
80°	112.7	104.4	96.3	88.1	79.8	73.6	69.4	65.2	61.0	56.8	56.2
82.5°	84.6	77.5	70.3	63.3	56.2	51.7	49.7	47.7	45.8	43.8	43.2
85°	47.8	43.4	39.0	34.5	30.1	27.6	27.0	26.4	25.8	25.2	24.9
87.5°	17.5	16.0	14.6	13.1	11.6	11.0	11.5	11.8	12.2	12.6	12.6
90°	0.7	2.2	3.7	5.2	6.6	8.4	10.3	12.2	14.2	16.2	16.8
92.5°	12.5	12.1	11.7	11.3	10.8	11.4	12.8	14.3	15.8	17.2	18.2
95°	41.1	35.0	28.8	22.6	16.5	14.3	15.9	17.6	19.2	20.8	22.0
97.5°	82.5	79.8	77.1	74.3	71.5	64.7	54.0	43.2	32.5	21.7	22.9
100°	113.7	116.8	119.8	122.7	125.7	115.5	92.2	68.9	45.5	22.2	23.4
102.5°	149.3	151.4	153.6	155.8	157.9	146.3	120.8	95.2	69.7	44.3	40.6
105°	200.6	202.2	203.9	205.5	207.2	201.3	187.8	174.4	160.8	147.4	121.0
107.5°	254.7	256.1	257.4	258.6	259.9	261.7	263.8	266.0	268.0	270.2	250.8
110°	290.8	292.0	293.2	294.4	295.6	297.0	298.7	300.3	302.0	303.6	298.7



TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	325.3	326.3	327.4	328.5	329.6	330.9	332.6	334.2	335.9	337.5	337.6
115°	376.3	377.2	378.1	379.0	379.9	381.0	382.4	383.7	385.0	386.4	387.9
117.5°	425.7	426.8	427.9	429.0	430.1	431.0	431.7	432.4	433.1	433.8	435.0
120°	456.4	457.7	459.1	460.4	461.8	462.7	463.1	463.6	464.0	464.4	465.6
122.5°	487.6	488.7	489.8	490.9	492.1	492.8	493.4	494.0	494.6	495.2	496.0
125°	530.5	531.6	532.8	534.0	535.2	536.1	536.7	537.3	537.9	538.5	538.8
127.5°	571.9	573.1	574.3	575.5	576.7	577.6	578.3	579.1	579.8	580.5	581.0
130°	597.7	598.9	600.1	601.3	602.5	603.4	604.0	604.6	605.2	605.8	606.4
132.5°	622.5	623.7	624.9	626.1	627.3	628.1	628.6	629.0	629.6	630.1	630.7
135°	660.3	661.2	662.1	663.1	663.9	664.7	665.3	665.9	666.5	667.1	667.5
137.5°	692.7	693.8	694.9	696.0	697.2	697.9	698.3	698.6	698.9	699.2	700.0
140°	714.2	715.1	716.0	716.9	717.8	718.4	718.9	719.4	719.8	720.2	720.8
142.5°	734.1	735.0	735.9	736.8	737.7	738.4	738.8	739.3	739.7	740.2	740.6
145°	762.0	763.0	764.1	765.1	766.2	766.8	767.2	767.4	767.8	768.0	768.4
147.5°	788.2	788.9	789.6	790.3	791.0	791.5	791.8	792.0	792.4	792.6	793.0
150°	804.3	804.9	805.3	805.7	806.2	806.6	806.8	807.2	807.4	807.8	808.0
152.5°	818.9	819.2	819.3	819.6	819.8	819.9	820.1	820.3	820.5	820.7	821.2
155°	839.4	839.1	838.8	838.5	838.2	838.1	838.3	838.4	838.5	838.7	839.5
157.5°	855.2	855.2	855.2	855.1	855.1	855.1	854.9	854.8	854.6	854.5	855.4
160°	865.0	864.8	864.7	864.5	864.4	864.2	864.1	863.9	863.8	863.6	864.5
162.5°	874.1	873.7	873.3	873.0	872.5	872.3	872.1	872.0	871.8	871.7	872.7
165°	885.2	884.7	884.2	883.8	883.4	883.0	883.0	882.8	882.6	882.4	883.6
167.5°	893.8	893.2	892.6	892.0	891.4	891.0	891.0	891.0	891.0	891.0	892.3
170°	898.6	898.0	897.4	896.8	896.2	896.0	896.0	896.0	896.0	896.0	897.2
172.5°	901.8	901.1	900.4	899.7	899.0	898.7	898.8	898.9	899.1	899.1	900.3
175°	906.0	905.3	904.6	903.8	903.0	902.8	902.8	903.0	903.2	903.4	904.4
177.5°	907.1	906.5	905.9	905.3	904.7	904.5	904.6	904.7	904.8	904.9	905.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0



TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6	1111.6
2.5°	1107.2	1109.0	1110.7	1111.5	1111.1	1110.8	1110.4	1110.2
5°	1099.8	1101.6	1103.5	1104.1	1103.8	1103.4	1102.9	1102.6
7.5°	1084.4	1085.4	1086.4	1086.6	1085.9	1085.2	1084.5	1083.8
10°	1070.6	1070.7	1070.9	1070.6	1069.5	1068.5	1067.6	1066.5
12.5°	1053.3	1053.2	1053.1	1052.4	1051.3	1050.1	1049.0	1047.8
15°	1023.0	1022.0	1021.1	1019.9	1018.5	1017.0	1015.6	1014.3
17.5°	986.9	984.8	982.7	980.6	978.4	976.4	974.3	972.2
20°	962.2	959.5	956.9	954.4	952.0	949.6	947.2	944.8
22.5°	935.6	932.4	929.1	926.3	924.1	921.9	919.6	917.4
25°	892.3	888.0	883.8	880.6	878.4	876.2	874.0	871.8
27.5°	844.9	839.1	833.3	828.6	825.3	821.9	818.6	815.2
30°	811.3	804.4	797.6	792.6	789.5	786.3	783.0	779.8
32.5°	778.3	770.9	763.4	757.9	754.6	751.2	747.9	744.5
35°	729.3	720.7	712.0	705.9	702.3	698.7	695.1	691.5
37.5°	676.6	666.8	657.0	650.0	645.5	641.0	636.6	632.1
40°	640.0	629.6	619.1	611.7	607.0	602.4	597.8	593.2
42.5°	604.9	593.5	582.1	574.4	570.2	566.1	562.0	557.8
45°	553.3	541.8	530.4	522.3	517.5	512.6	507.9	503.1
47.5°	499.8	487.4	475.0	466.7	462.4	458.1	453.8	449.5
50°	463.8	451.3	438.9	430.4	425.9	421.2	416.6	412.0
52.5°	429.0	416.0	403.1	394.6	390.5	386.3	382.2	378.1
55°	377.0	365.4	353.8	345.9	342.0	337.9	334.0	329.9
57.5°	326.1	315.0	304.1	296.9	293.5	290.1	286.6	283.3
60°	293.9	283.1	272.2	265.2	261.7	258.3	254.9	251.5
62.5°	262.0	251.8	241.7	234.8	231.2	227.6	224.1	220.5
65°	216.5	206.7	196.9	190.9	188.7	186.5	184.3	182.1
67.5°	173.2	165.9	158.5	153.7	151.4	149.0	146.6	144.2
70°	146.5	139.4	132.4	127.9	125.6	123.4	121.2	119.0
72.5°	122.3	116.6	110.9	107.5	106.6	105.7	104.8	103.8
75°	91.5	89.5	87.6	86.4	85.9	85.6	85.2	84.7
77.5°	69.1	67.9	66.9	66.1	65.8	65.3	64.9	64.6
80°	55.6	55.0	54.4	53.9	53.5	53.1	52.7	52.3
82.5°	42.6	42.0	41.4	41.1	41.0	40.9	40.8	40.7
85°	24.5	24.0	23.7	23.4	23.4	23.4	23.4	23.4
87.5°	12.5	12.5	12.5	12.4	12.3	12.1	12.1	12.0
90°	17.4	17.9	18.5	19.0	19.3	19.6	19.9	20.2
92.5°	19.1	20.1	21.1	21.6	21.8	22.0	22.1	22.4
95°	23.0	24.0	25.1	25.6	25.6	25.6	25.6	25.6
97.5°	24.1	25.2	26.4	27.1	27.3	27.5	27.6	27.7
100°	24.6	25.8	27.0	27.6	27.8	28.0	28.2	28.2
102.5°	36.9	33.1	29.4	27.7	28.0	28.2	28.5	28.8
105°	94.5	68.0	41.5	28.4	28.8	29.0	29.4	29.6
107.5°	231.4	212.0	192.5	172.8	152.9	132.9	113.0	93.0
110°	293.7	288.8	283.9	270.7	249.3	227.9	206.5	185.1



TEST NUMBER: P332315-935

CATALOG NUMBER: S123RDIP-S775D805U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	337.7	337.8	337.9	335.6	331.1	326.6	322.1	317.6
115°	389.3	390.9	392.4	393.4	394.0	394.6	395.2	395.8
117.5°	436.2	437.4	438.5	439.2	439.4	439.5	439.5	439.7
120°	466.8	468.0	469.2	469.8	469.8	469.8	469.8	469.8
122.5°	496.8	497.7	498.5	498.9	499.1	499.2	499.4	499.5
125°	539.1	539.4	539.7	540.0	540.3	540.6	540.9	541.2
127.5°	581.4	581.9	582.4	582.5	582.2	581.9	581.6	581.3
130°	607.0	607.6	608.2	608.4	608.0	607.8	607.4	607.2
132.5°	631.2	631.8	632.4	632.5	632.1	631.7	631.3	630.9
135°	668.0	668.4	668.8	668.8	668.4	668.0	667.5	667.1
137.5°	700.7	701.4	702.1	702.3	702.1	701.7	701.5	701.1
140°	721.4	722.0	722.6	722.8	722.5	722.2	721.9	721.6
142.5°	741.1	741.6	742.1	742.1	741.7	741.2	740.9	740.5
145°	768.6	769.0	769.2	769.4	769.4	769.4	769.4	769.4
147.5°	793.2	793.6	793.8	793.7	793.0	792.3	791.6	790.9
150°	808.3	808.7	808.9	808.9	808.4	808.0	807.5	807.1
152.5°	821.7	822.3	822.9	822.8	822.1	821.4	820.7	820.0
155°	840.2	840.9	841.7	841.6	840.8	839.8	839.0	838.0
157.5°	856.3	857.1	858.1	857.9	856.8	855.6	854.5	853.3
160°	865.4	866.3	867.2	867.1	866.1	865.0	864.0	863.0
162.5°	873.7	874.8	875.7	875.8	874.9	873.9	873.1	872.1
165°	884.8	886.1	887.3	887.3	886.3	885.2	884.2	883.1
167.5°	893.5	894.7	895.9	895.9	894.7	893.5	892.3	891.0
170°	898.3	899.5	900.7	900.7	899.5	898.3	897.2	896.0
172.5°	901.6	902.8	904.0	903.9	902.6	901.3	899.9	898.6
175°	905.4	906.5	907.5	907.4	906.3	905.1	903.9	902.7
177.5°	906.9	907.8	908.8	908.7	907.5	906.3	905.1	903.9
180°	906.0	906.0	906.0	906.0	906.0	906.0	906.0	906.0

(END OF REPORT)