

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332074

Luminaire Tested: **S123DIP-S1165D1025U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332074  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D1025U835-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8609.6 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332074  
CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	53	49
2	91	84	78	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	67	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	26
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	37	32	39	34	29	34	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	31	27	23	27	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17460	17460	17460	17460
5°	20822	17535	15540	17535
10°	26063	17446	14036	17446
15°	31967	17306	13067	17306
20°	38080	17087	12441	17087
25°	40435	16820	12302	16820
30°	34657	16625	12367	16625
35°	24103	16348	12496	16348
40°	18156	16024	12456	16024
45°	15075	15541	12298	15541
50°	13504	14555	12188	14555
55°	12624	13495	12035	13495
60°	11842	12385	11911	12385
65°	11130	11291	11530	11291
70°	10439	10043	10980	10043
75°	9349	8792	10069	8792
80°	8182	7209	8672	7209
85°	6410	5236	5829	5236



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.8	1.9
10°-20°	512.4	6.0
20°-30°	859.9	10.0
30°-40°	973.7	11.3
40°-50°	873.2	10.1
50°-60°	704.7	8.2
60°-70°	491.0	5.7
70°-80°	258.1	3.0
80°-90°	66.9	0.8
90°-100°	274.4	3.2
100°-110°	777.0	9.0
110°-120°	764.4	8.9
120°-130°	609.7	7.1
130°-140°	480.7	5.6
140°-150°	358.8	4.2
150°-160°	250.1	2.9
160°-170°	146.9	1.7
170°-180°	47.8	0.6
0°-30°	1532.1	17.8
0°-40°	2505.8	29.1
0°-60°	4083.7	47.4
0°-90°	4899.8	56.9
90°-120°	1815.8	21.1
90°-150°	3265.1	37.9
90°-180°	3710.0	43.1
0°-180°	8609.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1622	1622	1622	1622	1622	
5°	1927	1623	1438	1623	1927	200
15°	2869	1553	1173	1553	2869	828
25°	3405	1416	1036	1416	3405	1493
35°	1834	1244	951	1244	1834	1192
45°	990	1021	808	1021	990	784
55°	673	719	641	719	673	604
65°	437	443	453	443	437	435
75°	225	211	242	211	225	241
85°	52	42	47	42	52	62
90°	29	2	29	2	29	18
95°	116	34	116	34	116	209
105°	1270	116	1270	116	1270	1253
115°	1544	205	1544	205	1544	1500
125°	1218	284	1218	284	1218	1104
135°	987	333	987	333	987	766
145°	772	380	772	380	772	491
155°	640	432	640	432	640	298
165°	558	472	558	472	558	159
175°	502	492	502	492	502	49
180°	493	493	493	493	493	



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1721.5	1720.2	1717.1	1719.6	1714.6	1707.6	1707.0	1700.7	1682.5	1681.2	1676.2
5°	1927.1	1920.8	1920.0	1919.2	1908.2	1893.3	1865.0	1862.6	1824.9	1806.0	1783.3
7.5°	2193.3	2196.6	2185.2	2175.1	2141.5	2119.3	2089.0	2050.2	2003.8	1956.8	1925.5
10°	2384.5	2410.4	2378.2	2356.2	2335.8	2297.2	2252.5	2196.6	2140.8	2075.6	2026.1
12.5°	2589.5	2602.2	2595.7	2575.0	2543.2	2484.6	2405.2	2343.8	2292.4	2183.8	2139.9
15°	2868.6	2916.6	2885.9	2815.2	2816.7	2760.9	2657.2	2543.2	2482.7	2387.6	2258.0
17.5°	3166.0	3172.0	3158.9	3100.0	3060.7	2984.0	2888.3	2779.0	2656.4	2541.4	2403.8
20°	3324.4	3319.7	3292.2	3261.6	3194.0	3134.3	3029.7	2907.9	2750.7	2637.6	2487.4
22.5°	3412.5	3404.6	3391.6	3365.9	3309.7	3245.5	3151.7	3018.6	2868.9	2713.0	2539.6
25°	3404.6	3414.8	3416.4	3409.3	3389.7	3351.2	3277.3	3171.2	3021.9	2821.5	2640.7
27.5°	3096.5	3111.0	3153.0	3190.2	3231.9	3274.3	3268.6	3216.0	3105.5	2932.4	2711.4
30°	2788.4	2757.0	2834.8	2933.1	2999.9	3117.7	3183.8	3187.7	3125.6	2977.1	2761.7
32.5°	2360.9	2395.5	2429.9	2550.8	2696.8	2829.2	2960.6	3066.4	3078.5	2979.6	2791.3
35°	1834.3	1877.6	1940.4	2003.3	2160.5	2295.7	2526.7	2727.9	2888.3	2909.5	2793.9
37.5°	1478.2	1499.5	1539.3	1602.3	1705.1	1865.5	2044.2	2298.5	2530.8	2703.6	2711.1
40°	1292.1	1298.3	1343.1	1391.1	1474.4	1606.4	1767.5	1992.3	2270.5	2511.8	2612.4
42.5°	1152.5	1166.3	1185.3	1231.4	1297.7	1397.1	1546.9	1732.6	1987.6	2265.3	2462.1
45°	990.3	1006.0	1017.8	1048.4	1095.6	1162.4	1266.9	1436.7	1630.8	1917.6	2182.5
47.5°	883.1	884.3	893.1	916.2	948.3	998.4	1072.3	1181.4	1359.6	1592.3	1864.2
50°	806.4	818.9	822.1	840.1	865.3	902.2	963.5	1056.3	1202.5	1406.8	1656.7
52.5°	752.3	756.1	764.9	777.9	799.9	828.7	881.8	954.4	1069.2	1243.3	1473.1
55°	672.7	672.7	681.4	691.6	704.2	730.1	765.5	818.9	906.2	1041.3	1231.5
57.5°	599.2	603.1	609.2	612.4	623.1	640.2	669.8	710.3	775.4	879.4	1030.7
60°	550.1	557.2	556.4	562.7	572.2	585.5	610.7	643.7	701.8	785.1	912.5
62.5°	507.4	506.9	506.8	514.3	523.7	536.5	552.8	581.4	630.8	704.7	813.1
65°	437.0	435.4	440.9	445.6	448.8	458.2	470.8	495.9	528.9	583.9	668.0
67.5°	374.4	369.9	372.8	374.4	379.8	387.1	398.9	414.5	440.7	484.9	548.3
70°	331.7	327.7	326.9	328.5	333.2	338.7	347.4	362.3	386.7	422.0	468.4
72.5°	287.6	285.0	284.8	288.3	290.5	294.1	300.2	313.9	333.2	359.8	403.0
75°	224.8	224.8	224.8	225.6	227.9	231.1	235.8	242.8	257.8	276.6	305.7
77.5°	168.5	168.3	167.4	167.2	170.7	172.1	173.2	179.8	188.1	200.9	222.1
80°	132.0	128.1	129.7	132.0	133.6	134.4	136.8	138.3	145.4	152.5	167.4
82.5°	98.1	94.8	95.1	98.7	99.0	99.8	102.2	104.4	107.0	113.5	121.5
85°	51.9	51.9	52.7	52.7	53.4	52.7	55.0	55.8	55.8	59.7	64.4
87.5°	24.7	23.6	24.0	24.5	24.0	24.3	24.7	25.1	25.5	26.4	26.4
90°	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0	24.0	25.0	22.0
92.5°	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0	115.8	153.5	168.9
95°	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3	480.1	591.9	527.0
97.5°	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8	981.4	917.3	671.6
100°	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9	1141.9	945.3	638.8
102.5°	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3	1149.9	893.4	590.9
105°	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6	1089.0	802.5	532.0
107.5°	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0	982.4	722.3	494.5
110°	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9	915.3	676.8	480.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6	857.0	646.4	472.1
115°	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2	786.6	613.9	469.1
117.5°	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0	744.0	594.7	470.9
120°	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4	721.7	585.9	474.1
122.5°	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9	703.3	580.3	479.7
125°	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6	679.8	573.0	488.1
127.5°	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2	659.0	569.4	497.7
130°	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7	647.8	567.0	504.1
132.5°	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7	637.4	566.2	508.9
135°	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7	623.9	565.0	516.1
137.5°	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2	612.1	562.8	520.8
140°	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8	604.9	562.0	524.0
142.5°	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2	598.5	560.4	526.4
145°	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9	589.9	558.0	528.0
147.5°	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5	581.5	554.2	528.0
150°	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9	575.9	551.0	528.0
152.5°	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1	569.6	547.0	525.6
155°	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9	560.0	540.0	523.0
157.5°	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0	549.2	533.8	519.7
160°	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0	542.0	529.0	518.1
162.5°	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4	534.8	524.2	514.9
165°	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0	525.0	517.1	510.1
167.5°	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2	515.7	509.9	505.3
170°	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1	510.1	505.1	502.1
172.5°	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7	504.5	501.1	499.7
175°	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1	498.1	496.1	496.1
177.5°	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1672.4	1667.4	1662.4	1653.6	1646.0	1635.3	1632.2	1628.4	1617.1	1607.1	1599.5
5°	1774.6	1755.7	1728.2	1703.1	1682.7	1655.2	1639.4	1622.9	1599.3	1578.1	1560.8
7.5°	1881.5	1844.4	1801.6	1755.4	1712.4	1670.9	1637.4	1607.5	1574.5	1543.2	1518.9
10°	1966.4	1912.9	1853.2	1788.8	1733.7	1680.3	1635.5	1596.2	1553.8	1516.8	1486.2
12.5°	2063.2	1984.0	1901.6	1823.3	1758.3	1684.1	1629.8	1579.9	1531.8	1487.3	1452.9
15°	2177.8	2077.2	1979.7	1872.1	1773.0	1680.3	1615.9	1553.0	1497.2	1451.6	1407.6
17.5°	2282.2	2168.2	2039.8	1908.8	1789.4	1679.4	1589.1	1518.1	1448.3	1392.5	1348.6
20°	2341.3	2211.6	2066.2	1930.2	1798.2	1675.6	1576.6	1491.7	1416.2	1357.3	1307.8
22.5°	2392.2	2240.5	2090.1	1944.7	1797.6	1665.5	1553.3	1465.9	1384.2	1326.5	1273.8
25°	2445.0	2263.5	2112.6	1942.0	1777.8	1641.0	1515.3	1416.2	1334.5	1266.9	1212.7
27.5°	2490.3	2261.9	2082.8	1899.4	1746.6	1609.6	1475.3	1369.1	1282.3	1208.9	1153.9
30°	2520.4	2265.0	2052.0	1870.5	1716.5	1575.0	1444.5	1337.6	1246.5	1171.8	1119.9
32.5°	2539.3	2263.1	2023.7	1830.3	1668.7	1543.5	1411.2	1300.5	1206.9	1133.5	1083.5
35°	2550.3	2249.3	1975.0	1747.1	1591.5	1469.7	1358.9	1244.1	1145.9	1077.5	1020.9
37.5°	2528.3	2220.2	1918.4	1666.9	1496.6	1376.6	1283.4	1185.6	1091.6	1016.4	967.6
40°	2493.7	2201.4	1874.4	1610.4	1431.2	1315.6	1236.3	1140.4	1047.6	976.1	930.5
42.5°	2427.7	2163.0	1826.0	1547.5	1363.3	1247.7	1174.6	1094.5	1006.8	939.6	894.1
45°	2266.6	2079.5	1753.4	1453.2	1263.0	1143.5	1079.1	1020.9	941.5	876.3	837.0
47.5°	2043.1	1954.0	1648.4	1353.7	1158.3	1043.4	976.4	929.6	871.6	818.9	781.2
50°	1887.8	1850.8	1577.3	1285.8	1088.5	976.1	911.7	869.2	827.6	774.9	740.3
52.5°	1708.6	1731.4	1494.4	1215.3	1017.5	907.0	846.3	812.6	774.8	731.5	701.4
55°	1456.3	1538.8	1351.0	1097.1	911.7	806.4	749.0	719.1	697.1	664.9	639.0
57.5°	1220.1	1325.1	1196.0	975.3	807.8	716.9	661.9	629.4	615.2	598.4	578.0
60°	1079.9	1183.6	1085.4	893.6	738.0	651.5	602.8	575.3	561.1	549.4	532.1
62.5°	954.7	1059.7	977.2	810.6	669.4	589.3	546.8	520.0	509.0	502.8	488.1
65°	782.8	873.2	818.1	681.4	571.4	500.6	462.1	443.3	433.0	430.7	421.3
67.5°	637.1	705.9	665.8	565.2	478.6	417.5	384.8	368.8	360.9	360.1	353.0
70°	541.5	605.9	575.3	484.1	409.5	361.5	333.2	319.1	314.4	313.6	309.7
72.5°	467.3	512.3	487.9	411.8	354.1	310.6	289.8	275.1	269.7	270.8	268.2
75°	345.8	379.6	365.5	312.8	266.4	238.1	220.8	211.4	206.7	209.1	205.9
77.5°	248.8	270.2	257.5	221.0	192.4	172.0	159.2	153.4	149.2	149.0	147.6
80°	187.8	200.4	193.3	171.3	147.8	130.5	120.2	116.3	114.0	113.2	112.4
82.5°	133.8	144.5	136.1	121.0	105.0	94.6	88.8	83.6	81.9	82.4	81.6
85°	67.6	71.5	68.4	58.9	52.7	47.9	44.8	42.4	40.9	41.7	40.1
87.5°	27.1	27.1	24.6	21.7	20.0	17.5	17.1	15.5	14.6	15.0	15.0
90°	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0	4.0	6.0	9.0
92.5°	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4	18.4	26.8	34.5
95°	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9	36.9	47.9	64.9
97.5°	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9	58.9	67.5	82.2
100°	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9	74.9	81.9	95.8
102.5°	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6	92.4	98.6	111.8
105°	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8	118.8	124.8	136.8
107.5°	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5	145.5	151.3	163.1
110°	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7	164.7	169.7	180.7





TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3	182.3	187.3	198.2
115°	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6	208.6	214.6	224.6
117.5°	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0	234.6	239.6	248.7
120°	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5	250.5	255.5	265.5
122.5°	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7	265.7	270.7	281.5
125°	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5	286.5	292.5	303.4
127.5°	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1	304.0	311.4	322.6
130°	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4	314.4	323.4	335.4
132.5°	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4	323.2	333.0	347.4
135°	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4	337.4	348.4	363.3
137.5°	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6	350.8	361.5	377.5
140°	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4	360.3	370.3	386.3
142.5°	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9	369.1	379.9	394.3
145°	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3	383.3	392.3	407.3
147.5°	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9	397.7	406.5	419.4
150°	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3	407.3	415.2	428.2
152.5°	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6	416.8	424.8	436.2
155°	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2	432.2	438.2	448.2
157.5°	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6	445.4	450.2	459.0
160°	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2	454.2	458.2	466.1
162.5°	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4	461.4	464.6	470.9
165°	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1	471.1	473.1	478.1
167.5°	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3	479.1	480.1	483.9
170°	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1	483.1	484.1	487.1
172.5°	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3	487.1	487.3	489.5
175°	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1	491.1	490.1	492.1
177.5°	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9	493.1	492.3	493.1
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1595.1	1590.7	1584.4	1575.0	1567.4	1555.5	1555.5	1557.4	1557.4	1556.8	1555.5
5°	1546.7	1534.9	1520.8	1504.3	1487.0	1469.7	1466.5	1460.2	1455.5	1452.4	1448.5
7.5°	1495.6	1474.7	1454.1	1431.0	1409.9	1392.5	1380.4	1370.3	1363.9	1357.0	1351.9
10°	1461.0	1435.1	1410.7	1386.4	1359.6	1338.4	1325.1	1315.6	1308.6	1302.3	1299.1
12.5°	1420.2	1390.5	1363.6	1340.5	1311.2	1289.4	1276.7	1272.2	1263.9	1250.7	1243.8
15°	1360.4	1332.9	1300.7	1265.3	1251.2	1224.5	1209.5	1202.5	1197.7	1187.5	1184.4
17.5°	1309.3	1273.3	1237.2	1210.8	1184.5	1162.8	1154.5	1145.7	1139.4	1131.1	1128.6
20°	1268.5	1236.3	1203.2	1175.0	1147.4	1123.9	1116.8	1110.5	1104.2	1100.3	1097.1
22.5°	1227.0	1194.8	1167.4	1141.0	1111.6	1096.2	1088.5	1081.6	1077.2	1074.5	1071.4
25°	1168.7	1140.4	1109.7	1086.1	1062.6	1052.3	1047.6	1043.7	1040.6	1036.6	1035.8
27.5°	1116.5	1085.7	1060.8	1038.8	1021.9	1013.4	1008.8	1006.9	1007.6	1009.0	1009.9
30°	1077.5	1049.2	1028.8	1009.9	994.2	986.3	985.5	985.5	988.7	989.5	991.0
32.5°	1041.7	1018.4	998.0	979.7	967.8	962.4	965.4	965.4	967.9	970.0	972.8
35°	989.5	969.0	953.3	937.6	927.4	929.7	931.3	932.9	936.8	941.5	944.7
37.5°	939.6	921.9	905.5	893.3	888.6	892.8	896.6	899.9	904.4	908.1	911.2
40°	903.8	890.4	874.7	863.7	865.3	867.7	870.8	874.7	878.7	881.0	884.2
42.5°	870.5	856.5	844.6	835.4	837.6	840.6	842.5	844.6	849.1	853.4	855.2
45°	819.7	808.7	797.7	792.2	793.8	795.4	796.9	799.3	803.2	806.4	807.1
47.5°	762.7	755.0	747.6	742.2	744.7	744.1	746.2	751.2	752.4	754.3	758.7
50°	726.2	719.1	710.5	708.9	708.9	708.9	709.7	716.0	716.0	719.1	722.3
52.5°	686.0	681.4	675.9	673.1	671.8	671.8	675.1	678.3	679.5	683.9	687.1
55°	626.4	621.7	616.9	614.6	613.0	614.6	620.9	622.4	626.4	628.7	631.1
57.5°	564.3	560.7	556.9	555.6	555.3	557.4	560.8	565.5	566.5	573.7	577.3
60°	523.4	517.9	514.8	514.8	513.2	520.3	518.7	526.6	528.1	532.9	538.4
62.5°	481.3	473.9	472.7	472.7	474.9	476.9	479.1	482.6	486.6	492.6	496.9
65°	413.4	409.5	415.0	414.2	412.6	417.3	417.3	421.3	426.0	431.5	440.1
67.5°	349.1	347.1	347.5	347.5	349.9	352.6	354.8	358.2	363.9	369.7	375.4
70°	305.7	308.1	304.2	307.3	309.7	310.4	312.0	316.7	323.0	326.9	333.2
72.5°	263.6	263.4	263.9	265.2	267.5	268.9	270.5	275.9	282.8	286.1	291.1
75°	202.8	202.0	204.3	204.3	208.3	209.8	211.4	213.8	220.1	224.8	228.7
77.5°	148.1	149.0	148.5	151.2	150.1	150.4	155.3	157.7	158.3	167.6	169.6
80°	111.6	113.2	114.0	114.7	115.5	114.0	119.5	121.8	121.8	127.3	131.2
82.5°	80.2	81.1	83.2	83.9	84.1	85.7	86.1	87.9	89.8	92.1	97.3
85°	40.1	42.4	43.2	42.4	43.2	41.7	44.0	44.8	45.6	45.6	45.6
87.5°	14.8	15.8	15.8	17.0	17.0	18.2	18.0	16.9	17.1	19.2	17.1
90°	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0	26.0	27.0	28.9
92.5°	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0	66.7	58.9	53.7
95°	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3	243.6	190.7	154.7
97.5°	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8	717.5	588.7	469.3
100°	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9	1096.0	979.2	837.5
102.5°	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3	1267.7	1199.6	1109.8
105°	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6	1397.5	1416.4	1390.5
107.5°	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0	1381.1	1468.5	1504.1
110°	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9	1327.6	1453.3	1523.2



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6	1257.3	1398.2	1488.1
115°	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2	1144.9	1291.6	1400.4
117.5°	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0	1049.9	1181.6	1292.0
120°	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4	997.2	1117.0	1217.8
122.5°	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9	954.9	1065.9	1159.5
125°	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6	902.4	998.2	1078.0
127.5°	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2	856.2	942.7	1015.3
130°	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7	827.5	908.3	976.2
132.5°	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7	800.3	875.6	940.3
135°	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7	761.6	826.5	883.4
137.5°	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2	724.3	780.2	829.5
140°	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8	702.7	750.6	793.6
142.5°	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2	682.0	723.5	760.8
145°	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9	654.8	686.7	715.7
147.5°	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5	634.6	660.4	681.0
150°	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9	621.9	642.8	661.8
152.5°	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1	609.9	628.5	644.2
155°	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9	592.9	607.9	619.9
157.5°	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0	576.3	587.9	597.3
160°	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0	566.0	575.9	582.9
162.5°	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4	554.8	564.0	570.2
165°	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0	539.0	546.0	551.0
167.5°	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2	526.8	530.8	534.4
170°	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1	518.1	522.0	524.0
172.5°	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7	510.9	514.1	515.3
175°	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1	501.1	503.1	503.1
177.5°	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7	495.5	496.3	496.3
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1551.1	1550.5	1554.9	1551.7	1554.9	1550.5	1551.1	1555.5	1556.8	1557.4	1557.4
5°	1443.7	1446.1	1438.2	1438.2	1438.2	1446.1	1443.7	1448.5	1452.4	1455.5	1460.2
7.5°	1348.2	1344.7	1345.0	1340.8	1345.0	1344.7	1348.2	1351.9	1357.0	1363.9	1370.3
10°	1289.7	1285.0	1283.4	1284.2	1283.4	1285.0	1289.7	1299.1	1302.3	1308.6	1315.6
12.5°	1241.3	1240.3	1230.0	1230.1	1230.0	1240.3	1241.3	1243.8	1250.7	1263.9	1272.2
15°	1184.4	1169.5	1167.9	1172.6	1167.9	1169.5	1184.4	1184.4	1187.5	1197.7	1202.5
17.5°	1127.3	1119.5	1119.9	1117.6	1119.9	1119.5	1127.3	1128.6	1131.1	1139.4	1145.7
20°	1097.1	1092.4	1091.6	1086.1	1091.6	1092.4	1097.1	1097.1	1100.3	1104.2	1110.5
22.5°	1069.5	1067.9	1068.4	1062.3	1068.4	1067.9	1069.5	1071.4	1074.5	1077.2	1081.6
25°	1035.1	1039.0	1035.8	1035.8	1035.8	1039.0	1035.1	1035.8	1036.6	1040.6	1043.7
27.5°	1011.8	1011.6	1010.1	1010.1	1010.1	1011.6	1011.8	1009.9	1009.0	1007.6	1006.9
30°	994.2	993.4	995.0	995.0	995.0	993.4	994.2	991.0	989.5	988.7	985.5
32.5°	976.6	977.7	978.0	978.6	978.0	977.7	976.6	972.8	970.0	967.9	965.4
35°	949.4	950.2	952.5	951.0	952.5	950.2	949.4	944.7	941.5	936.8	932.9
37.5°	912.6	916.2	915.4	916.7	915.4	916.2	912.6	911.2	908.1	904.4	899.9
40°	884.9	887.3	886.5	886.5	886.5	887.3	884.9	884.2	881.0	878.7	874.7
42.5°	856.7	858.4	856.3	855.1	856.3	858.4	856.7	855.2	853.4	849.1	844.6
45°	810.3	808.7	811.1	807.9	811.1	808.7	810.3	807.1	806.4	803.2	799.3
47.5°	758.4	760.0	760.6	763.0	760.6	760.0	758.4	758.7	754.3	752.4	751.2
50°	723.8	728.5	728.5	727.8	728.5	728.5	723.8	722.3	719.1	716.0	716.0
52.5°	689.9	692.1	695.2	695.1	695.2	692.1	689.9	687.1	683.9	679.5	678.3
55°	637.4	639.0	640.5	641.3	640.5	639.0	637.4	631.1	628.7	626.4	622.4
57.5°	583.0	582.4	586.1	587.2	586.1	582.4	583.0	577.3	573.7	566.5	565.5
60°	544.6	544.6	550.9	553.3	550.9	544.6	544.6	538.4	532.9	528.1	526.6
62.5°	503.8	506.3	512.6	509.3	512.6	506.3	503.8	496.9	492.6	486.6	482.6
65°	444.0	450.3	449.5	452.7	449.5	450.3	444.0	440.1	431.5	426.0	421.3
67.5°	381.6	385.6	391.2	391.7	391.2	385.6	381.6	375.4	369.7	363.9	358.2
70°	339.5	343.4	346.6	348.9	346.6	343.4	339.5	333.2	326.9	323.0	316.7
72.5°	298.7	300.7	308.2	304.9	308.2	300.7	298.7	291.1	286.1	282.8	275.9
75°	234.2	239.7	244.4	242.1	244.4	239.7	234.2	228.7	224.8	220.1	213.8
77.5°	173.2	178.7	180.9	178.9	180.9	178.7	173.2	169.6	167.6	158.3	157.7
80°	136.8	136.0	140.7	139.9	140.7	136.0	136.8	131.2	127.3	121.8	121.8
82.5°	100.3	99.5	101.7	102.2	101.7	99.5	100.3	97.3	92.1	89.8	87.9
85°	48.7	51.1	47.9	47.2	47.9	51.1	48.7	45.6	45.6	45.6	44.8
87.5°	16.9	17.1	16.7	15.8	16.7	17.1	16.9	17.1	19.2	17.1	16.9
90°	27.9	28.9	29.9	28.9	29.9	28.9	27.9	28.9	27.0	26.0	25.0
92.5°	51.9	48.9	49.9	48.1	49.9	48.9	51.9	53.7	58.9	66.7	84.0
95°	135.8	126.8	119.8	115.8	119.8	126.8	135.8	154.7	190.7	243.6	359.3
97.5°	395.7	350.8	323.8	315.2	323.8	350.8	395.7	469.3	588.7	717.5	895.8
100°	736.7	663.8	624.9	625.9	624.9	663.8	736.7	837.5	979.2	1096.0	1176.9
102.5°	1031.3	973.6	941.1	918.1	941.1	973.6	1031.3	1109.8	1199.6	1267.7	1270.3
105°	1344.5	1306.6	1274.7	1269.7	1274.7	1306.6	1344.5	1390.5	1416.4	1397.5	1297.6
107.5°	1504.9	1492.1	1481.3	1472.1	1481.3	1492.1	1504.9	1504.1	1468.5	1381.1	1219.0
110°	1551.2	1559.2	1557.2	1555.2	1557.2	1559.2	1551.2	1523.2	1453.3	1327.6	1143.9



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1539.2	1563.9	1571.5	1571.9	1571.5	1563.9	1539.2	1488.1	1398.2	1257.3	1069.6
115°	1475.3	1519.2	1539.2	1544.2	1539.2	1519.2	1475.3	1400.4	1291.6	1144.9	971.2
117.5°	1370.1	1420.4	1449.2	1455.9	1449.2	1420.4	1370.1	1292.0	1181.6	1049.9	900.0
120°	1296.6	1352.5	1376.5	1382.5	1376.5	1352.5	1296.6	1217.8	1117.0	997.2	862.4
122.5°	1229.6	1279.9	1306.2	1313.8	1306.2	1279.9	1229.6	1159.5	1065.9	954.9	832.9
125°	1141.9	1185.8	1210.8	1217.8	1210.8	1185.8	1141.9	1078.0	998.2	902.4	793.6
127.5°	1072.2	1109.8	1132.3	1138.7	1132.3	1109.8	1072.2	1015.3	942.7	856.2	759.2
130°	1029.1	1065.1	1086.0	1094.0	1086.0	1065.1	1029.1	976.2	908.3	827.5	737.7
132.5°	990.0	1025.9	1044.5	1050.1	1044.5	1025.9	990.0	940.3	875.6	800.3	717.7
135°	932.3	962.2	980.2	987.2	980.2	962.2	932.3	883.4	826.5	761.6	690.7
137.5°	870.6	901.0	916.1	920.7	916.1	901.0	870.6	829.5	780.2	724.3	666.2
140°	831.5	859.4	875.4	874.4	875.4	859.4	831.5	793.6	750.6	702.7	651.8
142.5°	793.2	817.9	832.3	831.3	832.3	817.9	793.2	760.8	723.5	682.0	638.2
145°	740.6	761.6	769.6	771.6	769.6	761.6	740.6	715.7	686.7	654.8	621.9
147.5°	699.9	714.1	721.7	722.5	721.7	714.1	699.9	681.0	660.4	634.6	608.5
150°	676.8	687.7	693.7	693.7	693.7	687.7	676.8	661.8	642.8	621.9	598.9
152.5°	656.0	666.2	669.8	669.8	669.8	666.2	656.0	644.2	628.5	609.9	590.1
155°	628.9	636.8	638.8	639.8	638.8	636.8	628.9	619.9	607.9	592.9	576.9
157.5°	605.1	611.1	612.7	612.5	612.7	611.1	605.1	597.3	587.9	576.3	563.0
160°	589.9	595.9	595.9	594.9	595.9	595.9	589.9	582.9	575.9	566.0	555.0
162.5°	574.8	579.9	579.9	578.9	579.9	579.9	574.8	570.2	564.0	554.8	545.4
165°	555.0	559.0	558.0	558.0	558.0	559.0	555.0	551.0	546.0	539.0	533.0
167.5°	536.2	539.0	538.0	538.0	538.0	539.0	536.2	534.4	530.8	526.8	522.2
170°	525.0	527.0	526.0	526.0	526.0	527.0	525.0	524.0	522.0	518.1	515.1
172.5°	515.5	517.5	515.7	514.9	515.7	517.5	515.5	515.3	514.1	510.9	508.7
175°	503.1	504.1	503.1	502.1	503.1	504.1	503.1	503.1	503.1	501.1	500.1
177.5°	495.5	496.3	494.7	494.7	494.7	496.3	495.5	496.3	496.3	495.5	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1555.5	1555.5	1567.4	1575.0	1584.4	1590.7	1595.1	1599.5	1607.1	1617.1	1628.4
5°	1466.5	1469.7	1487.0	1504.3	1520.8	1534.9	1546.7	1560.8	1578.1	1599.3	1622.9
7.5°	1380.4	1392.5	1409.9	1431.0	1454.1	1474.7	1495.6	1518.9	1543.2	1574.5	1607.5
10°	1325.1	1338.4	1359.6	1386.4	1410.7	1435.1	1461.0	1486.2	1516.8	1553.8	1596.2
12.5°	1276.7	1289.4	1311.2	1340.5	1363.6	1390.5	1420.2	1452.9	1487.3	1531.8	1579.9
15°	1209.5	1224.5	1251.2	1265.3	1300.7	1332.9	1360.4	1407.6	1451.6	1497.2	1553.0
17.5°	1154.5	1162.8	1184.5	1210.8	1237.2	1273.3	1309.3	1348.6	1392.5	1448.3	1518.1
20°	1116.8	1123.9	1147.4	1175.0	1203.2	1236.3	1268.5	1307.8	1357.3	1416.2	1491.7
22.5°	1088.5	1096.2	1111.6	1141.0	1167.4	1194.8	1227.0	1273.8	1326.5	1384.2	1465.9
25°	1047.6	1052.3	1062.6	1086.1	1109.7	1140.4	1168.7	1212.7	1266.9	1334.5	1416.2
27.5°	1008.8	1013.4	1021.9	1038.8	1060.8	1085.7	1116.5	1153.9	1208.9	1282.3	1369.1
30°	985.5	986.3	994.2	1009.9	1028.8	1049.2	1077.5	1119.9	1171.8	1246.5	1337.6
32.5°	965.4	962.4	967.8	979.7	998.0	1018.4	1041.7	1083.5	1133.5	1206.9	1300.5
35°	931.3	929.7	927.4	937.6	953.3	969.0	989.5	1020.9	1077.5	1145.9	1244.1
37.5°	896.6	892.8	888.6	893.3	905.5	921.9	939.6	967.6	1016.4	1091.6	1185.6
40°	870.8	867.7	865.3	863.7	874.7	890.4	903.8	930.5	976.1	1047.6	1140.4
42.5°	842.5	840.6	837.6	835.4	844.6	856.5	870.5	894.1	939.6	1006.8	1094.5
45°	796.9	795.4	793.8	792.2	797.7	808.7	819.7	837.0	876.3	941.5	1020.9
47.5°	746.2	744.1	744.7	742.2	747.6	755.0	762.7	781.2	818.9	871.6	929.6
50°	709.7	708.9	708.9	708.9	710.5	719.1	726.2	740.3	774.9	827.6	869.2
52.5°	675.1	671.8	671.8	673.1	675.9	681.4	686.0	701.4	731.5	774.8	812.6
55°	620.9	614.6	613.0	614.6	616.9	621.7	626.4	639.0	664.9	697.1	719.1
57.5°	560.8	557.4	555.3	555.6	556.9	560.7	564.3	578.0	598.4	615.2	629.4
60°	518.7	520.3	513.2	514.8	514.8	517.9	523.4	532.1	549.4	561.1	575.3
62.5°	479.1	476.9	474.9	472.7	472.7	473.9	481.3	488.1	502.8	509.0	520.0
65°	417.3	417.3	412.6	414.2	415.0	409.5	413.4	421.3	430.7	433.0	443.3
67.5°	354.8	352.6	349.9	347.5	347.5	347.1	349.1	353.0	360.1	360.9	368.8
70°	312.0	310.4	309.7	307.3	304.2	308.1	305.7	309.7	313.6	314.4	319.1
72.5°	270.5	268.9	267.5	265.2	263.9	263.4	263.6	268.2	270.8	269.7	275.1
75°	211.4	209.8	208.3	204.3	204.3	202.0	202.8	205.9	209.1	206.7	211.4
77.5°	155.3	150.4	150.1	151.2	148.5	149.0	148.1	147.6	149.0	149.2	153.4
80°	119.5	114.0	115.5	114.7	114.0	113.2	111.6	112.4	113.2	114.0	116.3
82.5°	86.1	85.7	84.1	83.9	83.2	81.1	80.2	81.6	82.4	81.9	83.6
85°	44.0	41.7	43.2	42.4	43.2	42.4	40.1	40.1	41.7	40.9	42.4
87.5°	18.0	18.2	17.0	17.0	15.8	15.8	14.8	15.0	15.0	14.6	15.5
90°	24.0	25.0	22.0	19.0	16.0	13.0	11.0	9.0	6.0	4.0	2.0
92.5°	115.8	153.5	168.9	126.8	83.8	57.7	42.9	34.5	26.8	18.4	12.4
95°	480.1	591.9	527.0	363.3	214.6	129.8	90.8	64.9	47.9	36.9	33.9
97.5°	981.4	917.3	671.6	398.7	231.0	149.9	107.8	82.2	67.5	58.9	57.9
100°	1141.9	945.3	638.8	376.3	228.6	158.7	119.8	95.8	81.9	74.9	73.9
102.5°	1149.9	893.4	590.9	357.1	231.8	169.1	133.4	111.8	98.6	92.4	90.6
105°	1089.0	802.5	532.0	343.4	240.6	186.7	155.7	136.8	124.8	118.8	115.8
107.5°	982.4	722.3	494.5	342.4	256.9	209.6	180.9	163.1	151.3	145.5	142.5
110°	915.3	676.8	480.1	346.4	270.5	225.6	197.6	180.7	169.7	164.7	161.7



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	857.0	646.4	472.1	354.4	284.1	242.4	215.2	198.2	187.3	182.3	179.3
115°	786.6	613.9	469.1	367.3	306.4	268.5	241.6	224.6	214.6	208.6	204.6
117.5°	744.0	594.7	470.9	384.5	330.2	292.7	267.7	248.7	239.6	234.6	230.0
120°	721.7	585.9	474.1	397.3	345.4	309.4	284.5	265.5	255.5	250.5	247.5
122.5°	703.3	580.3	479.7	409.3	361.3	326.2	299.7	281.5	270.7	265.7	262.7
125°	679.8	573.0	488.1	428.2	384.3	349.4	322.4	303.4	292.5	286.5	284.5
127.5°	659.0	569.4	497.7	443.8	404.3	370.5	343.6	322.6	311.4	304.0	301.1
130°	647.8	567.0	504.1	454.2	416.2	383.3	356.3	335.4	323.4	314.4	311.4
132.5°	637.4	566.2	508.9	463.8	426.6	394.5	368.3	347.4	333.0	323.2	319.4
135°	623.9	565.0	516.1	476.1	442.2	411.2	384.3	363.3	348.4	337.4	333.4
137.5°	612.1	562.8	520.8	485.3	453.0	423.2	398.3	377.5	361.5	350.8	346.6
140°	604.9	562.0	524.0	490.1	460.2	431.2	406.3	386.3	370.3	360.3	355.4
142.5°	598.5	560.4	526.4	494.9	465.8	437.6	414.2	394.3	379.9	369.1	364.9
145°	589.9	558.0	528.0	500.1	473.1	447.2	424.2	407.3	392.3	383.3	380.3
147.5°	581.5	554.2	528.0	503.3	479.1	455.4	435.8	419.4	406.5	397.7	395.9
150°	575.9	551.0	528.0	504.1	483.1	460.2	442.2	428.2	415.2	407.3	406.3
152.5°	569.6	547.0	525.6	505.7	485.5	465.8	448.6	436.2	424.8	416.8	416.6
155°	560.0	540.0	523.0	506.1	490.1	473.1	459.2	448.2	438.2	432.2	432.2
157.5°	549.2	533.8	519.7	507.1	492.7	479.1	468.3	459.0	450.2	445.4	444.6
160°	542.0	529.0	518.1	507.1	495.1	483.1	473.1	466.1	458.2	454.2	454.2
162.5°	534.8	524.2	514.9	506.3	495.9	485.5	477.1	470.9	464.6	461.4	461.4
165°	525.0	517.1	510.1	504.1	497.1	489.1	482.1	478.1	473.1	471.1	472.1
167.5°	515.7	509.9	505.3	502.5	496.9	491.1	486.7	483.9	480.1	479.1	480.3
170°	510.1	505.1	502.1	500.1	496.1	491.1	489.1	487.1	484.1	483.1	485.1
172.5°	504.5	501.1	499.7	499.3	496.1	491.9	490.7	489.5	487.3	487.1	488.3
175°	498.1	496.1	496.1	497.1	495.1	493.1	492.1	492.1	490.1	491.1	492.1
177.5°	493.9	493.1	493.9	495.5	493.9	493.1	493.1	493.1	492.3	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1632.2	1635.3	1646.0	1653.6	1662.4	1667.4	1672.4	1676.2	1681.2	1682.5	1700.7
5°	1639.4	1655.2	1682.7	1703.1	1728.2	1755.7	1774.6	1783.3	1806.0	1824.9	1862.6
7.5°	1637.4	1670.9	1712.4	1755.4	1801.6	1844.4	1881.5	1925.5	1956.8	2003.8	2050.2
10°	1635.5	1680.3	1733.7	1788.8	1853.2	1912.9	1966.4	2026.1	2075.6	2140.8	2196.6
12.5°	1629.8	1684.1	1758.3	1823.3	1901.6	1984.0	2063.2	2139.9	2183.8	2292.4	2343.8
15°	1615.9	1680.3	1773.0	1872.1	1979.7	2077.2	2177.8	2258.0	2387.6	2482.7	2543.2
17.5°	1589.1	1679.4	1789.4	1908.8	2039.8	2168.2	2282.2	2403.8	2541.4	2656.4	2779.0
20°	1576.6	1675.6	1798.2	1930.2	2066.2	2211.6	2341.3	2487.4	2637.6	2750.7	2907.9
22.5°	1553.3	1665.5	1797.6	1944.7	2090.1	2240.5	2392.2	2539.6	2713.0	2868.9	3018.6
25°	1515.3	1641.0	1777.8	1942.0	2112.6	2263.5	2445.0	2640.7	2821.5	3021.9	3171.2
27.5°	1475.3	1609.6	1746.6	1899.4	2082.8	2261.9	2490.3	2711.4	2932.4	3105.5	3216.0
30°	1444.5	1575.0	1716.5	1870.5	2052.0	2265.0	2520.4	2761.7	2977.1	3125.6	3187.7
32.5°	1411.2	1543.5	1668.7	1830.3	2023.7	2263.1	2539.3	2791.3	2979.6	3078.5	3066.4
35°	1358.9	1469.7	1591.5	1747.1	1975.0	2249.3	2550.3	2793.9	2909.5	2888.3	2727.9
37.5°	1283.4	1376.6	1496.6	1666.9	1918.4	2220.2	2528.3	2711.1	2703.6	2530.8	2298.5
40°	1236.3	1315.6	1431.2	1610.4	1874.4	2201.4	2493.7	2612.4	2511.8	2270.5	1992.3
42.5°	1174.6	1247.7	1363.3	1547.5	1826.0	2163.0	2427.7	2462.1	2265.3	1987.6	1732.6
45°	1079.1	1143.5	1263.0	1453.2	1753.4	2079.5	2266.6	2182.5	1917.6	1630.8	1436.7
47.5°	976.4	1043.4	1158.3	1353.7	1648.4	1954.0	2043.1	1864.2	1592.3	1359.6	1181.4
50°	911.7	976.1	1088.5	1285.8	1577.3	1850.8	1887.8	1656.7	1406.8	1202.5	1056.3
52.5°	846.3	907.0	1017.5	1215.3	1494.4	1731.4	1708.6	1473.1	1243.3	1069.2	954.4
55°	749.0	806.4	911.7	1097.1	1351.0	1538.8	1456.3	1231.5	1041.3	906.2	818.9
57.5°	661.9	716.9	807.8	975.3	1196.0	1325.1	1220.1	1030.7	879.4	775.4	710.3
60°	602.8	651.5	738.0	893.6	1085.4	1183.6	1079.9	912.5	785.1	701.8	643.7
62.5°	546.8	589.3	669.4	810.6	977.2	1059.7	954.7	813.1	704.7	630.8	581.4
65°	462.1	500.6	571.4	681.4	818.1	873.2	782.8	668.0	583.9	528.9	495.9
67.5°	384.8	417.5	478.6	565.2	665.8	705.9	637.1	548.3	484.9	440.7	414.5
70°	333.2	361.5	409.5	484.1	575.3	605.9	541.5	468.4	422.0	386.7	362.3
72.5°	289.8	310.6	354.1	411.8	487.9	512.3	467.3	403.0	359.8	333.2	313.9
75°	220.8	238.1	266.4	312.8	365.5	379.6	345.8	305.7	276.6	257.8	242.8
77.5°	159.2	172.0	192.4	221.0	257.5	270.2	248.8	222.1	200.9	188.1	179.8
80°	120.2	130.5	147.8	171.3	193.3	200.4	187.8	167.4	152.5	145.4	138.3
82.5°	88.8	94.6	105.0	121.0	136.1	144.5	133.8	121.5	113.5	107.0	104.4
85°	44.8	47.9	52.7	58.9	68.4	71.5	67.6	64.4	59.7	55.8	55.8
87.5°	17.1	17.5	20.0	21.7	24.6	27.1	27.1	26.4	26.4	25.5	25.1
90°	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0	25.0
92.5°	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8	84.0
95°	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1	359.3
97.5°	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4	895.8
100°	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9	1176.9
102.5°	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9	1270.3
105°	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0	1297.6
107.5°	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4	1219.0
110°	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3	1143.9





TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0	1069.6
115°	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6	971.2
117.5°	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0	900.0
120°	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7	862.4
122.5°	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3	832.9
125°	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8	793.6
127.5°	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0	759.2
130°	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8	737.7
132.5°	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4	717.7
135°	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9	690.7
137.5°	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1	666.2
140°	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9	651.8
142.5°	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5	638.2
145°	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9	621.9
147.5°	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5	608.5
150°	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9	598.9
152.5°	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6	590.1
155°	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0	576.9
157.5°	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2	563.0
160°	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0	555.0
162.5°	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8	545.4
165°	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0	533.0
167.5°	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7	522.2
170°	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1	515.1
172.5°	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5	508.7
175°	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1	500.1
177.5°	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1707.0	1707.6	1714.6	1719.6	1717.1	1720.2	1721.5
5°	1865.0	1893.3	1908.2	1919.2	1920.0	1920.8	1927.1
7.5°	2089.0	2119.3	2141.5	2175.1	2185.2	2196.6	2193.3
10°	2252.5	2297.2	2335.8	2356.2	2378.2	2410.4	2384.5
12.5°	2405.2	2484.6	2543.2	2575.0	2595.7	2602.2	2589.5
15°	2657.2	2760.9	2816.7	2815.2	2885.9	2916.6	2868.6
17.5°	2888.3	2984.0	3060.7	3100.0	3158.9	3172.0	3166.0
20°	3029.7	3134.3	3194.0	3261.6	3292.2	3319.7	3324.4
22.5°	3151.7	3245.5	3309.7	3365.9	3391.6	3404.6	3412.5
25°	3277.3	3351.2	3389.7	3409.3	3416.4	3414.8	3404.6
27.5°	3268.6	3274.3	3231.9	3190.2	3153.0	3111.0	3096.5
30°	3183.8	3117.7	2999.9	2933.1	2834.8	2757.0	2788.4
32.5°	2960.6	2829.2	2696.8	2550.8	2429.9	2395.5	2360.9
35°	2526.7	2295.7	2160.5	2003.3	1940.4	1877.6	1834.3
37.5°	2044.2	1865.5	1705.1	1602.3	1539.3	1499.5	1478.2
40°	1767.5	1606.4	1474.4	1391.1	1343.1	1298.3	1292.1
42.5°	1546.9	1397.1	1297.7	1231.4	1185.3	1166.3	1152.5
45°	1266.9	1162.4	1095.6	1048.4	1017.8	1006.0	990.3
47.5°	1072.3	998.4	948.3	916.2	893.1	884.3	883.1
50°	963.5	902.2	865.3	840.1	822.1	818.9	806.4
52.5°	881.8	828.7	799.9	777.9	764.9	756.1	752.3
55°	765.5	730.1	704.2	691.6	681.4	672.7	672.7
57.5°	669.8	640.2	623.1	612.4	609.2	603.1	599.2
60°	610.7	585.5	572.2	562.7	556.4	557.2	550.1
62.5°	552.8	536.5	523.7	514.3	506.8	506.9	507.4
65°	470.8	458.2	448.8	445.6	440.9	435.4	437.0
67.5°	398.9	387.1	379.8	374.4	372.8	369.9	374.4
70°	347.4	338.7	333.2	328.5	326.9	327.7	331.7
72.5°	300.2	294.1	290.5	288.3	284.8	285.0	287.6
75°	235.8	231.1	227.9	225.6	224.8	224.8	224.8
77.5°	173.2	172.1	170.7	167.2	167.4	168.3	168.5
80°	136.8	134.4	133.6	132.0	129.7	128.1	132.0
82.5°	102.2	99.8	99.0	98.7	95.1	94.8	98.1
85°	55.0	52.7	53.4	52.7	52.7	51.9	51.9
87.5°	24.7	24.3	24.0	24.5	24.0	23.6	24.7
90°	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P332074

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)