

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831053

Luminaire Tested: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831053  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D1025U840-4F0-1E-UDD-G4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8404.2 lumens  
Efficiency: N/A  
Efficacy: 137.8 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 61  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831053  
CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

### Luminous Intensity Polar Plot





TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53	48				
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41				
3	84	75	67	62	78	70	63	58	60	56	52	52	48	46	44	42	39	36				
4	77	66	59	53	71	62	56	50	54	49	45	47	43	40	40	37	35	31				
5	71	60	52	46	66	56	49	44	49	44	39	42	38	35	36	33	31	28				
6	66	54	46	40	61	51	44	39	45	39	35	39	34	31	33	30	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22				
8	57	45	37	32	53	42	36	31	37	32	28	33	29	25	29	25	23	20				
9	53	41	34	29	50	39	32	28	35	29	25	30	26	23	27	23	21	19				
10	50	38	31	26	47	36	30	25	32	27	23	28	24	21	25	22	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	31174	31174	31174	31174	31174
5°	39425	37211	31453	25348	23292
10°	39808	41013	31244	20205	17656
15°	29983	38078	31032	17111	14931
20°	20890	30812	30636	14963	13562
25°	15930	23695	29960	13767	12721
30°	13781	18825	28881	12920	12044
35°	12786	15895	27638	12309	11567
40°	12105	14258	25891	11727	11405
45°	11702	13195	23669	11272	11333
50°	11501	12355	21043	10860	11275
55°	11072	11740	18462	10466	11324
60°	10676	11080	15913	10097	11138
65°	10030	10458	13726	9704	10919
70°	9262	9665	11673	9051	10279
75°	8384	8663	10006	8413	9391
80°	6912	7581	7916	7333	7916
85°	5483	6138	5805	6225	6311

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 27026 cd/sqm



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	273.8	3.3
10°-20°	681.2	8.1
20°-30°	806.5	9.6
30°-40°	811.0	9.6
40°-50°	744.0	8.9
50°-60°	614.1	7.3
60°-70°	434.4	5.2
70°-80°	231.9	2.8
80°-90°	61.6	0.7
90°-100°	270.2	3.2
100°-110°	791.1	9.4
110°-120°	772.6	9.2
120°-130°	615.3	7.3
130°-140°	485.4	5.8
140°-150°	362.1	4.3
150°-160°	252.5	3.0
160°-170°	148.3	1.8
170°-180°	48.2	0.6
0°-30°	1761.5	21.0
0°-40°	2572.5	30.6
0°-60°	3930.6	46.8
0°-90°	4658.5	55.4
90°-120°	1833.9	21.8
90°-150°	3296.7	39.2
90°-180°	3746.0	44.6
0°-180°	8404.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	2896	2896	2896	2896	2896	
5°	3649	3444	2911	2346	2156	348
15°	2691	3417	2785	1536	1340	743
25°	1341	1995	2523	1159	1071	633
35°	973	1210	2103	937	880	611
45°	769	867	1555	740	744	595
55°	590	626	984	558	603	528
65°	394	411	539	381	429	391
75°	202	208	241	202	226	212
85°	44	50	47	50	51	50
90°	29	25	2	25	29	18
95°	117	598	34	598	117	190
105°	1282	810	117	810	1282	1279
115°	1559	620	207	620	1559	1521
125°	1230	579	287	579	1230	1113
135°	997	570	337	570	997	773
145°	779	564	384	564	779	495
155°	646	545	436	545	646	301
165°	564	522	477	522	564	161
175°	507	501	497	501	507	49
180°	498	498	498	498	498	



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2
2.5°	3264.4	3261.1	3257.7	3240.9	3224.1	3216.1	3208.0	3183.8	3159.6	3132.7	3105.9
5°	3648.8	3658.2	3667.6	3656.9	3646.1	3613.2	3580.3	3536.6	3492.9	3443.9	3394.8
7.5°	3826.2	3831.6	3837.0	3830.2	3823.5	3814.8	3806.1	3767.1	3728.1	3677.7	3627.3
10°	3642.1	3654.2	3666.3	3692.5	3718.7	3748.3	3777.8	3772.5	3767.1	3752.3	3737.5
12.5°	3237.6	3252.4	3267.1	3319.5	3372.0	3439.2	3506.4	3564.1	3621.9	3662.3	3702.6
15°	2690.6	2731.6	2772.6	2820.3	2868.0	2966.8	3065.5	3187.2	3308.8	3417.0	3525.2
17.5°	2216.2	2231.6	2247.1	2298.1	2349.2	2473.5	2597.8	2738.3	2878.7	3058.2	3237.6
20°	1823.7	1837.8	1852.0	1919.2	1986.4	2083.8	2181.2	2339.1	2497.1	2689.9	2882.8
22.5°	1532.1	1554.3	1576.4	1614.1	1651.7	1745.1	1838.5	1979.0	2119.4	2332.4	2545.4
25°	1341.3	1357.4	1373.5	1396.4	1419.2	1493.8	1568.4	1684.0	1799.5	1995.1	2190.6
27.5°	1210.9	1217.6	1224.3	1247.2	1270.0	1318.4	1366.8	1466.2	1565.7	1731.7	1897.7
30°	1108.8	1113.5	1118.2	1138.3	1158.5	1191.4	1224.3	1296.2	1368.1	1514.6	1661.1
32.5°	1037.5	1040.9	1044.2	1059.7	1075.2	1098.7	1122.2	1174.6	1227.0	1348.0	1468.9
35°	973.0	975.0	977.0	988.5	999.9	1017.4	1034.8	1074.5	1114.1	1209.6	1305.0
37.5°	916.6	919.3	921.9	928.7	935.4	950.8	966.3	997.9	1029.5	1102.7	1176.0
40°	861.5	866.2	870.9	875.6	880.3	893.1	905.8	930.0	954.2	1014.7	1075.2
42.5°	814.4	819.1	823.8	825.9	827.9	835.3	842.7	864.8	887.0	932.0	977.0
45°	768.7	770.8	772.8	774.8	776.8	782.8	788.9	808.4	827.9	866.8	905.8
47.5°	727.1	727.1	727.1	728.4	729.8	735.1	740.5	754.6	768.7	799.0	829.2
50°	686.8	686.8	686.8	684.7	682.7	686.1	689.4	700.2	710.9	737.8	764.7
52.5°	638.4	638.4	638.4	639.0	639.7	639.7	639.7	649.1	658.5	682.7	706.9
55°	590.0	592.7	595.4	593.4	591.3	592.7	594.0	600.1	606.1	625.6	645.1
57.5°	541.6	543.0	544.3	543.6	543.0	543.6	544.3	549.7	555.0	569.8	584.6
60°	495.9	495.9	495.9	494.6	493.2	494.6	495.9	498.6	501.3	514.7	528.2
62.5°	444.8	445.5	446.2	446.9	447.5	446.2	444.8	448.2	451.6	461.6	471.7
65°	393.8	394.4	395.1	397.1	399.2	397.8	396.5	399.8	403.2	410.6	418.0
67.5°	348.1	346.7	345.4	346.1	346.7	348.8	350.8	351.4	352.1	360.2	368.2
70°	294.3	295.7	297.0	296.3	295.7	296.3	297.0	299.0	301.0	307.1	313.1
72.5°	245.9	246.6	247.3	247.3	247.3	248.6	250.0	252.0	254.0	257.4	260.7
75°	201.6	201.6	201.6	202.9	204.3	205.0	205.6	205.6	205.6	208.3	211.0
77.5°	153.2	156.6	159.9	159.3	158.6	159.9	161.3	163.3	165.3	166.6	168.0
80°	111.5	111.5	111.5	112.2	112.9	114.9	116.9	118.3	119.6	122.3	125.0
82.5°	71.2	71.9	72.6	74.6	76.6	77.9	79.3	81.3	83.3	83.3	83.3
85°	44.4	43.0	41.7	43.0	44.4	45.7	47.0	47.7	48.4	49.7	51.1
87.5°	21.5	21.5	21.5	21.5	21.5	22.2	22.8	22.8	22.8	22.8	22.8
90°	29.2	30.2	29.2	28.2	29.2	27.2	26.2	25.2	24.2	25.2	22.2
92.5°	53.4	55.4	54.4	58.5	60.5	67.5	77.6	99.8	140.1	187.5	207.7
95°	116.9	121.0	128.0	137.1	156.2	192.5	246.0	362.9	484.9	597.8	532.2
97.5°	239.9	251.0	275.2	313.5	381.0	495.9	629.0	833.6	950.6	919.3	686.5
100°	632.0	631.0	670.3	743.9	845.7	988.9	1106.8	1188.5	1153.2	954.6	645.1
102.5°	1001.0	1030.2	1061.5	1115.9	1189.5	1267.1	1323.5	1306.4	1163.3	889.1	584.7
105°	1282.2	1287.3	1319.5	1357.8	1404.2	1430.4	1411.2	1310.4	1099.8	810.5	537.3
107.5°	1465.7	1476.8	1489.9	1508.0	1514.1	1486.8	1408.2	1250.0	1009.0	740.9	503.0
110°	1570.5	1572.5	1574.5	1566.5	1538.2	1467.7	1340.7	1155.2	924.4	683.4	484.9



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1591.7	1590.7	1580.6	1551.4	1493.9	1398.1	1252.0	1061.5	850.8	645.1	474.8
115°	1559.4	1554.4	1534.2	1489.9	1414.3	1304.4	1156.2	980.8	794.3	619.9	473.8
117.5°	1488.9	1481.8	1451.6	1402.2	1323.5	1209.6	1073.5	918.3	757.0	602.8	474.8
120°	1396.1	1390.1	1365.9	1309.4	1229.8	1128.0	1007.0	870.9	728.8	591.7	478.8
122.5°	1309.4	1301.4	1274.1	1224.8	1156.2	1063.5	953.6	833.6	705.6	584.7	485.9
125°	1229.8	1222.7	1197.5	1153.2	1088.7	1008.0	911.3	801.4	686.5	578.6	492.9
127.5°	1161.2	1155.2	1132.0	1093.7	1035.2	960.6	871.9	772.1	668.3	575.6	501.0
130°	1104.8	1096.7	1075.6	1039.3	985.9	917.3	835.7	744.9	654.2	572.6	509.1
132.5°	1049.4	1044.3	1026.2	989.9	940.5	876.0	801.4	719.7	641.1	571.6	515.1
135°	996.9	989.9	971.7	941.5	892.1	834.6	769.1	697.6	630.0	570.5	521.1
137.5°	941.5	935.4	920.3	889.1	846.7	795.3	736.9	676.4	619.9	568.5	525.2
140°	883.0	884.0	867.9	839.7	801.4	758.0	709.7	658.2	610.9	567.5	529.2
142.5°	828.6	829.6	815.5	791.3	760.1	723.8	683.4	641.1	602.8	565.5	532.2
145°	779.2	777.2	769.1	748.0	722.8	693.5	661.3	628.0	595.7	563.5	533.2
147.5°	736.9	735.9	727.8	712.7	692.5	671.3	644.1	616.9	588.7	560.5	533.2
150°	700.6	700.6	694.5	683.4	668.3	649.2	628.0	604.8	581.6	556.4	533.2
152.5°	670.3	670.3	667.3	657.2	646.1	631.0	612.9	593.7	573.6	551.4	530.2
155°	646.1	645.1	643.1	635.1	626.0	613.9	598.8	582.6	565.5	545.3	528.2
157.5°	623.0	623.0	620.9	614.9	606.8	596.8	584.7	570.5	556.4	540.3	525.2
160°	600.8	601.8	601.8	595.7	588.7	581.6	571.6	560.5	547.4	534.3	523.2
162.5°	580.6	581.6	581.6	576.6	572.6	566.5	557.4	548.4	538.3	528.2	519.1
165°	563.5	563.5	564.5	560.5	556.4	551.4	544.3	538.3	530.2	522.2	515.1
167.5°	546.4	546.4	547.4	544.3	542.3	538.3	534.3	529.2	522.2	516.1	511.1
170°	531.2	531.2	532.2	530.2	529.2	527.2	523.2	520.1	515.1	510.1	507.0
172.5°	517.1	518.1	520.1	518.1	518.1	517.1	514.1	512.1	508.0	505.0	504.0
175°	507.0	508.0	509.1	508.0	508.0	508.0	506.0	505.0	503.0	501.0	501.0
177.5°	500.0	500.0	502.0	501.0	502.0	502.0	501.0	500.0	499.0	498.0	499.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2
2.5°	3097.8	3089.7	3060.2	3030.6	2997.0	2963.4	2938.5	2913.7	2876.7	2839.8	2809.5
5°	3357.2	3319.5	3257.1	3194.6	3109.9	3025.2	2968.1	2911.0	2834.4	2757.8	2696.6
7.5°	3562.8	3498.3	3410.9	3323.6	3212.7	3101.8	2997.0	2892.2	2775.2	2658.3	2562.9
10°	3693.8	3650.2	3549.4	3448.6	3300.1	3151.6	3005.1	2858.6	2708.1	2557.5	2431.2
12.5°	3706.6	3710.6	3617.9	3525.2	3357.2	3189.2	3011.1	2833.0	2643.5	2454.0	2306.9
15°	3594.4	3663.6	3612.5	3561.5	3392.1	3222.8	3003.7	2784.7	2566.3	2347.9	2177.9
17.5°	3386.1	3534.6	3542.0	3549.4	3380.0	3210.7	2968.1	2725.5	2478.2	2231.0	2052.2
20°	3101.8	3320.9	3396.2	3471.4	3333.7	3195.9	2935.2	2674.5	2397.6	2120.7	1933.3
22.5°	2811.5	3077.6	3215.4	3353.1	3251.0	3148.9	2871.3	2593.8	2301.5	2009.2	1819.0
25°	2480.9	2771.2	2982.9	3194.6	3132.1	3069.6	2796.1	2522.6	2211.5	1900.3	1706.1
27.5°	2192.6	2487.6	2743.0	2998.3	2984.9	2971.5	2700.0	2428.5	2110.0	1791.5	1604.0
30°	1936.0	2210.8	2496.4	2782.0	2814.9	2847.8	2585.8	2323.7	2004.5	1685.3	1504.5
32.5°	1708.8	1948.7	2255.1	2561.6	2626.1	2690.6	2454.0	2217.5	1901.7	1585.9	1411.8
35°	1522.7	1740.4	2046.8	2353.3	2433.9	2514.5	2308.9	2103.3	1795.5	1487.7	1321.8
37.5°	1358.1	1540.2	1839.2	2138.2	2237.0	2335.8	2151.7	1967.5	1679.3	1391.0	1238.4
40°	1221.6	1368.1	1643.0	1917.8	2032.0	2146.3	1994.4	1842.6	1569.1	1295.6	1155.1
42.5°	1107.4	1237.8	1487.1	1736.4	1845.9	1955.4	1827.1	1698.7	1455.5	1212.2	1083.9
45°	1010.0	1114.1	1340.6	1567.0	1671.2	1775.4	1665.1	1554.9	1340.6	1126.2	1006.6
47.5°	918.6	1008.0	1201.5	1395.0	1487.7	1580.5	1494.5	1408.5	1227.0	1045.6	937.4
50°	836.6	908.5	1077.8	1247.2	1327.8	1408.5	1332.5	1256.6	1107.4	958.2	864.2
52.5°	765.4	823.8	965.6	1107.4	1176.6	1245.8	1180.7	1115.5	997.2	878.9	797.0
55°	694.8	744.5	867.5	990.5	1037.5	1084.6	1034.2	983.8	888.3	792.9	723.7
57.5°	629.0	673.3	774.1	874.9	911.2	947.5	901.8	856.1	784.2	712.3	654.5
60°	564.5	600.7	684.7	768.7	790.9	813.1	776.1	739.2	688.8	638.4	586.6
62.5°	504.7	537.6	600.1	662.6	677.3	692.1	663.9	635.7	597.4	559.1	518.8
65°	442.8	467.7	518.8	569.8	579.2	588.6	563.8	538.9	510.0	481.1	451.6
67.5°	385.7	403.2	444.8	486.5	487.2	487.9	467.7	447.5	431.4	415.3	391.8
70°	329.9	346.7	374.3	401.8	402.5	403.2	387.1	370.9	358.8	346.7	329.3
72.5°	272.8	284.9	305.7	326.6	325.2	323.9	313.8	303.7	294.3	284.9	272.1
75°	221.1	231.2	245.3	259.4	255.3	251.3	245.9	240.6	232.5	224.4	216.4
77.5°	174.0	180.1	188.2	196.2	193.5	190.8	186.1	181.4	175.4	169.3	166.0
80°	127.7	130.4	135.7	141.1	139.8	138.4	133.1	127.7	126.3	125.0	120.3
82.5°	86.7	90.0	91.4	92.7	92.1	91.4	87.4	83.3	82.0	80.6	80.0
85°	51.7	52.4	53.1	53.8	51.7	49.7	48.4	47.0	47.0	47.0	46.4
87.5°	23.5	24.2	24.2	24.2	23.5	22.8	21.5	20.2	20.8	21.5	21.5
90°	19.2	16.1	13.1	11.1	9.1	6.0	4.0	2.0	4.0	6.0	9.1
92.5°	155.2	101.8	69.6	51.4	41.3	32.3	22.2	15.1	22.2	32.3	41.3
95°	366.9	216.7	131.0	91.7	65.5	48.4	37.3	34.3	37.3	48.4	65.5
97.5°	408.3	233.9	149.2	105.8	79.6	64.5	55.4	54.4	55.4	64.5	79.6
100°	380.0	230.8	160.3	121.0	96.8	82.7	75.6	74.6	75.6	82.7	96.8
102.5°	355.8	234.9	173.4	138.1	116.9	103.8	97.8	95.8	97.8	103.8	116.9
105°	346.8	242.9	188.5	157.3	138.1	126.0	120.0	116.9	120.0	126.0	138.1
107.5°	344.7	256.0	207.7	178.4	160.3	148.2	142.1	139.1	142.1	148.2	160.3
110°	349.8	273.2	227.8	199.6	182.5	171.4	166.3	163.3	166.3	171.4	182.5





TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	359.9	290.3	249.0	221.8	204.6	193.5	188.5	185.5	188.5	193.5	204.6
115°	371.0	309.5	271.2	243.9	226.8	216.7	210.7	206.6	210.7	216.7	226.8
117.5°	385.1	329.6	291.3	266.1	247.0	237.9	232.9	227.8	232.9	237.9	247.0
120°	401.2	348.8	312.5	287.3	268.1	258.1	253.0	250.0	253.0	258.1	268.1
122.5°	416.3	368.9	333.7	306.4	288.3	277.2	272.2	269.1	272.2	277.2	288.3
125°	432.4	388.1	352.8	325.6	306.4	295.4	289.3	287.3	289.3	295.4	306.4
127.5°	445.5	405.2	371.0	343.7	322.6	311.5	304.4	301.4	304.4	311.5	322.6
130°	458.7	420.3	387.1	359.9	338.7	326.6	317.5	314.5	317.5	326.6	338.7
132.5°	470.7	433.5	401.2	375.0	353.8	338.7	328.6	324.6	328.6	338.7	353.8
135°	480.8	446.6	415.3	388.1	366.9	351.8	340.7	336.7	340.7	351.8	366.9
137.5°	488.9	455.6	425.4	400.2	379.0	362.9	351.8	347.8	351.8	362.9	379.0
140°	494.9	464.7	435.5	410.3	390.1	374.0	363.9	358.9	363.9	374.0	390.1
142.5°	501.0	471.8	443.5	420.3	400.2	386.1	375.0	371.0	375.0	386.1	400.2
145°	505.0	477.8	451.6	428.4	411.3	396.2	387.1	384.1	387.1	396.2	411.3
147.5°	508.0	482.8	458.7	438.5	421.4	408.3	399.2	397.2	399.2	408.3	421.4
150°	509.1	487.9	464.7	446.6	432.4	419.3	411.3	410.3	411.3	419.3	432.4
152.5°	511.1	490.9	471.8	454.6	442.5	431.4	423.4	423.4	423.4	431.4	442.5
155°	511.1	494.9	477.8	463.7	452.6	442.5	436.5	436.5	436.5	442.5	452.6
157.5°	512.1	497.0	482.8	471.8	461.7	452.6	447.6	446.6	447.6	452.6	461.7
160°	512.1	500.0	487.9	477.8	470.7	462.7	458.7	458.7	458.7	462.7	470.7
162.5°	511.1	501.0	490.9	482.8	476.8	470.7	467.7	467.7	467.7	470.7	476.8
165°	509.1	502.0	493.9	486.9	482.8	477.8	475.8	476.8	475.8	477.8	482.8
167.5°	508.0	502.0	495.9	490.9	487.9	483.9	482.8	483.9	482.8	483.9	487.9
170°	505.0	501.0	495.9	493.9	491.9	488.9	487.9	489.9	487.9	488.9	491.9
172.5°	504.0	501.0	497.0	495.9	494.9	492.9	492.9	493.9	492.9	492.9	494.9
175°	502.0	500.0	498.0	497.0	497.0	494.9	495.9	497.0	495.9	494.9	497.0
177.5°	501.0	499.0	498.0	498.0	498.0	497.0	498.0	499.0	498.0	497.0	498.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2
2.5°	2779.3	2753.1	2726.9	2706.7	2686.5	2652.3	2618.0	2609.9	2601.9	2590.5	2579.0
5°	2635.5	2571.0	2506.5	2448.7	2390.9	2345.9	2300.8	2271.3	2241.7	2220.2	2198.7
7.5°	2467.5	2370.7	2274.0	2205.4	2136.9	2071.7	2006.5	1985.7	1964.8	1936.6	1908.4
10°	2304.9	2198.0	2091.2	2001.8	1912.4	1848.6	1784.8	1759.2	1733.7	1698.1	1662.5
12.5°	2159.7	2042.8	1925.9	1835.8	1745.8	1684.0	1622.1	1585.2	1548.2	1528.1	1507.9
15°	2007.9	1882.9	1757.9	1674.6	1591.2	1535.5	1479.7	1447.4	1415.2	1395.7	1376.2
17.5°	1873.5	1749.8	1626.2	1546.2	1466.2	1415.2	1364.1	1335.9	1307.7	1292.9	1278.1
20°	1745.8	1624.8	1503.9	1425.9	1348.0	1306.3	1264.7	1246.5	1228.4	1216.3	1204.2
22.5°	1628.9	1509.9	1391.0	1324.5	1257.9	1224.3	1190.7	1178.0	1165.2	1155.1	1145.0
25°	1511.9	1405.8	1299.6	1243.2	1186.7	1159.2	1131.6	1118.8	1106.1	1096.0	1085.9
27.5°	1416.5	1315.1	1213.6	1165.2	1116.8	1095.3	1073.8	1063.7	1053.7	1044.2	1034.8
30°	1323.8	1233.1	1142.4	1100.7	1059.0	1039.5	1020.1	1010.0	999.9	991.2	982.4
32.5°	1237.8	1159.8	1081.9	1043.6	1005.3	989.1	973.0	960.9	948.8	942.1	935.4
35°	1155.8	1085.9	1016.0	984.4	952.9	936.7	920.6	910.5	900.4	895.1	889.7
37.5°	1085.9	1023.4	960.9	930.7	900.4	885.0	869.5	860.8	852.1	850.0	848.0
40°	1014.7	960.9	907.2	877.6	848.0	834.6	821.2	815.8	810.4	809.1	807.7
42.5°	955.5	903.1	850.7	823.8	797.0	785.5	774.1	771.4	768.7	770.8	772.8
45°	887.0	843.3	799.6	774.8	749.9	740.5	731.1	729.1	727.1	731.1	735.1
47.5°	829.2	788.9	748.6	725.1	701.5	694.8	688.1	687.4	686.8	692.1	697.5
50°	770.1	731.1	692.1	673.3	654.5	648.5	642.4	644.4	646.4	655.2	663.9
52.5°	715.0	678.7	642.4	624.9	607.5	603.4	599.4	604.1	608.8	618.2	627.6
55°	654.5	621.6	588.6	575.2	561.8	557.7	553.7	563.1	572.5	581.3	590.0
57.5°	596.7	567.8	538.9	526.8	514.7	514.1	513.4	522.1	530.9	540.3	549.7
60°	534.9	510.7	486.5	477.1	467.7	469.0	470.4	480.5	490.5	497.9	505.3
62.5°	478.4	458.3	438.1	429.4	420.7	424.0	427.4	437.5	447.5	456.3	465.0
65°	422.0	405.2	388.4	382.4	376.3	381.0	385.7	394.4	403.2	409.2	415.3
67.5°	368.2	354.1	340.0	335.3	330.6	335.3	340.0	348.8	357.5	363.5	369.6
70°	311.8	300.4	288.9	285.6	282.2	287.6	293.0	300.4	307.8	313.8	319.9
72.5°	259.4	250.6	241.9	241.2	240.6	245.3	250.0	257.4	264.8	268.8	272.8
75°	208.3	203.6	198.9	198.2	197.6	202.3	207.0	211.0	215.0	218.4	221.8
77.5°	162.6	158.6	154.6	155.2	155.9	159.3	162.6	166.6	170.7	172.7	174.7
80°	115.6	114.2	112.9	114.2	115.6	118.3	121.0	123.6	126.3	127.7	129.0
82.5°	79.3	77.9	76.6	78.6	80.6	82.7	84.7	86.7	88.7	89.4	90.0
85°	45.7	47.7	49.7	49.7	49.7	50.4	51.1	51.7	52.4	51.7	51.1
87.5°	21.5	22.2	22.8	22.8	22.8	23.5	24.2	24.2	24.2	23.5	22.8
90°	11.1	13.1	16.1	19.2	22.2	25.2	24.2	25.2	26.2	27.2	29.2
92.5°	51.4	69.6	101.8	155.2	207.7	187.5	140.1	99.8	77.6	67.5	60.5
95°	91.7	131.0	216.7	366.9	532.2	597.8	484.9	362.9	246.0	192.5	156.2
97.5°	105.8	149.2	233.9	408.3	686.5	919.3	950.6	833.6	629.0	495.9	381.0
100°	121.0	160.3	230.8	380.0	645.1	954.6	1153.2	1188.5	1106.8	988.9	845.7
102.5°	138.1	173.4	234.9	355.8	584.7	889.1	1163.3	1306.4	1323.5	1267.1	1189.5
105°	157.3	188.5	242.9	346.8	537.3	810.5	1099.8	1310.4	1411.2	1430.4	1404.2
107.5°	178.4	207.7	256.0	344.7	503.0	740.9	1009.0	1250.0	1408.2	1486.8	1514.1
110°	199.6	227.8	273.2	349.8	484.9	683.4	924.4	1155.2	1340.7	1467.7	1538.2



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	221.8	249.0	290.3	359.9	474.8	645.1	850.8	1061.5	1252.0	1398.1	1493.9
115°	243.9	271.2	309.5	371.0	473.8	619.9	794.3	980.8	1156.2	1304.4	1414.3
117.5°	266.1	291.3	329.6	385.1	474.8	602.8	757.0	918.3	1073.5	1209.6	1323.5
120°	287.3	312.5	348.8	401.2	478.8	591.7	728.8	870.9	1007.0	1128.0	1229.8
122.5°	306.4	333.7	368.9	416.3	485.9	584.7	705.6	833.6	953.6	1063.5	1156.2
125°	325.6	352.8	388.1	432.4	492.9	578.6	686.5	801.4	911.3	1008.0	1088.7
127.5°	343.7	371.0	405.2	445.5	501.0	575.6	668.3	772.1	871.9	960.6	1035.2
130°	359.9	387.1	420.3	458.7	509.1	572.6	654.2	744.9	835.7	917.3	985.9
132.5°	375.0	401.2	433.5	470.7	515.1	571.6	641.1	719.7	801.4	876.0	940.5
135°	388.1	415.3	446.6	480.8	521.1	570.5	630.0	697.6	769.1	834.6	892.1
137.5°	400.2	425.4	455.6	488.9	525.2	568.5	619.9	676.4	736.9	795.3	846.7
140°	410.3	435.5	464.7	494.9	529.2	567.5	610.9	658.2	709.7	758.0	801.4
142.5°	420.3	443.5	471.8	501.0	532.2	565.5	602.8	641.1	683.4	723.8	760.1
145°	428.4	451.6	477.8	505.0	533.2	563.5	595.7	628.0	661.3	693.5	722.8
147.5°	438.5	458.7	482.8	508.0	533.2	560.5	588.7	616.9	644.1	671.3	692.5
150°	446.6	464.7	487.9	509.1	533.2	556.4	581.6	604.8	628.0	649.2	668.3
152.5°	454.6	471.8	490.9	511.1	530.2	551.4	573.6	593.7	612.9	631.0	646.1
155°	463.7	477.8	494.9	511.1	528.2	545.3	565.5	582.6	598.8	613.9	626.0
157.5°	471.8	482.8	497.0	512.1	525.2	540.3	556.4	570.5	584.7	596.8	606.8
160°	477.8	487.9	500.0	512.1	523.2	534.3	547.4	560.5	571.6	581.6	588.7
162.5°	482.8	490.9	501.0	511.1	519.1	528.2	538.3	548.4	557.4	566.5	572.6
165°	486.9	493.9	502.0	509.1	515.1	522.2	530.2	538.3	544.3	551.4	556.4
167.5°	490.9	495.9	502.0	508.0	511.1	516.1	522.2	529.2	534.3	538.3	542.3
170°	493.9	495.9	501.0	505.0	507.0	510.1	515.1	520.1	523.2	527.2	529.2
172.5°	495.9	497.0	501.0	504.0	504.0	505.0	508.0	512.1	514.1	517.1	518.1
175°	497.0	498.0	500.0	502.0	501.0	501.0	503.0	505.0	506.0	508.0	508.0
177.5°	498.0	498.0	499.0	501.0	499.0	498.0	499.0	500.0	501.0	502.0	502.0
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	2896.2	2896.2	2896.2	2896.2
2.5°	2574.3	2569.6	2550.8	2532.0
5°	2182.6	2166.4	2161.1	2155.7
7.5°	1907.1	1905.7	1877.5	1849.3
10°	1664.5	1666.5	1641.0	1615.4
12.5°	1491.1	1474.3	1472.3	1470.3
15°	1360.7	1345.3	1342.6	1339.9
17.5°	1268.7	1259.3	1256.6	1253.9
20°	1198.8	1193.4	1188.7	1184.0
22.5°	1138.3	1131.6	1127.6	1123.5
25°	1079.9	1073.8	1072.5	1071.1
27.5°	1027.4	1020.1	1020.1	1020.1
30°	977.7	973.0	971.0	969.0
32.5°	931.4	927.3	927.3	927.3
35°	887.7	885.7	883.0	880.3
37.5°	848.0	848.0	846.7	845.3
40°	809.7	811.7	811.7	811.7
42.5°	774.8	776.8	776.8	776.8
45°	738.5	741.9	743.2	744.5
47.5°	702.9	708.3	709.6	710.9
50°	667.9	672.0	672.6	673.3
52.5°	632.3	637.0	640.4	643.8
55°	594.7	599.4	601.4	603.4
57.5°	554.4	559.1	559.8	560.4
60°	510.0	514.7	516.1	517.4
62.5°	467.7	470.4	471.7	473.1
65°	419.3	423.3	426.0	428.7
67.5°	372.9	376.3	376.3	376.3
70°	321.2	322.5	324.6	326.6
72.5°	273.5	274.2	274.2	274.2
75°	223.1	224.4	225.1	225.8
77.5°	175.4	176.1	176.1	176.1
80°	128.3	127.7	127.7	127.7
82.5°	88.0	86.0	86.0	86.0
85°	50.4	49.7	50.4	51.1
87.5°	22.8	22.8	22.8	22.8
90°	28.2	29.2	30.2	29.2
92.5°	58.5	54.4	55.4	53.4
95°	137.1	128.0	121.0	116.9
97.5°	313.5	275.2	251.0	239.9
100°	743.9	670.3	631.0	632.0
102.5°	1115.9	1061.5	1030.2	1001.0
105°	1357.8	1319.5	1287.3	1282.2
107.5°	1508.0	1489.9	1476.8	1465.7
110°	1566.5	1574.5	1572.5	1570.5



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	1551.4	1580.6	1590.7	1591.7
115°	1489.9	1534.2	1554.4	1559.4
117.5°	1402.2	1451.6	1481.8	1488.9
120°	1309.4	1365.9	1390.1	1396.1
122.5°	1224.8	1274.1	1301.4	1309.4
125°	1153.2	1197.5	1222.7	1229.8
127.5°	1093.7	1132.0	1155.2	1161.2
130°	1039.3	1075.6	1096.7	1104.8
132.5°	989.9	1026.2	1044.3	1049.4
135°	941.5	971.7	989.9	996.9
137.5°	889.1	920.3	935.4	941.5
140°	839.7	867.9	884.0	883.0
142.5°	791.3	815.5	829.6	828.6
145°	748.0	769.1	777.2	779.2
147.5°	712.7	727.8	735.9	736.9
150°	683.4	694.5	700.6	700.6
152.5°	657.2	667.3	670.3	670.3
155°	635.1	643.1	645.1	646.1
157.5°	614.9	620.9	623.0	623.0
160°	595.7	601.8	601.8	600.8
162.5°	576.6	581.6	581.6	580.6
165°	560.5	564.5	563.5	563.5
167.5°	544.3	547.4	546.4	546.4
170°	530.2	532.2	531.2	531.2
172.5°	518.1	520.1	518.1	517.1
175°	508.0	509.1	508.0	507.0
177.5°	501.0	502.0	500.0	500.0
180°	498.0	498.0	498.0	498.0



TEST NUMBER: P831053

CATALOG NUMBER: S123DIP-S1000D1025U840-4F0-1E-UDD-G4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.01	16.88	16.93	17.81	19.01	18.25	19.12	19.16	20.05	21.24
	3H	17.66	18.44	18.59	19.38	20.60	19.67	20.45	20.60	21.39	22.61
	4H	18.24	18.97	19.18	19.92	21.15	20.12	20.86	21.07	21.81	23.03
	6H	18.61	19.29	19.56	20.24	21.48	20.40	21.08	21.36	22.03	23.27
	8H	18.70	19.35	19.67	20.32	21.56	20.46	21.11	21.43	22.08	23.31
	12H	18.75	19.36	19.72	20.33	21.59	20.48	21.10	21.45	22.06	23.32
4H	2H	16.59	17.33	17.54	18.27	19.50	18.41	19.15	19.36	20.09	21.32
	3H	18.42	19.03	19.38	20.01	21.25	20.03	20.65	20.99	21.62	22.86
	4H	19.12	19.68	20.08	20.64	21.91	20.62	21.18	21.58	22.15	23.41
	6H	19.59	20.07	20.57	21.07	22.33	21.02	21.50	22.00	22.50	23.76
	8H	19.73	20.18	20.71	21.16	22.44	21.13	21.58	22.12	22.57	23.85
	12H	19.80	20.20	20.80	21.20	22.49	21.18	21.58	22.18	22.59	23.87
8H	4H	19.38	19.83	20.36	20.82	22.10	20.72	21.17	21.71	22.16	23.44
	6H	19.97	20.34	20.98	21.37	22.65	21.23	21.60	22.23	22.62	23.90
	8H	20.18	20.51	21.19	21.52	22.82	21.41	21.73	22.42	22.75	24.04
	12H	20.30	20.59	21.32	21.60	22.94	21.51	21.80	22.53	22.80	24.15
12H	4H	19.38	19.79	20.38	20.79	22.08	20.70	21.10	21.70	22.11	23.39
	6H	20.02	20.35	21.04	21.36	22.66	21.24	21.57	22.26	22.58	23.88
	8H	20.26	20.54	21.28	21.55	22.90	21.44	21.73	22.46	22.74	24.08