

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332036-840

Luminaire Tested: **S123DIP-S1000D1195U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332036-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1000D1195U840-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9101.3 lumens  
Efficiency: N/A  
Efficacy: 139.2 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15268	15268	15268	15268
5°	18208	15333	13588	15333
10°	22789	15255	12273	15255
15°	27952	15133	11426	15133
20°	33298	14940	10879	14940
25°	35357	14707	10757	14707
30°	30305	14537	10813	14537
35°	21077	14294	10926	14294
40°	15874	14011	10893	14011
45°	13181	13589	10753	13589
50°	11807	12727	10655	12727
55°	11038	11798	10524	11798
60°	10355	10828	10415	10828
65°	9732	9872	10083	9872
70°	9127	8781	9602	8781
75°	8172	7690	8804	7690
80°	7153	6304	7581	6304
85°	5595	4582	5088	4582



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.7	1.5
10°-20°	448.0	4.9
20°-30°	751.9	8.3
30°-40°	851.4	9.4
40°-50°	763.5	8.4
50°-60°	616.1	6.8
60°-70°	429.4	4.7
70°-80°	225.7	2.5
80°-90°	59.6	0.7
90°-100°	57.4	0.6
100°-110°	273.6	3.0
110°-120°	657.3	7.2
120°-130°	837.0	9.2
130°-140°	894.3	9.8
140°-150°	836.3	9.2
150°-160°	674.6	7.4
160°-170°	435.4	4.8
170°-180°	150.0	1.6
0°-30°	1339.7	14.7
0°-40°	2191.1	24.1
0°-60°	3570.7	39.2
0°-90°	4285.4	47.1
90°-120°	988.3	10.9
90°-150°	3555.9	39.1
90°-180°	4816.0	52.9
0°-180°	9101.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1685	1419	1258	1419	1685	175
15°	2508	1358	1025	1358	2508	724
25°	2977	1238	906	1238	2977	1306
35°	1604	1088	832	1088	1604	1042
45°	866	893	706	893	866	685
55°	588	629	561	629	588	528
65°	382	388	396	388	382	380
75°	196	185	212	185	196	210
85°	45	37	41	37	45	55
90°	35	1	35	1	35	18
95°	44	72	44	72	44	37
105°	52	350	52	350	52	118
115°	690	656	690	656	690	637
125°	943	924	943	924	943	842
135°	1163	1151	1163	1151	1163	897
145°	1341	1328	1341	1328	1341	837
155°	1461	1463	1461	1463	1461	674
165°	1539	1543	1539	1543	1539	435
175°	1573	1579	1573	1579	1573	150
180°	1579	1579	1579	1579	1579	



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1505.2	1504.2	1501.4	1503.6	1499.2	1493.2	1492.6	1487.1	1471.2	1470.1	1465.7
5°	1685.1	1679.5	1678.8	1678.2	1668.5	1655.5	1630.7	1628.7	1595.7	1579.2	1559.2
7.5°	1917.8	1920.8	1910.7	1901.9	1872.5	1853.1	1826.5	1792.6	1752.1	1711.0	1683.6
10°	2085.0	2107.7	2079.5	2060.2	2042.4	2008.7	1969.5	1920.8	1872.0	1814.9	1771.6
12.5°	2264.2	2275.3	2269.7	2251.6	2223.8	2172.5	2103.1	2049.4	2004.5	1909.5	1871.1
15°	2508.3	2550.2	2523.5	2461.5	2463.0	2414.2	2323.4	2223.8	2170.9	2087.7	1974.4
17.5°	2768.3	2773.6	2762.2	2710.6	2676.2	2609.2	2525.5	2429.9	2322.8	2222.1	2101.9
20°	2906.9	2902.8	2878.7	2851.9	2792.8	2740.6	2649.2	2542.6	2405.2	2306.2	2175.0
22.5°	2983.8	2977.0	2965.6	2943.2	2894.0	2837.9	2755.8	2639.4	2508.6	2372.3	2220.6
25°	2977.0	2985.9	2987.3	2981.1	2964.0	2930.2	2865.6	2772.9	2642.3	2467.1	2309.1
27.5°	2707.5	2720.3	2756.9	2789.6	2825.9	2863.1	2858.1	2812.1	2715.4	2564.0	2370.9
30°	2438.2	2410.7	2478.7	2564.7	2623.0	2726.1	2783.9	2787.3	2733.0	2603.1	2414.8
32.5°	2064.4	2094.6	2124.7	2230.4	2358.0	2473.8	2588.7	2681.2	2691.8	2605.4	2440.6
35°	1604.0	1641.7	1696.7	1751.7	1889.2	2007.3	2209.4	2385.3	2525.5	2544.1	2443.0
37.5°	1292.5	1311.2	1345.9	1401.1	1491.0	1631.1	1787.5	2009.8	2212.9	2364.0	2370.6
40°	1129.7	1135.3	1174.5	1216.4	1289.2	1404.6	1545.5	1742.0	1985.3	2196.4	2284.3
42.5°	1007.7	1019.8	1036.4	1076.7	1134.7	1221.5	1352.5	1515.0	1738.0	1980.7	2152.8
45°	865.9	879.6	889.9	916.8	958.0	1016.3	1107.8	1256.2	1425.9	1676.8	1908.3
47.5°	772.1	773.3	780.9	801.1	829.2	873.0	937.7	1033.0	1188.8	1392.3	1630.0
50°	705.1	716.1	718.8	734.6	756.6	788.9	842.5	923.6	1051.5	1230.1	1448.7
52.5°	657.8	661.1	668.8	680.2	699.4	724.6	771.0	834.6	934.8	1087.1	1288.1
55°	588.2	588.2	595.8	604.7	615.7	638.4	669.3	716.1	792.3	910.6	1076.8
57.5°	523.9	527.4	532.7	535.4	544.8	559.8	585.6	621.1	678.0	769.0	901.2
60°	481.0	487.3	486.6	492.0	500.3	512.0	533.9	562.8	613.7	686.5	797.9
62.5°	443.6	443.2	443.1	449.7	458.0	469.1	483.4	508.4	551.6	616.1	710.9
65°	382.1	380.7	385.6	389.6	392.4	400.6	411.6	433.6	462.5	510.6	584.1
67.5°	327.4	323.4	326.0	327.4	332.0	338.5	348.8	362.4	385.4	424.0	479.4
70°	290.0	286.6	285.9	287.2	291.3	296.2	303.8	316.8	338.1	369.0	409.6
72.5°	251.6	249.1	249.0	252.1	254.0	257.1	262.5	274.5	291.3	314.6	352.4
75°	196.5	196.5	196.5	197.2	199.2	202.1	206.1	212.4	225.4	241.9	267.3
77.5°	147.3	147.2	146.3	146.2	149.3	150.5	151.5	157.2	164.5	175.6	194.2
80°	115.4	112.0	113.4	115.4	116.8	117.5	119.6	121.0	127.1	133.3	146.3
82.5°	85.7	82.9	83.1	86.3	86.5	87.3	89.4	91.3	93.6	99.3	106.2
85°	45.3	45.3	46.0	46.0	46.8	46.0	48.1	48.8	48.8	52.2	56.4
87.5°	23.5	22.3	22.8	23.2	22.5	22.9	23.3	23.6	23.9	24.3	24.2
90°	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.2	29.2	28.2	24.7
92.5°	39.0	38.7	38.4	38.0	37.7	36.8	35.0	33.3	31.7	30.0	27.5
95°	44.5	44.5	44.5	44.5	44.5	43.6	41.8	40.0	38.2	36.4	33.5
97.5°	48.4	48.1	47.9	47.6	47.3	46.2	44.0	41.9	39.9	37.8	35.6
100°	49.3	49.0	48.8	48.5	48.3	47.1	44.9	42.9	40.8	38.7	37.4
102.5°	50.2	49.8	49.3	48.8	48.4	51.3	57.8	64.2	70.7	77.2	121.6
105°	51.6	51.1	50.6	50.1	49.6	72.3	118.5	164.6	210.8	256.9	280.4
107.5°	162.2	196.9	231.7	266.5	301.2	335.6	369.4	403.2	437.1	471.0	467.3
110°	322.7	359.9	397.2	434.5	471.8	494.7	503.3	511.9	520.6	529.2	526.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	553.5	561.4	569.3	577.1	585.0	589.0	588.8	588.5	588.4	588.2	585.4
115°	689.8	688.8	687.8	686.7	685.7	683.9	681.3	678.6	676.1	673.5	671.2
117.5°	766.4	766.2	766.0	765.8	765.6	764.4	762.3	760.2	758.1	756.1	754.9
120°	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7	811.6	809.5	808.8
122.5°	870.6	870.4	870.1	869.9	869.7	868.9	867.5	866.0	864.5	863.0	862.0
125°	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7	939.2	938.6	937.6
127.5°	1013.2	1013.8	1014.3	1014.8	1015.3	1015.1	1014.3	1013.5	1012.7	1011.8	1010.6
130°	1058.3	1058.8	1059.3	1059.9	1060.4	1060.2	1059.0	1058.0	1057.0	1055.9	1054.9
132.5°	1099.5	1100.3	1101.1	1101.8	1102.5	1102.4	1101.4	1100.2	1099.2	1098.2	1097.3
135°	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8	1161.6
137.5°	1222.0	1222.6	1223.1	1223.7	1224.2	1223.8	1222.5	1221.3	1220.0	1218.8	1218.2
140°	1257.8	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5	1256.5	1255.4	1254.7
142.5°	1290.6	1291.3	1292.0	1292.8	1293.5	1293.4	1292.6	1291.8	1291.0	1290.1	1289.4
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.8	1339.2	1338.7	1338.2
147.5°	1378.6	1379.8	1381.0	1382.2	1383.4	1383.7	1383.2	1382.7	1382.2	1381.6	1381.1
150°	1406.7	1407.5	1408.4	1409.1	1409.9	1410.0	1409.5	1409.0	1408.5	1408.0	1407.4
152.5°	1429.3	1430.5	1431.7	1432.9	1434.1	1434.2	1433.3	1432.3	1431.4	1430.5	1430.2
155°	1460.8	1462.3	1463.9	1465.4	1466.9	1467.1	1465.8	1464.5	1463.2	1461.9	1461.7
157.5°	1487.2	1489.2	1491.3	1493.4	1495.4	1495.6	1494.0	1492.5	1491.0	1489.3	1489.7
160°	1504.1	1505.9	1507.8	1509.6	1511.5	1511.6	1510.0	1508.4	1506.9	1505.3	1505.6
162.5°	1520.0	1521.7	1523.3	1524.9	1526.5	1526.5	1524.7	1523.0	1521.2	1519.3	1519.6
165°	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.4	1540.2	1538.1	1538.4
167.5°	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2	1553.2
170°	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7	1561.7
172.5°	1566.3	1568.6	1570.9	1573.2	1575.5	1575.6	1573.5	1571.5	1569.3	1567.2	1567.0
175°	1573.4	1575.5	1577.5	1579.6	1581.7	1581.9	1580.0	1578.2	1576.4	1574.5	1574.3
177.5°	1575.5	1577.5	1579.6	1581.8	1583.8	1584.0	1582.4	1580.6	1579.0	1577.3	1577.1
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1462.4	1457.9	1453.6	1445.9	1439.3	1430.0	1427.1	1423.9	1414.0	1405.2	1398.6
5°	1551.7	1535.2	1511.2	1489.1	1471.3	1447.2	1433.5	1419.1	1398.5	1379.9	1364.8
7.5°	1645.2	1612.8	1575.4	1534.9	1497.3	1461.0	1431.7	1405.6	1376.7	1349.4	1328.1
10°	1719.4	1672.6	1620.4	1564.1	1516.0	1469.3	1430.1	1395.7	1358.6	1326.3	1299.5
12.5°	1804.0	1734.7	1662.7	1594.3	1537.4	1472.6	1425.1	1381.4	1339.4	1300.5	1270.4
15°	1904.2	1816.2	1731.1	1636.9	1550.3	1469.3	1412.9	1358.0	1309.1	1269.3	1230.8
17.5°	1995.5	1895.8	1783.5	1669.1	1564.6	1468.4	1389.6	1327.4	1266.4	1217.6	1179.2
20°	2047.2	1933.8	1806.6	1687.8	1572.4	1465.1	1378.6	1304.3	1238.3	1186.8	1143.5
22.5°	2091.7	1959.0	1827.6	1700.4	1571.8	1456.3	1358.2	1281.8	1210.3	1159.8	1113.8
25°	2137.9	1979.1	1847.2	1698.1	1554.5	1434.9	1324.9	1238.3	1166.9	1107.8	1060.4
27.5°	2177.5	1977.8	1821.2	1660.8	1527.2	1407.3	1290.0	1197.1	1121.3	1057.0	1009.0
30°	2203.8	1980.5	1794.3	1635.6	1500.9	1377.2	1263.0	1169.6	1089.9	1024.6	979.3
32.5°	2220.4	1978.8	1769.6	1600.3	1459.1	1349.7	1234.0	1137.2	1055.3	991.1	947.4
35°	2230.0	1966.8	1727.0	1527.6	1391.6	1285.1	1188.2	1087.8	1002.0	942.2	892.7
37.5°	2210.7	1941.4	1677.5	1457.5	1308.6	1203.7	1122.2	1036.7	954.5	888.7	846.1
40°	2180.5	1924.9	1639.0	1408.1	1251.4	1150.3	1081.0	997.1	916.0	853.5	813.6
42.5°	2122.7	1891.3	1596.7	1353.1	1192.0	1091.0	1027.1	957.0	880.3	821.6	781.7
45°	1981.9	1818.4	1533.2	1270.6	1104.3	999.9	943.5	892.7	823.2	766.2	731.8
47.5°	1786.5	1708.5	1441.4	1183.7	1012.8	912.3	853.7	812.8	762.1	716.1	683.1
50°	1650.6	1618.4	1379.2	1124.3	951.8	853.5	797.2	760.0	723.7	677.6	647.3
52.5°	1494.0	1513.9	1306.7	1062.7	889.7	793.0	740.0	710.5	677.4	639.6	613.3
55°	1273.4	1345.5	1181.3	959.4	797.2	705.1	654.9	628.7	609.6	581.4	558.7
57.5°	1066.8	1158.6	1045.8	852.8	706.3	626.8	578.8	550.3	538.0	523.2	505.3
60°	944.2	1034.9	949.1	781.3	645.3	569.7	527.0	503.0	490.7	480.4	465.2
62.5°	834.9	926.7	854.4	708.8	585.3	515.2	478.2	454.6	445.0	439.7	426.8
65°	684.5	763.5	715.4	595.8	499.6	437.8	404.0	387.6	378.7	376.6	368.3
67.5°	557.0	617.2	582.2	494.2	418.5	365.1	336.5	322.4	315.6	314.9	308.7
70°	473.5	529.9	503.0	423.3	358.0	316.1	291.3	279.0	274.9	274.2	270.7
72.5°	408.6	447.9	426.6	360.1	309.6	271.6	253.5	240.5	235.8	236.8	234.5
75°	302.4	331.9	319.5	273.5	233.0	208.2	193.1	184.9	180.8	182.8	180.1
77.5°	217.5	236.3	225.1	193.3	168.2	150.4	139.3	134.1	130.5	130.3	129.1
80°	164.2	175.2	169.1	149.8	129.2	114.1	105.1	101.7	99.7	99.0	98.3
82.5°	116.9	126.3	119.1	105.8	91.8	82.7	77.7	73.1	71.6	72.0	71.3
85°	59.1	62.5	59.8	51.5	46.0	41.9	39.2	37.1	35.7	36.5	35.0
87.5°	24.6	24.4	22.1	19.4	17.8	15.6	15.0	13.4	12.8	13.3	13.3
90°	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2	3.7	6.4	9.0
92.5°	24.9	22.4	19.8	18.9	19.6	20.4	21.1	21.8	21.1	20.4	19.6
95°	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6	60.9	50.2	39.5
97.5°	75.3	94.1	112.9	124.6	129.5	134.2	139.1	143.8	139.1	134.2	129.5
100°	120.1	160.8	201.4	219.1	213.9	208.7	203.5	198.2	203.5	208.7	213.9
102.5°	166.0	210.5	254.9	275.3	271.5	267.7	264.0	260.2	264.0	267.7	271.5
105°	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6	352.5	355.4	358.2
107.5°	463.5	459.9	456.2	453.1	450.8	448.6	446.3	443.9	446.3	448.6	450.8
110°	523.4	520.6	517.7	515.2	513.1	511.0	509.0	506.9	509.0	511.0	513.1





TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	582.6	579.7	576.8	574.4	572.6	570.7	568.8	566.9	568.8	570.7	572.6
115°	668.7	666.4	664.1	662.1	660.6	658.9	657.4	655.9	657.4	658.9	660.6
117.5°	753.7	752.5	751.2	749.7	747.8	745.8	743.9	741.9	743.9	745.8	747.8
120°	808.0	807.2	806.5	804.9	802.5	800.2	797.8	795.5	797.8	800.2	802.5
122.5°	861.1	860.1	859.1	857.7	855.7	853.7	851.8	849.9	851.8	853.7	855.7
125°	936.5	935.4	934.4	932.9	930.8	928.7	926.7	924.5	926.7	928.7	930.8
127.5°	1009.4	1008.0	1006.8	1005.1	1003.1	1001.0	998.9	996.8	998.9	1001.0	1003.1
130°	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9	1044.0	1046.0	1048.1
132.5°	1096.5	1095.7	1094.8	1093.4	1091.3	1089.2	1087.1	1085.0	1087.1	1089.2	1091.3
135°	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.6	1150.9	1152.6	1154.1	1155.7
137.5°	1217.7	1217.1	1216.5	1215.3	1213.3	1211.2	1209.3	1207.3	1209.3	1211.2	1213.3
140°	1253.8	1253.0	1252.2	1251.1	1249.5	1248.0	1246.4	1244.9	1246.4	1248.0	1249.5
142.5°	1288.6	1287.8	1287.0	1285.9	1284.2	1282.7	1281.1	1279.6	1281.1	1282.7	1284.2
145°	1337.7	1337.2	1336.7	1335.4	1333.6	1331.8	1330.0	1328.2	1330.0	1331.8	1333.6
147.5°	1380.6	1380.1	1379.6	1378.7	1377.5	1376.3	1375.1	1373.9	1375.1	1376.3	1377.5
150°	1406.8	1406.3	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1	1402.8	1403.6	1404.4
152.5°	1429.9	1429.5	1429.2	1428.9	1428.5	1428.2	1427.7	1427.4	1427.7	1428.2	1428.5
155°	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.6	1463.1	1462.6	1462.0	1461.5
157.5°	1489.9	1490.2	1490.4	1490.6	1490.6	1490.7	1490.7	1490.8	1490.7	1490.7	1490.6
160°	1505.8	1506.1	1506.3	1506.6	1506.9	1507.1	1507.4	1507.6	1507.4	1507.1	1506.9
162.5°	1519.9	1520.1	1520.5	1520.9	1521.6	1522.3	1523.0	1523.6	1523.0	1522.3	1521.6
165°	1538.6	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9	1542.1	1541.3	1540.5
167.5°	1553.2	1553.2	1553.2	1553.7	1554.8	1555.8	1556.8	1557.9	1556.8	1555.8	1554.8
170°	1561.7	1561.7	1561.7	1562.2	1563.2	1564.3	1565.3	1566.3	1565.3	1564.3	1563.2
172.5°	1566.8	1566.6	1566.4	1566.9	1568.2	1569.4	1570.7	1572.0	1570.7	1569.4	1568.2
175°	1574.0	1573.8	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2	1577.9	1576.6	1575.3
177.5°	1576.9	1576.7	1576.5	1576.9	1578.0	1579.0	1580.0	1581.1	1580.0	1579.0	1578.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1394.7	1390.9	1385.4	1377.2	1370.6	1360.1	1360.1	1361.8	1361.8	1361.2	1360.1
5°	1352.4	1342.1	1329.8	1315.3	1300.2	1285.1	1282.3	1276.9	1272.7	1269.9	1266.5
7.5°	1307.8	1289.5	1271.4	1251.2	1232.8	1217.6	1207.0	1198.2	1192.5	1186.5	1182.1
10°	1277.5	1254.9	1233.6	1212.2	1188.8	1170.3	1158.6	1150.3	1144.2	1138.7	1136.0
12.5°	1241.7	1215.8	1192.3	1172.0	1146.5	1127.4	1116.3	1112.5	1105.2	1093.6	1087.5
15°	1189.5	1165.5	1137.3	1106.4	1094.0	1070.7	1057.6	1051.5	1047.3	1038.3	1035.6
17.5°	1144.9	1113.4	1081.8	1058.7	1035.7	1016.8	1009.5	1001.8	996.3	989.1	986.8
20°	1109.1	1081.0	1052.1	1027.3	1003.3	982.7	976.5	971.0	965.5	962.1	959.4
22.5°	1072.9	1044.7	1020.8	997.6	972.0	958.5	951.8	945.7	941.9	939.6	936.8
25°	1021.9	997.1	970.4	949.7	929.1	920.2	916.0	912.6	909.9	906.5	905.7
27.5°	976.2	949.3	927.6	908.4	893.5	886.1	882.1	880.4	881.0	882.2	883.0
30°	942.2	917.5	899.6	883.0	869.3	862.4	861.7	861.7	864.5	865.2	866.6
32.5°	910.8	890.5	872.6	856.7	846.3	841.5	844.1	844.1	846.4	848.2	850.6
35°	865.2	847.3	833.5	819.8	810.9	812.9	814.4	815.7	819.1	823.2	826.1
37.5°	821.6	806.1	791.8	781.0	777.0	780.6	784.0	786.9	790.8	794.0	796.8
40°	790.3	778.6	764.9	755.3	756.6	758.7	761.4	764.9	768.3	770.3	773.2
42.5°	761.1	748.9	738.5	730.5	732.5	735.1	736.7	738.5	742.5	746.2	747.8
45°	716.8	707.1	697.5	692.7	694.1	695.5	696.8	698.9	702.4	705.1	705.8
47.5°	666.8	660.1	653.7	649.0	651.2	650.7	652.5	656.8	657.9	659.5	663.4
50°	635.0	628.7	621.3	619.9	619.9	619.9	620.6	626.0	626.0	628.7	631.6
52.5°	599.8	595.8	591.0	588.5	587.4	587.4	590.3	593.1	594.2	598.0	600.8
55°	547.8	543.6	539.5	537.3	536.0	537.3	542.9	544.2	547.8	549.8	551.8
57.5°	493.4	490.3	487.0	485.8	485.5	487.4	490.4	494.5	495.3	501.7	504.8
60°	457.7	452.8	450.1	450.1	448.8	454.9	453.5	460.4	461.8	466.0	470.7
62.5°	420.8	414.3	413.2	413.2	415.3	417.0	418.9	421.9	425.6	430.7	434.4
65°	361.4	358.0	362.8	362.1	360.8	364.9	364.9	368.3	372.4	377.3	384.9
67.5°	305.3	303.5	303.9	303.9	306.0	308.3	310.2	313.3	318.2	323.3	328.2
70°	267.3	269.4	266.0	268.7	270.7	271.5	272.9	276.9	282.5	285.9	291.3
72.5°	230.5	230.4	230.8	231.9	233.9	235.2	236.5	241.3	247.2	250.1	254.6
75°	177.3	176.6	178.6	178.6	182.1	183.5	184.9	186.9	192.4	196.5	200.0
77.5°	129.5	130.3	129.9	132.2	131.3	131.5	135.8	137.8	138.5	146.5	148.3
80°	97.6	99.0	99.7	100.4	101.0	99.7	104.4	106.5	106.5	111.3	114.7
82.5°	70.1	70.9	72.7	73.4	73.5	74.9	75.3	76.9	78.5	80.6	85.0
85°	35.0	37.1	37.8	37.1	37.8	36.5	38.5	39.2	39.9	39.9	39.9
87.5°	13.3	14.4	14.6	15.9	16.0	17.2	17.4	16.5	16.7	18.6	16.6
90°	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.2	31.3	32.3	33.1
92.5°	18.9	19.8	22.4	24.9	27.5	30.0	31.7	33.3	35.0	36.8	37.7
95°	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0	41.8	43.6	44.5
97.5°	124.6	112.9	94.1	75.3	56.6	37.8	39.9	41.9	44.0	46.2	47.3
100°	219.1	201.4	160.8	120.1	79.4	38.7	40.8	42.9	44.9	47.1	48.3
102.5°	275.3	254.9	210.5	166.0	121.6	77.2	70.7	64.2	57.8	51.3	48.4
105°	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6	118.5	72.3	49.6
107.5°	453.1	456.2	459.9	463.5	467.3	471.0	437.1	403.2	369.4	335.6	301.2
110°	515.2	517.7	520.6	523.4	526.2	529.2	520.6	511.9	503.3	494.7	471.8



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	574.4	576.8	579.7	582.6	585.4	588.2	588.4	588.5	588.8	589.0	585.0
115°	662.1	664.1	666.4	668.7	671.2	673.5	676.1	678.6	681.3	683.9	685.7
117.5°	749.7	751.2	752.5	753.7	754.9	756.1	758.1	760.2	762.3	764.4	765.6
120°	804.9	806.5	807.2	808.0	808.8	809.5	811.6	813.7	815.8	817.9	818.9
122.5°	857.7	859.1	860.1	861.1	862.0	863.0	864.5	866.0	867.5	868.9	869.7
125°	932.9	934.4	935.4	936.5	937.6	938.6	939.2	939.7	940.2	940.7	941.2
127.5°	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7	1013.5	1014.3	1015.1	1015.3
130°	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0	1059.0	1060.2	1060.4
132.5°	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2	1100.2	1101.4	1102.4	1102.5
135°	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9
137.5°	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0	1221.3	1222.5	1223.8	1224.2
140°	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5	1257.5	1258.5	1259.6	1259.8
142.5°	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0	1291.8	1292.6	1293.4	1293.5
145°	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2	1339.8	1340.3	1340.8	1341.0
147.5°	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.7	1383.2	1383.7	1383.4
150°	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5	1409.0	1409.5	1410.0	1409.9
152.5°	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4	1432.3	1433.3	1434.2	1434.1
155°	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2	1464.5	1465.8	1467.1	1466.9
157.5°	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0	1492.5	1494.0	1495.6	1495.4
160°	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4	1510.0	1511.6	1511.5
162.5°	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2	1523.0	1524.7	1526.5	1526.5
165°	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2	1542.4	1544.4	1546.5	1546.6
167.5°	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6
170°	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9
172.5°	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3	1571.5	1573.5	1575.6	1575.5
175°	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4	1578.2	1580.0	1581.9	1581.7
177.5°	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0	1580.6	1582.4	1584.0	1583.8
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1356.2	1355.7	1359.6	1356.9	1359.6	1355.7	1356.2	1360.1	1361.2	1361.8	1361.8
5°	1262.4	1264.5	1257.6	1257.6	1257.6	1264.5	1262.4	1266.5	1269.9	1272.7	1276.9
7.5°	1178.8	1175.8	1176.1	1172.4	1176.1	1175.8	1178.8	1182.1	1186.5	1192.5	1198.2
10°	1127.7	1123.6	1122.2	1122.9	1122.2	1123.6	1127.7	1136.0	1138.7	1144.2	1150.3
12.5°	1085.4	1084.6	1075.5	1075.6	1075.5	1084.6	1085.4	1087.5	1093.6	1105.2	1112.5
15°	1035.6	1022.6	1021.2	1025.3	1021.2	1022.6	1035.6	1035.6	1038.3	1047.3	1051.5
17.5°	985.7	978.9	979.3	977.2	979.3	978.9	985.7	986.8	989.1	996.3	1001.8
20°	959.4	955.2	954.5	949.7	954.5	955.2	959.4	959.4	962.1	965.5	971.0
22.5°	935.1	933.8	934.2	928.9	934.2	933.8	935.1	936.8	939.6	941.9	945.7
25°	905.0	908.5	905.7	905.7	905.7	908.5	905.0	905.7	906.5	909.9	912.6
27.5°	884.7	884.5	883.2	883.2	883.2	884.5	884.7	883.0	882.2	881.0	880.4
30°	869.3	868.6	870.0	870.0	870.0	868.6	869.3	866.6	865.2	864.5	861.7
32.5°	853.9	854.9	855.2	855.7	855.2	854.9	853.9	850.6	848.2	846.4	844.1
35°	830.1	830.8	832.9	831.5	832.9	830.8	830.1	826.1	823.2	819.1	815.7
37.5°	798.0	801.1	800.4	801.5	800.4	801.1	798.0	796.8	794.0	790.8	786.9
40°	773.8	775.9	775.2	775.2	775.2	775.9	773.8	773.2	770.3	768.3	764.9
42.5°	749.0	750.5	748.8	747.7	748.8	750.5	749.0	747.8	746.2	742.5	738.5
45°	708.5	707.1	709.2	706.4	709.2	707.1	708.5	705.8	705.1	702.4	698.9
47.5°	663.2	664.5	665.1	667.1	665.1	664.5	663.2	663.4	659.5	657.9	656.8
50°	632.9	637.0	637.0	636.3	637.0	637.0	632.9	631.6	628.7	626.0	626.0
52.5°	603.2	605.1	607.9	607.7	607.9	605.1	603.2	600.8	598.0	594.2	593.1
55°	557.3	558.7	560.1	560.8	560.1	558.7	557.3	551.8	549.8	547.8	544.2
57.5°	509.8	509.2	512.5	513.5	512.5	509.2	509.8	504.8	501.7	495.3	494.5
60°	476.3	476.3	481.7	483.8	481.7	476.3	476.3	470.7	466.0	461.8	460.4
62.5°	440.5	442.7	448.2	445.4	448.2	442.7	440.5	434.4	430.7	425.6	421.9
65°	388.3	393.7	393.0	395.9	393.0	393.7	388.3	384.9	377.3	372.4	368.3
67.5°	333.7	337.1	342.0	342.5	342.0	337.1	333.7	328.2	323.3	318.2	313.3
70°	296.9	300.3	303.1	305.1	303.1	300.3	296.9	291.3	285.9	282.5	276.9
72.5°	261.2	263.0	269.5	266.6	269.5	263.0	261.2	254.6	250.1	247.2	241.3
75°	204.8	209.5	213.7	211.7	213.7	209.5	204.8	200.0	196.5	192.4	186.9
77.5°	151.5	156.2	158.1	156.4	158.1	156.2	151.5	148.3	146.5	138.5	137.8
80°	119.6	118.9	123.0	122.3	123.0	118.9	119.6	114.7	111.3	106.5	106.5
82.5°	87.7	87.1	89.0	89.4	89.0	87.1	87.7	85.0	80.6	78.5	76.9
85°	42.6	44.6	41.9	41.2	41.9	44.6	42.6	39.9	39.9	39.9	39.2
87.5°	16.7	16.8	16.3	15.9	16.3	16.8	16.7	16.6	18.6	16.7	16.5
90°	33.6	34.1	34.6	35.2	34.6	34.1	33.6	33.1	32.3	31.3	30.2
92.5°	38.0	38.4	38.7	39.0	38.7	38.4	38.0	37.7	36.8	35.0	33.3
95°	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	43.6	41.8	40.0
97.5°	47.6	47.9	48.1	48.4	48.1	47.9	47.6	47.3	46.2	44.0	41.9
100°	48.5	48.8	49.0	49.3	49.0	48.8	48.5	48.3	47.1	44.9	42.9
102.5°	48.8	49.3	49.8	50.2	49.8	49.3	48.8	48.4	51.3	57.8	64.2
105°	50.1	50.6	51.1	51.6	51.1	50.6	50.1	49.6	72.3	118.5	164.6
107.5°	266.5	231.7	196.9	162.2	196.9	231.7	266.5	301.2	335.6	369.4	403.2
110°	434.5	397.2	359.9	322.7	359.9	397.2	434.5	471.8	494.7	503.3	511.9



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	577.1	569.3	561.4	553.5	561.4	569.3	577.1	585.0	589.0	588.8	588.5
115°	686.7	687.8	688.8	689.8	688.8	687.8	686.7	685.7	683.9	681.3	678.6
117.5°	765.8	766.0	766.2	766.4	766.2	766.0	765.8	765.6	764.4	762.3	760.2
120°	818.9	818.9	818.9	818.9	818.9	818.9	818.9	818.9	817.9	815.8	813.7
122.5°	869.9	870.1	870.4	870.6	870.4	870.1	869.9	869.7	868.9	867.5	866.0
125°	941.7	942.3	942.8	943.3	942.8	942.3	941.7	941.2	940.7	940.2	939.7
127.5°	1014.8	1014.3	1013.8	1013.2	1013.8	1014.3	1014.8	1015.3	1015.1	1014.3	1013.5
130°	1059.9	1059.3	1058.8	1058.3	1058.8	1059.3	1059.9	1060.4	1060.2	1059.0	1058.0
132.5°	1101.8	1101.1	1100.3	1099.5	1100.3	1101.1	1101.8	1102.5	1102.4	1101.4	1100.2
135°	1165.1	1164.3	1163.5	1162.8	1163.5	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3
137.5°	1223.7	1223.1	1222.6	1222.0	1222.6	1223.1	1223.7	1224.2	1223.8	1222.5	1221.3
140°	1259.3	1258.8	1258.3	1257.8	1258.3	1258.8	1259.3	1259.8	1259.6	1258.5	1257.5
142.5°	1292.8	1292.0	1291.3	1290.6	1291.3	1292.0	1292.8	1293.5	1293.4	1292.6	1291.8
145°	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1341.0	1340.8	1340.3	1339.8
147.5°	1382.2	1381.0	1379.8	1378.6	1379.8	1381.0	1382.2	1383.4	1383.7	1383.2	1382.7
150°	1409.1	1408.4	1407.5	1406.7	1407.5	1408.4	1409.1	1409.9	1410.0	1409.5	1409.0
152.5°	1432.9	1431.7	1430.5	1429.3	1430.5	1431.7	1432.9	1434.1	1434.2	1433.3	1432.3
155°	1465.4	1463.9	1462.3	1460.8	1462.3	1463.9	1465.4	1466.9	1467.1	1465.8	1464.5
157.5°	1493.4	1491.3	1489.2	1487.2	1489.2	1491.3	1493.4	1495.4	1495.6	1494.0	1492.5
160°	1509.6	1507.8	1505.9	1504.1	1505.9	1507.8	1509.6	1511.5	1511.6	1510.0	1508.4
162.5°	1524.9	1523.3	1521.7	1520.0	1521.7	1523.3	1524.9	1526.5	1526.5	1524.7	1523.0
165°	1544.8	1543.0	1541.2	1539.3	1541.2	1543.0	1544.8	1546.6	1546.5	1544.4	1542.4
167.5°	1559.4	1557.3	1555.3	1553.2	1555.3	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3
170°	1567.9	1565.8	1563.7	1561.7	1563.7	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8
172.5°	1573.2	1570.9	1568.6	1566.3	1568.6	1570.9	1573.2	1575.5	1575.6	1573.5	1571.5
175°	1579.6	1577.5	1575.5	1573.4	1575.5	1577.5	1579.6	1581.7	1581.9	1580.0	1578.2
177.5°	1581.8	1579.6	1577.5	1575.5	1577.5	1579.6	1581.8	1583.8	1584.0	1582.4	1580.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1360.1	1360.1	1370.6	1377.2	1385.4	1390.9	1394.7	1398.6	1405.2	1414.0	1423.9
5°	1282.3	1285.1	1300.2	1315.3	1329.8	1342.1	1352.4	1364.8	1379.9	1398.5	1419.1
7.5°	1207.0	1217.6	1232.8	1251.2	1271.4	1289.5	1307.8	1328.1	1349.4	1376.7	1405.6
10°	1158.6	1170.3	1188.8	1212.2	1233.6	1254.9	1277.5	1299.5	1326.3	1358.6	1395.7
12.5°	1116.3	1127.4	1146.5	1172.0	1192.3	1215.8	1241.7	1270.4	1300.5	1339.4	1381.4
15°	1057.6	1070.7	1094.0	1106.4	1137.3	1165.5	1189.5	1230.8	1269.3	1309.1	1358.0
17.5°	1009.5	1016.8	1035.7	1058.7	1081.8	1113.4	1144.9	1179.2	1217.6	1266.4	1327.4
20°	976.5	982.7	1003.3	1027.3	1052.1	1081.0	1109.1	1143.5	1186.8	1238.3	1304.3
22.5°	951.8	958.5	972.0	997.6	1020.8	1044.7	1072.9	1113.8	1159.8	1210.3	1281.8
25°	916.0	920.2	929.1	949.7	970.4	997.1	1021.9	1060.4	1107.8	1166.9	1238.3
27.5°	882.1	886.1	893.5	908.4	927.6	949.3	976.2	1009.0	1057.0	1121.3	1197.1
30°	861.7	862.4	869.3	883.0	899.6	917.5	942.2	979.3	1024.6	1089.9	1169.6
32.5°	844.1	841.5	846.3	856.7	872.6	890.5	910.8	947.4	991.1	1055.3	1137.2
35°	814.4	812.9	810.9	819.8	833.5	847.3	865.2	892.7	942.2	1002.0	1087.8
37.5°	784.0	780.6	777.0	781.0	791.8	806.1	821.6	846.1	888.7	954.5	1036.7
40°	761.4	758.7	756.6	755.3	764.9	778.6	790.3	813.6	853.5	916.0	997.1
42.5°	736.7	735.1	732.5	730.5	738.5	748.9	761.1	781.7	821.6	880.3	957.0
45°	696.8	695.5	694.1	692.7	697.5	707.1	716.8	731.8	766.2	823.2	892.7
47.5°	652.5	650.7	651.2	649.0	653.7	660.1	666.8	683.1	716.1	762.1	812.8
50°	620.6	619.9	619.9	619.9	621.3	628.7	635.0	647.3	677.6	723.7	760.0
52.5°	590.3	587.4	587.4	588.5	591.0	595.8	599.8	613.3	639.6	677.4	710.5
55°	542.9	537.3	536.0	537.3	539.5	543.6	547.8	558.7	581.4	609.6	628.7
57.5°	490.4	487.4	485.5	485.8	487.0	490.3	493.4	505.3	523.2	538.0	550.3
60°	453.5	454.9	448.8	450.1	450.1	452.8	457.7	465.2	480.4	490.7	503.0
62.5°	418.9	417.0	415.3	413.2	413.2	414.3	420.8	426.8	439.7	445.0	454.6
65°	364.9	364.9	360.8	362.1	362.8	358.0	361.4	368.3	376.6	378.7	387.6
67.5°	310.2	308.3	306.0	303.9	303.9	303.5	305.3	308.7	314.9	315.6	322.4
70°	272.9	271.5	270.7	268.7	266.0	269.4	267.3	270.7	274.2	274.9	279.0
72.5°	236.5	235.2	233.9	231.9	230.8	230.4	230.5	234.5	236.8	235.8	240.5
75°	184.9	183.5	182.1	178.6	178.6	176.6	177.3	180.1	182.8	180.8	184.9
77.5°	135.8	131.5	131.3	132.2	129.9	130.3	129.5	129.1	130.3	130.5	134.1
80°	104.4	99.7	101.0	100.4	99.7	99.0	97.6	98.3	99.0	99.7	101.7
82.5°	75.3	74.9	73.5	73.4	72.7	70.9	70.1	71.3	72.0	71.6	73.1
85°	38.5	36.5	37.8	37.1	37.8	37.1	35.0	35.0	36.5	35.7	37.1
87.5°	17.4	17.2	16.0	15.9	14.6	14.4	13.3	13.3	13.3	12.8	13.4
90°	29.2	28.2	24.7	21.4	18.0	14.6	11.6	9.0	6.4	3.7	1.2
92.5°	31.7	30.0	27.5	24.9	22.4	19.8	18.9	19.6	20.4	21.1	21.8
95°	38.2	36.4	33.5	30.6	27.8	24.9	28.8	39.5	50.2	60.9	71.6
97.5°	39.9	37.8	56.6	75.3	94.1	112.9	124.6	129.5	134.2	139.1	143.8
100°	40.8	38.7	79.4	120.1	160.8	201.4	219.1	213.9	208.7	203.5	198.2
102.5°	70.7	77.2	121.6	166.0	210.5	254.9	275.3	271.5	267.7	264.0	260.2
105°	210.8	256.9	280.4	303.9	327.3	350.8	361.1	358.2	355.4	352.5	349.6
107.5°	437.1	471.0	467.3	463.5	459.9	456.2	453.1	450.8	448.6	446.3	443.9
110°	520.6	529.2	526.2	523.4	520.6	517.7	515.2	513.1	511.0	509.0	506.9



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	588.4	588.2	585.4	582.6	579.7	576.8	574.4	572.6	570.7	568.8	566.9
115°	676.1	673.5	671.2	668.7	666.4	664.1	662.1	660.6	658.9	657.4	655.9
117.5°	758.1	756.1	754.9	753.7	752.5	751.2	749.7	747.8	745.8	743.9	741.9
120°	811.6	809.5	808.8	808.0	807.2	806.5	804.9	802.5	800.2	797.8	795.5
122.5°	864.5	863.0	862.0	861.1	860.1	859.1	857.7	855.7	853.7	851.8	849.9
125°	939.2	938.6	937.6	936.5	935.4	934.4	932.9	930.8	928.7	926.7	924.5
127.5°	1012.7	1011.8	1010.6	1009.4	1008.0	1006.8	1005.1	1003.1	1001.0	998.9	996.8
130°	1057.0	1055.9	1054.9	1053.9	1052.8	1051.8	1050.2	1048.1	1046.0	1044.0	1041.9
132.5°	1099.2	1098.2	1097.3	1096.5	1095.7	1094.8	1093.4	1091.3	1089.2	1087.1	1085.0
135°	1163.5	1162.8	1161.6	1160.6	1159.6	1158.5	1157.2	1155.7	1154.1	1152.6	1150.9
137.5°	1220.0	1218.8	1218.2	1217.7	1217.1	1216.5	1215.3	1213.3	1211.2	1209.3	1207.3
140°	1256.5	1255.4	1254.7	1253.8	1253.0	1252.2	1251.1	1249.5	1248.0	1246.4	1244.9
142.5°	1291.0	1290.1	1289.4	1288.6	1287.8	1287.0	1285.9	1284.2	1282.7	1281.1	1279.6
145°	1339.2	1338.7	1338.2	1337.7	1337.2	1336.7	1335.4	1333.6	1331.8	1330.0	1328.2
147.5°	1382.2	1381.6	1381.1	1380.6	1380.1	1379.6	1378.7	1377.5	1376.3	1375.1	1373.9
150°	1408.5	1408.0	1407.4	1406.8	1406.3	1405.8	1405.2	1404.4	1403.6	1402.8	1402.1
152.5°	1431.4	1430.5	1430.2	1429.9	1429.5	1429.2	1428.9	1428.5	1428.2	1427.7	1427.4
155°	1463.2	1461.9	1461.7	1461.4	1461.1	1460.9	1461.0	1461.5	1462.0	1462.6	1463.1
157.5°	1491.0	1489.3	1489.7	1489.9	1490.2	1490.4	1490.6	1490.6	1490.7	1490.7	1490.8
160°	1506.9	1505.3	1505.6	1505.8	1506.1	1506.3	1506.6	1506.9	1507.1	1507.4	1507.6
162.5°	1521.2	1519.3	1519.6	1519.9	1520.1	1520.5	1520.9	1521.6	1522.3	1523.0	1523.6
165°	1540.2	1538.1	1538.4	1538.6	1538.9	1539.2	1539.7	1540.5	1541.3	1542.1	1542.9
167.5°	1555.3	1553.2	1553.2	1553.2	1553.2	1553.2	1553.7	1554.8	1555.8	1556.8	1557.9
170°	1563.7	1561.7	1561.7	1561.7	1561.7	1561.7	1562.2	1563.2	1564.3	1565.3	1566.3
172.5°	1569.3	1567.2	1567.0	1566.8	1566.6	1566.4	1566.9	1568.2	1569.4	1570.7	1572.0
175°	1576.4	1574.5	1574.3	1574.0	1573.8	1573.5	1574.0	1575.3	1576.6	1577.9	1579.2
177.5°	1579.0	1577.3	1577.1	1576.9	1576.7	1576.5	1576.9	1578.0	1579.0	1580.0	1581.1
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1427.1	1430.0	1439.3	1445.9	1453.6	1457.9	1462.4	1465.7	1470.1	1471.2	1487.1
5°	1433.5	1447.2	1471.3	1489.1	1511.2	1535.2	1551.7	1559.2	1579.2	1595.7	1628.7
7.5°	1431.7	1461.0	1497.3	1534.9	1575.4	1612.8	1645.2	1683.6	1711.0	1752.1	1792.6
10°	1430.1	1469.3	1516.0	1564.1	1620.4	1672.6	1719.4	1771.6	1814.9	1872.0	1920.8
12.5°	1425.1	1472.6	1537.4	1594.3	1662.7	1734.7	1804.0	1871.1	1909.5	2004.5	2049.4
15°	1412.9	1469.3	1550.3	1636.9	1731.1	1816.2	1904.2	1974.4	2087.7	2170.9	2223.8
17.5°	1389.6	1468.4	1564.6	1669.1	1783.5	1895.8	1995.5	2101.9	2222.1	2322.8	2429.9
20°	1378.6	1465.1	1572.4	1687.8	1806.6	1933.8	2047.2	2175.0	2306.2	2405.2	2542.6
22.5°	1358.2	1456.3	1571.8	1700.4	1827.6	1959.0	2091.7	2220.6	2372.3	2508.6	2639.4
25°	1324.9	1434.9	1554.5	1698.1	1847.2	1979.1	2137.9	2309.1	2467.1	2642.3	2772.9
27.5°	1290.0	1407.3	1527.2	1660.8	1821.2	1977.8	2177.5	2370.9	2564.0	2715.4	2812.1
30°	1263.0	1377.2	1500.9	1635.6	1794.3	1980.5	2203.8	2414.8	2603.1	2733.0	2787.3
32.5°	1234.0	1349.7	1459.1	1600.3	1769.6	1978.8	2220.4	2440.6	2605.4	2691.8	2681.2
35°	1188.2	1285.1	1391.6	1527.6	1727.0	1966.8	2230.0	2443.0	2544.1	2525.5	2385.3
37.5°	1122.2	1203.7	1308.6	1457.5	1677.5	1941.4	2210.7	2370.6	2364.0	2212.9	2009.8
40°	1081.0	1150.3	1251.4	1408.1	1639.0	1924.9	2180.5	2284.3	2196.4	1985.3	1742.0
42.5°	1027.1	1091.0	1192.0	1353.1	1596.7	1891.3	2122.7	2152.8	1980.7	1738.0	1515.0
45°	943.5	999.9	1104.3	1270.6	1533.2	1818.4	1981.9	1908.3	1676.8	1425.9	1256.2
47.5°	853.7	912.3	1012.8	1183.7	1441.4	1708.5	1786.5	1630.0	1392.3	1188.8	1033.0
50°	797.2	853.5	951.8	1124.3	1379.2	1618.4	1650.6	1448.7	1230.1	1051.5	923.6
52.5°	740.0	793.0	889.7	1062.7	1306.7	1513.9	1494.0	1288.1	1087.1	934.8	834.6
55°	654.9	705.1	797.2	959.4	1181.3	1345.5	1273.4	1076.8	910.6	792.3	716.1
57.5°	578.8	626.8	706.3	852.8	1045.8	1158.6	1066.8	901.2	769.0	678.0	621.1
60°	527.0	569.7	645.3	781.3	949.1	1034.9	944.2	797.9	686.5	613.7	562.8
62.5°	478.2	515.2	585.3	708.8	854.4	926.7	834.9	710.9	616.1	551.6	508.4
65°	404.0	437.8	499.6	595.8	715.4	763.5	684.5	584.1	510.6	462.5	433.6
67.5°	336.5	365.1	418.5	494.2	582.2	617.2	557.0	479.4	424.0	385.4	362.4
70°	291.3	316.1	358.0	423.3	503.0	529.9	473.5	409.6	369.0	338.1	316.8
72.5°	253.5	271.6	309.6	360.1	426.6	447.9	408.6	352.4	314.6	291.3	274.5
75°	193.1	208.2	233.0	273.5	319.5	331.9	302.4	267.3	241.9	225.4	212.4
77.5°	139.3	150.4	168.2	193.3	225.1	236.3	217.5	194.2	175.6	164.5	157.2
80°	105.1	114.1	129.2	149.8	169.1	175.2	164.2	146.3	133.3	127.1	121.0
82.5°	77.7	82.7	91.8	105.8	119.1	126.3	116.9	106.2	99.3	93.6	91.3
85°	39.2	41.9	46.0	51.5	59.8	62.5	59.1	56.4	52.2	48.8	48.8
87.5°	15.0	15.6	17.8	19.4	22.1	24.4	24.6	24.2	24.3	23.9	23.6
90°	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2	30.2
92.5°	21.1	20.4	19.6	18.9	19.8	22.4	24.9	27.5	30.0	31.7	33.3
95°	60.9	50.2	39.5	28.8	24.9	27.8	30.6	33.5	36.4	38.2	40.0
97.5°	139.1	134.2	129.5	124.6	112.9	94.1	75.3	56.6	37.8	39.9	41.9
100°	203.5	208.7	213.9	219.1	201.4	160.8	120.1	79.4	38.7	40.8	42.9
102.5°	264.0	267.7	271.5	275.3	254.9	210.5	166.0	121.6	77.2	70.7	64.2
105°	352.5	355.4	358.2	361.1	350.8	327.3	303.9	280.4	256.9	210.8	164.6
107.5°	446.3	448.6	450.8	453.1	456.2	459.9	463.5	467.3	471.0	437.1	403.2
110°	509.0	511.0	513.1	515.2	517.7	520.6	523.4	526.2	529.2	520.6	511.9





TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	568.8	570.7	572.6	574.4	576.8	579.7	582.6	585.4	588.2	588.4	588.5
115°	657.4	658.9	660.6	662.1	664.1	666.4	668.7	671.2	673.5	676.1	678.6
117.5°	743.9	745.8	747.8	749.7	751.2	752.5	753.7	754.9	756.1	758.1	760.2
120°	797.8	800.2	802.5	804.9	806.5	807.2	808.0	808.8	809.5	811.6	813.7
122.5°	851.8	853.7	855.7	857.7	859.1	860.1	861.1	862.0	863.0	864.5	866.0
125°	926.7	928.7	930.8	932.9	934.4	935.4	936.5	937.6	938.6	939.2	939.7
127.5°	998.9	1001.0	1003.1	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7	1013.5
130°	1044.0	1046.0	1048.1	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0	1058.0
132.5°	1087.1	1089.2	1091.3	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2	1100.2
135°	1152.6	1154.1	1155.7	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5	1164.3
137.5°	1209.3	1211.2	1213.3	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0	1221.3
140°	1246.4	1248.0	1249.5	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5	1257.5
142.5°	1281.1	1282.7	1284.2	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0	1291.8
145°	1330.0	1331.8	1333.6	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2	1339.8
147.5°	1375.1	1376.3	1377.5	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2	1382.7
150°	1402.8	1403.6	1404.4	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5	1409.0
152.5°	1427.7	1428.2	1428.5	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4	1432.3
155°	1462.6	1462.0	1461.5	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2	1464.5
157.5°	1490.7	1490.7	1490.6	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0	1492.5
160°	1507.4	1507.1	1506.9	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9	1508.4
162.5°	1523.0	1522.3	1521.6	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2	1523.0
165°	1542.1	1541.3	1540.5	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2	1542.4
167.5°	1556.8	1555.8	1554.8	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3	1557.3
170°	1565.3	1564.3	1563.2	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7	1565.8
172.5°	1570.7	1569.4	1568.2	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3	1571.5
175°	1577.9	1576.6	1575.3	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4	1578.2
177.5°	1580.0	1579.0	1578.0	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0	1580.6
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1492.6	1493.2	1499.2	1503.6	1501.4	1504.2	1505.2
5°	1630.7	1655.5	1668.5	1678.2	1678.8	1679.5	1685.1
7.5°	1826.5	1853.1	1872.5	1901.9	1910.7	1920.8	1917.8
10°	1969.5	2008.7	2042.4	2060.2	2079.5	2107.7	2085.0
12.5°	2103.1	2172.5	2223.8	2251.6	2269.7	2275.3	2264.2
15°	2323.4	2414.2	2463.0	2461.5	2523.5	2550.2	2508.3
17.5°	2525.5	2609.2	2676.2	2710.6	2762.2	2773.6	2768.3
20°	2649.2	2740.6	2792.8	2851.9	2878.7	2902.8	2906.9
22.5°	2755.8	2837.9	2894.0	2943.2	2965.6	2977.0	2983.8
25°	2865.6	2930.2	2964.0	2981.1	2987.3	2985.9	2977.0
27.5°	2858.1	2863.1	2825.9	2789.6	2756.9	2720.3	2707.5
30°	2783.9	2726.1	2623.0	2564.7	2478.7	2410.7	2438.2
32.5°	2588.7	2473.8	2358.0	2230.4	2124.7	2094.6	2064.4
35°	2209.4	2007.3	1889.2	1751.7	1696.7	1641.7	1604.0
37.5°	1787.5	1631.1	1491.0	1401.1	1345.9	1311.2	1292.5
40°	1545.5	1404.6	1289.2	1216.4	1174.5	1135.3	1129.7
42.5°	1352.5	1221.5	1134.7	1076.7	1036.4	1019.8	1007.7
45°	1107.8	1016.3	958.0	916.8	889.9	879.6	865.9
47.5°	937.7	873.0	829.2	801.1	780.9	773.3	772.1
50°	842.5	788.9	756.6	734.6	718.8	716.1	705.1
52.5°	771.0	724.6	699.4	680.2	668.8	661.1	657.8
55°	669.3	638.4	615.7	604.7	595.8	588.2	588.2
57.5°	585.6	559.8	544.8	535.4	532.7	527.4	523.9
60°	533.9	512.0	500.3	492.0	486.6	487.3	481.0
62.5°	483.4	469.1	458.0	449.7	443.1	443.2	443.6
65°	411.6	400.6	392.4	389.6	385.6	380.7	382.1
67.5°	348.8	338.5	332.0	327.4	326.0	323.4	327.4
70°	303.8	296.2	291.3	287.2	285.9	286.6	290.0
72.5°	262.5	257.1	254.0	252.1	249.0	249.1	251.6
75°	206.1	202.1	199.2	197.2	196.5	196.5	196.5
77.5°	151.5	150.5	149.3	146.2	146.3	147.2	147.3
80°	119.6	117.5	116.8	115.4	113.4	112.0	115.4
82.5°	89.4	87.3	86.5	86.3	83.1	82.9	85.7
85°	48.1	46.0	46.8	46.0	46.0	45.3	45.3
87.5°	23.3	22.9	22.5	23.2	22.8	22.3	23.5
90°	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	35.0	36.8	37.7	38.0	38.4	38.7	39.0
95°	41.8	43.6	44.5	44.5	44.5	44.5	44.5
97.5°	44.0	46.2	47.3	47.6	47.9	48.1	48.4
100°	44.9	47.1	48.3	48.5	48.8	49.0	49.3
102.5°	57.8	51.3	48.4	48.8	49.3	49.8	50.2
105°	118.5	72.3	49.6	50.1	50.6	51.1	51.6
107.5°	369.4	335.6	301.2	266.5	231.7	196.9	162.2
110°	503.3	494.7	471.8	434.5	397.2	359.9	322.7



TEST NUMBER: P332036-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	588.8	589.0	585.0	577.1	569.3	561.4	553.5
115°	681.3	683.9	685.7	686.7	687.8	688.8	689.8
117.5°	762.3	764.4	765.6	765.8	766.0	766.2	766.4
120°	815.8	817.9	818.9	818.9	818.9	818.9	818.9
122.5°	867.5	868.9	869.7	869.9	870.1	870.4	870.6
125°	940.2	940.7	941.2	941.7	942.3	942.8	943.3
127.5°	1014.3	1015.1	1015.3	1014.8	1014.3	1013.8	1013.2
130°	1059.0	1060.2	1060.4	1059.9	1059.3	1058.8	1058.3
132.5°	1101.4	1102.4	1102.5	1101.8	1101.1	1100.3	1099.5
135°	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8
137.5°	1222.5	1223.8	1224.2	1223.7	1223.1	1222.6	1222.0
140°	1258.5	1259.6	1259.8	1259.3	1258.8	1258.3	1257.8
142.5°	1292.6	1293.4	1293.5	1292.8	1292.0	1291.3	1290.6
145°	1340.3	1340.8	1341.0	1341.0	1341.0	1341.0	1341.0
147.5°	1383.2	1383.7	1383.4	1382.2	1381.0	1379.8	1378.6
150°	1409.5	1410.0	1409.9	1409.1	1408.4	1407.5	1406.7
152.5°	1433.3	1434.2	1434.1	1432.9	1431.7	1430.5	1429.3
155°	1465.8	1467.1	1466.9	1465.4	1463.9	1462.3	1460.8
157.5°	1494.0	1495.6	1495.4	1493.4	1491.3	1489.2	1487.2
160°	1510.0	1511.6	1511.5	1509.6	1507.8	1505.9	1504.1
162.5°	1524.7	1526.5	1526.5	1524.9	1523.3	1521.7	1520.0
165°	1544.4	1546.5	1546.6	1544.8	1543.0	1541.2	1539.3
167.5°	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2
170°	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7
172.5°	1573.5	1575.6	1575.5	1573.2	1570.9	1568.6	1566.3
175°	1580.0	1581.9	1581.7	1579.6	1577.5	1575.5	1573.4
177.5°	1582.4	1584.0	1583.8	1581.8	1579.6	1577.5	1575.5
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

(END OF REPORT)