

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332079

Luminaire Tested: **S123DIP-S1165D1025U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332079  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D1025U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8281.4 lumens  
Efficiency: N/A  
Efficacy: 124.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45	40
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	57	49	43	64	54	46	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.2	2.1
10°-20°	486.2	5.9
20°-30°	718.3	8.7
30°-40°	839.0	10.1
40°-50°	843.5	10.2
50°-60°	740.9	8.9
60°-70°	552.0	6.7
70°-80°	314.5	3.8
80°-90°	94.0	1.1
90°-100°	82.8	1.0
100°-110°	247.8	3.0
110°-120°	421.4	5.1
120°-130°	554.3	6.7
130°-140°	623.0	7.5
140°-150°	612.4	7.4
150°-160°	515.6	6.2
160°-170°	343.2	4.1
170°-180°	120.2	1.5
0°-30°	1376.7	16.6
0°-40°	2215.7	26.8
0°-60°	3800.2	45.9
0°-90°	4760.7	57.5
90°-120°	752.0	9.1
90°-150°	2541.8	30.7
90°-180°	3521.0	42.5
0°-180°	8281.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	1	11	24	28	30	8
95°	59	66	74	78	78	66
105°	225	227	236	236	238	241
115°	424	427	425	426	425	420
125°	621	624	622	618	614	553
135°	806	811	810	807	805	621
145°	977	979	982	981	977	610
155°	1119	1119	1120	1123	1117	515
165°	1219	1216	1216	1221	1215	344
175°	1268	1264	1264	1269	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	32.9	32.5	32.1	31.7	31.3	31.3	31.6	31.9	32.2	32.5	32.4
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	24.2	25.7	27.2	28.7	30.2	31.8	33.4	35.0	36.7	38.3	39.0
95°	58.9	60.4	62.0	63.6	65.1	66.8	68.5	70.3	72.1	73.9	74.8
97.5°	104.6	105.8	106.9	108.1	109.2	110.4	111.7	113.0	114.3	115.6	116.6
100°	135.8	137.1	138.4	139.7	141.1	142.3	143.4	144.5	145.6	146.7	147.4
102.5°	171.7	172.5	173.3	174.1	174.9	176.0	177.5	178.9	180.4	181.9	182.5
105°	224.6	225.0	225.5	225.9	226.4	227.6	229.6	231.6	233.6	235.6	235.6
107.5°	286.1	286.4	286.6	286.9	287.2	287.7	288.5	289.3	290.1	290.9	291.6
110°	324.4	324.9	325.3	325.7	326.2	326.6	327.1	327.5	328.0	328.4	329.3



TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	364.3	364.6	364.9	365.1	365.4	365.6	365.7	365.8	365.9	365.9	367.0
115°	424.2	424.9	425.6	426.2	426.9	427.0	426.6	426.1	425.7	425.2	425.5
117.5°	484.5	485.0	485.4	485.9	486.3	486.2	485.7	485.1	484.5	483.9	483.9
120°	522.1	523.4	524.7	526.1	527.4	527.5	526.4	525.3	524.2	523.1	522.8
122.5°	561.2	562.2	563.1	564.1	565.1	565.3	564.7	564.1	563.6	563.0	562.4
125°	620.9	621.6	622.2	622.9	623.5	623.7	623.2	622.8	622.3	621.9	621.0
127.5°	676.0	677.4	678.8	680.2	681.7	682.1	681.6	681.2	680.7	680.2	678.9
130°	712.7	714.5	716.3	718.0	719.8	720.4	719.7	719.0	718.4	717.7	716.8
132.5°	749.5	751.2	753.0	754.8	756.6	757.2	756.7	756.2	755.7	755.2	754.2
135°	805.6	806.9	808.2	809.5	810.9	811.4	811.2	811.0	810.8	810.5	809.7
137.5°	857.5	858.6	859.7	860.8	861.9	862.7	863.3	863.9	864.5	865.0	864.1
140°	893.4	894.5	895.6	896.7	897.8	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	926.1	927.2	928.4	929.5	930.6	931.3	931.7	932.1	932.5	932.9	932.7
145°	977.2	977.7	978.1	978.6	979.0	979.6	980.2	980.9	981.6	982.2	982.0
147.5°	1022.0	1022.8	1023.6	1024.4	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4
150°	1053.1	1053.6	1054.0	1054.4	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1
152.5°	1078.7	1079.3	1079.9	1080.5	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0
155°	1119.0	1119.0	1119.0	1119.0	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9
157.5°	1153.3	1153.1	1152.8	1152.5	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9
160°	1174.9	1174.4	1174.0	1173.6	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0
162.5°	1194.1	1193.4	1192.8	1192.2	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2
165°	1218.8	1218.1	1217.5	1216.8	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1
167.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8
170°	1249.8	1248.9	1248.0	1247.1	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3
172.5°	1258.5	1257.7	1256.8	1255.9	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9
175°	1267.7	1266.8	1265.9	1265.1	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1
177.5°	1271.5	1270.8	1270.1	1269.4	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	32.3	32.2	32.0	32.0	32.1	32.2	32.3	32.4
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	39.8	40.5	41.2	41.4	41.1	40.9	40.6	40.3
95°	75.6	76.5	77.4	77.9	77.9	77.9	77.9	77.9
97.5°	117.6	118.7	119.7	120.1	120.1	120.0	119.9	119.8
100°	148.1	148.7	149.4	150.0	150.4	150.8	151.3	151.7
102.5°	183.2	183.9	184.5	184.8	184.7	184.6	184.6	184.5
105°	235.6	235.6	235.6	235.8	236.2	236.7	237.1	237.6
107.5°	292.3	293.0	293.7	293.9	293.7	293.4	293.1	292.9
110°	330.2	331.1	332.0	332.2	331.7	331.3	330.9	330.4





TEST NUMBER: P332079

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.1	369.1	370.2	370.7	370.6	370.5	370.4	370.3
115°	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2
117.5°	483.8	483.8	483.8	483.4	482.8	482.2	481.6	480.9
120°	522.6	522.4	522.2	521.8	521.4	521.0	520.5	520.1
122.5°	561.8	561.3	560.7	560.1	559.5	558.8	558.2	557.6
125°	620.1	619.2	618.3	617.4	616.6	615.7	614.8	613.9
127.5°	677.7	676.5	675.2	674.1	673.1	672.0	671.0	670.0
130°	715.9	715.0	714.2	712.9	711.4	709.8	708.3	706.7
132.5°	753.1	752.1	751.0	749.9	748.7	747.5	746.3	745.1
135°	808.8	807.9	807.0	806.3	805.9	805.4	805.0	804.6
137.5°	863.2	862.3	861.3	860.4	859.6	858.7	857.9	857.1
140°	898.9	898.7	898.5	897.6	896.1	894.5	893.0	891.4
142.5°	932.5	932.3	932.0	931.3	930.1	928.9	927.7	926.5
145°	981.8	981.6	981.3	980.8	979.9	979.0	978.1	977.2
147.5°	1028.4	1028.4	1028.4	1027.7	1026.4	1025.0	1023.7	1022.4
150°	1057.1	1057.1	1057.1	1056.4	1055.1	1053.8	1052.4	1051.1
152.5°	1083.4	1083.7	1084.1	1083.7	1082.5	1081.4	1080.2	1079.1
155°	1121.8	1122.7	1123.5	1123.2	1121.7	1120.1	1118.5	1117.0
157.5°	1154.8	1155.7	1156.7	1156.5	1155.3	1154.0	1152.8	1151.5
160°	1175.1	1176.2	1177.3	1177.4	1176.6	1175.7	1174.8	1173.9
162.5°	1194.3	1195.4	1196.5	1196.3	1194.9	1193.5	1192.1	1190.7
165°	1218.5	1219.8	1221.1	1221.0	1219.5	1217.9	1216.4	1214.8
167.5°	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4
170°	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8
172.5°	1257.3	1258.7	1260.0	1260.0	1258.4	1256.9	1255.3	1253.7
175°	1266.4	1267.7	1269.1	1268.9	1267.4	1265.8	1264.3	1262.7
177.5°	1270.5	1271.5	1272.6	1272.5	1271.3	1270.0	1268.8	1267.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7

(END OF REPORT)