

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332042-840

Luminaire Tested: **S123DIP-S1000D1195U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332042-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8979.8 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	97	93	89	85	89	85	82	79	71	69	67	58	57	55	47	45	44	39
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37	33
3	80	71	64	58	74	65	59	54	55	50	46	45	42	39	36	34	32	28
4	74	63	55	49	67	58	51	46	49	44	39	40	36	33	32	30	27	24
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24	20
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21	18
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	1.7
10°-20°	425.2	4.7
20°-30°	628.0	7.0
30°-40°	733.6	8.2
40°-50°	737.6	8.2
50°-60°	647.9	7.2
60°-70°	482.7	5.4
70°-80°	275.0	3.1
80°-90°	83.4	0.9
90°-100°	57.4	0.6
100°-110°	273.6	3.0
110°-120°	657.3	7.3
120°-130°	837.0	9.3
130°-140°	894.3	10.0
140°-150°	836.3	9.3
150°-160°	674.6	7.5
160°-170°	435.4	4.8
170°-180°	150.0	1.7
0°-30°	1203.8	13.4
0°-40°	1937.4	21.6
0°-60°	3322.8	37.0
0°-90°	4163.9	46.4
90°-120°	988.3	11.0
90°-150°	3555.9	39.6
90°-180°	4816.0	53.6
0°-180°	8979.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	1	13	28	33	35	7
95°	72	27	36	44	44	88
105°	350	356	257	61	52	371
115°	656	663	674	685	690	647
125°	924	934	939	941	943	825
135°	1151	1158	1163	1166	1163	886
145°	1328	1336	1339	1341	1341	831
155°	1463	1461	1462	1467	1461	674
165°	1543	1539	1538	1547	1539	436
175°	1579	1574	1574	1582	1573	150
180°	1579	1579	1579	1579	1579	



TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.8	28.6	28.4	28.2	28.0	28.1	28.5	29.0	29.4	29.8	29.8
90°	1.2	3.7	6.4	9.0	11.6	14.6	18.0	21.4	24.7	28.2	29.2
92.5°	21.8	21.1	20.4	19.6	18.9	19.8	22.4	24.9	27.5	30.0	31.7
95°	71.6	60.9	50.2	39.5	28.8	24.9	27.8	30.6	33.5	36.4	38.2
97.5°	143.8	139.1	134.2	129.5	124.6	112.9	94.1	75.3	56.6	37.8	39.9
100°	198.2	203.5	208.7	213.9	219.1	201.4	160.8	120.1	79.4	38.7	40.8
102.5°	260.2	264.0	267.7	271.5	275.3	254.9	210.5	166.0	121.6	77.2	70.7
105°	349.6	352.5	355.4	358.2	361.1	350.8	327.3	303.9	280.4	256.9	210.8
107.5°	443.9	446.3	448.6	450.8	453.1	456.2	459.9	463.5	467.3	471.0	437.1
110°	506.9	509.0	511.0	513.1	515.2	517.7	520.6	523.4	526.2	529.2	520.6



TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	566.9	568.8	570.7	572.6	574.4	576.8	579.7	582.6	585.4	588.2	588.4
115°	655.9	657.4	658.9	660.6	662.1	664.1	666.4	668.7	671.2	673.5	676.1
117.5°	741.9	743.9	745.8	747.8	749.7	751.2	752.5	753.7	754.9	756.1	758.1
120°	795.5	797.8	800.2	802.5	804.9	806.5	807.2	808.0	808.8	809.5	811.6
122.5°	849.9	851.8	853.7	855.7	857.7	859.1	860.1	861.1	862.0	863.0	864.5
125°	924.5	926.7	928.7	930.8	932.9	934.4	935.4	936.5	937.6	938.6	939.2
127.5°	996.8	998.9	1001.0	1003.1	1005.1	1006.8	1008.0	1009.4	1010.6	1011.8	1012.7
130°	1041.9	1044.0	1046.0	1048.1	1050.2	1051.8	1052.8	1053.9	1054.9	1055.9	1057.0
132.5°	1085.0	1087.1	1089.2	1091.3	1093.4	1094.8	1095.7	1096.5	1097.3	1098.2	1099.2
135°	1150.9	1152.6	1154.1	1155.7	1157.2	1158.5	1159.6	1160.6	1161.6	1162.8	1163.5
137.5°	1207.3	1209.3	1211.2	1213.3	1215.3	1216.5	1217.1	1217.7	1218.2	1218.8	1220.0
140°	1244.9	1246.4	1248.0	1249.5	1251.1	1252.2	1253.0	1253.8	1254.7	1255.4	1256.5
142.5°	1279.6	1281.1	1282.7	1284.2	1285.9	1287.0	1287.8	1288.6	1289.4	1290.1	1291.0
145°	1328.2	1330.0	1331.8	1333.6	1335.4	1336.7	1337.2	1337.7	1338.2	1338.7	1339.2
147.5°	1373.9	1375.1	1376.3	1377.5	1378.7	1379.6	1380.1	1380.6	1381.1	1381.6	1382.2
150°	1402.1	1402.8	1403.6	1404.4	1405.2	1405.8	1406.3	1406.8	1407.4	1408.0	1408.5
152.5°	1427.4	1427.7	1428.2	1428.5	1428.9	1429.2	1429.5	1429.9	1430.2	1430.5	1431.4
155°	1463.1	1462.6	1462.0	1461.5	1461.0	1460.9	1461.1	1461.4	1461.7	1461.9	1463.2
157.5°	1490.8	1490.7	1490.7	1490.6	1490.6	1490.4	1490.2	1489.9	1489.7	1489.3	1491.0
160°	1507.6	1507.4	1507.1	1506.9	1506.6	1506.3	1506.1	1505.8	1505.6	1505.3	1506.9
162.5°	1523.6	1523.0	1522.3	1521.6	1520.9	1520.5	1520.1	1519.9	1519.6	1519.3	1521.2
165°	1542.9	1542.1	1541.3	1540.5	1539.7	1539.2	1538.9	1538.6	1538.4	1538.1	1540.2
167.5°	1557.9	1556.8	1555.8	1554.8	1553.7	1553.2	1553.2	1553.2	1553.2	1553.2	1555.3
170°	1566.3	1565.3	1564.3	1563.2	1562.2	1561.7	1561.7	1561.7	1561.7	1561.7	1563.7
172.5°	1572.0	1570.7	1569.4	1568.2	1566.9	1566.4	1566.6	1566.8	1567.0	1567.2	1569.3
175°	1579.2	1577.9	1576.6	1575.3	1574.0	1573.5	1573.8	1574.0	1574.3	1574.5	1576.4
177.5°	1581.1	1580.0	1579.0	1578.0	1576.9	1576.5	1576.7	1576.9	1577.1	1577.3	1579.0
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2



TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	29.8	29.7	29.7	29.7	29.8	29.9	30.0	30.1
90°	30.2	31.3	32.3	33.1	33.6	34.1	34.6	35.2
92.5°	33.3	35.0	36.8	37.7	38.0	38.4	38.7	39.0
95°	40.0	41.8	43.6	44.5	44.5	44.5	44.5	44.5
97.5°	41.9	44.0	46.2	47.3	47.6	47.9	48.1	48.4
100°	42.9	44.9	47.1	48.3	48.5	48.8	49.0	49.3
102.5°	64.2	57.8	51.3	48.4	48.8	49.3	49.8	50.2
105°	164.6	118.5	72.3	49.6	50.1	50.6	51.1	51.6
107.5°	403.2	369.4	335.6	301.2	266.5	231.7	196.9	162.2
110°	511.9	503.3	494.7	471.8	434.5	397.2	359.9	322.7



TEST NUMBER: P332042-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	588.5	588.8	589.0	585.0	577.1	569.3	561.4	553.5
115°	678.6	681.3	683.9	685.7	686.7	687.8	688.8	689.8
117.5°	760.2	762.3	764.4	765.6	765.8	766.0	766.2	766.4
120°	813.7	815.8	817.9	818.9	818.9	818.9	818.9	818.9
122.5°	866.0	867.5	868.9	869.7	869.9	870.1	870.4	870.6
125°	939.7	940.2	940.7	941.2	941.7	942.3	942.8	943.3
127.5°	1013.5	1014.3	1015.1	1015.3	1014.8	1014.3	1013.8	1013.2
130°	1058.0	1059.0	1060.2	1060.4	1059.9	1059.3	1058.8	1058.3
132.5°	1100.2	1101.4	1102.4	1102.5	1101.8	1101.1	1100.3	1099.5
135°	1164.3	1165.1	1165.9	1165.9	1165.1	1164.3	1163.5	1162.8
137.5°	1221.3	1222.5	1223.8	1224.2	1223.7	1223.1	1222.6	1222.0
140°	1257.5	1258.5	1259.6	1259.8	1259.3	1258.8	1258.3	1257.8
142.5°	1291.8	1292.6	1293.4	1293.5	1292.8	1292.0	1291.3	1290.6
145°	1339.8	1340.3	1340.8	1341.0	1341.0	1341.0	1341.0	1341.0
147.5°	1382.7	1383.2	1383.7	1383.4	1382.2	1381.0	1379.8	1378.6
150°	1409.0	1409.5	1410.0	1409.9	1409.1	1408.4	1407.5	1406.7
152.5°	1432.3	1433.3	1434.2	1434.1	1432.9	1431.7	1430.5	1429.3
155°	1464.5	1465.8	1467.1	1466.9	1465.4	1463.9	1462.3	1460.8
157.5°	1492.5	1494.0	1495.6	1495.4	1493.4	1491.3	1489.2	1487.2
160°	1508.4	1510.0	1511.6	1511.5	1509.6	1507.8	1505.9	1504.1
162.5°	1523.0	1524.7	1526.5	1526.5	1524.9	1523.3	1521.7	1520.0
165°	1542.4	1544.4	1546.5	1546.6	1544.8	1543.0	1541.2	1539.3
167.5°	1557.3	1559.4	1561.6	1561.6	1559.4	1557.3	1555.3	1553.2
170°	1565.8	1567.9	1569.9	1569.9	1567.9	1565.8	1563.7	1561.7
172.5°	1571.5	1573.5	1575.6	1575.5	1573.2	1570.9	1568.6	1566.3
175°	1578.2	1580.0	1581.9	1581.7	1579.6	1577.5	1575.5	1573.4
177.5°	1580.6	1582.4	1584.0	1583.8	1581.8	1579.6	1577.5	1575.5
180°	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2	1579.2

(END OF REPORT)