

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332080

Luminaire Tested: **S123DIP-S1165D1025U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332080
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8470.6 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	2.0
10°-20°	486.2	5.7
20°-30°	718.3	8.5
30°-40°	839.0	9.9
40°-50°	843.5	10.0
50°-60°	740.9	8.7
60°-70°	552.0	6.5
70°-80°	314.5	3.7
80°-90°	94.1	1.1
90°-100°	274.4	3.2
100°-110°	777.0	9.2
110°-120°	764.4	9.0
120°-130°	609.7	7.2
130°-140°	480.7	5.7
140°-150°	358.8	4.2
150°-160°	250.1	3.0
160°-170°	146.9	1.7
170°-180°	47.8	0.6
0°-30°	1376.7	16.3
0°-40°	2215.7	26.2
0°-60°	3800.2	44.9
0°-90°	4760.8	56.2
90°-120°	1815.8	21.4
90°-150°	3265.1	38.5
90°-180°	3710.0	43.8
0°-180°	8470.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	2	12	25	28	29	7
95°	34	110	592	173	116	37
105°	116	171	802	1403	1270	123
115°	205	255	614	1346	1544	203
125°	284	336	573	1038	1218	252
135°	333	398	565	855	987	258
145°	380	436	558	701	772	238
155°	432	466	540	614	640	199
165°	472	486	517	548	558	133
175°	492	493	496	503	502	47
180°	493	493	493	493	493	



TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	33.1	32.7	32.2	32.0	31.5	31.4	31.7	32.0	32.3	32.7	32.2
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8
95°	33.9	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1
97.5°	57.9	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4
100°	73.9	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9
102.5°	90.6	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9
105°	115.8	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0
107.5°	142.5	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4
110°	161.7	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3



TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0
115°	204.6	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6
117.5°	230.0	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0
120°	247.5	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7
122.5°	262.7	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3
125°	284.5	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8
127.5°	301.1	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0
130°	311.4	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8
132.5°	319.4	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4
135°	333.4	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9
137.5°	346.6	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1
140°	355.4	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9
142.5°	364.9	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5
145°	380.3	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9
147.5°	395.9	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5
150°	406.3	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9
152.5°	416.6	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6
155°	432.2	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0
157.5°	444.6	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2
160°	454.2	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0
162.5°	461.4	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8
165°	472.1	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0
167.5°	480.3	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7
170°	485.1	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1
172.5°	488.3	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5
175°	492.1	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1
177.5°	493.9	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	32.1	32.0	31.9	32.2	32.0	32.2	32.4	32.2
90°	25.0	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	84.0	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	359.3	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	895.8	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1176.9	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1270.3	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1297.6	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1219.0	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1143.9	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P332080

CATALOG NUMBER: S123DIP-S1165D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1069.6	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	971.2	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	900.0	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	862.4	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	832.9	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	793.6	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	759.2	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	737.7	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	717.7	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	690.7	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	666.2	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	651.8	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	638.2	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	621.9	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	608.5	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	598.9	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	590.1	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	576.9	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	563.0	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	555.0	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	545.4	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	533.0	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	522.2	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	515.1	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	508.7	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	500.1	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	494.7	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)