

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332081

Luminaire Tested: **S123DIP-S1165D1195U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332081
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1195U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9669.1 lumens
Efficiency: N/A
Efficacy: 134.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51									51																			
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	49	48	43									43																			
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37									37																			
3	82	73	65	60	75	67	61	56	58	53	49	48	45	42	40	37	35	31									31																			
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27									27																			
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	24									24																			
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21									21																			
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18									18																			
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17									17																			
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15									15																			
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	14									14																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17460	17460	17460	17460
5°	20822	17535	15540	17535
10°	26063	17446	14036	17446
15°	31967	17306	13067	17306
20°	38080	17087	12441	17087
25°	40435	16820	12302	16820
30°	34657	16625	12367	16625
35°	24103	16348	12496	16348
40°	18156	16024	12456	16024
45°	15075	15541	12298	15541
50°	13504	14555	12188	14555
55°	12624	13495	12035	13495
60°	11842	12385	11911	12385
65°	11130	11291	11530	11291
70°	10439	10043	10980	10043
75°	9349	8792	10069	8792
80°	8182	7209	8672	7209
85°	6410	5236	5829	5236



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.8	1.7
10°-20°	512.4	5.3
20°-30°	859.9	8.9
30°-40°	973.7	10.1
40°-50°	873.2	9.0
50°-60°	704.7	7.3
60°-70°	491.0	5.1
70°-80°	258.1	2.7
80°-90°	67.5	0.7
90°-100°	56.9	0.6
100°-110°	271.0	2.8
110°-120°	650.9	6.7
120°-130°	828.8	8.6
130°-140°	885.6	9.2
140°-150°	828.1	8.6
150°-160°	668.0	6.9
160°-170°	431.1	4.5
170°-180°	148.6	1.5
0°-30°	1532.1	15.8
0°-40°	2505.8	25.9
0°-60°	4083.7	42.2
0°-90°	4900.3	50.7
90°-120°	978.7	10.1
90°-150°	3521.2	36.4
90°-180°	4769.0	49.3
0°-180°	9669.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1622	1622	1622	1622	1622	
5°	1927	1623	1438	1623	1927	200
15°	2869	1553	1173	1553	2869	828
25°	3405	1416	1036	1416	3405	1493
35°	1834	1244	951	1244	1834	1192
45°	990	1021	808	1021	990	784
55°	673	719	641	719	673	604
65°	437	443	453	443	437	435
75°	225	211	242	211	225	241
85°	52	42	47	42	52	62
90°	35	1	35	1	35	18
95°	44	71	44	71	44	37
105°	51	346	51	346	51	117
115°	683	650	683	650	683	631
125°	934	916	934	916	934	834
135°	1151	1140	1151	1140	1151	888
145°	1328	1315	1328	1315	1328	829
155°	1446	1449	1446	1449	1446	667
165°	1524	1528	1524	1528	1524	430
175°	1558	1564	1558	1564	1558	148
180°	1564	1564	1564	1564	1564	



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1721.5	1720.2	1717.1	1719.6	1714.6	1707.6	1707.0	1700.7	1682.5	1681.2	1676.2
5°	1927.1	1920.8	1920.0	1919.2	1908.2	1893.3	1865.0	1862.6	1824.9	1806.0	1783.3
7.5°	2193.3	2196.6	2185.2	2175.1	2141.5	2119.3	2089.0	2050.2	2003.8	1956.8	1925.5
10°	2384.5	2410.4	2378.2	2356.2	2335.8	2297.2	2252.5	2196.6	2140.8	2075.6	2026.1
12.5°	2589.5	2602.2	2595.7	2575.0	2543.2	2484.6	2405.2	2343.8	2292.4	2183.8	2139.9
15°	2868.6	2916.6	2885.9	2815.2	2816.7	2760.9	2657.2	2543.2	2482.7	2387.6	2258.0
17.5°	3166.0	3172.0	3158.9	3100.0	3060.7	2984.0	2888.3	2779.0	2656.4	2541.4	2403.8
20°	3324.4	3319.7	3292.2	3261.6	3194.0	3134.3	3029.7	2907.9	2750.7	2637.6	2487.4
22.5°	3412.5	3404.6	3391.6	3365.9	3309.7	3245.5	3151.7	3018.6	2868.9	2713.0	2539.6
25°	3404.6	3414.8	3416.4	3409.3	3389.7	3351.2	3277.3	3171.2	3021.9	2821.5	2640.7
27.5°	3096.5	3111.0	3153.0	3190.2	3231.9	3274.3	3268.6	3216.0	3105.5	2932.4	2711.4
30°	2788.4	2757.0	2834.8	2933.1	2999.9	3117.7	3183.8	3187.7	3125.6	2977.1	2761.7
32.5°	2360.9	2395.5	2429.9	2550.8	2696.8	2829.2	2960.6	3066.4	3078.5	2979.6	2791.3
35°	1834.3	1877.6	1940.4	2003.3	2160.5	2295.7	2526.7	2727.9	2888.3	2909.5	2793.9
37.5°	1478.2	1499.5	1539.3	1602.3	1705.1	1865.5	2044.2	2298.5	2530.8	2703.6	2711.1
40°	1292.1	1298.3	1343.1	1391.1	1474.4	1606.4	1767.5	1992.3	2270.5	2511.8	2612.4
42.5°	1152.5	1166.3	1185.3	1231.4	1297.7	1397.1	1546.9	1732.6	1987.6	2265.3	2462.1
45°	990.3	1006.0	1017.8	1048.4	1095.6	1162.4	1266.9	1436.7	1630.8	1917.6	2182.5
47.5°	883.1	884.3	893.1	916.2	948.3	998.4	1072.3	1181.4	1359.6	1592.3	1864.2
50°	806.4	818.9	822.1	840.1	865.3	902.2	963.5	1056.3	1202.5	1406.8	1656.7
52.5°	752.3	756.1	764.9	777.9	799.9	828.7	881.8	954.4	1069.2	1243.3	1473.1
55°	672.7	672.7	681.4	691.6	704.2	730.1	765.5	818.9	906.2	1041.3	1231.5
57.5°	599.2	603.1	609.2	612.4	623.1	640.2	669.8	710.3	775.4	879.4	1030.7
60°	550.1	557.2	556.4	562.7	572.2	585.5	610.7	643.7	701.8	785.1	912.5
62.5°	507.4	506.9	506.8	514.3	523.7	536.5	552.8	581.4	630.8	704.7	813.1
65°	437.0	435.4	440.9	445.6	448.8	458.2	470.8	495.9	528.9	583.9	668.0
67.5°	374.4	369.9	372.8	374.4	379.8	387.1	398.9	414.5	440.7	484.9	548.3
70°	331.7	327.7	326.9	328.5	333.2	338.7	347.4	362.3	386.7	422.0	468.4
72.5°	287.6	285.0	284.8	288.3	290.5	294.1	300.2	313.9	333.2	359.8	403.0
75°	224.8	224.8	224.8	225.6	227.9	231.1	235.8	242.8	257.8	276.6	305.7
77.5°	168.5	168.3	167.4	167.2	170.7	172.1	173.2	179.8	188.1	200.9	222.1
80°	132.0	128.1	129.7	132.0	133.6	134.4	136.8	138.3	145.4	152.5	167.4
82.5°	98.1	94.8	95.1	98.7	99.0	99.8	102.2	104.4	107.0	113.5	121.5
85°	51.9	51.9	52.7	52.7	53.4	52.7	55.0	55.8	55.8	59.7	64.4
87.5°	25.8	24.5	25.0	25.5	24.8	25.3	25.7	26.1	26.5	27.0	26.9
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9	28.9	27.9	24.5
92.5°	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0	31.4	29.7	27.2
95°	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6	37.8	36.0	33.2
97.5°	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5	39.5	37.4	35.0
100°	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5	40.4	38.3	35.6
102.5°	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6	70.0	76.4	120.4
105°	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0	208.7	254.4	277.7
107.5°	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3	432.8	466.4	462.7
110°	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9	515.5	524.0	521.1



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8	582.7	582.5	579.7
115°	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0	669.5	666.9	664.6
117.5°	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8	750.7	748.7	747.5
120°	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8	803.7	801.6	800.9
122.5°	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5	856.1	854.6	853.6
125°	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5	930.0	929.4	928.4
127.5°	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6	1002.8	1001.9	1000.7
130°	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7	1046.7	1045.6	1044.6
132.5°	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5	1088.5	1087.5	1086.6
135°	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4	1150.3
137.5°	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4	1208.1	1206.9	1206.3
140°	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2	1244.2	1243.1	1242.4
142.5°	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2	1278.4	1277.5	1276.8
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7	1326.1	1325.6	1325.1
147.5°	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2	1368.7	1368.1	1367.6
150°	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2	1394.7	1394.2	1393.7
152.5°	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3	1417.4	1416.5	1416.2
155°	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2	1448.9	1447.6	1447.4
157.5°	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9	1476.4	1474.8	1475.1
160°	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7	1492.2	1490.6	1490.9
162.5°	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1	1506.3	1504.5	1504.8
165°	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3	1525.2	1523.1	1523.4
167.5°	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0	1538.0
170°	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4	1546.4
172.5°	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1	1554.0	1551.9	1551.7
175°	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8	1561.0	1559.1	1558.9
177.5°	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2	1563.6	1561.9	1561.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1672.4	1667.4	1662.4	1653.6	1646.0	1635.3	1632.2	1628.4	1617.1	1607.1	1599.5
5°	1774.6	1755.7	1728.2	1703.1	1682.7	1655.2	1639.4	1622.9	1599.3	1578.1	1560.8
7.5°	1881.5	1844.4	1801.6	1755.4	1712.4	1670.9	1637.4	1607.5	1574.5	1543.2	1518.9
10°	1966.4	1912.9	1853.2	1788.8	1733.7	1680.3	1635.5	1596.2	1553.8	1516.8	1486.2
12.5°	2063.2	1984.0	1901.6	1823.3	1758.3	1684.1	1629.8	1579.9	1531.8	1487.3	1452.9
15°	2177.8	2077.2	1979.7	1872.1	1773.0	1680.3	1615.9	1553.0	1497.2	1451.6	1407.6
17.5°	2282.2	2168.2	2039.8	1908.8	1789.4	1679.4	1589.1	1518.1	1448.3	1392.5	1348.6
20°	2341.3	2211.6	2066.2	1930.2	1798.2	1675.6	1576.6	1491.7	1416.2	1357.3	1307.8
22.5°	2392.2	2240.5	2090.1	1944.7	1797.6	1665.5	1553.3	1465.9	1384.2	1326.5	1273.8
25°	2445.0	2263.5	2112.6	1942.0	1777.8	1641.0	1515.3	1416.2	1334.5	1266.9	1212.7
27.5°	2490.3	2261.9	2082.8	1899.4	1746.6	1609.6	1475.3	1369.1	1282.3	1208.9	1153.9
30°	2520.4	2265.0	2052.0	1870.5	1716.5	1575.0	1444.5	1337.6	1246.5	1171.8	1119.9
32.5°	2539.3	2263.1	2023.7	1830.3	1668.7	1543.5	1411.2	1300.5	1206.9	1133.5	1083.5
35°	2550.3	2249.3	1975.0	1747.1	1591.5	1469.7	1358.9	1244.1	1145.9	1077.5	1020.9
37.5°	2528.3	2220.2	1918.4	1666.9	1496.6	1376.6	1283.4	1185.6	1091.6	1016.4	967.6
40°	2493.7	2201.4	1874.4	1610.4	1431.2	1315.6	1236.3	1140.4	1047.6	976.1	930.5
42.5°	2427.7	2163.0	1826.0	1547.5	1363.3	1247.7	1174.6	1094.5	1006.8	939.6	894.1
45°	2266.6	2079.5	1753.4	1453.2	1263.0	1143.5	1079.1	1020.9	941.5	876.3	837.0
47.5°	2043.1	1954.0	1648.4	1353.7	1158.3	1043.4	976.4	929.6	871.6	818.9	781.2
50°	1887.8	1850.8	1577.3	1285.8	1088.5	976.1	911.7	869.2	827.6	774.9	740.3
52.5°	1708.6	1731.4	1494.4	1215.3	1017.5	907.0	846.3	812.6	774.8	731.5	701.4
55°	1456.3	1538.8	1351.0	1097.1	911.7	806.4	749.0	719.1	697.1	664.9	639.0
57.5°	1220.1	1325.1	1196.0	975.3	807.8	716.9	661.9	629.4	615.2	598.4	578.0
60°	1079.9	1183.6	1085.4	893.6	738.0	651.5	602.8	575.3	561.1	549.4	532.1
62.5°	954.7	1059.7	977.2	810.6	669.4	589.3	546.8	520.0	509.0	502.8	488.1
65°	782.8	873.2	818.1	681.4	571.4	500.6	462.1	443.3	433.0	430.7	421.3
67.5°	637.1	705.9	665.8	565.2	478.6	417.5	384.8	368.8	360.9	360.1	353.0
70°	541.5	605.9	575.3	484.1	409.5	361.5	333.2	319.1	314.4	313.6	309.7
72.5°	467.3	512.3	487.9	411.8	354.1	310.6	289.8	275.1	269.7	270.8	268.2
75°	345.8	379.6	365.5	312.8	266.4	238.1	220.8	211.4	206.7	209.1	205.9
77.5°	248.8	270.2	257.5	221.0	192.4	172.0	159.2	153.4	149.2	149.0	147.6
80°	187.8	200.4	193.3	171.3	147.8	130.5	120.2	116.3	114.0	113.2	112.4
82.5°	133.8	144.5	136.1	121.0	105.0	94.6	88.8	83.6	81.9	82.4	81.6
85°	67.6	71.5	68.4	58.9	52.7	47.9	44.8	42.4	40.9	41.7	40.1
87.5°	27.5	27.5	24.9	21.8	20.0	17.6	17.1	15.3	14.6	15.1	15.0
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6	20.9	20.2	19.4
95°	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9	60.3	49.7	39.1
97.5°	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4	137.7	132.9	128.2
100°	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3	201.5	206.7	211.8
102.5°	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7	261.4	265.1	268.8
105°	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2	349.1	351.9	354.7
107.5°	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6	441.9	444.2	446.4
110°	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9	504.0	506.0	508.1



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4	563.2	565.1	567.0
115°	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5	651.0	652.5	654.1
117.5°	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7	736.6	738.5	740.5
120°	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7	790.0	792.4	794.7
122.5°	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6	843.5	845.4	847.3
125°	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5	917.6	919.6	921.7
127.5°	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1	989.1	991.2	993.3
130°	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7	1033.8	1035.8	1037.9
132.5°	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4	1076.5	1078.6	1080.6
135°	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7	1141.3	1142.8	1144.4
137.5°	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5	1197.5	1199.4	1201.4
140°	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7	1234.2	1235.8	1237.3
142.5°	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1	1268.6	1270.2	1271.7
145°	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2	1317.0	1318.8	1320.6
147.5°	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5	1361.7	1362.9	1364.0
150°	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4	1389.1	1389.9	1390.7
152.5°	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5	1413.8	1414.2	1414.5
155°	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8	1448.3	1447.7	1447.2
157.5°	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2	1476.1	1476.1	1476.0
160°	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9	1492.7	1492.4	1492.2
162.5°	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7	1508.1	1507.4	1506.7
165°	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8	1527.0	1526.2	1525.5
167.5°	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7	1541.6	1540.6	1539.6
170°	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0	1550.0	1549.0	1547.9
172.5°	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6	1555.4	1554.1	1552.9
175°	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8	1562.5	1561.2	1559.9
177.5°	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7	1564.6	1563.6	1562.6
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1595.1	1590.7	1584.4	1575.0	1567.4	1555.5	1555.5	1557.4	1557.4	1556.8	1555.5
5°	1546.7	1534.9	1520.8	1504.3	1487.0	1469.7	1466.5	1460.2	1455.5	1452.4	1448.5
7.5°	1495.6	1474.7	1454.1	1431.0	1409.9	1392.5	1380.4	1370.3	1363.9	1357.0	1351.9
10°	1461.0	1435.1	1410.7	1386.4	1359.6	1338.4	1325.1	1315.6	1308.6	1302.3	1299.1
12.5°	1420.2	1390.5	1363.6	1340.5	1311.2	1289.4	1276.7	1272.2	1263.9	1250.7	1243.8
15°	1360.4	1332.9	1300.7	1265.3	1251.2	1224.5	1209.5	1202.5	1197.7	1187.5	1184.4
17.5°	1309.3	1273.3	1237.2	1210.8	1184.5	1162.8	1154.5	1145.7	1139.4	1131.1	1128.6
20°	1268.5	1236.3	1203.2	1175.0	1147.4	1123.9	1116.8	1110.5	1104.2	1100.3	1097.1
22.5°	1227.0	1194.8	1167.4	1141.0	1111.6	1096.2	1088.5	1081.6	1077.2	1074.5	1071.4
25°	1168.7	1140.4	1109.7	1086.1	1062.6	1052.3	1047.6	1043.7	1040.6	1036.6	1035.8
27.5°	1116.5	1085.7	1060.8	1038.8	1021.9	1013.4	1008.8	1006.9	1007.6	1009.0	1009.9
30°	1077.5	1049.2	1028.8	1009.9	994.2	986.3	985.5	985.5	988.7	989.5	991.0
32.5°	1041.7	1018.4	998.0	979.7	967.8	962.4	965.4	965.4	967.9	970.0	972.8
35°	989.5	969.0	953.3	937.6	927.4	929.7	931.3	932.9	936.8	941.5	944.7
37.5°	939.6	921.9	905.5	893.3	888.6	892.8	896.6	899.9	904.4	908.1	911.2
40°	903.8	890.4	874.7	863.7	865.3	867.7	870.8	874.7	878.7	881.0	884.2
42.5°	870.5	856.5	844.6	835.4	837.6	840.6	842.5	844.6	849.1	853.4	855.2
45°	819.7	808.7	797.7	792.2	793.8	795.4	796.9	799.3	803.2	806.4	807.1
47.5°	762.7	755.0	747.6	742.2	744.7	744.1	746.2	751.2	752.4	754.3	758.7
50°	726.2	719.1	710.5	708.9	708.9	708.9	709.7	716.0	716.0	719.1	722.3
52.5°	686.0	681.4	675.9	673.1	671.8	671.8	675.1	678.3	679.5	683.9	687.1
55°	626.4	621.7	616.9	614.6	613.0	614.6	620.9	622.4	626.4	628.7	631.1
57.5°	564.3	560.7	556.9	555.6	555.3	557.4	560.8	565.5	566.5	573.7	577.3
60°	523.4	517.9	514.8	514.8	513.2	520.3	518.7	526.6	528.1	532.9	538.4
62.5°	481.3	473.9	472.7	472.7	474.9	476.9	479.1	482.6	486.6	492.6	496.9
65°	413.4	409.5	415.0	414.2	412.6	417.3	417.3	421.3	426.0	431.5	440.1
67.5°	349.1	347.1	347.5	347.5	349.9	352.6	354.8	358.2	363.9	369.7	375.4
70°	305.7	308.1	304.2	307.3	309.7	310.4	312.0	316.7	323.0	326.9	333.2
72.5°	263.6	263.4	263.9	265.2	267.5	268.9	270.5	275.9	282.8	286.1	291.1
75°	202.8	202.0	204.3	204.3	208.3	209.8	211.4	213.8	220.1	224.8	228.7
77.5°	148.1	149.0	148.5	151.2	150.1	150.4	155.3	157.7	158.3	167.6	169.6
80°	111.6	113.2	114.0	114.7	115.5	114.0	119.5	121.8	121.8	127.3	131.2
82.5°	80.2	81.1	83.2	83.9	84.1	85.7	86.1	87.9	89.8	92.1	97.3
85°	40.1	42.4	43.2	42.4	43.2	41.7	44.0	44.8	45.6	45.6	45.6
87.5°	14.9	16.1	16.1	17.4	17.5	18.8	19.0	17.9	18.1	20.2	17.9
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9	31.0	32.0	32.8
92.5°	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0	34.7	36.4	37.3
95°	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6	41.4	43.2	44.1
97.5°	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5	43.6	45.7	46.8
100°	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5	44.5	46.6	47.8
102.5°	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6	57.2	50.8	47.9
105°	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0	117.3	71.6	49.1
107.5°	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3	365.8	332.3	298.3
110°	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9	498.4	489.9	467.2



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8	583.0	583.2	579.3
115°	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0	674.6	677.2	679.0
117.5°	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8	754.9	756.9	758.1
120°	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8	807.8	809.9	810.9
122.5°	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5	859.0	860.4	861.2
125°	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5	931.0	931.5	932.0
127.5°	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6	1004.4	1005.2	1005.4
130°	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7	1048.7	1049.8	1050.0
132.5°	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5	1090.6	1091.6	1091.7
135°	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5
137.5°	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4	1210.6	1211.8	1212.2
140°	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2	1246.2	1247.3	1247.5
142.5°	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2	1280.0	1280.8	1280.9
145°	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7	1327.2	1327.7	1327.9
147.5°	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2	1369.7	1370.2	1369.9
150°	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2	1395.7	1396.2	1396.1
152.5°	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3	1419.3	1420.2	1420.1
155°	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2	1451.5	1452.8	1452.6
157.5°	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9	1479.4	1481.0	1480.8
160°	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7	1495.2	1496.8	1496.7
162.5°	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1	1509.8	1511.6	1511.6
165°	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3	1529.3	1531.4	1531.5
167.5°	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3
170°	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6
172.5°	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1	1558.1	1560.2	1560.1
175°	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8	1564.6	1566.4	1566.2
177.5°	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2	1566.9	1568.5	1568.3
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1551.1	1550.5	1554.9	1551.7	1554.9	1550.5	1551.1	1555.5	1556.8	1557.4	1557.4
5°	1443.7	1446.1	1438.2	1438.2	1438.2	1446.1	1443.7	1448.5	1452.4	1455.5	1460.2
7.5°	1348.2	1344.7	1345.0	1340.8	1345.0	1344.7	1348.2	1351.9	1357.0	1363.9	1370.3
10°	1289.7	1285.0	1283.4	1284.2	1283.4	1285.0	1289.7	1299.1	1302.3	1308.6	1315.6
12.5°	1241.3	1240.3	1230.0	1230.1	1230.0	1240.3	1241.3	1243.8	1250.7	1263.9	1272.2
15°	1184.4	1169.5	1167.9	1172.6	1167.9	1169.5	1184.4	1184.4	1187.5	1197.7	1202.5
17.5°	1127.3	1119.5	1119.9	1117.6	1119.9	1119.5	1127.3	1128.6	1131.1	1139.4	1145.7
20°	1097.1	1092.4	1091.6	1086.1	1091.6	1092.4	1097.1	1097.1	1100.3	1104.2	1110.5
22.5°	1069.5	1067.9	1068.4	1062.3	1068.4	1067.9	1069.5	1071.4	1074.5	1077.2	1081.6
25°	1035.1	1039.0	1035.8	1035.8	1035.8	1039.0	1035.1	1035.8	1036.6	1040.6	1043.7
27.5°	1011.8	1011.6	1010.1	1010.1	1010.1	1011.6	1011.8	1009.9	1009.0	1007.6	1006.9
30°	994.2	993.4	995.0	995.0	995.0	993.4	994.2	991.0	989.5	988.7	985.5
32.5°	976.6	977.7	978.0	978.6	978.0	977.7	976.6	972.8	970.0	967.9	965.4
35°	949.4	950.2	952.5	951.0	952.5	950.2	949.4	944.7	941.5	936.8	932.9
37.5°	912.6	916.2	915.4	916.7	915.4	916.2	912.6	911.2	908.1	904.4	899.9
40°	884.9	887.3	886.5	886.5	886.5	887.3	884.9	884.2	881.0	878.7	874.7
42.5°	856.7	858.4	856.3	855.1	856.3	858.4	856.7	855.2	853.4	849.1	844.6
45°	810.3	808.7	811.1	807.9	811.1	808.7	810.3	807.1	806.4	803.2	799.3
47.5°	758.4	760.0	760.6	763.0	760.6	760.0	758.4	758.7	754.3	752.4	751.2
50°	723.8	728.5	728.5	727.8	728.5	728.5	723.8	722.3	719.1	716.0	716.0
52.5°	689.9	692.1	695.2	695.1	695.2	692.1	689.9	687.1	683.9	679.5	678.3
55°	637.4	639.0	640.5	641.3	640.5	639.0	637.4	631.1	628.7	626.4	622.4
57.5°	583.0	582.4	586.1	587.2	586.1	582.4	583.0	577.3	573.7	566.5	565.5
60°	544.6	544.6	550.9	553.3	550.9	544.6	544.6	538.4	532.9	528.1	526.6
62.5°	503.8	506.3	512.6	509.3	512.6	506.3	503.8	496.9	492.6	486.6	482.6
65°	444.0	450.3	449.5	452.7	449.5	450.3	444.0	440.1	431.5	426.0	421.3
67.5°	381.6	385.6	391.2	391.7	391.2	385.6	381.6	375.4	369.7	363.9	358.2
70°	339.5	343.4	346.6	348.9	346.6	343.4	339.5	333.2	326.9	323.0	316.7
72.5°	298.7	300.7	308.2	304.9	308.2	300.7	298.7	291.1	286.1	282.8	275.9
75°	234.2	239.7	244.4	242.1	244.4	239.7	234.2	228.7	224.8	220.1	213.8
77.5°	173.2	178.7	180.9	178.9	180.9	178.7	173.2	169.6	167.6	158.3	157.7
80°	136.8	136.0	140.7	139.9	140.7	136.0	136.8	131.2	127.3	121.8	121.8
82.5°	100.3	99.5	101.7	102.2	101.7	99.5	100.3	97.3	92.1	89.8	87.9
85°	48.7	51.1	47.9	47.2	47.9	51.1	48.7	45.6	45.6	45.6	44.8
87.5°	18.0	18.1	17.6	17.0	17.6	18.1	18.0	17.9	20.2	18.1	17.9
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	32.0	31.0	29.9
92.5°	37.6	38.0	38.3	38.6	38.3	38.0	37.6	37.3	36.4	34.7	33.0
95°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.1	43.2	41.4	39.6
97.5°	47.1	47.4	47.6	47.9	47.6	47.4	47.1	46.8	45.7	43.6	41.5
100°	48.0	48.3	48.5	48.8	48.5	48.3	48.0	47.8	46.6	44.5	42.5
102.5°	48.3	48.8	49.3	49.7	49.3	48.8	48.3	47.9	50.8	57.2	63.6
105°	49.6	50.1	50.6	51.1	50.6	50.1	49.6	49.1	71.6	117.3	163.0
107.5°	263.9	229.4	195.0	160.6	195.0	229.4	263.9	298.3	332.3	365.8	399.3
110°	430.3	393.3	356.4	319.5	356.4	393.3	430.3	467.2	489.9	498.4	506.9



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	571.5	563.7	555.9	548.1	555.9	563.7	571.5	579.3	583.2	583.0	582.8
115°	680.0	681.1	682.1	683.1	682.1	681.1	680.0	679.0	677.2	674.6	672.0
117.5°	758.3	758.5	758.7	758.9	758.7	758.5	758.3	758.1	756.9	754.9	752.8
120°	810.9	810.9	810.9	810.9	810.9	810.9	810.9	810.9	809.9	807.8	805.8
122.5°	861.4	861.6	861.9	862.1	861.9	861.6	861.4	861.2	860.4	859.0	857.5
125°	932.5	933.1	933.6	934.1	933.6	933.1	932.5	932.0	931.5	931.0	930.5
127.5°	1004.9	1004.4	1003.9	1003.3	1003.9	1004.4	1004.9	1005.4	1005.2	1004.4	1003.6
130°	1049.5	1049.0	1048.5	1048.0	1048.5	1049.0	1049.5	1050.0	1049.8	1048.7	1047.7
132.5°	1091.0	1090.3	1089.6	1088.8	1089.6	1090.3	1091.0	1091.7	1091.6	1090.6	1089.5
135°	1153.7	1152.9	1152.1	1151.4	1152.1	1152.9	1153.7	1154.5	1154.5	1153.7	1152.9
137.5°	1211.7	1211.2	1210.7	1210.1	1210.7	1211.2	1211.7	1212.2	1211.8	1210.6	1209.4
140°	1247.0	1246.5	1246.0	1245.5	1246.0	1246.5	1247.0	1247.5	1247.3	1246.2	1245.2
142.5°	1280.2	1279.4	1278.7	1278.0	1278.7	1279.4	1280.2	1280.9	1280.8	1280.0	1279.2
145°	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.9	1327.7	1327.2	1326.7
147.5°	1368.7	1367.5	1366.3	1365.1	1366.3	1367.5	1368.7	1369.9	1370.2	1369.7	1369.2
150°	1395.3	1394.6	1393.8	1393.0	1393.8	1394.6	1395.3	1396.1	1396.2	1395.7	1395.2
152.5°	1418.9	1417.7	1416.5	1415.3	1416.5	1417.7	1418.9	1420.1	1420.2	1419.3	1418.3
155°	1451.1	1449.6	1448.0	1446.5	1448.0	1449.6	1451.1	1452.6	1452.8	1451.5	1450.2
157.5°	1478.8	1476.7	1474.7	1472.7	1474.7	1476.7	1478.8	1480.8	1481.0	1479.4	1477.9
160°	1494.9	1493.1	1491.2	1489.4	1491.2	1493.1	1494.9	1496.7	1496.8	1495.2	1493.7
162.5°	1510.0	1508.4	1506.8	1505.2	1506.8	1508.4	1510.0	1511.6	1511.6	1509.8	1508.1
165°	1529.7	1527.9	1526.1	1524.3	1526.1	1527.9	1529.7	1531.5	1531.4	1529.3	1527.3
167.5°	1544.2	1542.1	1540.1	1538.0	1540.1	1542.1	1544.2	1546.3	1546.3	1544.2	1542.1
170°	1552.6	1550.5	1548.4	1546.4	1548.4	1550.5	1552.6	1554.6	1554.6	1552.6	1550.5
172.5°	1557.8	1555.6	1553.3	1551.0	1553.3	1555.6	1557.8	1560.1	1560.2	1558.1	1556.1
175°	1564.2	1562.1	1560.1	1558.0	1560.1	1562.1	1564.2	1566.2	1566.4	1564.6	1562.8
177.5°	1566.3	1564.2	1562.1	1560.1	1562.1	1564.2	1566.3	1568.3	1568.5	1566.9	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1555.5	1555.5	1567.4	1575.0	1584.4	1590.7	1595.1	1599.5	1607.1	1617.1	1628.4
5°	1466.5	1469.7	1487.0	1504.3	1520.8	1534.9	1546.7	1560.8	1578.1	1599.3	1622.9
7.5°	1380.4	1392.5	1409.9	1431.0	1454.1	1474.7	1495.6	1518.9	1543.2	1574.5	1607.5
10°	1325.1	1338.4	1359.6	1386.4	1410.7	1435.1	1461.0	1486.2	1516.8	1553.8	1596.2
12.5°	1276.7	1289.4	1311.2	1340.5	1363.6	1390.5	1420.2	1452.9	1487.3	1531.8	1579.9
15°	1209.5	1224.5	1251.2	1265.3	1300.7	1332.9	1360.4	1407.6	1451.6	1497.2	1553.0
17.5°	1154.5	1162.8	1184.5	1210.8	1237.2	1273.3	1309.3	1348.6	1392.5	1448.3	1518.1
20°	1116.8	1123.9	1147.4	1175.0	1203.2	1236.3	1268.5	1307.8	1357.3	1416.2	1491.7
22.5°	1088.5	1096.2	1111.6	1141.0	1167.4	1194.8	1227.0	1273.8	1326.5	1384.2	1465.9
25°	1047.6	1052.3	1062.6	1086.1	1109.7	1140.4	1168.7	1212.7	1266.9	1334.5	1416.2
27.5°	1008.8	1013.4	1021.9	1038.8	1060.8	1085.7	1116.5	1153.9	1208.9	1282.3	1369.1
30°	985.5	986.3	994.2	1009.9	1028.8	1049.2	1077.5	1119.9	1171.8	1246.5	1337.6
32.5°	965.4	962.4	967.8	979.7	998.0	1018.4	1041.7	1083.5	1133.5	1206.9	1300.5
35°	931.3	929.7	927.4	937.6	953.3	969.0	989.5	1020.9	1077.5	1145.9	1244.1
37.5°	896.6	892.8	888.6	893.3	905.5	921.9	939.6	967.6	1016.4	1091.6	1185.6
40°	870.8	867.7	865.3	863.7	874.7	890.4	903.8	930.5	976.1	1047.6	1140.4
42.5°	842.5	840.6	837.6	835.4	844.6	856.5	870.5	894.1	939.6	1006.8	1094.5
45°	796.9	795.4	793.8	792.2	797.7	808.7	819.7	837.0	876.3	941.5	1020.9
47.5°	746.2	744.1	744.7	742.2	747.6	755.0	762.7	781.2	818.9	871.6	929.6
50°	709.7	708.9	708.9	708.9	710.5	719.1	726.2	740.3	774.9	827.6	869.2
52.5°	675.1	671.8	671.8	673.1	675.9	681.4	686.0	701.4	731.5	774.8	812.6
55°	620.9	614.6	613.0	614.6	616.9	621.7	626.4	639.0	664.9	697.1	719.1
57.5°	560.8	557.4	555.3	555.6	556.9	560.7	564.3	578.0	598.4	615.2	629.4
60°	518.7	520.3	513.2	514.8	514.8	517.9	523.4	532.1	549.4	561.1	575.3
62.5°	479.1	476.9	474.9	472.7	472.7	473.9	481.3	488.1	502.8	509.0	520.0
65°	417.3	417.3	412.6	414.2	415.0	409.5	413.4	421.3	430.7	433.0	443.3
67.5°	354.8	352.6	349.9	347.5	347.5	347.1	349.1	353.0	360.1	360.9	368.8
70°	312.0	310.4	309.7	307.3	304.2	308.1	305.7	309.7	313.6	314.4	319.1
72.5°	270.5	268.9	267.5	265.2	263.9	263.4	263.6	268.2	270.8	269.7	275.1
75°	211.4	209.8	208.3	204.3	204.3	202.0	202.8	205.9	209.1	206.7	211.4
77.5°	155.3	150.4	150.1	151.2	148.5	149.0	148.1	147.6	149.0	149.2	153.4
80°	119.5	114.0	115.5	114.7	114.0	113.2	111.6	112.4	113.2	114.0	116.3
82.5°	86.1	85.7	84.1	83.9	83.2	81.1	80.2	81.6	82.4	81.9	83.6
85°	44.0	41.7	43.2	42.4	43.2	42.4	40.1	40.1	41.7	40.9	42.4
87.5°	19.0	18.8	17.5	17.4	16.1	16.1	14.9	15.0	15.1	14.6	15.3
90°	28.9	27.9	24.5	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2
92.5°	31.4	29.7	27.2	24.7	22.2	19.6	18.7	19.4	20.2	20.9	21.6
95°	37.8	36.0	33.2	30.3	27.5	24.7	28.5	39.1	49.7	60.3	70.9
97.5°	39.5	37.4	56.0	74.6	93.2	111.8	123.4	128.2	132.9	137.7	142.4
100°	40.4	38.3	78.6	118.9	159.2	199.4	217.0	211.8	206.7	201.5	196.3
102.5°	70.0	76.4	120.4	164.4	208.4	252.4	272.6	268.8	265.1	261.4	257.7
105°	208.7	254.4	277.7	300.9	324.1	347.4	357.6	354.7	351.9	349.1	346.2
107.5°	432.8	466.4	462.7	459.0	455.4	451.7	448.7	446.4	444.2	441.9	439.6
110°	515.5	524.0	521.1	518.3	515.5	512.6	510.2	508.1	506.0	504.0	501.9



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	582.7	582.5	579.7	576.9	574.0	571.2	568.8	567.0	565.1	563.2	561.4
115°	669.5	666.9	664.6	662.2	659.9	657.6	655.6	654.1	652.5	651.0	649.5
117.5°	750.7	748.7	747.5	746.3	745.1	743.9	742.4	740.5	738.5	736.6	734.7
120°	803.7	801.6	800.9	800.1	799.3	798.6	797.0	794.7	792.4	790.0	787.7
122.5°	856.1	854.6	853.6	852.7	851.7	850.7	849.3	847.3	845.4	843.5	841.6
125°	930.0	929.4	928.4	927.4	926.3	925.3	923.8	921.7	919.6	917.6	915.5
127.5°	1002.8	1001.9	1000.7	999.5	998.2	997.0	995.3	993.3	991.2	989.1	987.1
130°	1046.7	1045.6	1044.6	1043.6	1042.5	1041.5	1039.9	1037.9	1035.8	1033.8	1031.7
132.5°	1088.5	1087.5	1086.6	1085.8	1085.0	1084.1	1082.7	1080.6	1078.6	1076.5	1074.4
135°	1152.1	1151.4	1150.3	1149.3	1148.3	1147.2	1145.9	1144.4	1142.8	1141.3	1139.7
137.5°	1208.1	1206.9	1206.3	1205.8	1205.2	1204.6	1203.4	1201.4	1199.4	1197.5	1195.5
140°	1244.2	1243.1	1242.4	1241.6	1240.8	1240.0	1238.9	1237.3	1235.8	1234.2	1232.7
142.5°	1278.4	1277.5	1276.8	1276.0	1275.2	1274.4	1273.3	1271.7	1270.2	1268.6	1267.1
145°	1326.1	1325.6	1325.1	1324.6	1324.1	1323.6	1322.4	1320.6	1318.8	1317.0	1315.2
147.5°	1368.7	1368.1	1367.6	1367.1	1366.6	1366.1	1365.2	1364.0	1362.9	1361.7	1360.5
150°	1394.7	1394.2	1393.7	1393.1	1392.6	1392.1	1391.5	1390.7	1389.9	1389.1	1388.4
152.5°	1417.4	1416.5	1416.2	1415.9	1415.5	1415.2	1414.9	1414.5	1414.2	1413.8	1413.5
155°	1448.9	1447.6	1447.4	1447.1	1446.8	1446.6	1446.7	1447.2	1447.7	1448.3	1448.8
157.5°	1476.4	1474.8	1475.1	1475.3	1475.6	1475.8	1476.0	1476.0	1476.1	1476.1	1476.2
160°	1492.2	1490.6	1490.9	1491.1	1491.4	1491.6	1491.9	1492.2	1492.4	1492.7	1492.9
162.5°	1506.3	1504.5	1504.8	1505.1	1505.3	1505.6	1506.0	1506.7	1507.4	1508.1	1508.7
165°	1525.2	1523.1	1523.4	1523.6	1523.9	1524.2	1524.7	1525.5	1526.2	1527.0	1527.8
167.5°	1540.1	1538.0	1538.0	1538.0	1538.0	1538.0	1538.5	1539.6	1540.6	1541.6	1542.7
170°	1548.4	1546.4	1546.4	1546.4	1546.4	1546.4	1546.9	1547.9	1549.0	1550.0	1551.0
172.5°	1554.0	1551.9	1551.7	1551.5	1551.3	1551.1	1551.6	1552.9	1554.1	1555.4	1556.6
175°	1561.0	1559.1	1558.9	1558.6	1558.4	1558.1	1558.6	1559.9	1561.2	1562.5	1563.8
177.5°	1563.6	1561.9	1561.7	1561.5	1561.3	1561.1	1561.5	1562.6	1563.6	1564.6	1565.7
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1632.2	1635.3	1646.0	1653.6	1662.4	1667.4	1672.4	1676.2	1681.2	1682.5	1700.7
5°	1639.4	1655.2	1682.7	1703.1	1728.2	1755.7	1774.6	1783.3	1806.0	1824.9	1862.6
7.5°	1637.4	1670.9	1712.4	1755.4	1801.6	1844.4	1881.5	1925.5	1956.8	2003.8	2050.2
10°	1635.5	1680.3	1733.7	1788.8	1853.2	1912.9	1966.4	2026.1	2075.6	2140.8	2196.6
12.5°	1629.8	1684.1	1758.3	1823.3	1901.6	1984.0	2063.2	2139.9	2183.8	2292.4	2343.8
15°	1615.9	1680.3	1773.0	1872.1	1979.7	2077.2	2177.8	2258.0	2387.6	2482.7	2543.2
17.5°	1589.1	1679.4	1789.4	1908.8	2039.8	2168.2	2282.2	2403.8	2541.4	2656.4	2779.0
20°	1576.6	1675.6	1798.2	1930.2	2066.2	2211.6	2341.3	2487.4	2637.6	2750.7	2907.9
22.5°	1553.3	1665.5	1797.6	1944.7	2090.1	2240.5	2392.2	2539.6	2713.0	2868.9	3018.6
25°	1515.3	1641.0	1777.8	1942.0	2112.6	2263.5	2445.0	2640.7	2821.5	3021.9	3171.2
27.5°	1475.3	1609.6	1746.6	1899.4	2082.8	2261.9	2490.3	2711.4	2932.4	3105.5	3216.0
30°	1444.5	1575.0	1716.5	1870.5	2052.0	2265.0	2520.4	2761.7	2977.1	3125.6	3187.7
32.5°	1411.2	1543.5	1668.7	1830.3	2023.7	2263.1	2539.3	2791.3	2979.6	3078.5	3066.4
35°	1358.9	1469.7	1591.5	1747.1	1975.0	2249.3	2550.3	2793.9	2909.5	2888.3	2727.9
37.5°	1283.4	1376.6	1496.6	1666.9	1918.4	2220.2	2528.3	2711.1	2703.6	2530.8	2298.5
40°	1236.3	1315.6	1431.2	1610.4	1874.4	2201.4	2493.7	2612.4	2511.8	2270.5	1992.3
42.5°	1174.6	1247.7	1363.3	1547.5	1826.0	2163.0	2427.7	2462.1	2265.3	1987.6	1732.6
45°	1079.1	1143.5	1263.0	1453.2	1753.4	2079.5	2266.6	2182.5	1917.6	1630.8	1436.7
47.5°	976.4	1043.4	1158.3	1353.7	1648.4	1954.0	2043.1	1864.2	1592.3	1359.6	1181.4
50°	911.7	976.1	1088.5	1285.8	1577.3	1850.8	1887.8	1656.7	1406.8	1202.5	1056.3
52.5°	846.3	907.0	1017.5	1215.3	1494.4	1731.4	1708.6	1473.1	1243.3	1069.2	954.4
55°	749.0	806.4	911.7	1097.1	1351.0	1538.8	1456.3	1231.5	1041.3	906.2	818.9
57.5°	661.9	716.9	807.8	975.3	1196.0	1325.1	1220.1	1030.7	879.4	775.4	710.3
60°	602.8	651.5	738.0	893.6	1085.4	1183.6	1079.9	912.5	785.1	701.8	643.7
62.5°	546.8	589.3	669.4	810.6	977.2	1059.7	954.7	813.1	704.7	630.8	581.4
65°	462.1	500.6	571.4	681.4	818.1	873.2	782.8	668.0	583.9	528.9	495.9
67.5°	384.8	417.5	478.6	565.2	665.8	705.9	637.1	548.3	484.9	440.7	414.5
70°	333.2	361.5	409.5	484.1	575.3	605.9	541.5	468.4	422.0	386.7	362.3
72.5°	289.8	310.6	354.1	411.8	487.9	512.3	467.3	403.0	359.8	333.2	313.9
75°	220.8	238.1	266.4	312.8	365.5	379.6	345.8	305.7	276.6	257.8	242.8
77.5°	159.2	172.0	192.4	221.0	257.5	270.2	248.8	222.1	200.9	188.1	179.8
80°	120.2	130.5	147.8	171.3	193.3	200.4	187.8	167.4	152.5	145.4	138.3
82.5°	88.8	94.6	105.0	121.0	136.1	144.5	133.8	121.5	113.5	107.0	104.4
85°	44.8	47.9	52.7	58.9	68.4	71.5	67.6	64.4	59.7	55.8	55.8
87.5°	17.1	17.6	20.0	21.8	24.9	27.5	27.5	26.9	27.0	26.5	26.1
90°	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9	29.9
92.5°	20.9	20.2	19.4	18.7	19.6	22.2	24.7	27.2	29.7	31.4	33.0
95°	60.3	49.7	39.1	28.5	24.7	27.5	30.3	33.2	36.0	37.8	39.6
97.5°	137.7	132.9	128.2	123.4	111.8	93.2	74.6	56.0	37.4	39.5	41.5
100°	201.5	206.7	211.8	217.0	199.4	159.2	118.9	78.6	38.3	40.4	42.5
102.5°	261.4	265.1	268.8	272.6	252.4	208.4	164.4	120.4	76.4	70.0	63.6
105°	349.1	351.9	354.7	357.6	347.4	324.1	300.9	277.7	254.4	208.7	163.0
107.5°	441.9	444.2	446.4	448.7	451.7	455.4	459.0	462.7	466.4	432.8	399.3
110°	504.0	506.0	508.1	510.2	512.6	515.5	518.3	521.1	524.0	515.5	506.9



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	563.2	565.1	567.0	568.8	571.2	574.0	576.9	579.7	582.5	582.7	582.8
115°	651.0	652.5	654.1	655.6	657.6	659.9	662.2	664.6	666.9	669.5	672.0
117.5°	736.6	738.5	740.5	742.4	743.9	745.1	746.3	747.5	748.7	750.7	752.8
120°	790.0	792.4	794.7	797.0	798.6	799.3	800.1	800.9	801.6	803.7	805.8
122.5°	843.5	845.4	847.3	849.3	850.7	851.7	852.7	853.6	854.6	856.1	857.5
125°	917.6	919.6	921.7	923.8	925.3	926.3	927.4	928.4	929.4	930.0	930.5
127.5°	989.1	991.2	993.3	995.3	997.0	998.2	999.5	1000.7	1001.9	1002.8	1003.6
130°	1033.8	1035.8	1037.9	1039.9	1041.5	1042.5	1043.6	1044.6	1045.6	1046.7	1047.7
132.5°	1076.5	1078.6	1080.6	1082.7	1084.1	1085.0	1085.8	1086.6	1087.5	1088.5	1089.5
135°	1141.3	1142.8	1144.4	1145.9	1147.2	1148.3	1149.3	1150.3	1151.4	1152.1	1152.9
137.5°	1197.5	1199.4	1201.4	1203.4	1204.6	1205.2	1205.8	1206.3	1206.9	1208.1	1209.4
140°	1234.2	1235.8	1237.3	1238.9	1240.0	1240.8	1241.6	1242.4	1243.1	1244.2	1245.2
142.5°	1268.6	1270.2	1271.7	1273.3	1274.4	1275.2	1276.0	1276.8	1277.5	1278.4	1279.2
145°	1317.0	1318.8	1320.6	1322.4	1323.6	1324.1	1324.6	1325.1	1325.6	1326.1	1326.7
147.5°	1361.7	1362.9	1364.0	1365.2	1366.1	1366.6	1367.1	1367.6	1368.1	1368.7	1369.2
150°	1389.1	1389.9	1390.7	1391.5	1392.1	1392.6	1393.1	1393.7	1394.2	1394.7	1395.2
152.5°	1413.8	1414.2	1414.5	1414.9	1415.2	1415.5	1415.9	1416.2	1416.5	1417.4	1418.3
155°	1448.3	1447.7	1447.2	1446.7	1446.6	1446.8	1447.1	1447.4	1447.6	1448.9	1450.2
157.5°	1476.1	1476.1	1476.0	1476.0	1475.8	1475.6	1475.3	1475.1	1474.8	1476.4	1477.9
160°	1492.7	1492.4	1492.2	1491.9	1491.6	1491.4	1491.1	1490.9	1490.6	1492.2	1493.7
162.5°	1508.1	1507.4	1506.7	1506.0	1505.6	1505.3	1505.1	1504.8	1504.5	1506.3	1508.1
165°	1527.0	1526.2	1525.5	1524.7	1524.2	1523.9	1523.6	1523.4	1523.1	1525.2	1527.3
167.5°	1541.6	1540.6	1539.6	1538.5	1538.0	1538.0	1538.0	1538.0	1538.0	1540.1	1542.1
170°	1550.0	1549.0	1547.9	1546.9	1546.4	1546.4	1546.4	1546.4	1546.4	1548.4	1550.5
172.5°	1555.4	1554.1	1552.9	1551.6	1551.1	1551.3	1551.5	1551.7	1551.9	1554.0	1556.1
175°	1562.5	1561.2	1559.9	1558.6	1558.1	1558.4	1558.6	1558.9	1559.1	1561.0	1562.8
177.5°	1564.6	1563.6	1562.6	1561.5	1561.1	1561.3	1561.5	1561.7	1561.9	1563.6	1565.2
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1707.0	1707.6	1714.6	1719.6	1717.1	1720.2	1721.5
5°	1865.0	1893.3	1908.2	1919.2	1920.0	1920.8	1927.1
7.5°	2089.0	2119.3	2141.5	2175.1	2185.2	2196.6	2193.3
10°	2252.5	2297.2	2335.8	2356.2	2378.2	2410.4	2384.5
12.5°	2405.2	2484.6	2543.2	2575.0	2595.7	2602.2	2589.5
15°	2657.2	2760.9	2816.7	2815.2	2885.9	2916.6	2868.6
17.5°	2888.3	2984.0	3060.7	3100.0	3158.9	3172.0	3166.0
20°	3029.7	3134.3	3194.0	3261.6	3292.2	3319.7	3324.4
22.5°	3151.7	3245.5	3309.7	3365.9	3391.6	3404.6	3412.5
25°	3277.3	3351.2	3389.7	3409.3	3416.4	3414.8	3404.6
27.5°	3268.6	3274.3	3231.9	3190.2	3153.0	3111.0	3096.5
30°	3183.8	3117.7	2999.9	2933.1	2834.8	2757.0	2788.4
32.5°	2960.6	2829.2	2696.8	2550.8	2429.9	2395.5	2360.9
35°	2526.7	2295.7	2160.5	2003.3	1940.4	1877.6	1834.3
37.5°	2044.2	1865.5	1705.1	1602.3	1539.3	1499.5	1478.2
40°	1767.5	1606.4	1474.4	1391.1	1343.1	1298.3	1292.1
42.5°	1546.9	1397.1	1297.7	1231.4	1185.3	1166.3	1152.5
45°	1266.9	1162.4	1095.6	1048.4	1017.8	1006.0	990.3
47.5°	1072.3	998.4	948.3	916.2	893.1	884.3	883.1
50°	963.5	902.2	865.3	840.1	822.1	818.9	806.4
52.5°	881.8	828.7	799.9	777.9	764.9	756.1	752.3
55°	765.5	730.1	704.2	691.6	681.4	672.7	672.7
57.5°	669.8	640.2	623.1	612.4	609.2	603.1	599.2
60°	610.7	585.5	572.2	562.7	556.4	557.2	550.1
62.5°	552.8	536.5	523.7	514.3	506.8	506.9	507.4
65°	470.8	458.2	448.8	445.6	440.9	435.4	437.0
67.5°	398.9	387.1	379.8	374.4	372.8	369.9	374.4
70°	347.4	338.7	333.2	328.5	326.9	327.7	331.7
72.5°	300.2	294.1	290.5	288.3	284.8	285.0	287.6
75°	235.8	231.1	227.9	225.6	224.8	224.8	224.8
77.5°	173.2	172.1	170.7	167.2	167.4	168.3	168.5
80°	136.8	134.4	133.6	132.0	129.7	128.1	132.0
82.5°	102.2	99.8	99.0	98.7	95.1	94.8	98.1
85°	55.0	52.7	53.4	52.7	52.7	51.9	51.9
87.5°	25.7	25.3	24.8	25.5	25.0	24.5	25.8
90°	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	34.7	36.4	37.3	37.6	38.0	38.3	38.6
95°	41.4	43.2	44.1	44.1	44.1	44.1	44.1
97.5°	43.6	45.7	46.8	47.1	47.4	47.6	47.9
100°	44.5	46.6	47.8	48.0	48.3	48.5	48.8
102.5°	57.2	50.8	47.9	48.3	48.8	49.3	49.7
105°	117.3	71.6	49.1	49.6	50.1	50.6	51.1
107.5°	365.8	332.3	298.3	263.9	229.4	195.0	160.6
110°	498.4	489.9	467.2	430.3	393.3	356.4	319.5



TEST NUMBER: P332081

CATALOG NUMBER: S123DIP-S1165D1195U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	583.0	583.2	579.3	571.5	563.7	555.9	548.1
115°	674.6	677.2	679.0	680.0	681.1	682.1	683.1
117.5°	754.9	756.9	758.1	758.3	758.5	758.7	758.9
120°	807.8	809.9	810.9	810.9	810.9	810.9	810.9
122.5°	859.0	860.4	861.2	861.4	861.6	861.9	862.1
125°	931.0	931.5	932.0	932.5	933.1	933.6	934.1
127.5°	1004.4	1005.2	1005.4	1004.9	1004.4	1003.9	1003.3
130°	1048.7	1049.8	1050.0	1049.5	1049.0	1048.5	1048.0
132.5°	1090.6	1091.6	1091.7	1091.0	1090.3	1089.6	1088.8
135°	1153.7	1154.5	1154.5	1153.7	1152.9	1152.1	1151.4
137.5°	1210.6	1211.8	1212.2	1211.7	1211.2	1210.7	1210.1
140°	1246.2	1247.3	1247.5	1247.0	1246.5	1246.0	1245.5
142.5°	1280.0	1280.8	1280.9	1280.2	1279.4	1278.7	1278.0
145°	1327.2	1327.7	1327.9	1327.9	1327.9	1327.9	1327.9
147.5°	1369.7	1370.2	1369.9	1368.7	1367.5	1366.3	1365.1
150°	1395.7	1396.2	1396.1	1395.3	1394.6	1393.8	1393.0
152.5°	1419.3	1420.2	1420.1	1418.9	1417.7	1416.5	1415.3
155°	1451.5	1452.8	1452.6	1451.1	1449.6	1448.0	1446.5
157.5°	1479.4	1481.0	1480.8	1478.8	1476.7	1474.7	1472.7
160°	1495.2	1496.8	1496.7	1494.9	1493.1	1491.2	1489.4
162.5°	1509.8	1511.6	1511.6	1510.0	1508.4	1506.8	1505.2
165°	1529.3	1531.4	1531.5	1529.7	1527.9	1526.1	1524.3
167.5°	1544.2	1546.3	1546.3	1544.2	1542.1	1540.1	1538.0
170°	1552.6	1554.6	1554.6	1552.6	1550.5	1548.4	1546.4
172.5°	1558.1	1560.2	1560.1	1557.8	1555.6	1553.3	1551.0
175°	1564.6	1566.4	1566.2	1564.2	1562.1	1560.1	1558.0
177.5°	1566.9	1568.5	1568.3	1566.3	1564.2	1562.1	1560.1
180°	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8	1563.8

(END OF REPORT)