

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332044-840

Luminaire Tested: **S123DIP-S1000D1195U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332044-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D1195U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8524.7 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41				
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34				
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29				
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29	25				
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22				
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19				
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17				
8	54	41	34	28	49	38	31	27	33	27	24	28	24	20	23	20	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	1.8
10°-20°	425.2	5.0
20°-30°	628.0	7.4
30°-40°	733.6	8.6
40°-50°	737.6	8.7
50°-60°	647.9	7.6
60°-70°	482.7	5.7
70°-80°	275.0	3.2
80°-90°	83.4	1.0
90°-100°	322.6	3.8
100°-110°	913.4	10.7
110°-120°	898.5	10.5
120°-130°	716.7	8.4
130°-140°	565.1	6.6
140°-150°	421.7	4.9
150°-160°	294.0	3.4
160°-170°	172.7	2.0
170°-180°	56.2	0.7
0°-30°	1203.8	14.1
0°-40°	1937.4	22.7
0°-60°	3322.8	39.0
0°-90°	4163.9	48.8
90°-120°	2134.4	25.0
90°-150°	3837.9	45.0
90°-180°	4361.0	51.2
0°-180°	8524.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	2	14	29	33	34	7
95°	40	130	696	203	136	43
105°	136	201	943	1650	1492	145
115°	240	300	722	1582	1815	238
125°	334	395	674	1220	1432	297
135°	392	468	664	1005	1160	303
145°	447	512	656	824	907	280
155°	508	548	635	722	752	234
165°	555	571	608	645	656	156
175°	578	579	583	591	590	55
180°	580	580	580	580	580	



TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	29.1	28.8	28.6	28.5	28.3	28.2	28.7	29.2	29.6	30.1	29.6
90°	2.3	4.6	7.1	10.6	12.9	15.2	18.8	22.3	25.9	29.3	28.2
92.5°	14.5	21.6	31.4	40.6	50.5	67.9	98.6	149.1	198.5	180.5	136.1
95°	39.9	43.4	56.4	76.2	106.7	152.5	252.3	427.1	619.6	695.8	564.3
97.5°	68.1	69.2	79.3	96.6	126.7	176.2	271.6	468.6	789.4	1078.2	1153.6
100°	86.8	88.0	96.2	112.6	140.8	186.5	268.7	442.3	750.9	1111.2	1342.3
102.5°	106.5	108.7	115.9	131.4	156.7	198.7	272.5	419.8	694.6	1050.2	1351.6
105°	136.1	139.7	146.6	160.8	183.0	219.4	282.8	403.6	625.4	943.3	1280.1
107.5°	167.5	171.1	177.8	191.7	212.6	246.4	302.1	402.4	581.3	849.0	1154.8
110°	190.1	193.6	199.4	212.4	232.3	265.2	318.0	407.2	564.3	795.5	1075.9



TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.8	214.3	220.2	233.0	253.0	284.9	334.0	416.6	555.0	759.8	1007.4
115°	240.5	245.2	252.3	264.0	284.0	315.6	360.2	431.8	551.5	721.5	924.5
117.5°	270.3	275.7	281.6	292.4	314.7	344.1	388.1	451.9	553.6	699.0	874.5
120°	290.9	294.5	300.3	312.1	334.4	363.8	406.0	467.0	557.3	688.7	848.3
122.5°	308.8	312.4	318.2	330.8	352.2	383.4	424.7	481.1	563.9	682.2	826.7
125°	334.4	336.8	343.8	356.7	379.0	410.6	451.7	503.3	573.7	673.5	799.0
127.5°	353.9	357.4	366.1	379.2	403.8	435.6	475.1	521.7	585.0	669.2	774.7
130°	366.1	369.6	380.1	394.3	418.9	450.5	489.3	533.8	592.5	666.4	761.4
132.5°	375.5	379.9	391.4	408.3	432.9	463.7	501.5	545.1	598.1	665.5	749.3
135°	391.9	396.6	409.5	427.1	451.7	483.4	519.8	559.7	606.6	664.1	733.4
137.5°	407.4	412.3	425.0	443.7	468.2	497.5	532.4	570.5	612.3	661.5	719.4
140°	417.7	423.5	435.3	454.0	477.6	506.9	540.9	576.1	616.0	660.6	711.0
142.5°	429.0	433.9	446.6	463.4	487.0	514.4	547.4	581.7	618.8	658.7	703.5
145°	447.1	450.5	461.1	478.7	498.7	525.6	556.1	587.8	620.7	655.9	693.5
147.5°	465.3	467.5	477.8	493.0	512.3	535.2	563.2	591.6	620.7	651.5	683.6
150°	477.6	478.7	488.1	503.3	519.8	540.9	567.8	592.5	620.7	647.6	677.0
152.5°	489.8	490.0	499.4	512.7	527.3	547.4	570.7	594.4	617.8	643.0	669.5
155°	508.1	508.1	515.1	526.8	539.7	556.1	576.1	594.9	614.8	634.8	658.2
157.5°	522.6	523.5	529.2	539.5	550.5	563.2	579.2	596.0	610.9	627.5	645.5
160°	533.8	533.8	538.6	548.0	556.1	567.8	582.0	596.0	608.9	621.9	637.1
162.5°	542.3	542.3	546.0	553.6	560.9	570.7	582.9	595.1	605.2	616.2	628.6
165°	555.0	553.8	556.1	562.0	566.7	574.9	584.3	592.5	599.6	607.7	617.1
167.5°	564.6	563.2	564.3	568.9	572.1	577.2	584.1	590.7	593.9	599.4	606.1
170°	570.3	567.8	569.1	572.6	574.9	577.2	583.1	587.8	590.2	593.7	599.6
172.5°	574.0	572.6	572.8	575.4	576.8	578.2	583.1	586.9	587.3	589.0	593.0
175°	578.5	577.2	576.1	578.5	578.5	579.7	582.0	584.3	583.1	583.1	585.5
177.5°	580.6	579.7	578.7	579.7	579.7	579.7	580.6	582.4	580.6	579.7	580.6
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7



TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	29.6	29.6	29.6	29.9	29.7	29.9	30.1	29.9
90°	29.3	30.5	31.7	34.0	32.8	34.0	35.2	34.0
92.5°	98.8	78.4	69.2	63.1	61.0	57.5	58.7	56.6
95°	422.4	286.3	224.1	181.9	159.6	149.1	140.8	136.1
97.5°	1052.9	843.3	692.1	551.7	465.1	412.3	380.6	370.5
100°	1383.3	1288.3	1151.0	984.4	865.9	780.2	734.5	735.7
102.5°	1493.2	1490.1	1410.1	1304.4	1212.2	1144.5	1106.2	1079.2
105°	1525.3	1642.6	1665.0	1634.5	1580.4	1535.9	1498.3	1492.5
107.5°	1432.8	1623.4	1726.2	1768.0	1768.9	1753.8	1741.2	1730.4
110°	1344.6	1560.5	1708.4	1790.5	1823.3	1832.7	1830.4	1828.1



TEST NUMBER: P332044-840

CATALOG NUMBER: S123DIP-S1000D1195U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1257.3	1477.9	1643.6	1749.2	1809.3	1838.4	1847.2	1847.8
115°	1141.7	1345.7	1518.2	1646.2	1734.1	1785.7	1809.3	1815.1
117.5°	1057.8	1234.1	1389.0	1518.7	1610.5	1669.6	1703.4	1711.4
120°	1013.7	1172.2	1312.9	1431.5	1524.1	1589.8	1618.0	1625.1
122.5°	979.0	1122.4	1252.8	1362.9	1445.3	1504.4	1535.4	1544.3
125°	932.8	1060.7	1173.3	1267.2	1342.3	1393.9	1423.2	1431.5
127.5°	892.4	1006.4	1108.0	1193.5	1260.4	1304.4	1331.0	1338.5
130°	867.1	972.7	1067.7	1147.5	1209.7	1251.9	1276.6	1286.0
132.5°	843.6	940.8	1029.3	1105.3	1163.7	1205.9	1227.8	1234.4
135°	811.9	895.2	971.5	1038.3	1095.9	1131.0	1152.2	1160.4
137.5°	783.0	851.3	917.1	975.0	1023.4	1059.0	1076.8	1082.3
140°	766.2	826.0	882.3	932.8	977.3	1010.3	1029.0	1027.8
142.5°	750.2	801.6	850.4	894.3	932.3	961.4	978.3	977.1
145°	730.9	769.7	807.3	841.2	870.6	895.2	904.6	907.0
147.5°	715.3	746.0	776.3	800.4	822.7	839.4	848.3	849.2
150°	704.0	730.9	755.6	777.9	795.5	808.4	815.5	815.5
152.5°	693.7	716.9	738.7	757.3	771.1	783.0	787.3	787.3
155°	678.1	696.9	714.6	728.6	739.2	748.6	750.9	752.0
157.5°	661.8	677.5	691.1	702.1	711.2	718.3	720.1	719.9
160°	652.4	665.3	677.0	685.2	693.5	700.4	700.4	699.3
162.5°	641.1	652.2	662.9	670.1	675.6	681.7	681.7	680.5
165°	626.5	633.6	641.8	647.6	652.4	657.0	655.9	655.9
167.5°	613.9	619.2	624.0	628.2	630.3	633.6	632.4	632.4
170°	605.4	608.9	613.6	616.0	617.1	619.6	618.3	618.3
172.5°	597.9	600.5	604.3	605.6	605.9	608.2	606.1	605.2
175°	587.8	589.0	591.4	591.4	591.4	592.5	591.4	590.2
177.5°	581.5	582.4	583.4	583.4	582.4	583.4	581.5	581.5
180°	579.7	579.7	579.7	579.7	579.7	579.7	579.7	579.7

(END OF REPORT)