

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332053

Luminaire Tested: **S123DIP-S1165D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332053  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D365U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6071.7 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	73	71	69	66
2	95	87	80	75	90	83	77	72	76	72	67	70	66	63	64	61	58	55
3	86	76	69	62	82	73	66	61	67	61	57	62	57	53	57	53	50	47
4	79	68	59	53	75	65	57	51	60	53	48	55	50	46	51	46	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	46	41	37	35
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	37	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	32	27	37	31	26	35	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.2	2.8
10°-20°	486.2	8.0
20°-30°	718.3	11.8
30°-40°	839.0	13.8
40°-50°	843.5	13.9
50°-60°	740.9	12.2
60°-70°	552.0	9.1
70°-80°	314.5	5.2
80°-90°	91.6	1.5
90°-100°	97.2	1.6
100°-110°	275.1	4.5
110°-120°	270.6	4.5
120°-130°	215.9	3.6
130°-140°	170.2	2.8
140°-150°	127.0	2.1
150°-160°	88.5	1.5
160°-170°	52.0	0.9
170°-180°	16.9	0.3
0°-30°	1376.7	22.7
0°-40°	2215.7	36.5
0°-60°	3800.2	62.6
0°-90°	4758.3	78.4
90°-120°	642.9	10.6
90°-150°	1155.9	19.0
90°-180°	1313.0	21.6
0°-180°	6071.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	1	4	9	10	10	5
95°	12	39	210	61	41	13
105°	41	61	284	497	450	44
115°	72	90	217	477	547	72
125°	101	119	203	368	431	89
135°	118	141	200	303	350	91
145°	135	154	198	248	273	84
155°	153	165	191	217	226	70
165°	167	172	183	194	198	47
175°	174	174	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	32.8	32.1	31.4	30.8	30.1	29.7	29.6	29.6	29.5	29.4	29.1
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.7	6.7	7.8	8.8	8.5
92.5°	4.4	6.5	9.5	12.2	15.2	20.4	29.7	44.9	59.8	54.3	41.0
95°	12.0	13.1	17.0	23.0	32.2	45.9	76.0	128.6	186.6	209.6	170.0
97.5°	20.5	20.8	23.9	29.1	38.2	53.1	81.8	141.1	237.8	324.8	347.4
100°	26.2	26.5	29.0	33.9	42.4	56.2	80.9	133.2	226.2	334.7	404.3
102.5°	32.1	32.7	34.9	39.6	47.2	59.9	82.1	126.4	209.2	316.3	407.1
105°	41.0	42.1	44.2	48.4	55.1	66.1	85.2	121.6	188.4	284.1	385.5
107.5°	50.5	51.5	53.6	57.7	64.0	74.2	91.0	121.2	175.1	255.7	347.8
110°	57.2	58.3	60.1	64.0	70.0	79.9	95.8	122.6	170.0	239.6	324.1



TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	63.5	64.5	66.3	70.2	76.2	85.8	100.6	125.5	167.1	228.8	303.4
115°	72.4	73.9	76.0	79.5	85.5	95.1	108.5	130.0	166.1	217.3	278.5
117.5°	81.4	83.0	84.8	88.1	94.8	103.6	116.9	136.1	166.7	210.5	263.4
120°	87.6	88.7	90.5	94.0	100.7	109.5	122.3	140.6	167.9	207.4	255.5
122.5°	93.0	94.1	95.8	99.7	106.1	115.5	127.9	144.9	169.8	205.5	249.0
125°	100.7	101.4	103.5	107.4	114.1	123.7	136.1	151.6	172.8	202.8	240.7
127.5°	106.6	107.6	110.3	114.2	121.6	131.2	143.1	157.1	176.2	201.6	233.3
130°	110.3	111.3	114.5	118.7	126.2	135.7	147.4	160.8	178.5	200.7	229.3
132.5°	113.1	114.4	117.9	123.0	130.4	139.7	151.0	164.2	180.2	200.4	225.7
135°	118.0	119.4	123.3	128.6	136.1	145.6	156.5	168.6	182.7	200.0	220.9
137.5°	122.7	124.2	128.0	133.6	141.0	149.8	160.4	171.8	184.4	199.2	216.7
140°	125.8	127.6	131.1	136.8	143.8	152.7	162.9	173.5	185.5	199.0	214.1
142.5°	129.2	130.7	134.5	139.6	146.7	154.9	164.9	175.2	186.4	198.4	211.9
145°	134.6	135.7	138.9	144.2	150.2	158.3	167.5	177.0	186.9	197.5	208.8
147.5°	140.2	140.8	143.9	148.5	154.3	161.2	169.6	178.2	186.9	196.2	205.9
150°	143.8	144.2	147.0	151.6	156.5	162.9	171.0	178.5	186.9	195.1	203.9
152.5°	147.5	147.6	150.4	154.4	158.8	164.9	171.9	179.0	186.1	193.7	201.6
155°	153.0	153.0	155.1	158.7	162.6	167.5	173.5	179.2	185.2	191.2	198.2
157.5°	157.4	157.7	159.4	162.5	165.8	169.6	174.4	179.5	184.0	189.0	194.4
160°	160.8	160.8	162.2	165.0	167.5	171.0	175.3	179.5	183.4	187.3	191.9
162.5°	163.3	163.3	164.5	166.7	168.9	171.9	175.6	179.2	182.3	185.6	189.3
165°	167.1	166.8	167.5	169.3	170.7	173.2	176.0	178.5	180.6	183.1	185.9
167.5°	170.0	169.6	170.0	171.3	172.3	173.9	175.9	177.9	178.9	180.5	182.6
170°	171.7	171.0	171.4	172.4	173.2	173.9	175.6	177.0	177.8	178.8	180.6
172.5°	172.9	172.4	172.5	173.3	173.7	174.1	175.6	176.8	176.9	177.4	178.6
175°	174.2	173.9	173.5	174.2	174.2	174.6	175.3	176.0	175.6	175.6	176.3
177.5°	174.9	174.6	174.3	174.6	174.6	174.6	174.9	175.4	174.9	174.6	174.9
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6



TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	28.9	28.7	28.5	28.5	28.4	28.5	28.5	28.5
90°	8.8	9.2	9.5	10.2	9.9	10.2	10.6	10.2
92.5°	29.8	23.6	20.8	19.0	18.4	17.3	17.7	17.0
95°	127.2	86.2	67.5	54.8	48.1	44.9	42.4	41.0
97.5°	317.1	254.0	208.4	166.2	140.1	124.2	114.6	111.6
100°	416.6	388.0	346.7	296.5	260.8	235.0	221.2	221.6
102.5°	449.7	448.8	424.7	392.9	365.1	344.7	333.2	325.0
105°	459.4	494.7	501.4	492.3	476.0	462.6	451.3	449.5
107.5°	431.5	488.9	519.9	532.5	532.8	528.2	524.4	521.2
110°	405.0	470.0	514.5	539.3	549.2	552.0	551.3	550.6





TEST NUMBER: P332053

CATALOG NUMBER: S123DIP-S1165D365U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.7	445.1	495.0	526.8	544.9	553.7	556.4	556.5
115°	343.8	405.3	457.3	495.8	522.3	537.8	544.9	546.7
117.5°	318.6	371.7	418.3	457.4	485.1	502.9	513.0	515.4
120°	305.3	353.0	395.4	431.1	459.0	478.8	487.3	489.4
122.5°	294.9	338.0	377.3	410.5	435.3	453.1	462.4	465.1
125°	280.9	319.5	353.4	381.7	404.3	419.8	428.7	431.1
127.5°	268.8	303.1	333.7	359.5	379.6	392.9	400.9	403.1
130°	261.1	293.0	321.6	345.6	364.3	377.1	384.5	387.3
132.5°	254.1	283.3	310.0	332.9	350.5	363.2	369.8	371.8
135°	244.5	269.6	292.6	312.7	330.1	340.7	347.0	349.5
137.5°	235.8	256.4	276.2	293.7	308.2	319.0	324.3	326.0
140°	230.8	248.8	265.7	280.9	294.4	304.3	309.9	309.6
142.5°	226.0	241.4	256.1	269.3	280.8	289.6	294.6	294.3
145°	220.2	231.8	243.1	253.4	262.2	269.6	272.5	273.2
147.5°	215.4	224.7	233.8	241.1	247.8	252.8	255.5	255.8
150°	212.0	220.2	227.6	234.3	239.6	243.5	245.6	245.6
152.5°	208.9	215.9	222.5	228.1	232.2	235.8	237.1	237.1
155°	204.3	209.9	215.2	219.4	222.6	225.5	226.2	226.5
157.5°	199.3	204.0	208.1	211.5	214.2	216.3	216.9	216.8
160°	196.5	200.4	203.9	206.4	208.8	211.0	211.0	210.6
162.5°	193.1	196.4	199.7	201.9	203.5	205.3	205.3	205.0
165°	188.7	190.8	193.3	195.1	196.5	197.9	197.5	197.5
167.5°	184.9	186.5	187.9	189.2	189.8	190.8	190.5	190.5
170°	182.3	183.4	184.8	185.5	185.9	186.6	186.2	186.2
172.5°	180.1	180.9	182.0	182.4	182.5	183.2	182.6	182.3
175°	177.0	177.4	178.1	178.1	178.1	178.5	178.1	177.8
177.5°	175.1	175.4	175.7	175.7	175.4	175.7	175.1	175.1
180°	174.6	174.6	174.6	174.6	174.6	174.6	174.6	174.6

(END OF REPORT)