

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332006-840

Luminaire Tested: **S123DIP-S1000D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332006-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D365U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5625.5 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97		87	87	87		78	78	78	74
1	103	99	94	91	98	94	90	87	85	82	79		77	74	72		69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66		67	64	60		61	58	55	52
3	86	76	68	62	81	72	65	60	66	60	55		59	55	51		54	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47		53	48	44		48	44	41	38
5	72	60	51	45	68	57	49	44	52	46	41		48	42	38		43	39	35	33
6	67	54	45	39	63	52	44	38	47	41	36		43	38	33		39	35	31	29
7	62	49	40	35	58	47	39	34	43	36	32		39	34	30		36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28		36	31	27		33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25		33	28	24		30	26	23	21
10	50	37	30	25	48	36	29	24	33	27	23		31	25	22		28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	2.7
10°-20°	425.2	7.6
20°-30°	628.0	11.2
30°-40°	733.6	13.0
40°-50°	737.6	13.1
50°-60°	647.9	11.5
60°-70°	482.7	8.6
70°-80°	275.0	4.9
80°-90°	80.3	1.4
90°-100°	17.5	0.3
100°-110°	83.2	1.5
110°-120°	199.9	3.6
120°-130°	254.6	4.5
130°-140°	272.0	4.8
140°-150°	254.4	4.5
150°-160°	205.2	3.6
160°-170°	132.4	2.4
170°-180°	45.6	0.8
0°-30°	1203.8	21.4
0°-40°	1937.4	34.4
0°-60°	3322.8	59.1
0°-90°	4160.8	74.0
90°-120°	300.6	5.3
90°-150°	1081.5	19.2
90°-180°	1465.0	26.0
0°-180°	5625.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	0	4	9	10	11	5
95°	22	8	11	13	14	27
105°	106	108	78	18	16	113
115°	199	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	269
145°	404	406	407	408	408	253
155°	445	444	445	446	444	205
165°	469	468	468	470	468	133
175°	480	479	479	481	479	46
180°	480	480	480	480	480	



TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.7	28.1	27.5	27.0	26.4	26.1	26.1	26.0	26.0	26.0	25.8
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	6.7	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6
95°	21.8	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6
97.5°	43.7	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1
100°	60.3	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4
102.5°	79.2	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5
105°	106.3	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1
107.5°	135.0	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9
110°	154.2	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3



TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.4	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9
115°	199.4	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6
117.5°	225.7	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6
120°	242.0	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9
122.5°	258.5	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0
125°	281.2	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7
127.5°	303.2	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0
130°	316.9	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4
132.5°	330.0	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4
135°	350.1	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9
137.5°	367.2	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1
140°	378.6	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1
142.5°	389.2	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6
145°	403.9	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4
147.5°	417.9	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4
150°	426.5	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4
152.5°	434.1	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4
155°	445.0	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0
157.5°	453.4	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4
160°	458.6	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3
162.5°	463.4	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6
165°	469.3	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5
167.5°	473.8	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0
170°	476.4	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6
172.5°	478.1	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4
175°	480.3	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5
177.5°	480.9	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	25.5	25.3	25.1	25.1	25.1	25.1	25.2	25.2
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.2	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.2	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	12.7	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	19.6	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	50.1	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	122.7	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	155.7	153.1	150.5	143.5	132.2	120.8	109.5	98.2



TEST NUMBER: P332006-840

CATALOG NUMBER: S123DIP-S1000D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	179.0	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	206.4	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.3	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	247.5	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.4	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	285.8	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.2	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	321.8	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	334.7	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.4	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.4	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	392.9	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.5	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.5	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.6	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	435.7	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.5	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	453.9	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	458.8	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.2	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.1	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.0	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.0	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	480.8	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)