

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831266

Luminaire Tested: S123DIP-S1165D585U835-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831266
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D585U835-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7445.5 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 57.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831266
CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72		
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62		
2	95	88	82	77	90	83	78	73	75	71	68	68	65	62	61	59	56	53		
3	87	78	71	65	82	74	68	63	67	62	58	61	57	53	55	52	49	46		
4	80	70	62	56	76	66	59	54	61	55	50	55	50	47	50	46	43	40		
5	74	63	55	49	70	60	53	47	55	49	44	50	45	41	45	42	38	36		
6	69	57	49	43	65	55	47	42	50	44	39	46	41	37	42	38	34	32		
7	64	52	44	39	61	50	43	38	46	40	35	42	37	33	38	34	31	29		
8	60	48	40	35	57	46	39	34	42	36	32	39	34	30	36	32	28	26		
9	56	44	37	32	53	42	35	31	39	33	29	36	31	28	33	29	26	24		
10	53	41	34	29	50	39	33	28	36	31	27	34	29	25	31	27	24	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	35652	35652	35652	35652	35652
5°	45089	42557	35971	28988	26639
10°	45527	46904	35732	23107	20193
15°	34290	43547	35489	19568	17076
20°	23891	35238	35035	17113	15511
25°	18218	27099	34264	15745	14549
30°	15760	21530	33030	14777	13774
35°	14623	18177	31608	14077	13228
40°	13843	16305	29609	13412	13045
45°	13384	15092	27070	12892	12962
50°	13152	14130	24065	12419	12894
55°	12662	13427	21114	11971	12951
60°	12211	12673	18200	11548	12738
65°	11469	11961	15697	11097	12488
70°	10593	11053	13350	10351	11755
75°	9590	9906	11441	9619	10738
80°	7910	8672	9050	8387	9050
85°	6262	7027	6644	7114	7213

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 30908 cd/sqm



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	313.1	4.2
10°-20°	779.0	10.5
20°-30°	922.4	12.4
30°-40°	927.4	12.5
40°-50°	850.9	11.4
50°-60°	702.3	9.4
60°-70°	496.8	6.7
70°-80°	265.2	3.6
80°-90°	68.8	0.9
90°-100°	152.9	2.1
100°-110°	447.6	6.0
110°-120°	437.1	5.9
120°-130°	348.1	4.7
130°-140°	274.7	3.7
140°-150°	204.9	2.8
150°-160°	142.9	1.9
160°-170°	83.9	1.1
170°-180°	27.3	0.4
0°-30°	2014.6	27.1
0°-40°	2942.0	39.5
0°-60°	4495.2	60.4
0°-90°	5326.1	71.5
90°-120°	1037.7	13.9
90°-150°	1865.4	25.1
90°-180°	2119.0	28.5
0°-180°	7445.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	3312	3312	3312	3312	3312	
5°	4173	3939	3329	2683	2465	398
15°	3077	3908	3185	1756	1532	850
25°	1534	2282	2885	1326	1225	724
35°	1113	1383	2405	1071	1007	699
45°	879	991	1778	847	852	681
55°	675	716	1125	638	690	604
65°	450	470	616	436	490	447
75°	231	238	275	231	258	242
85°	51	57	54	58	58	57
90°	16	14	1	14	16	12
95°	66	338	19	338	66	108
105°	726	459	66	459	726	724
115°	882	351	117	351	882	860
125°	696	327	163	327	696	630
135°	564	323	190	323	564	438
145°	441	319	217	319	441	280
155°	366	309	247	309	366	170
165°	319	296	270	296	319	91
175°	287	284	281	284	287	28
180°	282	282	282	282	282	



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2
2.5°	3733.4	3729.5	3725.7	3706.5	3687.3	3678.0	3668.8	3641.2	3613.5	3582.8	3552.0
5°	4173.0	4183.7	4194.5	4182.2	4169.9	4132.2	4094.6	4044.6	3994.7	3938.6	3882.5
7.5°	4375.8	4382.0	4388.1	4380.5	4372.8	4362.8	4352.8	4308.2	4263.6	4206.0	4148.4
10°	4165.3	4179.1	4192.9	4222.9	4252.9	4286.7	4320.5	4314.4	4308.2	4291.3	4274.4
12.5°	3702.6	3719.5	3736.5	3796.4	3856.3	3933.2	4010.0	4076.1	4142.2	4188.3	4234.4
15°	3077.1	3124.0	3170.8	3225.4	3280.0	3392.9	3505.9	3645.0	3784.1	3907.8	4031.6
17.5°	2534.5	2552.2	2569.9	2628.3	2686.7	2828.9	2971.0	3131.6	3292.3	3497.5	3702.6
20°	2085.7	2101.9	2118.0	2194.8	2271.7	2383.1	2494.6	2675.2	2855.8	3076.3	3296.9
22.5°	1752.2	1777.5	1802.9	1845.9	1889.0	1995.8	2102.6	2263.2	2423.9	2667.5	2911.1
25°	1533.9	1552.4	1570.8	1596.9	1623.1	1708.4	1793.7	1925.9	2058.0	2281.7	2505.3
27.5°	1384.8	1392.5	1400.2	1426.3	1452.5	1507.8	1563.1	1676.9	1790.6	1980.4	2170.2
30°	1268.0	1273.4	1278.8	1301.8	1324.9	1362.6	1400.2	1482.4	1564.7	1732.2	1899.7
32.5°	1186.6	1190.4	1194.3	1211.9	1229.6	1256.5	1283.4	1343.3	1403.3	1541.6	1679.9
35°	1112.8	1115.1	1117.4	1130.5	1143.5	1163.5	1183.5	1228.8	1274.2	1383.3	1492.4
37.5°	1048.2	1051.3	1054.4	1062.1	1069.8	1087.4	1105.1	1141.2	1177.3	1261.1	1344.9
40°	985.2	990.6	996.0	1001.4	1006.7	1021.3	1035.9	1063.6	1091.3	1160.4	1229.6
42.5°	931.4	936.8	942.2	944.5	946.8	955.2	963.7	989.1	1014.4	1065.9	1117.4
45°	879.2	881.5	883.8	886.1	888.4	895.3	902.2	924.5	946.8	991.4	1035.9
47.5°	831.5	831.5	831.5	833.1	834.6	840.7	846.9	863.0	879.2	913.7	948.3
50°	785.4	785.4	785.4	783.1	780.8	784.6	788.5	800.8	813.1	843.8	874.6
52.5°	730.1	730.1	730.1	730.8	731.6	731.6	731.6	742.4	753.1	780.8	808.5
55°	674.7	677.8	680.9	678.6	676.3	677.8	679.4	686.3	693.2	715.5	737.8
57.5°	619.4	620.9	622.5	621.7	620.9	621.7	622.5	628.6	634.8	651.7	668.6
60°	567.2	567.2	567.2	565.6	564.1	565.6	567.2	570.2	573.3	588.7	604.0
62.5°	508.7	509.5	510.3	511.1	511.8	510.3	508.7	512.6	516.4	528.0	539.5
65°	450.3	451.1	451.9	454.2	456.5	455.0	453.4	457.3	461.1	469.6	478.0
67.5°	398.1	396.5	395.0	395.8	396.5	398.9	401.2	401.9	402.7	411.9	421.1
70°	336.6	338.1	339.7	338.9	338.1	338.9	339.7	342.0	344.3	351.2	358.1
72.5°	281.3	282.0	282.8	282.8	282.8	284.3	285.9	288.2	290.5	294.3	298.2
75°	230.6	230.6	230.6	232.1	233.6	234.4	235.2	235.2	235.2	238.2	241.3
77.5°	175.2	179.1	182.9	182.1	181.4	182.9	184.4	186.7	189.1	190.6	192.1
80°	127.6	127.6	127.6	128.3	129.1	131.4	133.7	135.3	136.8	139.9	142.9
82.5°	81.5	82.2	83.0	85.3	87.6	89.1	90.7	93.0	95.3	95.3	95.3
85°	50.7	49.2	47.6	49.2	50.7	52.3	53.8	54.6	55.3	56.9	58.4
87.5°	24.6	24.6	24.6	24.6	24.6	25.4	26.1	26.1	26.1	26.1	26.1
90°	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3	13.7	14.3	12.5
92.5°	30.2	31.4	30.8	33.1	34.2	38.2	43.9	56.5	79.3	106.1	117.5
95°	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3	274.3	338.2	301.2
97.5°	135.7	142.0	155.7	177.4	215.6	280.6	355.9	471.7	537.9	520.2	388.4
100°	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5	652.5	540.1	365.0
102.5°	566.4	582.9	600.6	631.4	673.0	717.0	748.9	739.2	658.2	503.1	330.8
105°	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5	622.3	458.6	304.0
107.5°	829.3	835.6	843.0	853.3	856.7	841.3	796.8	707.3	570.9	419.2	284.6
110°	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6	523.0	386.7	274.3



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	900.6	900.1	894.3	877.8	845.3	791.1	708.4	600.6	481.4	365.0	268.6
115°	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0	449.5	350.8	268.1
117.5°	842.4	838.4	821.3	793.4	748.9	684.4	607.4	519.6	428.4	341.1	268.6
120°	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8	412.4	334.8	270.9
122.5°	740.9	736.4	721.0	693.0	654.2	601.7	539.6	471.7	399.3	330.8	274.9
125°	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4	388.4	327.4	278.9
127.5°	657.1	653.6	640.5	618.9	585.8	543.6	493.4	436.9	378.2	325.7	283.5
130°	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5	370.2	324.0	288.0
132.5°	593.8	590.9	580.6	560.1	532.2	495.7	453.4	407.2	362.8	323.4	291.5
135°	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7	356.5	322.8	294.9
137.5°	532.7	529.3	520.8	503.1	479.1	450.0	416.9	382.7	350.8	321.7	297.2
140°	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5	345.6	321.1	299.4
142.5°	468.8	469.4	461.4	447.7	430.1	409.5	386.7	362.8	341.1	320.0	301.2
145°	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3	337.1	318.8	301.7
147.5°	416.9	416.4	411.8	403.3	391.8	379.9	364.5	349.1	333.1	317.1	301.7
150°	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2	329.1	314.8	301.7
152.5°	379.3	379.3	377.6	371.9	365.6	357.1	346.8	336.0	324.5	312.0	300.0
155°	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7	320.0	308.6	298.9
157.5°	352.5	352.5	351.4	347.9	343.4	337.7	330.8	322.8	314.8	305.7	297.2
160°	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1	309.7	302.3	296.0
162.5°	328.5	329.1	329.1	326.3	324.0	320.6	315.4	310.3	304.6	298.9	293.7
165°	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6	300.0	295.5	291.5
167.5°	309.1	309.1	309.7	308.0	306.9	304.6	302.3	299.4	295.5	292.0	289.2
170°	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3	291.5	288.6	286.9
172.5°	292.6	293.2	294.3	293.2	293.2	292.6	290.9	289.8	287.5	285.8	285.2
175°	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8	284.6	283.5	283.5
177.5°	282.9	282.9	284.0	283.5	284.0	284.0	283.5	282.9	282.3	281.8	282.3
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2
2.5°	3542.8	3533.6	3499.8	3465.9	3427.5	3389.1	3360.7	3332.2	3290.0	3247.7	3213.1
5°	3839.4	3796.4	3724.9	3653.5	3556.6	3459.8	3394.5	3329.1	3241.5	3153.9	3084.0
7.5°	4074.6	4000.8	3900.9	3801.0	3674.2	3547.4	3427.5	3307.6	3173.9	3040.2	2931.1
10°	4224.5	4174.5	4059.2	3944.0	3774.1	3604.3	3436.7	3269.2	3097.1	2924.9	2780.4
12.5°	4239.1	4243.7	4137.6	4031.6	3839.4	3647.3	3443.7	3240.0	3023.3	2806.6	2638.3
15°	4110.7	4189.9	4131.5	4073.1	3879.4	3685.7	3435.2	3184.7	2934.9	2685.1	2490.7
17.5°	3872.5	4042.3	4050.8	4059.2	3865.6	3671.9	3394.5	3117.0	2834.2	2551.4	2347.0
20°	3547.4	3797.9	3884.0	3970.1	3812.5	3655.0	3356.8	3058.6	2742.0	2425.4	2211.0
22.5°	3215.4	3519.7	3677.3	3834.8	3718.0	3601.2	3283.8	2966.4	2632.1	2297.8	2080.3
25°	2837.3	3169.3	3411.4	3653.5	3582.0	3510.5	3197.7	2885.0	2529.1	2173.3	1951.2
27.5°	2507.6	2845.0	3137.0	3429.1	3413.7	3398.3	3087.8	2777.4	2413.1	2048.8	1834.4
30°	2214.1	2528.4	2855.0	3181.6	3219.3	3256.9	2957.2	2657.5	2292.4	1927.4	1720.7
32.5°	1954.3	2228.7	2579.1	2929.5	3003.3	3077.1	2806.6	2536.1	2174.9	1813.7	1614.6
35°	1741.4	1990.4	2340.9	2691.3	2783.5	2875.7	2640.6	2405.4	2053.4	1701.5	1511.6
37.5°	1553.1	1761.4	2103.4	2445.4	2558.3	2671.3	2460.7	2250.2	1920.5	1590.8	1416.3
40°	1397.1	1564.7	1879.0	2193.3	2323.9	2454.6	2280.9	2107.2	1794.5	1481.7	1321.1
42.5°	1266.5	1415.6	1700.7	1985.8	2111.1	2236.3	2089.6	1942.8	1664.6	1386.4	1239.6
45°	1155.1	1274.2	1533.2	1792.1	1911.3	2030.4	1904.3	1778.3	1533.2	1288.0	1151.2
47.5°	1050.5	1152.8	1374.1	1595.4	1701.5	1807.5	1709.1	1610.8	1403.3	1195.8	1072.1
50°	956.8	1039.0	1232.7	1426.3	1518.6	1610.8	1523.9	1437.1	1266.5	1095.9	988.3
52.5°	875.3	942.2	1104.3	1266.5	1345.6	1424.8	1350.3	1275.7	1140.5	1005.2	911.4
55°	794.6	851.5	992.1	1132.8	1186.6	1240.4	1182.7	1125.1	1016.0	906.8	827.7
57.5°	719.3	770.0	885.3	1000.6	1042.1	1083.6	1031.3	979.1	896.8	814.6	748.5
60°	645.5	687.0	783.1	879.2	904.5	929.9	887.6	845.4	787.7	730.1	670.9
62.5°	577.1	614.8	686.3	757.7	774.6	791.6	759.3	727.0	683.2	639.4	593.3
65°	506.4	534.9	593.3	651.7	662.4	673.2	644.8	616.3	583.3	550.2	516.4
67.5°	441.1	461.1	508.7	556.4	557.2	557.9	534.9	511.8	493.4	474.9	448.0
70°	377.3	396.5	428.1	459.6	460.3	461.1	442.7	424.2	410.4	396.5	376.6
72.5°	312.0	325.8	349.7	373.5	372.0	370.4	358.9	347.4	336.6	325.8	311.2
75°	252.8	264.4	280.5	296.6	292.0	287.4	281.3	275.1	265.9	256.7	247.5
77.5°	199.0	206.0	215.2	224.4	221.3	218.3	212.9	207.5	200.6	193.7	189.8
80°	146.0	149.1	155.2	161.4	159.8	158.3	152.2	146.0	144.5	142.9	137.6
82.5°	99.1	103.0	104.5	106.1	105.3	104.5	99.9	95.3	93.8	92.2	91.5
85°	59.2	59.9	60.7	61.5	59.2	56.9	55.3	53.8	53.8	53.8	53.0
87.5°	26.9	27.7	27.7	27.7	26.9	26.1	24.6	23.1	23.8	24.6	24.6
90°	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	87.8	57.6	39.4	29.1	23.4	18.3	12.5	8.6	12.5	18.3	23.4
95°	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	231.0	132.3	84.4	59.9	45.1	36.5	31.4	30.8	31.4	36.5	45.1
100°	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2	42.8	46.8	54.8
102.5°	201.3	132.9	98.1	78.1	66.2	58.7	55.3	54.2	55.3	58.7	66.2
105°	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2	67.9	71.3	78.1
107.5°	195.1	144.9	117.5	101.0	90.7	83.8	80.4	78.7	80.4	83.8	90.7
110°	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4	94.1	97.0	103.2



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	203.6	164.3	140.9	125.5	115.8	109.5	106.7	104.9	106.7	109.5	115.8
115°	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9	119.2	122.6	128.3
117.5°	217.9	186.5	164.8	150.6	139.7	134.6	131.8	128.9	131.8	134.6	139.7
120°	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5	143.2	146.0	151.7
122.5°	235.6	208.8	188.8	173.4	163.1	156.9	154.0	152.3	154.0	156.9	163.1
125°	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6	163.7	167.1	173.4
127.5°	252.1	229.3	209.9	194.5	182.5	176.2	172.3	170.5	172.3	176.2	182.5
130°	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0	179.7	184.8	191.6
132.5°	266.4	245.3	227.0	212.2	200.2	191.6	185.9	183.7	185.9	191.6	200.2
135°	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5	192.8	199.1	207.6
137.5°	276.6	257.8	240.7	226.4	214.5	205.3	199.1	196.8	199.1	205.3	214.5
140°	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1	205.9	211.6	220.7
142.5°	283.5	266.9	251.0	237.8	226.4	218.5	212.2	209.9	212.2	218.5	226.4
145°	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3	219.0	224.2	232.7
147.5°	287.5	273.2	259.5	248.1	238.4	231.0	225.9	224.7	225.9	231.0	238.4
150°	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1	232.7	237.3	244.7
152.5°	289.2	277.8	266.9	257.2	250.4	244.1	239.6	239.6	239.6	244.1	250.4
155°	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0	247.0	250.4	256.1
157.5°	289.8	281.2	273.2	266.9	261.2	256.1	253.2	252.7	253.2	256.1	261.2
160°	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5	259.5	261.8	266.4
162.5°	289.2	283.5	277.8	273.2	269.8	266.4	264.7	264.7	264.7	266.4	269.8
165°	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8	269.2	270.4	273.2
167.5°	287.5	284.0	280.6	277.8	276.1	273.8	273.2	273.8	273.2	273.8	276.1
170°	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2	276.1	276.6	278.3
172.5°	285.2	283.5	281.2	280.6	280.1	278.9	278.9	279.5	278.9	278.9	280.1
175°	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2	280.6	280.1	281.2
177.5°	283.5	282.3	281.8	281.8	281.8	281.2	281.8	282.3	281.8	281.2	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2	3312.2
2.5°	3178.5	3148.6	3118.6	3095.5	3072.5	3033.3	2994.1	2984.9	2975.6	2962.6	2949.5
5°	3014.1	2940.3	2866.5	2800.4	2734.3	2682.8	2631.4	2597.5	2563.7	2539.1	2514.5
7.5°	2821.9	2711.3	2600.6	2522.2	2443.8	2369.3	2294.7	2270.9	2247.1	2214.8	2182.5
10°	2636.0	2513.8	2391.6	2289.4	2187.2	2114.1	2041.1	2011.9	1982.7	1942.0	1901.3
12.5°	2470.0	2336.2	2202.5	2099.5	1996.6	1925.9	1855.2	1812.9	1770.6	1747.6	1724.5
15°	2296.3	2153.3	2010.4	1915.1	1819.8	1756.0	1692.2	1655.4	1618.5	1596.2	1573.9
17.5°	2142.6	2001.2	1859.8	1768.3	1676.9	1618.5	1560.1	1527.8	1495.5	1478.6	1461.7
20°	1996.6	1858.2	1719.9	1630.8	1541.6	1494.0	1446.3	1425.6	1404.8	1391.0	1377.2
22.5°	1862.8	1726.8	1590.8	1514.7	1438.6	1400.2	1361.8	1347.2	1332.6	1321.1	1309.5
25°	1729.1	1607.7	1486.3	1421.7	1357.2	1325.7	1294.2	1279.6	1265.0	1253.4	1241.9
27.5°	1620.0	1504.0	1387.9	1332.6	1277.2	1252.7	1228.1	1216.5	1205.0	1194.3	1183.5
30°	1513.9	1410.2	1306.5	1258.8	1211.2	1188.9	1166.6	1155.1	1143.5	1133.5	1123.5
32.5°	1415.6	1326.4	1237.3	1193.5	1149.7	1131.2	1112.8	1099.0	1085.1	1077.4	1069.8
35°	1321.8	1241.9	1162.0	1125.9	1089.7	1071.3	1052.8	1041.3	1029.8	1023.6	1017.5
37.5°	1241.9	1170.4	1099.0	1064.4	1029.8	1012.1	994.4	984.5	974.5	972.2	969.8
40°	1160.4	1099.0	1037.5	1003.7	969.8	954.5	939.1	933.0	926.8	925.3	923.7
42.5°	1092.8	1032.9	972.9	942.2	911.4	898.4	885.3	882.2	879.2	881.5	883.8
45°	1014.4	964.5	914.5	886.1	857.6	846.9	836.1	833.8	831.5	836.1	840.7
47.5°	948.3	902.2	856.1	829.2	802.3	794.6	786.9	786.2	785.4	791.6	797.7
50°	880.7	836.1	791.6	770.0	748.5	741.6	734.7	737.0	739.3	749.3	759.3
52.5°	817.7	776.2	734.7	714.7	694.7	690.1	685.5	690.9	696.3	707.0	717.8
55°	748.5	710.9	673.2	657.8	642.5	637.9	633.2	644.0	654.8	664.8	674.7
57.5°	682.4	649.4	616.3	602.5	588.7	587.9	587.1	597.1	607.1	617.9	628.6
60°	611.7	584.1	556.4	545.6	534.9	536.4	538.0	549.5	561.0	569.5	577.9
62.5°	547.2	524.1	501.1	491.1	481.1	484.9	488.8	500.3	511.8	521.8	531.8
65°	482.6	463.4	444.2	437.3	430.4	435.7	441.1	451.1	461.1	468.0	474.9
67.5°	421.1	405.0	388.9	383.5	378.1	383.5	388.9	398.9	408.8	415.8	422.7
70°	356.6	343.5	330.5	326.6	322.8	328.9	335.1	343.5	352.0	358.9	365.8
72.5°	296.6	286.7	276.7	275.9	275.1	280.5	285.9	294.3	302.8	307.4	312.0
75°	238.2	232.9	227.5	226.7	225.9	231.3	236.7	241.3	245.9	249.8	253.6
77.5°	186.0	181.4	176.8	177.5	178.3	182.1	186.0	190.6	195.2	197.5	199.8
80°	132.2	130.6	129.1	130.6	132.2	135.3	138.3	141.4	144.5	146.0	147.6
82.5°	90.7	89.1	87.6	89.9	92.2	94.5	96.8	99.1	101.4	102.2	103.0
85°	52.3	54.6	56.9	56.9	56.9	57.6	58.4	59.2	59.9	59.2	58.4
87.5°	24.6	25.4	26.1	26.1	26.1	26.9	27.7	27.7	27.7	26.9	26.1
90°	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3	14.8	15.4	16.5
92.5°	29.1	39.4	57.6	87.8	117.5	106.1	79.3	56.5	43.9	38.2	34.2
95°	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3	139.2	108.9	88.4
97.5°	59.9	84.4	132.3	231.0	388.4	520.2	537.9	471.7	355.9	280.6	215.6
100°	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5	626.3	559.5	478.5
102.5°	78.1	98.1	132.9	201.3	330.8	503.1	658.2	739.2	748.9	717.0	673.0
105°	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5	798.5	809.4	794.5
107.5°	101.0	117.5	144.9	195.1	284.6	419.2	570.9	707.3	796.8	841.3	856.7
110°	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6	758.6	830.5	870.4

TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	125.5	140.9	164.3	203.6	268.6	365.0	481.4	600.6	708.4	791.1	845.3
115°	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0	654.2	738.1	800.2
117.5°	150.6	164.8	186.5	217.9	268.6	341.1	428.4	519.6	607.4	684.4	748.9
120°	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8	569.8	638.2	695.9
122.5°	173.4	188.8	208.8	235.6	274.9	330.8	399.3	471.7	539.6	601.7	654.2
125°	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4	515.6	570.4	616.0
127.5°	194.5	209.9	229.3	252.1	283.5	325.7	378.2	436.9	493.4	543.6	585.8
130°	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5	472.8	519.0	557.8
132.5°	212.2	227.0	245.3	266.4	291.5	323.4	362.8	407.2	453.4	495.7	532.2
135°	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7	435.2	472.3	504.8
137.5°	226.4	240.7	257.8	276.6	297.2	321.7	350.8	382.7	416.9	450.0	479.1
140°	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5	401.5	428.9	453.4
142.5°	237.8	251.0	266.9	283.5	301.2	320.0	341.1	362.8	386.7	409.5	430.1
145°	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3	374.2	392.4	409.0
147.5°	248.1	259.5	273.2	287.5	301.7	317.1	333.1	349.1	364.5	379.9	391.8
150°	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2	355.3	367.3	378.2
152.5°	257.2	266.9	277.8	289.2	300.0	312.0	324.5	336.0	346.8	357.1	365.6
155°	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7	338.8	347.4	354.2
157.5°	266.9	273.2	281.2	289.8	297.2	305.7	314.8	322.8	330.8	337.7	343.4
160°	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1	323.4	329.1	333.1
162.5°	273.2	277.8	283.5	289.2	293.7	298.9	304.6	310.3	315.4	320.6	324.0
165°	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6	308.0	312.0	314.8
167.5°	277.8	280.6	284.0	287.5	289.2	292.0	295.5	299.4	302.3	304.6	306.9
170°	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3	296.0	298.3	299.4
172.5°	280.6	281.2	283.5	285.2	285.2	285.8	287.5	289.8	290.9	292.6	293.2
175°	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8	286.3	287.5	287.5
177.5°	281.8	281.8	282.3	283.5	282.3	281.8	282.3	282.9	283.5	284.0	284.0
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	3312.2	3312.2	3312.2	3312.2
2.5°	2944.1	2938.8	2917.2	2895.7
5°	2496.1	2477.6	2471.5	2465.4
7.5°	2181.0	2179.5	2147.2	2114.9
10°	1903.6	1905.9	1876.7	1847.5
12.5°	1705.3	1686.1	1683.8	1681.5
15°	1556.2	1538.5	1535.5	1532.4
17.5°	1450.9	1440.2	1437.1	1434.0
20°	1371.0	1364.9	1359.5	1354.1
22.5°	1301.8	1294.2	1289.5	1284.9
25°	1235.0	1228.1	1226.5	1225.0
27.5°	1175.0	1166.6	1166.6	1166.6
30°	1118.2	1112.8	1110.5	1108.2
32.5°	1065.1	1060.5	1060.5	1060.5
35°	1015.2	1012.9	1009.8	1006.7
37.5°	969.8	969.8	968.3	966.8
40°	926.0	928.4	928.4	928.4
42.5°	886.1	888.4	888.4	888.4
45°	844.6	848.4	850.0	851.5
47.5°	803.9	810.0	811.5	813.1
50°	763.9	768.5	769.3	770.0
52.5°	723.2	728.5	732.4	736.2
55°	680.1	685.5	687.8	690.1
57.5°	634.0	639.4	640.2	640.9
60°	583.3	588.7	590.2	591.7
62.5°	534.9	538.0	539.5	541.0
65°	479.5	484.2	487.2	490.3
67.5°	426.5	430.4	430.4	430.4
70°	367.3	368.9	371.2	373.5
72.5°	312.8	313.5	313.5	313.5
75°	255.1	256.7	257.4	258.2
77.5°	200.6	201.3	201.3	201.3
80°	146.8	146.0	146.0	146.0
82.5°	100.7	98.4	98.4	98.4
85°	57.6	56.9	57.6	58.4
87.5°	26.1	26.1	26.1	26.1
90°	16.0	16.5	17.1	16.5
92.5°	33.1	30.8	31.4	30.2
95°	77.6	72.4	68.4	66.2
97.5°	177.4	155.7	142.0	135.7
100°	420.9	379.3	357.1	357.6
102.5°	631.4	600.6	582.9	566.4
105°	768.3	746.6	728.4	725.5
107.5°	853.3	843.0	835.6	829.3
110°	886.4	890.9	889.8	888.6



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	877.8	894.3	900.1	900.6
115°	843.0	868.1	879.5	882.4
117.5°	793.4	821.3	838.4	842.4
120°	740.9	772.9	786.5	790.0
122.5°	693.0	721.0	736.4	740.9
125°	652.5	677.6	691.9	695.9
127.5°	618.9	640.5	653.6	657.1
130°	588.1	608.6	620.6	625.1
132.5°	560.1	580.6	590.9	593.8
135°	532.7	549.8	560.1	564.1
137.5°	503.1	520.8	529.3	532.7
140°	475.1	491.1	500.2	499.6
142.5°	447.7	461.4	469.4	468.8
145°	423.2	435.2	439.8	440.9
147.5°	403.3	411.8	416.4	416.9
150°	386.7	393.0	396.4	396.4
152.5°	371.9	377.6	379.3	379.3
155°	359.3	363.9	365.0	365.6
157.5°	347.9	351.4	352.5	352.5
160°	337.1	340.5	340.5	339.9
162.5°	326.3	329.1	329.1	328.5
165°	317.1	319.4	318.8	318.8
167.5°	308.0	309.7	309.1	309.1
170°	300.0	301.2	300.6	300.6
172.5°	293.2	294.3	293.2	292.6
175°	287.5	288.0	287.5	286.9
177.5°	283.5	284.0	282.9	282.9
180°	281.8	281.8	281.8	281.8



TEST NUMBER: P831266

CATALOG NUMBER: S123DIP-S1165D585U835-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.80	18.84	18.56	19.61	20.54	20.04	21.07	20.79	21.84	22.77
	3H	19.46	20.39	20.23	21.17	22.13	21.47	22.40	22.24	23.18	24.14
	4H	20.04	20.92	20.83	21.71	22.68	21.93	22.81	22.72	23.60	24.57
	6H	20.42	21.23	21.22	22.03	23.01	22.22	23.02	23.01	23.82	24.81
	8H	20.53	21.29	21.33	22.11	23.10	22.28	23.05	23.09	23.87	24.85
	12H	20.58	21.31	21.39	22.12	23.13	22.31	23.04	23.12	23.85	24.86
4H	2H	18.40	19.27	19.19	20.06	21.03	20.22	21.10	21.01	21.88	22.86
	3H	20.24	20.97	21.04	21.79	22.78	21.85	22.58	22.66	23.41	24.39
	4H	20.94	21.60	21.76	22.43	23.45	22.44	23.11	23.26	23.93	24.95
	6H	21.43	22.00	22.26	22.85	23.87	22.86	23.43	23.69	24.28	25.30
	8H	21.57	22.10	22.40	22.94	23.98	22.97	23.51	23.81	24.35	25.38
	12H	21.64	22.12	22.50	22.99	24.03	23.03	23.50	23.88	24.37	25.41
8H	4H	21.22	21.76	22.06	22.60	23.63	22.56	23.10	23.40	23.94	24.97
	6H	21.82	22.26	22.68	23.14	24.18	23.07	23.51	23.94	24.40	25.43
	8H	22.03	22.42	22.90	23.30	24.35	23.25	23.64	24.13	24.52	25.58
	12H	22.16	22.50	23.03	23.37	24.48	23.36	23.71	24.24	24.58	25.68
12H	4H	21.23	21.71	22.09	22.57	23.61	22.55	23.02	23.40	23.89	24.93
	6H	21.87	22.26	22.74	23.14	24.19	23.09	23.48	23.96	24.36	25.41
	8H	22.11	22.45	22.99	23.33	24.43	23.29	23.64	24.17	24.51	25.62