

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332065

Luminaire Tested: **S123DIP-S1165D805U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332065  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D805U835-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7804.7 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	95	91	88	84	80	77	75	70	68	66	61	59	58	54
2	92	85	79	74	86	80	74	70	70	66	63	62	59	56	54	51	49	45
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42	39
4	77	66	59	52	72	63	56	50	56	50	46	49	45	41	43	40	37	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	26
7	61	48	40	35	57	46	39	33	41	35	31	36	32	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	32	27	33	29	25	30	26	23	20
9	53	40	33	28	49	38	31	27	34	29	24	31	26	22	27	23	21	18
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17460	17460	17460	17460
5°	20822	17535	15540	17535
10°	26063	17446	14036	17446
15°	31967	17306	13067	17306
20°	38080	17087	12441	17087
25°	40435	16820	12302	16820
30°	34657	16625	12367	16625
35°	24103	16348	12496	16348
40°	18156	16024	12456	16024
45°	15075	15541	12298	15541
50°	13504	14555	12188	14555
55°	12624	13495	12035	13495
60°	11842	12385	11911	12385
65°	11130	11291	11530	11291
70°	10439	10043	10980	10043
75°	9349	8792	10069	8792
80°	8182	7209	8672	7209
85°	6410	5236	5829	5236



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.8	2.0
10°-20°	512.4	6.6
20°-30°	859.9	11.0
30°-40°	973.7	12.5
40°-50°	873.2	11.2
50°-60°	704.7	9.0
60°-70°	491.0	6.3
70°-80°	258.1	3.3
80°-90°	66.1	0.8
90°-100°	214.9	2.8
100°-110°	608.6	7.8
110°-120°	598.7	7.7
120°-130°	477.5	6.1
130°-140°	376.5	4.8
140°-150°	281.0	3.6
150°-160°	195.9	2.5
160°-170°	115.1	1.5
170°-180°	37.4	0.5
0°-30°	1532.1	19.6
0°-40°	2505.8	32.1
0°-60°	4083.7	52.3
0°-90°	4898.9	62.8
90°-120°	1422.2	18.2
90°-150°	2557.3	32.8
90°-180°	2906.0	37.2
0°-180°	7804.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1622	1622	1622	1622	1622	
5°	1927	1623	1438	1623	1927	200
15°	2869	1553	1173	1553	2869	828
25°	3405	1416	1036	1416	3405	1493
35°	1834	1244	951	1244	1834	1192
45°	990	1021	808	1021	990	784
55°	673	719	641	719	673	604
65°	437	443	453	443	437	435
75°	225	211	242	211	225	241
85°	52	42	47	42	52	62
90°	23	2	23	2	23	15
95°	91	27	91	27	91	163
105°	994	91	994	91	994	981
115°	1210	160	1210	160	1210	1175
125°	954	223	954	223	954	864
135°	773	261	773	261	773	600
145°	604	298	604	298	604	384
155°	501	338	501	338	501	234
165°	437	370	437	370	437	125
175°	393	385	393	385	393	38
180°	386	386	386	386	386	



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1721.5	1720.2	1717.1	1719.6	1714.6	1707.6	1707.0	1700.7	1682.5	1681.2	1676.2
5°	1927.1	1920.8	1920.0	1919.2	1908.2	1893.3	1865.0	1862.6	1824.9	1806.0	1783.3
7.5°	2193.3	2196.6	2185.2	2175.1	2141.5	2119.3	2089.0	2050.2	2003.8	1956.8	1925.5
10°	2384.5	2410.4	2378.2	2356.2	2335.8	2297.2	2252.5	2196.6	2140.8	2075.6	2026.1
12.5°	2589.5	2602.2	2595.7	2575.0	2543.2	2484.6	2405.2	2343.8	2292.4	2183.8	2139.9
15°	2868.6	2916.6	2885.9	2815.2	2816.7	2760.9	2657.2	2543.2	2482.7	2387.6	2258.0
17.5°	3166.0	3172.0	3158.9	3100.0	3060.7	2984.0	2888.3	2779.0	2656.4	2541.4	2403.8
20°	3324.4	3319.7	3292.2	3261.6	3194.0	3134.3	3029.7	2907.9	2750.7	2637.6	2487.4
22.5°	3412.5	3404.6	3391.6	3365.9	3309.7	3245.5	3151.7	3018.6	2868.9	2713.0	2539.6
25°	3404.6	3414.8	3416.4	3409.3	3389.7	3351.2	3277.3	3171.2	3021.9	2821.5	2640.7
27.5°	3096.5	3111.0	3153.0	3190.2	3231.9	3274.3	3268.6	3216.0	3105.5	2932.4	2711.4
30°	2788.4	2757.0	2834.8	2933.1	2999.9	3117.7	3183.8	3187.7	3125.6	2977.1	2761.7
32.5°	2360.9	2395.5	2429.9	2550.8	2696.8	2829.2	2960.6	3066.4	3078.5	2979.6	2791.3
35°	1834.3	1877.6	1940.4	2003.3	2160.5	2295.7	2526.7	2727.9	2888.3	2909.5	2793.9
37.5°	1478.2	1499.5	1539.3	1602.3	1705.1	1865.5	2044.2	2298.5	2530.8	2703.6	2711.1
40°	1292.1	1298.3	1343.1	1391.1	1474.4	1606.4	1767.5	1992.3	2270.5	2511.8	2612.4
42.5°	1152.5	1166.3	1185.3	1231.4	1297.7	1397.1	1546.9	1732.6	1987.6	2265.3	2462.1
45°	990.3	1006.0	1017.8	1048.4	1095.6	1162.4	1266.9	1436.7	1630.8	1917.6	2182.5
47.5°	883.1	884.3	893.1	916.2	948.3	998.4	1072.3	1181.4	1359.6	1592.3	1864.2
50°	806.4	818.9	822.1	840.1	865.3	902.2	963.5	1056.3	1202.5	1406.8	1656.7
52.5°	752.3	756.1	764.9	777.9	799.9	828.7	881.8	954.4	1069.2	1243.3	1473.1
55°	672.7	672.7	681.4	691.6	704.2	730.1	765.5	818.9	906.2	1041.3	1231.5
57.5°	599.2	603.1	609.2	612.4	623.1	640.2	669.8	710.3	775.4	879.4	1030.7
60°	550.1	557.2	556.4	562.7	572.2	585.5	610.7	643.7	701.8	785.1	912.5
62.5°	507.4	506.9	506.8	514.3	523.7	536.5	552.8	581.4	630.8	704.7	813.1
65°	437.0	435.4	440.9	445.6	448.8	458.2	470.8	495.9	528.9	583.9	668.0
67.5°	374.4	369.9	372.8	374.4	379.8	387.1	398.9	414.5	440.7	484.9	548.3
70°	331.7	327.7	326.9	328.5	333.2	338.7	347.4	362.3	386.7	422.0	468.4
72.5°	287.6	285.0	284.8	288.3	290.5	294.1	300.2	313.9	333.2	359.8	403.0
75°	224.8	224.8	224.8	225.6	227.9	231.1	235.8	242.8	257.8	276.6	305.7
77.5°	168.5	168.3	167.4	167.2	170.7	172.1	173.2	179.8	188.1	200.9	222.1
80°	132.0	128.1	129.7	132.0	133.6	134.4	136.8	138.3	145.4	152.5	167.4
82.5°	98.1	94.8	95.1	98.7	99.0	99.8	102.2	104.4	107.0	113.5	121.5
85°	51.9	51.9	52.7	52.7	53.4	52.7	55.0	55.8	55.8	59.7	64.4
87.5°	23.4	22.3	22.8	23.2	22.8	23.1	23.6	24.0	24.5	25.3	25.4
90°	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5	18.8	19.5	17.2
92.5°	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8	90.7	120.2	132.3
95°	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5	376.1	463.6	412.8
97.5°	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6	768.7	718.5	526.0
100°	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8	894.4	740.4	500.4
102.5°	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9	900.7	699.7	462.8
105°	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4	853.0	628.6	416.7
107.5°	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8	769.5	565.7	387.3
110°	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0	716.9	530.1	376.1



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8	671.3	506.3	369.8
115°	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7	616.1	480.8	367.5
117.5°	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9	582.8	465.8	368.9
120°	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5	565.3	458.9	371.4
122.5°	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4	550.9	454.6	375.7
125°	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5	532.4	448.8	382.3
127.5°	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7	516.2	446.0	389.8
130°	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8	507.4	444.1	394.8
132.5°	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1	499.3	443.4	398.6
135°	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0	488.6	442.5	404.2
137.5°	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8	479.4	440.8	408.0
140°	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5	473.8	440.2	410.5
142.5°	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9	468.8	438.9	412.3
145°	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1	462.1	437.0	413.6
147.5°	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6	455.5	434.1	413.6
150°	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1	451.1	431.6	413.6
152.5°	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2	446.1	428.4	411.7
155°	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9	438.6	423.0	409.7
157.5°	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9	430.2	418.1	407.0
160°	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7	424.5	414.4	405.8
162.5°	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2	418.9	410.6	403.3
165°	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5	411.2	405.0	399.5
167.5°	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0	403.9	399.4	395.8
170°	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4	399.5	395.6	393.3
172.5°	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4	395.1	392.5	391.4
175°	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7	390.1	388.6	388.6
177.5°	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1672.4	1667.4	1662.4	1653.6	1646.0	1635.3	1632.2	1628.4	1617.1	1607.1	1599.5
5°	1774.6	1755.7	1728.2	1703.1	1682.7	1655.2	1639.4	1622.9	1599.3	1578.1	1560.8
7.5°	1881.5	1844.4	1801.6	1755.4	1712.4	1670.9	1637.4	1607.5	1574.5	1543.2	1518.9
10°	1966.4	1912.9	1853.2	1788.8	1733.7	1680.3	1635.5	1596.2	1553.8	1516.8	1486.2
12.5°	2063.2	1984.0	1901.6	1823.3	1758.3	1684.1	1629.8	1579.9	1531.8	1487.3	1452.9
15°	2177.8	2077.2	1979.7	1872.1	1773.0	1680.3	1615.9	1553.0	1497.2	1451.6	1407.6
17.5°	2282.2	2168.2	2039.8	1908.8	1789.4	1679.4	1589.1	1518.1	1448.3	1392.5	1348.6
20°	2341.3	2211.6	2066.2	1930.2	1798.2	1675.6	1576.6	1491.7	1416.2	1357.3	1307.8
22.5°	2392.2	2240.5	2090.1	1944.7	1797.6	1665.5	1553.3	1465.9	1384.2	1326.5	1273.8
25°	2445.0	2263.5	2112.6	1942.0	1777.8	1641.0	1515.3	1416.2	1334.5	1266.9	1212.7
27.5°	2490.3	2261.9	2082.8	1899.4	1746.6	1609.6	1475.3	1369.1	1282.3	1208.9	1153.9
30°	2520.4	2265.0	2052.0	1870.5	1716.5	1575.0	1444.5	1337.6	1246.5	1171.8	1119.9
32.5°	2539.3	2263.1	2023.7	1830.3	1668.7	1543.5	1411.2	1300.5	1206.9	1133.5	1083.5
35°	2550.3	2249.3	1975.0	1747.1	1591.5	1469.7	1358.9	1244.1	1145.9	1077.5	1020.9
37.5°	2528.3	2220.2	1918.4	1666.9	1496.6	1376.6	1283.4	1185.6	1091.6	1016.4	967.6
40°	2493.7	2201.4	1874.4	1610.4	1431.2	1315.6	1236.3	1140.4	1047.6	976.1	930.5
42.5°	2427.7	2163.0	1826.0	1547.5	1363.3	1247.7	1174.6	1094.5	1006.8	939.6	894.1
45°	2266.6	2079.5	1753.4	1453.2	1263.0	1143.5	1079.1	1020.9	941.5	876.3	837.0
47.5°	2043.1	1954.0	1648.4	1353.7	1158.3	1043.4	976.4	929.6	871.6	818.9	781.2
50°	1887.8	1850.8	1577.3	1285.8	1088.5	976.1	911.7	869.2	827.6	774.9	740.3
52.5°	1708.6	1731.4	1494.4	1215.3	1017.5	907.0	846.3	812.6	774.8	731.5	701.4
55°	1456.3	1538.8	1351.0	1097.1	911.7	806.4	749.0	719.1	697.1	664.9	639.0
57.5°	1220.1	1325.1	1196.0	975.3	807.8	716.9	661.9	629.4	615.2	598.4	578.0
60°	1079.9	1183.6	1085.4	893.6	738.0	651.5	602.8	575.3	561.1	549.4	532.1
62.5°	954.7	1059.7	977.2	810.6	669.4	589.3	546.8	520.0	509.0	502.8	488.1
65°	782.8	873.2	818.1	681.4	571.4	500.6	462.1	443.3	433.0	430.7	421.3
67.5°	637.1	705.9	665.8	565.2	478.6	417.5	384.8	368.8	360.9	360.1	353.0
70°	541.5	605.9	575.3	484.1	409.5	361.5	333.2	319.1	314.4	313.6	309.7
72.5°	467.3	512.3	487.9	411.8	354.1	310.6	289.8	275.1	269.7	270.8	268.2
75°	345.8	379.6	365.5	312.8	266.4	238.1	220.8	211.4	206.7	209.1	205.9
77.5°	248.8	270.2	257.5	221.0	192.4	172.0	159.2	153.4	149.2	149.0	147.6
80°	187.8	200.4	193.3	171.3	147.8	130.5	120.2	116.3	114.0	113.2	112.4
82.5°	133.8	144.5	136.1	121.0	105.0	94.6	88.8	83.6	81.9	82.4	81.6
85°	67.6	71.5	68.4	58.9	52.7	47.9	44.8	42.4	40.9	41.7	40.1
87.5°	26.2	26.4	24.0	21.2	19.6	17.3	17.0	15.4	14.5	14.8	14.6
90°	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6	3.1	4.7	7.0
92.5°	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7	14.4	21.0	27.1
95°	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6	28.9	37.5	50.8
97.5°	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3	46.1	52.9	64.4
100°	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9	58.6	64.1	75.1
102.5°	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0	72.4	77.2	87.6
105°	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7	93.0	97.7	107.1
107.5°	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6	114.0	118.5	127.7
110°	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7	129.0	132.9	141.5





TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4	142.8	146.7	155.3
115°	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3	163.4	168.1	175.9
117.5°	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1	183.7	187.6	194.8
120°	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9	196.2	200.1	208.0
122.5°	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8	208.1	212.0	220.5
125°	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8	224.4	229.1	237.7
127.5°	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8	238.1	243.9	252.7
130°	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9	246.3	253.3	262.7
132.5°	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2	253.2	260.8	272.1
135°	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1	264.3	272.9	284.6
137.5°	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4	274.7	283.2	295.7
140°	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3	282.2	290.1	302.6
142.5°	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8	289.1	297.6	308.8
145°	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9	300.2	307.3	319.0
147.5°	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1	311.5	318.4	328.5
150°	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2	319.0	325.2	335.4
152.5°	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3	326.5	332.7	341.7
155°	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5	338.5	343.2	351.0
157.5°	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2	348.8	352.6	359.5
160°	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7	355.7	358.9	365.1
162.5°	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4	361.4	363.9	368.9
165°	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8	369.0	370.6	374.5
167.5°	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2	375.3	376.1	379.0
170°	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0	378.4	379.2	381.5
172.5°	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5	381.5	381.7	383.4
175°	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4	384.7	383.9	385.4
177.5°	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8	386.2	385.6	386.2
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1595.1	1590.7	1584.4	1575.0	1567.4	1555.5	1555.5	1557.4	1557.4	1556.8	1555.5
5°	1546.7	1534.9	1520.8	1504.3	1487.0	1469.7	1466.5	1460.2	1455.5	1452.4	1448.5
7.5°	1495.6	1474.7	1454.1	1431.0	1409.9	1392.5	1380.4	1370.3	1363.9	1357.0	1351.9
10°	1461.0	1435.1	1410.7	1386.4	1359.6	1338.4	1325.1	1315.6	1308.6	1302.3	1299.1
12.5°	1420.2	1390.5	1363.6	1340.5	1311.2	1289.4	1276.7	1272.2	1263.9	1250.7	1243.8
15°	1360.4	1332.9	1300.7	1265.3	1251.2	1224.5	1209.5	1202.5	1197.7	1187.5	1184.4
17.5°	1309.3	1273.3	1237.2	1210.8	1184.5	1162.8	1154.5	1145.7	1139.4	1131.1	1128.6
20°	1268.5	1236.3	1203.2	1175.0	1147.4	1123.9	1116.8	1110.5	1104.2	1100.3	1097.1
22.5°	1227.0	1194.8	1167.4	1141.0	1111.6	1096.2	1088.5	1081.6	1077.2	1074.5	1071.4
25°	1168.7	1140.4	1109.7	1086.1	1062.6	1052.3	1047.6	1043.7	1040.6	1036.6	1035.8
27.5°	1116.5	1085.7	1060.8	1038.8	1021.9	1013.4	1008.8	1006.9	1007.6	1009.0	1009.9
30°	1077.5	1049.2	1028.8	1009.9	994.2	986.3	985.5	985.5	988.7	989.5	991.0
32.5°	1041.7	1018.4	998.0	979.7	967.8	962.4	965.4	965.4	967.9	970.0	972.8
35°	989.5	969.0	953.3	937.6	927.4	929.7	931.3	932.9	936.8	941.5	944.7
37.5°	939.6	921.9	905.5	893.3	888.6	892.8	896.6	899.9	904.4	908.1	911.2
40°	903.8	890.4	874.7	863.7	865.3	867.7	870.8	874.7	878.7	881.0	884.2
42.5°	870.5	856.5	844.6	835.4	837.6	840.6	842.5	844.6	849.1	853.4	855.2
45°	819.7	808.7	797.7	792.2	793.8	795.4	796.9	799.3	803.2	806.4	807.1
47.5°	762.7	755.0	747.6	742.2	744.7	744.1	746.2	751.2	752.4	754.3	758.7
50°	726.2	719.1	710.5	708.9	708.9	708.9	709.7	716.0	716.0	719.1	722.3
52.5°	686.0	681.4	675.9	673.1	671.8	671.8	675.1	678.3	679.5	683.9	687.1
55°	626.4	621.7	616.9	614.6	613.0	614.6	620.9	622.4	626.4	628.7	631.1
57.5°	564.3	560.7	556.9	555.6	555.3	557.4	560.8	565.5	566.5	573.7	577.3
60°	523.4	517.9	514.8	514.8	513.2	520.3	518.7	526.6	528.1	532.9	538.4
62.5°	481.3	473.9	472.7	472.7	474.9	476.9	479.1	482.6	486.6	492.6	496.9
65°	413.4	409.5	415.0	414.2	412.6	417.3	417.3	421.3	426.0	431.5	440.1
67.5°	349.1	347.1	347.5	347.5	349.9	352.6	354.8	358.2	363.9	369.7	375.4
70°	305.7	308.1	304.2	307.3	309.7	310.4	312.0	316.7	323.0	326.9	333.2
72.5°	263.6	263.4	263.9	265.2	267.5	268.9	270.5	275.9	282.8	286.1	291.1
75°	202.8	202.0	204.3	204.3	208.3	209.8	211.4	213.8	220.1	224.8	228.7
77.5°	148.1	149.0	148.5	151.2	150.1	150.4	155.3	157.7	158.3	167.6	169.6
80°	111.6	113.2	114.0	114.7	115.5	114.0	119.5	121.8	121.8	127.3	131.2
82.5°	80.2	81.1	83.2	83.9	84.1	85.7	86.1	87.9	89.8	92.1	97.3
85°	40.1	42.4	43.2	42.4	43.2	41.7	44.0	44.8	45.6	45.6	45.6
87.5°	14.3	15.2	15.1	16.2	16.0	17.1	17.0	15.9	16.0	18.1	15.9
90°	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5	20.3	21.1	22.7
92.5°	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8	52.2	46.1	42.1
95°	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5	190.8	149.3	121.2
97.5°	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6	562.0	461.1	367.6
100°	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8	858.4	767.0	655.9
102.5°	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9	992.9	939.6	869.2
105°	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4	1094.5	1109.4	1089.1
107.5°	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8	1081.7	1150.2	1178.0
110°	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0	1039.8	1138.3	1193.1



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8	984.8	1095.2	1165.5
115°	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7	896.7	1011.7	1096.9
117.5°	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9	822.3	925.5	1012.0
120°	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5	781.0	874.9	953.8
122.5°	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4	747.9	834.8	908.2
125°	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5	706.8	781.8	844.4
127.5°	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7	670.6	738.4	795.3
130°	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8	648.1	711.5	764.6
132.5°	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1	626.9	685.8	736.5
135°	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0	596.5	647.3	691.9
137.5°	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8	567.3	611.1	649.7
140°	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5	550.4	587.9	621.5
142.5°	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9	534.1	566.7	595.9
145°	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1	512.9	537.9	560.6
147.5°	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6	497.1	517.3	533.4
150°	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1	487.1	503.5	518.3
152.5°	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2	477.7	492.2	504.6
155°	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9	464.4	476.1	485.5
157.5°	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9	451.4	460.5	467.8
160°	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7	443.3	451.1	456.6
162.5°	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2	434.5	441.7	446.6
165°	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5	422.2	427.7	431.6
167.5°	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0	412.6	415.8	418.6
170°	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4	405.8	408.9	410.5
172.5°	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4	400.1	402.6	403.6
175°	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7	392.5	394.0	394.0
177.5°	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5	388.1	388.7	388.7
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1551.1	1550.5	1554.9	1551.7	1554.9	1550.5	1551.1	1555.5	1556.8	1557.4	1557.4
5°	1443.7	1446.1	1438.2	1438.2	1438.2	1446.1	1443.7	1448.5	1452.4	1455.5	1460.2
7.5°	1348.2	1344.7	1345.0	1340.8	1345.0	1344.7	1348.2	1351.9	1357.0	1363.9	1370.3
10°	1289.7	1285.0	1283.4	1284.2	1283.4	1285.0	1289.7	1299.1	1302.3	1308.6	1315.6
12.5°	1241.3	1240.3	1230.0	1230.1	1230.0	1240.3	1241.3	1243.8	1250.7	1263.9	1272.2
15°	1184.4	1169.5	1167.9	1172.6	1167.9	1169.5	1184.4	1184.4	1187.5	1197.7	1202.5
17.5°	1127.3	1119.5	1119.9	1117.6	1119.9	1119.5	1127.3	1128.6	1131.1	1139.4	1145.7
20°	1097.1	1092.4	1091.6	1086.1	1091.6	1092.4	1097.1	1097.1	1100.3	1104.2	1110.5
22.5°	1069.5	1067.9	1068.4	1062.3	1068.4	1067.9	1069.5	1071.4	1074.5	1077.2	1081.6
25°	1035.1	1039.0	1035.8	1035.8	1035.8	1039.0	1035.1	1035.8	1036.6	1040.6	1043.7
27.5°	1011.8	1011.6	1010.1	1010.1	1010.1	1011.6	1011.8	1009.9	1009.0	1007.6	1006.9
30°	994.2	993.4	995.0	995.0	995.0	993.4	994.2	991.0	989.5	988.7	985.5
32.5°	976.6	977.7	978.0	978.6	978.0	977.7	976.6	972.8	970.0	967.9	965.4
35°	949.4	950.2	952.5	951.0	952.5	950.2	949.4	944.7	941.5	936.8	932.9
37.5°	912.6	916.2	915.4	916.7	915.4	916.2	912.6	911.2	908.1	904.4	899.9
40°	884.9	887.3	886.5	886.5	886.5	887.3	884.9	884.2	881.0	878.7	874.7
42.5°	856.7	858.4	856.3	855.1	856.3	858.4	856.7	855.2	853.4	849.1	844.6
45°	810.3	808.7	811.1	807.9	811.1	808.7	810.3	807.1	806.4	803.2	799.3
47.5°	758.4	760.0	760.6	763.0	760.6	760.0	758.4	758.7	754.3	752.4	751.2
50°	723.8	728.5	728.5	727.8	728.5	728.5	723.8	722.3	719.1	716.0	716.0
52.5°	689.9	692.1	695.2	695.1	695.2	692.1	689.9	687.1	683.9	679.5	678.3
55°	637.4	639.0	640.5	641.3	640.5	639.0	637.4	631.1	628.7	626.4	622.4
57.5°	583.0	582.4	586.1	587.2	586.1	582.4	583.0	577.3	573.7	566.5	565.5
60°	544.6	544.6	550.9	553.3	550.9	544.6	544.6	538.4	532.9	528.1	526.6
62.5°	503.8	506.3	512.6	509.3	512.6	506.3	503.8	496.9	492.6	486.6	482.6
65°	444.0	450.3	449.5	452.7	449.5	450.3	444.0	440.1	431.5	426.0	421.3
67.5°	381.6	385.6	391.2	391.7	391.2	385.6	381.6	375.4	369.7	363.9	358.2
70°	339.5	343.4	346.6	348.9	346.6	343.4	339.5	333.2	326.9	323.0	316.7
72.5°	298.7	300.7	308.2	304.9	308.2	300.7	298.7	291.1	286.1	282.8	275.9
75°	234.2	239.7	244.4	242.1	244.4	239.7	234.2	228.7	224.8	220.1	213.8
77.5°	173.2	178.7	180.9	178.9	180.9	178.7	173.2	169.6	167.6	158.3	157.7
80°	136.8	136.0	140.7	139.9	140.7	136.0	136.8	131.2	127.3	121.8	121.8
82.5°	100.3	99.5	101.7	102.2	101.7	99.5	100.3	97.3	92.1	89.8	87.9
85°	48.7	51.1	47.9	47.2	47.9	51.1	48.7	45.6	45.6	45.6	44.8
87.5°	15.7	15.9	15.4	14.6	15.4	15.9	15.7	15.9	18.1	16.0	15.9
90°	21.9	22.7	23.5	22.7	23.5	22.7	21.9	22.7	21.1	20.3	19.5
92.5°	40.7	38.3	39.1	37.7	39.1	38.3	40.7	42.1	46.1	52.2	65.8
95°	106.3	99.3	93.8	90.7	93.8	99.3	106.3	121.2	149.3	190.8	281.5
97.5°	309.9	274.7	253.6	246.9	253.6	274.7	309.9	367.6	461.1	562.0	701.6
100°	577.0	519.9	489.4	490.2	489.4	519.9	577.0	655.9	767.0	858.4	921.8
102.5°	807.8	762.6	737.1	719.1	737.1	762.6	807.8	869.2	939.6	992.9	994.9
105°	1053.1	1023.4	998.4	994.5	998.4	1023.4	1053.1	1089.1	1109.4	1094.5	1016.4
107.5°	1178.7	1168.7	1160.2	1153.0	1160.2	1168.7	1178.7	1178.0	1150.2	1081.7	954.8
110°	1214.9	1221.2	1219.6	1218.1	1219.6	1221.2	1214.9	1193.1	1138.3	1039.8	896.0



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1205.6	1225.0	1230.9	1231.2	1230.9	1225.0	1205.6	1165.5	1095.2	984.8	837.8
115°	1155.5	1189.9	1205.6	1209.5	1205.6	1189.9	1155.5	1096.9	1011.7	896.7	760.7
117.5°	1073.1	1112.5	1135.0	1140.4	1135.0	1112.5	1073.1	1012.0	925.5	822.3	704.9
120°	1015.6	1059.4	1078.1	1082.8	1078.1	1059.4	1015.6	953.8	874.9	781.0	675.5
122.5°	963.0	1002.4	1023.1	1029.0	1023.1	1002.4	963.0	908.2	834.8	747.9	652.4
125°	894.4	928.8	948.3	953.8	948.3	928.8	894.4	844.4	781.8	706.8	621.5
127.5°	839.8	869.2	886.9	891.9	886.9	869.2	839.8	795.3	738.4	670.6	594.7
130°	806.1	834.2	850.6	856.9	850.6	834.2	806.1	764.6	711.5	648.1	577.8
132.5°	775.4	803.6	818.1	822.5	818.1	803.6	775.4	736.5	685.8	626.9	562.1
135°	730.2	753.7	767.7	773.2	767.7	753.7	730.2	691.9	647.3	596.5	541.0
137.5°	681.9	705.7	717.6	721.2	717.6	705.7	681.9	649.7	611.1	567.3	521.8
140°	651.3	673.1	685.7	684.9	685.7	673.1	651.3	621.5	587.9	550.4	510.5
142.5°	621.2	640.6	651.9	651.1	651.9	640.6	621.2	595.9	566.7	534.1	499.9
145°	580.1	596.5	602.8	604.3	602.8	596.5	580.1	560.6	537.9	512.9	487.1
147.5°	548.2	559.3	565.3	565.9	565.3	559.3	548.2	533.4	517.3	497.1	476.6
150°	530.1	538.7	543.4	543.4	543.4	538.7	530.1	518.3	503.5	487.1	469.1
152.5°	513.8	521.8	524.6	524.6	524.6	521.8	513.8	504.6	492.2	477.7	462.2
155°	492.5	498.8	500.4	501.1	500.4	498.8	492.5	485.5	476.1	464.4	451.9
157.5°	473.9	478.6	479.9	479.7	479.9	478.6	473.9	467.8	460.5	451.4	440.9
160°	462.1	466.7	466.7	466.0	466.7	466.7	462.1	456.6	451.1	443.3	434.7
162.5°	450.2	454.2	454.2	453.5	454.2	454.2	450.2	446.6	441.7	434.5	427.2
165°	434.7	437.8	437.0	437.0	437.0	437.8	434.7	431.6	427.7	422.2	417.5
167.5°	420.0	422.2	421.4	421.4	421.4	422.2	420.0	418.6	415.8	412.6	409.0
170°	411.2	412.8	412.0	412.0	412.0	412.8	411.2	410.5	408.9	405.8	403.4
172.5°	403.7	405.3	403.9	403.3	403.9	405.3	403.7	403.6	402.6	400.1	398.4
175°	394.0	394.8	394.0	393.3	394.0	394.8	394.0	394.0	394.0	392.5	391.7
177.5°	388.1	388.7	387.5	387.5	387.5	388.7	388.1	388.7	388.7	388.1	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1555.5	1555.5	1567.4	1575.0	1584.4	1590.7	1595.1	1599.5	1607.1	1617.1	1628.4
5°	1466.5	1469.7	1487.0	1504.3	1520.8	1534.9	1546.7	1560.8	1578.1	1599.3	1622.9
7.5°	1380.4	1392.5	1409.9	1431.0	1454.1	1474.7	1495.6	1518.9	1543.2	1574.5	1607.5
10°	1325.1	1338.4	1359.6	1386.4	1410.7	1435.1	1461.0	1486.2	1516.8	1553.8	1596.2
12.5°	1276.7	1289.4	1311.2	1340.5	1363.6	1390.5	1420.2	1452.9	1487.3	1531.8	1579.9
15°	1209.5	1224.5	1251.2	1265.3	1300.7	1332.9	1360.4	1407.6	1451.6	1497.2	1553.0
17.5°	1154.5	1162.8	1184.5	1210.8	1237.2	1273.3	1309.3	1348.6	1392.5	1448.3	1518.1
20°	1116.8	1123.9	1147.4	1175.0	1203.2	1236.3	1268.5	1307.8	1357.3	1416.2	1491.7
22.5°	1088.5	1096.2	1111.6	1141.0	1167.4	1194.8	1227.0	1273.8	1326.5	1384.2	1465.9
25°	1047.6	1052.3	1062.6	1086.1	1109.7	1140.4	1168.7	1212.7	1266.9	1334.5	1416.2
27.5°	1008.8	1013.4	1021.9	1038.8	1060.8	1085.7	1116.5	1153.9	1208.9	1282.3	1369.1
30°	985.5	986.3	994.2	1009.9	1028.8	1049.2	1077.5	1119.9	1171.8	1246.5	1337.6
32.5°	965.4	962.4	967.8	979.7	998.0	1018.4	1041.7	1083.5	1133.5	1206.9	1300.5
35°	931.3	929.7	927.4	937.6	953.3	969.0	989.5	1020.9	1077.5	1145.9	1244.1
37.5°	896.6	892.8	888.6	893.3	905.5	921.9	939.6	967.6	1016.4	1091.6	1185.6
40°	870.8	867.7	865.3	863.7	874.7	890.4	903.8	930.5	976.1	1047.6	1140.4
42.5°	842.5	840.6	837.6	835.4	844.6	856.5	870.5	894.1	939.6	1006.8	1094.5
45°	796.9	795.4	793.8	792.2	797.7	808.7	819.7	837.0	876.3	941.5	1020.9
47.5°	746.2	744.1	744.7	742.2	747.6	755.0	762.7	781.2	818.9	871.6	929.6
50°	709.7	708.9	708.9	708.9	710.5	719.1	726.2	740.3	774.9	827.6	869.2
52.5°	675.1	671.8	671.8	673.1	675.9	681.4	686.0	701.4	731.5	774.8	812.6
55°	620.9	614.6	613.0	614.6	616.9	621.7	626.4	639.0	664.9	697.1	719.1
57.5°	560.8	557.4	555.3	555.6	556.9	560.7	564.3	578.0	598.4	615.2	629.4
60°	518.7	520.3	513.2	514.8	514.8	517.9	523.4	532.1	549.4	561.1	575.3
62.5°	479.1	476.9	474.9	472.7	472.7	473.9	481.3	488.1	502.8	509.0	520.0
65°	417.3	417.3	412.6	414.2	415.0	409.5	413.4	421.3	430.7	433.0	443.3
67.5°	354.8	352.6	349.9	347.5	347.5	347.1	349.1	353.0	360.1	360.9	368.8
70°	312.0	310.4	309.7	307.3	304.2	308.1	305.7	309.7	313.6	314.4	319.1
72.5°	270.5	268.9	267.5	265.2	263.9	263.4	263.6	268.2	270.8	269.7	275.1
75°	211.4	209.8	208.3	204.3	204.3	202.0	202.8	205.9	209.1	206.7	211.4
77.5°	155.3	150.4	150.1	151.2	148.5	149.0	148.1	147.6	149.0	149.2	153.4
80°	119.5	114.0	115.5	114.7	114.0	113.2	111.6	112.4	113.2	114.0	116.3
82.5°	86.1	85.7	84.1	83.9	83.2	81.1	80.2	81.6	82.4	81.9	83.6
85°	44.0	41.7	43.2	42.4	43.2	42.4	40.1	40.1	41.7	40.9	42.4
87.5°	17.0	17.1	16.0	16.2	15.1	15.2	14.3	14.6	14.8	14.5	15.4
90°	18.8	19.5	17.2	14.9	12.5	10.2	8.6	7.0	4.7	3.1	1.6
92.5°	90.7	120.2	132.3	99.3	65.7	45.2	33.6	27.1	21.0	14.4	9.7
95°	376.1	463.6	412.8	284.6	168.1	101.6	71.1	50.8	37.5	28.9	26.6
97.5°	768.7	718.5	526.0	312.3	180.9	117.4	84.4	64.4	52.9	46.1	45.3
100°	894.4	740.4	500.4	294.7	179.0	124.3	93.8	75.1	64.1	58.6	57.9
102.5°	900.7	699.7	462.8	279.7	181.5	132.4	104.5	87.6	77.2	72.4	71.0
105°	853.0	628.6	416.7	268.9	188.4	146.2	122.0	107.1	97.7	93.0	90.7
107.5°	769.5	565.7	387.3	268.2	201.2	164.2	141.7	127.7	118.5	114.0	111.6
110°	716.9	530.1	376.1	271.3	211.9	176.7	154.8	141.5	132.9	129.0	126.7



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	671.3	506.3	369.8	277.5	222.5	189.8	168.6	155.3	146.7	142.8	140.4
115°	616.1	480.8	367.5	287.7	240.0	210.3	189.2	175.9	168.1	163.4	160.3
117.5°	582.8	465.8	368.9	301.2	258.6	229.2	209.7	194.8	187.6	183.7	180.1
120°	565.3	458.9	371.4	311.2	270.5	242.4	222.8	208.0	200.1	196.2	193.9
122.5°	550.9	454.6	375.7	320.5	283.0	255.5	234.7	220.5	212.0	208.1	205.8
125°	532.4	448.8	382.3	335.4	301.0	273.6	252.5	237.7	229.1	224.4	222.8
127.5°	516.2	446.0	389.8	347.6	316.6	290.2	269.1	252.7	243.9	238.1	235.8
130°	507.4	444.1	394.8	355.7	326.0	300.2	279.1	262.7	253.3	246.3	243.9
132.5°	499.3	443.4	398.6	363.2	334.1	309.0	288.5	272.1	260.8	253.2	250.2
135°	488.6	442.5	404.2	372.9	346.3	322.1	301.0	284.6	272.9	264.3	261.1
137.5°	479.4	440.8	408.0	380.1	354.8	331.5	311.9	295.7	283.2	274.7	271.4
140°	473.8	440.2	410.5	383.9	360.4	337.7	318.2	302.6	290.1	282.2	278.3
142.5°	468.8	438.9	412.3	387.6	364.8	342.7	324.5	308.8	297.6	289.1	285.8
145°	462.1	437.0	413.6	391.7	370.6	350.3	332.3	319.0	307.3	300.2	297.9
147.5°	455.5	434.1	413.6	394.2	375.3	356.7	341.3	328.5	318.4	311.5	310.1
150°	451.1	431.6	413.6	394.8	378.4	360.4	346.3	335.4	325.2	319.0	318.2
152.5°	446.1	428.4	411.7	396.1	380.3	364.8	351.3	341.7	332.7	326.5	326.3
155°	438.6	423.0	409.7	396.4	383.9	370.6	359.6	351.0	343.2	338.5	338.5
157.5°	430.2	418.1	407.0	397.2	385.9	375.3	366.8	359.5	352.6	348.8	348.2
160°	424.5	414.4	405.8	397.2	387.8	378.4	370.6	365.1	358.9	355.7	355.7
162.5°	418.9	410.6	403.3	396.5	388.4	380.3	373.7	368.9	363.9	361.4	361.4
165°	411.2	405.0	399.5	394.8	389.3	383.1	377.6	374.5	370.6	369.0	369.8
167.5°	403.9	399.4	395.8	393.6	389.2	384.7	381.2	379.0	376.1	375.3	376.2
170°	399.5	395.6	393.3	391.7	388.6	384.7	383.1	381.5	379.2	378.4	380.0
172.5°	395.1	392.5	391.4	391.1	388.6	385.3	384.3	383.4	381.7	381.5	382.5
175°	390.1	388.6	388.6	389.3	387.8	386.2	385.4	385.4	383.9	384.7	385.4
177.5°	386.8	386.2	386.8	388.1	386.8	386.2	386.2	386.2	385.6	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1632.2	1635.3	1646.0	1653.6	1662.4	1667.4	1672.4	1676.2	1681.2	1682.5	1700.7
5°	1639.4	1655.2	1682.7	1703.1	1728.2	1755.7	1774.6	1783.3	1806.0	1824.9	1862.6
7.5°	1637.4	1670.9	1712.4	1755.4	1801.6	1844.4	1881.5	1925.5	1956.8	2003.8	2050.2
10°	1635.5	1680.3	1733.7	1788.8	1853.2	1912.9	1966.4	2026.1	2075.6	2140.8	2196.6
12.5°	1629.8	1684.1	1758.3	1823.3	1901.6	1984.0	2063.2	2139.9	2183.8	2292.4	2343.8
15°	1615.9	1680.3	1773.0	1872.1	1979.7	2077.2	2177.8	2258.0	2387.6	2482.7	2543.2
17.5°	1589.1	1679.4	1789.4	1908.8	2039.8	2168.2	2282.2	2403.8	2541.4	2656.4	2779.0
20°	1576.6	1675.6	1798.2	1930.2	2066.2	2211.6	2341.3	2487.4	2637.6	2750.7	2907.9
22.5°	1553.3	1665.5	1797.6	1944.7	2090.1	2240.5	2392.2	2539.6	2713.0	2868.9	3018.6
25°	1515.3	1641.0	1777.8	1942.0	2112.6	2263.5	2445.0	2640.7	2821.5	3021.9	3171.2
27.5°	1475.3	1609.6	1746.6	1899.4	2082.8	2261.9	2490.3	2711.4	2932.4	3105.5	3216.0
30°	1444.5	1575.0	1716.5	1870.5	2052.0	2265.0	2520.4	2761.7	2977.1	3125.6	3187.7
32.5°	1411.2	1543.5	1668.7	1830.3	2023.7	2263.1	2539.3	2791.3	2979.6	3078.5	3066.4
35°	1358.9	1469.7	1591.5	1747.1	1975.0	2249.3	2550.3	2793.9	2909.5	2888.3	2727.9
37.5°	1283.4	1376.6	1496.6	1666.9	1918.4	2220.2	2528.3	2711.1	2703.6	2530.8	2298.5
40°	1236.3	1315.6	1431.2	1610.4	1874.4	2201.4	2493.7	2612.4	2511.8	2270.5	1992.3
42.5°	1174.6	1247.7	1363.3	1547.5	1826.0	2163.0	2427.7	2462.1	2265.3	1987.6	1732.6
45°	1079.1	1143.5	1263.0	1453.2	1753.4	2079.5	2266.6	2182.5	1917.6	1630.8	1436.7
47.5°	976.4	1043.4	1158.3	1353.7	1648.4	1954.0	2043.1	1864.2	1592.3	1359.6	1181.4
50°	911.7	976.1	1088.5	1285.8	1577.3	1850.8	1887.8	1656.7	1406.8	1202.5	1056.3
52.5°	846.3	907.0	1017.5	1215.3	1494.4	1731.4	1708.6	1473.1	1243.3	1069.2	954.4
55°	749.0	806.4	911.7	1097.1	1351.0	1538.8	1456.3	1231.5	1041.3	906.2	818.9
57.5°	661.9	716.9	807.8	975.3	1196.0	1325.1	1220.1	1030.7	879.4	775.4	710.3
60°	602.8	651.5	738.0	893.6	1085.4	1183.6	1079.9	912.5	785.1	701.8	643.7
62.5°	546.8	589.3	669.4	810.6	977.2	1059.7	954.7	813.1	704.7	630.8	581.4
65°	462.1	500.6	571.4	681.4	818.1	873.2	782.8	668.0	583.9	528.9	495.9
67.5°	384.8	417.5	478.6	565.2	665.8	705.9	637.1	548.3	484.9	440.7	414.5
70°	333.2	361.5	409.5	484.1	575.3	605.9	541.5	468.4	422.0	386.7	362.3
72.5°	289.8	310.6	354.1	411.8	487.9	512.3	467.3	403.0	359.8	333.2	313.9
75°	220.8	238.1	266.4	312.8	365.5	379.6	345.8	305.7	276.6	257.8	242.8
77.5°	159.2	172.0	192.4	221.0	257.5	270.2	248.8	222.1	200.9	188.1	179.8
80°	120.2	130.5	147.8	171.3	193.3	200.4	187.8	167.4	152.5	145.4	138.3
82.5°	88.8	94.6	105.0	121.0	136.1	144.5	133.8	121.5	113.5	107.0	104.4
85°	44.8	47.9	52.7	58.9	68.4	71.5	67.6	64.4	59.7	55.8	55.8
87.5°	17.0	17.3	19.6	21.2	24.0	26.4	26.2	25.4	25.3	24.5	24.0
90°	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8	19.5
92.5°	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7	65.8
95°	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1	281.5
97.5°	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7	701.6
100°	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4	921.8
102.5°	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7	994.9
105°	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0	1016.4
107.5°	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5	954.8
110°	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9	896.0





TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3	837.8
115°	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1	760.7
117.5°	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8	704.9
120°	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3	675.5
122.5°	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9	652.4
125°	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4	621.5
127.5°	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2	594.7
130°	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4	577.8
132.5°	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3	562.1
135°	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6	541.0
137.5°	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4	521.8
140°	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8	510.5
142.5°	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8	499.9
145°	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1	487.1
147.5°	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5	476.6
150°	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1	469.1
152.5°	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1	462.2
155°	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6	451.9
157.5°	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2	440.9
160°	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5	434.7
162.5°	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9	427.2
165°	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2	417.5
167.5°	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9	409.0
170°	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5	403.4
172.5°	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1	398.4
175°	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1	391.7
177.5°	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1	1622.1
2.5°	1707.0	1707.6	1714.6	1719.6	1717.1	1720.2	1721.5
5°	1865.0	1893.3	1908.2	1919.2	1920.0	1920.8	1927.1
7.5°	2089.0	2119.3	2141.5	2175.1	2185.2	2196.6	2193.3
10°	2252.5	2297.2	2335.8	2356.2	2378.2	2410.4	2384.5
12.5°	2405.2	2484.6	2543.2	2575.0	2595.7	2602.2	2589.5
15°	2657.2	2760.9	2816.7	2815.2	2885.9	2916.6	2868.6
17.5°	2888.3	2984.0	3060.7	3100.0	3158.9	3172.0	3166.0
20°	3029.7	3134.3	3194.0	3261.6	3292.2	3319.7	3324.4
22.5°	3151.7	3245.5	3309.7	3365.9	3391.6	3404.6	3412.5
25°	3277.3	3351.2	3389.7	3409.3	3416.4	3414.8	3404.6
27.5°	3268.6	3274.3	3231.9	3190.2	3153.0	3111.0	3096.5
30°	3183.8	3117.7	2999.9	2933.1	2834.8	2757.0	2788.4
32.5°	2960.6	2829.2	2696.8	2550.8	2429.9	2395.5	2360.9
35°	2526.7	2295.7	2160.5	2003.3	1940.4	1877.6	1834.3
37.5°	2044.2	1865.5	1705.1	1602.3	1539.3	1499.5	1478.2
40°	1767.5	1606.4	1474.4	1391.1	1343.1	1298.3	1292.1
42.5°	1546.9	1397.1	1297.7	1231.4	1185.3	1166.3	1152.5
45°	1266.9	1162.4	1095.6	1048.4	1017.8	1006.0	990.3
47.5°	1072.3	998.4	948.3	916.2	893.1	884.3	883.1
50°	963.5	902.2	865.3	840.1	822.1	818.9	806.4
52.5°	881.8	828.7	799.9	777.9	764.9	756.1	752.3
55°	765.5	730.1	704.2	691.6	681.4	672.7	672.7
57.5°	669.8	640.2	623.1	612.4	609.2	603.1	599.2
60°	610.7	585.5	572.2	562.7	556.4	557.2	550.1
62.5°	552.8	536.5	523.7	514.3	506.8	506.9	507.4
65°	470.8	458.2	448.8	445.6	440.9	435.4	437.0
67.5°	398.9	387.1	379.8	374.4	372.8	369.9	374.4
70°	347.4	338.7	333.2	328.5	326.9	327.7	331.7
72.5°	300.2	294.1	290.5	288.3	284.8	285.0	287.6
75°	235.8	231.1	227.9	225.6	224.8	224.8	224.8
77.5°	173.2	172.1	170.7	167.2	167.4	168.3	168.5
80°	136.8	134.4	133.6	132.0	129.7	128.1	132.0
82.5°	102.2	99.8	99.0	98.7	95.1	94.8	98.1
85°	55.0	52.7	53.4	52.7	52.7	51.9	51.9
87.5°	23.6	23.1	22.8	23.2	22.8	22.3	23.4
90°	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P332065

CATALOG NUMBER: S123DIP-S1165D805U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)