

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331893

Luminaire Tested: **S123DIP-S340D1025U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331893  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1025U835-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4975.8 lumens  
Efficiency: N/A  
Efficacy: 133.4 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16				
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14				
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10				
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11	9				
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	1.0
10°-20°	151.9	3.1
20°-30°	254.9	5.1
30°-40°	288.6	5.8
40°-50°	258.8	5.2
50°-60°	208.9	4.2
60°-70°	145.6	2.9
70°-80°	76.5	1.5
80°-90°	22.5	0.5
90°-100°	82.8	1.7
100°-110°	247.8	5.0
110°-120°	421.4	8.5
120°-130°	554.3	11.1
130°-140°	623.0	12.5
140°-150°	612.4	12.3
150°-160°	515.6	10.4
160°-170°	343.2	6.9
170°-180°	120.2	2.4
0°-30°	454.2	9.1
0°-40°	742.8	14.9
0°-60°	1210.5	24.3
0°-90°	1455.0	29.2
90°-120°	752.0	15.1
90°-150°	2541.8	51.1
90°-180°	3521.0	70.8
0°-180°	4975.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	30	1	30	1	30	15
95°	78	59	78	59	78	80
105°	238	225	238	225	238	252
115°	425	424	425	424	425	421
125°	614	621	614	621	614	549
135°	805	806	805	806	805	619
145°	977	977	977	977	977	610
155°	1117	1119	1117	1119	1117	514
165°	1215	1219	1215	1219	1215	343
175°	1263	1268	1263	1268	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	11.6	11.1	11.2	11.3	11.0	11.1	11.1	11.1	11.1	11.1	10.7
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	40.3	40.6	40.9	41.1	41.4	41.2	40.5	39.8	39.0	38.3	36.7
95°	77.9	77.9	77.9	77.9	77.9	77.4	76.5	75.6	74.8	73.9	72.1
97.5°	119.8	119.9	120.0	120.1	120.1	119.7	118.7	117.6	116.6	115.6	114.3
100°	151.7	151.3	150.8	150.4	150.0	149.4	148.7	148.1	147.4	146.7	145.6
102.5°	184.5	184.6	184.6	184.7	184.8	184.5	183.9	183.2	182.5	181.9	180.4
105°	237.6	237.1	236.7	236.2	235.8	235.6	235.6	235.6	235.6	235.6	233.6
107.5°	292.9	293.1	293.4	293.7	293.9	293.7	293.0	292.3	291.6	290.9	290.1
110°	330.4	330.9	331.3	331.7	332.2	332.0	331.1	330.2	329.3	328.4	328.0



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	370.3	370.4	370.5	370.6	370.7	370.2	369.1	368.1	367.0	365.9	365.9
115°	425.2	425.5	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2	425.7
117.5°	480.9	481.6	482.2	482.8	483.4	483.8	483.8	483.8	483.9	483.9	484.5
120°	520.1	520.5	521.0	521.4	521.8	522.2	522.4	522.6	522.8	523.1	524.2
122.5°	557.6	558.2	558.8	559.5	560.1	560.7	561.3	561.8	562.4	563.0	563.6
125°	613.9	614.8	615.7	616.6	617.4	618.3	619.2	620.1	621.0	621.9	622.3
127.5°	670.0	671.0	672.0	673.1	674.1	675.2	676.5	677.7	678.9	680.2	680.7
130°	706.7	708.3	709.8	711.4	712.9	714.2	715.0	715.9	716.8	717.7	718.4
132.5°	745.1	746.3	747.5	748.7	749.9	751.0	752.1	753.1	754.2	755.2	755.7
135°	804.6	805.0	805.4	805.9	806.3	807.0	807.9	808.8	809.7	810.5	810.8
137.5°	857.1	857.9	858.7	859.6	860.4	861.3	862.3	863.2	864.1	865.0	864.5
140°	891.4	893.0	894.5	896.1	897.6	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	926.5	927.7	928.9	930.1	931.3	932.0	932.3	932.5	932.7	932.9	932.5
145°	977.2	978.1	979.0	979.9	980.8	981.3	981.6	981.8	982.0	982.2	981.6
147.5°	1022.4	1023.7	1025.0	1026.4	1027.7	1028.4	1028.4	1028.4	1028.4	1028.4	1027.7
150°	1051.1	1052.4	1053.8	1055.1	1056.4	1057.1	1057.1	1057.1	1057.1	1057.1	1056.7
152.5°	1079.1	1080.2	1081.4	1082.5	1083.7	1084.1	1083.7	1083.4	1083.0	1082.7	1082.4
155°	1117.0	1118.5	1120.1	1121.7	1123.2	1123.5	1122.7	1121.8	1120.9	1120.0	1119.8
157.5°	1151.5	1152.8	1154.0	1155.3	1156.5	1156.7	1155.7	1154.8	1153.9	1152.9	1152.8
160°	1173.9	1174.8	1175.7	1176.6	1177.4	1177.3	1176.2	1175.1	1174.0	1172.9	1172.9
162.5°	1190.7	1192.1	1193.5	1194.9	1196.3	1196.5	1195.4	1194.3	1193.2	1192.1	1191.9
165°	1214.8	1216.4	1217.9	1219.5	1221.0	1221.1	1219.8	1218.5	1217.1	1215.8	1215.8
167.5°	1235.4	1236.8	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4	1235.2
170°	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8	1245.8
172.5°	1253.7	1255.3	1256.9	1258.4	1260.0	1260.0	1258.7	1257.3	1255.9	1254.5	1254.5
175°	1262.7	1264.3	1265.8	1267.4	1268.9	1269.1	1267.7	1266.4	1265.1	1263.7	1263.7
177.5°	1267.5	1268.8	1270.0	1271.3	1272.5	1272.6	1271.5	1270.5	1269.4	1268.3	1268.3
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	10.5	10.1	9.0	7.8	6.9	5.9	5.5	4.7	4.7	5.2	5.4
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	35.0	33.4	31.8	30.2	28.7	27.2	25.7	24.2	25.7	27.2	28.7
95°	70.3	68.5	66.8	65.1	63.6	62.0	60.4	58.9	60.4	62.0	63.6
97.5°	113.0	111.7	110.4	109.2	108.1	106.9	105.8	104.6	105.8	106.9	108.1
100°	144.5	143.4	142.3	141.1	139.7	138.4	137.1	135.8	137.1	138.4	139.7
102.5°	178.9	177.5	176.0	174.9	174.1	173.3	172.5	171.7	172.5	173.3	174.1
105°	231.6	229.6	227.6	226.4	225.9	225.5	225.0	224.6	225.0	225.5	225.9
107.5°	289.3	288.5	287.7	287.2	286.9	286.6	286.4	286.1	286.4	286.6	286.9
110°	327.5	327.1	326.6	326.2	325.7	325.3	324.9	324.4	324.9	325.3	325.7





TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	365.8	365.7	365.6	365.4	365.1	364.9	364.6	364.3	364.6	364.9	365.1
115°	426.1	426.6	427.0	426.9	426.2	425.6	424.9	424.2	424.9	425.6	426.2
117.5°	485.1	485.7	486.2	486.3	485.9	485.4	485.0	484.5	485.0	485.4	485.9
120°	525.3	526.4	527.5	527.4	526.1	524.7	523.4	522.1	523.4	524.7	526.1
122.5°	564.1	564.7	565.3	565.1	564.1	563.1	562.2	561.2	562.2	563.1	564.1
125°	622.8	623.2	623.7	623.5	622.9	622.2	621.6	620.9	621.6	622.2	622.9
127.5°	681.2	681.6	682.1	681.7	680.2	678.8	677.4	676.0	677.4	678.8	680.2
130°	719.0	719.7	720.4	719.8	718.0	716.3	714.5	712.7	714.5	716.3	718.0
132.5°	756.2	756.7	757.2	756.6	754.8	753.0	751.2	749.5	751.2	753.0	754.8
135°	811.0	811.2	811.4	810.9	809.5	808.2	806.9	805.6	806.9	808.2	809.5
137.5°	863.9	863.3	862.7	861.9	860.8	859.7	858.6	857.5	858.6	859.7	860.8
140°	898.9	898.7	898.5	897.8	896.7	895.6	894.5	893.4	894.5	895.6	896.7
142.5°	932.1	931.7	931.3	930.6	929.5	928.4	927.2	926.1	927.2	928.4	929.5
145°	980.9	980.2	979.6	979.0	978.6	978.1	977.7	977.2	977.7	978.1	978.6
147.5°	1027.1	1026.5	1025.9	1025.2	1024.4	1023.6	1022.8	1022.0	1022.8	1023.6	1024.4
150°	1056.2	1055.8	1055.3	1054.9	1054.4	1054.0	1053.6	1053.1	1053.6	1054.0	1054.4
152.5°	1082.1	1081.9	1081.6	1081.1	1080.5	1079.9	1079.3	1078.7	1079.3	1079.9	1080.5
155°	1119.5	1119.3	1119.1	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0
157.5°	1152.6	1152.4	1152.2	1152.3	1152.5	1152.8	1153.1	1153.3	1153.1	1152.8	1152.5
160°	1172.9	1172.9	1172.9	1173.1	1173.6	1174.0	1174.4	1174.9	1174.4	1174.0	1173.6
162.5°	1191.7	1191.5	1191.4	1191.6	1192.2	1192.8	1193.4	1194.1	1193.4	1192.8	1192.2
165°	1215.8	1215.8	1215.8	1216.2	1216.8	1217.5	1218.1	1218.8	1218.1	1217.5	1216.8
167.5°	1235.0	1234.9	1234.7	1235.0	1235.9	1236.8	1237.7	1238.6	1237.7	1236.8	1235.9
170°	1245.8	1245.8	1245.8	1246.2	1247.1	1248.0	1248.9	1249.8	1248.9	1248.0	1247.1
172.5°	1254.5	1254.5	1254.5	1255.0	1255.9	1256.8	1257.7	1258.5	1257.7	1256.8	1255.9
175°	1263.7	1263.7	1263.7	1264.2	1265.1	1265.9	1266.8	1267.7	1266.8	1265.9	1265.1
177.5°	1268.3	1268.3	1268.3	1268.7	1269.4	1270.1	1270.8	1271.5	1270.8	1270.1	1269.4
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	5.7	6.4	6.8	7.6	7.9	8.7	8.9	8.7	8.9	9.6	9.0
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	30.2	31.8	33.4	35.0	36.7	38.3	39.0	39.8	40.5	41.2	41.4
95°	65.1	66.8	68.5	70.3	72.1	73.9	74.8	75.6	76.5	77.4	77.9
97.5°	109.2	110.4	111.7	113.0	114.3	115.6	116.6	117.6	118.7	119.7	120.1
100°	141.1	142.3	143.4	144.5	145.6	146.7	147.4	148.1	148.7	149.4	150.0
102.5°	174.9	176.0	177.5	178.9	180.4	181.9	182.5	183.2	183.9	184.5	184.8
105°	226.4	227.6	229.6	231.6	233.6	235.6	235.6	235.6	235.6	235.6	235.8
107.5°	287.2	287.7	288.5	289.3	290.1	290.9	291.6	292.3	293.0	293.7	293.9
110°	326.2	326.6	327.1	327.5	328.0	328.4	329.3	330.2	331.1	332.0	332.2



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	365.4	365.6	365.7	365.8	365.9	365.9	367.0	368.1	369.1	370.2	370.7
115°	426.9	427.0	426.6	426.1	425.7	425.2	425.5	425.7	425.9	426.1	426.1
117.5°	486.3	486.2	485.7	485.1	484.5	483.9	483.9	483.8	483.8	483.8	483.4
120°	527.4	527.5	526.4	525.3	524.2	523.1	522.8	522.6	522.4	522.2	521.8
122.5°	565.1	565.3	564.7	564.1	563.6	563.0	562.4	561.8	561.3	560.7	560.1
125°	623.5	623.7	623.2	622.8	622.3	621.9	621.0	620.1	619.2	618.3	617.4
127.5°	681.7	682.1	681.6	681.2	680.7	680.2	678.9	677.7	676.5	675.2	674.1
130°	719.8	720.4	719.7	719.0	718.4	717.7	716.8	715.9	715.0	714.2	712.9
132.5°	756.6	757.2	756.7	756.2	755.7	755.2	754.2	753.1	752.1	751.0	749.9
135°	810.9	811.4	811.2	811.0	810.8	810.5	809.7	808.8	807.9	807.0	806.3
137.5°	861.9	862.7	863.3	863.9	864.5	865.0	864.1	863.2	862.3	861.3	860.4
140°	897.8	898.5	898.7	898.9	899.2	899.4	899.2	898.9	898.7	898.5	897.6
142.5°	930.6	931.3	931.7	932.1	932.5	932.9	932.7	932.5	932.3	932.0	931.3
145°	979.0	979.6	980.2	980.9	981.6	982.2	982.0	981.8	981.6	981.3	980.8
147.5°	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4	1028.4	1028.4	1028.4	1027.7
150°	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1	1057.1	1057.1	1057.1	1056.4
152.5°	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0	1083.4	1083.7	1084.1	1083.7
155°	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9	1121.8	1122.7	1123.5	1123.2
157.5°	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9	1154.8	1155.7	1156.7	1156.5
160°	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0	1175.1	1176.2	1177.3	1177.4
162.5°	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2	1194.3	1195.4	1196.5	1196.3
165°	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1	1218.5	1219.8	1221.1	1221.0
167.5°	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8	1238.1	1239.5	1240.9	1240.9
170°	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0
172.5°	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9	1257.3	1258.7	1260.0	1260.0
175°	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1	1266.4	1267.7	1269.1	1268.9
177.5°	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4	1270.5	1271.5	1272.6	1272.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	9.1	9.2	9.1	9.0	9.1	9.2	9.1	9.0	9.6	8.9	8.7
90°	28.6	29.1	29.5	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7
92.5°	41.1	40.9	40.6	40.3	40.6	40.9	41.1	41.4	41.2	40.5	39.8
95°	77.9	77.9	77.9	77.9	77.9	77.9	77.9	77.9	77.4	76.5	75.6
97.5°	120.1	120.0	119.9	119.8	119.9	120.0	120.1	120.1	119.7	118.7	117.6
100°	150.4	150.8	151.3	151.7	151.3	150.8	150.4	150.0	149.4	148.7	148.1
102.5°	184.7	184.6	184.6	184.5	184.6	184.6	184.7	184.8	184.5	183.9	183.2
105°	236.2	236.7	237.1	237.6	237.1	236.7	236.2	235.8	235.6	235.6	235.6
107.5°	293.7	293.4	293.1	292.9	293.1	293.4	293.7	293.9	293.7	293.0	292.3
110°	331.7	331.3	330.9	330.4	330.9	331.3	331.7	332.2	332.0	331.1	330.2



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	370.6	370.5	370.4	370.3	370.4	370.5	370.6	370.7	370.2	369.1	368.1
115°	425.9	425.7	425.5	425.2	425.5	425.7	425.9	426.1	426.1	425.9	425.7
117.5°	482.8	482.2	481.6	480.9	481.6	482.2	482.8	483.4	483.8	483.8	483.8
120°	521.4	521.0	520.5	520.1	520.5	521.0	521.4	521.8	522.2	522.4	522.6
122.5°	559.5	558.8	558.2	557.6	558.2	558.8	559.5	560.1	560.7	561.3	561.8
125°	616.6	615.7	614.8	613.9	614.8	615.7	616.6	617.4	618.3	619.2	620.1
127.5°	673.1	672.0	671.0	670.0	671.0	672.0	673.1	674.1	675.2	676.5	677.7
130°	711.4	709.8	708.3	706.7	708.3	709.8	711.4	712.9	714.2	715.0	715.9
132.5°	748.7	747.5	746.3	745.1	746.3	747.5	748.7	749.9	751.0	752.1	753.1
135°	805.9	805.4	805.0	804.6	805.0	805.4	805.9	806.3	807.0	807.9	808.8
137.5°	859.6	858.7	857.9	857.1	857.9	858.7	859.6	860.4	861.3	862.3	863.2
140°	896.1	894.5	893.0	891.4	893.0	894.5	896.1	897.6	898.5	898.7	898.9
142.5°	930.1	928.9	927.7	926.5	927.7	928.9	930.1	931.3	932.0	932.3	932.5
145°	979.9	979.0	978.1	977.2	978.1	979.0	979.9	980.8	981.3	981.6	981.8
147.5°	1026.4	1025.0	1023.7	1022.4	1023.7	1025.0	1026.4	1027.7	1028.4	1028.4	1028.4
150°	1055.1	1053.8	1052.4	1051.1	1052.4	1053.8	1055.1	1056.4	1057.1	1057.1	1057.1
152.5°	1082.5	1081.4	1080.2	1079.1	1080.2	1081.4	1082.5	1083.7	1084.1	1083.7	1083.4
155°	1121.7	1120.1	1118.5	1117.0	1118.5	1120.1	1121.7	1123.2	1123.5	1122.7	1121.8
157.5°	1155.3	1154.0	1152.8	1151.5	1152.8	1154.0	1155.3	1156.5	1156.7	1155.7	1154.8
160°	1176.6	1175.7	1174.8	1173.9	1174.8	1175.7	1176.6	1177.4	1177.3	1176.2	1175.1
162.5°	1194.9	1193.5	1192.1	1190.7	1192.1	1193.5	1194.9	1196.3	1196.5	1195.4	1194.3
165°	1219.5	1217.9	1216.4	1214.8	1216.4	1217.9	1219.5	1221.0	1221.1	1219.8	1218.5
167.5°	1239.5	1238.1	1236.8	1235.4	1236.8	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1
170°	1250.4	1248.9	1247.3	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9
172.5°	1258.4	1256.9	1255.3	1253.7	1255.3	1256.9	1258.4	1260.0	1260.0	1258.7	1257.3
175°	1267.4	1265.8	1264.3	1262.7	1264.3	1265.8	1267.4	1268.9	1269.1	1267.7	1266.4
177.5°	1271.3	1270.0	1268.8	1267.5	1268.8	1270.0	1271.3	1272.5	1272.6	1271.5	1270.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	8.9	8.7	7.9	7.6	6.8	6.4	5.7	5.4	5.2	4.7	4.7
90°	24.8	24.0	21.1	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0
92.5°	39.0	38.3	36.7	35.0	33.4	31.8	30.2	28.7	27.2	25.7	24.2
95°	74.8	73.9	72.1	70.3	68.5	66.8	65.1	63.6	62.0	60.4	58.9
97.5°	116.6	115.6	114.3	113.0	111.7	110.4	109.2	108.1	106.9	105.8	104.6
100°	147.4	146.7	145.6	144.5	143.4	142.3	141.1	139.7	138.4	137.1	135.8
102.5°	182.5	181.9	180.4	178.9	177.5	176.0	174.9	174.1	173.3	172.5	171.7
105°	235.6	235.6	233.6	231.6	229.6	227.6	226.4	225.9	225.5	225.0	224.6
107.5°	291.6	290.9	290.1	289.3	288.5	287.7	287.2	286.9	286.6	286.4	286.1
110°	329.3	328.4	328.0	327.5	327.1	326.6	326.2	325.7	325.3	324.9	324.4



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	367.0	365.9	365.9	365.8	365.7	365.6	365.4	365.1	364.9	364.6	364.3
115°	425.5	425.2	425.7	426.1	426.6	427.0	426.9	426.2	425.6	424.9	424.2
117.5°	483.9	483.9	484.5	485.1	485.7	486.2	486.3	485.9	485.4	485.0	484.5
120°	522.8	523.1	524.2	525.3	526.4	527.5	527.4	526.1	524.7	523.4	522.1
122.5°	562.4	563.0	563.6	564.1	564.7	565.3	565.1	564.1	563.1	562.2	561.2
125°	621.0	621.9	622.3	622.8	623.2	623.7	623.5	622.9	622.2	621.6	620.9
127.5°	678.9	680.2	680.7	681.2	681.6	682.1	681.7	680.2	678.8	677.4	676.0
130°	716.8	717.7	718.4	719.0	719.7	720.4	719.8	718.0	716.3	714.5	712.7
132.5°	754.2	755.2	755.7	756.2	756.7	757.2	756.6	754.8	753.0	751.2	749.5
135°	809.7	810.5	810.8	811.0	811.2	811.4	810.9	809.5	808.2	806.9	805.6
137.5°	864.1	865.0	864.5	863.9	863.3	862.7	861.9	860.8	859.7	858.6	857.5
140°	899.2	899.4	899.2	898.9	898.7	898.5	897.8	896.7	895.6	894.5	893.4
142.5°	932.7	932.9	932.5	932.1	931.7	931.3	930.6	929.5	928.4	927.2	926.1
145°	982.0	982.2	981.6	980.9	980.2	979.6	979.0	978.6	978.1	977.7	977.2
147.5°	1028.4	1028.4	1027.7	1027.1	1026.5	1025.9	1025.2	1024.4	1023.6	1022.8	1022.0
150°	1057.1	1057.1	1056.7	1056.2	1055.8	1055.3	1054.9	1054.4	1054.0	1053.6	1053.1
152.5°	1083.0	1082.7	1082.4	1082.1	1081.9	1081.6	1081.1	1080.5	1079.9	1079.3	1078.7
155°	1120.9	1120.0	1119.8	1119.5	1119.3	1119.1	1119.0	1119.0	1119.0	1119.0	1119.0
157.5°	1153.9	1152.9	1152.8	1152.6	1152.4	1152.2	1152.3	1152.5	1152.8	1153.1	1153.3
160°	1174.0	1172.9	1172.9	1172.9	1172.9	1172.9	1173.1	1173.6	1174.0	1174.4	1174.9
162.5°	1193.2	1192.1	1191.9	1191.7	1191.5	1191.4	1191.6	1192.2	1192.8	1193.4	1194.1
165°	1217.1	1215.8	1215.8	1215.8	1215.8	1215.8	1216.2	1216.8	1217.5	1218.1	1218.8
167.5°	1236.8	1235.4	1235.2	1235.0	1234.9	1234.7	1235.0	1235.9	1236.8	1237.7	1238.6
170°	1247.3	1245.8	1245.8	1245.8	1245.8	1245.8	1246.2	1247.1	1248.0	1248.9	1249.8
172.5°	1255.9	1254.5	1254.5	1254.5	1254.5	1254.5	1255.0	1255.9	1256.8	1257.7	1258.5
175°	1265.1	1263.7	1263.7	1263.7	1263.7	1263.7	1264.2	1265.1	1265.9	1266.8	1267.7
177.5°	1269.4	1268.3	1268.3	1268.3	1268.3	1268.3	1268.7	1269.4	1270.1	1270.8	1271.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.5	5.9	6.9	7.8	9.0	10.1	10.5	10.7	11.1	11.1	11.1
90°	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7
92.5°	25.7	27.2	28.7	30.2	31.8	33.4	35.0	36.7	38.3	39.0	39.8
95°	60.4	62.0	63.6	65.1	66.8	68.5	70.3	72.1	73.9	74.8	75.6
97.5°	105.8	106.9	108.1	109.2	110.4	111.7	113.0	114.3	115.6	116.6	117.6
100°	137.1	138.4	139.7	141.1	142.3	143.4	144.5	145.6	146.7	147.4	148.1
102.5°	172.5	173.3	174.1	174.9	176.0	177.5	178.9	180.4	181.9	182.5	183.2
105°	225.0	225.5	225.9	226.4	227.6	229.6	231.6	233.6	235.6	235.6	235.6
107.5°	286.4	286.6	286.9	287.2	287.7	288.5	289.3	290.1	290.9	291.6	292.3
110°	324.9	325.3	325.7	326.2	326.6	327.1	327.5	328.0	328.4	329.3	330.2





TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	364.6	364.9	365.1	365.4	365.6	365.7	365.8	365.9	365.9	367.0	368.1
115°	424.9	425.6	426.2	426.9	427.0	426.6	426.1	425.7	425.2	425.5	425.7
117.5°	485.0	485.4	485.9	486.3	486.2	485.7	485.1	484.5	483.9	483.9	483.8
120°	523.4	524.7	526.1	527.4	527.5	526.4	525.3	524.2	523.1	522.8	522.6
122.5°	562.2	563.1	564.1	565.1	565.3	564.7	564.1	563.6	563.0	562.4	561.8
125°	621.6	622.2	622.9	623.5	623.7	623.2	622.8	622.3	621.9	621.0	620.1
127.5°	677.4	678.8	680.2	681.7	682.1	681.6	681.2	680.7	680.2	678.9	677.7
130°	714.5	716.3	718.0	719.8	720.4	719.7	719.0	718.4	717.7	716.8	715.9
132.5°	751.2	753.0	754.8	756.6	757.2	756.7	756.2	755.7	755.2	754.2	753.1
135°	806.9	808.2	809.5	810.9	811.4	811.2	811.0	810.8	810.5	809.7	808.8
137.5°	858.6	859.7	860.8	861.9	862.7	863.3	863.9	864.5	865.0	864.1	863.2
140°	894.5	895.6	896.7	897.8	898.5	898.7	898.9	899.2	899.4	899.2	898.9
142.5°	927.2	928.4	929.5	930.6	931.3	931.7	932.1	932.5	932.9	932.7	932.5
145°	977.7	978.1	978.6	979.0	979.6	980.2	980.9	981.6	982.2	982.0	981.8
147.5°	1022.8	1023.6	1024.4	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4	1028.4
150°	1053.6	1054.0	1054.4	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1	1057.1
152.5°	1079.3	1079.9	1080.5	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0	1083.4
155°	1119.0	1119.0	1119.0	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9	1121.8
157.5°	1153.1	1152.8	1152.5	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9	1154.8
160°	1174.4	1174.0	1173.6	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0	1175.1
162.5°	1193.4	1192.8	1192.2	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2	1194.3
165°	1218.1	1217.5	1216.8	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1	1218.5
167.5°	1237.7	1236.8	1235.9	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8	1238.1
170°	1248.9	1248.0	1247.1	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3	1248.9
172.5°	1257.7	1256.8	1255.9	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9	1257.3
175°	1266.8	1265.9	1265.1	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1	1266.4
177.5°	1270.8	1270.1	1269.4	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4	1270.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	11.1	11.1	11.0	11.3	11.2	11.1	11.6
90°	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	40.5	41.2	41.4	41.1	40.9	40.6	40.3
95°	76.5	77.4	77.9	77.9	77.9	77.9	77.9
97.5°	118.7	119.7	120.1	120.1	120.0	119.9	119.8
100°	148.7	149.4	150.0	150.4	150.8	151.3	151.7
102.5°	183.9	184.5	184.8	184.7	184.6	184.6	184.5
105°	235.6	235.6	235.8	236.2	236.7	237.1	237.6
107.5°	293.0	293.7	293.9	293.7	293.4	293.1	292.9
110°	331.1	332.0	332.2	331.7	331.3	330.9	330.4



TEST NUMBER: P331893

CATALOG NUMBER: S123DIP-S340D1025U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.1	370.2	370.7	370.6	370.5	370.4	370.3
115°	425.9	426.1	426.1	425.9	425.7	425.5	425.2
117.5°	483.8	483.8	483.4	482.8	482.2	481.6	480.9
120°	522.4	522.2	521.8	521.4	521.0	520.5	520.1
122.5°	561.3	560.7	560.1	559.5	558.8	558.2	557.6
125°	619.2	618.3	617.4	616.6	615.7	614.8	613.9
127.5°	676.5	675.2	674.1	673.1	672.0	671.0	670.0
130°	715.0	714.2	712.9	711.4	709.8	708.3	706.7
132.5°	752.1	751.0	749.9	748.7	747.5	746.3	745.1
135°	807.9	807.0	806.3	805.9	805.4	805.0	804.6
137.5°	862.3	861.3	860.4	859.6	858.7	857.9	857.1
140°	898.7	898.5	897.6	896.1	894.5	893.0	891.4
142.5°	932.3	932.0	931.3	930.1	928.9	927.7	926.5
145°	981.6	981.3	980.8	979.9	979.0	978.1	977.2
147.5°	1028.4	1028.4	1027.7	1026.4	1025.0	1023.7	1022.4
150°	1057.1	1057.1	1056.4	1055.1	1053.8	1052.4	1051.1
152.5°	1083.7	1084.1	1083.7	1082.5	1081.4	1080.2	1079.1
155°	1122.7	1123.5	1123.2	1121.7	1120.1	1118.5	1117.0
157.5°	1155.7	1156.7	1156.5	1155.3	1154.0	1152.8	1151.5
160°	1176.2	1177.3	1177.4	1176.6	1175.7	1174.8	1173.9
162.5°	1195.4	1196.5	1196.3	1194.9	1193.5	1192.1	1190.7
165°	1219.8	1221.1	1221.0	1219.5	1217.9	1216.4	1214.8
167.5°	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4
170°	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8
172.5°	1258.7	1260.0	1260.0	1258.4	1256.9	1255.3	1253.7
175°	1267.7	1269.1	1268.9	1267.4	1265.8	1264.3	1262.7
177.5°	1271.5	1272.6	1272.5	1271.3	1270.0	1268.8	1267.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7

(END OF REPORT)