

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831133

Luminaire Tested: S123DIP-S1000D585U840-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831133
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D585U840-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6689.0 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 50.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70	
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	65	64	64	64	64	60	
2	94	87	81	76	89	83	77	73	74	70	67	67	64	61	60	57	55	55	55	55	52	
3	87	77	70	65	82	74	67	62	66	61	57	60	56	52	54	51	48	48	48	48	45	
4	80	69	62	56	75	66	59	54	60	54	50	54	50	46	49	45	42	42	42	42	39	
5	74	62	54	49	70	60	52	47	54	48	44	49	44	41	44	41	37	37	37	37	35	
6	68	57	49	43	65	54	47	42	49	43	39	45	40	36	41	37	34	34	34	34	31	
7	64	52	44	38	60	49	42	37	45	39	35	41	36	33	38	34	30	30	30	30	28	
8	60	47	40	34	56	45	38	33	42	36	32	38	33	30	35	31	28	28	28	28	26	
9	56	44	36	31	53	42	35	30	39	33	29	35	31	27	32	28	25	25	25	25	23	
10	52	40	33	29	50	39	32	28	36	30	26	33	28	25	30	26	23	23	23	23	22	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	31174	31174	31174	31174	31174
5°	39425	37211	31453	25348	23292
10°	39808	41013	31244	20205	17656
15°	29983	38078	31032	17111	14931
20°	20890	30812	30636	14963	13562
25°	15930	23695	29960	13767	12721
30°	13781	18825	28881	12920	12044
35°	12786	15895	27638	12309	11567
40°	12105	14258	25891	11727	11405
45°	11702	13195	23669	11272	11333
50°	11501	12355	21043	10860	11275
55°	11072	11740	18462	10466	11324
60°	10676	11080	15913	10097	11138
65°	10030	10458	13726	9704	10919
70°	9262	9665	11673	9051	10279
75°	8384	8663	10006	8413	9391
80°	6912	7581	7916	7333	7916
85°	5483	6138	5805	6225	6311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 27026 cd/sqm



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.8	4.1
10°-20°	681.2	10.2
20°-30°	806.5	12.1
30°-40°	811.0	12.1
40°-50°	744.0	11.1
50°-60°	614.1	9.2
60°-70°	434.4	6.5
70°-80°	231.9	3.5
80°-90°	60.4	0.9
90°-100°	47.2	0.7
100°-110°	142.9	2.1
110°-120°	243.2	3.6
120°-130°	320.0	4.8
130°-140°	359.7	5.4
140°-150°	353.6	5.3
150°-160°	297.7	4.5
160°-170°	198.2	3.0
170°-180°	69.4	1.0
0°-30°	1761.5	26.3
0°-40°	2572.5	38.5
0°-60°	3930.6	58.8
0°-90°	4657.3	69.6
90°-120°	433.3	6.5
90°-150°	1466.5	21.9
90°-180°	2032.0	30.4
0°-180°	6689.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2896	2896	2896	2896	2896	
5°	3649	3444	2911	2346	2156	348
15°	2691	3417	2785	1536	1340	743
25°	1341	1995	2523	1159	1071	633
35°	973	1210	2103	937	880	611
45°	769	867	1555	740	744	595
55°	590	626	984	558	603	528
65°	394	411	539	381	429	391
75°	202	208	241	202	226	212
85°	44	50	47	50	51	50
90°	17	14	1	14	17	11
95°	45	43	34	43	45	45
105°	137	136	130	136	137	145
115°	245	245	245	245	245	243
125°	354	359	358	359	354	317
135°	464	468	465	468	464	357
145°	564	567	564	567	564	352
155°	645	646	646	646	645	297
165°	701	702	703	702	701	198
175°	729	729	732	729	729	69
180°	733	733	733	733	733	

TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2
2.5°	3264.4	3261.1	3257.7	3240.9	3224.1	3216.1	3208.0	3183.8	3159.6	3132.7	3105.9
5°	3648.8	3658.2	3667.6	3656.9	3646.1	3613.2	3580.3	3536.6	3492.9	3443.9	3394.8
7.5°	3826.2	3831.6	3837.0	3830.2	3823.5	3814.8	3806.1	3767.1	3728.1	3677.7	3627.3
10°	3642.1	3654.2	3666.3	3692.5	3718.7	3748.3	3777.8	3772.5	3767.1	3752.3	3737.5
12.5°	3237.6	3252.4	3267.1	3319.5	3372.0	3439.2	3506.4	3564.1	3621.9	3662.3	3702.6
15°	2690.6	2731.6	2772.6	2820.3	2868.0	2966.8	3065.5	3187.2	3308.8	3417.0	3525.2
17.5°	2216.2	2231.6	2247.1	2298.1	2349.2	2473.5	2597.8	2738.3	2878.7	3058.2	3237.6
20°	1823.7	1837.8	1852.0	1919.2	1986.4	2083.8	2181.2	2339.1	2497.1	2689.9	2882.8
22.5°	1532.1	1554.3	1576.4	1614.1	1651.7	1745.1	1838.5	1979.0	2119.4	2332.4	2545.4
25°	1341.3	1357.4	1373.5	1396.4	1419.2	1493.8	1568.4	1684.0	1799.5	1995.1	2190.6
27.5°	1210.9	1217.6	1224.3	1247.2	1270.0	1318.4	1366.8	1466.2	1565.7	1731.7	1897.7
30°	1108.8	1113.5	1118.2	1138.3	1158.5	1191.4	1224.3	1296.2	1368.1	1514.6	1661.1
32.5°	1037.5	1040.9	1044.2	1059.7	1075.2	1098.7	1122.2	1174.6	1227.0	1348.0	1468.9
35°	973.0	975.0	977.0	988.5	999.9	1017.4	1034.8	1074.5	1114.1	1209.6	1305.0
37.5°	916.6	919.3	921.9	928.7	935.4	950.8	966.3	997.9	1029.5	1102.7	1176.0
40°	861.5	866.2	870.9	875.6	880.3	893.1	905.8	930.0	954.2	1014.7	1075.2
42.5°	814.4	819.1	823.8	825.9	827.9	835.3	842.7	864.8	887.0	932.0	977.0
45°	768.7	770.8	772.8	774.8	776.8	782.8	788.9	808.4	827.9	866.8	905.8
47.5°	727.1	727.1	727.1	728.4	729.8	735.1	740.5	754.6	768.7	799.0	829.2
50°	686.8	686.8	686.8	684.7	682.7	686.1	689.4	700.2	710.9	737.8	764.7
52.5°	638.4	638.4	638.4	639.0	639.7	639.7	639.7	649.1	658.5	682.7	706.9
55°	590.0	592.7	595.4	593.4	591.3	592.7	594.0	600.1	606.1	625.6	645.1
57.5°	541.6	543.0	544.3	543.6	543.0	543.6	544.3	549.7	555.0	569.8	584.6
60°	495.9	495.9	495.9	494.6	493.2	494.6	495.9	498.6	501.3	514.7	528.2
62.5°	444.8	445.5	446.2	446.9	447.5	446.2	444.8	448.2	451.6	461.6	471.7
65°	393.8	394.4	395.1	397.1	399.2	397.8	396.5	399.8	403.2	410.6	418.0
67.5°	348.1	346.7	345.4	346.1	346.7	348.8	350.8	351.4	352.1	360.2	368.2
70°	294.3	295.7	297.0	296.3	295.7	296.3	297.0	299.0	301.0	307.1	313.1
72.5°	245.9	246.6	247.3	247.3	247.3	248.6	250.0	252.0	254.0	257.4	260.7
75°	201.6	201.6	201.6	202.9	204.3	205.0	205.6	205.6	205.6	208.3	211.0
77.5°	153.2	156.6	159.9	159.3	158.6	159.9	161.3	163.3	165.3	166.6	168.0
80°	111.5	111.5	111.5	112.2	112.9	114.9	116.9	118.3	119.6	122.3	125.0
82.5°	71.2	71.9	72.6	74.6	76.6	77.9	79.3	81.3	83.3	83.3	83.3
85°	44.4	43.0	41.7	43.0	44.4	45.7	47.0	47.7	48.4	49.7	51.1
87.5°	21.5	21.5	21.5	21.5	21.5	22.2	22.8	22.8	22.8	22.8	22.8
90°	17.3	17.0	16.8	16.5	16.3	15.9	15.4	14.8	14.3	13.8	12.2
92.5°	24.8	25.0	25.3	25.5	25.8	25.7	25.3	25.0	24.6	24.2	23.4
95°	44.9	44.9	44.9	44.9	44.9	44.7	44.2	43.6	43.1	42.6	41.6
97.5°	64.5	64.6	64.8	64.9	65.0	64.8	64.1	63.5	62.8	62.2	61.4
100°	87.6	87.3	87.0	86.8	86.5	86.2	85.8	85.4	85.1	84.7	84.0
102.5°	111.2	111.3	111.4	111.6	111.7	111.6	111.2	110.8	110.4	110.0	109.1
105°	137.1	136.8	136.6	136.3	136.1	135.9	135.9	135.9	135.9	135.9	134.8
107.5°	163.6	163.7	163.8	164.0	164.1	164.0	163.6	163.2	162.8	162.4	161.9
110°	190.7	190.9	191.2	191.4	191.7	191.6	191.0	190.5	190.0	189.5	189.3



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.5	219.5	219.5	219.5	219.5	219.1	218.5	217.9	217.2	216.6	216.6
115°	245.4	245.5	245.6	245.8	245.9	245.9	245.8	245.6	245.5	245.4	245.6
117.5°	271.9	272.3	272.6	273.0	273.4	273.6	273.6	273.6	273.6	273.6	273.9
120°	300.1	300.4	300.6	300.9	301.1	301.3	301.4	301.6	301.7	301.8	302.5
122.5°	327.2	327.6	327.9	328.3	328.7	329.1	329.5	329.9	330.3	330.6	330.9
125°	354.3	354.8	355.3	355.8	356.3	356.8	357.3	357.8	358.3	358.9	359.1
127.5°	381.3	381.8	382.3	382.9	383.4	384.0	384.8	385.5	386.3	387.1	387.3
130°	407.8	408.7	409.6	410.5	411.4	412.1	412.6	413.1	413.6	414.2	414.5
132.5°	435.5	436.1	436.7	437.4	438.0	438.7	439.3	439.9	440.6	441.2	441.5
135°	464.3	464.5	464.8	465.0	465.3	465.7	466.2	466.7	467.2	467.7	467.9
137.5°	489.6	490.0	490.4	490.8	491.2	491.7	492.3	492.9	493.6	494.2	493.8
140°	514.4	515.3	516.2	517.1	518.0	518.5	518.6	518.7	518.9	519.0	518.9
142.5°	539.7	540.4	541.0	541.6	542.3	542.7	542.8	542.9	543.1	543.2	542.9
145°	563.9	564.4	564.9	565.5	566.0	566.3	566.4	566.5	566.7	566.8	566.4
147.5°	585.8	586.6	587.3	588.1	588.9	589.3	589.3	589.3	589.3	589.3	588.9
150°	606.5	607.3	608.1	608.9	609.6	610.0	610.0	610.0	610.0	610.0	609.7
152.5°	626.7	627.3	628.0	628.6	629.3	629.5	629.2	628.9	628.7	628.4	628.3
155°	644.6	645.5	646.4	647.3	648.1	648.3	647.8	647.3	646.8	646.3	646.2
157.5°	661.3	662.0	662.8	663.6	664.3	664.5	664.0	663.4	662.9	662.4	662.3
160°	677.4	677.9	678.4	678.9	679.4	679.4	678.7	678.1	677.5	676.8	676.8
162.5°	689.5	690.4	691.3	692.2	693.1	693.2	692.6	691.9	691.3	690.6	690.5
165°	701.0	701.9	702.8	703.7	704.6	704.7	703.9	703.1	702.4	701.6	701.6
167.5°	711.4	712.2	712.9	713.7	714.5	714.5	713.7	712.9	712.2	711.4	711.3
170°	718.9	719.8	720.7	721.6	722.5	722.5	721.6	720.7	719.8	718.9	718.9
172.5°	724.6	725.5	726.4	727.3	728.2	728.3	727.5	726.7	726.0	725.2	725.2
175°	728.7	729.6	730.5	731.4	732.2	732.3	731.5	730.8	730.0	729.2	729.2
177.5°	731.0	731.9	732.8	733.7	734.6	734.6	733.8	733.1	732.3	731.5	731.5
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2
2.5°	3097.8	3089.7	3060.2	3030.6	2997.0	2963.4	2938.5	2913.7	2876.7	2839.8	2809.5
5°	3357.2	3319.5	3257.1	3194.6	3109.9	3025.2	2968.1	2911.0	2834.4	2757.8	2696.6
7.5°	3562.8	3498.3	3410.9	3323.6	3212.7	3101.8	2997.0	2892.2	2775.2	2658.3	2562.9
10°	3693.8	3650.2	3549.4	3448.6	3300.1	3151.6	3005.1	2858.6	2708.1	2557.5	2431.2
12.5°	3706.6	3710.6	3617.9	3525.2	3357.2	3189.2	3011.1	2833.0	2643.5	2454.0	2306.9
15°	3594.4	3663.6	3612.5	3561.5	3392.1	3222.8	3003.7	2784.7	2566.3	2347.9	2177.9
17.5°	3386.1	3534.6	3542.0	3549.4	3380.0	3210.7	2968.1	2725.5	2478.2	2231.0	2052.2
20°	3101.8	3320.9	3396.2	3471.4	3333.7	3195.9	2935.2	2674.5	2397.6	2120.7	1933.3
22.5°	2811.5	3077.6	3215.4	3353.1	3251.0	3148.9	2871.3	2593.8	2301.5	2009.2	1819.0
25°	2480.9	2771.2	2982.9	3194.6	3132.1	3069.6	2796.1	2522.6	2211.5	1900.3	1706.1
27.5°	2192.6	2487.6	2743.0	2998.3	2984.9	2971.5	2700.0	2428.5	2110.0	1791.5	1604.0
30°	1936.0	2210.8	2496.4	2782.0	2814.9	2847.8	2585.8	2323.7	2004.5	1685.3	1504.5
32.5°	1708.8	1948.7	2255.1	2561.6	2626.1	2690.6	2454.0	2217.5	1901.7	1585.9	1411.8
35°	1522.7	1740.4	2046.8	2353.3	2433.9	2514.5	2308.9	2103.3	1795.5	1487.7	1321.8
37.5°	1358.1	1540.2	1839.2	2138.2	2237.0	2335.8	2151.7	1967.5	1679.3	1391.0	1238.4
40°	1221.6	1368.1	1643.0	1917.8	2032.0	2146.3	1994.4	1842.6	1569.1	1295.6	1155.1
42.5°	1107.4	1237.8	1487.1	1736.4	1845.9	1955.4	1827.1	1698.7	1455.5	1212.2	1083.9
45°	1010.0	1114.1	1340.6	1567.0	1671.2	1775.4	1665.1	1554.9	1340.6	1126.2	1006.6
47.5°	918.6	1008.0	1201.5	1395.0	1487.7	1580.5	1494.5	1408.5	1227.0	1045.6	937.4
50°	836.6	908.5	1077.8	1247.2	1327.8	1408.5	1332.5	1256.6	1107.4	958.2	864.2
52.5°	765.4	823.8	965.6	1107.4	1176.6	1245.8	1180.7	1115.5	997.2	878.9	797.0
55°	694.8	744.5	867.5	990.5	1037.5	1084.6	1034.2	983.8	888.3	792.9	723.7
57.5°	629.0	673.3	774.1	874.9	911.2	947.5	901.8	856.1	784.2	712.3	654.5
60°	564.5	600.7	684.7	768.7	790.9	813.1	776.1	739.2	688.8	638.4	586.6
62.5°	504.7	537.6	600.1	662.6	677.3	692.1	663.9	635.7	597.4	559.1	518.8
65°	442.8	467.7	518.8	569.8	579.2	588.6	563.8	538.9	510.0	481.1	451.6
67.5°	385.7	403.2	444.8	486.5	487.2	487.9	467.7	447.5	431.4	415.3	391.8
70°	329.9	346.7	374.3	401.8	402.5	403.2	387.1	370.9	358.8	346.7	329.3
72.5°	272.8	284.9	305.7	326.6	325.2	323.9	313.8	303.7	294.3	284.9	272.1
75°	221.1	231.2	245.3	259.4	255.3	251.3	245.9	240.6	232.5	224.4	216.4
77.5°	174.0	180.1	188.2	196.2	193.5	190.8	186.1	181.4	175.4	169.3	166.0
80°	127.7	130.4	135.7	141.1	139.8	138.4	133.1	127.7	126.3	125.0	120.3
82.5°	86.7	90.0	91.4	92.7	92.1	91.4	87.4	83.3	82.0	80.6	80.0
85°	51.7	52.4	53.1	53.8	51.7	49.7	48.4	47.0	47.0	47.0	46.4
87.5°	23.5	24.2	24.2	24.2	23.5	22.8	21.5	20.2	20.8	21.5	21.5
90°	10.5	8.8	7.2	5.7	4.4	3.1	1.9	0.6	1.9	3.1	4.4
92.5°	22.7	21.9	21.1	20.4	19.6	18.8	18.0	17.3	18.0	18.8	19.6
95°	40.6	39.6	38.5	37.6	36.7	35.8	34.9	34.0	34.9	35.8	36.7
97.5°	60.7	59.9	59.1	58.4	57.8	57.2	56.5	55.9	56.5	57.2	57.8
100°	83.4	82.8	82.1	81.4	80.6	79.9	79.1	78.3	79.1	79.9	80.6
102.5°	108.2	107.3	106.4	105.8	105.4	105.0	104.6	104.3	104.6	105.0	105.4
105°	133.6	132.5	131.3	130.6	130.4	130.1	129.9	129.6	129.9	130.1	130.4
107.5°	161.4	160.9	160.4	160.1	159.9	159.8	159.7	159.6	159.7	159.8	159.9
110°	189.0	188.7	188.5	188.2	188.0	187.7	187.5	187.2	187.5	187.7	188.0



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	216.6	216.6	216.6	216.5	216.4	216.3	216.1	216.0	216.1	216.3	216.4
115°	245.9	246.2	246.4	246.3	246.0	245.6	245.2	244.8	245.2	245.6	246.0
117.5°	274.1	274.4	274.6	274.7	274.6	274.4	274.3	274.2	274.3	274.4	274.6
120°	303.1	303.8	304.4	304.3	303.6	302.8	302.0	301.3	302.0	302.8	303.6
122.5°	331.1	331.4	331.7	331.5	331.0	330.5	330.0	329.5	330.0	330.5	331.0
125°	359.4	359.6	359.9	359.8	359.4	359.1	358.7	358.3	358.7	359.1	359.4
127.5°	387.6	387.9	388.1	387.9	387.1	386.3	385.5	384.8	385.5	386.3	387.1
130°	414.9	415.3	415.7	415.4	414.3	413.3	412.3	411.3	412.3	413.3	414.3
132.5°	441.7	442.0	442.3	441.9	440.8	439.8	438.8	437.8	438.8	439.8	440.8
135°	468.0	468.1	468.2	467.9	467.2	466.4	465.6	464.8	465.6	466.4	467.2
137.5°	493.5	493.1	492.7	492.2	491.5	490.9	490.3	489.6	490.3	490.9	491.5
140°	518.7	518.6	518.5	518.1	517.5	516.8	516.2	515.5	516.2	516.8	517.5
142.5°	542.7	542.4	542.2	541.7	541.1	540.4	539.8	539.2	539.8	540.4	541.1
145°	566.0	565.6	565.3	564.9	564.7	564.4	564.2	563.9	564.2	564.4	564.7
147.5°	588.5	588.1	587.7	587.3	586.8	586.3	585.7	585.2	585.7	586.3	586.8
150°	609.5	609.2	609.0	608.7	608.5	608.2	608.0	607.7	608.0	608.2	608.5
152.5°	628.2	628.1	627.9	627.7	627.3	626.9	626.5	626.1	626.5	626.9	627.3
155°	646.0	645.9	645.8	645.7	645.7	645.7	645.7	645.7	645.7	645.7	645.7
157.5°	662.2	662.0	661.9	661.9	662.0	662.2	662.3	662.4	662.3	662.2	662.0
160°	676.8	676.8	676.8	676.9	677.2	677.5	677.7	678.0	677.7	677.5	677.2
162.5°	690.4	690.3	690.1	690.3	690.6	691.0	691.4	691.8	691.4	691.0	690.6
165°	701.6	701.6	701.6	701.8	702.2	702.5	702.9	703.3	702.9	702.5	702.2
167.5°	711.1	711.0	710.9	711.1	711.6	712.1	712.6	713.1	712.6	712.1	711.6
170°	718.9	718.9	718.9	719.1	719.6	720.2	720.7	721.2	720.7	720.2	719.6
172.5°	725.2	725.2	725.2	725.5	726.0	726.5	727.0	727.5	727.0	726.5	726.0
175°	729.2	729.2	729.2	729.5	730.0	730.5	731.0	731.5	731.0	730.5	730.0
177.5°	731.5	731.5	731.5	731.8	732.3	732.8	733.3	733.8	733.3	732.8	732.3
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2	2896.2
2.5°	2779.3	2753.1	2726.9	2706.7	2686.5	2652.3	2618.0	2609.9	2601.9	2590.5	2579.0
5°	2635.5	2571.0	2506.5	2448.7	2390.9	2345.9	2300.8	2271.3	2241.7	2220.2	2198.7
7.5°	2467.5	2370.7	2274.0	2205.4	2136.9	2071.7	2006.5	1985.7	1964.8	1936.6	1908.4
10°	2304.9	2198.0	2091.2	2001.8	1912.4	1848.6	1784.8	1759.2	1733.7	1698.1	1662.5
12.5°	2159.7	2042.8	1925.9	1835.8	1745.8	1684.0	1622.1	1585.2	1548.2	1528.1	1507.9
15°	2007.9	1882.9	1757.9	1674.6	1591.2	1535.5	1479.7	1447.4	1415.2	1395.7	1376.2
17.5°	1873.5	1749.8	1626.2	1546.2	1466.2	1415.2	1364.1	1335.9	1307.7	1292.9	1278.1
20°	1745.8	1624.8	1503.9	1425.9	1348.0	1306.3	1264.7	1246.5	1228.4	1216.3	1204.2
22.5°	1628.9	1509.9	1391.0	1324.5	1257.9	1224.3	1190.7	1178.0	1165.2	1155.1	1145.0
25°	1511.9	1405.8	1299.6	1243.2	1186.7	1159.2	1131.6	1118.8	1106.1	1096.0	1085.9
27.5°	1416.5	1315.1	1213.6	1165.2	1116.8	1095.3	1073.8	1063.7	1053.7	1044.2	1034.8
30°	1323.8	1233.1	1142.4	1100.7	1059.0	1039.5	1020.1	1010.0	999.9	991.2	982.4
32.5°	1237.8	1159.8	1081.9	1043.6	1005.3	989.1	973.0	960.9	948.8	942.1	935.4
35°	1155.8	1085.9	1016.0	984.4	952.9	936.7	920.6	910.5	900.4	895.1	889.7
37.5°	1085.9	1023.4	960.9	930.7	900.4	885.0	869.5	860.8	852.1	850.0	848.0
40°	1014.7	960.9	907.2	877.6	848.0	834.6	821.2	815.8	810.4	809.1	807.7
42.5°	955.5	903.1	850.7	823.8	797.0	785.5	774.1	771.4	768.7	770.8	772.8
45°	887.0	843.3	799.6	774.8	749.9	740.5	731.1	729.1	727.1	731.1	735.1
47.5°	829.2	788.9	748.6	725.1	701.5	694.8	688.1	687.4	686.8	692.1	697.5
50°	770.1	731.1	692.1	673.3	654.5	648.5	642.4	644.4	646.4	655.2	663.9
52.5°	715.0	678.7	642.4	624.9	607.5	603.4	599.4	604.1	608.8	618.2	627.6
55°	654.5	621.6	588.6	575.2	561.8	557.7	553.7	563.1	572.5	581.3	590.0
57.5°	596.7	567.8	538.9	526.8	514.7	514.1	513.4	522.1	530.9	540.3	549.7
60°	534.9	510.7	486.5	477.1	467.7	469.0	470.4	480.5	490.5	497.9	505.3
62.5°	478.4	458.3	438.1	429.4	420.7	424.0	427.4	437.5	447.5	456.3	465.0
65°	422.0	405.2	388.4	382.4	376.3	381.0	385.7	394.4	403.2	409.2	415.3
67.5°	368.2	354.1	340.0	335.3	330.6	335.3	340.0	348.8	357.5	363.5	369.6
70°	311.8	300.4	288.9	285.6	282.2	287.6	293.0	300.4	307.8	313.8	319.9
72.5°	259.4	250.6	241.9	241.2	240.6	245.3	250.0	257.4	264.8	268.8	272.8
75°	208.3	203.6	198.9	198.2	197.6	202.3	207.0	211.0	215.0	218.4	221.8
77.5°	162.6	158.6	154.6	155.2	155.9	159.3	162.6	166.6	170.7	172.7	174.7
80°	115.6	114.2	112.9	114.2	115.6	118.3	121.0	123.6	126.3	127.7	129.0
82.5°	79.3	77.9	76.6	78.6	80.6	82.7	84.7	86.7	88.7	89.4	90.0
85°	45.7	47.7	49.7	49.7	49.7	50.4	51.1	51.7	52.4	51.7	51.1
87.5°	21.5	22.2	22.8	22.8	22.8	23.5	24.2	24.2	24.2	23.5	22.8
90°	5.7	7.2	8.8	10.5	12.2	13.8	14.3	14.8	15.4	15.9	16.3
92.5°	20.4	21.1	21.9	22.7	23.4	24.2	24.6	25.0	25.3	25.7	25.8
95°	37.6	38.5	39.6	40.6	41.6	42.6	43.1	43.6	44.2	44.7	44.9
97.5°	58.4	59.1	59.9	60.7	61.4	62.2	62.8	63.5	64.1	64.8	65.0
100°	81.4	82.1	82.8	83.4	84.0	84.7	85.1	85.4	85.8	86.2	86.5
102.5°	105.8	106.4	107.3	108.2	109.1	110.0	110.4	110.8	111.2	111.6	111.7
105°	130.6	131.3	132.5	133.6	134.8	135.9	135.9	135.9	135.9	135.9	136.1
107.5°	160.1	160.4	160.9	161.4	161.9	162.4	162.8	163.2	163.6	164.0	164.1
110°	188.2	188.5	188.7	189.0	189.3	189.5	190.0	190.5	191.0	191.6	191.7



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	216.5	216.6	216.6	216.6	216.6	216.6	217.2	217.9	218.5	219.1	219.5
115°	246.3	246.4	246.2	245.9	245.6	245.4	245.5	245.6	245.8	245.9	245.9
117.5°	274.7	274.6	274.4	274.1	273.9	273.6	273.6	273.6	273.6	273.6	273.4
120°	304.3	304.4	303.8	303.1	302.5	301.8	301.7	301.6	301.4	301.3	301.1
122.5°	331.5	331.7	331.4	331.1	330.9	330.6	330.3	329.9	329.5	329.1	328.7
125°	359.8	359.9	359.6	359.4	359.1	358.9	358.3	357.8	357.3	356.8	356.3
127.5°	387.9	388.1	387.9	387.6	387.3	387.1	386.3	385.5	384.8	384.0	383.4
130°	415.4	415.7	415.3	414.9	414.5	414.2	413.6	413.1	412.6	412.1	411.4
132.5°	441.9	442.3	442.0	441.7	441.5	441.2	440.6	439.9	439.3	438.7	438.0
135°	467.9	468.2	468.1	468.0	467.9	467.7	467.2	466.7	466.2	465.7	465.3
137.5°	492.2	492.7	493.1	493.5	493.8	494.2	493.6	492.9	492.3	491.7	491.2
140°	518.1	518.5	518.6	518.7	518.9	519.0	518.9	518.7	518.6	518.5	518.0
142.5°	541.7	542.2	542.4	542.7	542.9	543.2	543.1	542.9	542.8	542.7	542.3
145°	564.9	565.3	565.6	566.0	566.4	566.8	566.7	566.5	566.4	566.3	566.0
147.5°	587.3	587.7	588.1	588.5	588.9	589.3	589.3	589.3	589.3	589.3	588.9
150°	608.7	609.0	609.2	609.5	609.7	610.0	610.0	610.0	610.0	610.0	609.6
152.5°	627.7	627.9	628.1	628.2	628.3	628.4	628.7	628.9	629.2	629.5	629.3
155°	645.7	645.8	645.9	646.0	646.2	646.3	646.8	647.3	647.8	648.3	648.1
157.5°	661.9	661.9	662.0	662.2	662.3	662.4	662.9	663.4	664.0	664.5	664.3
160°	676.9	676.8	676.8	676.8	676.8	676.8	677.5	678.1	678.7	679.4	679.4
162.5°	690.3	690.1	690.3	690.4	690.5	690.6	691.3	691.9	692.6	693.2	693.1
165°	701.8	701.6	701.6	701.6	701.6	701.6	702.4	703.1	703.9	704.7	704.6
167.5°	711.1	710.9	711.0	711.1	711.3	711.4	712.2	712.9	713.7	714.5	714.5
170°	719.1	718.9	718.9	718.9	718.9	718.9	719.8	720.7	721.6	722.5	722.5
172.5°	725.5	725.2	725.2	725.2	725.2	725.2	726.0	726.7	727.5	728.3	728.2
175°	729.5	729.2	729.2	729.2	729.2	729.2	730.0	730.8	731.5	732.3	732.2
177.5°	731.8	731.5	731.5	731.5	731.5	731.5	732.3	733.1	733.8	734.6	734.6
180°	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3	733.3



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2896.2	2896.2	2896.2	2896.2
2.5°	2574.3	2569.6	2550.8	2532.0
5°	2182.6	2166.4	2161.1	2155.7
7.5°	1907.1	1905.7	1877.5	1849.3
10°	1664.5	1666.5	1641.0	1615.4
12.5°	1491.1	1474.3	1472.3	1470.3
15°	1360.7	1345.3	1342.6	1339.9
17.5°	1268.7	1259.3	1256.6	1253.9
20°	1198.8	1193.4	1188.7	1184.0
22.5°	1138.3	1131.6	1127.6	1123.5
25°	1079.9	1073.8	1072.5	1071.1
27.5°	1027.4	1020.1	1020.1	1020.1
30°	977.7	973.0	971.0	969.0
32.5°	931.4	927.3	927.3	927.3
35°	887.7	885.7	883.0	880.3
37.5°	848.0	848.0	846.7	845.3
40°	809.7	811.7	811.7	811.7
42.5°	774.8	776.8	776.8	776.8
45°	738.5	741.9	743.2	744.5
47.5°	702.9	708.3	709.6	710.9
50°	667.9	672.0	672.6	673.3
52.5°	632.3	637.0	640.4	643.8
55°	594.7	599.4	601.4	603.4
57.5°	554.4	559.1	559.8	560.4
60°	510.0	514.7	516.1	517.4
62.5°	467.7	470.4	471.7	473.1
65°	419.3	423.3	426.0	428.7
67.5°	372.9	376.3	376.3	376.3
70°	321.2	322.5	324.6	326.6
72.5°	273.5	274.2	274.2	274.2
75°	223.1	224.4	225.1	225.8
77.5°	175.4	176.1	176.1	176.1
80°	128.3	127.7	127.7	127.7
82.5°	88.0	86.0	86.0	86.0
85°	50.4	49.7	50.4	51.1
87.5°	22.8	22.8	22.8	22.8
90°	16.5	16.8	17.0	17.3
92.5°	25.5	25.3	25.0	24.8
95°	44.9	44.9	44.9	44.9
97.5°	64.9	64.8	64.6	64.5
100°	86.8	87.0	87.3	87.6
102.5°	111.6	111.4	111.3	111.2
105°	136.3	136.6	136.8	137.1
107.5°	164.0	163.8	163.7	163.6
110°	191.4	191.2	190.9	190.7



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	219.5	219.5	219.5	219.5
115°	245.8	245.6	245.5	245.4
117.5°	273.0	272.6	272.3	271.9
120°	300.9	300.6	300.4	300.1
122.5°	328.3	327.9	327.6	327.2
125°	355.8	355.3	354.8	354.3
127.5°	382.9	382.3	381.8	381.3
130°	410.5	409.6	408.7	407.8
132.5°	437.4	436.7	436.1	435.5
135°	465.0	464.8	464.5	464.3
137.5°	490.8	490.4	490.0	489.6
140°	517.1	516.2	515.3	514.4
142.5°	541.6	541.0	540.4	539.7
145°	565.5	564.9	564.4	563.9
147.5°	588.1	587.3	586.6	585.8
150°	608.9	608.1	607.3	606.5
152.5°	628.6	628.0	627.3	626.7
155°	647.3	646.4	645.5	644.6
157.5°	663.6	662.8	662.0	661.3
160°	678.9	678.4	677.9	677.4
162.5°	692.2	691.3	690.4	689.5
165°	703.7	702.8	701.9	701.0
167.5°	713.7	712.9	712.2	711.4
170°	721.6	720.7	719.8	718.9
172.5°	727.3	726.4	725.5	724.6
175°	731.4	730.5	729.6	728.7
177.5°	733.7	732.8	731.9	731.0
180°	733.3	733.3	733.3	733.3



TEST NUMBER: P831133

CATALOG NUMBER: S123DIP-S1000D585U840-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.18	18.20	17.96	18.99	19.95	19.42	20.43	20.20	21.23	22.19
	3H	18.84	19.75	19.63	20.55	21.55	20.86	21.77	21.65	22.57	23.56
	4H	19.43	20.28	20.23	21.09	22.10	21.31	22.17	22.12	22.98	23.99
	6H	19.80	20.59	20.62	21.41	22.43	21.60	22.39	22.42	23.21	24.22
	8H	19.91	20.66	20.73	21.49	22.51	21.66	22.41	22.49	23.25	24.27
	12H	19.96	20.67	20.79	21.50	22.55	21.69	22.40	22.52	23.23	24.28
4H	2H	17.78	18.63	18.59	19.44	20.45	19.60	20.46	20.41	21.27	22.28
	3H	19.62	20.33	20.44	21.18	22.20	21.23	21.95	22.06	22.79	23.81
	4H	20.32	20.97	21.16	21.81	22.86	21.82	22.47	22.66	23.31	24.36
	6H	20.81	21.36	21.66	22.23	23.29	22.24	22.80	23.09	23.66	24.72
	8H	20.95	21.47	21.80	22.33	23.40	22.35	22.87	23.21	23.74	24.80
	12H	21.02	21.49	21.89	22.37	23.44	22.40	22.87	23.28	23.76	24.83
8H	4H	20.60	21.12	21.46	21.98	23.05	21.94	22.46	22.80	23.33	24.39
	6H	21.19	21.63	22.08	22.53	23.60	22.45	22.88	23.33	23.78	24.85
	8H	21.40	21.78	22.30	22.68	23.77	22.63	23.01	23.52	23.91	24.99
	12H	21.53	21.87	22.43	22.76	23.90	22.74	23.07	23.63	23.96	25.10
12H	4H	20.61	21.08	21.48	21.96	23.03	21.92	22.39	22.80	23.27	24.35
	6H	21.25	21.63	22.14	22.53	23.61	22.46	22.85	23.36	23.75	24.83
	8H	21.49	21.82	22.38	22.71	23.85	22.67	23.01	23.57	23.90	25.03