

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332019-840

Luminaire Tested: **S123DIP-S1000D805U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332019-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7068.7 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	63	58	62	56	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	39	34	39	34	31	34	30	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15268	15268	15268	15268
5°	18208	15333	13588	15333
10°	22789	15255	12273	15255
15°	27952	15133	11426	15133
20°	33298	14940	10879	14940
25°	35357	14707	10757	14707
30°	30305	14537	10813	14537
35°	21077	14294	10926	14294
40°	15874	14011	10893	14011
45°	13181	13589	10753	13589
50°	11807	12727	10655	12727
55°	11038	11798	10524	11798
60°	10355	10828	10415	10828
65°	9732	9872	10083	9872
70°	9127	8781	9602	8781
75°	8172	7690	8804	7690
80°	7153	6304	7581	6304
85°	5595	4582	5088	4582



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.7	2.0
10°-20°	448.0	6.3
20°-30°	751.9	10.6
30°-40°	851.4	12.0
40°-50°	763.5	10.8
50°-60°	616.1	8.7
60°-70°	429.4	6.1
70°-80°	225.7	3.2
80°-90°	58.2	0.8
90°-100°	65.5	0.9
100°-110°	196.0	2.8
110°-120°	333.3	4.7
120°-130°	438.5	6.2
130°-140°	492.8	7.0
140°-150°	484.4	6.9
150°-160°	407.8	5.8
160°-170°	271.5	3.8
170°-180°	95.1	1.3
0°-30°	1339.7	19.0
0°-40°	2191.1	31.0
0°-60°	3570.7	50.5
0°-90°	4283.9	60.6
90°-120°	594.8	8.4
90°-150°	2010.5	28.4
90°-180°	2785.0	39.4
0°-180°	7068.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1685	1419	1258	1419	1685	175
15°	2508	1358	1025	1358	2508	724
25°	2977	1238	906	1238	2977	1306
35°	1604	1088	832	1088	1604	1042
45°	866	893	706	893	866	685
55°	588	629	561	629	588	528
65°	382	388	396	388	382	380
75°	196	185	212	185	196	210
85°	45	37	41	37	45	54
90°	24	1	24	1	24	14
95°	62	47	62	47	62	63
105°	188	178	188	178	188	199
115°	336	336	336	336	336	333
125°	486	491	486	491	486	434
135°	636	637	636	637	636	489
145°	773	773	773	773	773	482
155°	884	885	884	885	884	407
165°	961	964	961	964	961	271
175°	999	1003	999	1003	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1505.2	1504.2	1501.4	1503.6	1499.2	1493.2	1492.6	1487.1	1471.2	1470.1	1465.7
5°	1685.1	1679.5	1678.8	1678.2	1668.5	1655.5	1630.7	1628.7	1595.7	1579.2	1559.2
7.5°	1917.8	1920.8	1910.7	1901.9	1872.5	1853.1	1826.5	1792.6	1752.1	1711.0	1683.6
10°	2085.0	2107.7	2079.5	2060.2	2042.4	2008.7	1969.5	1920.8	1872.0	1814.9	1771.6
12.5°	2264.2	2275.3	2269.7	2251.6	2223.8	2172.5	2103.1	2049.4	2004.5	1909.5	1871.1
15°	2508.3	2550.2	2523.5	2461.5	2463.0	2414.2	2323.4	2223.8	2170.9	2087.7	1974.4
17.5°	2768.3	2773.6	2762.2	2710.6	2676.2	2609.2	2525.5	2429.9	2322.8	2222.1	2101.9
20°	2906.9	2902.8	2878.7	2851.9	2792.8	2740.6	2649.2	2542.6	2405.2	2306.2	2175.0
22.5°	2983.8	2977.0	2965.6	2943.2	2894.0	2837.9	2755.8	2639.4	2508.6	2372.3	2220.6
25°	2977.0	2985.9	2987.3	2981.1	2964.0	2930.2	2865.6	2772.9	2642.3	2467.1	2309.1
27.5°	2707.5	2720.3	2756.9	2789.6	2825.9	2863.1	2858.1	2812.1	2715.4	2564.0	2370.9
30°	2438.2	2410.7	2478.7	2564.7	2623.0	2726.1	2783.9	2787.3	2733.0	2603.1	2414.8
32.5°	2064.4	2094.6	2124.7	2230.4	2358.0	2473.8	2588.7	2681.2	2691.8	2605.4	2440.6
35°	1604.0	1641.7	1696.7	1751.7	1889.2	2007.3	2209.4	2385.3	2525.5	2544.1	2443.0
37.5°	1292.5	1311.2	1345.9	1401.1	1491.0	1631.1	1787.5	2009.8	2212.9	2364.0	2370.6
40°	1129.7	1135.3	1174.5	1216.4	1289.2	1404.6	1545.5	1742.0	1985.3	2196.4	2284.3
42.5°	1007.7	1019.8	1036.4	1076.7	1134.7	1221.5	1352.5	1515.0	1738.0	1980.7	2152.8
45°	865.9	879.6	889.9	916.8	958.0	1016.3	1107.8	1256.2	1425.9	1676.8	1908.3
47.5°	772.1	773.3	780.9	801.1	829.2	873.0	937.7	1033.0	1188.8	1392.3	1630.0
50°	705.1	716.1	718.8	734.6	756.6	788.9	842.5	923.6	1051.5	1230.1	1448.7
52.5°	657.8	661.1	668.8	680.2	699.4	724.6	771.0	834.6	934.8	1087.1	1288.1
55°	588.2	588.2	595.8	604.7	615.7	638.4	669.3	716.1	792.3	910.6	1076.8
57.5°	523.9	527.4	532.7	535.4	544.8	559.8	585.6	621.1	678.0	769.0	901.2
60°	481.0	487.3	486.6	492.0	500.3	512.0	533.9	562.8	613.7	686.5	797.9
62.5°	443.6	443.2	443.1	449.7	458.0	469.1	483.4	508.4	551.6	616.1	710.9
65°	382.1	380.7	385.6	389.6	392.4	400.6	411.6	433.6	462.5	510.6	584.1
67.5°	327.4	323.4	326.0	327.4	332.0	338.5	348.8	362.4	385.4	424.0	479.4
70°	290.0	286.6	285.9	287.2	291.3	296.2	303.8	316.8	338.1	369.0	409.6
72.5°	251.6	249.1	249.0	252.1	254.0	257.1	262.5	274.5	291.3	314.6	352.4
75°	196.5	196.5	196.5	197.2	199.2	202.1	206.1	212.4	225.4	241.9	267.3
77.5°	147.3	147.2	146.3	146.2	149.3	150.5	151.5	157.2	164.5	175.6	194.2
80°	115.4	112.0	113.4	115.4	116.8	117.5	119.6	121.0	127.1	133.3	146.3
82.5°	85.7	82.9	83.1	86.3	86.5	87.3	89.4	91.3	93.6	99.3	106.2
85°	45.3	45.3	46.0	46.0	46.8	46.0	48.1	48.8	48.8	52.2	56.4
87.5°	21.2	20.1	20.5	21.0	20.4	20.8	21.2	21.7	22.1	22.5	22.6
90°	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4	19.7	19.0	16.7
92.5°	31.9	32.1	32.3	32.5	32.7	32.5	32.0	31.4	30.9	30.3	29.0
95°	61.6	61.6	61.6	61.6	61.6	61.2	60.5	59.8	59.2	58.5	57.1
97.5°	94.7	94.8	94.9	94.9	95.0	94.6	93.8	93.0	92.2	91.4	90.4
100°	120.0	119.7	119.3	119.0	118.7	118.2	117.6	117.1	116.6	116.0	115.2
102.5°	145.9	146.0	146.0	146.1	146.2	145.9	145.4	144.9	144.4	143.9	142.7
105°	187.9	187.5	187.2	186.8	186.5	186.3	186.3	186.3	186.3	186.3	184.8
107.5°	231.7	231.9	232.1	232.3	232.5	232.4	231.8	231.2	230.7	230.0	229.4
110°	261.4	261.7	262.1	262.4	262.8	262.6	261.9	261.2	260.4	259.7	259.4



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.0	293.0	293.1	293.2	293.2	292.9	292.0	291.1	290.3	289.4	289.4
115°	336.4	336.5	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4	336.7
117.5°	380.4	380.9	381.4	381.9	382.3	382.6	382.6	382.7	382.7	382.7	383.2
120°	411.3	411.7	412.0	412.4	412.7	413.0	413.2	413.3	413.5	413.7	414.7
122.5°	441.0	441.5	442.0	442.5	443.0	443.5	443.9	444.4	444.8	445.4	445.8
125°	485.5	486.3	487.0	487.7	488.4	489.1	489.8	490.5	491.2	491.9	492.2
127.5°	530.0	530.8	531.6	532.4	533.2	534.1	535.0	536.0	537.0	538.0	538.4
130°	559.0	560.3	561.5	562.7	563.9	564.9	565.6	566.3	566.9	567.6	568.3
132.5°	589.4	590.3	591.2	592.2	593.1	594.0	594.8	595.7	596.5	597.3	597.7
135°	636.4	636.7	637.1	637.4	637.8	638.3	639.0	639.7	640.5	641.2	641.3
137.5°	677.9	678.6	679.2	679.9	680.5	681.3	682.1	682.8	683.5	684.2	683.8
140°	705.1	706.3	707.5	708.7	710.0	710.6	710.8	711.0	711.2	711.3	711.2
142.5°	732.9	733.8	734.8	735.7	736.7	737.2	737.4	737.6	737.7	737.9	737.6
145°	773.0	773.7	774.4	775.1	775.8	776.2	776.4	776.6	776.8	776.9	776.4
147.5°	808.7	809.7	810.7	811.8	812.8	813.4	813.4	813.4	813.4	813.4	812.9
150°	831.4	832.4	833.5	834.6	835.7	836.2	836.2	836.2	836.2	836.2	835.8
152.5°	853.5	854.4	855.4	856.3	857.2	857.5	857.2	856.9	856.7	856.4	856.2
155°	883.5	884.7	886.0	887.2	888.4	888.7	888.0	887.3	886.6	885.9	885.8
157.5°	910.8	911.8	912.8	913.8	914.7	914.8	914.1	913.4	912.7	911.9	911.8
160°	928.5	929.2	929.9	930.6	931.3	931.2	930.4	929.5	928.6	927.8	927.8
162.5°	941.8	942.9	944.0	945.1	946.2	946.4	945.5	944.6	943.7	942.9	942.7
165°	960.9	962.1	963.3	964.6	965.8	965.9	964.8	963.8	962.7	961.7	961.7
167.5°	977.1	978.3	979.4	980.4	981.5	981.5	980.4	979.4	978.3	977.1	977.0
170°	985.3	986.6	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.3	985.3
172.5°	991.7	992.9	994.1	995.3	996.6	996.6	995.6	994.5	993.4	992.3	992.3
175°	998.8	1000.0	1001.3	1002.5	1003.7	1003.8	1002.7	1001.7	1000.7	999.6	999.6
177.5°	1002.6	1003.6	1004.5	1005.5	1006.5	1006.5	1005.7	1004.9	1004.0	1003.2	1003.2
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1462.4	1457.9	1453.6	1445.9	1439.3	1430.0	1427.1	1423.9	1414.0	1405.2	1398.6
5°	1551.7	1535.2	1511.2	1489.1	1471.3	1447.2	1433.5	1419.1	1398.5	1379.9	1364.8
7.5°	1645.2	1612.8	1575.4	1534.9	1497.3	1461.0	1431.7	1405.6	1376.7	1349.4	1328.1
10°	1719.4	1672.6	1620.4	1564.1	1516.0	1469.3	1430.1	1395.7	1358.6	1326.3	1299.5
12.5°	1804.0	1734.7	1662.7	1594.3	1537.4	1472.6	1425.1	1381.4	1339.4	1300.5	1270.4
15°	1904.2	1816.2	1731.1	1636.9	1550.3	1469.3	1412.9	1358.0	1309.1	1269.3	1230.8
17.5°	1995.5	1895.8	1783.5	1669.1	1564.6	1468.4	1389.6	1327.4	1266.4	1217.6	1179.2
20°	2047.2	1933.8	1806.6	1687.8	1572.4	1465.1	1378.6	1304.3	1238.3	1186.8	1143.5
22.5°	2091.7	1959.0	1827.6	1700.4	1571.8	1456.3	1358.2	1281.8	1210.3	1159.8	1113.8
25°	2137.9	1979.1	1847.2	1698.1	1554.5	1434.9	1324.9	1238.3	1166.9	1107.8	1060.4
27.5°	2177.5	1977.8	1821.2	1660.8	1527.2	1407.3	1290.0	1197.1	1121.3	1057.0	1009.0
30°	2203.8	1980.5	1794.3	1635.6	1500.9	1377.2	1263.0	1169.6	1089.9	1024.6	979.3
32.5°	2220.4	1978.8	1769.6	1600.3	1459.1	1349.7	1234.0	1137.2	1055.3	991.1	947.4
35°	2230.0	1966.8	1727.0	1527.6	1391.6	1285.1	1188.2	1087.8	1002.0	942.2	892.7
37.5°	2210.7	1941.4	1677.5	1457.5	1308.6	1203.7	1122.2	1036.7	954.5	888.7	846.1
40°	2180.5	1924.9	1639.0	1408.1	1251.4	1150.3	1081.0	997.1	916.0	853.5	813.6
42.5°	2122.7	1891.3	1596.7	1353.1	1192.0	1091.0	1027.1	957.0	880.3	821.6	781.7
45°	1981.9	1818.4	1533.2	1270.6	1104.3	999.9	943.5	892.7	823.2	766.2	731.8
47.5°	1786.5	1708.5	1441.4	1183.7	1012.8	912.3	853.7	812.8	762.1	716.1	683.1
50°	1650.6	1618.4	1379.2	1124.3	951.8	853.5	797.2	760.0	723.7	677.6	647.3
52.5°	1494.0	1513.9	1306.7	1062.7	889.7	793.0	740.0	710.5	677.4	639.6	613.3
55°	1273.4	1345.5	1181.3	959.4	797.2	705.1	654.9	628.7	609.6	581.4	558.7
57.5°	1066.8	1158.6	1045.8	852.8	706.3	626.8	578.8	550.3	538.0	523.2	505.3
60°	944.2	1034.9	949.1	781.3	645.3	569.7	527.0	503.0	490.7	480.4	465.2
62.5°	834.9	926.7	854.4	708.8	585.3	515.2	478.2	454.6	445.0	439.7	426.8
65°	684.5	763.5	715.4	595.8	499.6	437.8	404.0	387.6	378.7	376.6	368.3
67.5°	557.0	617.2	582.2	494.2	418.5	365.1	336.5	322.4	315.6	314.9	308.7
70°	473.5	529.9	503.0	423.3	358.0	316.1	291.3	279.0	274.9	274.2	270.7
72.5°	408.6	447.9	426.6	360.1	309.6	271.6	253.5	240.5	235.8	236.8	234.5
75°	302.4	331.9	319.5	273.5	233.0	208.2	193.1	184.9	180.8	182.8	180.1
77.5°	217.5	236.3	225.1	193.3	168.2	150.4	139.3	134.1	130.5	130.3	129.1
80°	164.2	175.2	169.1	149.8	129.2	114.1	105.1	101.7	99.7	99.0	98.3
82.5°	116.9	126.3	119.1	105.8	91.8	82.7	77.7	73.1	71.6	72.0	71.3
85°	59.1	62.5	59.8	51.5	46.0	41.9	39.2	37.1	35.7	36.5	35.0
87.5°	23.2	23.3	21.2	18.6	17.2	15.1	14.8	13.3	12.6	12.9	12.7
90°	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	27.8	26.5	25.1	23.8	22.7	21.5	20.3	19.1	20.3	21.5	22.7
95°	55.6	54.2	52.8	51.5	50.3	49.1	47.8	46.6	47.8	49.1	50.3
97.5°	89.4	88.4	87.4	86.4	85.4	84.5	83.6	82.7	83.6	84.5	85.4
100°	114.3	113.4	112.6	111.6	110.6	109.5	108.5	107.3	108.5	109.5	110.6
102.5°	141.6	140.4	139.3	138.4	137.7	137.0	136.4	135.8	136.4	137.0	137.7
105°	183.2	181.6	180.1	179.0	178.7	178.3	178.0	177.6	178.0	178.3	178.7
107.5°	228.8	228.2	227.5	227.1	226.9	226.7	226.5	226.3	226.5	226.7	226.9
110°	259.0	258.7	258.3	258.0	257.6	257.3	256.9	256.6	256.9	257.3	257.6



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.3	289.2	289.1	289.0	288.8	288.6	288.4	288.2	288.4	288.6	288.8
115°	337.1	337.4	337.8	337.7	337.1	336.6	336.1	335.6	336.1	336.6	337.1
117.5°	383.6	384.2	384.6	384.7	384.3	384.0	383.6	383.2	383.6	384.0	384.3
120°	415.5	416.4	417.3	417.2	416.1	415.1	413.9	412.9	413.9	415.1	416.1
122.5°	446.3	446.7	447.2	447.0	446.2	445.5	444.6	443.9	444.6	445.5	446.2
125°	492.6	492.9	493.3	493.2	492.7	492.1	491.6	491.1	491.6	492.1	492.7
127.5°	538.8	539.2	539.6	539.2	538.1	536.9	535.8	534.7	535.8	536.9	538.1
130°	568.8	569.3	569.8	569.4	567.9	566.5	565.1	563.7	565.1	566.5	567.9
132.5°	598.1	598.5	599.0	598.4	597.0	595.6	594.2	592.8	594.2	595.6	597.0
135°	641.5	641.7	641.9	641.4	640.4	639.2	638.2	637.1	638.2	639.2	640.4
137.5°	683.3	682.9	682.4	681.8	680.9	679.9	679.1	678.2	679.1	679.9	680.9
140°	711.0	710.8	710.6	710.1	709.3	708.4	707.5	706.6	707.5	708.4	709.3
142.5°	737.3	737.0	736.7	736.1	735.2	734.3	733.5	732.6	733.5	734.3	735.2
145°	775.9	775.4	774.8	774.4	774.1	773.7	773.4	773.0	773.4	773.7	774.1
147.5°	812.4	811.9	811.4	810.9	810.2	809.6	809.0	808.4	809.0	809.6	810.2
150°	835.5	835.1	834.8	834.4	834.0	833.6	833.3	832.9	833.3	833.6	834.0
152.5°	856.0	855.8	855.6	855.2	854.6	854.1	853.6	853.2	853.6	854.1	854.6
155°	885.6	885.3	885.1	885.0	885.0	885.0	885.0	885.0	885.0	885.0	885.0
157.5°	911.7	911.5	911.4	911.4	911.6	911.8	912.0	912.2	912.0	911.8	911.6
160°	927.8	927.8	927.8	927.9	928.3	928.6	929.0	929.3	929.0	928.6	928.3
162.5°	942.6	942.5	942.3	942.5	943.0	943.5	944.0	944.4	944.0	943.5	943.0
165°	961.7	961.7	961.7	961.9	962.5	963.0	963.5	964.0	963.5	963.0	962.5
167.5°	976.8	976.7	976.6	976.8	977.5	978.3	979.0	979.7	979.0	978.3	977.5
170°	985.3	985.3	985.3	985.7	986.4	987.1	987.8	988.6	987.8	987.1	986.4
172.5°	992.3	992.3	992.3	992.7	993.4	994.1	994.8	995.4	994.8	994.1	993.4
175°	999.6	999.6	999.6	1000.0	1000.7	1001.4	1002.0	1002.7	1002.0	1001.4	1000.7
177.5°	1003.2	1003.2	1003.2	1003.5	1004.0	1004.6	1005.2	1005.7	1005.2	1004.6	1004.0
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1394.7	1390.9	1385.4	1377.2	1370.6	1360.1	1360.1	1361.8	1361.8	1361.2	1360.1
5°	1352.4	1342.1	1329.8	1315.3	1300.2	1285.1	1282.3	1276.9	1272.7	1269.9	1266.5
7.5°	1307.8	1289.5	1271.4	1251.2	1232.8	1217.6	1207.0	1198.2	1192.5	1186.5	1182.1
10°	1277.5	1254.9	1233.6	1212.2	1188.8	1170.3	1158.6	1150.3	1144.2	1138.7	1136.0
12.5°	1241.7	1215.8	1192.3	1172.0	1146.5	1127.4	1116.3	1112.5	1105.2	1093.6	1087.5
15°	1189.5	1165.5	1137.3	1106.4	1094.0	1070.7	1057.6	1051.5	1047.3	1038.3	1035.6
17.5°	1144.9	1113.4	1081.8	1058.7	1035.7	1016.8	1009.5	1001.8	996.3	989.1	986.8
20°	1109.1	1081.0	1052.1	1027.3	1003.3	982.7	976.5	971.0	965.5	962.1	959.4
22.5°	1072.9	1044.7	1020.8	997.6	972.0	958.5	951.8	945.7	941.9	939.6	936.8
25°	1021.9	997.1	970.4	949.7	929.1	920.2	916.0	912.6	909.9	906.5	905.7
27.5°	976.2	949.3	927.6	908.4	893.5	886.1	882.1	880.4	881.0	882.2	883.0
30°	942.2	917.5	899.6	883.0	869.3	862.4	861.7	861.7	864.5	865.2	866.6
32.5°	910.8	890.5	872.6	856.7	846.3	841.5	844.1	844.1	846.4	848.2	850.6
35°	865.2	847.3	833.5	819.8	810.9	812.9	814.4	815.7	819.1	823.2	826.1
37.5°	821.6	806.1	791.8	781.0	777.0	780.6	784.0	786.9	790.8	794.0	796.8
40°	790.3	778.6	764.9	755.3	756.6	758.7	761.4	764.9	768.3	770.3	773.2
42.5°	761.1	748.9	738.5	730.5	732.5	735.1	736.7	738.5	742.5	746.2	747.8
45°	716.8	707.1	697.5	692.7	694.1	695.5	696.8	698.9	702.4	705.1	705.8
47.5°	666.8	660.1	653.7	649.0	651.2	650.7	652.5	656.8	657.9	659.5	663.4
50°	635.0	628.7	621.3	619.9	619.9	619.9	620.6	626.0	626.0	628.7	631.6
52.5°	599.8	595.8	591.0	588.5	587.4	587.4	590.3	593.1	594.2	598.0	600.8
55°	547.8	543.6	539.5	537.3	536.0	537.3	542.9	544.2	547.8	549.8	551.8
57.5°	493.4	490.3	487.0	485.8	485.5	487.4	490.4	494.5	495.3	501.7	504.8
60°	457.7	452.8	450.1	450.1	448.8	454.9	453.5	460.4	461.8	466.0	470.7
62.5°	420.8	414.3	413.2	413.2	415.3	417.0	418.9	421.9	425.6	430.7	434.4
65°	361.4	358.0	362.8	362.1	360.8	364.9	364.9	368.3	372.4	377.3	384.9
67.5°	305.3	303.5	303.9	303.9	306.0	308.3	310.2	313.3	318.2	323.3	328.2
70°	267.3	269.4	266.0	268.7	270.7	271.5	272.9	276.9	282.5	285.9	291.3
72.5°	230.5	230.4	230.8	231.9	233.9	235.2	236.5	241.3	247.2	250.1	254.6
75°	177.3	176.6	178.6	178.6	182.1	183.5	184.9	186.9	192.4	196.5	200.0
77.5°	129.5	130.3	129.9	132.2	131.3	131.5	135.8	137.8	138.5	146.5	148.3
80°	97.6	99.0	99.7	100.4	101.0	99.7	104.4	106.5	106.5	111.3	114.7
82.5°	70.1	70.9	72.7	73.4	73.5	74.9	75.3	76.9	78.5	80.6	85.0
85°	35.0	37.1	37.8	37.1	37.8	36.5	38.5	39.2	39.9	39.9	39.9
87.5°	12.5	13.5	13.4	14.4	14.3	15.3	15.5	14.5	14.6	16.5	14.3
90°	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4	21.0	21.7	22.3
92.5°	23.8	25.1	26.5	27.8	29.0	30.3	30.9	31.4	32.0	32.5	32.7
95°	51.5	52.8	54.2	55.6	57.1	58.5	59.2	59.8	60.5	61.2	61.6
97.5°	86.4	87.4	88.4	89.4	90.4	91.4	92.2	93.0	93.8	94.6	95.0
100°	111.6	112.6	113.4	114.3	115.2	116.0	116.6	117.1	117.6	118.2	118.7
102.5°	138.4	139.3	140.4	141.6	142.7	143.9	144.4	144.9	145.4	145.9	146.2
105°	179.0	180.1	181.6	183.2	184.8	186.3	186.3	186.3	186.3	186.3	186.5
107.5°	227.1	227.5	228.2	228.8	229.4	230.0	230.7	231.2	231.8	232.4	232.5
110°	258.0	258.3	258.7	259.0	259.4	259.7	260.4	261.2	261.9	262.6	262.8



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.0	289.1	289.2	289.3	289.4	289.4	290.3	291.1	292.0	292.9	293.2
115°	337.7	337.8	337.4	337.1	336.7	336.4	336.5	336.7	336.9	337.1	337.1
117.5°	384.7	384.6	384.2	383.6	383.2	382.7	382.7	382.7	382.6	382.6	382.3
120°	417.2	417.3	416.4	415.5	414.7	413.7	413.5	413.3	413.2	413.0	412.7
122.5°	447.0	447.2	446.7	446.3	445.8	445.4	444.8	444.4	443.9	443.5	443.0
125°	493.2	493.3	492.9	492.6	492.2	491.9	491.2	490.5	489.8	489.1	488.4
127.5°	539.2	539.6	539.2	538.8	538.4	538.0	537.0	536.0	535.0	534.1	533.2
130°	569.4	569.8	569.3	568.8	568.3	567.6	566.9	566.3	565.6	564.9	563.9
132.5°	598.4	599.0	598.5	598.1	597.7	597.3	596.5	595.7	594.8	594.0	593.1
135°	641.4	641.9	641.7	641.5	641.3	641.2	640.5	639.7	639.0	638.3	637.8
137.5°	681.8	682.4	682.9	683.3	683.8	684.2	683.5	682.8	682.1	681.3	680.5
140°	710.1	710.6	710.8	711.0	711.2	711.3	711.2	711.0	710.8	710.6	710.0
142.5°	736.1	736.7	737.0	737.3	737.6	737.9	737.7	737.6	737.4	737.2	736.7
145°	774.4	774.8	775.4	775.9	776.4	776.9	776.8	776.6	776.4	776.2	775.8
147.5°	810.9	811.4	811.9	812.4	812.9	813.4	813.4	813.4	813.4	813.4	812.8
150°	834.4	834.8	835.1	835.5	835.8	836.2	836.2	836.2	836.2	836.2	835.7
152.5°	855.2	855.6	855.8	856.0	856.2	856.4	856.7	856.9	857.2	857.5	857.2
155°	885.0	885.1	885.3	885.6	885.8	885.9	886.6	887.3	888.0	888.7	888.4
157.5°	911.4	911.4	911.5	911.7	911.8	911.9	912.7	913.4	914.1	914.8	914.7
160°	927.9	927.8	927.8	927.8	927.8	927.8	928.6	929.5	930.4	931.2	931.3
162.5°	942.5	942.3	942.5	942.6	942.7	942.9	943.7	944.6	945.5	946.4	946.2
165°	961.9	961.7	961.7	961.7	961.7	961.7	962.7	963.8	964.8	965.9	965.8
167.5°	976.8	976.6	976.7	976.8	977.0	977.1	978.3	979.4	980.4	981.5	981.5
170°	985.7	985.3	985.3	985.3	985.3	985.3	986.6	987.8	989.1	990.3	990.3
172.5°	992.7	992.3	992.3	992.3	992.3	992.3	993.4	994.5	995.6	996.6	996.6
175°	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7	1001.7	1002.7	1003.8	1003.7
177.5°	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0	1004.9	1005.7	1006.5	1006.5
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1356.2	1355.7	1359.6	1356.9	1359.6	1355.7	1356.2	1360.1	1361.2	1361.8	1361.8
5°	1262.4	1264.5	1257.6	1257.6	1257.6	1264.5	1262.4	1266.5	1269.9	1272.7	1276.9
7.5°	1178.8	1175.8	1176.1	1172.4	1176.1	1175.8	1178.8	1182.1	1186.5	1192.5	1198.2
10°	1127.7	1123.6	1122.2	1122.9	1122.2	1123.6	1127.7	1136.0	1138.7	1144.2	1150.3
12.5°	1085.4	1084.6	1075.5	1075.6	1075.5	1084.6	1085.4	1087.5	1093.6	1105.2	1112.5
15°	1035.6	1022.6	1021.2	1025.3	1021.2	1022.6	1035.6	1035.6	1038.3	1047.3	1051.5
17.5°	985.7	978.9	979.3	977.2	979.3	978.9	985.7	986.8	989.1	996.3	1001.8
20°	959.4	955.2	954.5	949.7	954.5	955.2	959.4	959.4	962.1	965.5	971.0
22.5°	935.1	933.8	934.2	928.9	934.2	933.8	935.1	936.8	939.6	941.9	945.7
25°	905.0	908.5	905.7	905.7	905.7	908.5	905.0	905.7	906.5	909.9	912.6
27.5°	884.7	884.5	883.2	883.2	883.2	884.5	884.7	883.0	882.2	881.0	880.4
30°	869.3	868.6	870.0	870.0	870.0	868.6	869.3	866.6	865.2	864.5	861.7
32.5°	853.9	854.9	855.2	855.7	855.2	854.9	853.9	850.6	848.2	846.4	844.1
35°	830.1	830.8	832.9	831.5	832.9	830.8	830.1	826.1	823.2	819.1	815.7
37.5°	798.0	801.1	800.4	801.5	800.4	801.1	798.0	796.8	794.0	790.8	786.9
40°	773.8	775.9	775.2	775.2	775.2	775.9	773.8	773.2	770.3	768.3	764.9
42.5°	749.0	750.5	748.8	747.7	748.8	750.5	749.0	747.8	746.2	742.5	738.5
45°	708.5	707.1	709.2	706.4	709.2	707.1	708.5	705.8	705.1	702.4	698.9
47.5°	663.2	664.5	665.1	667.1	665.1	664.5	663.2	663.4	659.5	657.9	656.8
50°	632.9	637.0	637.0	636.3	637.0	637.0	632.9	631.6	628.7	626.0	626.0
52.5°	603.2	605.1	607.9	607.7	607.9	605.1	603.2	600.8	598.0	594.2	593.1
55°	557.3	558.7	560.1	560.8	560.1	558.7	557.3	551.8	549.8	547.8	544.2
57.5°	509.8	509.2	512.5	513.5	512.5	509.2	509.8	504.8	501.7	495.3	494.5
60°	476.3	476.3	481.7	483.8	481.7	476.3	476.3	470.7	466.0	461.8	460.4
62.5°	440.5	442.7	448.2	445.4	448.2	442.7	440.5	434.4	430.7	425.6	421.9
65°	388.3	393.7	393.0	395.9	393.0	393.7	388.3	384.9	377.3	372.4	368.3
67.5°	333.7	337.1	342.0	342.5	342.0	337.1	333.7	328.2	323.3	318.2	313.3
70°	296.9	300.3	303.1	305.1	303.1	300.3	296.9	291.3	285.9	282.5	276.9
72.5°	261.2	263.0	269.5	266.6	269.5	263.0	261.2	254.6	250.1	247.2	241.3
75°	204.8	209.5	213.7	211.7	213.7	209.5	204.8	200.0	196.5	192.4	186.9
77.5°	151.5	156.2	158.1	156.4	158.1	156.2	151.5	148.3	146.5	138.5	137.8
80°	119.6	118.9	123.0	122.3	123.0	118.9	119.6	114.7	111.3	106.5	106.5
82.5°	87.7	87.1	89.0	89.4	89.0	87.1	87.7	85.0	80.6	78.5	76.9
85°	42.6	44.6	41.9	41.2	41.9	44.6	42.6	39.9	39.9	39.9	39.2
87.5°	14.4	14.5	14.0	13.5	14.0	14.5	14.4	14.3	16.5	14.6	14.5
90°	22.6	23.0	23.3	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4
92.5°	32.5	32.3	32.1	31.9	32.1	32.3	32.5	32.7	32.5	32.0	31.4
95°	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.6	61.2	60.5	59.8
97.5°	94.9	94.9	94.8	94.7	94.8	94.9	94.9	95.0	94.6	93.8	93.0
100°	119.0	119.3	119.7	120.0	119.7	119.3	119.0	118.7	118.2	117.6	117.1
102.5°	146.1	146.0	146.0	145.9	146.0	146.0	146.1	146.2	145.9	145.4	144.9
105°	186.8	187.2	187.5	187.9	187.5	187.2	186.8	186.5	186.3	186.3	186.3
107.5°	232.3	232.1	231.9	231.7	231.9	232.1	232.3	232.5	232.4	231.8	231.2
110°	262.4	262.1	261.7	261.4	261.7	262.1	262.4	262.8	262.6	261.9	261.2



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	293.2	293.1	293.0	293.0	293.0	293.1	293.2	293.2	292.9	292.0	291.1
115°	336.9	336.7	336.5	336.4	336.5	336.7	336.9	337.1	337.1	336.9	336.7
117.5°	381.9	381.4	380.9	380.4	380.9	381.4	381.9	382.3	382.6	382.6	382.7
120°	412.4	412.0	411.7	411.3	411.7	412.0	412.4	412.7	413.0	413.2	413.3
122.5°	442.5	442.0	441.5	441.0	441.5	442.0	442.5	443.0	443.5	443.9	444.4
125°	487.7	487.0	486.3	485.5	486.3	487.0	487.7	488.4	489.1	489.8	490.5
127.5°	532.4	531.6	530.8	530.0	530.8	531.6	532.4	533.2	534.1	535.0	536.0
130°	562.7	561.5	560.3	559.0	560.3	561.5	562.7	563.9	564.9	565.6	566.3
132.5°	592.2	591.2	590.3	589.4	590.3	591.2	592.2	593.1	594.0	594.8	595.7
135°	637.4	637.1	636.7	636.4	636.7	637.1	637.4	637.8	638.3	639.0	639.7
137.5°	679.9	679.2	678.6	677.9	678.6	679.2	679.9	680.5	681.3	682.1	682.8
140°	708.7	707.5	706.3	705.1	706.3	707.5	708.7	710.0	710.6	710.8	711.0
142.5°	735.7	734.8	733.8	732.9	733.8	734.8	735.7	736.7	737.2	737.4	737.6
145°	775.1	774.4	773.7	773.0	773.7	774.4	775.1	775.8	776.2	776.4	776.6
147.5°	811.8	810.7	809.7	808.7	809.7	810.7	811.8	812.8	813.4	813.4	813.4
150°	834.6	833.5	832.4	831.4	832.4	833.5	834.6	835.7	836.2	836.2	836.2
152.5°	856.3	855.4	854.4	853.5	854.4	855.4	856.3	857.2	857.5	857.2	856.9
155°	887.2	886.0	884.7	883.5	884.7	886.0	887.2	888.4	888.7	888.0	887.3
157.5°	913.8	912.8	911.8	910.8	911.8	912.8	913.8	914.7	914.8	914.1	913.4
160°	930.6	929.9	929.2	928.5	929.2	929.9	930.6	931.3	931.2	930.4	929.5
162.5°	945.1	944.0	942.9	941.8	942.9	944.0	945.1	946.2	946.4	945.5	944.6
165°	964.6	963.3	962.1	960.9	962.1	963.3	964.6	965.8	965.9	964.8	963.8
167.5°	980.4	979.4	978.3	977.1	978.3	979.4	980.4	981.5	981.5	980.4	979.4
170°	989.1	987.8	986.6	985.3	986.6	987.8	989.1	990.3	990.3	989.1	987.8
172.5°	995.3	994.1	992.9	991.7	992.9	994.1	995.3	996.6	996.6	995.6	994.5
175°	1002.5	1001.3	1000.0	998.8	1000.0	1001.3	1002.5	1003.7	1003.8	1002.7	1001.7
177.5°	1005.5	1004.5	1003.6	1002.6	1003.6	1004.5	1005.5	1006.5	1006.5	1005.7	1004.9
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1360.1	1360.1	1370.6	1377.2	1385.4	1390.9	1394.7	1398.6	1405.2	1414.0	1423.9
5°	1282.3	1285.1	1300.2	1315.3	1329.8	1342.1	1352.4	1364.8	1379.9	1398.5	1419.1
7.5°	1207.0	1217.6	1232.8	1251.2	1271.4	1289.5	1307.8	1328.1	1349.4	1376.7	1405.6
10°	1158.6	1170.3	1188.8	1212.2	1233.6	1254.9	1277.5	1299.5	1326.3	1358.6	1395.7
12.5°	1116.3	1127.4	1146.5	1172.0	1192.3	1215.8	1241.7	1270.4	1300.5	1339.4	1381.4
15°	1057.6	1070.7	1094.0	1106.4	1137.3	1165.5	1189.5	1230.8	1269.3	1309.1	1358.0
17.5°	1009.5	1016.8	1035.7	1058.7	1081.8	1113.4	1144.9	1179.2	1217.6	1266.4	1327.4
20°	976.5	982.7	1003.3	1027.3	1052.1	1081.0	1109.1	1143.5	1186.8	1238.3	1304.3
22.5°	951.8	958.5	972.0	997.6	1020.8	1044.7	1072.9	1113.8	1159.8	1210.3	1281.8
25°	916.0	920.2	929.1	949.7	970.4	997.1	1021.9	1060.4	1107.8	1166.9	1238.3
27.5°	882.1	886.1	893.5	908.4	927.6	949.3	976.2	1009.0	1057.0	1121.3	1197.1
30°	861.7	862.4	869.3	883.0	899.6	917.5	942.2	979.3	1024.6	1089.9	1169.6
32.5°	844.1	841.5	846.3	856.7	872.6	890.5	910.8	947.4	991.1	1055.3	1137.2
35°	814.4	812.9	810.9	819.8	833.5	847.3	865.2	892.7	942.2	1002.0	1087.8
37.5°	784.0	780.6	777.0	781.0	791.8	806.1	821.6	846.1	888.7	954.5	1036.7
40°	761.4	758.7	756.6	755.3	764.9	778.6	790.3	813.6	853.5	916.0	997.1
42.5°	736.7	735.1	732.5	730.5	738.5	748.9	761.1	781.7	821.6	880.3	957.0
45°	696.8	695.5	694.1	692.7	697.5	707.1	716.8	731.8	766.2	823.2	892.7
47.5°	652.5	650.7	651.2	649.0	653.7	660.1	666.8	683.1	716.1	762.1	812.8
50°	620.6	619.9	619.9	619.9	621.3	628.7	635.0	647.3	677.6	723.7	760.0
52.5°	590.3	587.4	587.4	588.5	591.0	595.8	599.8	613.3	639.6	677.4	710.5
55°	542.9	537.3	536.0	537.3	539.5	543.6	547.8	558.7	581.4	609.6	628.7
57.5°	490.4	487.4	485.5	485.8	487.0	490.3	493.4	505.3	523.2	538.0	550.3
60°	453.5	454.9	448.8	450.1	450.1	452.8	457.7	465.2	480.4	490.7	503.0
62.5°	418.9	417.0	415.3	413.2	413.2	414.3	420.8	426.8	439.7	445.0	454.6
65°	364.9	364.9	360.8	362.1	362.8	358.0	361.4	368.3	376.6	378.7	387.6
67.5°	310.2	308.3	306.0	303.9	303.9	303.5	305.3	308.7	314.9	315.6	322.4
70°	272.9	271.5	270.7	268.7	266.0	269.4	267.3	270.7	274.2	274.9	279.0
72.5°	236.5	235.2	233.9	231.9	230.8	230.4	230.5	234.5	236.8	235.8	240.5
75°	184.9	183.5	182.1	178.6	178.6	176.6	177.3	180.1	182.8	180.8	184.9
77.5°	135.8	131.5	131.3	132.2	129.9	130.3	129.5	129.1	130.3	130.5	134.1
80°	104.4	99.7	101.0	100.4	99.7	99.0	97.6	98.3	99.0	99.7	101.7
82.5°	75.3	74.9	73.5	73.4	72.7	70.9	70.1	71.3	72.0	71.6	73.1
85°	38.5	36.5	37.8	37.1	37.8	37.1	35.0	35.0	36.5	35.7	37.1
87.5°	15.5	15.3	14.3	14.4	13.4	13.5	12.5	12.7	12.9	12.6	13.3
90°	19.7	19.0	16.7	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	30.9	30.3	29.0	27.8	26.5	25.1	23.8	22.7	21.5	20.3	19.1
95°	59.2	58.5	57.1	55.6	54.2	52.8	51.5	50.3	49.1	47.8	46.6
97.5°	92.2	91.4	90.4	89.4	88.4	87.4	86.4	85.4	84.5	83.6	82.7
100°	116.6	116.0	115.2	114.3	113.4	112.6	111.6	110.6	109.5	108.5	107.3
102.5°	144.4	143.9	142.7	141.6	140.4	139.3	138.4	137.7	137.0	136.4	135.8
105°	186.3	186.3	184.8	183.2	181.6	180.1	179.0	178.7	178.3	178.0	177.6
107.5°	230.7	230.0	229.4	228.8	228.2	227.5	227.1	226.9	226.7	226.5	226.3
110°	260.4	259.7	259.4	259.0	258.7	258.3	258.0	257.6	257.3	256.9	256.6



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.3	289.4	289.4	289.3	289.2	289.1	289.0	288.8	288.6	288.4	288.2
115°	336.5	336.4	336.7	337.1	337.4	337.8	337.7	337.1	336.6	336.1	335.6
117.5°	382.7	382.7	383.2	383.6	384.2	384.6	384.7	384.3	384.0	383.6	383.2
120°	413.5	413.7	414.7	415.5	416.4	417.3	417.2	416.1	415.1	413.9	412.9
122.5°	444.8	445.4	445.8	446.3	446.7	447.2	447.0	446.2	445.5	444.6	443.9
125°	491.2	491.9	492.2	492.6	492.9	493.3	493.2	492.7	492.1	491.6	491.1
127.5°	537.0	538.0	538.4	538.8	539.2	539.6	539.2	538.1	536.9	535.8	534.7
130°	566.9	567.6	568.3	568.8	569.3	569.8	569.4	567.9	566.5	565.1	563.7
132.5°	596.5	597.3	597.7	598.1	598.5	599.0	598.4	597.0	595.6	594.2	592.8
135°	640.5	641.2	641.3	641.5	641.7	641.9	641.4	640.4	639.2	638.2	637.1
137.5°	683.5	684.2	683.8	683.3	682.9	682.4	681.8	680.9	679.9	679.1	678.2
140°	711.2	711.3	711.2	711.0	710.8	710.6	710.1	709.3	708.4	707.5	706.6
142.5°	737.7	737.9	737.6	737.3	737.0	736.7	736.1	735.2	734.3	733.5	732.6
145°	776.8	776.9	776.4	775.9	775.4	774.8	774.4	774.1	773.7	773.4	773.0
147.5°	813.4	813.4	812.9	812.4	811.9	811.4	810.9	810.2	809.6	809.0	808.4
150°	836.2	836.2	835.8	835.5	835.1	834.8	834.4	834.0	833.6	833.3	832.9
152.5°	856.7	856.4	856.2	856.0	855.8	855.6	855.2	854.6	854.1	853.6	853.2
155°	886.6	885.9	885.8	885.6	885.3	885.1	885.0	885.0	885.0	885.0	885.0
157.5°	912.7	911.9	911.8	911.7	911.5	911.4	911.4	911.6	911.8	912.0	912.2
160°	928.6	927.8	927.8	927.8	927.8	927.8	927.9	928.3	928.6	929.0	929.3
162.5°	943.7	942.9	942.7	942.6	942.5	942.3	942.5	943.0	943.5	944.0	944.4
165°	962.7	961.7	961.7	961.7	961.7	961.7	961.9	962.5	963.0	963.5	964.0
167.5°	978.3	977.1	977.0	976.8	976.7	976.6	976.8	977.5	978.3	979.0	979.7
170°	986.6	985.3	985.3	985.3	985.3	985.3	985.7	986.4	987.1	987.8	988.6
172.5°	993.4	992.3	992.3	992.3	992.3	992.3	992.7	993.4	994.1	994.8	995.4
175°	1000.7	999.6	999.6	999.6	999.6	999.6	1000.0	1000.7	1001.4	1002.0	1002.7
177.5°	1004.0	1003.2	1003.2	1003.2	1003.2	1003.2	1003.5	1004.0	1004.6	1005.2	1005.7
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1427.1	1430.0	1439.3	1445.9	1453.6	1457.9	1462.4	1465.7	1470.1	1471.2	1487.1
5°	1433.5	1447.2	1471.3	1489.1	1511.2	1535.2	1551.7	1559.2	1579.2	1595.7	1628.7
7.5°	1431.7	1461.0	1497.3	1534.9	1575.4	1612.8	1645.2	1683.6	1711.0	1752.1	1792.6
10°	1430.1	1469.3	1516.0	1564.1	1620.4	1672.6	1719.4	1771.6	1814.9	1872.0	1920.8
12.5°	1425.1	1472.6	1537.4	1594.3	1662.7	1734.7	1804.0	1871.1	1909.5	2004.5	2049.4
15°	1412.9	1469.3	1550.3	1636.9	1731.1	1816.2	1904.2	1974.4	2087.7	2170.9	2223.8
17.5°	1389.6	1468.4	1564.6	1669.1	1783.5	1895.8	1995.5	2101.9	2222.1	2322.8	2429.9
20°	1378.6	1465.1	1572.4	1687.8	1806.6	1933.8	2047.2	2175.0	2306.2	2405.2	2542.6
22.5°	1358.2	1456.3	1571.8	1700.4	1827.6	1959.0	2091.7	2220.6	2372.3	2508.6	2639.4
25°	1324.9	1434.9	1554.5	1698.1	1847.2	1979.1	2137.9	2309.1	2467.1	2642.3	2772.9
27.5°	1290.0	1407.3	1527.2	1660.8	1821.2	1977.8	2177.5	2370.9	2564.0	2715.4	2812.1
30°	1263.0	1377.2	1500.9	1635.6	1794.3	1980.5	2203.8	2414.8	2603.1	2733.0	2787.3
32.5°	1234.0	1349.7	1459.1	1600.3	1769.6	1978.8	2220.4	2440.6	2605.4	2691.8	2681.2
35°	1188.2	1285.1	1391.6	1527.6	1727.0	1966.8	2230.0	2443.0	2544.1	2525.5	2385.3
37.5°	1122.2	1203.7	1308.6	1457.5	1677.5	1941.4	2210.7	2370.6	2364.0	2212.9	2009.8
40°	1081.0	1150.3	1251.4	1408.1	1639.0	1924.9	2180.5	2284.3	2196.4	1985.3	1742.0
42.5°	1027.1	1091.0	1192.0	1353.1	1596.7	1891.3	2122.7	2152.8	1980.7	1738.0	1515.0
45°	943.5	999.9	1104.3	1270.6	1533.2	1818.4	1981.9	1908.3	1676.8	1425.9	1256.2
47.5°	853.7	912.3	1012.8	1183.7	1441.4	1708.5	1786.5	1630.0	1392.3	1188.8	1033.0
50°	797.2	853.5	951.8	1124.3	1379.2	1618.4	1650.6	1448.7	1230.1	1051.5	923.6
52.5°	740.0	793.0	889.7	1062.7	1306.7	1513.9	1494.0	1288.1	1087.1	934.8	834.6
55°	654.9	705.1	797.2	959.4	1181.3	1345.5	1273.4	1076.8	910.6	792.3	716.1
57.5°	578.8	626.8	706.3	852.8	1045.8	1158.6	1066.8	901.2	769.0	678.0	621.1
60°	527.0	569.7	645.3	781.3	949.1	1034.9	944.2	797.9	686.5	613.7	562.8
62.5°	478.2	515.2	585.3	708.8	854.4	926.7	834.9	710.9	616.1	551.6	508.4
65°	404.0	437.8	499.6	595.8	715.4	763.5	684.5	584.1	510.6	462.5	433.6
67.5°	336.5	365.1	418.5	494.2	582.2	617.2	557.0	479.4	424.0	385.4	362.4
70°	291.3	316.1	358.0	423.3	503.0	529.9	473.5	409.6	369.0	338.1	316.8
72.5°	253.5	271.6	309.6	360.1	426.6	447.9	408.6	352.4	314.6	291.3	274.5
75°	193.1	208.2	233.0	273.5	319.5	331.9	302.4	267.3	241.9	225.4	212.4
77.5°	139.3	150.4	168.2	193.3	225.1	236.3	217.5	194.2	175.6	164.5	157.2
80°	105.1	114.1	129.2	149.8	169.1	175.2	164.2	146.3	133.3	127.1	121.0
82.5°	77.7	82.7	91.8	105.8	119.1	126.3	116.9	106.2	99.3	93.6	91.3
85°	39.2	41.9	46.0	51.5	59.8	62.5	59.1	56.4	52.2	48.8	48.8
87.5°	14.8	15.1	17.2	18.6	21.2	23.3	23.2	22.6	22.5	22.1	21.7
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4
92.5°	20.3	21.5	22.7	23.8	25.1	26.5	27.8	29.0	30.3	30.9	31.4
95°	47.8	49.1	50.3	51.5	52.8	54.2	55.6	57.1	58.5	59.2	59.8
97.5°	83.6	84.5	85.4	86.4	87.4	88.4	89.4	90.4	91.4	92.2	93.0
100°	108.5	109.5	110.6	111.6	112.6	113.4	114.3	115.2	116.0	116.6	117.1
102.5°	136.4	137.0	137.7	138.4	139.3	140.4	141.6	142.7	143.9	144.4	144.9
105°	178.0	178.3	178.7	179.0	180.1	181.6	183.2	184.8	186.3	186.3	186.3
107.5°	226.5	226.7	226.9	227.1	227.5	228.2	228.8	229.4	230.0	230.7	231.2
110°	256.9	257.3	257.6	258.0	258.3	258.7	259.0	259.4	259.7	260.4	261.2



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.4	288.6	288.8	289.0	289.1	289.2	289.3	289.4	289.4	290.3	291.1
115°	336.1	336.6	337.1	337.7	337.8	337.4	337.1	336.7	336.4	336.5	336.7
117.5°	383.6	384.0	384.3	384.7	384.6	384.2	383.6	383.2	382.7	382.7	382.7
120°	413.9	415.1	416.1	417.2	417.3	416.4	415.5	414.7	413.7	413.5	413.3
122.5°	444.6	445.5	446.2	447.0	447.2	446.7	446.3	445.8	445.4	444.8	444.4
125°	491.6	492.1	492.7	493.2	493.3	492.9	492.6	492.2	491.9	491.2	490.5
127.5°	535.8	536.9	538.1	539.2	539.6	539.2	538.8	538.4	538.0	537.0	536.0
130°	565.1	566.5	567.9	569.4	569.8	569.3	568.8	568.3	567.6	566.9	566.3
132.5°	594.2	595.6	597.0	598.4	599.0	598.5	598.1	597.7	597.3	596.5	595.7
135°	638.2	639.2	640.4	641.4	641.9	641.7	641.5	641.3	641.2	640.5	639.7
137.5°	679.1	679.9	680.9	681.8	682.4	682.9	683.3	683.8	684.2	683.5	682.8
140°	707.5	708.4	709.3	710.1	710.6	710.8	711.0	711.2	711.3	711.2	711.0
142.5°	733.5	734.3	735.2	736.1	736.7	737.0	737.3	737.6	737.9	737.7	737.6
145°	773.4	773.7	774.1	774.4	774.8	775.4	775.9	776.4	776.9	776.8	776.6
147.5°	809.0	809.6	810.2	810.9	811.4	811.9	812.4	812.9	813.4	813.4	813.4
150°	833.3	833.6	834.0	834.4	834.8	835.1	835.5	835.8	836.2	836.2	836.2
152.5°	853.6	854.1	854.6	855.2	855.6	855.8	856.0	856.2	856.4	856.7	856.9
155°	885.0	885.0	885.0	885.0	885.1	885.3	885.6	885.8	885.9	886.6	887.3
157.5°	912.0	911.8	911.6	911.4	911.4	911.5	911.7	911.8	911.9	912.7	913.4
160°	929.0	928.6	928.3	927.9	927.8	927.8	927.8	927.8	927.8	928.6	929.5
162.5°	944.0	943.5	943.0	942.5	942.3	942.5	942.6	942.7	942.9	943.7	944.6
165°	963.5	963.0	962.5	961.9	961.7	961.7	961.7	961.7	961.7	962.7	963.8
167.5°	979.0	978.3	977.5	976.8	976.6	976.7	976.8	977.0	977.1	978.3	979.4
170°	987.8	987.1	986.4	985.7	985.3	985.3	985.3	985.3	985.3	986.6	987.8
172.5°	994.8	994.1	993.4	992.7	992.3	992.3	992.3	992.3	992.3	993.4	994.5
175°	1002.0	1001.4	1000.7	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7	1001.7
177.5°	1005.2	1004.6	1004.0	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0	1004.9
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4	1418.4
2.5°	1492.6	1493.2	1499.2	1503.6	1501.4	1504.2	1505.2
5°	1630.7	1655.5	1668.5	1678.2	1678.8	1679.5	1685.1
7.5°	1826.5	1853.1	1872.5	1901.9	1910.7	1920.8	1917.8
10°	1969.5	2008.7	2042.4	2060.2	2079.5	2107.7	2085.0
12.5°	2103.1	2172.5	2223.8	2251.6	2269.7	2275.3	2264.2
15°	2323.4	2414.2	2463.0	2461.5	2523.5	2550.2	2508.3
17.5°	2525.5	2609.2	2676.2	2710.6	2762.2	2773.6	2768.3
20°	2649.2	2740.6	2792.8	2851.9	2878.7	2902.8	2906.9
22.5°	2755.8	2837.9	2894.0	2943.2	2965.6	2977.0	2983.8
25°	2865.6	2930.2	2964.0	2981.1	2987.3	2985.9	2977.0
27.5°	2858.1	2863.1	2825.9	2789.6	2756.9	2720.3	2707.5
30°	2783.9	2726.1	2623.0	2564.7	2478.7	2410.7	2438.2
32.5°	2588.7	2473.8	2358.0	2230.4	2124.7	2094.6	2064.4
35°	2209.4	2007.3	1889.2	1751.7	1696.7	1641.7	1604.0
37.5°	1787.5	1631.1	1491.0	1401.1	1345.9	1311.2	1292.5
40°	1545.5	1404.6	1289.2	1216.4	1174.5	1135.3	1129.7
42.5°	1352.5	1221.5	1134.7	1076.7	1036.4	1019.8	1007.7
45°	1107.8	1016.3	958.0	916.8	889.9	879.6	865.9
47.5°	937.7	873.0	829.2	801.1	780.9	773.3	772.1
50°	842.5	788.9	756.6	734.6	718.8	716.1	705.1
52.5°	771.0	724.6	699.4	680.2	668.8	661.1	657.8
55°	669.3	638.4	615.7	604.7	595.8	588.2	588.2
57.5°	585.6	559.8	544.8	535.4	532.7	527.4	523.9
60°	533.9	512.0	500.3	492.0	486.6	487.3	481.0
62.5°	483.4	469.1	458.0	449.7	443.1	443.2	443.6
65°	411.6	400.6	392.4	389.6	385.6	380.7	382.1
67.5°	348.8	338.5	332.0	327.4	326.0	323.4	327.4
70°	303.8	296.2	291.3	287.2	285.9	286.6	290.0
72.5°	262.5	257.1	254.0	252.1	249.0	249.1	251.6
75°	206.1	202.1	199.2	197.2	196.5	196.5	196.5
77.5°	151.5	150.5	149.3	146.2	146.3	147.2	147.3
80°	119.6	117.5	116.8	115.4	113.4	112.0	115.4
82.5°	89.4	87.3	86.5	86.3	83.1	82.9	85.7
85°	48.1	46.0	46.8	46.0	46.0	45.3	45.3
87.5°	21.2	20.8	20.4	21.0	20.5	20.1	21.2
90°	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	32.0	32.5	32.7	32.5	32.3	32.1	31.9
95°	60.5	61.2	61.6	61.6	61.6	61.6	61.6
97.5°	93.8	94.6	95.0	94.9	94.9	94.8	94.7
100°	117.6	118.2	118.7	119.0	119.3	119.7	120.0
102.5°	145.4	145.9	146.2	146.1	146.0	146.0	145.9
105°	186.3	186.3	186.5	186.8	187.2	187.5	187.9
107.5°	231.8	232.4	232.5	232.3	232.1	231.9	231.7
110°	261.9	262.6	262.8	262.4	262.1	261.7	261.4



TEST NUMBER: P332019-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.0	292.9	293.2	293.2	293.1	293.0	293.0
115°	336.9	337.1	337.1	336.9	336.7	336.5	336.4
117.5°	382.6	382.6	382.3	381.9	381.4	380.9	380.4
120°	413.2	413.0	412.7	412.4	412.0	411.7	411.3
122.5°	443.9	443.5	443.0	442.5	442.0	441.5	441.0
125°	489.8	489.1	488.4	487.7	487.0	486.3	485.5
127.5°	535.0	534.1	533.2	532.4	531.6	530.8	530.0
130°	565.6	564.9	563.9	562.7	561.5	560.3	559.0
132.5°	594.8	594.0	593.1	592.2	591.2	590.3	589.4
135°	639.0	638.3	637.8	637.4	637.1	636.7	636.4
137.5°	682.1	681.3	680.5	679.9	679.2	678.6	677.9
140°	710.8	710.6	710.0	708.7	707.5	706.3	705.1
142.5°	737.4	737.2	736.7	735.7	734.8	733.8	732.9
145°	776.4	776.2	775.8	775.1	774.4	773.7	773.0
147.5°	813.4	813.4	812.8	811.8	810.7	809.7	808.7
150°	836.2	836.2	835.7	834.6	833.5	832.4	831.4
152.5°	857.2	857.5	857.2	856.3	855.4	854.4	853.5
155°	888.0	888.7	888.4	887.2	886.0	884.7	883.5
157.5°	914.1	914.8	914.7	913.8	912.8	911.8	910.8
160°	930.4	931.2	931.3	930.6	929.9	929.2	928.5
162.5°	945.5	946.4	946.2	945.1	944.0	942.9	941.8
165°	964.8	965.9	965.8	964.6	963.3	962.1	960.9
167.5°	980.4	981.5	981.5	980.4	979.4	978.3	977.1
170°	989.1	990.3	990.3	989.1	987.8	986.6	985.3
172.5°	995.6	996.6	996.6	995.3	994.1	992.9	991.7
175°	1002.7	1003.8	1003.7	1002.5	1001.3	1000.0	998.8
177.5°	1005.7	1006.5	1006.5	1005.5	1004.5	1003.6	1002.6
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

(END OF REPORT)