

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332026-840

Luminaire Tested: **S123DIP-S1000D805U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332026-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1000D805U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7096.9 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																				
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	57	55	54	49																				
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45	41																				
3	83	73	66	60	77	68	62	56	60	55	50	52	48	44	44	41	39	35																				
4	76	65	57	50	70	61	53	48	53	47	43	46	42	38	39	36	33	30																				
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29	26																				
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26	23																				
7	59	47	39	33	55	44	37	31	39	33	29	34	29	26	29	26	23	20																				
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18																				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18	16																				
10	48	36	28	23	45	34	27	22	30	24	21	26	22	19	23	19	17	15																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17206	17206	17206
5°	17286	17049	17168
10°	17171	16901	17006
15°	16971	16710	16741
20°	16736	16436	16452
25°	16422	16112	16079
30°	16075	15751	15631
35°	15713	15369	15172
40°	15336	14948	14716
45°	14918	14562	14206
50°	14502	14086	13695
55°	13955	13594	13181
60°	13403	13020	12605
65°	12918	12394	12006
70°	12198	11679	11160
75°	11146	10746	10289
80°	10054	9627	9540
85°	8830	8497	8139



TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	2.1
10°-20°	425.2	6.0
20°-30°	628.0	8.8
30°-40°	733.6	10.3
40°-50°	737.6	10.4
50°-60°	647.9	9.1
60°-70°	482.7	6.8
70°-80°	275.0	3.9
80°-90°	82.0	1.2
90°-100°	217.1	3.1
100°-110°	614.6	8.7
110°-120°	604.6	8.5
120°-130°	482.3	6.8
130°-140°	380.2	5.4
140°-150°	283.8	4.0
150°-160°	197.8	2.8
160°-170°	116.2	1.6
170°-180°	37.8	0.5
0°-30°	1203.8	17.0
0°-40°	1937.4	27.3
0°-60°	3322.8	46.8
0°-90°	4162.5	58.7
90°-120°	1436.3	20.2
90°-150°	2582.6	36.4
90°-180°	2934.0	41.3
0°-180°	7096.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1598	1598	1598	1598	1598	
5°	1600	1593	1578	1591	1589	152
15°	1523	1517	1500	1509	1502	429
25°	1383	1374	1357	1358	1354	637
35°	1196	1187	1170	1162	1155	748
45°	980	974	957	941	933	756
55°	744	741	724	710	702	666
65°	507	500	487	476	471	500
75°	268	263	258	252	247	287
85°	72	69	69	66	66	78
90°	2	10	20	22	23	6
95°	27	87	468	137	92	29
105°	92	135	635	1110	1004	97
115°	162	202	486	1065	1221	160
125°	225	266	453	821	963	200
135°	264	315	447	676	781	204
145°	301	345	441	555	610	189
155°	342	369	427	486	506	157
165°	373	384	409	434	441	105
175°	389	390	392	398	397	37
180°	390	390	390	390	390	



TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1604.0	1603.1	1602.0	1601.0	1600.1	1598.2	1595.6	1592.9	1590.2	1587.5	1589.9
5°	1599.8	1598.3	1596.8	1595.3	1593.8	1591.3	1588.0	1584.6	1581.2	1577.9	1580.9
7.5°	1584.2	1582.7	1581.1	1579.6	1578.1	1575.6	1572.2	1568.6	1565.2	1561.7	1564.4
10°	1571.0	1569.5	1567.9	1566.4	1564.9	1562.2	1558.2	1554.2	1550.2	1546.3	1549.0
12.5°	1553.4	1552.2	1550.8	1549.5	1548.3	1545.8	1542.1	1538.3	1534.6	1530.9	1532.9
15°	1522.9	1521.7	1520.5	1519.2	1518.0	1515.4	1511.5	1507.5	1503.5	1499.5	1502.0
17.5°	1487.4	1485.8	1484.3	1482.7	1481.1	1478.3	1474.3	1470.4	1466.4	1462.4	1464.1
20°	1461.1	1459.3	1457.4	1455.5	1453.7	1450.8	1446.8	1442.9	1439.0	1434.9	1436.1
22.5°	1431.4	1429.6	1427.7	1425.8	1424.0	1421.2	1417.1	1413.2	1409.3	1405.2	1406.2
25°	1382.7	1380.9	1379.1	1377.3	1375.3	1372.5	1368.5	1364.5	1360.6	1356.6	1356.9
27.5°	1330.8	1329.0	1327.2	1325.4	1323.6	1320.6	1316.4	1312.1	1307.8	1303.5	1303.7
30°	1293.3	1291.8	1290.3	1288.8	1287.3	1284.3	1280.1	1275.8	1271.5	1267.3	1267.3
32.5°	1256.0	1253.9	1251.9	1249.9	1247.9	1245.3	1241.9	1238.7	1235.4	1232.0	1230.3
35°	1195.8	1194.0	1192.1	1190.3	1188.4	1185.6	1181.5	1177.6	1173.7	1169.6	1167.8
37.5°	1134.2	1131.9	1129.5	1127.2	1124.9	1121.8	1117.7	1113.7	1109.6	1105.6	1103.4
40°	1091.4	1089.4	1087.6	1085.8	1084.0	1081.0	1076.6	1072.4	1068.1	1063.8	1061.4
42.5°	1048.4	1046.3	1044.3	1042.2	1040.2	1036.9	1032.7	1028.4	1024.1	1019.9	1017.4
45°	980.0	978.8	977.5	976.3	975.1	972.5	968.6	964.5	960.6	956.6	953.0
47.5°	912.1	910.3	908.6	906.8	905.0	902.2	898.6	894.8	891.1	887.4	883.7
50°	866.0	864.3	862.8	861.3	859.8	857.1	853.0	849.1	845.2	841.2	837.8
52.5°	817.5	816.5	815.5	814.5	813.3	810.7	806.6	802.3	798.1	793.9	791.0
55°	743.6	743.3	743.0	742.7	742.4	740.2	736.3	732.3	728.3	724.4	720.9
57.5°	673.2	672.2	671.2	670.1	669.0	666.9	663.8	660.6	657.4	654.3	651.3
60°	622.6	622.3	622.0	621.7	621.4	619.5	615.7	612.1	608.4	604.8	602.0
62.5°	577.5	576.7	575.9	575.1	574.4	572.2	568.5	564.8	561.2	557.4	554.7
65°	507.2	505.6	504.1	502.6	501.1	498.8	495.7	492.7	489.6	486.6	484.1
67.5°	432.7	431.3	430.0	428.7	427.3	425.5	423.1	420.8	418.5	416.2	414.0
70°	387.6	385.8	384.0	382.1	380.3	378.4	376.6	374.8	372.9	371.1	369.0
72.5°	340.3	339.0	337.6	336.3	335.0	333.3	331.1	329.1	327.0	324.9	323.1
75°	268.0	266.8	265.6	264.4	263.2	262.1	261.2	260.2	259.3	258.4	256.9
77.5°	204.0	203.3	202.6	202.0	201.3	200.4	199.3	198.2	197.1	196.0	195.0
80°	162.2	161.3	160.4	159.5	158.5	157.7	157.1	156.5	155.9	155.3	155.0
82.5°	121.5	121.3	121.2	121.0	120.8	120.6	120.5	120.4	120.3	120.2	119.6
85°	71.5	70.9	70.3	69.7	69.1	68.8	68.8	68.8	68.8	68.8	68.1
87.5°	28.9	28.5	28.1	27.8	27.4	27.3	27.5	27.7	27.9	28.2	27.8
90°	1.6	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0
92.5°	9.8	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6
95°	26.9	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8
97.5°	45.7	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3
100°	58.5	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2
102.5°	71.7	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6
105°	91.6	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4
107.5°	112.7	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1
110°	127.9	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0



TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.8	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9
115°	161.9	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2
117.5°	181.9	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5
120°	195.8	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9
122.5°	207.8	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3
125°	225.0	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7
127.5°	238.1	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3
130°	246.3	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4
132.5°	252.7	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2
135°	263.7	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4
137.5°	274.1	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1
140°	281.0	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5
142.5°	288.6	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4
145°	300.8	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7
147.5°	313.2	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0
150°	321.3	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6
152.5°	329.5	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5
155°	341.8	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9
157.5°	351.6	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4
160°	359.2	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7
162.5°	365.0	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0
165°	373.4	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3
167.5°	379.9	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9
170°	383.7	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4
172.5°	386.3	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0
175°	389.2	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9
177.5°	390.6	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5	1598.5
2.5°	1592.4	1594.9	1597.3	1598.4	1598.1	1597.9	1597.6	1597.4
5°	1584.0	1587.0	1590.1	1591.3	1590.7	1590.1	1589.5	1588.9
7.5°	1567.2	1569.9	1572.7	1573.9	1573.5	1573.2	1572.8	1572.4
10°	1551.8	1554.5	1557.3	1558.3	1557.7	1557.1	1556.5	1555.9
12.5°	1534.9	1536.9	1538.9	1539.7	1539.4	1539.0	1538.6	1538.3
15°	1504.4	1506.8	1509.3	1509.6	1507.8	1505.9	1504.1	1502.3
17.5°	1465.8	1467.5	1469.3	1469.8	1469.2	1468.4	1467.7	1467.1
20°	1437.3	1438.7	1439.9	1440.0	1439.1	1438.1	1437.2	1436.3
22.5°	1407.2	1408.2	1409.2	1409.1	1408.0	1406.7	1405.6	1404.4
25°	1357.2	1357.6	1357.9	1357.6	1356.6	1355.6	1354.7	1353.8
27.5°	1304.0	1304.2	1304.5	1304.0	1302.9	1301.7	1300.6	1299.4
30°	1267.3	1267.3	1267.3	1266.2	1264.0	1261.9	1259.8	1257.6
32.5°	1228.6	1227.0	1225.3	1223.8	1222.6	1221.4	1220.3	1219.1
35°	1166.0	1164.2	1162.4	1160.6	1159.1	1157.6	1156.1	1154.6
37.5°	1101.3	1099.0	1096.8	1095.2	1094.3	1093.3	1092.3	1091.4
40°	1058.9	1056.5	1054.1	1052.2	1051.0	1049.8	1048.5	1047.3
42.5°	1014.9	1012.5	1010.1	1008.2	1007.0	1005.8	1004.6	1003.4
45°	949.3	945.6	942.0	939.4	937.9	936.3	934.8	933.2
47.5°	880.1	876.6	872.9	870.5	869.1	867.8	866.5	865.1
50°	834.5	831.1	827.7	825.2	823.3	821.4	819.6	817.8
52.5°	788.1	785.3	782.4	780.0	778.2	776.4	774.6	772.7
55°	717.6	714.3	710.9	708.4	706.9	705.4	703.9	702.4
57.5°	648.2	645.3	642.3	639.9	638.1	636.3	634.6	632.8
60°	599.3	596.5	593.8	591.7	590.1	588.5	587.0	585.5
62.5°	552.0	549.3	546.4	544.6	543.5	542.5	541.5	540.5
65°	481.7	479.2	476.8	475.1	474.2	473.3	472.3	471.4
67.5°	411.9	409.8	407.7	406.0	404.7	403.3	402.0	400.8
70°	366.8	364.7	362.5	360.7	359.2	357.7	356.2	354.6
72.5°	321.1	319.2	317.3	316.0	315.2	314.4	313.7	312.9
75°	255.4	253.8	252.3	251.1	250.1	249.2	248.3	247.4
77.5°	193.9	192.9	191.9	191.4	191.4	191.4	191.4	191.4
80°	154.7	154.4	154.1	153.9	153.9	153.9	153.9	153.9
82.5°	119.1	118.5	118.0	117.5	117.2	117.0	116.8	116.5
85°	67.5	66.9	66.2	65.9	65.9	65.9	65.9	65.9
87.5°	27.7	27.6	27.5	27.7	27.5	27.7	27.9	27.7
90°	19.7	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	66.4	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	284.3	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	708.5	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	930.9	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1004.7	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1026.4	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	964.2	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	904.8	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1



TEST NUMBER: P332026-840

CATALOG NUMBER: S123DIP-S1000D805U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	846.1	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	768.2	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	711.9	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	682.2	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	658.8	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	627.6	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	600.6	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	583.5	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	567.6	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	546.3	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	526.9	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	515.5	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	504.8	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	491.9	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	481.3	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	473.7	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	466.8	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	456.4	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	445.2	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	439.0	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	431.4	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	421.6	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	413.0	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	407.4	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	402.3	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	395.6	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.3	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)