

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331908

Luminaire Tested: **S123DIP-S340D1195U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331908
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1195U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5512.4 lumens
Efficiency: N/A
Efficacy: 130.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	16	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	0.9
10°-20°	144.1	2.6
20°-30°	212.9	3.9
30°-40°	248.7	4.5
40°-50°	250.0	4.5
50°-60°	219.6	4.0
60°-70°	163.6	3.0
70°-80°	93.2	1.7
80°-90°	31.1	0.6
90°-100°	96.4	1.7
100°-110°	288.4	5.2
110°-120°	490.5	8.9
120°-130°	645.2	11.7
130°-140°	725.2	13.2
140°-150°	712.8	12.9
150°-160°	600.1	10.9
160°-170°	399.5	7.2
170°-180°	139.9	2.5
0°-30°	408.1	7.4
0°-40°	656.8	11.9
0°-60°	1126.5	20.4
0°-90°	1414.5	25.7
90°-120°	875.3	15.9
90°-150°	2958.5	53.7
90°-180°	4098.0	74.3
0°-180°	5512.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	1	13	28	32	35	6
95°	69	77	86	90	91	77
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	723	726	724	719	715	644
135°	938	944	943	939	936	722
145°	1138	1140	1143	1142	1138	710
155°	1302	1303	1304	1308	1300	599
165°	1419	1415	1415	1421	1414	400
175°	1476	1471	1471	1477	1470	140
180°	1479	1479	1479	1479	1479	



TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.9	10.2	10.5	10.7	11.0	11.4	12.0	12.6	13.2	13.8	13.9
90°	1.2	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9
92.5°	28.1	29.9	31.6	33.4	35.1	37.0	38.9	40.8	42.7	44.6	45.4
95°	68.6	70.4	72.2	74.0	75.8	77.7	79.8	81.8	83.9	86.0	87.0
97.5°	121.8	123.1	124.5	125.8	127.1	128.6	130.1	131.6	133.0	134.5	135.7
100°	158.0	159.6	161.1	162.7	164.2	165.6	166.9	168.2	169.5	170.8	171.6
102.5°	199.8	200.8	201.7	202.6	203.6	204.9	206.6	208.3	210.0	211.7	212.5
105°	261.4	261.9	262.5	263.0	263.5	264.9	267.2	269.6	271.9	274.2	274.2
107.5°	333.0	333.3	333.6	333.9	334.2	334.9	335.8	336.7	337.6	338.6	339.4
110°	377.6	378.1	378.6	379.2	379.7	380.2	380.7	381.2	381.7	382.3	383.3



TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	424.1	424.4	424.7	425.0	425.3	425.5	425.6	425.7	425.8	425.9	427.2
115°	493.8	494.6	495.3	496.1	496.9	497.0	496.5	496.0	495.5	495.0	495.2
117.5°	564.0	564.5	565.0	565.5	566.0	566.0	565.3	564.6	564.0	563.3	563.2
120°	607.7	609.2	610.8	612.3	613.9	614.0	612.7	611.4	610.1	608.8	608.6
122.5°	653.2	654.3	655.5	656.6	657.8	658.0	657.3	656.6	656.0	655.3	654.6
125°	722.7	723.5	724.2	725.0	725.8	725.9	725.4	724.9	724.4	723.9	722.8
127.5°	786.8	788.5	790.1	791.8	793.4	794.0	793.4	792.8	792.3	791.7	790.3
130°	829.6	831.6	833.7	835.8	837.8	838.5	837.7	836.9	836.2	835.4	834.4
132.5°	872.3	874.4	876.5	878.5	880.6	881.4	880.8	880.2	879.6	879.1	877.8
135°	937.6	939.2	940.7	942.3	943.8	944.5	944.2	944.0	943.7	943.4	942.4
137.5°	998.1	999.3	1000.6	1001.9	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8
140°	1039.9	1041.2	1042.5	1043.8	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6
142.5°	1078.0	1079.3	1080.6	1081.9	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6
145°	1137.5	1138.0	1138.5	1139.0	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0
147.5°	1189.5	1190.5	1191.4	1192.3	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0
150°	1225.8	1226.3	1226.8	1227.3	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4
152.5°	1255.5	1256.3	1257.0	1257.7	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6
155°	1302.5	1302.5	1302.5	1302.5	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7
157.5°	1342.4	1342.1	1341.8	1341.5	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1
160°	1367.5	1367.0	1366.5	1366.0	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5
162.5°	1389.8	1389.1	1388.4	1387.7	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8
165°	1418.7	1417.9	1417.1	1416.3	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7
167.5°	1441.7	1440.6	1439.6	1438.6	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5
170°	1454.7	1453.6	1452.6	1451.6	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8
172.5°	1464.9	1463.9	1462.8	1461.8	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9
175°	1475.6	1474.6	1473.5	1472.5	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5
177.5°	1480.0	1479.2	1478.4	1477.5	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	14.0	14.1	14.3	14.4	14.5	14.6	14.7	14.8
90°	30.0	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	46.3	47.1	47.9	48.2	47.9	47.6	47.2	46.9
95°	88.0	89.1	90.1	90.6	90.6	90.6	90.6	90.6
97.5°	136.9	138.1	139.3	139.8	139.7	139.6	139.5	139.4
100°	172.3	173.1	173.9	174.5	175.1	175.6	176.1	176.6
102.5°	213.2	214.0	214.8	215.1	215.0	214.9	214.8	214.7
105°	274.2	274.2	274.2	274.5	275.0	275.5	276.0	276.5
107.5°	340.2	341.1	341.9	342.1	341.8	341.5	341.2	340.9
110°	384.3	385.4	386.4	386.6	386.1	385.6	385.1	384.6



TEST NUMBER: P331908

CATALOG NUMBER: S123DIP-S340D1195U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	428.4	429.7	430.9	431.5	431.4	431.3	431.2	431.1
115°	495.5	495.7	496.0	496.0	495.7	495.5	495.2	495.0
117.5°	563.2	563.1	563.1	562.7	562.0	561.2	560.5	559.8
120°	608.3	608.1	607.8	607.4	606.9	606.4	605.9	605.3
122.5°	654.0	653.3	652.6	651.9	651.2	650.5	649.7	649.0
125°	721.8	720.8	719.7	718.7	717.7	716.6	715.6	714.6
127.5°	788.8	787.4	785.9	784.6	783.4	782.2	781.0	779.9
130°	833.3	832.3	831.3	829.8	828.0	826.2	824.4	822.6
132.5°	876.6	875.4	874.1	872.8	871.4	870.0	868.6	867.2
135°	941.4	940.3	939.3	938.5	938.0	937.5	937.0	936.5
137.5°	1004.7	1003.6	1002.5	1001.5	1000.5	999.6	998.6	997.6
140°	1046.3	1046.1	1045.8	1044.8	1043.0	1041.2	1039.4	1037.6
142.5°	1085.4	1085.1	1084.9	1084.0	1082.6	1081.2	1079.9	1078.5
145°	1142.8	1142.5	1142.3	1141.6	1140.6	1139.5	1138.5	1137.5
147.5°	1197.0	1197.0	1197.0	1196.2	1194.6	1193.1	1191.5	1190.0
150°	1230.4	1230.4	1230.4	1229.7	1228.1	1226.6	1225.0	1223.5
152.5°	1261.0	1261.4	1261.8	1261.4	1260.0	1258.7	1257.3	1256.0
155°	1305.7	1306.7	1307.8	1307.4	1305.6	1303.8	1302.0	1300.1
157.5°	1344.1	1345.2	1346.3	1346.1	1344.7	1343.2	1341.8	1340.3
160°	1367.8	1369.1	1370.4	1370.5	1369.5	1368.4	1367.4	1366.4
162.5°	1390.1	1391.4	1392.7	1392.5	1390.8	1389.2	1387.5	1385.9
165°	1418.3	1419.8	1421.4	1421.2	1419.4	1417.6	1415.8	1414.0
167.5°	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9
170°	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0
172.5°	1463.5	1465.1	1466.7	1466.6	1464.7	1462.9	1461.1	1459.3
175°	1474.0	1475.6	1477.1	1477.0	1475.2	1473.4	1471.6	1469.8
177.5°	1478.8	1480.0	1481.2	1481.1	1479.7	1478.2	1476.8	1475.4
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1

(END OF REPORT)