

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331871

Luminaire Tested: **S123DIP-S340D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331871
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D365U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2861.9 lumens
Efficiency: N/A
Efficacy: 141.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49																			
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41																			
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35																			
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29																			
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25																			
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22																			
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	25	22	19																			
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17																			
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15																			
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	22	18	16	14																			
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	1.8
10°-20°	144.1	5.0
20°-30°	212.9	7.4
30°-40°	248.7	8.7
40°-50°	250.0	8.7
50°-60°	219.6	7.7
60°-70°	163.6	5.7
70°-80°	93.2	3.3
80°-90°	28.1	1.0
90°-100°	17.3	0.6
100°-110°	82.4	2.9
110°-120°	198.0	6.9
120°-130°	252.1	8.8
130°-140°	269.3	9.4
140°-150°	251.9	8.8
150°-160°	203.2	7.1
160°-170°	131.1	4.6
170°-180°	45.2	1.6
0°-30°	408.1	14.3
0°-40°	656.8	22.9
0°-60°	1126.5	39.4
0°-90°	1411.4	49.3
90°-120°	297.7	10.4
90°-150°	1071.0	37.4
90°-180°	1450.0	50.7
0°-180°	2861.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	0	4	8	10	11	2
95°	22	8	11	13	13	27
105°	105	107	77	18	16	112
115°	198	200	203	206	208	195
125°	278	281	283	283	284	249
135°	347	349	350	351	350	267
145°	400	402	403	404	404	250
155°	441	440	440	442	440	203
165°	465	464	463	466	464	131
175°	476	474	474	476	474	45
180°	476	476	476	476	476	



TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.8	9.7	9.6	9.5	9.4	9.4	9.5	9.7	9.8	9.9	9.9
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.4	6.4	7.5	8.5	8.8
92.5°	6.6	6.4	6.1	5.9	5.7	6.0	6.7	7.5	8.3	9.0	9.5
95°	21.6	18.3	15.1	11.9	8.7	7.5	8.4	9.2	10.1	11.0	11.5
97.5°	43.3	41.9	40.4	39.0	37.5	34.0	28.3	22.7	17.0	11.4	12.0
100°	59.7	61.3	62.9	64.4	66.0	60.7	48.4	36.2	23.9	11.7	12.3
102.5°	78.4	79.5	80.6	81.8	82.9	76.8	63.4	50.0	36.6	23.3	21.3
105°	105.3	106.2	107.0	107.9	108.8	105.7	98.6	91.5	84.5	77.4	63.5
107.5°	133.7	134.4	135.1	135.8	136.5	137.4	138.5	139.6	140.7	141.8	131.6
110°	152.7	153.3	153.9	154.5	155.2	155.9	156.8	157.6	158.5	159.4	156.8



TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.7	171.3	171.9	172.4	173.0	173.7	174.6	175.5	176.3	177.2	177.2
115°	197.5	198.0	198.5	198.9	199.4	200.0	200.7	201.4	202.1	202.8	203.6
117.5°	223.5	224.1	224.6	225.2	225.8	226.3	226.6	227.0	227.4	227.7	228.3
120°	239.6	240.3	241.0	241.7	242.4	242.9	243.1	243.4	243.6	243.8	244.5
122.5°	256.0	256.6	257.1	257.7	258.3	258.7	259.0	259.3	259.6	259.9	260.4
125°	278.5	279.1	279.7	280.3	281.0	281.4	281.8	282.1	282.4	282.7	282.9
127.5°	300.2	300.9	301.5	302.1	302.7	303.2	303.6	304.0	304.4	304.7	305.0
130°	313.8	314.4	315.0	315.7	316.3	316.8	317.1	317.4	317.7	318.0	318.3
132.5°	326.8	327.4	328.1	328.7	329.3	329.7	330.0	330.3	330.5	330.8	331.1
135°	346.7	347.1	347.6	348.1	348.5	348.9	349.2	349.6	349.9	350.2	350.4
137.5°	363.6	364.2	364.8	365.4	366.0	366.4	366.6	366.7	366.9	367.1	367.5
140°	374.9	375.4	375.9	376.3	376.8	377.2	377.4	377.6	377.9	378.1	378.4
142.5°	385.4	385.9	386.3	386.8	387.3	387.6	387.9	388.1	388.3	388.6	388.8
145°	400.0	400.6	401.1	401.7	402.2	402.6	402.7	402.9	403.0	403.2	403.4
147.5°	413.8	414.2	414.5	414.9	415.2	415.5	415.7	415.8	416.0	416.1	416.3
150°	422.3	422.5	422.7	423.0	423.2	423.4	423.6	423.7	423.9	424.0	424.2
152.5°	429.9	430.0	430.1	430.2	430.3	430.5	430.5	430.6	430.7	430.8	431.1
155°	440.7	440.5	440.3	440.2	440.0	440.0	440.1	440.1	440.2	440.3	440.7
157.5°	449.0	449.0	449.0	448.9	448.9	448.9	448.8	448.7	448.6	448.6	449.0
160°	454.1	454.0	453.9	453.8	453.8	453.7	453.6	453.5	453.5	453.4	453.8
162.5°	458.9	458.7	458.5	458.3	458.1	457.9	457.8	457.8	457.7	457.6	458.1
165°	464.7	464.4	464.2	464.0	463.7	463.6	463.5	463.4	463.3	463.3	463.9
167.5°	469.2	468.9	468.6	468.3	467.9	467.8	467.8	467.8	467.8	467.8	468.4
170°	471.7	471.4	471.1	470.8	470.5	470.3	470.3	470.3	470.3	470.3	471.0
172.5°	473.4	473.1	472.7	472.3	471.9	471.8	471.8	471.9	472.0	472.0	472.7
175°	475.6	475.2	474.8	474.5	474.1	473.9	474.0	474.1	474.1	474.2	474.8
177.5°	476.2	475.9	475.6	475.3	474.9	474.8	474.9	474.9	475.0	475.1	475.6
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6



TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	9.9	9.8	9.8	9.8	9.9	9.9	9.9	9.9
90°	9.1	9.4	9.7	10.0	10.1	10.3	10.4	10.6
92.5°	10.1	10.6	11.1	11.4	11.4	11.5	11.6	11.7
95°	12.1	12.6	13.2	13.4	13.4	13.4	13.4	13.4
97.5°	12.6	13.3	13.9	14.2	14.3	14.4	14.5	14.6
100°	12.9	13.5	14.2	14.5	14.6	14.7	14.8	14.8
102.5°	19.4	17.4	15.5	14.6	14.7	14.8	15.0	15.1
105°	49.6	35.7	21.8	14.9	15.1	15.2	15.4	15.5
107.5°	121.5	111.3	101.1	90.7	80.3	69.8	59.3	48.8
110°	154.2	151.6	149.0	142.1	130.9	119.6	108.4	97.2



TEST NUMBER: P331871

CATALOG NUMBER: S123DIP-S340D365U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	177.3	177.3	177.4	176.2	173.8	171.5	169.1	166.7
115°	204.4	205.2	206.0	206.5	206.8	207.2	207.5	207.8
117.5°	229.0	229.6	230.2	230.6	230.6	230.7	230.8	230.8
120°	245.1	245.7	246.3	246.7	246.7	246.7	246.7	246.7
122.5°	260.8	261.3	261.7	261.9	262.0	262.1	262.1	262.2
125°	283.0	283.2	283.3	283.5	283.6	283.8	284.0	284.1
127.5°	305.2	305.5	305.8	305.8	305.6	305.5	305.3	305.2
130°	318.7	319.0	319.3	319.4	319.2	319.1	318.9	318.7
132.5°	331.4	331.7	332.0	332.1	331.8	331.6	331.4	331.2
135°	350.7	350.9	351.1	351.1	350.9	350.7	350.4	350.2
137.5°	367.8	368.2	368.6	368.7	368.5	368.4	368.2	368.1
140°	378.7	379.0	379.4	379.4	379.3	379.1	379.0	378.8
142.5°	389.1	389.3	389.6	389.6	389.4	389.1	388.9	388.7
145°	403.5	403.7	403.8	403.9	403.9	403.9	403.9	403.9
147.5°	416.4	416.6	416.8	416.7	416.3	415.9	415.6	415.2
150°	424.4	424.5	424.7	424.6	424.4	424.2	423.9	423.7
152.5°	431.4	431.7	432.0	431.9	431.6	431.2	430.8	430.5
155°	441.1	441.5	441.9	441.8	441.4	440.9	440.4	439.9
157.5°	449.5	450.0	450.5	450.4	449.8	449.2	448.5	447.9
160°	454.3	454.8	455.3	455.2	454.7	454.1	453.6	453.0
162.5°	458.7	459.2	459.7	459.8	459.3	458.8	458.3	457.8
165°	464.5	465.2	465.8	465.8	465.3	464.7	464.2	463.6
167.5°	469.0	469.7	470.3	470.3	469.7	469.0	468.4	467.8
170°	471.6	472.2	472.8	472.8	472.2	471.6	471.0	470.3
172.5°	473.3	473.9	474.5	474.5	473.8	473.1	472.4	471.7
175°	475.3	475.9	476.4	476.4	475.8	475.1	474.5	473.9
177.5°	476.1	476.6	477.1	477.0	476.4	475.8	475.1	474.5
180°	475.6	475.6	475.6	475.6	475.6	475.6	475.6	475.6

(END OF REPORT)