

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331880

Luminaire Tested: **S123DIP-S340D585U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331880  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D585U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3753.3 lumens  
Efficiency: N/A  
Efficacy: 146.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32
2	86	79	73	68	78	72	67	62	59	55	52	46	44	41	35	33	32	26
3	79	69	62	57	71	63	57	52	52	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.0	1.4
10°-20°	144.1	3.8
20°-30°	212.9	5.7
30°-40°	248.7	6.6
40°-50°	250.0	6.7
50°-60°	219.6	5.9
60°-70°	163.6	4.4
70°-80°	93.2	2.5
80°-90°	28.9	0.8
90°-100°	27.9	0.7
100°-110°	133.0	3.5
110°-120°	319.5	8.5
120°-130°	406.9	10.8
130°-140°	434.7	11.6
140°-150°	406.5	10.8
150°-160°	327.9	8.7
160°-170°	211.6	5.6
170°-180°	72.9	1.9
0°-30°	408.1	10.9
0°-40°	656.8	17.5
0°-60°	1126.5	30.0
0°-90°	1412.2	37.6
90°-120°	480.5	12.8
90°-150°	1728.6	46.1
90°-180°	2341.0	62.4
0°-180°	3753.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	1	6	14	16	17	3
95°	35	13	18	21	22	43
105°	170	173	125	30	25	180
115°	319	322	327	333	335	315
125°	449	454	456	457	459	401
135°	560	563	565	567	565	431
145°	646	650	651	652	652	404
155°	711	710	711	713	710	328
165°	750	748	748	752	748	212
175°	768	765	765	769	765	73
180°	768	768	768	768	768	



TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.8	9.8	9.8	9.8	9.8	10.0	10.2	10.4	10.7	10.9	11.0
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	10.6	10.3	9.9	9.5	9.2	9.6	10.9	12.1	13.4	14.6	15.4
95°	34.8	29.6	24.4	19.2	14.0	12.1	13.5	14.9	16.3	17.7	18.6
97.5°	69.9	67.6	65.3	62.9	60.6	54.9	45.7	36.6	27.5	18.4	19.4
100°	96.4	98.9	101.5	104.0	106.5	97.9	78.1	58.4	38.6	18.8	19.8
102.5°	126.5	128.3	130.2	132.0	133.8	123.9	102.3	80.7	59.1	37.5	34.4
105°	170.0	171.4	172.8	174.1	175.5	170.5	159.1	147.7	136.3	124.9	102.5
107.5°	215.8	216.9	218.1	219.2	220.3	221.7	223.5	225.3	227.1	228.9	212.5
110°	246.4	247.4	248.4	249.4	250.4	251.7	253.0	254.4	255.8	257.2	253.0



TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.6	276.5	277.4	278.3	279.2	280.4	281.8	283.2	284.6	286.0	286.1
115°	318.8	319.6	320.3	321.1	321.9	322.8	324.0	325.1	326.2	327.4	328.7
117.5°	360.7	361.6	362.6	363.5	364.4	365.2	365.8	366.4	367.0	367.5	368.6
120°	386.7	387.8	389.0	390.1	391.3	392.0	392.4	392.8	393.2	393.5	394.6
122.5°	413.2	414.1	415.0	416.0	416.9	417.6	418.1	418.6	419.1	419.6	420.3
125°	449.4	450.5	451.5	452.5	453.5	454.3	454.8	455.3	455.8	456.3	456.5
127.5°	484.6	485.6	486.6	487.6	488.6	489.4	490.0	490.7	491.3	491.9	492.3
130°	506.5	507.5	508.5	509.5	510.5	511.3	511.8	512.3	512.8	513.3	513.8
132.5°	527.5	528.5	529.5	530.5	531.5	532.2	532.6	533.0	533.4	533.9	534.4
135°	559.5	560.3	561.0	561.8	562.6	563.2	563.7	564.2	564.7	565.2	565.6
137.5°	586.9	587.9	588.8	589.8	590.7	591.4	591.6	591.9	592.2	592.5	593.1
140°	605.1	605.9	606.7	607.4	608.2	608.8	609.1	609.5	609.9	610.3	610.8
142.5°	622.0	622.8	623.6	624.3	625.1	625.6	626.0	626.4	626.8	627.2	627.6
145°	645.6	646.5	647.4	648.3	649.2	649.8	650.0	650.3	650.5	650.8	651.0
147.5°	667.9	668.5	669.1	669.6	670.2	670.6	670.9	671.1	671.4	671.7	671.9
150°	681.6	682.0	682.3	682.7	683.1	683.4	683.7	683.9	684.2	684.4	684.7
152.5°	693.9	694.1	694.2	694.4	694.6	694.8	694.9	695.1	695.2	695.4	695.8
155°	711.2	711.0	710.7	710.5	710.2	710.2	710.3	710.4	710.5	710.7	711.3
157.5°	724.7	724.7	724.6	724.6	724.6	724.5	724.4	724.3	724.1	724.0	724.8
160°	732.9	732.8	732.7	732.5	732.4	732.3	732.1	732.0	731.9	731.8	732.5
162.5°	740.7	740.3	740.0	739.7	739.3	739.1	739.0	738.9	738.7	738.6	739.5
165°	750.0	749.6	749.3	748.9	748.5	748.2	748.1	748.0	747.9	747.7	748.8
167.5°	757.3	756.8	756.3	755.8	755.3	755.0	755.0	755.0	755.0	755.0	756.1
170°	761.4	760.9	760.4	759.9	759.4	759.1	759.1	759.1	759.1	759.1	760.2
172.5°	764.2	763.6	762.9	762.3	761.7	761.5	761.6	761.7	761.8	761.9	762.9
175°	767.7	767.1	766.4	765.8	765.2	764.9	765.0	765.2	765.3	765.4	766.3
177.5°	768.6	768.1	767.6	767.1	766.6	766.4	766.5	766.6	766.7	766.8	767.6
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7



TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	11.0	11.0	11.0	11.0	11.1	11.1	11.2	11.3
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	16.2	17.0	17.8	18.3	18.5	18.6	18.8	18.9
95°	19.5	20.3	21.2	21.7	21.7	21.7	21.7	21.7
97.5°	20.4	21.4	22.4	23.0	23.1	23.2	23.4	23.5
100°	20.8	21.9	22.9	23.4	23.6	23.7	23.8	24.0
102.5°	31.2	28.1	25.0	23.5	23.7	24.0	24.2	24.4
105°	80.0	57.6	35.2	24.1	24.3	24.6	24.8	25.1
107.5°	196.0	179.6	163.1	146.5	129.5	112.6	95.7	78.8
110°	248.9	244.7	240.5	229.3	211.2	193.1	175.0	156.8





TEST NUMBER: P331880

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	286.1	286.2	286.3	284.4	280.6	276.7	272.9	269.1
115°	329.9	331.2	332.5	333.3	333.8	334.4	334.9	335.4
117.5°	369.6	370.6	371.6	372.2	372.3	372.4	372.5	372.6
120°	395.6	396.6	397.6	398.1	398.1	398.1	398.1	398.1
122.5°	421.0	421.7	422.4	422.8	422.9	423.0	423.1	423.2
125°	456.8	457.0	457.3	457.6	457.8	458.1	458.3	458.6
127.5°	492.7	493.1	493.5	493.6	493.3	493.1	492.8	492.6
130°	514.3	514.8	515.3	515.5	515.2	515.0	514.7	514.5
132.5°	534.9	535.4	535.9	536.0	535.6	535.2	534.9	534.5
135°	566.0	566.4	566.7	566.7	566.4	566.0	565.6	565.2
137.5°	593.7	594.3	594.9	595.1	594.8	594.6	594.3	594.1
140°	611.3	611.8	612.3	612.4	612.2	611.9	611.7	611.4
142.5°	628.0	628.4	628.8	628.8	628.5	628.1	627.7	627.4
145°	651.3	651.5	651.8	651.9	651.9	651.9	651.9	651.9
147.5°	672.2	672.4	672.7	672.5	671.9	671.3	670.8	670.2
150°	684.9	685.2	685.4	685.4	685.0	684.6	684.2	683.9
152.5°	696.3	696.7	697.2	697.1	696.6	696.0	695.4	694.8
155°	711.9	712.6	713.2	713.1	712.4	711.6	710.9	710.1
157.5°	725.5	726.3	727.1	726.9	725.9	725.0	724.0	723.0
160°	733.3	734.0	734.8	734.7	733.9	733.0	732.1	731.2
162.5°	740.3	741.2	742.1	742.1	741.3	740.5	739.7	739.0
165°	749.8	750.8	751.8	751.9	751.0	750.1	749.2	748.3
167.5°	757.1	758.1	759.1	759.1	758.1	757.1	756.1	755.0
170°	761.2	762.2	763.2	763.2	762.2	761.2	760.2	759.1
172.5°	763.9	764.9	765.9	765.9	764.8	763.7	762.5	761.4
175°	767.2	768.1	769.0	768.9	767.9	766.9	765.9	764.8
177.5°	768.4	769.2	770.0	769.9	768.9	767.9	766.9	765.9
180°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)