

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331881

Luminaire Tested: **S123DIP-S340D585U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331881  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D585U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3424.0 lumens  
Efficiency: N/A  
Efficacy: 133.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41
1	96	91	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29
3	79	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	23	19	17	19	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5833	5833	5833
5°	5861	5780	5820
10°	5821	5729	5766
15°	5753	5665	5675
20°	5674	5573	5577
25°	5567	5462	5451
30°	5450	5340	5299
35°	5327	5210	5143
40°	5199	5067	4990
45°	5057	4937	4816
50°	4915	4776	4642
55°	4731	4609	4468
60°	4545	4413	4273
65°	4378	4200	4070
70°	4135	3959	3783
75°	3780	3643	3489
80°	3409	3267	3236
85°	2989	2878	2766



TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.0	1.5
10°-20°	144.1	4.2
20°-30°	212.9	6.2
30°-40°	248.7	7.3
40°-50°	250.0	7.3
50°-60°	219.6	6.4
60°-70°	163.6	4.8
70°-80°	93.2	2.7
80°-90°	28.9	0.8
90°-100°	47.3	1.4
100°-110°	141.6	4.1
110°-120°	240.8	7.0
120°-130°	316.7	9.3
130°-140°	356.0	10.4
140°-150°	349.9	10.2
150°-160°	294.6	8.6
160°-170°	196.1	5.7
170°-180°	68.7	2.0
0°-30°	408.1	11.9
0°-40°	656.8	19.2
0°-60°	1126.5	32.9
0°-90°	1412.2	41.2
90°-120°	429.7	12.5
90°-150°	1452.4	42.4
90°-180°	2012.0	58.8
0°-180°	3424.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	540	535	539	539	51
15°	516	514	508	512	509	145
25°	469	466	460	460	459	216
35°	405	402	396	394	391	254
45°	332	330	324	319	316	256
55°	252	251	246	241	238	226
65°	172	170	165	161	160	170
75°	91	89	88	85	84	97
85°	24	23	23	22	22	27
90°	1	6	14	16	17	3
95°	34	38	42	44	44	38
105°	128	130	135	135	136	137
115°	242	244	243	244	243	240
125°	355	356	355	353	351	316
135°	460	464	463	461	460	355
145°	558	560	561	561	558	349
155°	639	639	640	642	638	294
165°	696	695	695	698	694	196
175°	724	722	722	725	722	69
180°	726	726	726	726	726	



TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	543.8	543.4	543.1	542.8	542.4	541.8	540.9	540.0	539.1	538.2	539.0
5°	542.4	541.8	541.3	540.8	540.3	539.5	538.3	537.2	536.0	534.9	535.9
7.5°	537.1	536.5	536.0	535.5	535.0	534.1	533.0	531.8	530.6	529.4	530.3
10°	532.6	532.1	531.5	531.0	530.5	529.6	528.2	526.9	525.5	524.2	525.1
12.5°	526.6	526.2	525.7	525.3	524.9	524.0	522.8	521.5	520.2	519.0	519.7
15°	516.3	515.9	515.4	515.0	514.6	513.7	512.4	511.0	509.7	508.4	509.2
17.5°	504.2	503.7	503.2	502.6	502.1	501.2	499.8	498.5	497.1	495.8	496.3
20°	495.3	494.7	494.1	493.4	492.8	491.8	490.5	489.1	487.8	486.5	486.9
22.5°	485.2	484.6	484.0	483.4	482.8	481.8	480.4	479.1	477.7	476.4	476.7
25°	468.7	468.1	467.5	466.9	466.3	465.3	463.9	462.6	461.2	459.9	460.0
27.5°	451.1	450.5	449.9	449.3	448.7	447.7	446.3	444.8	443.4	441.9	442.0
30°	438.5	437.9	437.4	436.9	436.4	435.4	434.0	432.5	431.1	429.6	429.6
32.5°	425.8	425.1	424.4	423.7	423.1	422.1	421.0	419.9	418.8	417.7	417.1
35°	405.4	404.8	404.1	403.5	402.9	401.9	400.6	399.2	397.9	396.5	395.9
37.5°	384.5	383.7	382.9	382.1	381.4	380.3	378.9	377.5	376.2	374.8	374.1
40°	370.0	369.3	368.7	368.1	367.5	366.4	365.0	363.5	362.1	360.6	359.8
42.5°	355.4	354.7	354.0	353.3	352.6	351.5	350.1	348.6	347.2	345.7	344.9
45°	332.2	331.8	331.4	331.0	330.6	329.7	328.3	327.0	325.6	324.3	323.1
47.5°	309.2	308.6	308.0	307.4	306.8	305.9	304.6	303.3	302.1	300.8	299.6
50°	293.5	293.0	292.5	292.0	291.5	290.5	289.2	287.9	286.5	285.2	284.0
52.5°	277.1	276.8	276.4	276.1	275.7	274.8	273.4	272.0	270.6	269.1	268.2
55°	252.1	252.0	251.9	251.8	251.7	250.9	249.6	248.2	246.9	245.6	244.4
57.5°	228.2	227.9	227.5	227.2	226.8	226.1	225.0	223.9	222.9	221.8	220.8
60°	211.1	211.0	210.9	210.8	210.7	210.0	208.7	207.5	206.3	205.0	204.1
62.5°	195.8	195.5	195.3	195.0	194.7	194.0	192.7	191.5	190.2	189.0	188.1
65°	171.9	171.4	170.9	170.4	169.9	169.1	168.1	167.0	166.0	164.9	164.1
67.5°	146.7	146.2	145.8	145.3	144.9	144.2	143.5	142.7	141.9	141.1	140.4
70°	131.4	130.8	130.2	129.5	128.9	128.3	127.7	127.0	126.4	125.8	125.1
72.5°	115.4	114.9	114.5	114.0	113.5	113.0	112.3	111.6	110.9	110.2	109.5
75°	90.9	90.4	90.0	89.6	89.2	88.8	88.5	88.2	87.9	87.6	87.1
77.5°	69.1	68.9	68.7	68.5	68.2	67.9	67.6	67.2	66.8	66.4	66.1
80°	55.0	54.7	54.4	54.1	53.7	53.5	53.3	53.1	52.9	52.7	52.5
82.5°	41.2	41.1	41.1	41.0	40.9	40.9	40.8	40.8	40.8	40.7	40.5
85°	24.2	24.0	23.8	23.6	23.4	23.3	23.3	23.3	23.3	23.3	23.1
87.5°	9.8	9.8	9.8	9.8	9.8	10.0	10.2	10.4	10.7	10.9	11.0
90°	0.6	1.8	3.1	4.4	5.6	7.1	8.7	10.4	12.0	13.7	14.2
92.5°	13.8	14.7	15.5	16.4	17.3	18.2	19.1	20.0	21.0	21.9	22.3
95°	33.7	34.5	35.4	36.3	37.2	38.2	39.2	40.2	41.2	42.2	42.7
97.5°	59.8	60.4	61.1	61.8	62.4	63.1	63.8	64.6	65.3	66.1	66.6
100°	77.6	78.3	79.1	79.9	80.6	81.3	81.9	82.6	83.2	83.8	84.2
102.5°	98.1	98.6	99.0	99.5	99.9	100.6	101.4	102.3	103.1	103.9	104.3
105°	128.3	128.6	128.8	129.1	129.4	130.0	131.2	132.3	133.5	134.6	134.6
107.5°	163.5	163.6	163.8	163.9	164.1	164.4	164.8	165.3	165.8	166.2	166.6
110°	185.4	185.6	185.9	186.1	186.4	186.6	186.9	187.2	187.4	187.7	188.2



TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.2	208.3	208.5	208.6	208.8	208.9	209.0	209.0	209.1	209.1	209.7
115°	242.4	242.8	243.2	243.6	243.9	244.0	243.7	243.5	243.2	243.0	243.1
117.5°	276.9	277.1	277.4	277.6	277.9	277.8	277.5	277.2	276.9	276.5	276.5
120°	298.3	299.1	299.8	300.6	301.4	301.4	300.8	300.2	299.5	298.9	298.8
122.5°	320.7	321.2	321.8	322.3	322.9	323.0	322.7	322.4	322.0	321.7	321.4
125°	354.8	355.2	355.5	355.9	356.3	356.4	356.1	355.9	355.6	355.4	354.8
127.5°	386.3	387.1	387.9	388.7	389.5	389.8	389.5	389.2	388.9	388.7	388.0
130°	407.3	408.3	409.3	410.3	411.3	411.6	411.3	410.9	410.5	410.1	409.6
132.5°	428.2	429.3	430.3	431.3	432.3	432.7	432.4	432.1	431.8	431.6	430.9
135°	460.3	461.1	461.8	462.6	463.3	463.7	463.5	463.4	463.3	463.2	462.7
137.5°	490.0	490.6	491.2	491.9	492.5	493.0	493.3	493.6	494.0	494.3	493.8
140°	510.5	511.1	511.8	512.4	513.0	513.4	513.5	513.7	513.8	513.9	513.8
142.5°	529.2	529.8	530.5	531.1	531.7	532.2	532.4	532.6	532.9	533.1	533.0
145°	558.4	558.7	558.9	559.2	559.4	559.7	560.1	560.5	560.9	561.3	561.1
147.5°	584.0	584.4	584.9	585.3	585.8	586.2	586.6	586.9	587.3	587.6	587.6
150°	601.8	602.0	602.3	602.5	602.8	603.0	603.3	603.5	603.8	604.0	604.0
152.5°	616.4	616.7	617.1	617.4	617.8	618.0	618.2	618.3	618.5	618.6	618.8
155°	639.4	639.4	639.4	639.4	639.4	639.5	639.6	639.7	639.9	640.0	640.5
157.5°	659.0	658.9	658.7	658.6	658.4	658.4	658.5	658.6	658.7	658.8	659.3
160°	671.3	671.1	670.8	670.6	670.3	670.2	670.2	670.2	670.2	670.2	670.8
162.5°	682.3	681.9	681.6	681.2	680.9	680.8	680.9	681.0	681.1	681.2	681.8
165°	696.4	696.1	695.7	695.3	694.9	694.7	694.7	694.7	694.7	694.7	695.5
167.5°	707.7	707.2	706.7	706.2	705.7	705.5	705.6	705.7	705.8	705.9	706.7
170°	714.1	713.6	713.1	712.6	712.1	711.8	711.8	711.8	711.8	711.8	712.7
172.5°	719.1	718.6	718.1	717.6	717.1	716.9	716.9	716.9	716.9	716.9	717.7
175°	724.4	723.9	723.4	722.9	722.4	722.1	722.1	722.1	722.1	722.1	722.9
177.5°	726.6	726.2	725.8	725.3	724.9	724.7	724.7	724.7	724.7	724.7	725.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1



TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.9	541.9	541.9	541.9	541.9	541.9	541.9	541.9
2.5°	539.8	540.7	541.5	541.9	541.8	541.7	541.6	541.5
5°	537.0	538.0	539.1	539.5	539.3	539.1	538.8	538.6
7.5°	531.3	532.2	533.1	533.5	533.4	533.3	533.2	533.0
10°	526.1	527.0	527.9	528.3	528.1	527.9	527.7	527.5
12.5°	520.3	521.0	521.7	522.0	521.9	521.7	521.6	521.5
15°	510.0	510.8	511.7	511.8	511.1	510.5	509.9	509.3
17.5°	496.9	497.5	498.1	498.3	498.0	497.8	497.6	497.4
20°	487.3	487.7	488.1	488.2	487.8	487.5	487.2	486.9
22.5°	477.0	477.4	477.7	477.7	477.3	476.9	476.5	476.1
25°	460.1	460.2	460.3	460.2	459.9	459.6	459.3	459.0
27.5°	442.1	442.2	442.2	442.1	441.7	441.3	440.9	440.5
30°	429.6	429.6	429.6	429.2	428.5	427.8	427.1	426.3
32.5°	416.5	415.9	415.4	414.9	414.5	414.1	413.7	413.3
35°	395.3	394.7	394.0	393.5	393.0	392.4	391.9	391.4
37.5°	373.3	372.6	371.8	371.3	371.0	370.6	370.3	370.0
40°	359.0	358.2	357.3	356.7	356.3	355.9	355.5	355.1
42.5°	344.1	343.2	342.4	341.8	341.4	341.0	340.6	340.1
45°	321.8	320.6	319.3	318.5	317.9	317.4	316.9	316.4
47.5°	298.4	297.2	295.9	295.1	294.6	294.2	293.7	293.3
50°	282.9	281.7	280.6	279.7	279.1	278.5	277.9	277.2
52.5°	267.2	266.2	265.2	264.4	263.8	263.2	262.6	262.0
55°	243.3	242.1	241.0	240.2	239.7	239.1	238.6	238.1
57.5°	219.8	218.7	217.7	216.9	216.3	215.7	215.1	214.5
60°	203.2	202.2	201.3	200.6	200.0	199.5	199.0	198.5
62.5°	187.1	186.2	185.3	184.6	184.3	183.9	183.6	183.2
65°	163.3	162.5	161.6	161.1	160.8	160.4	160.1	159.8
67.5°	139.6	138.9	138.2	137.6	137.2	136.7	136.3	135.9
70°	124.4	123.6	122.9	122.3	121.8	121.3	120.7	120.2
72.5°	108.9	108.2	107.6	107.1	106.9	106.6	106.3	106.0
75°	86.6	86.0	85.5	85.1	84.8	84.5	84.2	83.9
77.5°	65.7	65.4	65.0	64.9	64.9	64.9	64.9	64.9
80°	52.4	52.3	52.2	52.2	52.2	52.2	52.2	52.2
82.5°	40.4	40.2	40.0	39.8	39.8	39.7	39.6	39.5
85°	22.9	22.7	22.5	22.4	22.4	22.4	22.4	22.4
87.5°	11.0	11.0	11.0	11.0	11.1	11.1	11.2	11.3
90°	14.7	15.2	15.7	16.1	16.4	16.6	16.9	17.1
92.5°	22.7	23.1	23.5	23.7	23.5	23.3	23.2	23.0
95°	43.2	43.7	44.2	44.5	44.5	44.5	44.5	44.5
97.5°	67.2	67.8	68.4	68.6	68.6	68.5	68.5	68.4
100°	84.6	85.0	85.4	85.7	85.9	86.2	86.4	86.7
102.5°	104.7	105.1	105.4	105.6	105.6	105.5	105.5	105.4
105°	134.6	134.6	134.6	134.7	135.0	135.2	135.5	135.8
107.5°	167.0	167.4	167.8	168.0	167.8	167.7	167.5	167.4
110°	188.7	189.2	189.7	189.8	189.6	189.3	189.1	188.8





TEST NUMBER: P331881

CATALOG NUMBER: S123DIP-S340D585U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	210.9	211.5	211.8	211.8	211.7	211.7	211.6
115°	243.2	243.4	243.5	243.5	243.4	243.2	243.1	243.0
117.5°	276.5	276.4	276.4	276.2	275.9	275.5	275.2	274.8
120°	298.6	298.5	298.4	298.2	297.9	297.7	297.4	297.2
122.5°	321.0	320.7	320.4	320.0	319.7	319.3	319.0	318.6
125°	354.3	353.8	353.3	352.8	352.3	351.8	351.3	350.8
127.5°	387.2	386.5	385.8	385.2	384.6	384.0	383.4	382.8
130°	409.1	408.6	408.1	407.4	406.5	405.6	404.7	403.8
132.5°	430.3	429.7	429.1	428.5	427.8	427.1	426.4	425.7
135°	462.1	461.6	461.1	460.7	460.5	460.2	460.0	459.7
137.5°	493.2	492.7	492.2	491.7	491.2	490.7	490.2	489.7
140°	513.7	513.5	513.4	512.9	512.0	511.1	510.2	509.4
142.5°	532.8	532.7	532.6	532.2	531.5	530.8	530.1	529.4
145°	561.0	560.9	560.8	560.4	559.9	559.4	558.9	558.4
147.5°	587.6	587.6	587.6	587.2	586.5	585.7	585.0	584.2
150°	604.0	604.0	604.0	603.7	602.9	602.1	601.4	600.6
152.5°	619.1	619.3	619.5	619.2	618.6	617.9	617.3	616.6
155°	641.0	641.5	642.0	641.8	640.9	640.0	639.2	638.3
157.5°	659.9	660.4	660.9	660.8	660.1	659.4	658.7	658.0
160°	671.5	672.1	672.7	672.8	672.3	671.8	671.3	670.8
162.5°	682.4	683.1	683.7	683.6	682.8	682.0	681.2	680.4
165°	696.3	697.0	697.8	697.7	696.8	695.9	695.1	694.2
167.5°	707.5	708.3	709.1	709.1	708.3	707.5	706.7	705.9
170°	713.6	714.5	715.4	715.4	714.5	713.6	712.7	711.8
172.5°	718.4	719.2	720.0	720.0	719.1	718.2	717.3	716.4
175°	723.6	724.4	725.2	725.1	724.2	723.3	722.4	721.5
177.5°	726.0	726.6	727.2	727.1	726.4	725.7	725.0	724.3
180°	726.1	726.1	726.1	726.1	726.1	726.1	726.1	726.1

(END OF REPORT)