

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332053-840

Luminaire Tested: **S123DIP-S1165D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332053-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D365U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6131.6 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	73	71	69	66
2	95	87	80	75	90	83	77	72	76	72	67	70	66	63	64	61	58	55
3	86	76	69	62	82	73	66	61	67	61	57	62	57	53	57	53	50	47
4	79	68	59	53	75	65	57	51	60	53	48	55	50	46	51	46	43	40
5	73	61	52	46	69	58	50	44	54	47	42	49	44	40	46	41	37	35
6	67	54	46	40	64	52	44	39	48	42	37	45	39	35	41	37	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	30	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	32	27	37	31	26	35	29	25	32	27	24	22
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	2.8
10°-20°	491.0	8.0
20°-30°	725.3	11.8
30°-40°	847.3	13.8
40°-50°	851.8	13.9
50°-60°	748.3	12.2
60°-70°	557.5	9.1
70°-80°	317.6	5.2
80°-90°	92.5	1.5
90°-100°	98.1	1.6
100°-110°	277.8	4.5
110°-120°	273.3	4.5
120°-130°	218.0	3.6
130°-140°	171.9	2.8
140°-150°	128.3	2.1
150°-160°	89.4	1.5
160°-170°	52.5	0.9
170°-180°	17.1	0.3
0°-30°	1390.3	22.7
0°-40°	2237.6	36.5
0°-60°	3837.7	62.6
0°-90°	4805.3	78.4
90°-120°	649.2	10.6
90°-150°	1167.3	19.0
90°-180°	1326.0	21.6
0°-180°	6131.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	1	4	9	10	10	5
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	219	481	552	72
125°	102	120	205	371	435	90
135°	119	142	202	306	353	92
145°	136	156	199	251	276	85
155°	154	167	193	219	229	71
165°	169	174	185	196	199	48
175°	176	176	177	180	180	17
180°	176	176	176	176	176	



TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.1	32.4	31.7	31.1	30.4	30.0	29.9	29.9	29.8	29.7	29.4
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.8	6.8	7.9	8.9	8.6
92.5°	4.4	6.6	9.6	12.3	15.3	20.6	30.0	45.3	60.4	54.8	41.4
95°	12.1	13.2	17.2	23.2	32.5	46.4	76.7	129.9	188.4	211.7	171.7
97.5°	20.7	21.0	24.1	29.4	38.6	53.6	82.6	142.5	240.1	328.0	350.8
100°	26.5	26.8	29.3	34.2	42.8	56.8	81.7	134.5	228.4	338.0	408.3
102.5°	32.4	33.0	35.2	40.0	47.7	60.5	82.9	127.6	211.3	319.4	411.1
105°	41.4	42.5	44.6	48.9	55.6	66.8	86.0	122.8	190.3	286.9	389.3
107.5°	51.0	52.0	54.1	58.3	64.6	74.9	91.9	122.4	176.8	258.2	351.2
110°	57.8	58.9	60.7	64.6	70.7	80.7	96.7	123.8	171.7	242.0	327.3



TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.1	65.1	67.0	70.9	77.0	86.6	101.6	126.7	168.7	231.1	306.4
115°	73.1	74.6	76.7	80.3	86.3	96.0	109.6	131.3	167.7	219.4	281.2
117.5°	82.2	83.8	85.6	89.0	95.7	104.6	118.1	137.4	168.3	212.6	266.0
120°	88.5	89.6	91.4	94.9	101.7	110.6	123.5	142.0	169.6	209.4	258.0
122.5°	93.9	95.0	96.7	100.7	107.1	116.6	129.2	146.3	171.5	207.5	251.5
125°	101.7	102.4	104.5	108.5	115.2	124.9	137.4	153.1	174.5	204.8	243.1
127.5°	107.7	108.7	111.4	115.3	122.8	132.5	144.5	158.6	177.9	203.6	235.6
130°	111.4	112.4	115.6	119.9	127.4	137.0	148.9	162.4	180.3	202.7	231.6
132.5°	114.2	115.5	119.1	124.2	131.7	141.1	152.5	165.8	182.0	202.4	227.9
135°	119.2	120.6	124.5	129.9	137.4	147.0	158.0	170.3	184.5	202.0	223.1
137.5°	123.9	125.4	129.3	134.9	142.4	151.3	162.0	173.5	186.2	201.2	218.8
140°	127.0	128.9	132.4	138.1	145.2	154.2	164.5	175.2	187.3	201.0	216.2
142.5°	130.5	132.0	135.8	141.0	148.1	156.4	166.5	176.9	188.2	200.4	214.0
145°	135.9	137.0	140.3	145.6	151.7	159.9	169.2	178.7	188.7	199.4	210.9
147.5°	141.6	142.2	145.3	150.0	155.8	162.8	171.3	180.0	188.7	198.1	207.9
150°	145.2	145.6	148.5	153.1	158.0	164.5	172.7	180.3	188.7	197.0	205.9
152.5°	149.0	149.1	151.9	155.9	160.4	166.5	173.6	180.8	187.9	195.6	203.6
155°	154.5	154.5	156.6	160.3	164.2	169.2	175.2	181.0	187.0	193.1	200.2
157.5°	159.0	159.3	161.0	164.1	167.4	171.3	176.1	181.3	185.8	190.9	196.3
160°	162.4	162.4	163.8	166.6	169.2	172.7	177.0	181.3	185.2	189.1	193.8
162.5°	164.9	164.9	166.1	168.3	170.6	173.6	177.3	181.0	184.1	187.4	191.2
165°	168.7	168.4	169.2	171.0	172.4	174.9	177.7	180.3	182.4	184.9	187.7
167.5°	171.7	171.3	171.7	173.0	174.0	175.6	177.6	179.7	180.7	182.3	184.4
170°	173.4	172.7	173.1	174.1	174.9	175.6	177.3	178.7	179.6	180.6	182.4
172.5°	174.6	174.1	174.2	175.0	175.4	175.8	177.3	178.5	178.6	179.2	180.4
175°	175.9	175.6	175.2	175.9	175.9	176.3	177.0	177.7	177.3	177.3	178.0
177.5°	176.6	176.3	176.0	176.3	176.3	176.3	176.6	177.1	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	29.2	29.0	28.8	28.8	28.7	28.8	28.8	28.8
90°	8.9	9.3	9.6	10.3	10.0	10.3	10.7	10.3
92.5°	30.1	23.8	21.0	19.2	18.6	17.5	17.9	17.2
95°	128.5	87.1	68.2	55.3	48.6	45.3	42.8	41.4
97.5°	320.2	256.5	210.5	167.8	141.5	125.4	115.7	112.7
100°	420.7	391.8	350.1	299.4	263.4	237.3	223.4	223.8
102.5°	454.1	453.2	428.9	396.8	368.7	348.1	336.5	328.2
105°	463.9	499.6	506.3	497.2	480.7	467.2	455.8	453.9
107.5°	435.8	493.7	525.0	537.8	538.1	533.4	529.6	526.3
110°	409.0	474.6	519.6	544.6	554.6	557.4	556.7	556.0



TEST NUMBER: P332053-840

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.4	449.5	499.9	532.0	550.3	559.2	561.9	562.0
115°	347.2	409.3	461.8	500.7	527.5	543.1	550.3	552.1
117.5°	321.7	375.4	422.4	461.9	489.9	507.9	518.1	520.5
120°	308.3	356.5	399.3	435.4	463.5	483.5	492.1	494.2
122.5°	297.8	341.3	381.0	414.5	439.6	457.6	467.0	469.7
125°	283.7	322.7	356.9	385.5	408.3	423.9	432.9	435.4
127.5°	271.5	306.1	337.0	363.0	383.3	396.8	404.9	407.1
130°	263.7	295.9	324.8	349.0	367.9	380.8	388.3	391.1
132.5°	256.6	286.1	313.1	336.2	354.0	366.8	373.4	375.5
135°	246.9	272.3	295.5	315.8	333.4	344.1	350.4	352.9
137.5°	238.1	258.9	278.9	296.6	311.2	322.1	327.5	329.2
140°	233.1	251.3	268.3	283.7	297.3	307.3	313.0	312.7
142.5°	228.2	243.8	258.6	272.0	283.6	292.5	297.5	297.2
145°	222.4	234.1	245.5	255.9	264.8	272.3	275.2	275.9
147.5°	217.5	226.9	236.1	243.5	250.2	255.3	258.0	258.3
150°	214.1	222.4	229.8	236.6	242.0	245.9	248.0	248.0
152.5°	211.0	218.0	224.7	230.4	234.5	238.1	239.4	239.4
155°	206.3	212.0	217.3	221.6	224.8	227.7	228.4	228.7
157.5°	201.3	206.0	210.2	213.6	216.3	218.4	219.0	218.9
160°	198.4	202.4	205.9	208.4	210.9	213.1	213.1	212.7
162.5°	195.0	198.3	201.7	203.9	205.5	207.3	207.3	207.0
165°	190.6	192.7	195.2	197.0	198.4	199.9	199.4	199.4
167.5°	186.7	188.3	189.8	191.1	191.7	192.7	192.4	192.4
170°	184.1	185.2	186.6	187.3	187.7	188.4	188.0	188.0
172.5°	181.9	182.7	183.8	184.2	184.3	185.0	184.4	184.1
175°	178.7	179.2	179.9	179.9	179.9	180.3	179.9	179.6
177.5°	176.8	177.1	177.4	177.4	177.1	177.4	176.8	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)