

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331883

Luminaire Tested: **S123DIP-S340D805U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331883  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D805U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4663.2 lumens  
Efficiency: N/A  
Efficacy: 149.5 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31	
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	35	34	33	27	
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	31	29	28	23	
3	78	69	62	56	70	62	56	52	50	45	42	38	35	33	27	25	24	27	25	24	19	
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	24	22	21	17	
5	65	54	46	41	59	49	42	37	39	35	31	30	27	24	22	20	18	22	20	18	14	
6	60	49	41	35	54	44	37	32	35	31	27	27	24	21	20	18	16	20	18	16	13	
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	25	21	19	11	
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	23	19	17	10	
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	21	17	15	9	
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	19	16	13	8	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.4	1.0
10°-20°	151.9	3.3
20°-30°	254.9	5.5
30°-40°	288.6	6.2
40°-50°	258.8	5.6
50°-60°	208.9	4.5
60°-70°	145.6	3.1
70°-80°	76.5	1.6
80°-90°	21.6	0.5
90°-100°	38.3	0.8
100°-110°	182.3	3.9
110°-120°	438.0	9.4
120°-130°	557.7	12.0
130°-140°	595.9	12.8
140°-150°	557.2	11.9
150°-160°	449.5	9.6
160°-170°	290.1	6.2
170°-180°	100.0	2.1
0°-30°	454.2	9.7
0°-40°	742.8	15.9
0°-60°	1210.5	26.0
0°-90°	1454.2	31.2
90°-120°	658.6	14.1
90°-150°	2369.4	50.8
90°-180°	3209.0	68.8
0°-180°	4663.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	24	1	24	1	24	11
95°	30	48	30	48	30	25
105°	34	233	34	233	34	79
115°	460	437	460	437	460	425
125°	629	616	629	616	629	561
135°	775	767	775	767	775	597
145°	894	885	894	885	894	558
155°	973	975	973	975	973	449
165°	1026	1028	1026	1028	1026	290
175°	1048	1052	1048	1052	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	10.3	9.8	10.0	10.1	9.8	9.9	9.9	10.0	10.0	10.1	9.8
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2	21.1	20.0	18.3
95°	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7	25.5	24.2	22.3
97.5°	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0	26.6	25.2	37.7
100°	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6	27.2	25.8	52.9
102.5°	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8	47.1	51.4	81.0
105°	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7	140.5	171.2	186.8
107.5°	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7	291.3	313.8	311.3
110°	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1	346.9	352.6	350.7



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2	392.1	392.0	390.1
115°	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2	450.5	448.8	447.2
117.5°	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6	505.2	503.8	503.0
120°	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2	540.8	539.4	538.9
122.5°	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0	576.1	575.1	574.4
125°	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1	625.8	625.4	624.7
127.5°	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3	674.8	674.2	673.4
130°	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0	704.3	703.6	702.9
132.5°	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1	732.5	731.8	731.2
135°	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8	774.1
137.5°	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8	813.0	812.1	811.7
140°	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9	837.2	836.5	836.0
142.5°	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8	860.2	859.7	859.1
145°	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7	892.4	892.0	891.7
147.5°	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3	921.0	920.6	920.3
150°	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8	938.5	938.2	937.8
152.5°	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4	953.8	953.2	953.0
155°	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9	975.0	974.1	973.9
157.5°	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5	993.5	992.4	992.6
160°	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1	1004.1	1003.0	1003.2
162.5°	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8	1013.6	1012.4	1012.6
165°	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7	1026.3	1024.9	1025.1
167.5°	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9	1034.9
170°	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6	1040.6
172.5°	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1	1045.7	1044.3	1044.2
175°	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6	1050.4	1049.2	1049.0
177.5°	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3	1052.2	1051.0	1050.9
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	9.7	9.5	8.5	7.3	6.6	5.7	5.3	4.6	4.6	5.0	5.1
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5	14.1	13.6	13.1
95°	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7	40.6	33.4	26.3
97.5°	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8	92.7	89.5	86.3
100°	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1	135.6	139.1	142.5
102.5°	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4	175.9	178.4	180.9
105°	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0	234.9	236.8	238.7
107.5°	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8	297.4	298.9	300.4
110°	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7	339.1	340.5	341.9





TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8	379.0	380.3	381.5
115°	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0	438.1	439.1	440.2
117.5°	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4	495.7	497.0	498.3
120°	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1	531.6	533.2	534.7
122.5°	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3	567.6	568.9	570.2
125°	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1	617.4	618.8	620.2
127.5°	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2	665.6	667.0	668.4
130°	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2	695.6	697.0	698.4
132.5°	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0	724.4	725.8	727.2
135°	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9	768.0	769.0	770.1
137.5°	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5	805.8	807.1	808.4
140°	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5	830.5	831.6	832.6
142.5°	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6	853.7	854.7	855.8
145°	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0	886.2	887.4	888.6
147.5°	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5	916.3	917.1	917.9
150°	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2	934.8	935.3	935.8
152.5°	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1	951.4	951.6	951.9
155°	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9	974.6	974.2	973.9
157.5°	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3	993.3	993.3	993.2
160°	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.4	1004.3	1004.1
162.5°	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2	1014.8	1014.3	1013.9
165°	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
167.5°	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1	1037.4	1036.7	1036.0
170°	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7	1043.0	1042.3	1041.6
172.5°	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4	1046.6	1045.8	1044.9
175°	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3	1051.4	1050.6	1049.7
177.5°	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5	1052.9	1052.2	1051.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	5.3	5.9	6.1	6.8	7.0	7.7	7.8	7.6	7.7	8.4	7.8
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2	23.3	24.5	25.1
95°	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7	27.9	29.1	29.7
97.5°	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0	29.3	30.7	31.5
100°	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6	30.0	31.4	32.1
102.5°	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8	38.5	34.2	32.2
105°	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7	79.0	48.2	33.0
107.5°	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7	246.2	223.6	200.7
110°	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1	335.4	329.7	314.4



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2	392.3	392.4	389.8
115°	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2	454.0	455.7	456.9
117.5°	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6	508.0	509.3	510.1
120°	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2	543.6	545.0	545.7
122.5°	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0	578.0	579.0	579.5
125°	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1	626.5	626.8	627.2
127.5°	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3	675.9	676.4	676.5
130°	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0	705.7	706.4	706.6
132.5°	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1	733.8	734.5	734.6
135°	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8	776.3	776.8	776.8
137.5°	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8	814.6	815.5	815.7
140°	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9	838.6	839.3	839.5
142.5°	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8	861.3	861.9	861.9
145°	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7	893.1	893.4	893.6
147.5°	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3	921.7	922.0	921.8
150°	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8	939.2	939.5	939.5
152.5°	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4	955.0	955.7	955.6
155°	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9	976.7	977.6	977.5
157.5°	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5	995.5	996.6	996.4
160°	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1	1006.2	1007.2	1007.1
162.5°	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8	1016.0	1017.1	1017.2
165°	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7	1029.1	1030.5	1030.6
167.5°	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5
170°	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1
172.5°	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1	1048.5	1049.9	1049.8
175°	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6	1052.8	1054.0	1053.9
177.5°	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3	1054.4	1055.5	1055.4
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	7.8	7.9	7.8	7.7	7.8	7.9	7.8	7.8	8.4	7.7	7.6
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	25.3	25.5	25.7	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2
95°	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7
97.5°	31.7	31.9	32.0	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0
100°	32.3	32.5	32.7	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6
102.5°	32.5	32.8	33.1	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8
105°	33.4	33.7	34.1	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7
107.5°	177.6	154.4	131.2	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7
110°	289.5	264.7	239.8	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	384.6	379.3	374.1	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2
115°	457.6	458.3	459.0	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2
117.5°	510.3	510.4	510.5	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6
120°	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2
122.5°	579.7	579.8	580.0	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0
125°	627.5	627.9	628.2	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1
127.5°	676.2	675.9	675.5	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3
130°	706.2	705.9	705.5	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0
132.5°	734.2	733.7	733.2	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1
135°	776.3	775.8	775.3	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8
137.5°	815.4	815.0	814.7	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8
140°	839.1	838.8	838.4	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9
142.5°	861.4	860.9	860.5	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8
145°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7
147.5°	921.0	920.2	919.4	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3
150°	938.9	938.4	937.9	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8
152.5°	954.8	954.0	953.2	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4
155°	976.5	975.4	974.4	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9
157.5°	995.1	993.7	992.4	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5
160°	1005.9	1004.7	1003.5	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1
162.5°	1016.1	1015.0	1014.0	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8
165°	1029.4	1028.1	1026.9	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7
167.5°	1039.1	1037.7	1036.3	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7
170°	1044.7	1043.3	1042.0	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3
172.5°	1048.3	1046.8	1045.2	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1
175°	1052.6	1051.2	1049.8	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6
177.5°	1054.0	1052.6	1051.2	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	7.8	7.7	7.0	6.8	6.1	5.9	5.3	5.1	5.0	4.6	4.6
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	21.1	20.0	18.3	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5
95°	25.5	24.2	22.3	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7
97.5°	26.6	25.2	37.7	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8
100°	27.2	25.8	52.9	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1
102.5°	47.1	51.4	81.0	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4
105°	140.5	171.2	186.8	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0
107.5°	291.3	313.8	311.3	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8
110°	346.9	352.6	350.7	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	392.1	392.0	390.1	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8
115°	450.5	448.8	447.2	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0
117.5°	505.2	503.8	503.0	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4
120°	540.8	539.4	538.9	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1
122.5°	576.1	575.1	574.4	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3
125°	625.8	625.4	624.7	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1
127.5°	674.8	674.2	673.4	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2
130°	704.3	703.6	702.9	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2
132.5°	732.5	731.8	731.2	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0
135°	775.3	774.8	774.1	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9
137.5°	813.0	812.1	811.7	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5
140°	837.2	836.5	836.0	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5
142.5°	860.2	859.7	859.1	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6
145°	892.4	892.0	891.7	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0
147.5°	921.0	920.6	920.3	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5
150°	938.5	938.2	937.8	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2
152.5°	953.8	953.2	953.0	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1
155°	975.0	974.1	973.9	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9
157.5°	993.5	992.4	992.6	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3
160°	1004.1	1003.0	1003.2	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
162.5°	1013.6	1012.4	1012.6	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2
165°	1026.3	1024.9	1025.1	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1
167.5°	1036.3	1034.9	1034.9	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1
170°	1042.0	1040.6	1040.6	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7
172.5°	1045.7	1044.3	1044.2	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4
175°	1050.4	1049.2	1049.0	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3
177.5°	1052.2	1051.0	1050.9	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.3	5.7	6.6	7.3	8.5	9.5	9.7	9.8	10.1	10.0	10.0
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	14.1	13.6	13.1	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2
95°	40.6	33.4	26.3	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7
97.5°	92.7	89.5	86.3	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0
100°	135.6	139.1	142.5	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6
102.5°	175.9	178.4	180.9	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8
105°	234.9	236.8	238.7	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7
107.5°	297.4	298.9	300.4	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7
110°	339.1	340.5	341.9	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1





TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	379.0	380.3	381.5	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2
115°	438.1	439.1	440.2	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2
117.5°	495.7	497.0	498.3	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6
120°	531.6	533.2	534.7	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2
122.5°	567.6	568.9	570.2	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0
125°	617.4	618.8	620.2	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1
127.5°	665.6	667.0	668.4	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3
130°	695.6	697.0	698.4	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0
132.5°	724.4	725.8	727.2	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1
135°	768.0	769.0	770.1	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8
137.5°	805.8	807.1	808.4	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8
140°	830.5	831.6	832.6	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9
142.5°	853.7	854.7	855.8	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8
145°	886.2	887.4	888.6	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7
147.5°	916.3	917.1	917.9	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3
150°	934.8	935.3	935.8	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8
152.5°	951.4	951.6	951.9	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4
155°	974.6	974.2	973.9	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9
157.5°	993.3	993.3	993.2	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5
160°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1
162.5°	1014.8	1014.3	1013.9	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8
165°	1027.5	1027.0	1026.5	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7
167.5°	1037.4	1036.7	1036.0	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7
170°	1043.0	1042.3	1041.6	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3
172.5°	1046.6	1045.8	1044.9	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1
175°	1051.4	1050.6	1049.7	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6
177.5°	1052.9	1052.2	1051.5	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	9.9	9.9	9.8	10.1	10.0	9.8	10.3
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	23.3	24.5	25.1	25.3	25.5	25.7	26.0
95°	27.9	29.1	29.7	29.7	29.7	29.7	29.7
97.5°	29.3	30.7	31.5	31.7	31.9	32.0	32.2
100°	30.0	31.4	32.1	32.3	32.5	32.7	32.8
102.5°	38.5	34.2	32.2	32.5	32.8	33.1	33.5
105°	79.0	48.2	33.0	33.4	33.7	34.1	34.4
107.5°	246.2	223.6	200.7	177.6	154.4	131.2	108.0
110°	335.4	329.7	314.4	289.5	264.7	239.8	215.0



TEST NUMBER: P331883

CATALOG NUMBER: S123DIP-S340D805U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	392.3	392.4	389.8	384.6	379.3	374.1	368.9
115°	454.0	455.7	456.9	457.6	458.3	459.0	459.7
117.5°	508.0	509.3	510.1	510.3	510.4	510.5	510.7
120°	543.6	545.0	545.7	545.7	545.7	545.7	545.7
122.5°	578.0	579.0	579.5	579.7	579.8	580.0	580.1
125°	626.5	626.8	627.2	627.5	627.9	628.2	628.6
127.5°	675.9	676.4	676.5	676.2	675.9	675.5	675.2
130°	705.7	706.4	706.6	706.2	705.9	705.5	705.2
132.5°	733.8	734.5	734.6	734.2	733.7	733.2	732.7
135°	776.3	776.8	776.8	776.3	775.8	775.3	774.8
137.5°	814.6	815.5	815.7	815.4	815.0	814.7	814.3
140°	838.6	839.3	839.5	839.1	838.8	838.4	838.1
142.5°	861.3	861.9	861.9	861.4	860.9	860.5	860.0
145°	893.1	893.4	893.6	893.6	893.6	893.6	893.6
147.5°	921.7	922.0	921.8	921.0	920.2	919.4	918.6
150°	939.2	939.5	939.5	938.9	938.4	937.9	937.4
152.5°	955.0	955.7	955.6	954.8	954.0	953.2	952.4
155°	976.7	977.6	977.5	976.5	975.4	974.4	973.3
157.5°	995.5	996.6	996.4	995.1	993.7	992.4	991.0
160°	1006.2	1007.2	1007.1	1005.9	1004.7	1003.5	1002.3
162.5°	1016.0	1017.1	1017.2	1016.1	1015.0	1014.0	1012.9
165°	1029.1	1030.5	1030.6	1029.4	1028.1	1026.9	1025.7
167.5°	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9
170°	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6
172.5°	1048.5	1049.9	1049.8	1048.3	1046.8	1045.2	1043.7
175°	1052.8	1054.0	1053.9	1052.6	1051.2	1049.8	1048.4
177.5°	1054.4	1055.5	1055.4	1054.0	1052.6	1051.2	1049.8
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

(END OF REPORT)