

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831240

Luminaire Tested: S123DIP-S1165D365U840-4F0-1E-UDD-G

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831240  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D365U840-4F0-1E-UDD-G  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6842.3 lumens  
Efficiency: N/A  
Efficacy: 131.1 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 52.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831240  
CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

### Luminous Intensity Polar Plot





TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	79		
1	105	101	97	94	100	96	93	90	88	86	83	81	79	77	74	73	71	68		
2	96	89	83	78	92	85	80	75	79	74	71	72	69	66	66	64	61	58		
3	89	79	72	66	84	76	70	64	70	65	61	65	60	57	60	56	53	50		
4	82	71	63	57	78	68	61	56	63	57	53	59	54	50	54	50	47	44		
5	76	64	56	50	72	62	54	49	57	51	46	53	48	44	49	45	42	39		
6	70	58	50	44	67	56	49	43	52	46	41	49	43	39	45	41	37	35		
7	65	53	45	40	63	51	44	39	48	42	37	45	40	36	42	37	34	32		
8	61	49	41	36	59	47	40	35	44	38	34	42	36	32	39	34	31	29		
9	57	45	38	33	55	44	37	32	41	35	31	39	33	30	36	32	28	26		
10	54	42	35	30	52	41	34	29	38	32	28	36	31	27	34	29	26	24		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	36004	36004	36004	36004	36004
5°	45533	42976	36327	29274	26901
10°	45976	47367	36085	23335	20392
15°	34628	43977	35839	19762	17245
20°	24127	35586	35381	17282	15664
25°	18398	27366	34601	15899	14693
30°	15915	21742	33356	14922	13909
35°	14767	18357	31919	14217	13360
40°	13980	16467	29901	13544	13173
45°	13515	15239	27338	13018	13090
50°	13283	14269	24303	12541	13021
55°	12787	13559	21322	12087	13078
60°	12329	12798	18378	11662	12865
65°	11584	12078	15852	11207	12610
70°	10697	11163	13482	10455	11871
75°	9682	10006	11553	9715	10846
80°	7984	8753	9143	8467	9143
85°	6323	7089	6706	7188	7287

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 31212 cd/sqm



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	316.2	4.6
10°-20°	786.7	11.5
20°-30°	931.5	13.6
30°-40°	936.6	13.7
40°-50°	859.3	12.6
50°-60°	709.2	10.4
60°-70°	501.7	7.3
70°-80°	267.8	3.9
80°-90°	68.9	1.0
90°-100°	16.9	0.2
100°-110°	81.9	1.2
110°-120°	200.7	2.9
120°-130°	254.8	3.7
130°-140°	272.2	4.0
140°-150°	254.5	3.7
150°-160°	205.3	3.0
160°-170°	132.5	1.9
170°-180°	45.7	0.7
0°-30°	2034.4	29.7
0°-40°	2971.0	43.4
0°-60°	4539.6	66.3
0°-90°	5378.0	78.6
90°-120°	299.5	4.4
90°-150°	1080.9	15.8
90°-180°	1464.0	21.4
0°-180°	6842.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3345	3345	3345	3345	3345	
5°	4214	3977	3362	2709	2490	402
15°	3107	3946	3216	1773	1548	858
25°	1549	2304	2913	1339	1237	731
35°	1124	1397	2429	1082	1017	706
45°	888	1001	1796	855	860	688
55°	681	722	1136	644	697	610
65°	455	474	622	440	495	452
75°	233	241	278	234	261	245
85°	51	57	54	58	59	57
90°	11	9	0	9	11	8
95°	14	11	22	11	14	11
105°	16	78	106	78	16	33
115°	210	205	200	205	210	197
125°	287	286	281	286	287	256
135°	354	354	350	354	354	273
145°	408	407	404	407	408	255
155°	444	445	445	445	444	205
165°	468	468	469	468	468	132
175°	478	479	480	479	478	46
180°	480	480	480	480	480	



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9
2.5°	3770.2	3766.3	3762.5	3743.1	3723.6	3714.3	3705.0	3677.1	3649.1	3618.1	3587.1
5°	4214.1	4225.0	4235.9	4223.4	4211.0	4173.0	4135.0	4084.5	4034.1	3977.4	3920.8
7.5°	4419.0	4425.2	4431.4	4423.7	4415.9	4405.8	4395.7	4350.7	4305.7	4247.5	4189.3
10°	4206.4	4220.3	4234.3	4264.6	4294.8	4329.0	4363.1	4356.9	4350.7	4333.7	4316.6
12.5°	3739.2	3756.2	3773.3	3833.9	3894.4	3972.0	4049.6	4116.3	4183.1	4229.7	4276.2
15°	3107.4	3154.8	3202.1	3257.2	3312.3	3426.4	3540.5	3681.0	3821.4	3946.4	4071.3
17.5°	2559.5	2577.4	2595.2	2654.2	2713.2	2856.8	3000.3	3162.5	3324.7	3532.0	3739.2
20°	2106.3	2122.6	2138.9	2216.5	2294.1	2406.6	2519.2	2701.5	2883.9	3106.7	3329.4
22.5°	1769.5	1795.1	1820.7	1864.2	1907.6	2015.5	2123.4	2285.6	2447.8	2693.8	2939.8
25°	1549.1	1567.7	1586.3	1612.7	1639.1	1725.2	1811.4	1944.9	2078.4	2304.2	2530.0
27.5°	1398.5	1406.3	1414.0	1440.4	1466.8	1522.7	1578.6	1693.4	1808.3	2000.0	2191.7
30°	1280.5	1286.0	1291.4	1314.7	1338.0	1376.0	1414.0	1497.1	1580.1	1749.3	1918.5
32.5°	1198.3	1202.2	1206.0	1223.9	1241.7	1268.9	1296.1	1356.6	1417.1	1556.8	1696.5
35°	1123.8	1126.1	1128.4	1141.6	1154.8	1175.0	1195.2	1241.0	1286.7	1397.0	1507.2
37.5°	1058.6	1061.7	1064.8	1072.5	1080.3	1098.2	1116.0	1152.5	1189.0	1273.6	1358.1
40°	994.9	1000.4	1005.8	1011.2	1016.7	1031.4	1046.2	1074.1	1102.0	1171.9	1241.7
42.5°	940.6	946.0	951.5	953.8	956.1	964.7	973.2	998.8	1024.4	1076.4	1128.4
45°	887.8	890.2	892.5	894.8	897.2	904.1	911.1	933.6	956.1	1001.1	1046.2
47.5°	839.7	839.7	839.7	841.3	842.8	849.0	855.2	871.5	887.8	922.8	957.7
50°	793.2	793.2	793.2	790.8	788.5	792.4	796.3	808.7	821.1	852.1	883.2
52.5°	737.3	737.3	737.3	738.1	738.8	738.8	738.8	749.7	760.6	788.5	816.4
55°	681.4	684.5	687.6	685.3	683.0	684.5	686.1	693.0	700.0	722.5	745.0
57.5°	625.5	627.1	628.6	627.9	627.1	627.9	628.6	634.8	641.0	658.1	675.2
60°	572.7	572.7	572.7	571.2	569.6	571.2	572.7	575.9	579.0	594.5	610.0
62.5°	513.8	514.5	515.3	516.1	516.9	515.3	513.8	517.6	521.5	533.2	544.8
65°	454.8	455.6	456.3	458.7	461.0	459.4	457.9	461.8	465.7	474.2	482.7
67.5°	402.0	400.5	398.9	399.7	400.5	402.8	405.1	405.9	406.7	416.0	425.3
70°	339.9	341.5	343.0	342.3	341.5	342.3	343.0	345.4	347.7	354.7	361.7
72.5°	284.0	284.8	285.6	285.6	285.6	287.2	288.7	291.0	293.4	297.2	301.1
75°	232.8	232.8	232.8	234.4	235.9	236.7	237.5	237.5	237.5	240.6	243.7
77.5°	176.9	180.8	184.7	183.9	183.2	184.7	186.3	188.6	190.9	192.5	194.0
80°	128.8	128.8	128.8	129.6	130.4	132.7	135.0	136.6	138.1	141.2	144.4
82.5°	82.3	83.0	83.8	86.1	88.5	90.0	91.6	93.9	96.2	96.2	96.2
85°	51.2	49.7	48.1	49.7	51.2	52.8	54.3	55.1	55.9	57.4	59.0
87.5°	24.8	24.8	24.8	24.8	24.8	25.6	26.4	26.4	26.4	26.4	26.4
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2	8.9	8.6	7.5
92.5°	12.1	12.1	12.0	11.9	11.8	11.5	10.9	10.4	9.8	9.3	8.6
95°	13.6	13.6	13.6	13.6	13.6	13.3	12.7	12.2	11.6	11.1	10.2
97.5°	14.6	14.6	14.5	14.4	14.3	14.0	13.3	12.7	12.1	11.4	15.5
100°	15.0	14.9	14.8	14.8	14.7	14.3	13.7	13.0	12.4	11.8	24.1
102.5°	15.3	15.2	15.0	14.9	14.7	15.9	18.6	21.2	23.8	26.4	40.2
105°	15.7	15.5	15.4	15.2	15.1	22.0	36.0	50.1	64.1	78.2	85.3
107.5°	37.1	47.5	57.9	68.3	78.7	90.0	102.2	114.4	126.6	138.8	137.6
110°	98.1	109.5	120.8	132.2	143.5	150.5	153.1	155.7	158.3	160.9	160.1



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	185.9	186.1	186.2	186.4	186.6	186.3	185.6	184.9	184.1	183.4	182.6
115°	209.8	209.5	209.2	208.9	208.6	208.0	207.2	206.4	205.6	204.8	204.1
117.5°	229.1	229.0	228.9	228.9	228.8	228.4	227.8	227.2	226.5	225.9	225.5
120°	249.1	249.1	249.1	249.1	249.1	248.8	248.1	247.5	246.9	246.2	246.0
122.5°	268.7	268.6	268.6	268.5	268.4	268.2	267.8	267.4	267.0	266.6	266.3
125°	286.9	286.8	286.6	286.4	286.3	286.1	286.0	285.8	285.6	285.5	285.2
127.5°	304.8	304.9	305.1	305.2	305.4	305.3	305.1	304.9	304.6	304.4	304.0
130°	321.9	322.0	322.2	322.4	322.5	322.4	322.1	321.8	321.5	321.2	320.9
132.5°	337.6	337.8	338.1	338.3	338.5	338.5	338.2	337.9	337.5	337.2	337.0
135°	353.6	353.9	354.1	354.4	354.6	354.6	354.4	354.1	353.9	353.6	353.3
137.5°	369.0	369.1	369.3	369.5	369.6	369.5	369.1	368.7	368.3	367.9	367.8
140°	382.5	382.7	382.9	383.0	383.2	383.1	382.8	382.5	382.2	381.8	381.6
142.5°	395.0	395.3	395.5	395.8	396.0	396.0	395.8	395.5	395.3	395.0	394.8
145°	407.9	407.9	407.9	407.9	407.9	407.8	407.6	407.5	407.3	407.2	407.0
147.5°	417.2	417.6	418.0	418.4	418.8	418.9	418.7	418.6	418.4	418.2	418.1
150°	427.9	428.1	428.3	428.6	428.8	428.9	428.7	428.5	428.4	428.2	428.1
152.5°	436.4	436.8	437.2	437.6	438.0	438.1	437.7	437.4	437.1	436.8	436.7
155°	444.3	444.8	445.2	445.7	446.2	446.2	445.8	445.4	445.0	444.6	444.6
157.5°	451.1	451.7	452.3	453.0	453.6	453.7	453.2	452.7	452.3	451.8	451.9
160°	457.5	458.0	458.6	459.2	459.7	459.7	459.3	458.8	458.3	457.8	457.9
162.5°	463.6	464.0	464.5	465.0	465.5	465.4	464.9	464.3	463.8	463.2	463.3
165°	468.2	468.7	469.3	469.9	470.4	470.4	469.7	469.1	468.5	467.8	467.9
167.5°	471.8	472.4	473.0	473.7	474.3	474.3	473.7	473.0	472.4	471.8	471.8
170°	475.0	475.6	476.2	476.9	477.5	477.5	476.9	476.2	475.6	475.0	475.0
172.5°	476.8	477.5	478.2	478.9	479.6	479.7	479.0	478.4	477.8	477.1	477.0
175°	478.5	479.2	479.8	480.4	481.1	481.1	480.6	480.0	479.5	478.9	478.8
177.5°	478.9	479.7	480.5	481.3	482.1	482.2	481.5	480.9	480.2	479.6	479.5
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9
2.5°	3577.7	3568.4	3534.3	3500.1	3461.3	3422.5	3393.8	3365.1	3322.4	3279.7	3244.8
5°	3877.3	3833.9	3761.7	3689.5	3591.7	3493.9	3428.0	3362.0	3273.5	3185.0	3114.4
7.5°	4114.8	4040.3	3939.4	3838.5	3710.5	3582.4	3461.3	3340.3	3205.2	3070.2	2960.0
10°	4266.1	4215.7	4099.3	3982.9	3811.3	3639.8	3470.6	3301.5	3127.6	2953.8	2807.9
12.5°	4280.9	4285.5	4178.4	4071.3	3877.3	3683.3	3477.6	3272.0	3053.1	2834.3	2664.3
15°	4151.3	4231.2	4172.2	4113.2	3917.7	3722.1	3469.1	3216.1	2963.9	2711.6	2515.3
17.5°	3910.7	4082.2	4090.7	4099.3	3903.7	3708.1	3428.0	3147.8	2862.2	2576.6	2370.2
20°	3582.4	3835.4	3922.3	4009.2	3850.2	3691.1	3389.9	3088.8	2769.1	2449.3	2232.8
22.5°	3247.1	3554.5	3713.6	3872.7	3754.7	3636.7	3316.2	2995.7	2658.1	2320.5	2100.9
25°	2865.3	3200.6	3445.0	3689.5	3617.3	3545.1	3229.3	2913.4	2554.1	2194.8	1970.5
27.5°	2532.4	2873.1	3168.0	3462.9	3447.4	3431.8	3118.3	2804.8	2436.9	2069.0	1852.5
30°	2235.9	2553.3	2883.2	3213.0	3251.0	3289.0	2986.4	2683.7	2315.1	1946.4	1737.7
32.5°	1973.6	2250.6	2604.5	2958.4	3032.9	3107.4	2834.3	2561.1	2196.3	1831.6	1630.6
35°	1758.6	2010.1	2364.0	2717.8	2811.0	2904.1	2666.6	2429.1	2073.7	1718.2	1526.6
37.5°	1568.5	1778.8	2124.1	2469.5	2583.6	2697.7	2485.0	2272.4	1939.4	1606.5	1430.3
40°	1410.9	1580.1	1897.5	2214.9	2346.9	2478.8	2303.4	2128.0	1812.2	1496.3	1334.1
42.5°	1279.0	1429.5	1717.5	2005.4	2131.9	2258.4	2110.2	1961.9	1681.0	1400.1	1251.8
45°	1166.5	1286.7	1548.3	1809.8	1930.1	2050.4	1923.1	1795.9	1548.3	1300.7	1162.6
47.5°	1060.9	1164.1	1387.6	1611.1	1718.2	1825.3	1726.0	1626.7	1417.1	1207.6	1082.6
50°	966.2	1049.3	1244.8	1440.4	1533.5	1626.7	1539.0	1451.3	1279.0	1106.7	998.0
52.5°	884.0	951.5	1115.2	1279.0	1358.9	1438.9	1363.6	1288.3	1151.7	1015.1	920.4
55°	802.5	859.9	1001.9	1143.9	1198.3	1252.6	1194.4	1136.2	1026.0	915.8	835.8
57.5°	726.4	777.6	894.0	1010.5	1052.4	1094.3	1041.5	988.7	905.7	822.6	755.9
60°	651.9	693.8	790.8	887.8	913.5	939.1	896.4	853.7	795.5	737.3	677.5
62.5°	582.8	620.9	693.0	765.2	782.3	799.4	766.8	734.2	689.9	645.7	599.1
65°	511.4	540.2	599.1	658.1	669.0	679.8	651.1	622.4	589.0	555.7	521.5
67.5°	445.5	465.7	513.8	561.9	562.7	563.4	540.2	516.9	498.2	479.6	452.5
70°	381.1	400.5	432.3	464.1	464.9	465.7	447.0	428.4	414.4	400.5	380.3
72.5°	315.1	329.1	353.1	377.2	375.6	374.1	362.4	350.8	339.9	329.1	314.3
75°	255.3	267.0	283.3	299.6	294.9	290.3	284.0	277.8	268.5	259.2	249.9
77.5°	201.0	208.0	217.3	226.6	223.5	220.4	215.0	209.5	202.6	195.6	191.7
80°	147.5	150.6	156.8	163.0	161.4	159.9	153.7	147.5	145.9	144.4	138.9
82.5°	100.1	104.0	105.5	107.1	106.3	105.5	100.9	96.2	94.7	93.1	92.4
85°	59.8	60.5	61.3	62.1	59.8	57.4	55.9	54.3	54.3	54.3	53.5
87.5°	27.2	27.9	27.9	27.9	27.2	26.4	24.8	23.3	24.1	24.8	24.8
90°	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.4	1.1	1.9	2.7
92.5°	7.9	7.1	6.4	6.3	6.8	7.3	7.7	8.2	7.7	7.3	6.8
95°	9.3	8.4	7.6	8.8	12.0	15.3	18.5	21.8	18.5	15.3	12.0
97.5°	19.5	23.6	27.6	30.7	32.9	35.2	37.4	39.6	37.4	35.2	32.9
100°	36.5	48.9	61.3	66.7	65.1	63.5	61.9	60.3	61.9	63.5	65.1
102.5°	54.0	67.8	81.6	88.0	87.0	85.9	84.9	83.9	84.9	85.9	87.0
105°	92.4	99.6	106.7	109.8	109.0	108.1	107.2	106.3	107.2	108.1	109.0
107.5°	136.4	135.2	134.1	133.1	132.4	131.7	131.0	130.3	131.0	131.7	132.4
110°	159.2	158.3	157.5	156.7	156.1	155.4	154.8	154.2	154.8	155.4	156.1





TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	181.7	180.8	179.9	179.2	178.7	178.1	177.6	177.0	177.6	178.1	178.7
115°	203.4	202.7	202.0	201.4	200.9	200.4	200.0	199.5	200.0	200.4	200.9
117.5°	225.1	224.7	224.3	223.8	223.3	222.7	222.2	221.6	222.2	222.7	223.3
120°	245.8	245.5	245.3	244.8	244.1	243.4	242.7	241.9	242.7	243.4	244.1
122.5°	265.9	265.6	265.3	264.9	264.3	263.8	263.2	262.6	263.2	263.8	264.3
125°	284.9	284.5	284.2	283.7	283.1	282.5	281.8	281.2	281.8	282.5	283.1
127.5°	303.6	303.2	302.8	302.3	301.7	301.0	300.4	299.8	300.4	301.0	301.7
130°	320.5	320.2	319.9	319.4	318.8	318.2	317.5	316.9	317.5	318.2	318.8
132.5°	336.8	336.5	336.3	335.8	335.2	334.6	333.9	333.3	333.9	334.6	335.2
135°	353.0	352.7	352.4	352.0	351.5	351.0	350.6	350.1	350.6	351.0	351.5
137.5°	367.6	367.4	367.3	366.9	366.3	365.6	365.0	364.3	365.0	365.6	366.3
140°	381.4	381.1	380.9	380.5	380.1	379.6	379.1	378.6	379.1	379.6	380.1
142.5°	394.6	394.3	394.1	393.7	393.3	392.8	392.3	391.8	392.3	392.8	393.3
145°	406.9	406.7	406.5	406.2	405.6	405.1	404.5	404.0	404.5	405.1	405.6
147.5°	417.9	417.8	417.6	417.3	416.9	416.5	416.1	415.7	416.1	416.5	416.9
150°	427.9	427.8	427.6	427.4	427.2	426.9	426.7	426.4	426.7	426.9	427.2
152.5°	436.6	436.6	436.5	436.4	436.3	436.2	436.2	436.1	436.2	436.2	436.3
155°	444.5	444.4	444.3	444.4	444.5	444.7	444.8	445.0	444.8	444.7	444.5
157.5°	451.9	452.0	452.1	452.1	452.1	452.1	452.1	452.1	452.1	452.1	452.1
160°	458.0	458.1	458.2	458.2	458.3	458.4	458.5	458.6	458.5	458.4	458.3
162.5°	463.4	463.4	463.5	463.7	463.9	464.2	464.4	464.6	464.4	464.2	463.9
165°	468.0	468.1	468.2	468.3	468.6	468.8	469.0	469.3	469.0	468.8	468.6
167.5°	471.8	471.8	471.8	471.9	472.2	472.6	472.9	473.2	472.9	472.6	472.2
170°	475.0	475.0	475.0	475.1	475.5	475.8	476.1	476.4	476.1	475.8	475.5
172.5°	477.0	476.9	476.8	477.0	477.4	477.8	478.1	478.5	478.1	477.8	477.4
175°	478.7	478.7	478.6	478.7	479.1	479.5	479.9	480.3	479.9	479.5	479.1
177.5°	479.5	479.4	479.3	479.5	479.9	480.2	480.6	481.0	480.6	480.2	479.9
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9	3344.9
2.5°	3209.9	3179.6	3149.3	3126.1	3102.8	3063.2	3023.6	3014.3	3005.0	2991.8	2978.6
5°	3043.8	2969.3	2894.8	2828.0	2761.3	2709.3	2657.3	2623.2	2589.0	2564.2	2539.3
7.5°	2849.8	2738.0	2626.3	2547.1	2467.9	2392.7	2317.4	2293.3	2269.3	2236.7	2204.1
10°	2662.0	2538.6	2415.2	2312.0	2208.7	2135.0	2061.3	2031.8	2002.3	1961.2	1920.0
12.5°	2494.3	2359.3	2224.3	2120.3	2016.3	1944.9	1873.5	1830.8	1788.1	1764.8	1741.5
15°	2318.9	2174.6	2030.2	1934.0	1837.8	1773.4	1708.9	1671.7	1634.4	1611.9	1589.4
17.5°	2163.7	2020.9	1878.1	1785.8	1693.4	1634.4	1575.4	1542.9	1510.3	1493.2	1476.1
20°	2016.3	1876.6	1736.9	1646.8	1556.8	1508.7	1460.6	1439.6	1418.7	1404.7	1390.7
22.5°	1881.2	1743.9	1606.5	1529.7	1452.8	1414.0	1375.2	1360.5	1345.7	1334.1	1322.4
25°	1746.2	1623.6	1500.9	1435.8	1370.6	1338.7	1306.9	1292.2	1277.4	1265.8	1254.2
27.5°	1636.0	1518.8	1401.6	1345.7	1289.9	1265.0	1240.2	1228.5	1216.9	1206.0	1195.2
30°	1528.9	1424.1	1319.3	1271.2	1223.1	1200.6	1178.1	1166.5	1154.8	1144.7	1134.6
32.5°	1429.5	1339.5	1249.5	1205.3	1161.0	1142.4	1123.8	1109.8	1095.8	1088.1	1080.3
35°	1334.9	1254.2	1173.4	1137.0	1100.5	1081.9	1063.2	1051.6	1040.0	1033.7	1027.5
37.5°	1254.2	1182.0	1109.8	1074.9	1040.0	1022.1	1004.3	994.2	984.1	981.7	979.4
40°	1171.9	1109.8	1047.7	1013.6	979.4	963.9	948.4	942.2	936.0	934.4	932.9
42.5°	1103.6	1043.1	982.5	951.5	920.4	907.2	894.0	890.9	887.8	890.2	892.5
45°	1024.4	974.0	923.5	894.8	866.1	855.2	844.4	842.1	839.7	844.4	849.0
47.5°	957.7	911.1	864.6	837.4	810.2	802.5	794.7	793.9	793.2	799.4	805.6
50°	889.4	844.4	799.4	777.6	755.9	748.9	741.9	744.3	746.6	756.7	766.8
52.5°	825.8	783.8	741.9	721.8	701.6	696.9	692.3	697.7	703.1	714.0	724.9
55°	755.9	717.9	679.8	664.3	648.8	644.1	639.5	650.4	661.2	671.3	681.4
57.5°	689.2	655.8	622.4	608.4	594.5	593.7	592.9	603.0	613.1	624.0	634.8
60°	617.8	589.8	561.9	551.0	540.2	541.7	543.3	554.9	566.5	575.1	583.6
62.5°	552.6	529.3	506.0	495.9	485.8	489.7	493.6	505.2	516.9	527.0	537.0
65°	487.4	468.0	448.6	441.6	434.6	440.0	445.5	455.6	465.7	472.6	479.6
67.5°	425.3	409.0	392.7	387.3	381.8	387.3	392.7	402.8	412.9	419.9	426.8
70°	360.1	346.9	333.7	329.8	326.0	332.2	338.4	346.9	355.4	362.4	369.4
72.5°	299.6	289.5	279.4	278.6	277.8	283.3	288.7	297.2	305.8	310.4	315.1
75°	240.6	235.2	229.7	228.9	228.2	233.6	239.0	243.7	248.3	252.2	256.1
77.5°	187.8	183.2	178.5	179.3	180.1	183.9	187.8	192.5	197.1	199.5	201.8
80°	133.5	131.9	130.4	131.9	133.5	136.6	139.7	142.8	145.9	147.5	149.0
82.5°	91.6	90.0	88.5	90.8	93.1	95.5	97.8	100.1	102.4	103.2	104.0
85°	52.8	55.1	57.4	57.4	57.4	58.2	59.0	59.8	60.5	59.8	59.0
87.5°	24.8	25.6	26.4	26.4	26.4	27.2	27.9	27.9	27.9	27.2	26.4
90°	3.5	4.4	5.5	6.5	7.5	8.6	8.9	9.2	9.5	9.8	10.1
92.5°	6.3	6.4	7.1	7.9	8.6	9.3	9.8	10.4	10.9	11.5	11.8
95°	8.8	7.6	8.4	9.3	10.2	11.1	11.6	12.2	12.7	13.3	13.6
97.5°	30.7	27.6	23.6	19.5	15.5	11.4	12.1	12.7	13.3	14.0	14.3
100°	66.7	61.3	48.9	36.5	24.1	11.8	12.4	13.0	13.7	14.3	14.7
102.5°	88.0	81.6	67.8	54.0	40.2	26.4	23.8	21.2	18.6	15.9	14.7
105°	109.8	106.7	99.6	92.4	85.3	78.2	64.1	50.1	36.0	22.0	15.1
107.5°	133.1	134.1	135.2	136.4	137.6	138.8	126.6	114.4	102.2	90.0	78.7
110°	156.7	157.5	158.3	159.2	160.1	160.9	158.3	155.7	153.1	150.5	143.5



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	179.2	179.9	180.8	181.7	182.6	183.4	184.1	184.9	185.6	186.3	186.6
115°	201.4	202.0	202.7	203.4	204.1	204.8	205.6	206.4	207.2	208.0	208.6
117.5°	223.8	224.3	224.7	225.1	225.5	225.9	226.5	227.2	227.8	228.4	228.8
120°	244.8	245.3	245.5	245.8	246.0	246.2	246.9	247.5	248.1	248.8	249.1
122.5°	264.9	265.3	265.6	265.9	266.3	266.6	267.0	267.4	267.8	268.2	268.4
125°	283.7	284.2	284.5	284.9	285.2	285.5	285.6	285.8	286.0	286.1	286.3
127.5°	302.3	302.8	303.2	303.6	304.0	304.4	304.6	304.9	305.1	305.3	305.4
130°	319.4	319.9	320.2	320.5	320.9	321.2	321.5	321.8	322.1	322.4	322.5
132.5°	335.8	336.3	336.5	336.8	337.0	337.2	337.5	337.9	338.2	338.5	338.5
135°	352.0	352.4	352.7	353.0	353.3	353.6	353.9	354.1	354.4	354.6	354.6
137.5°	366.9	367.3	367.4	367.6	367.8	367.9	368.3	368.7	369.1	369.5	369.6
140°	380.5	380.9	381.1	381.4	381.6	381.8	382.2	382.5	382.8	383.1	383.2
142.5°	393.7	394.1	394.3	394.6	394.8	395.0	395.3	395.5	395.8	396.0	396.0
145°	406.2	406.5	406.7	406.9	407.0	407.2	407.3	407.5	407.6	407.8	407.9
147.5°	417.3	417.6	417.8	417.9	418.1	418.2	418.4	418.6	418.7	418.9	418.8
150°	427.4	427.6	427.8	427.9	428.1	428.2	428.4	428.5	428.7	428.9	428.8
152.5°	436.4	436.5	436.6	436.6	436.7	436.8	437.1	437.4	437.7	438.1	438.0
155°	444.4	444.3	444.4	444.5	444.6	444.6	445.0	445.4	445.8	446.2	446.2
157.5°	452.1	452.1	452.0	451.9	451.9	451.8	452.3	452.7	453.2	453.7	453.6
160°	458.2	458.2	458.1	458.0	457.9	457.8	458.3	458.8	459.3	459.7	459.7
162.5°	463.7	463.5	463.4	463.4	463.3	463.2	463.8	464.3	464.9	465.4	465.5
165°	468.3	468.2	468.1	468.0	467.9	467.8	468.5	469.1	469.7	470.4	470.4
167.5°	471.9	471.8	471.8	471.8	471.8	471.8	472.4	473.0	473.7	474.3	474.3
170°	475.1	475.0	475.0	475.0	475.0	475.0	475.6	476.2	476.9	477.5	477.5
172.5°	477.0	476.8	476.9	477.0	477.0	477.1	477.8	478.4	479.0	479.7	479.6
175°	478.7	478.6	478.7	478.7	478.8	478.9	479.5	480.0	480.6	481.1	481.1
177.5°	479.5	479.3	479.4	479.5	479.5	479.6	480.2	480.9	481.5	482.2	482.1
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	3344.9	3344.9	3344.9	3344.9
2.5°	2973.2	2967.7	2946.0	2924.3
5°	2520.7	2502.1	2495.9	2489.7
7.5°	2202.5	2201.0	2168.4	2135.8
10°	1922.4	1924.7	1895.2	1865.7
12.5°	1722.1	1702.7	1700.4	1698.1
15°	1571.6	1553.7	1550.6	1547.5
17.5°	1465.2	1454.4	1451.3	1448.2
20°	1384.5	1378.3	1372.9	1367.5
22.5°	1314.7	1306.9	1302.3	1297.6
25°	1247.2	1240.2	1238.6	1237.1
27.5°	1186.6	1178.1	1178.1	1178.1
30°	1129.2	1123.8	1121.4	1119.1
32.5°	1075.7	1071.0	1071.0	1071.0
35°	1025.2	1022.9	1019.8	1016.7
37.5°	979.4	979.4	977.9	976.3
40°	935.2	937.5	937.5	937.5
42.5°	894.8	897.2	897.2	897.2
45°	852.9	856.8	858.3	859.9
47.5°	811.8	818.0	819.5	821.1
50°	771.4	776.1	776.9	777.6
52.5°	730.3	735.7	739.6	743.5
55°	686.8	692.3	694.6	696.9
57.5°	640.3	645.7	646.5	647.3
60°	589.0	594.5	596.0	597.6
62.5°	540.2	543.3	544.8	546.4
65°	484.3	488.9	492.0	495.1
67.5°	430.7	434.6	434.6	434.6
70°	371.0	372.5	374.8	377.2
72.5°	315.9	316.6	316.6	316.6
75°	257.7	259.2	260.0	260.8
77.5°	202.6	203.3	203.3	203.3
80°	148.2	147.5	147.5	147.5
82.5°	101.7	99.3	99.3	99.3
85°	58.2	57.4	58.2	59.0
87.5°	26.4	26.4	26.4	26.4
90°	10.2	10.4	10.5	10.7
92.5°	11.9	12.0	12.1	12.1
95°	13.6	13.6	13.6	13.6
97.5°	14.4	14.5	14.6	14.6
100°	14.8	14.8	14.9	15.0
102.5°	14.9	15.0	15.2	15.3
105°	15.2	15.4	15.5	15.7
107.5°	68.3	57.9	47.5	37.1
110°	132.2	120.8	109.5	98.1



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	186.4	186.2	186.1	185.9
115°	208.9	209.2	209.5	209.8
117.5°	228.9	228.9	229.0	229.1
120°	249.1	249.1	249.1	249.1
122.5°	268.5	268.6	268.6	268.7
125°	286.4	286.6	286.8	286.9
127.5°	305.2	305.1	304.9	304.8
130°	322.4	322.2	322.0	321.9
132.5°	338.3	338.1	337.8	337.6
135°	354.4	354.1	353.9	353.6
137.5°	369.5	369.3	369.1	369.0
140°	383.0	382.9	382.7	382.5
142.5°	395.8	395.5	395.3	395.0
145°	407.9	407.9	407.9	407.9
147.5°	418.4	418.0	417.6	417.2
150°	428.6	428.3	428.1	427.9
152.5°	437.6	437.2	436.8	436.4
155°	445.7	445.2	444.8	444.3
157.5°	453.0	452.3	451.7	451.1
160°	459.2	458.6	458.0	457.5
162.5°	465.0	464.5	464.0	463.6
165°	469.9	469.3	468.7	468.2
167.5°	473.7	473.0	472.4	471.8
170°	476.9	476.2	475.6	475.0
172.5°	478.9	478.2	477.5	476.8
175°	480.4	479.8	479.2	478.5
177.5°	481.3	480.5	479.7	478.9
180°	480.3	480.3	480.3	480.3



TEST NUMBER: P831240

CATALOG NUMBER: S123DIP-S1165D365U840-4F0-1E-UDD-G

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.37	19.50	19.04	20.18	20.98	20.61	21.73	21.28	22.42	23.21
	3H	20.04	21.05	20.72	21.74	22.57	22.05	23.06	22.74	23.75	24.59
	4H	20.63	21.58	21.33	22.28	23.13	22.51	23.46	23.22	24.17	25.01
	6H	21.01	21.89	21.73	22.60	23.46	22.80	23.68	23.52	24.39	25.25
	8H	21.11	21.95	21.84	22.68	23.54	22.87	23.70	23.60	24.44	25.30
	12H	21.17	21.96	21.90	22.69	23.58	22.90	23.69	23.63	24.42	25.31
4H	2H	18.98	19.93	19.69	20.63	21.48	20.80	21.75	21.51	22.46	23.30
	3H	20.83	21.62	21.55	22.36	23.22	22.44	23.23	23.16	23.98	24.84
	4H	21.54	22.25	22.27	23.00	23.89	23.04	23.75	23.77	24.50	25.39
	6H	22.02	22.64	22.78	23.41	24.32	23.45	24.07	24.21	24.84	25.75
	8H	22.17	22.75	22.93	23.51	24.42	23.57	24.15	24.33	24.92	25.83
	12H	22.25	22.76	23.03	23.55	24.47	23.63	24.15	24.41	24.94	25.85
8H	4H	21.82	22.40	22.58	23.17	24.08	23.16	23.74	23.92	24.51	25.42
	6H	22.42	22.90	23.21	23.71	24.62	23.67	24.15	24.46	24.96	25.87
	8H	22.63	23.05	23.43	23.86	24.79	23.85	24.28	24.66	25.09	26.02
	12H	22.76	23.14	23.57	23.93	24.92	23.97	24.34	24.77	25.14	26.13
12H	4H	21.83	22.35	22.61	23.14	24.06	23.15	23.67	23.93	24.46	25.37
	6H	22.47	22.90	23.27	23.71	24.63	23.69	24.11	24.49	24.92	25.85
	8H	22.72	23.09	23.52	23.89	24.88	23.90	24.27	24.70	25.07	26.06