

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831454

Luminaire Tested: S123DIP-S560D1025U835-4F0-1E-UDD-G1

Issue Date: 05/03/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P831454  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 05/03/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1025U835-4F0-1E-UDD-G1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, GRAZE OPTIC  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6118.3 lumens  
Efficiency: N/A  
Efficacy: 134.5 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

### Luminous Intensity Polar Plot





TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	42	
	1	97	92	89	85	88	85	81	79	70	68	66	56	55	54	44	43	42	37	
	2	88	81	75	71	80	74	70	65	62	58	55	50	48	46	39	38	36	31	
	3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32	27	
	4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24	
	5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	27	25	21	
	6	63	52	44	38	58	48	41	36	40	35	31	33	29	27	27	24	22	19	
	7	59	47	39	34	53	43	37	32	37	31	28	30	27	24	25	22	20	17	
	8	54	43	35	30	50	40	33	28	34	28	25	28	24	21	23	20	18	16	
	9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	21	18	16	14	
	10	48	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	17374	17374	17374	17374	17374
5°	21973	20738	17530	14126	12981
10°	22186	22857	17413	11261	9840
15°	16710	21222	17295	9536	8322
20°	11643	17172	17073	8339	7559
25°	8878	13206	16697	7672	7090
30°	7680	10491	16096	7201	6712
35°	7126	8858	15403	6861	6447
40°	6746	7946	14429	6535	6357
45°	6521	7354	13192	6282	6317
50°	6409	6886	11727	6052	6285
55°	6170	6544	10290	5833	6311
60°	5950	6176	8869	5627	6209
65°	5591	5827	7651	5407	6085
70°	5161	5385	6505	5045	5728
75°	4675	4828	5577	4687	5232
80°	3856	4228	4413	4085	4413
85°	3051	3421	3236	3470	3520

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 80°  
 Vertical Angle: 45°  
 Luminance: 15061 cd/sqm



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.6	2.5
10°-20°	379.6	6.2
20°-30°	449.5	7.3
30°-40°	452.0	7.4
40°-50°	414.7	6.8
50°-60°	342.3	5.6
60°-70°	242.1	4.0
70°-80°	129.2	2.1
80°-90°	35.5	0.6
90°-100°	81.8	1.3
100°-110°	247.6	4.0
110°-120°	421.5	6.9
120°-130°	554.5	9.1
130°-140°	623.3	10.2
140°-150°	612.7	10.0
150°-160°	515.9	8.4
160°-170°	343.4	5.6
170°-180°	120.3	2.0
0°-30°	981.7	16.0
0°-40°	1433.7	23.4
0°-60°	2190.6	35.8
0°-90°	2597.4	42.5
90°-120°	750.9	12.3
90°-150°	2541.3	41.5
90°-180°	3521.0	57.5
0°-180°	6118.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1614	1614	1614	1614	1614	
5°	2034	1919	1622	1307	1201	194
15°	1500	1904	1552	856	747	414
25°	748	1112	1406	646	597	353
35°	542	674	1172	522	491	341
45°	428	483	867	413	415	332
55°	329	349	548	311	336	294
65°	220	229	300	212	239	218
75°	112	116	134	113	126	118
85°	25	28	26	28	28	28
90°	30	24	1	24	30	16
95°	78	74	59	74	78	78
105°	238	236	225	236	238	252
115°	425	425	424	425	425	421
125°	614	622	621	622	614	549
135°	805	810	806	810	805	619
145°	977	982	977	982	977	610
155°	1117	1120	1119	1120	1117	515
165°	1215	1216	1219	1216	1215	343
175°	1263	1264	1268	1264	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1819.3	1817.5	1815.6	1806.2	1796.9	1792.4	1787.9	1774.4	1760.9	1745.9	1731.0
5°	2033.6	2038.8	2044.1	2038.1	2032.1	2013.7	1995.4	1971.0	1946.7	1919.3	1892.0
7.5°	2132.4	2135.4	2138.4	2134.7	2130.9	2126.1	2121.2	2099.5	2077.8	2049.7	2021.6
10°	2029.8	2036.6	2043.3	2057.9	2072.5	2089.0	2105.5	2102.5	2099.5	2091.2	2083.0
12.5°	1804.4	1812.6	1820.8	1850.1	1879.3	1916.7	1954.2	1986.4	2018.6	2041.1	2063.5
15°	1499.5	1522.4	1545.2	1571.8	1598.4	1653.4	1708.5	1776.3	1844.1	1904.4	1964.7
17.5°	1235.1	1243.7	1252.3	1280.8	1309.3	1378.6	1447.8	1526.1	1604.4	1704.4	1804.4
20°	1016.4	1024.3	1032.1	1069.6	1107.0	1161.3	1215.6	1303.7	1391.7	1499.1	1606.6
22.5°	853.9	866.2	878.6	899.6	920.5	972.6	1024.6	1102.9	1181.2	1299.9	1418.6
25°	747.5	756.5	765.5	778.2	791.0	832.5	874.1	938.5	1002.9	1111.9	1220.9
27.5°	674.9	678.6	682.3	695.1	707.8	734.8	761.7	817.2	872.6	965.1	1057.6
30°	617.9	620.6	623.2	634.4	645.6	664.0	682.3	722.4	762.5	844.1	925.8
32.5°	578.2	580.1	582.0	590.6	599.2	612.3	625.4	654.6	683.8	751.3	818.7
35°	542.3	543.4	544.5	550.9	557.3	567.0	576.7	598.8	620.9	674.1	727.3
37.5°	510.8	512.3	513.8	517.6	521.3	529.9	538.5	556.1	573.7	614.6	655.4
40°	480.1	482.7	485.4	488.0	490.6	497.7	504.8	518.3	531.8	565.5	599.2
42.5°	453.9	456.5	459.1	460.3	461.4	465.5	469.6	482.0	494.3	519.4	544.5
45°	428.4	429.6	430.7	431.8	432.9	436.3	439.7	450.5	461.4	483.1	504.8
47.5°	405.2	405.2	405.2	406.0	406.7	409.7	412.7	420.6	428.4	445.3	462.1
50°	382.7	382.7	382.7	381.6	380.5	382.4	384.2	390.2	396.2	411.2	426.2
52.5°	355.8	355.8	355.8	356.2	356.5	356.5	356.5	361.8	367.0	380.5	394.0
55°	328.8	330.3	331.8	330.7	329.6	330.3	331.1	334.4	337.8	348.7	359.5
57.5°	301.9	302.6	303.3	303.0	302.6	303.0	303.3	306.3	309.3	317.6	325.8
60°	276.4	276.4	276.4	275.6	274.9	275.6	276.4	277.9	279.4	286.9	294.4
62.5°	247.9	248.3	248.7	249.0	249.4	248.7	247.9	249.8	251.7	257.3	262.9
65°	219.5	219.8	220.2	221.3	222.5	221.7	221.0	222.8	224.7	228.8	232.9
67.5°	194.0	193.2	192.5	192.9	193.2	194.4	195.5	195.9	196.2	200.7	205.2
70°	164.0	164.8	165.5	165.2	164.8	165.2	165.5	166.7	167.8	171.1	174.5
72.5°	137.1	137.4	137.8	137.8	137.8	138.6	139.3	140.4	141.6	143.4	145.3
75°	112.4	112.4	112.4	113.1	113.8	114.2	114.6	114.6	114.6	116.1	117.6
77.5°	85.4	87.3	89.1	88.8	88.4	89.1	89.9	91.0	92.1	92.9	93.6
80°	62.2	62.2	62.2	62.5	62.9	64.0	65.2	65.9	66.7	68.2	69.7
82.5°	39.7	40.1	40.4	41.6	42.7	43.4	44.2	45.3	46.4	46.4	46.4
85°	24.7	24.0	23.2	24.0	24.7	25.5	26.2	26.6	27.0	27.7	28.5
87.5°	12.0	12.0	12.0	12.0	12.0	12.4	12.7	12.7	12.7	12.7	12.7
90°	29.9	29.5	29.1	28.6	28.2	27.5	26.6	25.7	24.8	24.0	21.1
92.5°	42.9	43.4	43.8	44.3	44.7	44.6	43.9	43.3	42.6	41.9	40.6
95°	77.9	77.9	77.9	77.9	77.9	77.4	76.5	75.6	74.8	73.9	72.1
97.5°	111.8	112.0	112.2	112.5	112.7	112.2	111.1	110.0	108.9	107.8	106.5
100°	151.7	151.3	150.8	150.4	150.0	149.4	148.7	148.1	147.4	146.7	145.6
102.5°	192.7	192.9	193.1	193.3	193.5	193.3	192.7	192.0	191.3	190.7	189.1
105°	237.6	237.1	236.7	236.2	235.8	235.6	235.6	235.6	235.6	235.6	233.6
107.5°	283.5	283.7	283.9	284.2	284.4	284.2	283.5	282.8	282.2	281.5	280.6
110°	330.4	330.9	331.3	331.7	332.2	332.0	331.1	330.2	329.3	328.4	328.0

TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	380.3	380.3	380.3	380.3	380.3	379.8	378.7	377.5	376.4	375.3	375.3
115°	425.2	425.5	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2	425.7
117.5°	471.2	471.8	472.5	473.2	473.8	474.1	474.1	474.1	474.1	474.1	474.6
120°	520.1	520.5	521.0	521.4	521.8	522.2	522.4	522.6	522.8	523.1	524.2
122.5°	567.0	567.6	568.3	569.0	569.6	570.3	571.0	571.6	572.3	573.0	573.4
125°	613.9	614.8	615.7	616.6	617.4	618.3	619.2	620.1	621.0	621.9	622.3
127.5°	660.8	661.7	662.6	663.5	664.4	665.5	666.8	668.1	669.5	670.8	671.2
130°	706.7	708.3	709.8	711.4	712.9	714.2	715.0	715.9	716.8	717.7	718.4
132.5°	754.6	755.8	756.9	758.0	759.1	760.2	761.3	762.4	763.5	764.6	765.1
135°	804.6	805.0	805.4	805.9	806.3	807.0	807.9	808.8	809.7	810.5	810.8
137.5°	848.5	849.1	849.8	850.5	851.1	852.0	853.1	854.2	855.4	856.5	855.8
140°	891.4	893.0	894.5	896.1	897.6	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	935.3	936.4	937.5	938.6	939.8	940.4	940.6	940.9	941.1	941.3	940.9
145°	977.2	978.1	979.0	979.9	980.8	981.3	981.6	981.8	982.0	982.2	981.6
147.5°	1015.2	1016.5	1017.8	1019.2	1020.5	1021.2	1021.2	1021.2	1021.2	1021.2	1020.5
150°	1051.1	1052.4	1053.8	1055.1	1056.4	1057.1	1057.1	1057.1	1057.1	1057.1	1056.7
152.5°	1086.1	1087.2	1088.3	1089.4	1090.5	1090.8	1090.4	1089.9	1089.5	1089.0	1088.8
155°	1117.0	1118.5	1120.1	1121.7	1123.2	1123.5	1122.7	1121.8	1120.9	1120.0	1119.8
157.5°	1145.9	1147.3	1148.6	1149.9	1151.3	1151.5	1150.6	1149.7	1148.8	1147.9	1147.7
160°	1173.9	1174.8	1175.7	1176.6	1177.4	1177.3	1176.2	1175.1	1174.0	1172.9	1172.9
162.5°	1194.9	1196.4	1198.0	1199.5	1201.1	1201.3	1200.2	1199.1	1198.0	1196.9	1196.6
165°	1214.8	1216.4	1217.9	1219.5	1221.0	1221.1	1219.8	1218.5	1217.1	1215.8	1215.8
167.5°	1232.8	1234.1	1235.4	1236.8	1238.1	1238.1	1236.8	1235.4	1234.1	1232.8	1232.6
170°	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8	1245.8
172.5°	1255.7	1257.3	1258.9	1260.4	1262.0	1262.1	1260.7	1259.4	1258.1	1256.7	1256.7
175°	1262.7	1264.3	1265.8	1267.4	1268.9	1269.1	1267.7	1266.4	1265.1	1263.7	1263.7
177.5°	1266.7	1268.3	1269.8	1271.4	1272.9	1273.0	1271.7	1270.4	1269.1	1267.7	1267.7
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1726.5	1722.0	1705.5	1689.0	1670.3	1651.6	1637.7	1623.9	1603.3	1582.7	1565.8
5°	1871.0	1850.1	1815.2	1780.4	1733.2	1686.0	1654.2	1622.4	1579.7	1537.0	1502.9
7.5°	1985.6	1949.7	1901.0	1852.3	1790.5	1728.7	1670.3	1611.9	1546.7	1481.5	1428.4
10°	2058.7	2034.3	1978.1	1922.0	1839.2	1756.4	1674.8	1593.1	1509.3	1425.4	1355.0
12.5°	2065.8	2068.0	2016.3	1964.7	1871.0	1777.4	1678.2	1578.9	1473.3	1367.7	1285.7
15°	2003.2	2041.8	2013.3	1984.9	1890.5	1796.1	1674.0	1552.0	1430.2	1308.5	1213.8
17.5°	1887.1	1969.9	1974.0	1978.1	1883.8	1789.4	1654.2	1519.0	1381.2	1243.4	1143.7
20°	1728.7	1850.8	1892.8	1934.7	1857.9	1781.2	1635.8	1490.5	1336.2	1181.9	1077.5
22.5°	1566.9	1715.2	1792.0	1868.8	1811.9	1754.9	1600.3	1445.6	1282.7	1119.8	1013.8
25°	1382.7	1544.5	1662.4	1780.4	1745.6	1710.7	1558.3	1405.9	1232.5	1059.1	950.9
27.5°	1222.0	1386.4	1528.7	1671.0	1663.6	1656.1	1504.8	1353.5	1175.9	998.4	893.9
30°	1079.0	1232.1	1391.3	1550.5	1568.8	1587.2	1441.1	1295.0	1117.2	939.3	838.5
32.5°	952.4	1086.1	1256.8	1427.6	1463.6	1499.5	1367.7	1235.9	1059.9	883.8	786.8
35°	848.6	970.0	1140.7	1311.5	1356.5	1401.4	1286.8	1172.2	1000.7	829.2	736.7
37.5°	756.9	858.4	1025.0	1191.7	1246.7	1301.8	1199.2	1096.6	935.9	775.2	690.2
40°	680.9	762.5	915.7	1068.8	1132.5	1196.2	1111.5	1026.9	874.5	722.0	643.8
42.5°	617.2	689.8	828.8	967.7	1028.8	1089.8	1018.3	946.8	811.2	675.6	604.1
45°	562.9	620.9	747.1	873.3	931.4	989.4	928.0	866.6	747.1	627.7	561.0
47.5°	511.9	561.8	669.6	777.5	829.2	880.8	832.9	785.0	683.8	582.7	522.4
50°	466.3	506.3	600.7	695.1	740.0	785.0	742.6	700.3	617.2	534.0	481.6
52.5°	426.6	459.1	538.2	617.2	655.8	694.3	658.0	621.7	555.8	489.9	444.2
55°	387.2	415.0	483.5	552.0	578.2	604.5	576.4	548.3	495.1	441.9	403.3
57.5°	350.5	375.3	431.4	487.6	507.8	528.1	502.6	477.1	437.0	397.0	364.8
60°	314.6	334.8	381.6	428.4	440.8	453.2	432.6	412.0	383.9	355.8	326.9
62.5°	281.3	299.6	334.4	369.3	377.5	385.7	370.0	354.3	332.9	311.6	289.1
65°	246.8	260.7	289.1	317.6	322.8	328.1	314.2	300.4	284.2	268.1	251.7
67.5°	215.0	224.7	247.9	271.1	271.5	271.9	260.7	249.4	240.4	231.4	218.3
70°	183.9	193.2	208.6	224.0	224.3	224.7	215.7	206.7	200.0	193.2	183.5
72.5°	152.0	158.8	170.4	182.0	181.3	180.5	174.9	169.3	164.0	158.8	151.7
75°	123.2	128.8	136.7	144.6	142.3	140.1	137.1	134.1	129.6	125.1	120.6
77.5°	97.0	100.4	104.9	109.4	107.9	106.4	103.7	101.1	97.7	94.4	92.5
80°	71.2	72.7	75.7	78.6	77.9	77.1	74.2	71.2	70.4	69.7	67.0
82.5°	48.3	50.2	50.9	51.7	51.3	50.9	48.7	46.4	45.7	44.9	44.6
85°	28.8	29.2	29.6	30.0	28.8	27.7	27.0	26.2	26.2	26.2	25.8
87.5°	13.1	13.5	13.5	13.5	13.1	12.7	12.0	11.2	11.6	12.0	12.0
90°	18.2	15.3	12.4	9.9	7.7	5.4	3.2	1.0	3.2	5.4	7.7
92.5°	39.3	37.9	36.6	35.3	33.9	32.6	31.3	29.9	31.3	32.6	33.9
95°	70.3	68.5	66.8	65.1	63.6	62.0	60.4	58.9	60.4	62.0	63.6
97.5°	105.1	103.8	102.5	101.3	100.2	99.0	97.9	96.8	97.9	99.0	100.2
100°	144.5	143.4	142.3	141.1	139.7	138.4	137.1	135.8	137.1	138.4	139.7
102.5°	187.6	186.0	184.4	183.3	182.7	182.0	181.3	180.7	181.3	182.0	182.7
105°	231.6	229.6	227.6	226.4	225.9	225.5	225.0	224.6	225.0	225.5	225.9
107.5°	279.7	278.8	277.9	277.4	277.2	276.9	276.7	276.5	276.7	276.9	277.2
110°	327.5	327.1	326.6	326.2	325.7	325.3	324.9	324.4	324.9	325.3	325.7





TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	375.3	375.3	375.3	375.2	375.0	374.8	374.5	374.3	374.5	374.8	375.0
115°	426.1	426.6	427.0	426.9	426.2	425.6	424.9	424.2	424.9	425.6	426.2
117.5°	475.0	475.5	475.9	476.0	475.8	475.6	475.4	475.1	475.4	475.6	475.8
120°	525.3	526.4	527.5	527.4	526.1	524.7	523.4	522.1	523.4	524.7	526.1
122.5°	573.9	574.3	574.7	574.5	573.6	572.7	571.9	571.0	571.9	572.7	573.6
125°	622.8	623.2	623.7	623.5	622.9	622.2	621.6	620.9	621.6	622.2	622.9
127.5°	671.7	672.1	672.6	672.1	670.8	669.5	668.1	666.8	668.1	669.5	670.8
130°	719.0	719.7	720.4	719.8	718.0	716.3	714.5	712.7	714.5	716.3	718.0
132.5°	765.5	766.0	766.4	765.7	764.0	762.2	760.4	758.6	760.4	762.2	764.0
135°	811.0	811.2	811.4	810.9	809.5	808.2	806.9	805.6	806.9	808.2	809.5
137.5°	855.1	854.5	853.8	852.9	851.8	850.7	849.6	848.5	849.6	850.7	851.8
140°	898.9	898.7	898.5	897.8	896.7	895.6	894.5	893.4	894.5	895.6	896.7
142.5°	940.4	940.0	939.5	938.8	937.7	936.5	935.4	934.3	935.4	936.5	937.7
145°	980.9	980.2	979.6	979.0	978.6	978.1	977.7	977.2	977.7	978.1	978.6
147.5°	1019.8	1019.2	1018.5	1017.7	1016.8	1016.0	1015.1	1014.2	1015.1	1016.0	1016.8
150°	1056.2	1055.8	1055.3	1054.9	1054.4	1054.0	1053.6	1053.1	1053.6	1054.0	1054.4
152.5°	1088.6	1088.4	1088.2	1087.7	1087.0	1086.4	1085.7	1085.1	1085.7	1086.4	1087.0
155°	1119.5	1119.3	1119.1	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0	1119.0
157.5°	1147.5	1147.3	1147.1	1147.1	1147.3	1147.5	1147.7	1147.9	1147.7	1147.5	1147.3
160°	1172.9	1172.9	1172.9	1173.1	1173.6	1174.0	1174.4	1174.9	1174.4	1174.0	1173.6
162.5°	1196.4	1196.2	1196.0	1196.2	1196.9	1197.5	1198.2	1198.8	1198.2	1197.5	1196.9
165°	1215.8	1215.8	1215.8	1216.2	1216.8	1217.5	1218.1	1218.8	1218.1	1217.5	1216.8
167.5°	1232.3	1232.1	1231.9	1232.2	1233.1	1234.0	1234.9	1235.8	1234.9	1234.0	1233.1
170°	1245.8	1245.8	1245.8	1246.2	1247.1	1248.0	1248.9	1249.8	1248.9	1248.0	1247.1
172.5°	1256.7	1256.7	1256.7	1257.2	1258.1	1259.0	1259.8	1260.7	1259.8	1259.0	1258.1
175°	1263.7	1263.7	1263.7	1264.2	1265.1	1265.9	1266.8	1267.7	1266.8	1265.9	1265.1
177.5°	1267.7	1267.7	1267.7	1268.2	1269.1	1269.9	1270.8	1271.7	1270.8	1269.9	1269.1
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1	1614.1
2.5°	1549.0	1534.4	1519.7	1508.5	1497.3	1478.2	1459.1	1454.6	1450.1	1443.7	1437.4
5°	1468.8	1432.9	1396.9	1364.7	1332.5	1307.4	1282.3	1265.8	1249.4	1237.4	1225.4
7.5°	1375.2	1321.3	1267.3	1229.1	1190.9	1154.6	1118.3	1106.7	1095.1	1079.3	1063.6
10°	1284.6	1225.0	1165.5	1115.7	1065.8	1030.3	994.7	980.5	966.2	946.4	926.5
12.5°	1203.7	1138.5	1073.3	1023.2	973.0	938.5	904.1	883.5	862.9	851.6	840.4
15°	1119.0	1049.4	979.7	933.3	886.8	855.7	824.7	806.7	788.7	777.8	767.0
17.5°	1044.1	975.2	906.3	861.7	817.2	788.7	760.2	744.5	728.8	720.5	712.3
20°	973.0	905.6	838.1	794.7	751.3	728.0	704.8	694.7	684.6	677.9	671.1
22.5°	907.8	841.5	775.2	738.2	701.1	682.3	663.6	656.5	649.4	643.8	638.2
25°	842.6	783.5	724.3	692.8	661.4	646.0	630.7	623.6	616.4	610.8	605.2
27.5°	789.5	732.9	676.4	649.4	622.4	610.4	598.5	592.8	587.2	582.0	576.7
30°	737.8	687.2	636.7	613.4	590.2	579.4	568.5	562.9	557.3	552.4	547.5
32.5°	689.8	646.4	603.0	581.6	560.3	551.3	542.3	535.5	528.8	525.1	521.3
35°	644.2	605.2	566.3	548.7	531.0	522.1	513.1	507.5	501.8	498.8	495.8
37.5°	605.2	570.4	535.5	518.7	501.8	493.2	484.6	479.7	474.9	473.7	472.6
40°	565.5	535.5	505.6	489.1	472.6	465.1	457.6	454.7	451.7	450.9	450.2
42.5°	532.5	503.3	474.1	459.1	444.2	437.8	431.4	429.9	428.4	429.6	430.7
45°	494.3	470.0	445.7	431.8	417.9	412.7	407.5	406.3	405.2	407.5	409.7
47.5°	462.1	439.7	417.2	404.1	391.0	387.2	383.5	383.1	382.7	385.7	388.7
50°	429.2	407.5	385.7	375.3	364.8	361.4	358.0	359.2	360.3	365.1	370.0
52.5°	398.5	378.3	358.0	348.3	338.6	336.3	334.1	336.7	339.3	344.5	349.8
55°	364.8	346.4	328.1	320.6	313.1	310.8	308.6	313.8	319.1	323.9	328.8
57.5°	332.6	316.5	300.4	293.6	286.9	286.5	286.1	291.0	295.9	301.1	306.3
60°	298.1	284.6	271.1	265.9	260.7	261.4	262.2	267.8	273.4	277.5	281.6
62.5°	266.6	255.4	244.2	239.3	234.4	236.3	238.2	243.8	249.4	254.3	259.2
65°	235.2	225.8	216.5	213.1	209.7	212.3	215.0	219.8	224.7	228.1	231.4
67.5°	205.2	197.4	189.5	186.9	184.3	186.9	189.5	194.4	199.2	202.6	206.0
70°	173.8	167.4	161.0	159.2	157.3	160.3	163.3	167.4	171.5	174.9	178.3
72.5°	144.6	139.7	134.8	134.4	134.1	136.7	139.3	143.4	147.6	149.8	152.0
75°	116.1	113.5	110.9	110.5	110.1	112.7	115.3	117.6	119.8	121.7	123.6
77.5°	90.6	88.4	86.1	86.5	86.9	88.8	90.6	92.9	95.1	96.2	97.4
80°	64.4	63.7	62.9	63.7	64.4	65.9	67.4	68.9	70.4	71.2	71.9
82.5°	44.2	43.4	42.7	43.8	44.9	46.1	47.2	48.3	49.4	49.8	50.2
85°	25.5	26.6	27.7	27.7	27.7	28.1	28.5	28.8	29.2	28.8	28.5
87.5°	12.0	12.4	12.7	12.7	12.7	13.1	13.5	13.5	13.5	13.1	12.7
90°	9.9	12.4	15.3	18.2	21.1	24.0	24.8	25.7	26.6	27.5	28.2
92.5°	35.3	36.6	37.9	39.3	40.6	41.9	42.6	43.3	43.9	44.6	44.7
95°	65.1	66.8	68.5	70.3	72.1	73.9	74.8	75.6	76.5	77.4	77.9
97.5°	101.3	102.5	103.8	105.1	106.5	107.8	108.9	110.0	111.1	112.2	112.7
100°	141.1	142.3	143.4	144.5	145.6	146.7	147.4	148.1	148.7	149.4	150.0
102.5°	183.3	184.4	186.0	187.6	189.1	190.7	191.3	192.0	192.7	193.3	193.5
105°	226.4	227.6	229.6	231.6	233.6	235.6	235.6	235.6	235.6	235.6	235.8
107.5°	277.4	277.9	278.8	279.7	280.6	281.5	282.2	282.8	283.5	284.2	284.4
110°	326.2	326.6	327.1	327.5	328.0	328.4	329.3	330.2	331.1	332.0	332.2



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.2	375.3	375.3	375.3	375.3	375.3	376.4	377.5	378.7	379.8	380.3
115°	426.9	427.0	426.6	426.1	425.7	425.2	425.5	425.7	425.9	426.1	426.1
117.5°	476.0	475.9	475.5	475.0	474.6	474.1	474.1	474.1	474.1	474.1	473.8
120°	527.4	527.5	526.4	525.3	524.2	523.1	522.8	522.6	522.4	522.2	521.8
122.5°	574.5	574.7	574.3	573.9	573.4	573.0	572.3	571.6	571.0	570.3	569.6
125°	623.5	623.7	623.2	622.8	622.3	621.9	621.0	620.1	619.2	618.3	617.4
127.5°	672.1	672.6	672.1	671.7	671.2	670.8	669.5	668.1	666.8	665.5	664.4
130°	719.8	720.4	719.7	719.0	718.4	717.7	716.8	715.9	715.0	714.2	712.9
132.5°	765.7	766.4	766.0	765.5	765.1	764.6	763.5	762.4	761.3	760.2	759.1
135°	810.9	811.4	811.2	811.0	810.8	810.5	809.7	808.8	807.9	807.0	806.3
137.5°	852.9	853.8	854.5	855.1	855.8	856.5	855.4	854.2	853.1	852.0	851.1
140°	897.8	898.5	898.7	898.9	899.2	899.4	899.2	898.9	898.7	898.5	897.6
142.5°	938.8	939.5	940.0	940.4	940.9	941.3	941.1	940.9	940.6	940.4	939.8
145°	979.0	979.6	980.2	980.9	981.6	982.2	982.0	981.8	981.6	981.3	980.8
147.5°	1017.7	1018.5	1019.2	1019.8	1020.5	1021.2	1021.2	1021.2	1021.2	1021.2	1020.5
150°	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1	1057.1	1057.1	1057.1	1056.4
152.5°	1087.7	1088.2	1088.4	1088.6	1088.8	1089.0	1089.5	1089.9	1090.4	1090.8	1090.5
155°	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9	1121.8	1122.7	1123.5	1123.2
157.5°	1147.1	1147.1	1147.3	1147.5	1147.7	1147.9	1148.8	1149.7	1150.6	1151.5	1151.3
160°	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0	1175.1	1176.2	1177.3	1177.4
162.5°	1196.2	1196.0	1196.2	1196.4	1196.6	1196.9	1198.0	1199.1	1200.2	1201.3	1201.1
165°	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1	1218.5	1219.8	1221.1	1221.0
167.5°	1232.2	1231.9	1232.1	1232.3	1232.6	1232.8	1234.1	1235.4	1236.8	1238.1	1238.1
170°	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3	1248.9	1250.4	1252.0	1252.0
172.5°	1257.2	1256.7	1256.7	1256.7	1256.7	1256.7	1258.1	1259.4	1260.7	1262.1	1262.0
175°	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1	1266.4	1267.7	1269.1	1268.9
177.5°	1268.2	1267.7	1267.7	1267.7	1267.7	1267.7	1269.1	1270.4	1271.7	1273.0	1272.9
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
0°	1614.1	1614.1	1614.1	1614.1
2.5°	1434.7	1432.1	1421.6	1411.1
5°	1216.4	1207.4	1204.4	1201.4
7.5°	1062.8	1062.1	1046.4	1030.6
10°	927.7	928.8	914.5	900.3
12.5°	831.0	821.7	820.5	819.4
15°	758.4	749.8	748.3	746.8
17.5°	707.1	701.8	700.3	698.8
20°	668.1	665.1	662.5	659.9
22.5°	634.4	630.7	628.4	626.2
25°	601.8	598.5	597.7	597.0
27.5°	572.6	568.5	568.5	568.5
30°	544.9	542.3	541.2	540.0
32.5°	519.1	516.8	516.8	516.8
35°	494.7	493.6	492.1	490.6
37.5°	472.6	472.6	471.9	471.1
40°	451.3	452.4	452.4	452.4
42.5°	431.8	432.9	432.9	432.9
45°	411.6	413.5	414.2	415.0
47.5°	391.7	394.7	395.5	396.2
50°	372.3	374.5	374.9	375.3
52.5°	352.4	355.0	356.9	358.8
55°	331.4	334.1	335.2	336.3
57.5°	309.0	311.6	312.0	312.3
60°	284.2	286.9	287.6	288.4
62.5°	260.7	262.2	262.9	263.7
65°	233.7	235.9	237.4	238.9
67.5°	207.9	209.7	209.7	209.7
70°	179.0	179.8	180.9	182.0
72.5°	152.4	152.8	152.8	152.8
75°	124.3	125.1	125.5	125.8
77.5°	97.7	98.1	98.1	98.1
80°	71.5	71.2	71.2	71.2
82.5°	49.1	47.9	47.9	47.9
85°	28.1	27.7	28.1	28.5
87.5°	12.7	12.7	12.7	12.7
90°	28.6	29.1	29.5	29.9
92.5°	44.3	43.8	43.4	42.9
95°	77.9	77.9	77.9	77.9
97.5°	112.5	112.2	112.0	111.8
100°	150.4	150.8	151.3	151.7
102.5°	193.3	193.1	192.9	192.7
105°	236.2	236.7	237.1	237.6
107.5°	284.2	283.9	283.7	283.5
110°	331.7	331.3	330.9	330.4



TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°
112.5°	380.3	380.3	380.3	380.3
115°	425.9	425.7	425.5	425.2
117.5°	473.2	472.5	471.8	471.2
120°	521.4	521.0	520.5	520.1
122.5°	569.0	568.3	567.6	567.0
125°	616.6	615.7	614.8	613.9
127.5°	663.5	662.6	661.7	660.8
130°	711.4	709.8	708.3	706.7
132.5°	758.0	756.9	755.8	754.6
135°	805.9	805.4	805.0	804.6
137.5°	850.5	849.8	849.1	848.5
140°	896.1	894.5	893.0	891.4
142.5°	938.6	937.5	936.4	935.3
145°	979.9	979.0	978.1	977.2
147.5°	1019.2	1017.8	1016.5	1015.2
150°	1055.1	1053.8	1052.4	1051.1
152.5°	1089.4	1088.3	1087.2	1086.1
155°	1121.7	1120.1	1118.5	1117.0
157.5°	1149.9	1148.6	1147.3	1145.9
160°	1176.6	1175.7	1174.8	1173.9
162.5°	1199.5	1198.0	1196.4	1194.9
165°	1219.5	1217.9	1216.4	1214.8
167.5°	1236.8	1235.4	1234.1	1232.8
170°	1250.4	1248.9	1247.3	1245.8
172.5°	1260.4	1258.9	1257.3	1255.7
175°	1267.4	1265.8	1264.3	1262.7
177.5°	1271.4	1269.8	1268.3	1266.7
180°	1270.7	1270.7	1270.7	1270.7

TEST NUMBER: P831454

CATALOG NUMBER: S123DIP-S560D1025U835-4F0-1E-UDD-G1

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.74	13.51	13.76	14.53	15.91	14.97	15.74	16.00	16.77	18.15
	3H	14.38	15.07	15.41	16.10	17.50	16.39	17.08	17.43	18.12	19.52
	4H	14.95	15.60	16.00	16.64	18.05	16.84	17.49	17.89	18.53	19.94
	6H	15.32	15.92	16.38	16.96	18.38	17.11	17.71	18.17	18.75	20.17
	8H	15.41	15.98	16.47	17.04	18.45	17.17	17.74	18.23	18.80	20.21
	12H	15.45	16.00	16.52	17.05	18.48	17.19	17.73	18.25	18.78	20.22
4H	2H	13.30	13.95	14.36	14.99	16.40	15.13	15.78	16.18	16.82	18.22
	3H	15.12	15.66	16.18	16.73	18.15	16.74	17.28	17.80	18.35	19.77
	4H	15.82	16.31	16.88	17.37	18.81	17.32	17.81	18.39	18.87	20.31
	6H	16.29	16.71	17.36	17.80	19.23	17.72	18.14	18.79	19.23	20.66
	8H	16.42	16.82	17.50	17.89	19.34	17.83	18.23	18.90	19.30	20.75
	12H	16.48	16.84	17.58	17.93	19.39	17.87	18.23	18.96	19.32	20.77
8H	4H	16.08	16.47	17.15	17.55	19.00	17.42	17.81	18.49	18.89	20.34
	6H	16.66	16.99	17.76	18.11	19.55	17.92	18.24	19.02	19.36	20.81
	8H	16.87	17.16	17.98	18.26	19.72	18.09	18.38	19.20	19.48	20.95
	12H	16.99	17.24	18.10	18.34	19.84	18.19	18.45	19.30	19.54	21.05
12H	4H	16.07	16.43	17.17	17.52	18.98	17.39	17.75	18.48	18.84	20.29
	6H	16.71	17.00	17.82	18.10	19.57	17.93	18.22	19.04	19.32	20.78
	8H	16.94	17.19	18.05	18.29	19.80	18.12	18.38	19.23	19.47	20.98