

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331947

Luminaire Tested: **S123DIP-S560D1195U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331947  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D1195U835-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6488.3 lumens  
Efficiency: N/A  
Efficacy: 131.3 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37				
1	95	91	87	84	86	83	79	77	67	65	63	52	51	50	39	38	38	31				
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32	27				
3	79	70	63	57	71	64	58	53	52	48	44	41	38	36	31	29	27	23				
4	72	62	54	49	65	57	50	45	46	41	38	37	33	30	28	25	24	20				
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	23	21	17				
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15				
7	56	45	37	31	51	41	34	29	34	29	25	27	23	20	21	18	16	13				
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	14	12				
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11				
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8509	8509	8509	8509
5°	10147	8546	7573	8546
10°	12701	8502	6840	8502
15°	15578	8433	6367	8433
20°	18558	8326	6063	8326
25°	19705	8197	5995	8197
30°	16890	8103	6027	8103
35°	11746	7967	6089	7967
40°	8847	7808	6070	7808
45°	7346	7573	5993	7573
50°	6581	7093	5940	7093
55°	6152	6576	5864	6576
60°	5772	6036	5804	6036
65°	5422	5501	5619	5501
70°	5086	4894	5350	4894
75°	4554	4284	4907	4284
80°	3986	3515	4228	3515
85°	3125	2556	2841	2556



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.9	1.2
10°-20°	249.7	3.8
20°-30°	419.1	6.5
30°-40°	474.5	7.3
40°-50°	425.5	6.6
50°-60°	343.4	5.3
60°-70°	239.3	3.7
70°-80°	125.8	1.9
80°-90°	35.1	0.5
90°-100°	96.4	1.5
100°-110°	288.4	4.4
110°-120°	490.5	7.6
120°-130°	645.2	9.9
130°-140°	725.2	11.2
140°-150°	712.8	11.0
150°-160°	600.1	9.2
160°-170°	399.5	6.2
170°-180°	139.9	2.2
0°-30°	746.6	11.5
0°-40°	1221.1	18.8
0°-60°	1990.1	30.7
0°-90°	2390.3	36.8
90°-120°	875.3	13.5
90°-150°	2958.5	45.6
90°-180°	4098.0	63.2
0°-180°	6488.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	790	790	790	790	790	
5°	939	791	701	791	939	97
15°	1398	757	571	757	1398	404
25°	1659	690	505	690	1659	728
35°	894	606	463	606	894	581
45°	483	498	394	498	483	382
55°	328	350	312	350	328	294
65°	213	216	221	216	213	212
75°	110	103	118	103	110	117
85°	25	21	23	21	25	31
90°	35	1	35	1	35	18
95°	91	69	91	69	91	93
105°	276	261	276	261	276	293
115°	495	494	495	494	495	490
125°	715	723	715	723	715	639
135°	936	938	936	938	936	720
145°	1138	1138	1138	1138	1138	710
155°	1300	1302	1300	1302	1300	599
165°	1414	1419	1414	1419	1414	399
175°	1470	1476	1470	1476	1470	140
180°	1479	1479	1479	1479	1479	



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	838.9	838.3	836.8	838.0	835.5	832.2	831.9	828.8	819.9	819.3	816.9
5°	939.1	936.0	935.7	935.3	929.9	922.6	908.8	907.7	889.3	880.1	869.0
7.5°	1068.9	1070.5	1064.9	1060.0	1043.6	1032.8	1018.0	999.1	976.5	953.6	938.3
10°	1162.0	1174.6	1158.9	1148.2	1138.3	1119.5	1097.7	1070.5	1043.3	1011.5	987.4
12.5°	1261.9	1268.1	1265.0	1254.8	1239.4	1210.8	1172.1	1142.2	1117.1	1064.2	1042.8
15°	1397.9	1421.3	1406.4	1371.9	1372.7	1345.5	1294.9	1239.4	1209.9	1163.5	1100.3
17.5°	1542.9	1545.8	1539.4	1510.7	1491.5	1454.2	1407.5	1354.3	1294.5	1238.5	1171.4
20°	1620.1	1617.8	1604.4	1589.4	1556.5	1527.4	1476.4	1417.1	1340.5	1285.3	1212.2
22.5°	1663.0	1659.1	1652.8	1640.3	1612.9	1581.6	1535.9	1471.0	1398.1	1322.1	1237.6
25°	1659.1	1664.1	1664.9	1661.4	1651.9	1633.1	1597.1	1545.4	1472.6	1375.0	1286.9
27.5°	1509.0	1516.0	1536.5	1554.7	1575.0	1595.6	1592.9	1567.2	1513.4	1429.0	1321.3
30°	1358.9	1343.5	1381.5	1429.3	1461.9	1519.3	1551.5	1553.4	1523.2	1450.8	1345.8
32.5°	1150.5	1167.4	1184.1	1243.0	1314.2	1378.7	1442.7	1494.3	1500.2	1452.0	1360.2
35°	893.9	915.0	945.6	976.3	1052.9	1118.7	1231.3	1329.4	1407.5	1417.8	1361.5
37.5°	720.3	730.8	750.1	780.8	830.9	909.1	996.2	1120.1	1233.3	1317.5	1321.2
40°	629.6	632.7	654.5	677.9	718.5	782.8	861.4	970.9	1106.5	1224.1	1273.1
42.5°	561.6	568.4	577.6	600.1	632.4	680.8	753.8	844.4	968.6	1103.9	1199.8
45°	482.6	490.2	496.0	510.9	533.9	566.4	617.4	700.1	794.7	934.5	1063.6
47.5°	430.3	430.9	435.2	446.5	462.1	486.6	522.6	575.7	662.6	775.9	908.5
50°	393.0	399.1	400.6	409.4	421.7	439.7	469.6	514.7	586.0	685.6	807.4
52.5°	366.6	368.4	372.7	379.1	389.8	403.8	429.7	465.1	521.0	605.9	717.9
55°	327.8	327.8	332.1	337.0	343.2	355.8	373.0	399.1	441.6	507.5	600.2
57.5°	292.0	293.9	296.9	298.4	303.6	312.0	326.4	346.2	377.9	428.6	502.3
60°	268.1	271.5	271.2	274.2	278.8	285.3	297.6	313.7	342.0	382.6	444.7
62.5°	247.3	247.0	247.0	250.6	255.2	261.4	269.4	283.3	307.4	343.4	396.2
65°	212.9	212.2	214.9	217.2	218.7	223.3	229.4	241.7	257.8	284.6	325.5
67.5°	182.5	180.2	181.7	182.5	185.1	188.7	194.4	202.0	214.8	236.3	267.2
70°	161.6	159.7	159.3	160.1	162.4	165.1	169.3	176.6	188.4	205.7	228.3
72.5°	140.2	138.9	138.8	140.5	141.6	143.3	146.3	153.0	162.4	175.3	196.4
75°	109.5	109.5	109.5	109.9	111.1	112.6	114.9	118.3	125.6	134.8	149.0
77.5°	82.1	82.0	81.6	81.5	83.2	83.9	84.4	87.6	91.7	97.9	108.2
80°	64.3	62.4	63.2	64.3	65.1	65.5	66.6	67.4	70.9	74.3	81.6
82.5°	47.8	46.2	46.3	48.1	48.3	48.6	49.8	50.9	52.2	55.3	59.2
85°	25.3	25.3	25.7	25.7	26.0	25.7	26.8	27.2	27.2	29.1	31.4
87.5°	16.2	15.4	15.7	15.9	15.4	15.6	15.7	15.8	15.9	16.0	15.6
90°	34.9	34.3	33.8	33.3	32.8	32.0	31.0	30.0	28.9	27.9	24.5
92.5°	46.9	47.2	47.6	47.9	48.2	47.9	47.1	46.3	45.4	44.6	42.7
95°	90.6	90.6	90.6	90.6	90.6	90.1	89.1	88.0	87.0	86.0	83.9
97.5°	139.4	139.5	139.6	139.7	139.8	139.3	138.1	136.9	135.7	134.5	133.0
100°	176.6	176.1	175.6	175.1	174.5	173.9	173.1	172.3	171.6	170.8	169.5
102.5°	214.7	214.8	214.9	215.0	215.1	214.8	214.0	213.2	212.5	211.7	210.0
105°	276.5	276.0	275.5	275.0	274.5	274.2	274.2	274.2	274.2	274.2	271.9
107.5°	340.9	341.2	341.5	341.8	342.1	341.9	341.1	340.2	339.4	338.6	337.6
110°	384.6	385.1	385.6	386.1	386.6	386.4	385.4	384.3	383.3	382.3	381.7



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	431.1	431.2	431.3	431.4	431.5	430.9	429.7	428.4	427.2	425.9	425.8
115°	495.0	495.2	495.5	495.7	496.0	496.0	495.7	495.5	495.2	495.0	495.5
117.5°	559.8	560.5	561.2	562.0	562.7	563.1	563.1	563.2	563.2	563.3	564.0
120°	605.3	605.9	606.4	606.9	607.4	607.8	608.1	608.3	608.6	608.8	610.1
122.5°	649.0	649.7	650.5	651.2	651.9	652.6	653.3	654.0	654.6	655.3	656.0
125°	714.6	715.6	716.6	717.7	718.7	719.7	720.8	721.8	722.8	723.9	724.4
127.5°	779.9	781.0	782.2	783.4	784.6	785.9	787.4	788.8	790.3	791.7	792.3
130°	822.6	824.4	826.2	828.0	829.8	831.3	832.3	833.3	834.4	835.4	836.2
132.5°	867.2	868.6	870.0	871.4	872.8	874.1	875.4	876.6	877.8	879.1	879.6
135°	936.5	937.0	937.5	938.0	938.5	939.3	940.3	941.4	942.4	943.4	943.7
137.5°	997.6	998.6	999.6	1000.5	1001.5	1002.5	1003.6	1004.7	1005.8	1006.9	1006.2
140°	1037.6	1039.4	1041.2	1043.0	1044.8	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6
142.5°	1078.5	1079.9	1081.2	1082.6	1084.0	1084.9	1085.1	1085.4	1085.6	1085.9	1085.4
145°	1137.5	1138.5	1139.5	1140.6	1141.6	1142.3	1142.5	1142.8	1143.0	1143.3	1142.5
147.5°	1190.0	1191.5	1193.1	1194.6	1196.2	1197.0	1197.0	1197.0	1197.0	1197.0	1196.2
150°	1223.5	1225.0	1226.6	1228.1	1229.7	1230.4	1230.4	1230.4	1230.4	1230.4	1229.9
152.5°	1256.0	1257.3	1258.7	1260.0	1261.4	1261.8	1261.4	1261.0	1260.6	1260.2	1259.9
155°	1300.1	1302.0	1303.8	1305.6	1307.4	1307.8	1306.7	1305.7	1304.7	1303.6	1303.4
157.5°	1340.3	1341.8	1343.2	1344.7	1346.1	1346.3	1345.2	1344.1	1343.1	1342.0	1341.8
160°	1366.4	1367.4	1368.4	1369.5	1370.5	1370.4	1369.1	1367.8	1366.5	1365.2	1365.2
162.5°	1385.9	1387.5	1389.2	1390.8	1392.5	1392.7	1391.4	1390.1	1388.8	1387.5	1387.3
165°	1414.0	1415.8	1417.6	1419.4	1421.2	1421.4	1419.8	1418.3	1416.7	1415.2	1415.2
167.5°	1437.9	1439.5	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9	1437.7
170°	1450.0	1451.8	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0	1450.0
172.5°	1459.3	1461.1	1462.9	1464.7	1466.6	1466.7	1465.1	1463.5	1461.9	1460.3	1460.3
175°	1469.8	1471.6	1473.4	1475.2	1477.0	1477.1	1475.6	1474.0	1472.5	1470.9	1470.9
177.5°	1475.4	1476.8	1478.2	1479.7	1481.1	1481.2	1480.0	1478.8	1477.5	1476.3	1476.3
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	815.0	812.6	810.1	805.8	802.1	796.9	795.4	793.6	788.1	783.1	779.5
5°	864.8	855.6	842.2	829.9	820.0	806.6	798.9	790.9	779.4	769.1	760.6
7.5°	916.9	898.8	878.0	855.5	834.5	814.2	797.9	783.4	767.3	752.0	740.2
10°	958.3	932.2	903.1	871.7	844.9	818.8	797.0	777.9	757.2	739.2	724.2
12.5°	1005.4	966.8	926.7	888.5	856.8	820.7	794.3	769.9	746.5	724.8	708.0
15°	1061.3	1012.3	964.8	912.3	864.0	818.8	787.4	756.8	729.6	707.4	685.9
17.5°	1112.1	1056.6	994.0	930.2	872.0	818.4	774.4	739.8	705.8	678.6	657.2
20°	1140.9	1077.7	1006.9	940.6	876.3	816.5	768.3	726.9	690.2	661.4	637.3
22.5°	1165.8	1091.8	1018.5	947.7	876.0	811.6	757.0	714.4	674.5	646.4	620.8
25°	1191.5	1103.0	1029.5	946.4	866.3	799.7	738.4	690.2	650.3	617.4	591.0
27.5°	1213.6	1102.3	1015.0	925.6	851.2	784.4	719.0	667.2	624.9	589.1	562.3
30°	1228.3	1103.8	1000.0	911.5	836.5	767.5	703.9	651.9	607.4	571.0	545.8
32.5°	1237.5	1102.9	986.2	891.9	813.2	752.2	687.7	633.8	588.1	552.4	528.0
35°	1242.8	1096.1	962.5	851.4	775.6	716.2	662.2	606.3	558.4	525.1	497.5
37.5°	1232.1	1082.0	934.9	812.3	729.3	670.9	625.4	577.8	532.0	495.3	471.5
40°	1215.2	1072.8	913.4	784.8	697.4	641.1	602.5	555.7	510.5	475.7	453.5
42.5°	1183.1	1054.1	889.9	754.1	664.3	608.0	572.4	533.4	490.6	457.9	435.7
45°	1104.6	1013.4	854.5	708.2	615.5	557.3	525.9	497.5	458.8	427.0	407.9
47.5°	995.6	952.2	803.3	659.7	564.5	508.5	475.8	453.0	424.7	399.1	380.7
50°	920.0	902.0	768.7	626.6	530.4	475.7	444.3	423.6	403.3	377.6	360.8
52.5°	832.6	843.7	728.2	592.3	495.8	442.0	412.4	396.0	377.6	356.5	341.8
55°	709.7	749.9	658.4	534.7	444.3	393.0	365.0	350.4	339.7	324.0	311.4
57.5°	594.6	645.7	582.8	475.3	393.6	349.4	322.6	306.7	299.8	291.6	281.7
60°	526.2	576.8	528.9	435.5	359.6	317.5	293.8	280.4	273.5	267.7	259.3
62.5°	465.3	516.4	476.2	395.0	326.2	287.2	266.5	253.4	248.0	245.0	237.8
65°	381.5	425.5	398.7	332.1	278.4	244.0	225.2	216.0	211.0	209.9	205.3
67.5°	310.5	344.0	324.5	275.4	233.2	203.4	187.5	179.7	175.9	175.5	172.0
70°	263.9	295.3	280.4	235.9	199.5	176.2	162.4	155.5	153.2	152.8	150.9
72.5°	227.7	249.6	237.8	200.7	172.6	151.4	141.2	134.0	131.4	132.0	130.7
75°	168.5	185.0	178.1	152.4	129.8	116.0	107.6	103.0	100.7	101.9	100.3
77.5°	121.3	131.7	125.5	107.7	93.8	83.8	77.6	74.8	72.7	72.6	71.9
80°	91.5	97.7	94.2	83.5	72.0	63.6	58.6	56.7	55.5	55.2	54.8
82.5°	65.2	70.4	66.3	59.0	51.2	46.1	43.3	40.8	39.9	40.1	39.8
85°	32.9	34.9	33.3	28.7	25.7	23.4	21.8	20.7	19.9	20.3	19.5
87.5°	15.6	15.2	13.6	11.8	10.7	9.2	8.7	7.6	7.5	8.0	8.2
90°	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2	3.7	6.3	8.9
92.5°	40.8	38.9	37.0	35.1	33.4	31.6	29.9	28.1	29.9	31.6	33.4
95°	81.8	79.8	77.7	75.8	74.0	72.2	70.4	68.6	70.4	72.2	74.0
97.5°	131.6	130.1	128.6	127.1	125.8	124.5	123.1	121.8	123.1	124.5	125.8
100°	168.2	166.9	165.6	164.2	162.7	161.1	159.6	158.0	159.6	161.1	162.7
102.5°	208.3	206.6	204.9	203.6	202.6	201.7	200.8	199.8	200.8	201.7	202.6
105°	269.6	267.2	264.9	263.5	263.0	262.5	261.9	261.4	261.9	262.5	263.0
107.5°	336.7	335.8	334.9	334.2	333.9	333.6	333.3	333.0	333.3	333.6	333.9
110°	381.2	380.7	380.2	379.7	379.2	378.6	378.1	377.6	378.1	378.6	379.2





TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	425.7	425.6	425.5	425.3	425.0	424.7	424.4	424.1	424.4	424.7	425.0
115°	496.0	496.5	497.0	496.9	496.1	495.3	494.6	493.8	494.6	495.3	496.1
117.5°	564.6	565.3	566.0	566.0	565.5	565.0	564.5	564.0	564.5	565.0	565.5
120°	611.4	612.7	614.0	613.9	612.3	610.8	609.2	607.7	609.2	610.8	612.3
122.5°	656.6	657.3	658.0	657.8	656.6	655.5	654.3	653.2	654.3	655.5	656.6
125°	724.9	725.4	725.9	725.8	725.0	724.2	723.5	722.7	723.5	724.2	725.0
127.5°	792.8	793.4	794.0	793.4	791.8	790.1	788.5	786.8	788.5	790.1	791.8
130°	836.9	837.7	838.5	837.8	835.8	833.7	831.6	829.6	831.6	833.7	835.8
132.5°	880.2	880.8	881.4	880.6	878.5	876.5	874.4	872.3	874.4	876.5	878.5
135°	944.0	944.2	944.5	943.8	942.3	940.7	939.2	937.6	939.2	940.7	942.3
137.5°	1005.5	1004.9	1004.2	1003.2	1001.9	1000.6	999.3	998.1	999.3	1000.6	1001.9
140°	1046.3	1046.1	1045.8	1045.0	1043.8	1042.5	1041.2	1039.9	1041.2	1042.5	1043.8
142.5°	1085.0	1084.5	1084.0	1083.2	1081.9	1080.6	1079.3	1078.0	1079.3	1080.6	1081.9
145°	1141.7	1141.0	1140.2	1139.5	1139.0	1138.5	1138.0	1137.5	1138.0	1138.5	1139.0
147.5°	1195.5	1194.8	1194.1	1193.3	1192.3	1191.4	1190.5	1189.5	1190.5	1191.4	1192.3
150°	1229.4	1228.9	1228.4	1227.9	1227.3	1226.8	1226.3	1225.8	1226.3	1226.8	1227.3
152.5°	1259.6	1259.2	1258.9	1258.4	1257.7	1257.0	1256.3	1255.5	1256.3	1257.0	1257.7
155°	1303.1	1302.9	1302.6	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5	1302.5
157.5°	1341.6	1341.4	1341.1	1341.2	1341.5	1341.8	1342.1	1342.4	1342.1	1341.8	1341.5
160°	1365.2	1365.2	1365.2	1365.5	1366.0	1366.5	1367.0	1367.5	1367.0	1366.5	1366.0
162.5°	1387.1	1386.9	1386.7	1387.0	1387.7	1388.4	1389.1	1389.8	1389.1	1388.4	1387.7
165°	1415.2	1415.2	1415.2	1415.6	1416.3	1417.1	1417.9	1418.7	1417.9	1417.1	1416.3
167.5°	1437.5	1437.3	1437.1	1437.5	1438.6	1439.6	1440.6	1441.7	1440.6	1439.6	1438.6
170°	1450.0	1450.0	1450.0	1450.5	1451.6	1452.6	1453.6	1454.7	1453.6	1452.6	1451.6
172.5°	1460.3	1460.3	1460.3	1460.8	1461.8	1462.8	1463.9	1464.9	1463.9	1462.8	1461.8
175°	1470.9	1470.9	1470.9	1471.5	1472.5	1473.5	1474.6	1475.6	1474.6	1473.5	1472.5
177.5°	1476.3	1476.3	1476.3	1476.7	1477.5	1478.4	1479.2	1480.0	1479.2	1478.4	1477.5
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	777.3	775.2	772.1	767.5	763.8	758.0	758.0	758.9	758.9	758.6	758.0
5°	753.7	748.0	741.1	733.1	724.6	716.2	714.7	711.6	709.3	707.8	705.9
7.5°	728.8	718.7	708.6	697.4	687.1	678.6	672.7	667.8	664.6	661.3	658.8
10°	712.0	699.3	687.5	675.6	662.6	652.2	645.7	641.1	637.7	634.6	633.1
12.5°	692.1	677.6	664.5	653.2	639.0	628.3	622.1	620.0	615.9	609.5	606.1
15°	663.0	649.6	633.9	616.6	609.7	596.7	589.4	586.0	583.7	578.7	577.2
17.5°	638.1	620.5	602.9	590.0	577.2	566.7	562.6	558.3	555.3	551.2	550.0
20°	618.2	602.5	586.4	572.6	559.2	547.7	544.2	541.2	538.1	536.2	534.7
22.5°	597.9	582.2	568.9	556.0	541.7	534.2	530.4	527.1	524.9	523.6	522.1
25°	569.5	555.7	540.8	529.3	517.8	512.8	510.5	508.6	507.1	505.2	504.8
27.5°	544.1	529.1	517.0	506.2	498.0	493.8	491.6	490.7	491.0	491.7	492.1
30°	525.1	511.3	501.3	492.1	484.5	480.7	480.3	480.3	481.8	482.2	483.0
32.5°	507.6	496.3	486.3	477.4	471.6	469.0	470.5	470.5	471.7	472.7	474.1
35°	482.2	472.2	464.6	456.9	451.9	453.1	453.8	454.6	456.5	458.8	460.4
37.5°	457.9	449.3	441.3	435.3	433.0	435.1	436.9	438.5	440.8	442.5	444.0
40°	440.4	433.9	426.3	420.9	421.7	422.8	424.4	426.3	428.2	429.3	430.9
42.5°	424.2	417.4	411.6	407.1	408.2	409.7	410.6	411.6	413.8	415.9	416.8
45°	399.5	394.1	388.7	386.1	386.8	387.6	388.4	389.5	391.4	393.0	393.3
47.5°	371.7	367.9	364.3	361.7	362.9	362.6	363.6	366.1	366.7	367.6	369.7
50°	353.9	350.4	346.2	345.5	345.5	345.5	345.8	348.9	348.9	350.4	352.0
52.5°	334.3	332.1	329.4	328.0	327.4	327.4	329.0	330.5	331.1	333.3	334.8
55°	305.2	302.9	300.7	299.5	298.7	299.5	302.6	303.3	305.2	306.4	307.5
57.5°	275.0	273.2	271.4	270.8	270.6	271.6	273.3	275.6	276.1	279.6	281.3
60°	255.1	252.4	250.9	250.9	250.1	253.5	252.8	256.6	257.4	259.7	262.4
62.5°	234.5	230.9	230.3	230.3	231.4	232.4	233.5	235.2	237.2	240.1	242.1
65°	201.5	199.5	202.2	201.8	201.1	203.4	203.4	205.3	207.6	210.3	214.5
67.5°	170.1	169.1	169.4	169.4	170.5	171.8	172.9	174.6	177.3	180.2	182.9
70°	149.0	150.1	148.2	149.8	150.9	151.3	152.0	154.3	157.4	159.3	162.4
72.5°	128.5	128.4	128.6	129.2	130.4	131.1	131.8	134.4	137.8	139.4	141.9
75°	98.8	98.4	99.6	99.6	101.5	102.3	103.0	104.2	107.2	109.5	111.5
77.5°	72.2	72.6	72.4	73.7	73.2	73.3	75.7	76.8	77.1	81.7	82.7
80°	54.4	55.2	55.5	55.9	56.3	55.5	58.2	59.4	59.4	62.0	64.0
82.5°	39.1	39.5	40.5	40.9	41.0	41.7	42.0	42.8	43.7	44.9	47.4
85°	19.5	20.7	21.1	20.7	21.1	20.3	21.4	21.8	22.2	22.2	22.2
87.5°	8.4	9.3	9.7	10.7	11.0	12.0	12.2	11.8	12.0	13.1	12.1
90°	11.5	14.5	17.8	21.2	24.5	27.9	28.9	30.0	31.0	32.0	32.8
92.5°	35.1	37.0	38.9	40.8	42.7	44.6	45.4	46.3	47.1	47.9	48.2
95°	75.8	77.7	79.8	81.8	83.9	86.0	87.0	88.0	89.1	90.1	90.6
97.5°	127.1	128.6	130.1	131.6	133.0	134.5	135.7	136.9	138.1	139.3	139.8
100°	164.2	165.6	166.9	168.2	169.5	170.8	171.6	172.3	173.1	173.9	174.5
102.5°	203.6	204.9	206.6	208.3	210.0	211.7	212.5	213.2	214.0	214.8	215.1
105°	263.5	264.9	267.2	269.6	271.9	274.2	274.2	274.2	274.2	274.2	274.5
107.5°	334.2	334.9	335.8	336.7	337.6	338.6	339.4	340.2	341.1	341.9	342.1
110°	379.7	380.2	380.7	381.2	381.7	382.3	383.3	384.3	385.4	386.4	386.6



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	425.3	425.5	425.6	425.7	425.8	425.9	427.2	428.4	429.7	430.9	431.5
115°	496.9	497.0	496.5	496.0	495.5	495.0	495.2	495.5	495.7	496.0	496.0
117.5°	566.0	566.0	565.3	564.6	564.0	563.3	563.2	563.2	563.1	563.1	562.7
120°	613.9	614.0	612.7	611.4	610.1	608.8	608.6	608.3	608.1	607.8	607.4
122.5°	657.8	658.0	657.3	656.6	656.0	655.3	654.6	654.0	653.3	652.6	651.9
125°	725.8	725.9	725.4	724.9	724.4	723.9	722.8	721.8	720.8	719.7	718.7
127.5°	793.4	794.0	793.4	792.8	792.3	791.7	790.3	788.8	787.4	785.9	784.6
130°	837.8	838.5	837.7	836.9	836.2	835.4	834.4	833.3	832.3	831.3	829.8
132.5°	880.6	881.4	880.8	880.2	879.6	879.1	877.8	876.6	875.4	874.1	872.8
135°	943.8	944.5	944.2	944.0	943.7	943.4	942.4	941.4	940.3	939.3	938.5
137.5°	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8	1004.7	1003.6	1002.5	1001.5
140°	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6	1046.3	1046.1	1045.8	1044.8
142.5°	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6	1085.4	1085.1	1084.9	1084.0
145°	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0	1142.8	1142.5	1142.3	1141.6
147.5°	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0	1197.0	1197.0	1197.0	1196.2
150°	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4	1230.4	1230.4	1230.4	1229.7
152.5°	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6	1261.0	1261.4	1261.8	1261.4
155°	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7	1305.7	1306.7	1307.8	1307.4
157.5°	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1	1344.1	1345.2	1346.3	1346.1
160°	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5	1367.8	1369.1	1370.4	1370.5
162.5°	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8	1390.1	1391.4	1392.7	1392.5
165°	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7	1418.3	1419.8	1421.4	1421.2
167.5°	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5	1441.1	1442.7	1444.3	1444.3
170°	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8	1453.6	1455.5	1457.3	1457.3
172.5°	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9	1463.5	1465.1	1466.7	1466.6
175°	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5	1474.0	1475.6	1477.1	1477.0
177.5°	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5	1478.8	1480.0	1481.2	1481.1
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	755.9	755.6	757.7	756.2	757.7	755.6	755.9	758.0	758.6	758.9	758.9
5°	703.6	704.7	700.9	700.9	700.9	704.7	703.6	705.9	707.8	709.3	711.6
7.5°	657.0	655.3	655.5	653.4	655.5	655.3	657.0	658.8	661.3	664.6	667.8
10°	628.5	626.2	625.4	625.8	625.4	626.2	628.5	633.1	634.6	637.7	641.1
12.5°	604.9	604.4	599.4	599.5	599.4	604.4	604.9	606.1	609.5	615.9	620.0
15°	577.2	569.9	569.1	571.4	569.1	569.9	577.2	577.2	578.7	583.7	586.0
17.5°	549.4	545.5	545.8	544.6	545.8	545.5	549.4	550.0	551.2	555.3	558.3
20°	534.7	532.4	532.0	529.3	532.0	532.4	534.7	534.7	536.2	538.1	541.2
22.5°	521.2	520.4	520.6	517.7	520.6	520.4	521.2	522.1	523.6	524.9	527.1
25°	504.4	506.3	504.8	504.8	504.8	506.3	504.4	504.8	505.2	507.1	508.6
27.5°	493.1	493.0	492.2	492.2	492.2	493.0	493.1	492.1	491.7	491.0	490.7
30°	484.5	484.1	484.9	484.9	484.9	484.1	484.5	483.0	482.2	481.8	480.3
32.5°	475.9	476.4	476.6	476.9	476.6	476.4	475.9	474.1	472.7	471.7	470.5
35°	462.7	463.0	464.2	463.4	464.2	463.0	462.7	460.4	458.8	456.5	454.6
37.5°	444.7	446.5	446.1	446.7	446.1	446.5	444.7	444.0	442.5	440.8	438.5
40°	431.3	432.4	432.0	432.0	432.0	432.4	431.3	430.9	429.3	428.2	426.3
42.5°	417.5	418.3	417.3	416.7	417.3	418.3	417.5	416.8	415.9	413.8	411.6
45°	394.9	394.1	395.3	393.7	395.3	394.1	394.9	393.3	393.0	391.4	389.5
47.5°	369.6	370.4	370.7	371.8	370.7	370.4	369.6	369.7	367.6	366.7	366.1
50°	352.7	355.0	355.0	354.7	355.0	355.0	352.7	352.0	350.4	348.9	348.9
52.5°	336.2	337.3	338.8	338.7	338.8	337.3	336.2	334.8	333.3	331.1	330.5
55°	310.6	311.4	312.1	312.5	312.1	311.4	310.6	307.5	306.4	305.2	303.3
57.5°	284.1	283.8	285.6	286.2	285.6	283.8	284.1	281.3	279.6	276.1	275.6
60°	265.4	265.4	268.5	269.6	268.5	265.4	265.4	262.4	259.7	257.4	256.6
62.5°	245.5	246.7	249.8	248.2	249.8	246.7	245.5	242.1	240.1	237.2	235.2
65°	216.4	219.5	219.1	220.6	219.1	219.5	216.4	214.5	210.3	207.6	205.3
67.5°	186.0	187.9	190.7	190.9	190.7	187.9	186.0	182.9	180.2	177.3	174.6
70°	165.5	167.4	168.9	170.0	168.9	167.4	165.5	162.4	159.3	157.4	154.3
72.5°	145.5	146.5	150.2	148.6	150.2	146.5	145.5	141.9	139.4	137.8	134.4
75°	114.1	116.8	119.1	118.0	119.1	116.8	114.1	111.5	109.5	107.2	104.2
77.5°	84.4	87.1	88.2	87.2	88.2	87.1	84.4	82.7	81.7	77.1	76.8
80°	66.6	66.3	68.6	68.2	68.6	66.3	66.6	64.0	62.0	59.4	59.4
82.5°	48.9	48.5	49.6	49.8	49.6	48.5	48.9	47.4	44.9	43.7	42.8
85°	23.7	24.9	23.4	23.0	23.4	24.9	23.7	22.2	22.2	22.2	21.8
87.5°	12.2	12.3	12.1	11.9	12.1	12.3	12.2	12.1	13.1	12.0	11.8
90°	33.3	33.8	34.3	34.9	34.3	33.8	33.3	32.8	32.0	31.0	30.0
92.5°	47.9	47.6	47.2	46.9	47.2	47.6	47.9	48.2	47.9	47.1	46.3
95°	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.6	90.1	89.1	88.0
97.5°	139.7	139.6	139.5	139.4	139.5	139.6	139.7	139.8	139.3	138.1	136.9
100°	175.1	175.6	176.1	176.6	176.1	175.6	175.1	174.5	173.9	173.1	172.3
102.5°	215.0	214.9	214.8	214.7	214.8	214.9	215.0	215.1	214.8	214.0	213.2
105°	275.0	275.5	276.0	276.5	276.0	275.5	275.0	274.5	274.2	274.2	274.2
107.5°	341.8	341.5	341.2	340.9	341.2	341.5	341.8	342.1	341.9	341.1	340.2
110°	386.1	385.6	385.1	384.6	385.1	385.6	386.1	386.6	386.4	385.4	384.3



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	431.4	431.3	431.2	431.1	431.2	431.3	431.4	431.5	430.9	429.7	428.4
115°	495.7	495.5	495.2	495.0	495.2	495.5	495.7	496.0	496.0	495.7	495.5
117.5°	562.0	561.2	560.5	559.8	560.5	561.2	562.0	562.7	563.1	563.1	563.2
120°	606.9	606.4	605.9	605.3	605.9	606.4	606.9	607.4	607.8	608.1	608.3
122.5°	651.2	650.5	649.7	649.0	649.7	650.5	651.2	651.9	652.6	653.3	654.0
125°	717.7	716.6	715.6	714.6	715.6	716.6	717.7	718.7	719.7	720.8	721.8
127.5°	783.4	782.2	781.0	779.9	781.0	782.2	783.4	784.6	785.9	787.4	788.8
130°	828.0	826.2	824.4	822.6	824.4	826.2	828.0	829.8	831.3	832.3	833.3
132.5°	871.4	870.0	868.6	867.2	868.6	870.0	871.4	872.8	874.1	875.4	876.6
135°	938.0	937.5	937.0	936.5	937.0	937.5	938.0	938.5	939.3	940.3	941.4
137.5°	1000.5	999.6	998.6	997.6	998.6	999.6	1000.5	1001.5	1002.5	1003.6	1004.7
140°	1043.0	1041.2	1039.4	1037.6	1039.4	1041.2	1043.0	1044.8	1045.8	1046.1	1046.3
142.5°	1082.6	1081.2	1079.9	1078.5	1079.9	1081.2	1082.6	1084.0	1084.9	1085.1	1085.4
145°	1140.6	1139.5	1138.5	1137.5	1138.5	1139.5	1140.6	1141.6	1142.3	1142.5	1142.8
147.5°	1194.6	1193.1	1191.5	1190.0	1191.5	1193.1	1194.6	1196.2	1197.0	1197.0	1197.0
150°	1228.1	1226.6	1225.0	1223.5	1225.0	1226.6	1228.1	1229.7	1230.4	1230.4	1230.4
152.5°	1260.0	1258.7	1257.3	1256.0	1257.3	1258.7	1260.0	1261.4	1261.8	1261.4	1261.0
155°	1305.6	1303.8	1302.0	1300.1	1302.0	1303.8	1305.6	1307.4	1307.8	1306.7	1305.7
157.5°	1344.7	1343.2	1341.8	1340.3	1341.8	1343.2	1344.7	1346.1	1346.3	1345.2	1344.1
160°	1369.5	1368.4	1367.4	1366.4	1367.4	1368.4	1369.5	1370.5	1370.4	1369.1	1367.8
162.5°	1390.8	1389.2	1387.5	1385.9	1387.5	1389.2	1390.8	1392.5	1392.7	1391.4	1390.1
165°	1419.4	1417.6	1415.8	1414.0	1415.8	1417.6	1419.4	1421.2	1421.4	1419.8	1418.3
167.5°	1442.7	1441.1	1439.5	1437.9	1439.5	1441.1	1442.7	1444.3	1444.3	1442.7	1441.1
170°	1455.5	1453.6	1451.8	1450.0	1451.8	1453.6	1455.5	1457.3	1457.3	1455.5	1453.6
172.5°	1464.7	1462.9	1461.1	1459.3	1461.1	1462.9	1464.7	1466.6	1466.7	1465.1	1463.5
175°	1475.2	1473.4	1471.6	1469.8	1471.6	1473.4	1475.2	1477.0	1477.1	1475.6	1474.0
177.5°	1479.7	1478.2	1476.8	1475.4	1476.8	1478.2	1479.7	1481.1	1481.2	1480.0	1478.8
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	758.0	758.0	763.8	767.5	772.1	775.2	777.3	779.5	783.1	788.1	793.6
5°	714.7	716.2	724.6	733.1	741.1	748.0	753.7	760.6	769.1	779.4	790.9
7.5°	672.7	678.6	687.1	697.4	708.6	718.7	728.8	740.2	752.0	767.3	783.4
10°	645.7	652.2	662.6	675.6	687.5	699.3	712.0	724.2	739.2	757.2	777.9
12.5°	622.1	628.3	639.0	653.2	664.5	677.6	692.1	708.0	724.8	746.5	769.9
15°	589.4	596.7	609.7	616.6	633.9	649.6	663.0	685.9	707.4	729.6	756.8
17.5°	562.6	566.7	577.2	590.0	602.9	620.5	638.1	657.2	678.6	705.8	739.8
20°	544.2	547.7	559.2	572.6	586.4	602.5	618.2	637.3	661.4	690.2	726.9
22.5°	530.4	534.2	541.7	556.0	568.9	582.2	597.9	620.8	646.4	674.5	714.4
25°	510.5	512.8	517.8	529.3	540.8	555.7	569.5	591.0	617.4	650.3	690.2
27.5°	491.6	493.8	498.0	506.2	517.0	529.1	544.1	562.3	589.1	624.9	667.2
30°	480.3	480.7	484.5	492.1	501.3	511.3	525.1	545.8	571.0	607.4	651.9
32.5°	470.5	469.0	471.6	477.4	486.3	496.3	507.6	528.0	552.4	588.1	633.8
35°	453.8	453.1	451.9	456.9	464.6	472.2	482.2	497.5	525.1	558.4	606.3
37.5°	436.9	435.1	433.0	435.3	441.3	449.3	457.9	471.5	495.3	532.0	577.8
40°	424.4	422.8	421.7	420.9	426.3	433.9	440.4	453.5	475.7	510.5	555.7
42.5°	410.6	409.7	408.2	407.1	411.6	417.4	424.2	435.7	457.9	490.6	533.4
45°	388.4	387.6	386.8	386.1	388.7	394.1	399.5	407.9	427.0	458.8	497.5
47.5°	363.6	362.6	362.9	361.7	364.3	367.9	371.7	380.7	399.1	424.7	453.0
50°	345.8	345.5	345.5	345.5	346.2	350.4	353.9	360.8	377.6	403.3	423.6
52.5°	329.0	327.4	327.4	328.0	329.4	332.1	334.3	341.8	356.5	377.6	396.0
55°	302.6	299.5	298.7	299.5	300.7	302.9	305.2	311.4	324.0	339.7	350.4
57.5°	273.3	271.6	270.6	270.8	271.4	273.2	275.0	281.7	291.6	299.8	306.7
60°	252.8	253.5	250.1	250.9	250.9	252.4	255.1	259.3	267.7	273.5	280.4
62.5°	233.5	232.4	231.4	230.3	230.3	230.9	234.5	237.8	245.0	248.0	253.4
65°	203.4	203.4	201.1	201.8	202.2	199.5	201.5	205.3	209.9	211.0	216.0
67.5°	172.9	171.8	170.5	169.4	169.4	169.1	170.1	172.0	175.5	175.9	179.7
70°	152.0	151.3	150.9	149.8	148.2	150.1	149.0	150.9	152.8	153.2	155.5
72.5°	131.8	131.1	130.4	129.2	128.6	128.4	128.5	130.7	132.0	131.4	134.0
75°	103.0	102.3	101.5	99.6	99.6	98.4	98.8	100.3	101.9	100.7	103.0
77.5°	75.7	73.3	73.2	73.7	72.4	72.6	72.2	71.9	72.6	72.7	74.8
80°	58.2	55.5	56.3	55.9	55.5	55.2	54.4	54.8	55.2	55.5	56.7
82.5°	42.0	41.7	41.0	40.9	40.5	39.5	39.1	39.8	40.1	39.9	40.8
85°	21.4	20.3	21.1	20.7	21.1	20.7	19.5	19.5	20.3	19.9	20.7
87.5°	12.2	12.0	11.0	10.7	9.7	9.3	8.4	8.2	8.0	7.5	7.6
90°	28.9	27.9	24.5	21.2	17.8	14.5	11.5	8.9	6.3	3.7	1.2
92.5°	45.4	44.6	42.7	40.8	38.9	37.0	35.1	33.4	31.6	29.9	28.1
95°	87.0	86.0	83.9	81.8	79.8	77.7	75.8	74.0	72.2	70.4	68.6
97.5°	135.7	134.5	133.0	131.6	130.1	128.6	127.1	125.8	124.5	123.1	121.8
100°	171.6	170.8	169.5	168.2	166.9	165.6	164.2	162.7	161.1	159.6	158.0
102.5°	212.5	211.7	210.0	208.3	206.6	204.9	203.6	202.6	201.7	200.8	199.8
105°	274.2	274.2	271.9	269.6	267.2	264.9	263.5	263.0	262.5	261.9	261.4
107.5°	339.4	338.6	337.6	336.7	335.8	334.9	334.2	333.9	333.6	333.3	333.0
110°	383.3	382.3	381.7	381.2	380.7	380.2	379.7	379.2	378.6	378.1	377.6



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	427.2	425.9	425.8	425.7	425.6	425.5	425.3	425.0	424.7	424.4	424.1
115°	495.2	495.0	495.5	496.0	496.5	497.0	496.9	496.1	495.3	494.6	493.8
117.5°	563.2	563.3	564.0	564.6	565.3	566.0	566.0	565.5	565.0	564.5	564.0
120°	608.6	608.8	610.1	611.4	612.7	614.0	613.9	612.3	610.8	609.2	607.7
122.5°	654.6	655.3	656.0	656.6	657.3	658.0	657.8	656.6	655.5	654.3	653.2
125°	722.8	723.9	724.4	724.9	725.4	725.9	725.8	725.0	724.2	723.5	722.7
127.5°	790.3	791.7	792.3	792.8	793.4	794.0	793.4	791.8	790.1	788.5	786.8
130°	834.4	835.4	836.2	836.9	837.7	838.5	837.8	835.8	833.7	831.6	829.6
132.5°	877.8	879.1	879.6	880.2	880.8	881.4	880.6	878.5	876.5	874.4	872.3
135°	942.4	943.4	943.7	944.0	944.2	944.5	943.8	942.3	940.7	939.2	937.6
137.5°	1005.8	1006.9	1006.2	1005.5	1004.9	1004.2	1003.2	1001.9	1000.6	999.3	998.1
140°	1046.6	1046.9	1046.6	1046.3	1046.1	1045.8	1045.0	1043.8	1042.5	1041.2	1039.9
142.5°	1085.6	1085.9	1085.4	1085.0	1084.5	1084.0	1083.2	1081.9	1080.6	1079.3	1078.0
145°	1143.0	1143.3	1142.5	1141.7	1141.0	1140.2	1139.5	1139.0	1138.5	1138.0	1137.5
147.5°	1197.0	1197.0	1196.2	1195.5	1194.8	1194.1	1193.3	1192.3	1191.4	1190.5	1189.5
150°	1230.4	1230.4	1229.9	1229.4	1228.9	1228.4	1227.9	1227.3	1226.8	1226.3	1225.8
152.5°	1260.6	1260.2	1259.9	1259.6	1259.2	1258.9	1258.4	1257.7	1257.0	1256.3	1255.5
155°	1304.7	1303.6	1303.4	1303.1	1302.9	1302.6	1302.5	1302.5	1302.5	1302.5	1302.5
157.5°	1343.1	1342.0	1341.8	1341.6	1341.4	1341.1	1341.2	1341.5	1341.8	1342.1	1342.4
160°	1366.5	1365.2	1365.2	1365.2	1365.2	1365.2	1365.5	1366.0	1366.5	1367.0	1367.5
162.5°	1388.8	1387.5	1387.3	1387.1	1386.9	1386.7	1387.0	1387.7	1388.4	1389.1	1389.8
165°	1416.7	1415.2	1415.2	1415.2	1415.2	1415.2	1415.6	1416.3	1417.1	1417.9	1418.7
167.5°	1439.5	1437.9	1437.7	1437.5	1437.3	1437.1	1437.5	1438.6	1439.6	1440.6	1441.7
170°	1451.8	1450.0	1450.0	1450.0	1450.0	1450.0	1450.5	1451.6	1452.6	1453.6	1454.7
172.5°	1461.9	1460.3	1460.3	1460.3	1460.3	1460.3	1460.8	1461.8	1462.8	1463.9	1464.9
175°	1472.5	1470.9	1470.9	1470.9	1470.9	1470.9	1471.5	1472.5	1473.5	1474.6	1475.6
177.5°	1477.5	1476.3	1476.3	1476.3	1476.3	1476.3	1476.7	1477.5	1478.4	1479.2	1480.0
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	795.4	796.9	802.1	805.8	810.1	812.6	815.0	816.9	819.3	819.9	828.8
5°	798.9	806.6	820.0	829.9	842.2	855.6	864.8	869.0	880.1	889.3	907.7
7.5°	797.9	814.2	834.5	855.5	878.0	898.8	916.9	938.3	953.6	976.5	999.1
10°	797.0	818.8	844.9	871.7	903.1	932.2	958.3	987.4	1011.5	1043.3	1070.5
12.5°	794.3	820.7	856.8	888.5	926.7	966.8	1005.4	1042.8	1064.2	1117.1	1142.2
15°	787.4	818.8	864.0	912.3	964.8	1012.3	1061.3	1100.3	1163.5	1209.9	1239.4
17.5°	774.4	818.4	872.0	930.2	994.0	1056.6	1112.1	1171.4	1238.5	1294.5	1354.3
20°	768.3	816.5	876.3	940.6	1006.9	1077.7	1140.9	1212.2	1285.3	1340.5	1417.1
22.5°	757.0	811.6	876.0	947.7	1018.5	1091.8	1165.8	1237.6	1322.1	1398.1	1471.0
25°	738.4	799.7	866.3	946.4	1029.5	1103.0	1191.5	1286.9	1375.0	1472.6	1545.4
27.5°	719.0	784.4	851.2	925.6	1015.0	1102.3	1213.6	1321.3	1429.0	1513.4	1567.2
30°	703.9	767.5	836.5	911.5	1000.0	1103.8	1228.3	1345.8	1450.8	1523.2	1553.4
32.5°	687.7	752.2	813.2	891.9	986.2	1102.9	1237.5	1360.2	1452.0	1500.2	1494.3
35°	662.2	716.2	775.6	851.4	962.5	1096.1	1242.8	1361.5	1417.8	1407.5	1329.4
37.5°	625.4	670.9	729.3	812.3	934.9	1082.0	1232.1	1321.2	1317.5	1233.3	1120.1
40°	602.5	641.1	697.4	784.8	913.4	1072.8	1215.2	1273.1	1224.1	1106.5	970.9
42.5°	572.4	608.0	664.3	754.1	889.9	1054.1	1183.1	1199.8	1103.9	968.6	844.4
45°	525.9	557.3	615.5	708.2	854.5	1013.4	1104.6	1063.6	934.5	794.7	700.1
47.5°	475.8	508.5	564.5	659.7	803.3	952.2	995.6	908.5	775.9	662.6	575.7
50°	444.3	475.7	530.4	626.6	768.7	902.0	920.0	807.4	685.6	586.0	514.7
52.5°	412.4	442.0	495.8	592.3	728.2	843.7	832.6	717.9	605.9	521.0	465.1
55°	365.0	393.0	444.3	534.7	658.4	749.9	709.7	600.2	507.5	441.6	399.1
57.5°	322.6	349.4	393.6	475.3	582.8	645.7	594.6	502.3	428.6	377.9	346.2
60°	293.8	317.5	359.6	435.5	528.9	576.8	526.2	444.7	382.6	342.0	313.7
62.5°	266.5	287.2	326.2	395.0	476.2	516.4	465.3	396.2	343.4	307.4	283.3
65°	225.2	244.0	278.4	332.1	398.7	425.5	381.5	325.5	284.6	257.8	241.7
67.5°	187.5	203.4	233.2	275.4	324.5	344.0	310.5	267.2	236.3	214.8	202.0
70°	162.4	176.2	199.5	235.9	280.4	295.3	263.9	228.3	205.7	188.4	176.6
72.5°	141.2	151.4	172.6	200.7	237.8	249.6	227.7	196.4	175.3	162.4	153.0
75°	107.6	116.0	129.8	152.4	178.1	185.0	168.5	149.0	134.8	125.6	118.3
77.5°	77.6	83.8	93.8	107.7	125.5	131.7	121.3	108.2	97.9	91.7	87.6
80°	58.6	63.6	72.0	83.5	94.2	97.7	91.5	81.6	74.3	70.9	67.4
82.5°	43.3	46.1	51.2	59.0	66.3	70.4	65.2	59.2	55.3	52.2	50.9
85°	21.8	23.4	25.7	28.7	33.3	34.9	32.9	31.4	29.1	27.2	27.2
87.5°	8.7	9.2	10.7	11.8	13.6	15.2	15.6	15.6	16.0	15.9	15.8
90°	3.7	6.3	8.9	11.5	14.5	17.8	21.2	24.5	27.9	28.9	30.0
92.5°	29.9	31.6	33.4	35.1	37.0	38.9	40.8	42.7	44.6	45.4	46.3
95°	70.4	72.2	74.0	75.8	77.7	79.8	81.8	83.9	86.0	87.0	88.0
97.5°	123.1	124.5	125.8	127.1	128.6	130.1	131.6	133.0	134.5	135.7	136.9
100°	159.6	161.1	162.7	164.2	165.6	166.9	168.2	169.5	170.8	171.6	172.3
102.5°	200.8	201.7	202.6	203.6	204.9	206.6	208.3	210.0	211.7	212.5	213.2
105°	261.9	262.5	263.0	263.5	264.9	267.2	269.6	271.9	274.2	274.2	274.2
107.5°	333.3	333.6	333.9	334.2	334.9	335.8	336.7	337.6	338.6	339.4	340.2
110°	378.1	378.6	379.2	379.7	380.2	380.7	381.2	381.7	382.3	383.3	384.3





TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	424.4	424.7	425.0	425.3	425.5	425.6	425.7	425.8	425.9	427.2	428.4
115°	494.6	495.3	496.1	496.9	497.0	496.5	496.0	495.5	495.0	495.2	495.5
117.5°	564.5	565.0	565.5	566.0	566.0	565.3	564.6	564.0	563.3	563.2	563.2
120°	609.2	610.8	612.3	613.9	614.0	612.7	611.4	610.1	608.8	608.6	608.3
122.5°	654.3	655.5	656.6	657.8	658.0	657.3	656.6	656.0	655.3	654.6	654.0
125°	723.5	724.2	725.0	725.8	725.9	725.4	724.9	724.4	723.9	722.8	721.8
127.5°	788.5	790.1	791.8	793.4	794.0	793.4	792.8	792.3	791.7	790.3	788.8
130°	831.6	833.7	835.8	837.8	838.5	837.7	836.9	836.2	835.4	834.4	833.3
132.5°	874.4	876.5	878.5	880.6	881.4	880.8	880.2	879.6	879.1	877.8	876.6
135°	939.2	940.7	942.3	943.8	944.5	944.2	944.0	943.7	943.4	942.4	941.4
137.5°	999.3	1000.6	1001.9	1003.2	1004.2	1004.9	1005.5	1006.2	1006.9	1005.8	1004.7
140°	1041.2	1042.5	1043.8	1045.0	1045.8	1046.1	1046.3	1046.6	1046.9	1046.6	1046.3
142.5°	1079.3	1080.6	1081.9	1083.2	1084.0	1084.5	1085.0	1085.4	1085.9	1085.6	1085.4
145°	1138.0	1138.5	1139.0	1139.5	1140.2	1141.0	1141.7	1142.5	1143.3	1143.0	1142.8
147.5°	1190.5	1191.4	1192.3	1193.3	1194.1	1194.8	1195.5	1196.2	1197.0	1197.0	1197.0
150°	1226.3	1226.8	1227.3	1227.9	1228.4	1228.9	1229.4	1229.9	1230.4	1230.4	1230.4
152.5°	1256.3	1257.0	1257.7	1258.4	1258.9	1259.2	1259.6	1259.9	1260.2	1260.6	1261.0
155°	1302.5	1302.5	1302.5	1302.5	1302.6	1302.9	1303.1	1303.4	1303.6	1304.7	1305.7
157.5°	1342.1	1341.8	1341.5	1341.2	1341.1	1341.4	1341.6	1341.8	1342.0	1343.1	1344.1
160°	1367.0	1366.5	1366.0	1365.5	1365.2	1365.2	1365.2	1365.2	1365.2	1366.5	1367.8
162.5°	1389.1	1388.4	1387.7	1387.0	1386.7	1386.9	1387.1	1387.3	1387.5	1388.8	1390.1
165°	1417.9	1417.1	1416.3	1415.6	1415.2	1415.2	1415.2	1415.2	1415.2	1416.7	1418.3
167.5°	1440.6	1439.6	1438.6	1437.5	1437.1	1437.3	1437.5	1437.7	1437.9	1439.5	1441.1
170°	1453.6	1452.6	1451.6	1450.5	1450.0	1450.0	1450.0	1450.0	1450.0	1451.8	1453.6
172.5°	1463.9	1462.8	1461.8	1460.8	1460.3	1460.3	1460.3	1460.3	1460.3	1461.9	1463.5
175°	1474.6	1473.5	1472.5	1471.5	1470.9	1470.9	1470.9	1470.9	1470.9	1472.5	1474.0
177.5°	1479.2	1478.4	1477.5	1476.7	1476.3	1476.3	1476.3	1476.3	1476.3	1477.5	1478.8
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	790.5	790.5	790.5	790.5	790.5	790.5	790.5
2.5°	831.9	832.2	835.5	838.0	836.8	838.3	838.9
5°	908.8	922.6	929.9	935.3	935.7	936.0	939.1
7.5°	1018.0	1032.8	1043.6	1060.0	1064.9	1070.5	1068.9
10°	1097.7	1119.5	1138.3	1148.2	1158.9	1174.6	1162.0
12.5°	1172.1	1210.8	1239.4	1254.8	1265.0	1268.1	1261.9
15°	1294.9	1345.5	1372.7	1371.9	1406.4	1421.3	1397.9
17.5°	1407.5	1454.2	1491.5	1510.7	1539.4	1545.8	1542.9
20°	1476.4	1527.4	1556.5	1589.4	1604.4	1617.8	1620.1
22.5°	1535.9	1581.6	1612.9	1640.3	1652.8	1659.1	1663.0
25°	1597.1	1633.1	1651.9	1661.4	1664.9	1664.1	1659.1
27.5°	1592.9	1595.6	1575.0	1554.7	1536.5	1516.0	1509.0
30°	1551.5	1519.3	1461.9	1429.3	1381.5	1343.5	1358.9
32.5°	1442.7	1378.7	1314.2	1243.0	1184.1	1167.4	1150.5
35°	1231.3	1118.7	1052.9	976.3	945.6	915.0	893.9
37.5°	996.2	909.1	830.9	780.8	750.1	730.8	720.3
40°	861.4	782.8	718.5	677.9	654.5	632.7	629.6
42.5°	753.8	680.8	632.4	600.1	577.6	568.4	561.6
45°	617.4	566.4	533.9	510.9	496.0	490.2	482.6
47.5°	522.6	486.6	462.1	446.5	435.2	430.9	430.3
50°	469.6	439.7	421.7	409.4	400.6	399.1	393.0
52.5°	429.7	403.8	389.8	379.1	372.7	368.4	366.6
55°	373.0	355.8	343.2	337.0	332.1	327.8	327.8
57.5°	326.4	312.0	303.6	298.4	296.9	293.9	292.0
60°	297.6	285.3	278.8	274.2	271.2	271.5	268.1
62.5°	269.4	261.4	255.2	250.6	247.0	247.0	247.3
65°	229.4	223.3	218.7	217.2	214.9	212.2	212.9
67.5°	194.4	188.7	185.1	182.5	181.7	180.2	182.5
70°	169.3	165.1	162.4	160.1	159.3	159.7	161.6
72.5°	146.3	143.3	141.6	140.5	138.8	138.9	140.2
75°	114.9	112.6	111.1	109.9	109.5	109.5	109.5
77.5°	84.4	83.9	83.2	81.5	81.6	82.0	82.1
80°	66.6	65.5	65.1	64.3	63.2	62.4	64.3
82.5°	49.8	48.6	48.3	48.1	46.3	46.2	47.8
85°	26.8	25.7	26.0	25.7	25.7	25.3	25.3
87.5°	15.7	15.6	15.4	15.9	15.7	15.4	16.2
90°	31.0	32.0	32.8	33.3	33.8	34.3	34.9
92.5°	47.1	47.9	48.2	47.9	47.6	47.2	46.9
95°	89.1	90.1	90.6	90.6	90.6	90.6	90.6
97.5°	138.1	139.3	139.8	139.7	139.6	139.5	139.4
100°	173.1	173.9	174.5	175.1	175.6	176.1	176.6
102.5°	214.0	214.8	215.1	215.0	214.9	214.8	214.7
105°	274.2	274.2	274.5	275.0	275.5	276.0	276.5
107.5°	341.1	341.9	342.1	341.8	341.5	341.2	340.9
110°	385.4	386.4	386.6	386.1	385.6	385.1	384.6



TEST NUMBER: P331947

CATALOG NUMBER: S123DIP-S560D1195U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	429.7	430.9	431.5	431.4	431.3	431.2	431.1
115°	495.7	496.0	496.0	495.7	495.5	495.2	495.0
117.5°	563.1	563.1	562.7	562.0	561.2	560.5	559.8
120°	608.1	607.8	607.4	606.9	606.4	605.9	605.3
122.5°	653.3	652.6	651.9	651.2	650.5	649.7	649.0
125°	720.8	719.7	718.7	717.7	716.6	715.6	714.6
127.5°	787.4	785.9	784.6	783.4	782.2	781.0	779.9
130°	832.3	831.3	829.8	828.0	826.2	824.4	822.6
132.5°	875.4	874.1	872.8	871.4	870.0	868.6	867.2
135°	940.3	939.3	938.5	938.0	937.5	937.0	936.5
137.5°	1003.6	1002.5	1001.5	1000.5	999.6	998.6	997.6
140°	1046.1	1045.8	1044.8	1043.0	1041.2	1039.4	1037.6
142.5°	1085.1	1084.9	1084.0	1082.6	1081.2	1079.9	1078.5
145°	1142.5	1142.3	1141.6	1140.6	1139.5	1138.5	1137.5
147.5°	1197.0	1197.0	1196.2	1194.6	1193.1	1191.5	1190.0
150°	1230.4	1230.4	1229.7	1228.1	1226.6	1225.0	1223.5
152.5°	1261.4	1261.8	1261.4	1260.0	1258.7	1257.3	1256.0
155°	1306.7	1307.8	1307.4	1305.6	1303.8	1302.0	1300.1
157.5°	1345.2	1346.3	1346.1	1344.7	1343.2	1341.8	1340.3
160°	1369.1	1370.4	1370.5	1369.5	1368.4	1367.4	1366.4
162.5°	1391.4	1392.7	1392.5	1390.8	1389.2	1387.5	1385.9
165°	1419.8	1421.4	1421.2	1419.4	1417.6	1415.8	1414.0
167.5°	1442.7	1444.3	1444.3	1442.7	1441.1	1439.5	1437.9
170°	1455.5	1457.3	1457.3	1455.5	1453.6	1451.8	1450.0
172.5°	1465.1	1466.7	1466.6	1464.7	1462.9	1461.1	1459.3
175°	1475.6	1477.1	1477.0	1475.2	1473.4	1471.6	1469.8
177.5°	1480.0	1481.2	1481.1	1479.7	1478.2	1476.8	1475.4
180°	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1	1479.1

(END OF REPORT)