

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332070-840

Luminaire Tested: **S123DIP-S1165D805U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332070-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D805U840-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7591.6 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	91	91	91		79	79	79		68	68	68	63
1	101	96	92	89	94	90	87	84	80	77	74		70	68	66		60	59	58	53
2	92	84	78	72	86	79	73	69	70	65	62		61	58	55		53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52		54	50	46		47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44		48	43	40		42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38		43	38	35		38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33		39	34	30		34	30	27	25
7	60	47	39	33	56	45	37	32	40	34	29		36	31	27		31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24		30	25	22		27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.9	2.3
10°-20°	491.0	6.5
20°-30°	725.3	9.6
30°-40°	847.3	11.2
40°-50°	851.8	11.2
50°-60°	748.3	9.9
60°-70°	557.5	7.3
70°-80°	317.6	4.2
80°-90°	94.1	1.2
90°-100°	65.5	0.9
100°-110°	196.0	2.6
110°-120°	333.3	4.4
120°-130°	438.5	5.8
130°-140°	492.8	6.5
140°-150°	484.4	6.4
150°-160°	407.8	5.4
160°-170°	271.5	3.6
170°-180°	95.1	1.3
0°-30°	1390.3	18.3
0°-40°	2237.6	29.5
0°-60°	3837.7	50.6
0°-90°	4806.9	63.3
90°-120°	594.8	7.8
90°-150°	2010.5	26.5
90°-180°	2785.0	36.7
0°-180°	7591.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	1	9	19	22	24	7
95°	47	52	58	61	62	52
105°	178	180	186	186	188	190
115°	336	338	336	337	336	332
125°	491	493	492	489	486	438
135°	637	642	641	638	636	491
145°	773	775	777	776	773	483
155°	885	885	886	889	884	407
165°	964	962	962	966	961	272
175°	1003	1000	1000	1004	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.2	32.7	32.2	31.7	31.2	31.0	31.2	31.4	31.5	31.7	31.6
90°	0.8	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7
92.5°	19.1	20.3	21.5	22.7	23.8	25.1	26.5	27.8	29.0	30.3	30.9
95°	46.6	47.8	49.1	50.3	51.5	52.8	54.2	55.6	57.1	58.5	59.2
97.5°	82.7	83.6	84.5	85.4	86.4	87.4	88.4	89.4	90.4	91.4	92.2
100°	107.3	108.5	109.5	110.6	111.6	112.6	113.4	114.3	115.2	116.0	116.6
102.5°	135.8	136.4	137.0	137.7	138.4	139.3	140.4	141.6	142.7	143.9	144.4
105°	177.6	178.0	178.3	178.7	179.0	180.1	181.6	183.2	184.8	186.3	186.3
107.5°	226.3	226.5	226.7	226.9	227.1	227.5	228.2	228.8	229.4	230.0	230.7
110°	256.6	256.9	257.3	257.6	258.0	258.3	258.7	259.0	259.4	259.7	260.4



TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.2	288.4	288.6	288.8	289.0	289.1	289.2	289.3	289.4	289.4	290.3
115°	335.6	336.1	336.6	337.1	337.7	337.8	337.4	337.1	336.7	336.4	336.5
117.5°	383.2	383.6	384.0	384.3	384.7	384.6	384.2	383.6	383.2	382.7	382.7
120°	412.9	413.9	415.1	416.1	417.2	417.3	416.4	415.5	414.7	413.7	413.5
122.5°	443.9	444.6	445.5	446.2	447.0	447.2	446.7	446.3	445.8	445.4	444.8
125°	491.1	491.6	492.1	492.7	493.2	493.3	492.9	492.6	492.2	491.9	491.2
127.5°	534.7	535.8	536.9	538.1	539.2	539.6	539.2	538.8	538.4	538.0	537.0
130°	563.7	565.1	566.5	567.9	569.4	569.8	569.3	568.8	568.3	567.6	566.9
132.5°	592.8	594.2	595.6	597.0	598.4	599.0	598.5	598.1	597.7	597.3	596.5
135°	637.1	638.2	639.2	640.4	641.4	641.9	641.7	641.5	641.3	641.2	640.5
137.5°	678.2	679.1	679.9	680.9	681.8	682.4	682.9	683.3	683.8	684.2	683.5
140°	706.6	707.5	708.4	709.3	710.1	710.6	710.8	711.0	711.2	711.3	711.2
142.5°	732.6	733.5	734.3	735.2	736.1	736.7	737.0	737.3	737.6	737.9	737.7
145°	773.0	773.4	773.7	774.1	774.4	774.8	775.4	775.9	776.4	776.9	776.8
147.5°	808.4	809.0	809.6	810.2	810.9	811.4	811.9	812.4	812.9	813.4	813.4
150°	832.9	833.3	833.6	834.0	834.4	834.8	835.1	835.5	835.8	836.2	836.2
152.5°	853.2	853.6	854.1	854.6	855.2	855.6	855.8	856.0	856.2	856.4	856.7
155°	885.0	885.0	885.0	885.0	885.0	885.1	885.3	885.6	885.8	885.9	886.6
157.5°	912.2	912.0	911.8	911.6	911.4	911.4	911.5	911.7	911.8	911.9	912.7
160°	929.3	929.0	928.6	928.3	927.9	927.8	927.8	927.8	927.8	927.8	928.6
162.5°	944.4	944.0	943.5	943.0	942.5	942.3	942.5	942.6	942.7	942.9	943.7
165°	964.0	963.5	963.0	962.5	961.9	961.7	961.7	961.7	961.7	961.7	962.7
167.5°	979.7	979.0	978.3	977.5	976.8	976.6	976.7	976.8	977.0	977.1	978.3
170°	988.6	987.8	987.1	986.4	985.7	985.3	985.3	985.3	985.3	985.3	986.6
172.5°	995.4	994.8	994.1	993.4	992.7	992.3	992.3	992.3	992.3	992.3	993.4
175°	1002.7	1002.0	1001.4	1000.7	1000.0	999.6	999.6	999.6	999.6	999.6	1000.7
177.5°	1005.7	1005.2	1004.6	1004.0	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.0
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1



TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	31.4	31.3	31.2	31.1	31.2	31.3	31.3	31.4
90°	20.4	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	31.4	32.0	32.5	32.7	32.5	32.3	32.1	31.9
95°	59.8	60.5	61.2	61.6	61.6	61.6	61.6	61.6
97.5°	93.0	93.8	94.6	95.0	94.9	94.9	94.8	94.7
100°	117.1	117.6	118.2	118.7	119.0	119.3	119.7	120.0
102.5°	144.9	145.4	145.9	146.2	146.1	146.0	146.0	145.9
105°	186.3	186.3	186.3	186.5	186.8	187.2	187.5	187.9
107.5°	231.2	231.8	232.4	232.5	232.3	232.1	231.9	231.7
110°	261.2	261.9	262.6	262.8	262.4	262.1	261.7	261.4



TEST NUMBER: P332070-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	291.1	292.0	292.9	293.2	293.2	293.1	293.0	293.0
115°	336.7	336.9	337.1	337.1	336.9	336.7	336.5	336.4
117.5°	382.7	382.6	382.6	382.3	381.9	381.4	380.9	380.4
120°	413.3	413.2	413.0	412.7	412.4	412.0	411.7	411.3
122.5°	444.4	443.9	443.5	443.0	442.5	442.0	441.5	441.0
125°	490.5	489.8	489.1	488.4	487.7	487.0	486.3	485.5
127.5°	536.0	535.0	534.1	533.2	532.4	531.6	530.8	530.0
130°	566.3	565.6	564.9	563.9	562.7	561.5	560.3	559.0
132.5°	595.7	594.8	594.0	593.1	592.2	591.2	590.3	589.4
135°	639.7	639.0	638.3	637.8	637.4	637.1	636.7	636.4
137.5°	682.8	682.1	681.3	680.5	679.9	679.2	678.6	677.9
140°	711.0	710.8	710.6	710.0	708.7	707.5	706.3	705.1
142.5°	737.6	737.4	737.2	736.7	735.7	734.8	733.8	732.9
145°	776.6	776.4	776.2	775.8	775.1	774.4	773.7	773.0
147.5°	813.4	813.4	813.4	812.8	811.8	810.7	809.7	808.7
150°	836.2	836.2	836.2	835.7	834.6	833.5	832.4	831.4
152.5°	856.9	857.2	857.5	857.2	856.3	855.4	854.4	853.5
155°	887.3	888.0	888.7	888.4	887.2	886.0	884.7	883.5
157.5°	913.4	914.1	914.8	914.7	913.8	912.8	911.8	910.8
160°	929.5	930.4	931.2	931.3	930.6	929.9	929.2	928.5
162.5°	944.6	945.5	946.4	946.2	945.1	944.0	942.9	941.8
165°	963.8	964.8	965.9	965.8	964.6	963.3	962.1	960.9
167.5°	979.4	980.4	981.5	981.5	980.4	979.4	978.3	977.1
170°	987.8	989.1	990.3	990.3	989.1	987.8	986.6	985.3
172.5°	994.5	995.6	996.6	996.6	995.3	994.1	992.9	991.7
175°	1001.7	1002.7	1003.8	1003.7	1002.5	1001.3	1000.0	998.8
177.5°	1004.9	1005.7	1006.5	1006.5	1005.5	1004.5	1003.6	1002.6
180°	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1	1005.1

(END OF REPORT)