

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332071-840

Luminaire Tested: **S123DIP-S1165D805U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332071-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S1165D805U840-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7741.3 lumens  
Efficiency: N/A  
Efficacy: 127.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	41	37
4	76	65	57	51	71	61	54	49	54	48	44	48	43	39	41	38	35	32
5	70	58	50	44	65	55	47	42	49	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19871	19871	19871
5°	19966	19690	19827
10°	19831	19519	19641
15°	19601	19299	19334
20°	19329	18984	19001
25°	18966	18608	18570
30°	18567	18191	18053
35°	18148	17751	17521
40°	17710	17265	16996
45°	17230	16818	16407
50°	16747	16268	15816
55°	16117	15700	15221
60°	15481	15035	14557
65°	14918	14314	13868
70°	14090	13489	12891
75°	12872	12410	11882
80°	11610	11120	11021
85°	10189	9806	9411



TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.9	2.2
10°-20°	491.0	6.3
20°-30°	725.3	9.4
30°-40°	847.3	10.9
40°-50°	851.8	11.0
50°-60°	748.3	9.7
60°-70°	557.5	7.2
70°-80°	317.6	4.1
80°-90°	94.2	1.2
90°-100°	217.1	2.8
100°-110°	614.6	7.9
110°-120°	604.6	7.8
120°-130°	482.3	6.2
130°-140°	380.2	4.9
140°-150°	283.8	3.7
150°-160°	197.8	2.6
160°-170°	116.2	1.5
170°-180°	37.8	0.5
0°-30°	1390.3	18.0
0°-40°	2237.6	28.9
0°-60°	3837.7	49.6
0°-90°	4806.9	62.1
90°-120°	1436.3	18.6
90°-150°	2582.6	33.4
90°-180°	2934.0	37.9
0°-180°	7741.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1846	1846	1846	1846	1846	
5°	1848	1839	1822	1837	1835	175
15°	1759	1752	1732	1743	1735	496
25°	1597	1587	1567	1568	1564	735
35°	1381	1371	1351	1341	1333	864
45°	1132	1125	1105	1086	1078	873
55°	859	856	837	820	811	769
65°	586	577	562	550	544	578
75°	310	303	298	291	286	331
85°	82	80	79	76	76	91
90°	2	10	20	22	23	6
95°	27	87	468	137	92	29
105°	92	135	635	1110	1004	97
115°	162	202	486	1065	1221	160
125°	225	266	453	821	963	200
135°	264	315	447	676	781	204
145°	301	345	441	555	610	189
155°	342	369	427	486	506	157
165°	373	384	409	434	441	105
175°	389	390	392	398	397	37
180°	390	390	390	390	390	



TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1852.5	1851.4	1850.3	1849.2	1848.0	1845.8	1842.8	1839.7	1836.5	1833.4	1836.2
5°	1847.8	1846.0	1844.2	1842.5	1840.7	1837.9	1834.0	1830.1	1826.2	1822.3	1825.8
7.5°	1829.7	1827.9	1826.1	1824.3	1822.6	1819.7	1815.6	1811.7	1807.7	1803.6	1806.7
10°	1814.4	1812.6	1810.9	1809.1	1807.4	1804.2	1799.6	1795.0	1790.4	1785.8	1789.0
12.5°	1794.1	1792.6	1791.1	1789.7	1788.2	1785.2	1781.0	1776.7	1772.3	1768.1	1770.4
15°	1758.9	1757.5	1756.1	1754.6	1753.2	1750.2	1745.7	1741.0	1736.5	1731.8	1734.6
17.5°	1717.9	1716.1	1714.2	1712.4	1710.5	1707.4	1702.7	1698.2	1693.5	1689.0	1691.0
20°	1687.4	1685.3	1683.1	1681.0	1679.0	1675.6	1671.0	1666.5	1661.8	1657.3	1658.7
22.5°	1653.1	1651.0	1648.9	1646.8	1644.7	1641.3	1636.7	1632.1	1627.6	1623.0	1624.1
25°	1596.9	1594.8	1592.7	1590.5	1588.5	1585.1	1580.5	1576.0	1571.3	1566.8	1567.1
27.5°	1536.9	1534.9	1532.9	1530.8	1528.7	1525.3	1520.4	1515.4	1510.5	1505.5	1505.8
30°	1493.8	1492.0	1490.3	1488.4	1486.7	1483.4	1478.4	1473.5	1468.5	1463.6	1463.6
32.5°	1450.6	1448.2	1445.9	1443.6	1441.3	1438.1	1434.4	1430.6	1426.7	1423.0	1421.0
35°	1381.1	1379.0	1376.8	1374.7	1372.6	1369.3	1364.6	1360.1	1355.4	1350.9	1348.8
37.5°	1309.9	1307.3	1304.5	1301.9	1299.2	1295.6	1290.9	1286.3	1281.6	1276.9	1274.3
40°	1260.4	1258.3	1256.2	1254.1	1251.9	1248.4	1243.4	1238.5	1233.6	1228.7	1225.9
42.5°	1210.8	1208.5	1206.1	1203.7	1201.2	1197.6	1192.7	1187.7	1182.8	1177.9	1175.1
45°	1131.9	1130.4	1129.0	1127.6	1126.2	1123.2	1118.6	1114.0	1109.4	1104.8	1100.7
47.5°	1053.4	1051.4	1049.4	1047.2	1045.2	1042.1	1037.7	1033.4	1029.2	1024.8	1020.7
50°	1000.1	998.4	996.5	994.8	993.0	989.9	985.2	980.7	976.0	971.5	967.7
52.5°	944.2	943.0	941.8	940.6	939.4	936.3	931.5	926.7	921.8	916.9	913.5
55°	858.8	858.5	858.1	857.8	857.4	855.0	850.3	845.8	841.1	836.6	832.7
57.5°	777.5	776.3	775.1	774.0	772.7	770.3	766.6	763.0	759.3	755.6	752.1
60°	719.1	718.7	718.4	718.0	717.7	715.4	711.1	706.9	702.7	698.4	695.3
62.5°	667.0	666.1	665.2	664.3	663.4	660.8	656.5	652.3	648.1	643.9	640.7
65°	585.7	584.0	582.2	580.5	578.7	576.0	572.5	569.0	565.4	562.0	559.2
67.5°	499.7	498.2	496.7	495.0	493.5	491.4	488.7	486.0	483.3	480.7	478.2
70°	447.7	445.6	443.4	441.3	439.2	437.1	434.9	432.8	430.7	428.6	426.2
72.5°	393.0	391.5	389.9	388.4	386.9	384.9	382.4	380.0	377.7	375.3	373.0
75°	309.5	308.1	306.7	305.3	303.9	302.7	301.6	300.5	299.5	298.4	296.7
77.5°	235.6	234.8	234.0	233.3	232.5	231.5	230.1	228.9	227.6	226.4	225.2
80°	187.3	186.2	185.2	184.1	183.1	182.2	181.5	180.8	180.1	179.4	179.0
82.5°	140.4	140.1	139.9	139.7	139.5	139.3	139.2	139.1	138.9	138.8	138.1
85°	82.5	81.8	81.1	80.4	79.7	79.4	79.4	79.4	79.4	79.4	78.7
87.5°	33.3	32.8	32.3	31.9	31.4	31.1	31.3	31.5	31.7	31.9	31.4
90°	1.6	3.1	4.7	7.1	8.7	10.3	12.6	15.0	17.4	19.7	19.0
92.5°	9.8	14.5	21.2	27.4	33.9	45.6	66.3	100.3	133.6	121.4	91.6
95°	26.9	29.2	37.9	51.3	71.8	102.6	169.8	287.4	416.9	468.2	379.8
97.5°	45.7	46.6	53.4	65.0	85.2	118.6	182.7	315.4	531.2	725.6	776.3
100°	58.5	59.2	64.7	75.8	94.7	125.5	180.8	297.6	505.3	747.7	903.2
102.5°	71.7	73.1	78.0	88.5	105.5	133.7	183.3	282.5	467.4	706.6	909.6
105°	91.6	93.9	98.7	108.2	123.2	147.6	190.3	271.6	420.8	634.8	861.4
107.5°	112.7	115.1	119.7	129.0	143.1	165.8	203.2	270.8	391.1	571.3	777.1
110°	127.9	130.3	134.2	142.9	156.3	178.4	214.0	274.0	379.8	535.3	724.0



TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	141.8	144.2	148.1	156.8	170.3	191.7	224.7	280.2	373.4	511.3	677.9
115°	161.9	165.0	169.8	177.6	191.1	212.4	242.4	290.5	371.1	485.5	622.2
117.5°	181.9	185.5	189.5	196.7	211.8	231.5	261.2	304.2	372.5	470.4	588.5
120°	195.8	198.1	202.1	210.1	225.0	244.8	273.2	314.3	375.1	463.4	570.9
122.5°	207.8	210.2	214.1	222.7	237.0	258.0	285.8	323.7	379.4	459.1	556.3
125°	225.0	226.6	231.4	240.0	255.0	276.3	304.0	338.7	386.1	453.2	537.7
127.5°	238.1	240.4	246.3	255.2	271.8	293.1	319.7	351.0	393.6	450.4	521.3
130°	246.3	248.7	255.8	265.3	281.9	303.2	329.2	359.2	398.7	448.5	512.4
132.5°	252.7	255.7	263.4	274.8	291.3	312.0	337.4	366.8	402.5	447.8	504.2
135°	263.7	266.9	275.6	287.4	304.0	325.3	349.7	376.6	408.2	446.9	493.4
137.5°	274.1	277.4	286.0	298.6	315.0	334.8	358.3	383.8	412.0	445.1	484.1
140°	281.0	285.0	293.0	305.6	321.3	341.0	364.0	387.7	414.5	444.5	478.5
142.5°	288.6	292.0	300.5	311.8	327.7	346.1	368.4	391.4	416.4	443.2	473.4
145°	300.8	303.2	310.3	322.1	335.6	353.8	374.3	395.6	417.7	441.3	466.7
147.5°	313.2	314.6	321.5	331.7	344.7	360.2	379.0	398.1	417.7	438.4	460.0
150°	321.3	322.1	328.4	338.7	349.7	364.0	382.1	398.7	417.7	435.9	455.6
152.5°	329.5	329.7	336.0	345.1	354.8	368.4	384.1	400.0	415.8	432.6	450.5
155°	341.8	341.8	346.6	354.5	363.1	374.3	387.7	400.3	413.7	427.2	442.9
157.5°	351.6	352.2	356.1	363.0	370.4	379.0	389.7	401.1	411.0	422.2	434.4
160°	359.2	359.2	362.4	368.7	374.3	382.1	391.6	401.1	409.8	418.5	428.7
162.5°	365.0	365.0	367.5	372.5	377.4	384.1	392.2	400.4	407.3	414.7	423.0
165°	373.4	372.6	374.3	378.2	381.3	386.9	393.1	398.7	403.4	409.0	415.3
167.5°	379.9	379.0	379.8	382.7	385.0	388.5	393.0	397.5	399.7	403.3	407.9
170°	383.7	382.1	382.9	385.3	386.9	388.5	392.4	395.6	397.2	399.5	403.4
172.5°	386.3	385.3	385.5	387.2	388.1	389.1	392.4	395.0	395.3	396.4	399.0
175°	389.2	388.5	387.7	389.2	389.2	390.0	391.6	393.1	392.4	392.4	393.9
177.5°	390.6	390.0	389.4	390.0	390.0	390.0	390.6	391.9	390.6	390.0	390.6
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0



TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1	1846.1
2.5°	1839.1	1841.9	1844.7	1846.0	1845.7	1845.4	1845.1	1844.9
5°	1829.4	1832.9	1836.4	1837.9	1837.1	1836.4	1835.7	1835.0
7.5°	1810.0	1813.1	1816.3	1817.7	1817.3	1816.8	1816.4	1816.0
10°	1792.2	1795.3	1798.6	1799.8	1799.1	1798.4	1797.7	1797.0
12.5°	1772.7	1775.0	1777.4	1778.4	1777.9	1777.5	1777.1	1776.7
15°	1737.5	1740.3	1743.1	1743.5	1741.4	1739.3	1737.2	1735.0
17.5°	1692.9	1695.0	1696.9	1697.5	1696.8	1696.0	1695.2	1694.5
20°	1660.1	1661.5	1662.9	1663.0	1662.0	1660.9	1659.9	1658.8
22.5°	1625.3	1626.4	1627.5	1627.4	1626.1	1624.7	1623.4	1622.0
25°	1567.5	1567.8	1568.2	1567.8	1566.8	1565.7	1564.7	1563.6
27.5°	1506.1	1506.3	1506.6	1506.1	1504.8	1503.4	1502.1	1500.8
30°	1463.6	1463.6	1463.6	1462.4	1459.9	1457.4	1454.9	1452.5
32.5°	1419.0	1417.0	1415.0	1413.4	1412.1	1410.7	1409.4	1408.1
35°	1346.7	1344.5	1342.4	1340.5	1338.7	1337.0	1335.1	1333.4
37.5°	1271.8	1269.3	1266.8	1265.0	1263.7	1262.6	1261.5	1260.4
40°	1223.0	1220.2	1217.4	1215.3	1213.9	1212.4	1211.0	1209.6
42.5°	1172.3	1169.4	1166.6	1164.5	1163.1	1161.6	1160.2	1158.8
45°	1096.4	1092.2	1087.9	1084.9	1083.2	1081.4	1079.6	1077.8
47.5°	1016.5	1012.4	1008.1	1005.3	1003.8	1002.2	1000.7	999.2
50°	963.7	959.9	955.9	953.0	950.9	948.8	946.6	944.5
52.5°	910.3	907.0	903.6	900.9	898.8	896.7	894.5	892.4
55°	828.8	825.0	821.0	818.2	816.5	814.7	812.9	811.1
57.5°	748.7	745.3	741.7	739.0	737.0	735.0	732.9	730.8
60°	692.2	688.9	685.8	683.3	681.6	679.7	678.0	676.2
62.5°	637.5	634.3	631.2	628.9	627.7	626.5	625.4	624.2
65°	556.3	553.5	550.7	548.8	547.6	546.6	545.5	544.5
67.5°	475.7	473.2	470.8	468.8	467.4	465.9	464.3	462.9
70°	423.6	421.2	418.7	416.6	414.9	413.0	411.3	409.6
72.5°	370.9	368.7	366.5	365.0	364.1	363.1	362.2	361.3
75°	294.9	293.2	291.3	289.9	288.9	287.8	286.8	285.7
77.5°	224.0	222.8	221.6	221.0	221.0	221.0	221.0	221.0
80°	178.6	178.3	177.9	177.8	177.8	177.8	177.8	177.8
82.5°	137.4	136.8	136.2	135.7	135.4	135.2	134.9	134.6
85°	78.0	77.3	76.5	76.2	76.2	76.2	76.2	76.2
87.5°	31.3	31.2	31.1	31.2	31.1	31.2	31.4	31.2
90°	19.7	20.5	21.3	22.9	22.1	22.9	23.7	22.9
92.5°	66.4	52.7	46.6	42.5	41.1	38.7	39.5	38.1
95°	284.3	192.7	150.8	122.4	107.3	100.3	94.7	91.6
97.5°	708.5	567.5	465.6	371.2	313.0	277.4	256.1	249.3
100°	930.9	866.9	774.6	662.4	582.7	525.0	494.2	495.0
102.5°	1004.7	1002.7	948.9	877.8	815.8	770.1	744.4	726.2
105°	1026.4	1105.3	1120.3	1099.8	1063.5	1033.5	1008.2	1004.3
107.5°	964.2	1092.4	1161.5	1189.6	1190.3	1180.2	1171.6	1164.4
110°	904.8	1050.1	1149.5	1204.9	1226.9	1233.2	1231.6	1230.1





TEST NUMBER: P332071-840

CATALOG NUMBER: S123DIP-S1165D805U840-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	846.1	994.5	1106.0	1177.0	1217.5	1237.1	1243.0	1243.3
115°	768.2	905.5	1021.7	1107.7	1166.9	1201.6	1217.5	1221.4
117.5°	711.9	830.4	934.6	1022.0	1083.7	1123.5	1146.2	1151.7
120°	682.2	788.7	883.5	963.2	1025.6	1069.9	1088.7	1093.5
122.5°	658.8	755.3	843.0	917.2	972.5	1012.3	1033.2	1039.2
125°	627.6	713.8	789.5	852.7	903.2	938.0	957.7	963.2
127.5°	600.6	677.2	745.7	803.1	848.1	877.8	895.6	900.7
130°	583.5	654.5	718.5	772.1	814.1	842.4	859.0	865.4
132.5°	567.6	633.1	692.6	743.8	783.0	811.5	826.2	830.6
135°	546.3	602.4	653.7	698.7	737.4	761.1	775.3	780.8
137.5°	526.9	572.9	617.1	656.1	688.6	712.7	724.7	728.3
140°	515.5	555.8	593.7	627.6	657.7	679.7	692.5	691.7
142.5°	504.8	539.4	572.3	601.8	627.3	646.9	658.3	657.5
145°	491.9	518.0	543.2	566.1	585.8	602.4	608.7	610.3
147.5°	481.3	502.0	522.4	538.7	553.6	564.8	570.9	571.5
150°	473.7	491.9	508.5	523.4	535.3	544.0	548.8	548.8
152.5°	466.8	482.4	497.1	509.6	518.9	526.9	529.8	529.8
155°	456.4	469.0	480.8	490.3	497.4	503.7	505.3	506.0
157.5°	445.2	455.9	465.0	472.4	478.6	483.3	484.6	484.4
160°	439.0	447.7	455.6	461.1	466.7	471.3	471.3	470.6
162.5°	431.4	438.8	446.1	451.0	454.6	458.7	458.7	458.0
165°	421.6	426.4	431.9	435.9	439.0	442.1	441.3	441.3
167.5°	413.0	416.7	419.9	422.7	424.1	426.4	425.6	425.6
170°	407.4	409.8	412.9	414.5	415.3	416.9	416.1	416.1
172.5°	402.3	404.0	406.6	407.6	407.7	409.3	407.9	407.3
175°	395.6	396.4	397.9	397.9	397.9	398.7	397.9	397.2
177.5°	391.3	391.9	392.5	392.5	391.9	392.5	391.3	391.3
180°	390.0	390.0	390.0	390.0	390.0	390.0	390.0	390.0

(END OF REPORT)