

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331936

Luminaire Tested: **S123DIP-S560D805U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331936
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D805U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5226.9 lumens
Efficiency: N/A
Efficacy: 136.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		65	65	65		51	51	51	44
1	96	92	88	85	88	85	81	78	70	68	66		57	55	54		45	44	43	37
2	88	80	74	69	80	74	69	64	61	58	54		50	47	45		40	38	36	31
3	80	71	63	58	73	65	59	54	54	49	46		44	41	38		35	33	31	26
4	73	62	55	49	67	57	51	45	48	43	39		39	36	33		31	29	26	23
5	67	56	48	42	61	51	44	39	43	38	33		35	31	28		28	25	23	20
6	62	50	42	36	56	46	39	34	39	33	29		32	28	25		26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23		26	22	19		21	18	16	14
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18		22	19	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.6
10°-20°	237.0	4.5
20°-30°	350.0	6.7
30°-40°	408.9	7.8
40°-50°	411.1	7.9
50°-60°	361.1	6.9
60°-70°	269.0	5.1
70°-80°	153.3	2.9
80°-90°	47.0	0.9
90°-100°	214.9	4.1
100°-110°	608.6	11.6
110°-120°	598.7	11.5
120°-130°	477.5	9.1
130°-140°	376.5	7.2
140°-150°	281.0	5.4
150°-160°	195.9	3.7
160°-170°	115.1	2.2
170°-180°	37.4	0.7
0°-30°	670.9	12.8
0°-40°	1079.8	20.7
0°-60°	1851.9	35.4
0°-90°	2321.1	44.4
90°-120°	1422.2	27.2
90°-150°	2557.3	48.9
90°-180°	2906.0	55.6
0°-180°	5226.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	2	9	20	22	23	4
95°	27	86	464	135	91	29
105°	91	134	629	1099	994	96
115°	160	200	481	1054	1210	159
125°	223	263	449	813	954	198
135°	261	312	442	670	773	202
145°	298	341	437	549	604	187
155°	338	365	423	481	501	156
165°	370	380	405	430	437	104
175°	385	386	389	394	393	37
180°	386	386	386	386	386	



TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.2	16.2	16.1	16.1	16.0	16.1	16.4	16.7	17.1	17.4	17.1
90°	1.6	3.1	4.7	7.0	8.6	10.2	12.5	14.9	17.2	19.5	18.8
92.5°	9.7	14.4	21.0	27.1	33.6	45.2	65.7	99.3	132.3	120.2	90.7
95°	26.6	28.9	37.5	50.8	71.1	101.6	168.1	284.6	412.8	463.6	376.1
97.5°	45.3	46.1	52.9	64.4	84.4	117.4	180.9	312.3	526.0	718.5	768.7
100°	57.9	58.6	64.1	75.1	93.8	124.3	179.0	294.7	500.4	740.4	894.4
102.5°	71.0	72.4	77.2	87.6	104.5	132.4	181.5	279.7	462.8	699.7	900.7
105°	90.7	93.0	97.7	107.1	122.0	146.2	188.4	268.9	416.7	628.6	853.0
107.5°	111.6	114.0	118.5	127.7	141.7	164.2	201.2	268.2	387.3	565.7	769.5
110°	126.7	129.0	132.9	141.5	154.8	176.7	211.9	271.3	376.1	530.1	716.9



TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	140.4	142.8	146.7	155.3	168.6	189.8	222.5	277.5	369.8	506.3	671.3
115°	160.3	163.4	168.1	175.9	189.2	210.3	240.0	287.7	367.5	480.8	616.1
117.5°	180.1	183.7	187.6	194.8	209.7	229.2	258.6	301.2	368.9	465.8	582.8
120°	193.9	196.2	200.1	208.0	222.8	242.4	270.5	311.2	371.4	458.9	565.3
122.5°	205.8	208.1	212.0	220.5	234.7	255.5	283.0	320.5	375.7	454.6	550.9
125°	222.8	224.4	229.1	237.7	252.5	273.6	301.0	335.4	382.3	448.8	532.4
127.5°	235.8	238.1	243.9	252.7	269.1	290.2	316.6	347.6	389.8	446.0	516.2
130°	243.9	246.3	253.3	262.7	279.1	300.2	326.0	355.7	394.8	444.1	507.4
132.5°	250.2	253.2	260.8	272.1	288.5	309.0	334.1	363.2	398.6	443.4	499.3
135°	261.1	264.3	272.9	284.6	301.0	322.1	346.3	372.9	404.2	442.5	488.6
137.5°	271.4	274.7	283.2	295.7	311.9	331.5	354.8	380.1	408.0	440.8	479.4
140°	278.3	282.2	290.1	302.6	318.2	337.7	360.4	383.9	410.5	440.2	473.8
142.5°	285.8	289.1	297.6	308.8	324.5	342.7	364.8	387.6	412.3	438.9	468.8
145°	297.9	300.2	307.3	319.0	332.3	350.3	370.6	391.7	413.6	437.0	462.1
147.5°	310.1	311.5	318.4	328.5	341.3	356.7	375.3	394.2	413.6	434.1	455.5
150°	318.2	319.0	325.2	335.4	346.3	360.4	378.4	394.8	413.6	431.6	451.1
152.5°	326.3	326.5	332.7	341.7	351.3	364.8	380.3	396.1	411.7	428.4	446.1
155°	338.5	338.5	343.2	351.0	359.6	370.6	383.9	396.4	409.7	423.0	438.6
157.5°	348.2	348.8	352.6	359.5	366.8	375.3	385.9	397.2	407.0	418.1	430.2
160°	355.7	355.7	358.9	365.1	370.6	378.4	387.8	397.2	405.8	414.4	424.5
162.5°	361.4	361.4	363.9	368.9	373.7	380.3	388.4	396.5	403.3	410.6	418.9
165°	369.8	369.0	370.6	374.5	377.6	383.1	389.3	394.8	399.5	405.0	411.2
167.5°	376.2	375.3	376.1	379.0	381.2	384.7	389.2	393.6	395.8	399.4	403.9
170°	380.0	378.4	379.2	381.5	383.1	384.7	388.6	391.7	393.3	395.6	399.5
172.5°	382.5	381.5	381.7	383.4	384.3	385.3	388.6	391.1	391.4	392.5	395.1
175°	385.4	384.7	383.9	385.4	385.4	386.2	387.8	389.3	388.6	388.6	390.1
177.5°	386.8	386.2	385.6	386.2	386.2	386.2	386.8	388.1	386.8	386.2	386.8
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2



TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	17.1	17.1	17.2	17.4	17.2	17.4	17.6	17.4
90°	19.5	20.3	21.1	22.7	21.9	22.7	23.5	22.7
92.5°	65.8	52.2	46.1	42.1	40.7	38.3	39.1	37.7
95°	281.5	190.8	149.3	121.2	106.3	99.3	93.8	90.7
97.5°	701.6	562.0	461.1	367.6	309.9	274.7	253.6	246.9
100°	921.8	858.4	767.0	655.9	577.0	519.9	489.4	490.2
102.5°	994.9	992.9	939.6	869.2	807.8	762.6	737.1	719.1
105°	1016.4	1094.5	1109.4	1089.1	1053.1	1023.4	998.4	994.5
107.5°	954.8	1081.7	1150.2	1178.0	1178.7	1168.7	1160.2	1153.0
110°	896.0	1039.8	1138.3	1193.1	1214.9	1221.2	1219.6	1218.1



TEST NUMBER: P331936

CATALOG NUMBER: S123DIP-S560D805U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	837.8	984.8	1095.2	1165.5	1205.6	1225.0	1230.9	1231.2
115°	760.7	896.7	1011.7	1096.9	1155.5	1189.9	1205.6	1209.5
117.5°	704.9	822.3	925.5	1012.0	1073.1	1112.5	1135.0	1140.4
120°	675.5	781.0	874.9	953.8	1015.6	1059.4	1078.1	1082.8
122.5°	652.4	747.9	834.8	908.2	963.0	1002.4	1023.1	1029.0
125°	621.5	706.8	781.8	844.4	894.4	928.8	948.3	953.8
127.5°	594.7	670.6	738.4	795.3	839.8	869.2	886.9	891.9
130°	577.8	648.1	711.5	764.6	806.1	834.2	850.6	856.9
132.5°	562.1	626.9	685.8	736.5	775.4	803.6	818.1	822.5
135°	541.0	596.5	647.3	691.9	730.2	753.7	767.7	773.2
137.5°	521.8	567.3	611.1	649.7	681.9	705.7	717.6	721.2
140°	510.5	550.4	587.9	621.5	651.3	673.1	685.7	684.9
142.5°	499.9	534.1	566.7	595.9	621.2	640.6	651.9	651.1
145°	487.1	512.9	537.9	560.6	580.1	596.5	602.8	604.3
147.5°	476.6	497.1	517.3	533.4	548.2	559.3	565.3	565.9
150°	469.1	487.1	503.5	518.3	530.1	538.7	543.4	543.4
152.5°	462.2	477.7	492.2	504.6	513.8	521.8	524.6	524.6
155°	451.9	464.4	476.1	485.5	492.5	498.8	500.4	501.1
157.5°	440.9	451.4	460.5	467.8	473.9	478.6	479.9	479.7
160°	434.7	443.3	451.1	456.6	462.1	466.7	466.7	466.0
162.5°	427.2	434.5	441.7	446.6	450.2	454.2	454.2	453.5
165°	417.5	422.2	427.7	431.6	434.7	437.8	437.0	437.0
167.5°	409.0	412.6	415.8	418.6	420.0	422.2	421.4	421.4
170°	403.4	405.8	408.9	410.5	411.2	412.8	412.0	412.0
172.5°	398.4	400.1	402.6	403.6	403.7	405.3	403.9	403.3
175°	391.7	392.5	394.0	394.0	394.0	394.8	394.0	393.3
177.5°	387.5	388.1	388.7	388.7	388.1	388.7	387.5	387.5
180°	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2

(END OF REPORT)