

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331892-840

Luminaire Tested: **S123DIP-S340D1025U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331892-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D1025U840-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1025 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5606.9 lumens  
Efficiency: N/A  
Efficacy: 150.3 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	68	61	55	50	48	44	40	35	33	31	24	22	21	16
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	21	20	18	14
5	65	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	10
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	5226	5226	5226	5226
5°	6232	5249	4652	5249
10°	7802	5223	4203	5223
15°	9569	5180	3911	5180
20°	11399	5116	3725	5116
25°	12105	5035	3682	5035
30°	10376	4977	3701	4977
35°	7215	4893	3741	4893
40°	5435	4796	3729	4796
45°	4512	4652	3682	4652
50°	4042	4357	3647	4357
55°	3780	4040	3603	4040
60°	3546	3707	3565	3707
65°	3331	3380	3451	3380
70°	3125	3006	3286	3006
75°	2799	2633	3015	2633
80°	2448	2157	2597	2157
85°	1927	1568	1741	1568



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.8	0.9
10°-20°	153.4	2.7
20°-30°	257.4	4.6
30°-40°	291.5	5.2
40°-50°	261.4	4.7
50°-60°	210.9	3.8
60°-70°	147.0	2.6
70°-80°	77.3	1.4
80°-90°	22.7	0.4
90°-100°	49.3	0.9
100°-110°	235.1	4.2
110°-120°	564.7	10.1
120°-130°	719.1	12.8
130°-140°	768.3	13.7
140°-150°	718.5	12.8
150°-160°	579.5	10.3
160°-170°	374.0	6.7
170°-180°	128.9	2.3
0°-30°	458.6	8.2
0°-40°	750.1	13.4
0°-60°	1222.4	21.8
0°-90°	1469.4	26.2
90°-120°	849.1	15.1
90°-150°	3055.0	54.5
90°-180°	4137.0	73.8
0°-180°	5606.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	486	486	486	486	486	
5°	577	486	430	486	577	60
15°	859	465	351	465	859	248
25°	1019	424	310	424	1019	447
35°	549	372	285	372	549	357
45°	296	306	242	306	296	235
55°	201	215	192	215	201	181
65°	131	133	136	133	131	130
75°	67	63	72	63	67	72
85°	16	13	14	13	16	19
90°	30	1	30	1	30	14
95°	38	62	38	62	38	32
105°	44	300	44	300	44	101
115°	593	564	593	564	593	548
125°	810	794	810	794	810	724
135°	999	989	999	989	999	770
145°	1152	1141	1152	1141	1152	719
155°	1255	1257	1255	1257	1255	579
165°	1322	1326	1322	1326	1322	373
175°	1352	1357	1352	1357	1352	129
180°	1357	1357	1357	1357	1357	



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	515.3	514.9	514.0	514.7	513.2	511.2	511.0	509.1	503.6	503.3	501.8
5°	576.8	575.0	574.7	574.5	571.2	566.7	558.3	557.5	546.2	540.7	533.8
7.5°	656.6	657.5	654.1	651.2	641.1	634.4	625.3	613.7	599.9	585.7	576.4
10°	713.8	721.5	712.0	705.3	699.2	687.7	674.3	657.5	640.9	621.4	606.5
12.5°	775.2	778.9	777.0	770.8	761.3	743.8	720.0	701.6	686.2	653.7	640.6
15°	858.7	873.0	863.8	842.7	843.1	826.5	795.5	761.3	743.2	714.7	675.9
17.5°	947.8	949.5	945.6	928.0	916.3	893.2	864.5	831.9	795.2	760.7	719.5
20°	995.1	993.7	985.5	976.3	956.1	938.3	907.0	870.5	823.4	789.5	744.6
22.5°	1021.5	1019.2	1015.2	1007.5	990.8	971.6	943.4	903.6	858.8	812.1	760.2
25°	1019.2	1022.2	1022.7	1020.6	1014.7	1003.2	981.1	949.3	904.6	844.6	790.5
27.5°	927.0	931.3	943.8	955.0	967.5	980.2	978.5	962.7	929.6	877.8	811.6
30°	834.8	825.3	848.6	878.0	898.0	933.3	953.0	954.2	935.6	891.2	826.7
32.5°	706.7	717.1	727.4	763.6	807.3	846.9	886.3	917.9	921.5	891.9	835.6
35°	549.1	562.1	580.9	599.7	646.7	687.2	756.4	816.6	864.5	870.9	836.4
37.5°	442.5	448.9	460.8	479.7	510.4	558.5	611.9	688.0	757.6	809.3	811.5
40°	386.8	388.7	402.0	416.4	441.3	480.9	529.1	596.4	679.6	751.9	782.0
42.5°	345.0	349.1	354.9	368.6	388.5	418.2	463.0	518.7	595.0	678.1	737.0
45°	296.4	301.1	304.7	313.9	328.0	348.0	379.2	430.1	488.2	574.0	653.3
47.5°	264.4	264.7	267.3	274.3	283.9	298.9	321.0	353.7	407.0	476.7	558.1
50°	241.4	245.1	246.1	251.5	259.0	270.0	288.4	316.2	359.9	421.1	495.9
52.5°	225.2	226.3	228.9	232.9	239.4	248.0	264.0	285.7	320.0	372.2	441.0
55°	201.4	201.4	204.0	207.0	210.8	218.5	229.1	245.1	271.2	311.7	368.7
57.5°	179.4	180.6	182.4	183.3	186.5	191.7	200.5	212.7	232.1	263.3	308.5
60°	164.7	166.8	166.5	168.4	171.3	175.3	182.8	192.7	210.1	235.0	273.2
62.5°	151.9	151.8	151.7	154.0	156.7	160.6	165.5	174.0	188.8	211.0	243.4
65°	130.8	130.4	132.0	133.4	134.3	137.1	140.9	148.5	158.3	174.8	200.0
67.5°	112.1	110.7	111.6	112.1	113.7	115.9	119.5	124.1	131.9	145.1	164.1
70°	99.3	98.1	97.9	98.4	99.8	101.4	104.0	108.5	115.7	126.3	140.2
72.5°	86.1	85.3	85.2	86.3	86.9	88.1	89.9	93.9	99.8	107.8	120.7
75°	67.3	67.3	67.3	67.6	68.3	69.2	70.6	72.7	77.2	82.8	91.5
77.5°	50.4	50.4	50.1	50.1	51.1	51.5	51.8	53.8	56.4	60.1	66.4
80°	39.5	38.4	38.8	39.5	40.0	40.2	40.9	41.4	43.5	45.6	50.1
82.5°	29.4	28.4	28.5	29.6	29.7	29.9	30.6	31.2	32.0	33.9	36.4
85°	15.6	15.6	15.8	15.8	16.0	15.8	16.5	16.7	16.7	17.9	19.3
87.5°	11.7	11.2	11.3	11.4	11.1	11.2	11.2	11.2	11.2	11.2	10.8
90°	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0	25.0	24.2	21.3
92.5°	33.4	33.2	32.9	32.6	32.4	31.5	30.1	28.7	27.3	25.9	23.6
95°	38.3	38.3	38.3	38.3	38.3	37.6	36.0	34.3	32.8	31.2	28.8
97.5°	41.5	41.3	41.1	40.9	40.6	39.6	37.9	36.1	34.2	32.4	28.6
100°	42.3	42.1	41.9	41.7	41.4	40.4	38.7	36.9	35.0	33.2	28.2
102.5°	43.1	42.7	42.3	41.9	41.5	44.1	49.7	55.2	60.8	66.3	104.5
105°	44.3	43.9	43.4	43.0	42.5	62.2	101.8	141.5	181.1	220.8	241.0
107.5°	139.3	169.2	199.0	228.9	258.8	288.3	317.4	346.5	375.6	404.7	401.4
110°	277.2	309.2	341.2	373.2	405.4	425.1	432.4	439.8	447.2	454.6	452.1



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	475.5	482.3	489.1	495.8	502.6	505.9	505.8	505.6	505.5	505.4	502.9
115°	592.7	591.8	590.9	590.0	589.2	587.5	585.3	583.1	580.9	578.6	576.5
117.5°	658.4	658.2	658.0	657.9	657.7	656.7	654.9	653.2	651.4	649.5	648.5
120°	703.6	703.6	703.6	703.6	703.6	702.7	700.8	699.1	697.3	695.5	694.9
122.5°	747.9	747.7	747.6	747.4	747.2	746.5	745.3	744.0	742.8	741.4	740.6
125°	810.4	810.0	809.5	809.1	808.6	808.2	807.7	807.3	806.9	806.4	805.5
127.5°	870.5	870.9	871.4	871.8	872.3	872.1	871.4	870.7	870.0	869.3	868.2
130°	909.2	909.7	910.1	910.6	911.0	910.8	909.9	909.0	908.1	907.2	906.3
132.5°	944.7	945.3	945.9	946.5	947.2	947.1	946.1	945.2	944.4	943.5	942.8
135°	999.0	999.6	1000.3	1001.0	1001.6	1001.6	1001.0	1000.3	999.6	999.0	998.0
137.5°	1050.0	1050.4	1050.9	1051.3	1051.7	1051.4	1050.4	1049.2	1048.1	1047.1	1046.6
140°	1080.6	1081.1	1081.5	1081.9	1082.4	1082.2	1081.3	1080.4	1079.4	1078.5	1077.9
142.5°	1108.8	1109.4	1110.0	1110.6	1111.3	1111.3	1110.5	1109.8	1109.1	1108.4	1107.7
145°	1152.2	1152.2	1152.2	1152.2	1152.2	1152.0	1151.4	1151.0	1150.5	1150.1	1149.6
147.5°	1184.4	1185.4	1186.5	1187.5	1188.5	1188.8	1188.3	1187.9	1187.5	1187.0	1186.6
150°	1208.6	1209.2	1209.9	1210.6	1211.2	1211.4	1210.9	1210.5	1210.0	1209.6	1209.1
152.5°	1227.9	1229.0	1230.0	1231.0	1232.0	1232.1	1231.3	1230.5	1229.7	1228.9	1228.7
155°	1255.0	1256.3	1257.7	1259.0	1260.3	1260.4	1259.3	1258.2	1257.1	1256.0	1255.8
157.5°	1277.8	1279.5	1281.2	1282.9	1284.8	1285.0	1283.5	1282.2	1280.9	1279.5	1279.8
160°	1292.2	1293.8	1295.4	1297.0	1298.5	1298.6	1297.3	1296.0	1294.6	1293.2	1293.4
162.5°	1306.0	1307.4	1308.7	1310.1	1311.5	1311.4	1309.9	1308.4	1306.9	1305.4	1305.6
165°	1322.5	1324.0	1325.6	1327.2	1328.8	1328.7	1326.9	1325.0	1323.2	1321.5	1321.7
167.5°	1334.3	1336.2	1338.0	1339.8	1341.5	1341.5	1339.8	1338.0	1336.2	1334.3	1334.3
170°	1341.6	1343.4	1345.2	1347.1	1348.8	1348.8	1347.1	1345.2	1343.4	1341.6	1341.6
172.5°	1345.6	1347.7	1349.6	1351.6	1353.5	1353.6	1351.8	1350.1	1348.3	1346.5	1346.3
175°	1351.7	1353.5	1355.3	1357.1	1358.9	1359.0	1357.5	1355.8	1354.3	1352.7	1352.5
177.5°	1353.5	1355.3	1357.2	1358.9	1360.7	1360.9	1359.5	1358.0	1356.6	1355.1	1354.9
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	500.6	499.2	497.7	495.0	492.7	489.6	488.6	487.5	484.0	481.1	478.8
5°	531.2	525.5	517.4	509.8	503.7	495.4	490.8	485.8	478.8	472.4	467.3
7.5°	563.2	552.1	539.3	525.5	512.6	500.2	490.2	481.2	471.3	462.0	454.6
10°	588.7	572.6	554.7	535.4	519.0	503.0	489.6	477.9	465.1	454.0	444.8
12.5°	617.6	593.9	569.3	545.8	526.3	504.1	487.9	472.9	458.5	445.2	434.9
15°	651.9	621.8	592.6	560.4	530.8	503.0	483.7	464.8	448.2	434.5	421.3
17.5°	683.2	649.0	610.6	571.4	535.6	502.7	475.7	454.4	433.5	416.9	403.7
20°	700.8	662.1	618.5	577.8	538.3	501.6	471.9	446.6	423.9	406.3	391.5
22.5°	716.1	670.7	625.6	582.1	538.1	498.6	464.9	438.8	414.3	397.1	381.3
25°	732.0	677.5	632.4	581.4	532.2	491.2	453.6	423.9	399.5	379.2	363.0
27.5°	745.5	677.1	623.5	568.6	522.8	481.8	441.6	409.8	383.8	361.8	345.4
30°	754.5	678.0	614.3	560.0	513.8	471.5	432.4	400.4	373.1	350.8	335.3
32.5°	760.1	677.4	605.8	547.9	499.5	462.0	422.4	389.3	361.2	339.3	324.4
35°	763.5	673.3	591.2	523.0	476.5	439.9	406.8	372.4	343.1	322.6	305.6
37.5°	756.8	664.6	574.3	499.0	448.0	412.1	384.2	355.0	326.8	304.3	289.6
40°	746.5	658.9	561.1	482.0	428.4	393.8	370.1	341.3	313.6	292.2	278.5
42.5°	726.7	647.5	546.6	463.2	408.1	373.5	351.6	327.6	301.3	281.2	267.6
45°	678.5	622.5	524.8	435.0	378.1	342.3	323.1	305.6	281.9	262.4	250.5
47.5°	611.6	584.9	493.4	405.3	346.7	312.4	292.3	278.3	260.9	245.1	233.9
50°	565.1	554.0	472.2	384.9	325.9	292.2	272.9	260.2	247.7	232.0	221.7
52.5°	511.5	518.3	447.4	363.9	304.6	271.5	253.4	243.3	232.0	218.9	210.0
55°	436.0	460.6	404.5	328.4	272.9	241.4	224.2	215.3	208.6	199.0	191.3
57.5°	365.3	396.7	358.0	292.0	241.8	214.6	198.1	188.4	184.2	179.2	173.0
60°	323.3	354.3	324.9	267.5	221.0	195.0	180.5	172.2	167.9	164.4	159.3
62.5°	285.8	317.2	292.6	242.7	200.4	176.4	163.7	155.6	152.4	150.6	146.1
65°	234.3	261.4	244.9	204.0	171.1	149.9	138.4	132.7	129.7	129.0	126.1
67.5°	190.7	211.3	199.3	169.2	143.3	125.0	115.2	110.4	108.1	107.8	105.6
70°	162.1	181.4	172.2	144.9	122.6	108.3	99.8	95.5	94.1	93.9	92.7
72.5°	139.9	153.3	146.0	123.3	106.0	93.0	86.7	82.3	80.8	81.1	80.3
75°	103.5	113.6	109.4	93.6	79.8	71.3	66.1	63.3	61.9	62.6	61.6
77.5°	74.5	80.9	77.1	66.1	57.6	51.5	47.7	45.9	44.6	44.6	44.2
80°	56.2	60.0	57.9	51.3	44.2	39.1	36.0	34.8	34.1	33.8	33.6
82.5°	40.1	43.2	40.7	36.3	31.4	28.3	26.6	25.0	24.5	24.6	24.4
85°	20.2	21.4	20.5	17.7	15.8	14.3	13.4	12.7	12.2	12.4	12.0
87.5°	10.6	10.2	9.1	7.9	7.0	6.0	5.6	4.7	4.7	5.3	5.5
90°	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	21.4	19.2	17.1	16.3	16.9	17.5	18.1	18.8	18.1	17.5	16.9
95°	26.4	23.8	21.4	24.7	33.9	43.1	52.3	61.5	52.3	43.1	33.9
97.5°	64.7	80.9	96.9	107.0	111.2	115.3	119.5	123.6	119.5	115.3	111.2
100°	103.1	138.0	173.0	188.2	183.8	179.4	174.8	170.4	174.8	179.4	183.8
102.5°	142.7	180.9	219.0	236.5	233.3	230.0	226.8	223.6	226.8	230.0	233.3
105°	261.1	281.2	301.3	310.2	307.8	305.3	302.9	300.3	302.9	305.3	307.8
107.5°	398.3	395.1	391.9	389.3	387.4	385.4	383.4	381.4	383.4	385.4	387.4
110°	449.7	447.2	444.7	442.6	440.8	439.0	437.3	435.5	437.3	439.0	440.8





TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	500.5	498.1	495.5	493.5	491.9	490.3	488.7	487.1	488.7	490.3	491.9
115°	574.5	572.5	570.6	568.9	567.5	566.1	564.8	563.5	564.8	566.1	567.5
117.5°	647.5	646.4	645.4	644.1	642.5	640.8	639.1	637.4	639.1	640.8	642.5
120°	694.2	693.5	692.9	691.5	689.4	687.4	685.4	683.4	685.4	687.4	689.4
122.5°	739.8	738.9	738.1	736.8	735.2	733.5	731.8	730.2	731.8	733.5	735.2
125°	804.6	803.8	802.8	801.4	799.7	797.9	796.1	794.3	796.1	797.9	799.7
127.5°	867.2	866.1	864.9	863.5	861.7	860.0	858.2	856.4	858.2	860.0	861.7
130°	905.4	904.5	903.6	902.3	900.5	898.7	896.9	895.1	896.9	898.7	900.5
132.5°	942.0	941.3	940.6	939.4	937.6	935.7	934.0	932.2	934.0	935.7	937.6
135°	997.1	996.2	995.3	994.2	992.9	991.5	990.2	988.9	990.2	991.5	992.9
137.5°	1046.1	1045.6	1045.1	1044.0	1042.4	1040.7	1038.9	1037.2	1038.9	1040.7	1042.4
140°	1077.2	1076.5	1075.9	1074.9	1073.5	1072.2	1070.9	1069.4	1070.9	1072.2	1073.5
142.5°	1107.0	1106.4	1105.7	1104.7	1103.4	1102.0	1100.7	1099.3	1100.7	1102.0	1103.4
145°	1149.2	1148.8	1148.3	1147.3	1145.8	1144.2	1142.7	1141.0	1142.7	1144.2	1145.8
147.5°	1186.1	1185.7	1185.2	1184.5	1183.5	1182.5	1181.4	1180.3	1181.4	1182.5	1183.5
150°	1208.7	1208.2	1207.8	1207.2	1206.6	1205.9	1205.3	1204.6	1205.3	1205.9	1206.6
152.5°	1228.4	1228.1	1227.9	1227.6	1227.3	1227.0	1226.7	1226.3	1226.7	1227.0	1227.3
155°	1255.5	1255.3	1255.1	1255.2	1255.7	1256.1	1256.5	1257.0	1256.5	1256.1	1255.7
157.5°	1280.0	1280.2	1280.4	1280.6	1280.6	1280.7	1280.7	1280.7	1280.7	1280.7	1280.6
160°	1293.7	1293.9	1294.1	1294.3	1294.6	1294.8	1295.1	1295.3	1295.1	1294.8	1294.6
162.5°	1305.8	1306.1	1306.3	1306.7	1307.3	1307.8	1308.4	1309.0	1308.4	1307.8	1307.3
165°	1321.9	1322.1	1322.4	1322.8	1323.5	1324.1	1324.8	1325.5	1324.8	1324.1	1323.5
167.5°	1334.3	1334.3	1334.3	1334.8	1335.7	1336.7	1337.6	1338.4	1337.6	1336.7	1335.7
170°	1341.6	1341.6	1341.6	1342.1	1343.0	1343.9	1344.7	1345.6	1344.7	1343.9	1343.0
172.5°	1346.2	1345.9	1345.7	1346.3	1347.3	1348.4	1349.5	1350.5	1349.5	1348.4	1347.3
175°	1352.3	1352.0	1351.8	1352.3	1353.4	1354.5	1355.6	1356.8	1355.6	1354.5	1353.4
177.5°	1354.8	1354.6	1354.4	1354.8	1355.6	1356.6	1357.5	1358.4	1357.5	1356.6	1355.6
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	477.5	476.2	474.3	471.5	469.2	465.6	465.6	466.2	466.2	466.1	465.6
5°	463.0	459.5	455.2	450.3	445.1	439.9	439.0	437.1	435.8	434.7	433.6
7.5°	447.7	441.4	435.3	428.4	422.0	416.9	413.2	410.2	408.3	406.2	404.7
10°	437.4	429.6	422.3	415.1	407.0	400.6	396.7	393.8	391.7	389.8	388.9
12.5°	425.2	416.3	408.2	401.2	392.5	386.0	382.1	380.8	378.4	374.4	372.3
15°	407.3	399.0	389.4	378.8	374.6	366.6	362.0	359.9	358.5	355.5	354.6
17.5°	391.9	381.2	370.3	362.4	354.6	348.1	345.6	343.0	341.1	338.6	337.8
20°	379.7	370.1	360.2	351.7	343.5	336.4	334.3	332.4	330.5	329.4	328.4
22.5°	367.3	357.7	349.4	341.5	332.8	328.1	325.9	323.8	322.4	321.6	320.7
25°	349.8	341.3	332.1	325.2	318.1	315.0	313.6	312.5	311.4	310.3	310.0
27.5°	334.3	325.0	317.6	310.9	305.9	303.4	301.9	301.4	301.6	302.1	302.4
30°	322.6	314.1	308.0	302.4	297.6	295.3	295.0	295.0	296.0	296.2	296.7
32.5°	311.8	304.9	298.7	293.3	289.7	288.1	289.0	289.0	289.7	290.3	291.2
35°	296.2	290.0	285.4	280.6	277.6	278.3	278.8	279.2	280.4	281.9	282.8
37.5°	281.2	276.0	271.0	267.4	266.0	267.2	268.4	269.3	270.7	271.9	272.8
40°	270.5	266.5	261.9	258.5	259.0	259.7	260.6	261.9	263.1	263.8	264.7
42.5°	260.5	256.4	252.8	250.0	250.7	251.7	252.2	252.8	254.2	255.5	256.0
45°	245.4	242.1	238.8	237.1	237.6	238.1	238.5	239.2	240.4	241.4	241.7
47.5°	228.3	226.0	223.8	222.2	223.0	222.8	223.4	224.9	225.2	225.8	227.1
50°	217.4	215.3	212.7	212.2	212.2	212.2	212.5	214.3	214.3	215.3	216.2
52.5°	205.3	204.0	202.4	201.5	201.1	201.1	202.1	203.0	203.4	204.7	205.7
55°	187.5	186.1	184.7	184.0	183.5	184.0	185.8	186.3	187.5	188.2	188.9
57.5°	169.0	167.8	166.7	166.3	166.2	166.8	167.8	169.3	169.6	171.8	172.8
60°	156.7	155.0	154.1	154.1	153.6	155.7	155.3	157.6	158.1	159.6	161.2
62.5°	144.1	141.9	141.5	141.5	142.2	142.8	143.4	144.4	145.7	147.4	148.8
65°	123.7	122.6	124.2	124.0	123.5	124.9	124.9	126.1	127.5	129.2	131.8
67.5°	104.5	103.9	104.0	104.0	104.7	105.5	106.2	107.2	109.0	110.7	112.4
70°	91.5	92.2	91.1	92.0	92.7	92.9	93.4	94.8	96.6	97.9	99.8
72.5°	78.9	78.9	79.0	79.4	80.1	80.5	81.0	82.6	84.6	85.6	87.2
75°	60.7	60.5	61.2	61.2	62.3	62.8	63.3	64.0	65.8	67.3	68.5
77.5°	44.3	44.6	44.4	45.2	44.9	45.0	46.5	47.2	47.4	50.2	50.8
80°	33.4	33.8	34.1	34.3	34.5	34.1	35.7	36.5	36.5	38.1	39.3
82.5°	24.0	24.2	24.8	25.1	25.1	25.7	25.8	26.3	26.9	27.6	29.1
85°	12.0	12.7	12.9	12.7	12.9	12.4	13.1	13.4	13.6	13.6	13.6
87.5°	5.8	6.5	6.9	7.7	8.0	8.8	9.0	8.8	9.0	9.7	9.1
90°	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0	26.9	27.8	28.5
92.5°	16.3	17.1	19.2	21.4	23.6	25.9	27.3	28.7	30.1	31.5	32.4
95°	24.7	21.4	23.8	26.4	28.8	31.2	32.8	34.3	36.0	37.6	38.3
97.5°	107.0	96.9	80.9	64.7	48.6	32.4	34.2	36.1	37.9	39.6	40.6
100°	188.2	173.0	138.0	103.1	68.2	33.2	35.0	36.9	38.7	40.4	41.4
102.5°	236.5	219.0	180.9	142.7	104.5	66.3	60.8	55.2	49.7	44.1	41.5
105°	310.2	301.3	281.2	261.1	241.0	220.8	181.1	141.5	101.8	62.2	42.5
107.5°	389.3	391.9	395.1	398.3	401.4	404.7	375.6	346.5	317.4	288.3	258.8
110°	442.6	444.7	447.2	449.7	452.1	454.6	447.2	439.8	432.4	425.1	405.4



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	493.5	495.5	498.1	500.5	502.9	505.4	505.5	505.6	505.8	505.9	502.6
115°	568.9	570.6	572.5	574.5	576.5	578.6	580.9	583.1	585.3	587.5	589.2
117.5°	644.1	645.4	646.4	647.5	648.5	649.5	651.4	653.2	654.9	656.7	657.7
120°	691.5	692.9	693.5	694.2	694.9	695.5	697.3	699.1	700.8	702.7	703.6
122.5°	736.8	738.1	738.9	739.8	740.6	741.4	742.8	744.0	745.3	746.5	747.2
125°	801.4	802.8	803.8	804.6	805.5	806.4	806.9	807.3	807.7	808.2	808.6
127.5°	863.5	864.9	866.1	867.2	868.2	869.3	870.0	870.7	871.4	872.1	872.3
130°	902.3	903.6	904.5	905.4	906.3	907.2	908.1	909.0	909.9	910.8	911.0
132.5°	939.4	940.6	941.3	942.0	942.8	943.5	944.4	945.2	946.1	947.1	947.2
135°	994.2	995.3	996.2	997.1	998.0	999.0	999.6	1000.3	1001.0	1001.6	1001.6
137.5°	1044.0	1045.1	1045.6	1046.1	1046.6	1047.1	1048.1	1049.2	1050.4	1051.4	1051.7
140°	1074.9	1075.9	1076.5	1077.2	1077.9	1078.5	1079.4	1080.4	1081.3	1082.2	1082.4
142.5°	1104.7	1105.7	1106.4	1107.0	1107.7	1108.4	1109.1	1109.8	1110.5	1111.3	1111.3
145°	1147.3	1148.3	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0	1151.4	1152.0	1152.2
147.5°	1184.5	1185.2	1185.7	1186.1	1186.6	1187.0	1187.5	1187.9	1188.3	1188.8	1188.5
150°	1207.2	1207.8	1208.2	1208.7	1209.1	1209.6	1210.0	1210.5	1210.9	1211.4	1211.2
152.5°	1227.6	1227.9	1228.1	1228.4	1228.7	1228.9	1229.7	1230.5	1231.3	1232.1	1232.0
155°	1255.2	1255.1	1255.3	1255.5	1255.8	1256.0	1257.1	1258.2	1259.3	1260.4	1260.3
157.5°	1280.6	1280.4	1280.2	1280.0	1279.8	1279.5	1280.9	1282.2	1283.5	1285.0	1284.8
160°	1294.3	1294.1	1293.9	1293.7	1293.4	1293.2	1294.6	1296.0	1297.3	1298.6	1298.5
162.5°	1306.7	1306.3	1306.1	1305.8	1305.6	1305.4	1306.9	1308.4	1309.9	1311.4	1311.5
165°	1322.8	1322.4	1322.1	1321.9	1321.7	1321.5	1323.2	1325.0	1326.9	1328.7	1328.8
167.5°	1334.8	1334.3	1334.3	1334.3	1334.3	1334.3	1336.2	1338.0	1339.8	1341.5	1341.5
170°	1342.1	1341.6	1341.6	1341.6	1341.6	1341.6	1343.4	1345.2	1347.1	1348.8	1348.8
172.5°	1346.3	1345.7	1345.9	1346.2	1346.3	1346.5	1348.3	1350.1	1351.8	1353.6	1353.5
175°	1352.3	1351.8	1352.0	1352.3	1352.5	1352.7	1354.3	1355.8	1357.5	1359.0	1358.9
177.5°	1354.8	1354.4	1354.6	1354.8	1354.9	1355.1	1356.6	1358.0	1359.5	1360.9	1360.7
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	464.3	464.1	465.4	464.5	465.4	464.1	464.3	465.6	466.1	466.2	466.2
5°	432.2	432.9	430.5	430.5	430.5	432.9	432.2	433.6	434.7	435.8	437.1
7.5°	403.5	402.5	402.6	401.3	402.6	402.5	403.5	404.7	406.2	408.3	410.2
10°	386.1	384.7	384.2	384.5	384.2	384.7	386.1	388.9	389.8	391.7	393.8
12.5°	371.5	371.3	368.2	368.2	368.2	371.3	371.5	372.3	374.4	378.4	380.8
15°	354.6	350.1	349.6	351.0	349.6	350.1	354.6	354.6	355.5	358.5	359.9
17.5°	337.5	335.1	335.3	334.6	335.3	335.1	337.5	337.8	338.6	341.1	343.0
20°	328.4	327.0	326.8	325.2	326.8	327.0	328.4	328.4	329.4	330.5	332.4
22.5°	320.1	319.7	319.8	318.0	319.8	319.7	320.1	320.7	321.6	322.4	323.8
25°	309.8	311.0	310.0	310.0	310.0	311.0	309.8	310.0	310.3	311.4	312.5
27.5°	302.9	302.9	302.4	302.4	302.4	302.9	302.9	302.4	302.1	301.6	301.4
30°	297.6	297.4	297.8	297.8	297.8	297.4	297.6	296.7	296.2	296.0	295.0
32.5°	292.4	292.7	292.8	293.0	292.8	292.7	292.4	291.2	290.3	289.7	289.0
35°	284.2	284.5	285.2	284.7	285.2	284.5	284.2	282.8	281.9	280.4	279.2
37.5°	273.2	274.3	274.1	274.4	274.1	274.3	273.2	272.8	271.9	270.7	269.3
40°	264.9	265.6	265.4	265.4	265.4	265.6	264.9	264.7	263.8	263.1	261.9
42.5°	256.4	256.9	256.3	256.0	256.3	256.9	256.4	256.0	255.5	254.2	252.8
45°	242.6	242.1	242.8	241.9	242.8	242.1	242.6	241.7	241.4	240.4	239.2
47.5°	227.0	227.5	227.7	228.4	227.7	227.5	227.0	227.1	225.8	225.2	224.9
50°	216.7	218.1	218.1	217.8	218.1	218.1	216.7	216.2	215.3	214.3	214.3
52.5°	206.5	207.1	208.1	208.0	208.1	207.1	206.5	205.7	204.7	203.4	203.0
55°	190.8	191.3	191.8	192.0	191.8	191.3	190.8	188.9	188.2	187.5	186.3
57.5°	174.5	174.3	175.4	175.8	175.4	174.3	174.5	172.8	171.8	169.6	169.3
60°	163.0	163.0	164.9	165.6	164.9	163.0	163.0	161.2	159.6	158.1	157.6
62.5°	150.8	151.6	153.4	152.5	153.4	151.6	150.8	148.8	147.4	145.7	144.4
65°	132.9	134.8	134.6	135.5	134.6	134.8	132.9	131.8	129.2	127.5	126.1
67.5°	114.2	115.4	117.1	117.2	117.1	115.4	114.2	112.4	110.7	109.0	107.2
70°	101.6	102.8	103.7	104.4	103.7	102.8	101.6	99.8	97.9	96.6	94.8
72.5°	89.4	90.0	92.3	91.3	92.3	90.0	89.4	87.2	85.6	84.6	82.6
75°	70.1	71.8	73.2	72.5	73.2	71.8	70.1	68.5	67.3	65.8	64.0
77.5°	51.8	53.5	54.1	53.5	54.1	53.5	51.8	50.8	50.2	47.4	47.2
80°	40.9	40.7	42.1	41.9	42.1	40.7	40.9	39.3	38.1	36.5	36.5
82.5°	30.0	29.8	30.4	30.6	30.4	29.8	30.0	29.1	27.6	26.9	26.3
85°	14.5	15.2	14.3	14.1	14.3	15.2	14.5	13.6	13.6	13.6	13.4
87.5°	9.2	9.3	9.2	9.1	9.2	9.3	9.2	9.1	9.7	9.0	8.8
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0
92.5°	32.6	32.9	33.2	33.4	33.2	32.9	32.6	32.4	31.5	30.1	28.7
95°	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	37.6	36.0	34.3
97.5°	40.9	41.1	41.3	41.5	41.3	41.1	40.9	40.6	39.6	37.9	36.1
100°	41.7	41.9	42.1	42.3	42.1	41.9	41.7	41.4	40.4	38.7	36.9
102.5°	41.9	42.3	42.7	43.1	42.7	42.3	41.9	41.5	44.1	49.7	55.2
105°	43.0	43.4	43.9	44.3	43.9	43.4	43.0	42.5	62.2	101.8	141.5
107.5°	228.9	199.0	169.2	139.3	169.2	199.0	228.9	258.8	288.3	317.4	346.5
110°	373.2	341.2	309.2	277.2	309.2	341.2	373.2	405.4	425.1	432.4	439.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	495.8	489.1	482.3	475.5	482.3	489.1	495.8	502.6	505.9	505.8	505.6
115°	590.0	590.9	591.8	592.7	591.8	590.9	590.0	589.2	587.5	585.3	583.1
117.5°	657.9	658.0	658.2	658.4	658.2	658.0	657.9	657.7	656.7	654.9	653.2
120°	703.6	703.6	703.6	703.6	703.6	703.6	703.6	703.6	702.7	700.8	699.1
122.5°	747.4	747.6	747.7	747.9	747.7	747.6	747.4	747.2	746.5	745.3	744.0
125°	809.1	809.5	810.0	810.4	810.0	809.5	809.1	808.6	808.2	807.7	807.3
127.5°	871.8	871.4	870.9	870.5	870.9	871.4	871.8	872.3	872.1	871.4	870.7
130°	910.6	910.1	909.7	909.2	909.7	910.1	910.6	911.0	910.8	909.9	909.0
132.5°	946.5	945.9	945.3	944.7	945.3	945.9	946.5	947.2	947.1	946.1	945.2
135°	1001.0	1000.3	999.6	999.0	999.6	1000.3	1001.0	1001.6	1001.6	1001.0	1000.3
137.5°	1051.3	1050.9	1050.4	1050.0	1050.4	1050.9	1051.3	1051.7	1051.4	1050.4	1049.2
140°	1081.9	1081.5	1081.1	1080.6	1081.1	1081.5	1081.9	1082.4	1082.2	1081.3	1080.4
142.5°	1110.6	1110.0	1109.4	1108.8	1109.4	1110.0	1110.6	1111.3	1111.3	1110.5	1109.8
145°	1152.2	1152.2	1152.2	1152.2	1152.2	1152.2	1152.2	1152.2	1152.0	1151.4	1151.0
147.5°	1187.5	1186.5	1185.4	1184.4	1185.4	1186.5	1187.5	1188.5	1188.8	1188.3	1187.9
150°	1210.6	1209.9	1209.2	1208.6	1209.2	1209.9	1210.6	1211.2	1211.4	1210.9	1210.5
152.5°	1231.0	1230.0	1229.0	1227.9	1229.0	1230.0	1231.0	1232.0	1232.1	1231.3	1230.5
155°	1259.0	1257.7	1256.3	1255.0	1256.3	1257.7	1259.0	1260.3	1260.4	1259.3	1258.2
157.5°	1282.9	1281.2	1279.5	1277.8	1279.5	1281.2	1282.9	1284.8	1285.0	1283.5	1282.2
160°	1297.0	1295.4	1293.8	1292.2	1293.8	1295.4	1297.0	1298.5	1298.6	1297.3	1296.0
162.5°	1310.1	1308.7	1307.4	1306.0	1307.4	1308.7	1310.1	1311.5	1311.4	1309.9	1308.4
165°	1327.2	1325.6	1324.0	1322.5	1324.0	1325.6	1327.2	1328.8	1328.7	1326.9	1325.0
167.5°	1339.8	1338.0	1336.2	1334.3	1336.2	1338.0	1339.8	1341.5	1341.5	1339.8	1338.0
170°	1347.1	1345.2	1343.4	1341.6	1343.4	1345.2	1347.1	1348.8	1348.8	1347.1	1345.2
172.5°	1351.6	1349.6	1347.7	1345.6	1347.7	1349.6	1351.6	1353.5	1353.6	1351.8	1350.1
175°	1357.1	1355.3	1353.5	1351.7	1353.5	1355.3	1357.1	1358.9	1359.0	1357.5	1355.8
177.5°	1358.9	1357.2	1355.3	1353.5	1355.3	1357.2	1358.9	1360.7	1360.9	1359.5	1358.0
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	465.6	465.6	469.2	471.5	474.3	476.2	477.5	478.8	481.1	484.0	487.5
5°	439.0	439.9	445.1	450.3	455.2	459.5	463.0	467.3	472.4	478.8	485.8
7.5°	413.2	416.9	422.0	428.4	435.3	441.4	447.7	454.6	462.0	471.3	481.2
10°	396.7	400.6	407.0	415.1	422.3	429.6	437.4	444.8	454.0	465.1	477.9
12.5°	382.1	386.0	392.5	401.2	408.2	416.3	425.2	434.9	445.2	458.5	472.9
15°	362.0	366.6	374.6	378.8	389.4	399.0	407.3	421.3	434.5	448.2	464.8
17.5°	345.6	348.1	354.6	362.4	370.3	381.2	391.9	403.7	416.9	433.5	454.4
20°	334.3	336.4	343.5	351.7	360.2	370.1	379.7	391.5	406.3	423.9	446.6
22.5°	325.9	328.1	332.8	341.5	349.4	357.7	367.3	381.3	397.1	414.3	438.8
25°	313.6	315.0	318.1	325.2	332.1	341.3	349.8	363.0	379.2	399.5	423.9
27.5°	301.9	303.4	305.9	310.9	317.6	325.0	334.3	345.4	361.8	383.8	409.8
30°	295.0	295.3	297.6	302.4	308.0	314.1	322.6	335.3	350.8	373.1	400.4
32.5°	289.0	288.1	289.7	293.3	298.7	304.9	311.8	324.4	339.3	361.2	389.3
35°	278.8	278.3	277.6	280.6	285.4	290.0	296.2	305.6	322.6	343.1	372.4
37.5°	268.4	267.2	266.0	267.4	271.0	276.0	281.2	289.6	304.3	326.8	355.0
40°	260.6	259.7	259.0	258.5	261.9	266.5	270.5	278.5	292.2	313.6	341.3
42.5°	252.2	251.7	250.7	250.0	252.8	256.4	260.5	267.6	281.2	301.3	327.6
45°	238.5	238.1	237.6	237.1	238.8	242.1	245.4	250.5	262.4	281.9	305.6
47.5°	223.4	222.8	223.0	222.2	223.8	226.0	228.3	233.9	245.1	260.9	278.3
50°	212.5	212.2	212.2	212.2	212.7	215.3	217.4	221.7	232.0	247.7	260.2
52.5°	202.1	201.1	201.1	201.5	202.4	204.0	205.3	210.0	218.9	232.0	243.3
55°	185.8	184.0	183.5	184.0	184.7	186.1	187.5	191.3	199.0	208.6	215.3
57.5°	167.8	166.8	166.2	166.3	166.7	167.8	169.0	173.0	179.2	184.2	188.4
60°	155.3	155.7	153.6	154.1	154.1	155.0	156.7	159.3	164.4	167.9	172.2
62.5°	143.4	142.8	142.2	141.5	141.5	141.9	144.1	146.1	150.6	152.4	155.6
65°	124.9	124.9	123.5	124.0	124.2	122.6	123.7	126.1	129.0	129.7	132.7
67.5°	106.2	105.5	104.7	104.0	104.0	103.9	104.5	105.6	107.8	108.1	110.4
70°	93.4	92.9	92.7	92.0	91.1	92.2	91.5	92.7	93.9	94.1	95.5
72.5°	81.0	80.5	80.1	79.4	79.0	78.9	78.9	80.3	81.1	80.8	82.3
75°	63.3	62.8	62.3	61.2	61.2	60.5	60.7	61.6	62.6	61.9	63.3
77.5°	46.5	45.0	44.9	45.2	44.4	44.6	44.3	44.2	44.6	44.6	45.9
80°	35.7	34.1	34.5	34.3	34.1	33.8	33.4	33.6	33.8	34.1	34.8
82.5°	25.8	25.7	25.1	25.1	24.8	24.2	24.0	24.4	24.6	24.5	25.0
85°	13.1	12.4	12.9	12.7	12.9	12.7	12.0	12.0	12.4	12.2	12.7
87.5°	9.0	8.8	8.0	7.7	6.9	6.5	5.8	5.5	5.3	4.7	4.7
90°	25.0	24.2	21.3	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0
92.5°	27.3	25.9	23.6	21.4	19.2	17.1	16.3	16.9	17.5	18.1	18.8
95°	32.8	31.2	28.8	26.4	23.8	21.4	24.7	33.9	43.1	52.3	61.5
97.5°	34.2	32.4	48.6	64.7	80.9	96.9	107.0	111.2	115.3	119.5	123.6
100°	35.0	33.2	68.2	103.1	138.0	173.0	188.2	183.8	179.4	174.8	170.4
102.5°	60.8	66.3	104.5	142.7	180.9	219.0	236.5	233.3	230.0	226.8	223.6
105°	181.1	220.8	241.0	261.1	281.2	301.3	310.2	307.8	305.3	302.9	300.3
107.5°	375.6	404.7	401.4	398.3	395.1	391.9	389.3	387.4	385.4	383.4	381.4
110°	447.2	454.6	452.1	449.7	447.2	444.7	442.6	440.8	439.0	437.3	435.5



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	505.5	505.4	502.9	500.5	498.1	495.5	493.5	491.9	490.3	488.7	487.1
115°	580.9	578.6	576.5	574.5	572.5	570.6	568.9	567.5	566.1	564.8	563.5
117.5°	651.4	649.5	648.5	647.5	646.4	645.4	644.1	642.5	640.8	639.1	637.4
120°	697.3	695.5	694.9	694.2	693.5	692.9	691.5	689.4	687.4	685.4	683.4
122.5°	742.8	741.4	740.6	739.8	738.9	738.1	736.8	735.2	733.5	731.8	730.2
125°	806.9	806.4	805.5	804.6	803.8	802.8	801.4	799.7	797.9	796.1	794.3
127.5°	870.0	869.3	868.2	867.2	866.1	864.9	863.5	861.7	860.0	858.2	856.4
130°	908.1	907.2	906.3	905.4	904.5	903.6	902.3	900.5	898.7	896.9	895.1
132.5°	944.4	943.5	942.8	942.0	941.3	940.6	939.4	937.6	935.7	934.0	932.2
135°	999.6	999.0	998.0	997.1	996.2	995.3	994.2	992.9	991.5	990.2	988.9
137.5°	1048.1	1047.1	1046.6	1046.1	1045.6	1045.1	1044.0	1042.4	1040.7	1038.9	1037.2
140°	1079.4	1078.5	1077.9	1077.2	1076.5	1075.9	1074.9	1073.5	1072.2	1070.9	1069.4
142.5°	1109.1	1108.4	1107.7	1107.0	1106.4	1105.7	1104.7	1103.4	1102.0	1100.7	1099.3
145°	1150.5	1150.1	1149.6	1149.2	1148.8	1148.3	1147.3	1145.8	1144.2	1142.7	1141.0
147.5°	1187.5	1187.0	1186.6	1186.1	1185.7	1185.2	1184.5	1183.5	1182.5	1181.4	1180.3
150°	1210.0	1209.6	1209.1	1208.7	1208.2	1207.8	1207.2	1206.6	1205.9	1205.3	1204.6
152.5°	1229.7	1228.9	1228.7	1228.4	1228.1	1227.9	1227.6	1227.3	1227.0	1226.7	1226.3
155°	1257.1	1256.0	1255.8	1255.5	1255.3	1255.1	1255.2	1255.7	1256.1	1256.5	1257.0
157.5°	1280.9	1279.5	1279.8	1280.0	1280.2	1280.4	1280.6	1280.6	1280.7	1280.7	1280.7
160°	1294.6	1293.2	1293.4	1293.7	1293.9	1294.1	1294.3	1294.6	1294.8	1295.1	1295.3
162.5°	1306.9	1305.4	1305.6	1305.8	1306.1	1306.3	1306.7	1307.3	1307.8	1308.4	1309.0
165°	1323.2	1321.5	1321.7	1321.9	1322.1	1322.4	1322.8	1323.5	1324.1	1324.8	1325.5
167.5°	1336.2	1334.3	1334.3	1334.3	1334.3	1334.3	1334.8	1335.7	1336.7	1337.6	1338.4
170°	1343.4	1341.6	1341.6	1341.6	1341.6	1341.6	1342.1	1343.0	1343.9	1344.7	1345.6
172.5°	1348.3	1346.5	1346.3	1346.2	1345.9	1345.7	1346.3	1347.3	1348.4	1349.5	1350.5
175°	1354.3	1352.7	1352.5	1352.3	1352.0	1351.8	1352.3	1353.4	1354.5	1355.6	1356.8
177.5°	1356.6	1355.1	1354.9	1354.8	1354.6	1354.4	1354.8	1355.6	1356.6	1357.5	1358.4
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	488.6	489.6	492.7	495.0	497.7	499.2	500.6	501.8	503.3	503.6	509.1
5°	490.8	495.4	503.7	509.8	517.4	525.5	531.2	533.8	540.7	546.2	557.5
7.5°	490.2	500.2	512.6	525.5	539.3	552.1	563.2	576.4	585.7	599.9	613.7
10°	489.6	503.0	519.0	535.4	554.7	572.6	588.7	606.5	621.4	640.9	657.5
12.5°	487.9	504.1	526.3	545.8	569.3	593.9	617.6	640.6	653.7	686.2	701.6
15°	483.7	503.0	530.8	560.4	592.6	621.8	651.9	675.9	714.7	743.2	761.3
17.5°	475.7	502.7	535.6	571.4	610.6	649.0	683.2	719.5	760.7	795.2	831.9
20°	471.9	501.6	538.3	577.8	618.5	662.1	700.8	744.6	789.5	823.4	870.5
22.5°	464.9	498.6	538.1	582.1	625.6	670.7	716.1	760.2	812.1	858.8	903.6
25°	453.6	491.2	532.2	581.4	632.4	677.5	732.0	790.5	844.6	904.6	949.3
27.5°	441.6	481.8	522.8	568.6	623.5	677.1	745.5	811.6	877.8	929.6	962.7
30°	432.4	471.5	513.8	560.0	614.3	678.0	754.5	826.7	891.2	935.6	954.2
32.5°	422.4	462.0	499.5	547.9	605.8	677.4	760.1	835.6	891.9	921.5	917.9
35°	406.8	439.9	476.5	523.0	591.2	673.3	763.5	836.4	870.9	864.5	816.6
37.5°	384.2	412.1	448.0	499.0	574.3	664.6	756.8	811.5	809.3	757.6	688.0
40°	370.1	393.8	428.4	482.0	561.1	658.9	746.5	782.0	751.9	679.6	596.4
42.5°	351.6	373.5	408.1	463.2	546.6	647.5	726.7	737.0	678.1	595.0	518.7
45°	323.1	342.3	378.1	435.0	524.8	622.5	678.5	653.3	574.0	488.2	430.1
47.5°	292.3	312.4	346.7	405.3	493.4	584.9	611.6	558.1	476.7	407.0	353.7
50°	272.9	292.2	325.9	384.9	472.2	554.0	565.1	495.9	421.1	359.9	316.2
52.5°	253.4	271.5	304.6	363.9	447.4	518.3	511.5	441.0	372.2	320.0	285.7
55°	224.2	241.4	272.9	328.4	404.5	460.6	436.0	368.7	311.7	271.2	245.1
57.5°	198.1	214.6	241.8	292.0	358.0	396.7	365.3	308.5	263.3	232.1	212.7
60°	180.5	195.0	221.0	267.5	324.9	354.3	323.3	273.2	235.0	210.1	192.7
62.5°	163.7	176.4	200.4	242.7	292.6	317.2	285.8	243.4	211.0	188.8	174.0
65°	138.4	149.9	171.1	204.0	244.9	261.4	234.3	200.0	174.8	158.3	148.5
67.5°	115.2	125.0	143.3	169.2	199.3	211.3	190.7	164.1	145.1	131.9	124.1
70°	99.8	108.3	122.6	144.9	172.2	181.4	162.1	140.2	126.3	115.7	108.5
72.5°	86.7	93.0	106.0	123.3	146.0	153.3	139.9	120.7	107.8	99.8	93.9
75°	66.1	71.3	79.8	93.6	109.4	113.6	103.5	91.5	82.8	77.2	72.7
77.5°	47.7	51.5	57.6	66.1	77.1	80.9	74.5	66.4	60.1	56.4	53.8
80°	36.0	39.1	44.2	51.3	57.9	60.0	56.2	50.1	45.6	43.5	41.4
82.5°	26.6	28.3	31.4	36.3	40.7	43.2	40.1	36.4	33.9	32.0	31.2
85°	13.4	14.3	15.8	17.7	20.5	21.4	20.2	19.3	17.9	16.7	16.7
87.5°	5.6	6.0	7.0	7.9	9.1	10.2	10.6	10.8	11.2	11.2	11.2
90°	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0
92.5°	18.1	17.5	16.9	16.3	17.1	19.2	21.4	23.6	25.9	27.3	28.7
95°	52.3	43.1	33.9	24.7	21.4	23.8	26.4	28.8	31.2	32.8	34.3
97.5°	119.5	115.3	111.2	107.0	96.9	80.9	64.7	48.6	32.4	34.2	36.1
100°	174.8	179.4	183.8	188.2	173.0	138.0	103.1	68.2	33.2	35.0	36.9
102.5°	226.8	230.0	233.3	236.5	219.0	180.9	142.7	104.5	66.3	60.8	55.2
105°	302.9	305.3	307.8	310.2	301.3	281.2	261.1	241.0	220.8	181.1	141.5
107.5°	383.4	385.4	387.4	389.3	391.9	395.1	398.3	401.4	404.7	375.6	346.5
110°	437.3	439.0	440.8	442.6	444.7	447.2	449.7	452.1	454.6	447.2	439.8





TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	488.7	490.3	491.9	493.5	495.5	498.1	500.5	502.9	505.4	505.5	505.6
115°	564.8	566.1	567.5	568.9	570.6	572.5	574.5	576.5	578.6	580.9	583.1
117.5°	639.1	640.8	642.5	644.1	645.4	646.4	647.5	648.5	649.5	651.4	653.2
120°	685.4	687.4	689.4	691.5	692.9	693.5	694.2	694.9	695.5	697.3	699.1
122.5°	731.8	733.5	735.2	736.8	738.1	738.9	739.8	740.6	741.4	742.8	744.0
125°	796.1	797.9	799.7	801.4	802.8	803.8	804.6	805.5	806.4	806.9	807.3
127.5°	858.2	860.0	861.7	863.5	864.9	866.1	867.2	868.2	869.3	870.0	870.7
130°	896.9	898.7	900.5	902.3	903.6	904.5	905.4	906.3	907.2	908.1	909.0
132.5°	934.0	935.7	937.6	939.4	940.6	941.3	942.0	942.8	943.5	944.4	945.2
135°	990.2	991.5	992.9	994.2	995.3	996.2	997.1	998.0	999.0	999.6	1000.3
137.5°	1038.9	1040.7	1042.4	1044.0	1045.1	1045.6	1046.1	1046.6	1047.1	1048.1	1049.2
140°	1070.9	1072.2	1073.5	1074.9	1075.9	1076.5	1077.2	1077.9	1078.5	1079.4	1080.4
142.5°	1100.7	1102.0	1103.4	1104.7	1105.7	1106.4	1107.0	1107.7	1108.4	1109.1	1109.8
145°	1142.7	1144.2	1145.8	1147.3	1148.3	1148.8	1149.2	1149.6	1150.1	1150.5	1151.0
147.5°	1181.4	1182.5	1183.5	1184.5	1185.2	1185.7	1186.1	1186.6	1187.0	1187.5	1187.9
150°	1205.3	1205.9	1206.6	1207.2	1207.8	1208.2	1208.7	1209.1	1209.6	1210.0	1210.5
152.5°	1226.7	1227.0	1227.3	1227.6	1227.9	1228.1	1228.4	1228.7	1228.9	1229.7	1230.5
155°	1256.5	1256.1	1255.7	1255.2	1255.1	1255.3	1255.5	1255.8	1256.0	1257.1	1258.2
157.5°	1280.7	1280.7	1280.6	1280.6	1280.4	1280.2	1280.0	1279.8	1279.5	1280.9	1282.2
160°	1295.1	1294.8	1294.6	1294.3	1294.1	1293.9	1293.7	1293.4	1293.2	1294.6	1296.0
162.5°	1308.4	1307.8	1307.3	1306.7	1306.3	1306.1	1305.8	1305.6	1305.4	1306.9	1308.4
165°	1324.8	1324.1	1323.5	1322.8	1322.4	1322.1	1321.9	1321.7	1321.5	1323.2	1325.0
167.5°	1337.6	1336.7	1335.7	1334.8	1334.3	1334.3	1334.3	1334.3	1334.3	1336.2	1338.0
170°	1344.7	1343.9	1343.0	1342.1	1341.6	1341.6	1341.6	1341.6	1341.6	1343.4	1345.2
172.5°	1349.5	1348.4	1347.3	1346.3	1345.7	1345.9	1346.2	1346.3	1346.5	1348.3	1350.1
175°	1355.6	1354.5	1353.4	1352.3	1351.8	1352.0	1352.3	1352.5	1352.7	1354.3	1355.8
177.5°	1357.5	1356.6	1355.6	1354.8	1354.4	1354.6	1354.8	1354.9	1355.1	1356.6	1358.0
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	511.0	511.2	513.2	514.7	514.0	514.9	515.3
5°	558.3	566.7	571.2	574.5	574.7	575.0	576.8
7.5°	625.3	634.4	641.1	651.2	654.1	657.5	656.6
10°	674.3	687.7	699.2	705.3	712.0	721.5	713.8
12.5°	720.0	743.8	761.3	770.8	777.0	778.9	775.2
15°	795.5	826.5	843.1	842.7	863.8	873.0	858.7
17.5°	864.5	893.2	916.3	928.0	945.6	949.5	947.8
20°	907.0	938.3	956.1	976.3	985.5	993.7	995.1
22.5°	943.4	971.6	990.8	1007.5	1015.2	1019.2	1021.5
25°	981.1	1003.2	1014.7	1020.6	1022.7	1022.2	1019.2
27.5°	978.5	980.2	967.5	955.0	943.8	931.3	927.0
30°	953.0	933.3	898.0	878.0	848.6	825.3	834.8
32.5°	886.3	846.9	807.3	763.6	727.4	717.1	706.7
35°	756.4	687.2	646.7	599.7	580.9	562.1	549.1
37.5°	611.9	558.5	510.4	479.7	460.8	448.9	442.5
40°	529.1	480.9	441.3	416.4	402.0	388.7	386.8
42.5°	463.0	418.2	388.5	368.6	354.9	349.1	345.0
45°	379.2	348.0	328.0	313.9	304.7	301.1	296.4
47.5°	321.0	298.9	283.9	274.3	267.3	264.7	264.4
50°	288.4	270.0	259.0	251.5	246.1	245.1	241.4
52.5°	264.0	248.0	239.4	232.9	228.9	226.3	225.2
55°	229.1	218.5	210.8	207.0	204.0	201.4	201.4
57.5°	200.5	191.7	186.5	183.3	182.4	180.6	179.4
60°	182.8	175.3	171.3	168.4	166.5	166.8	164.7
62.5°	165.5	160.6	156.7	154.0	151.7	151.8	151.9
65°	140.9	137.1	134.3	133.4	132.0	130.4	130.8
67.5°	119.5	115.9	113.7	112.1	111.6	110.7	112.1
70°	104.0	101.4	99.8	98.4	97.9	98.1	99.3
72.5°	89.9	88.1	86.9	86.3	85.2	85.3	86.1
75°	70.6	69.2	68.3	67.6	67.3	67.3	67.3
77.5°	51.8	51.5	51.1	50.1	50.1	50.4	50.4
80°	40.9	40.2	40.0	39.5	38.8	38.4	39.5
82.5°	30.6	29.9	29.7	29.6	28.5	28.4	29.4
85°	16.5	15.8	16.0	15.8	15.8	15.6	15.6
87.5°	11.2	11.2	11.1	11.4	11.3	11.2	11.7
90°	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	30.1	31.5	32.4	32.6	32.9	33.2	33.4
95°	36.0	37.6	38.3	38.3	38.3	38.3	38.3
97.5°	37.9	39.6	40.6	40.9	41.1	41.3	41.5
100°	38.7	40.4	41.4	41.7	41.9	42.1	42.3
102.5°	49.7	44.1	41.5	41.9	42.3	42.7	43.1
105°	101.8	62.2	42.5	43.0	43.4	43.9	44.3
107.5°	317.4	288.3	258.8	228.9	199.0	169.2	139.3
110°	432.4	425.1	405.4	373.2	341.2	309.2	277.2



TEST NUMBER: P331892-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	505.8	505.9	502.6	495.8	489.1	482.3	475.5
115°	585.3	587.5	589.2	590.0	590.9	591.8	592.7
117.5°	654.9	656.7	657.7	657.9	658.0	658.2	658.4
120°	700.8	702.7	703.6	703.6	703.6	703.6	703.6
122.5°	745.3	746.5	747.2	747.4	747.6	747.7	747.9
125°	807.7	808.2	808.6	809.1	809.5	810.0	810.4
127.5°	871.4	872.1	872.3	871.8	871.4	870.9	870.5
130°	909.9	910.8	911.0	910.6	910.1	909.7	909.2
132.5°	946.1	947.1	947.2	946.5	945.9	945.3	944.7
135°	1001.0	1001.6	1001.6	1001.0	1000.3	999.6	999.0
137.5°	1050.4	1051.4	1051.7	1051.3	1050.9	1050.4	1050.0
140°	1081.3	1082.2	1082.4	1081.9	1081.5	1081.1	1080.6
142.5°	1110.5	1111.3	1111.3	1110.6	1110.0	1109.4	1108.8
145°	1151.4	1152.0	1152.2	1152.2	1152.2	1152.2	1152.2
147.5°	1188.3	1188.8	1188.5	1187.5	1186.5	1185.4	1184.4
150°	1210.9	1211.4	1211.2	1210.6	1209.9	1209.2	1208.6
152.5°	1231.3	1232.1	1232.0	1231.0	1230.0	1229.0	1227.9
155°	1259.3	1260.4	1260.3	1259.0	1257.7	1256.3	1255.0
157.5°	1283.5	1285.0	1284.8	1282.9	1281.2	1279.5	1277.8
160°	1297.3	1298.6	1298.5	1297.0	1295.4	1293.8	1292.2
162.5°	1309.9	1311.4	1311.5	1310.1	1308.7	1307.4	1306.0
165°	1326.9	1328.7	1328.8	1327.2	1325.6	1324.0	1322.5
167.5°	1339.8	1341.5	1341.5	1339.8	1338.0	1336.2	1334.3
170°	1347.1	1348.8	1348.8	1347.1	1345.2	1343.4	1341.6
172.5°	1351.8	1353.6	1353.5	1351.6	1349.6	1347.7	1345.6
175°	1357.5	1359.0	1358.9	1357.1	1355.3	1353.5	1351.7
177.5°	1359.5	1360.9	1360.7	1358.9	1357.2	1355.3	1353.5
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8

(END OF REPORT)