

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331988

Luminaire Tested: **S123DIP-S775D1025U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331988
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7269.5 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44				44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42				37	
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36				31	
3	80	71	63	57	73	65	58	53	54	49	45	44	40	38	35	32	30				26	
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26				22	
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23				19	
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20				17	
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18				15	
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16				13	
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14				12	
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13				11	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	1.6
10°-20°	323.9	4.5
20°-30°	478.4	6.6
30°-40°	558.9	7.7
40°-50°	561.9	7.7
50°-60°	493.6	6.8
60°-70°	367.7	5.1
70°-80°	209.5	2.9
80°-90°	63.9	0.9
90°-100°	48.8	0.7
100°-110°	232.8	3.2
110°-120°	559.2	7.7
120°-130°	712.1	9.8
130°-140°	760.8	10.5
140°-150°	711.5	9.8
150°-160°	573.9	7.9
160°-170°	370.4	5.1
170°-180°	127.6	1.8
0°-30°	917.1	12.6
0°-40°	1475.9	20.3
0°-60°	2531.4	34.8
0°-90°	3172.5	43.6
90°-120°	840.8	11.6
90°-150°	3025.2	41.6
90°-180°	4097.0	56.4
0°-180°	7269.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	1	11	24	28	30	6
95°	61	23	31	38	38	75
105°	297	303	219	52	44	315
115°	558	564	573	583	587	551
125°	786	794	798	800	802	702
135°	979	985	989	992	989	754
145°	1130	1137	1139	1141	1141	707
155°	1245	1243	1244	1248	1243	573
165°	1313	1310	1309	1316	1310	371
175°	1344	1339	1340	1346	1338	128
180°	1344	1344	1344	1344	1344	



TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	22.0	21.9	21.7	21.6	21.5	21.7	22.0	22.4	22.8	23.2	23.2
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	18.6	17.9	17.3	16.7	16.1	16.9	19.0	21.2	23.4	25.6	27.0
95°	60.9	51.8	42.7	33.6	24.5	21.2	23.6	26.1	28.5	30.9	32.5
97.5°	122.4	118.3	114.2	110.1	106.0	96.0	80.1	64.1	48.1	32.1	33.9
100°	168.7	173.1	177.6	182.0	186.4	171.3	136.7	102.1	67.5	32.9	34.7
102.5°	221.4	224.6	227.8	231.0	234.2	216.9	179.1	141.3	103.5	65.7	60.2
105°	297.4	299.9	302.3	304.8	307.2	298.4	278.5	258.5	238.6	218.6	179.3
107.5°	377.7	379.7	381.6	383.6	385.5	388.1	391.2	394.4	397.5	400.7	371.9
110°	431.2	433.0	434.7	436.5	438.3	440.4	442.8	445.3	447.7	450.2	442.8



TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	482.3	483.9	485.5	487.1	488.7	490.7	493.2	495.6	498.0	500.5	500.6
115°	558.0	559.3	560.6	562.0	563.3	565.0	566.9	568.9	570.9	572.9	575.2
117.5°	631.2	632.9	634.5	636.2	637.8	639.1	640.1	641.2	642.2	643.2	645.0
120°	676.7	678.7	680.7	682.7	684.7	686.1	686.7	687.4	688.1	688.7	690.5
122.5°	723.1	724.7	726.3	728.0	729.6	730.9	731.7	732.6	733.4	734.2	735.5
125°	786.5	788.3	790.1	791.9	793.6	795.0	795.9	796.7	797.6	798.5	799.0
127.5°	848.0	849.8	851.6	853.3	855.1	856.5	857.6	858.7	859.7	860.8	861.5
130°	886.4	888.1	889.9	891.7	893.5	894.8	895.7	896.6	897.4	898.3	899.2
132.5°	923.1	924.9	926.6	928.4	930.2	931.4	932.1	932.8	933.6	934.3	935.2
135°	979.2	980.5	981.8	983.2	984.5	985.6	986.5	987.4	988.3	989.2	989.8
137.5°	1027.1	1028.8	1030.5	1032.2	1033.8	1034.9	1035.4	1035.9	1036.4	1036.9	1037.9
140°	1059.0	1060.4	1061.7	1063.0	1064.4	1065.4	1066.0	1066.7	1067.4	1068.0	1068.9
142.5°	1088.6	1089.9	1091.2	1092.6	1093.9	1094.9	1095.6	1096.2	1096.9	1097.6	1098.3
145°	1129.9	1131.5	1133.0	1134.6	1136.1	1137.1	1137.6	1138.0	1138.4	1138.9	1139.3
147.5°	1168.8	1169.9	1170.9	1171.9	1172.9	1173.6	1174.1	1174.5	1175.0	1175.4	1175.9
150°	1192.8	1193.5	1194.1	1194.8	1195.4	1196.0	1196.4	1196.9	1197.3	1197.8	1198.2
152.5°	1214.3	1214.7	1215.0	1215.3	1215.6	1215.9	1216.1	1216.4	1216.7	1216.9	1217.7
155°	1244.7	1244.2	1243.8	1243.4	1242.9	1242.8	1243.0	1243.2	1243.5	1243.7	1244.8
157.5°	1268.2	1268.2	1268.2	1268.1	1268.1	1267.9	1267.7	1267.5	1267.3	1267.0	1268.4
160°	1282.6	1282.4	1282.2	1282.0	1281.7	1281.5	1281.3	1281.1	1280.8	1280.6	1282.0
162.5°	1296.2	1295.6	1295.0	1294.5	1293.9	1293.5	1293.3	1293.0	1292.8	1292.6	1294.1
165°	1312.6	1311.9	1311.2	1310.6	1309.9	1309.5	1309.2	1309.0	1308.8	1308.6	1310.3
167.5°	1325.3	1324.5	1323.6	1322.7	1321.8	1321.3	1321.3	1321.3	1321.3	1321.3	1323.1
170°	1332.5	1331.6	1330.8	1329.9	1329.0	1328.5	1328.5	1328.5	1328.5	1328.5	1330.3
172.5°	1337.3	1336.3	1335.2	1334.1	1333.1	1332.6	1332.8	1333.0	1333.1	1333.3	1335.1
175°	1343.5	1342.4	1341.3	1340.2	1339.1	1338.6	1338.8	1339.1	1339.3	1339.5	1341.1
177.5°	1345.1	1344.2	1343.3	1342.4	1341.6	1341.2	1341.4	1341.6	1341.7	1341.9	1343.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5



TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	23.2	23.2	23.2	23.2	23.3	23.4	23.5	23.6
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	28.4	29.8	31.2	32.1	32.3	32.6	32.9	33.1
95°	34.0	35.6	37.2	37.9	37.9	37.9	37.9	37.9
97.5°	35.7	37.5	39.2	40.2	40.5	40.7	40.9	41.1
100°	36.5	38.3	40.0	41.0	41.3	41.5	41.7	41.9
102.5°	54.7	49.2	43.7	41.1	41.5	41.9	42.3	42.7
105°	140.1	100.8	61.6	42.1	42.6	43.0	43.5	43.9
107.5°	343.1	314.3	285.5	256.3	226.7	197.1	167.5	137.9
110°	435.5	428.2	420.9	401.4	369.6	337.9	306.2	274.5



TEST NUMBER: P331988

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	500.7	500.9	501.0	497.7	491.0	484.3	477.6	470.9
115°	577.4	579.6	581.8	583.4	584.2	585.1	586.0	586.9
117.5°	646.8	648.5	650.3	651.3	651.5	651.6	651.8	652.0
120°	692.3	694.0	695.8	696.7	696.7	696.7	696.7	696.7
122.5°	736.7	738.0	739.2	739.9	740.1	740.3	740.4	740.6
125°	799.4	799.8	800.3	800.7	801.2	801.6	802.1	802.5
127.5°	862.2	862.9	863.6	863.8	863.3	862.9	862.4	862.0
130°	900.1	901.0	901.9	902.1	901.7	901.2	900.8	900.3
132.5°	936.0	936.9	937.8	937.9	937.3	936.7	936.1	935.5
135°	990.5	991.2	991.8	991.8	991.2	990.5	989.8	989.2
137.5°	1039.0	1040.1	1041.1	1041.4	1041.0	1040.6	1040.1	1039.7
140°	1069.8	1070.7	1071.6	1071.8	1071.3	1070.9	1070.5	1070.0
142.5°	1099.0	1099.7	1100.4	1100.4	1099.8	1099.2	1098.6	1098.0
145°	1139.8	1140.2	1140.7	1140.9	1140.9	1140.9	1140.9	1140.9
147.5°	1176.3	1176.7	1177.2	1176.9	1175.9	1174.9	1173.8	1172.8
150°	1198.7	1199.1	1199.6	1199.4	1198.8	1198.1	1197.4	1196.8
152.5°	1218.5	1219.3	1220.1	1220.0	1219.0	1218.0	1217.0	1215.9
155°	1245.9	1247.0	1248.1	1248.0	1246.7	1245.4	1244.0	1242.7
157.5°	1269.7	1271.0	1272.4	1272.2	1270.4	1268.7	1267.0	1265.3
160°	1283.3	1284.6	1285.9	1285.8	1284.3	1282.7	1281.2	1279.6
162.5°	1295.6	1297.1	1298.6	1298.7	1297.3	1295.9	1294.6	1293.2
165°	1312.1	1313.9	1315.7	1315.8	1314.2	1312.7	1311.1	1309.6
167.5°	1324.9	1326.7	1328.4	1328.4	1326.7	1324.9	1323.1	1321.3
170°	1332.1	1333.9	1335.6	1335.6	1333.9	1332.1	1330.3	1328.5
172.5°	1336.9	1338.6	1340.4	1340.3	1338.4	1336.4	1334.5	1332.5
175°	1342.6	1344.2	1345.7	1345.6	1343.8	1342.1	1340.3	1338.5
177.5°	1344.7	1346.2	1347.6	1347.4	1345.6	1343.9	1342.1	1340.3
180°	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5

(END OF REPORT)