

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331989

Luminaire Tested: **S123DIP-S775D1025U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331989
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6693.2 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	47	47	47														
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40	40	40	40	40	40	40														
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33	33	33	33	33	33	33														
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28	28	28	28	28	28	28														
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24	24	24	24														
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21	21	21	21	21	21	21														
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18	18	18	18	18	18	18														
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16	16	16	16	16	16	16														
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15	15	15	15	15	15	15														
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13	13	13	13														
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12	12	12	12														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	1.7
10°-20°	323.9	4.8
20°-30°	478.4	7.1
30°-40°	558.9	8.4
40°-50°	561.9	8.4
50°-60°	493.6	7.4
60°-70°	367.7	5.5
70°-80°	209.5	3.1
80°-90°	63.9	1.0
90°-100°	82.8	1.2
100°-110°	247.8	3.7
110°-120°	421.4	6.3
120°-130°	554.3	8.3
130°-140°	623.0	9.3
140°-150°	612.4	9.1
150°-160°	515.6	7.7
160°-170°	343.2	5.1
170°-180°	120.2	1.8
0°-30°	917.1	13.7
0°-40°	1475.9	22.1
0°-60°	2531.4	37.8
0°-90°	3172.5	47.4
90°-120°	752.0	11.2
90°-150°	2541.8	38.0
90°-180°	3521.0	52.6
0°-180°	6693.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	1	11	24	28	30	7
95°	59	66	74	78	78	66
105°	225	227	236	236	238	241
115°	424	427	425	426	425	420
125°	621	624	622	618	614	553
135°	806	811	810	807	805	621
145°	977	979	982	981	977	610
155°	1119	1119	1120	1123	1117	515
165°	1219	1216	1216	1221	1215	344
175°	1268	1264	1264	1269	1263	120
180°	1271	1271	1271	1271	1271	



TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	22.0	21.9	21.7	21.6	21.5	21.7	22.0	22.4	22.8	23.2	23.2
90°	1.0	3.2	5.4	7.7	9.9	12.4	15.3	18.2	21.1	24.0	24.8
92.5°	24.2	25.7	27.2	28.7	30.2	31.8	33.4	35.0	36.7	38.3	39.0
95°	58.9	60.4	62.0	63.6	65.1	66.8	68.5	70.3	72.1	73.9	74.8
97.5°	104.6	105.8	106.9	108.1	109.2	110.4	111.7	113.0	114.3	115.6	116.6
100°	135.8	137.1	138.4	139.7	141.1	142.3	143.4	144.5	145.6	146.7	147.4
102.5°	171.7	172.5	173.3	174.1	174.9	176.0	177.5	178.9	180.4	181.9	182.5
105°	224.6	225.0	225.5	225.9	226.4	227.6	229.6	231.6	233.6	235.6	235.6
107.5°	286.1	286.4	286.6	286.9	287.2	287.7	288.5	289.3	290.1	290.9	291.6
110°	324.4	324.9	325.3	325.7	326.2	326.6	327.1	327.5	328.0	328.4	329.3



TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	364.3	364.6	364.9	365.1	365.4	365.6	365.7	365.8	365.9	365.9	367.0
115°	424.2	424.9	425.6	426.2	426.9	427.0	426.6	426.1	425.7	425.2	425.5
117.5°	484.5	485.0	485.4	485.9	486.3	486.2	485.7	485.1	484.5	483.9	483.9
120°	522.1	523.4	524.7	526.1	527.4	527.5	526.4	525.3	524.2	523.1	522.8
122.5°	561.2	562.2	563.1	564.1	565.1	565.3	564.7	564.1	563.6	563.0	562.4
125°	620.9	621.6	622.2	622.9	623.5	623.7	623.2	622.8	622.3	621.9	621.0
127.5°	676.0	677.4	678.8	680.2	681.7	682.1	681.6	681.2	680.7	680.2	678.9
130°	712.7	714.5	716.3	718.0	719.8	720.4	719.7	719.0	718.4	717.7	716.8
132.5°	749.5	751.2	753.0	754.8	756.6	757.2	756.7	756.2	755.7	755.2	754.2
135°	805.6	806.9	808.2	809.5	810.9	811.4	811.2	811.0	810.8	810.5	809.7
137.5°	857.5	858.6	859.7	860.8	861.9	862.7	863.3	863.9	864.5	865.0	864.1
140°	893.4	894.5	895.6	896.7	897.8	898.5	898.7	898.9	899.2	899.4	899.2
142.5°	926.1	927.2	928.4	929.5	930.6	931.3	931.7	932.1	932.5	932.9	932.7
145°	977.2	977.7	978.1	978.6	979.0	979.6	980.2	980.9	981.6	982.2	982.0
147.5°	1022.0	1022.8	1023.6	1024.4	1025.2	1025.9	1026.5	1027.1	1027.7	1028.4	1028.4
150°	1053.1	1053.6	1054.0	1054.4	1054.9	1055.3	1055.8	1056.2	1056.7	1057.1	1057.1
152.5°	1078.7	1079.3	1079.9	1080.5	1081.1	1081.6	1081.9	1082.1	1082.4	1082.7	1083.0
155°	1119.0	1119.0	1119.0	1119.0	1119.0	1119.1	1119.3	1119.5	1119.8	1120.0	1120.9
157.5°	1153.3	1153.1	1152.8	1152.5	1152.3	1152.2	1152.4	1152.6	1152.8	1152.9	1153.9
160°	1174.9	1174.4	1174.0	1173.6	1173.1	1172.9	1172.9	1172.9	1172.9	1172.9	1174.0
162.5°	1194.1	1193.4	1192.8	1192.2	1191.6	1191.4	1191.5	1191.7	1191.9	1192.1	1193.2
165°	1218.8	1218.1	1217.5	1216.8	1216.2	1215.8	1215.8	1215.8	1215.8	1215.8	1217.1
167.5°	1238.6	1237.7	1236.8	1235.9	1235.0	1234.7	1234.9	1235.0	1235.2	1235.4	1236.8
170°	1249.8	1248.9	1248.0	1247.1	1246.2	1245.8	1245.8	1245.8	1245.8	1245.8	1247.3
172.5°	1258.5	1257.7	1256.8	1255.9	1255.0	1254.5	1254.5	1254.5	1254.5	1254.5	1255.9
175°	1267.7	1266.8	1265.9	1265.1	1264.2	1263.7	1263.7	1263.7	1263.7	1263.7	1265.1
177.5°	1271.5	1270.8	1270.1	1269.4	1268.7	1268.3	1268.3	1268.3	1268.3	1268.3	1269.4
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7



TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	23.2	23.2	23.2	23.2	23.3	23.4	23.5	23.6
90°	25.7	26.6	27.5	28.2	28.6	29.1	29.5	29.9
92.5°	39.8	40.5	41.2	41.4	41.1	40.9	40.6	40.3
95°	75.6	76.5	77.4	77.9	77.9	77.9	77.9	77.9
97.5°	117.6	118.7	119.7	120.1	120.1	120.0	119.9	119.8
100°	148.1	148.7	149.4	150.0	150.4	150.8	151.3	151.7
102.5°	183.2	183.9	184.5	184.8	184.7	184.6	184.6	184.5
105°	235.6	235.6	235.6	235.8	236.2	236.7	237.1	237.6
107.5°	292.3	293.0	293.7	293.9	293.7	293.4	293.1	292.9
110°	330.2	331.1	332.0	332.2	331.7	331.3	330.9	330.4



TEST NUMBER: P331989

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	368.1	369.1	370.2	370.7	370.6	370.5	370.4	370.3
115°	425.7	425.9	426.1	426.1	425.9	425.7	425.5	425.2
117.5°	483.8	483.8	483.8	483.4	482.8	482.2	481.6	480.9
120°	522.6	522.4	522.2	521.8	521.4	521.0	520.5	520.1
122.5°	561.8	561.3	560.7	560.1	559.5	558.8	558.2	557.6
125°	620.1	619.2	618.3	617.4	616.6	615.7	614.8	613.9
127.5°	677.7	676.5	675.2	674.1	673.1	672.0	671.0	670.0
130°	715.9	715.0	714.2	712.9	711.4	709.8	708.3	706.7
132.5°	753.1	752.1	751.0	749.9	748.7	747.5	746.3	745.1
135°	808.8	807.9	807.0	806.3	805.9	805.4	805.0	804.6
137.5°	863.2	862.3	861.3	860.4	859.6	858.7	857.9	857.1
140°	898.9	898.7	898.5	897.6	896.1	894.5	893.0	891.4
142.5°	932.5	932.3	932.0	931.3	930.1	928.9	927.7	926.5
145°	981.8	981.6	981.3	980.8	979.9	979.0	978.1	977.2
147.5°	1028.4	1028.4	1028.4	1027.7	1026.4	1025.0	1023.7	1022.4
150°	1057.1	1057.1	1057.1	1056.4	1055.1	1053.8	1052.4	1051.1
152.5°	1083.4	1083.7	1084.1	1083.7	1082.5	1081.4	1080.2	1079.1
155°	1121.8	1122.7	1123.5	1123.2	1121.7	1120.1	1118.5	1117.0
157.5°	1154.8	1155.7	1156.7	1156.5	1155.3	1154.0	1152.8	1151.5
160°	1175.1	1176.2	1177.3	1177.4	1176.6	1175.7	1174.8	1173.9
162.5°	1194.3	1195.4	1196.5	1196.3	1194.9	1193.5	1192.1	1190.7
165°	1218.5	1219.8	1221.1	1221.0	1219.5	1217.9	1216.4	1214.8
167.5°	1238.1	1239.5	1240.9	1240.9	1239.5	1238.1	1236.8	1235.4
170°	1248.9	1250.4	1252.0	1252.0	1250.4	1248.9	1247.3	1245.8
172.5°	1257.3	1258.7	1260.0	1260.0	1258.4	1256.9	1255.3	1253.7
175°	1266.4	1267.7	1269.1	1268.9	1267.4	1265.8	1264.3	1262.7
177.5°	1270.5	1271.5	1272.6	1272.5	1271.3	1270.0	1268.8	1267.5
180°	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7	1270.7

(END OF REPORT)