

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331893-840

Luminaire Tested: **S123DIP-S340D1025U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331893-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5024.9 lumens
Efficiency: N/A
Efficacy: 134.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5226	5226	5226	5226
5°	6232	5249	4652	5249
10°	7802	5223	4203	5223
15°	9569	5180	3911	5180
20°	11399	5116	3725	5116
25°	12105	5035	3682	5035
30°	10376	4977	3701	4977
35°	7215	4893	3741	4893
40°	5435	4796	3729	4796
45°	4512	4652	3682	4652
50°	4042	4357	3647	4357
55°	3780	4040	3603	4040
60°	3546	3707	3565	3707
65°	3331	3380	3451	3380
70°	3125	3006	3286	3006
75°	2799	2633	3015	2633
80°	2448	2157	2597	2157
85°	1927	1568	1741	1568



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.0
10°-20°	153.4	3.1
20°-30°	257.4	5.1
30°-40°	291.5	5.8
40°-50°	261.4	5.2
50°-60°	210.9	4.2
60°-70°	147.0	2.9
70°-80°	77.3	1.5
80°-90°	22.7	0.5
90°-100°	83.6	1.7
100°-110°	250.2	5.0
110°-120°	425.6	8.5
120°-130°	559.8	11.1
130°-140°	629.2	12.5
140°-150°	618.5	12.3
150°-160°	520.7	10.4
160°-170°	346.6	6.9
170°-180°	121.4	2.4
0°-30°	458.6	9.1
0°-40°	750.1	14.9
0°-60°	1222.4	24.3
0°-90°	1469.4	29.2
90°-120°	759.4	15.1
90°-150°	2566.9	51.1
90°-180°	3555.0	70.7
0°-180°	5024.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	486	486	486	486	486	
5°	577	486	430	486	577	60
15°	859	465	351	465	859	248
25°	1019	424	310	424	1019	447
35°	549	372	285	372	549	357
45°	296	306	242	306	296	235
55°	201	215	192	215	201	181
65°	131	133	136	133	131	130
75°	67	63	72	63	67	72
85°	16	13	14	13	16	19
90°	30	1	30	1	30	15
95°	79	60	79	60	79	81
105°	240	227	240	227	240	255
115°	429	428	429	428	429	425
125°	620	627	620	627	620	554
135°	812	814	812	814	812	625
145°	987	987	987	987	987	616
155°	1128	1130	1128	1130	1128	519
165°	1227	1231	1227	1231	1227	346
175°	1275	1280	1275	1280	1275	121
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	515.3	514.9	514.0	514.7	513.2	511.2	511.0	509.1	503.6	503.3	501.8
5°	576.8	575.0	574.7	574.5	571.2	566.7	558.3	557.5	546.2	540.7	533.8
7.5°	656.6	657.5	654.1	651.2	641.1	634.4	625.3	613.7	599.9	585.7	576.4
10°	713.8	721.5	712.0	705.3	699.2	687.7	674.3	657.5	640.9	621.4	606.5
12.5°	775.2	778.9	777.0	770.8	761.3	743.8	720.0	701.6	686.2	653.7	640.6
15°	858.7	873.0	863.8	842.7	843.1	826.5	795.5	761.3	743.2	714.7	675.9
17.5°	947.8	949.5	945.6	928.0	916.3	893.2	864.5	831.9	795.2	760.7	719.5
20°	995.1	993.7	985.5	976.3	956.1	938.3	907.0	870.5	823.4	789.5	744.6
22.5°	1021.5	1019.2	1015.2	1007.5	990.8	971.6	943.4	903.6	858.8	812.1	760.2
25°	1019.2	1022.2	1022.7	1020.6	1014.7	1003.2	981.1	949.3	904.6	844.6	790.5
27.5°	927.0	931.3	943.8	955.0	967.5	980.2	978.5	962.7	929.6	877.8	811.6
30°	834.8	825.3	848.6	878.0	898.0	933.3	953.0	954.2	935.6	891.2	826.7
32.5°	706.7	717.1	727.4	763.6	807.3	846.9	886.3	917.9	921.5	891.9	835.6
35°	549.1	562.1	580.9	599.7	646.7	687.2	756.4	816.6	864.5	870.9	836.4
37.5°	442.5	448.9	460.8	479.7	510.4	558.5	611.9	688.0	757.6	809.3	811.5
40°	386.8	388.7	402.0	416.4	441.3	480.9	529.1	596.4	679.6	751.9	782.0
42.5°	345.0	349.1	354.9	368.6	388.5	418.2	463.0	518.7	595.0	678.1	737.0
45°	296.4	301.1	304.7	313.9	328.0	348.0	379.2	430.1	488.2	574.0	653.3
47.5°	264.4	264.7	267.3	274.3	283.9	298.9	321.0	353.7	407.0	476.7	558.1
50°	241.4	245.1	246.1	251.5	259.0	270.0	288.4	316.2	359.9	421.1	495.9
52.5°	225.2	226.3	228.9	232.9	239.4	248.0	264.0	285.7	320.0	372.2	441.0
55°	201.4	201.4	204.0	207.0	210.8	218.5	229.1	245.1	271.2	311.7	368.7
57.5°	179.4	180.6	182.4	183.3	186.5	191.7	200.5	212.7	232.1	263.3	308.5
60°	164.7	166.8	166.5	168.4	171.3	175.3	182.8	192.7	210.1	235.0	273.2
62.5°	151.9	151.8	151.7	154.0	156.7	160.6	165.5	174.0	188.8	211.0	243.4
65°	130.8	130.4	132.0	133.4	134.3	137.1	140.9	148.5	158.3	174.8	200.0
67.5°	112.1	110.7	111.6	112.1	113.7	115.9	119.5	124.1	131.9	145.1	164.1
70°	99.3	98.1	97.9	98.4	99.8	101.4	104.0	108.5	115.7	126.3	140.2
72.5°	86.1	85.3	85.2	86.3	86.9	88.1	89.9	93.9	99.8	107.8	120.7
75°	67.3	67.3	67.3	67.6	68.3	69.2	70.6	72.7	77.2	82.8	91.5
77.5°	50.4	50.4	50.1	50.1	51.1	51.5	51.8	53.8	56.4	60.1	66.4
80°	39.5	38.4	38.8	39.5	40.0	40.2	40.9	41.4	43.5	45.6	50.1
82.5°	29.4	28.4	28.5	29.6	29.7	29.9	30.6	31.2	32.0	33.9	36.4
85°	15.6	15.6	15.8	15.8	16.0	15.8	16.5	16.7	16.7	17.9	19.3
87.5°	11.7	11.2	11.3	11.4	11.1	11.2	11.2	11.2	11.2	11.2	10.8
90°	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0	25.0	24.2	21.3
92.5°	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2	39.4	38.7	37.1
95°	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3	75.5	74.6	72.8
97.5°	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8	117.8	116.7	115.4
100°	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6	148.9	148.1	147.0
102.5°	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0	184.3	183.7	182.2
105°	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9	237.9	237.9	235.9
107.5°	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2	294.5	293.8	293.0
110°	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5	332.5	331.6	331.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7	370.6	369.5	369.5
115°	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4	429.9
117.5°	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6	488.7	488.7	489.3
120°	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8	528.0	528.3	529.4
122.5°	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3	567.9	568.6	569.2
125°	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2	627.1	628.0	628.4
127.5°	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4	685.6	686.9	687.4
130°	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0	723.9	724.8	725.5
132.5°	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5	761.6	762.7	763.2
135°	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8	817.7	818.5	818.8
137.5°	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7	872.6	873.5	873.0
140°	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7	941.9	942.1	941.7
145°	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5	991.7	991.9	991.3
147.5°	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5	1067.5	1067.5	1067.1
152.5°	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1	1093.7	1093.4	1093.1
155°	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9	1132.0	1131.0	1130.8
157.5°	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2	1165.3	1164.3	1164.2
160°	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7	1185.6	1184.5	1184.5
162.5°	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1	1205.0	1203.9	1203.7
165°	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5	1229.1	1227.8	1227.8
167.5°	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6	1247.4
170°	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1	1258.1
172.5°	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7	1268.3	1266.9	1266.9
175°	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9	1277.6	1276.2	1276.2
177.5°	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0	1281.9	1280.8	1280.8
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	500.6	499.2	497.7	495.0	492.7	489.6	488.6	487.5	484.0	481.1	478.8
5°	531.2	525.5	517.4	509.8	503.7	495.4	490.8	485.8	478.8	472.4	467.3
7.5°	563.2	552.1	539.3	525.5	512.6	500.2	490.2	481.2	471.3	462.0	454.6
10°	588.7	572.6	554.7	535.4	519.0	503.0	489.6	477.9	465.1	454.0	444.8
12.5°	617.6	593.9	569.3	545.8	526.3	504.1	487.9	472.9	458.5	445.2	434.9
15°	651.9	621.8	592.6	560.4	530.8	503.0	483.7	464.8	448.2	434.5	421.3
17.5°	683.2	649.0	610.6	571.4	535.6	502.7	475.7	454.4	433.5	416.9	403.7
20°	700.8	662.1	618.5	577.8	538.3	501.6	471.9	446.6	423.9	406.3	391.5
22.5°	716.1	670.7	625.6	582.1	538.1	498.6	464.9	438.8	414.3	397.1	381.3
25°	732.0	677.5	632.4	581.4	532.2	491.2	453.6	423.9	399.5	379.2	363.0
27.5°	745.5	677.1	623.5	568.6	522.8	481.8	441.6	409.8	383.8	361.8	345.4
30°	754.5	678.0	614.3	560.0	513.8	471.5	432.4	400.4	373.1	350.8	335.3
32.5°	760.1	677.4	605.8	547.9	499.5	462.0	422.4	389.3	361.2	339.3	324.4
35°	763.5	673.3	591.2	523.0	476.5	439.9	406.8	372.4	343.1	322.6	305.6
37.5°	756.8	664.6	574.3	499.0	448.0	412.1	384.2	355.0	326.8	304.3	289.6
40°	746.5	658.9	561.1	482.0	428.4	393.8	370.1	341.3	313.6	292.2	278.5
42.5°	726.7	647.5	546.6	463.2	408.1	373.5	351.6	327.6	301.3	281.2	267.6
45°	678.5	622.5	524.8	435.0	378.1	342.3	323.1	305.6	281.9	262.4	250.5
47.5°	611.6	584.9	493.4	405.3	346.7	312.4	292.3	278.3	260.9	245.1	233.9
50°	565.1	554.0	472.2	384.9	325.9	292.2	272.9	260.2	247.7	232.0	221.7
52.5°	511.5	518.3	447.4	363.9	304.6	271.5	253.4	243.3	232.0	218.9	210.0
55°	436.0	460.6	404.5	328.4	272.9	241.4	224.2	215.3	208.6	199.0	191.3
57.5°	365.3	396.7	358.0	292.0	241.8	214.6	198.1	188.4	184.2	179.2	173.0
60°	323.3	354.3	324.9	267.5	221.0	195.0	180.5	172.2	167.9	164.4	159.3
62.5°	285.8	317.2	292.6	242.7	200.4	176.4	163.7	155.6	152.4	150.6	146.1
65°	234.3	261.4	244.9	204.0	171.1	149.9	138.4	132.7	129.7	129.0	126.1
67.5°	190.7	211.3	199.3	169.2	143.3	125.0	115.2	110.4	108.1	107.8	105.6
70°	162.1	181.4	172.2	144.9	122.6	108.3	99.8	95.5	94.1	93.9	92.7
72.5°	139.9	153.3	146.0	123.3	106.0	93.0	86.7	82.3	80.8	81.1	80.3
75°	103.5	113.6	109.4	93.6	79.8	71.3	66.1	63.3	61.9	62.6	61.6
77.5°	74.5	80.9	77.1	66.1	57.6	51.5	47.7	45.9	44.6	44.6	44.2
80°	56.2	60.0	57.9	51.3	44.2	39.1	36.0	34.8	34.1	33.8	33.6
82.5°	40.1	43.2	40.7	36.3	31.4	28.3	26.6	25.0	24.5	24.6	24.4
85°	20.2	21.4	20.5	17.7	15.8	14.3	13.4	12.7	12.2	12.4	12.0
87.5°	10.6	10.2	9.1	7.9	7.0	6.0	5.6	4.7	4.7	5.3	5.5
90°	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4	26.0	27.5	29.0
95°	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5	61.0	62.6	64.2
97.5°	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6	106.8	108.0	109.2
100°	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1	138.5	139.8	141.1
102.5°	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4	174.2	175.0	175.8
105°	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8	227.2	227.7	228.1
107.5°	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9	289.2	289.4	289.7
110°	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6	328.1	328.5	328.9



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9	368.2	368.5	368.7
115°	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4	429.1	429.8	430.4
117.5°	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3	489.8	490.2	490.7
120°	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3	528.6	529.9	531.3
122.5°	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7	567.7	568.7	569.7
125°	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0	627.7	628.3	629.0
127.5°	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7	684.1	685.5	686.9
130°	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7	721.5	723.4	725.1
132.5°	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9	758.6	760.4	762.2
135°	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5	814.9	816.2	817.5
137.5°	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0	867.1	868.2	869.3
140°	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2	903.3	904.4	905.5
142.5°	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2	936.3	937.6	938.7
145°	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8	987.3	987.7	988.3
147.5°	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1	1032.9	1033.7	1034.5
150°	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5	1064.0	1064.4	1064.8
152.5°	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3	1089.9	1090.6	1091.2
155°	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7	1164.5	1164.2	1163.9
160°	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5	1186.0	1185.6	1185.2
162.5°	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9	1205.2	1204.6	1204.0
165°	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8	1230.1	1229.5	1228.8
167.5°	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8	1249.9	1249.0	1248.1
170°	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1	1261.2	1260.3	1259.4
172.5°	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9	1270.1	1269.2	1268.3
175°	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2	1279.3	1278.4	1277.6
177.5°	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0	1283.3	1282.6	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	477.5	476.2	474.3	471.5	469.2	465.6	465.6	466.2	466.2	466.1	465.6
5°	463.0	459.5	455.2	450.3	445.1	439.9	439.0	437.1	435.8	434.7	433.6
7.5°	447.7	441.4	435.3	428.4	422.0	416.9	413.2	410.2	408.3	406.2	404.7
10°	437.4	429.6	422.3	415.1	407.0	400.6	396.7	393.8	391.7	389.8	388.9
12.5°	425.2	416.3	408.2	401.2	392.5	386.0	382.1	380.8	378.4	374.4	372.3
15°	407.3	399.0	389.4	378.8	374.6	366.6	362.0	359.9	358.5	355.5	354.6
17.5°	391.9	381.2	370.3	362.4	354.6	348.1	345.6	343.0	341.1	338.6	337.8
20°	379.7	370.1	360.2	351.7	343.5	336.4	334.3	332.4	330.5	329.4	328.4
22.5°	367.3	357.7	349.4	341.5	332.8	328.1	325.9	323.8	322.4	321.6	320.7
25°	349.8	341.3	332.1	325.2	318.1	315.0	313.6	312.5	311.4	310.3	310.0
27.5°	334.3	325.0	317.6	310.9	305.9	303.4	301.9	301.4	301.6	302.1	302.4
30°	322.6	314.1	308.0	302.4	297.6	295.3	295.0	295.0	296.0	296.2	296.7
32.5°	311.8	304.9	298.7	293.3	289.7	288.1	289.0	289.0	289.7	290.3	291.2
35°	296.2	290.0	285.4	280.6	277.6	278.3	278.8	279.2	280.4	281.9	282.8
37.5°	281.2	276.0	271.0	267.4	266.0	267.2	268.4	269.3	270.7	271.9	272.8
40°	270.5	266.5	261.9	258.5	259.0	259.7	260.6	261.9	263.1	263.8	264.7
42.5°	260.5	256.4	252.8	250.0	250.7	251.7	252.2	252.8	254.2	255.5	256.0
45°	245.4	242.1	238.8	237.1	237.6	238.1	238.5	239.2	240.4	241.4	241.7
47.5°	228.3	226.0	223.8	222.2	223.0	222.8	223.4	224.9	225.2	225.8	227.1
50°	217.4	215.3	212.7	212.2	212.2	212.2	212.5	214.3	214.3	215.3	216.2
52.5°	205.3	204.0	202.4	201.5	201.1	201.1	202.1	203.0	203.4	204.7	205.7
55°	187.5	186.1	184.7	184.0	183.5	184.0	185.8	186.3	187.5	188.2	188.9
57.5°	169.0	167.8	166.7	166.3	166.2	166.8	167.8	169.3	169.6	171.8	172.8
60°	156.7	155.0	154.1	154.1	153.6	155.7	155.3	157.6	158.1	159.6	161.2
62.5°	144.1	141.9	141.5	141.5	142.2	142.8	143.4	144.4	145.7	147.4	148.8
65°	123.7	122.6	124.2	124.0	123.5	124.9	124.9	126.1	127.5	129.2	131.8
67.5°	104.5	103.9	104.0	104.0	104.7	105.5	106.2	107.2	109.0	110.7	112.4
70°	91.5	92.2	91.1	92.0	92.7	92.9	93.4	94.8	96.6	97.9	99.8
72.5°	78.9	78.9	79.0	79.4	80.1	80.5	81.0	82.6	84.6	85.6	87.2
75°	60.7	60.5	61.2	61.2	62.3	62.8	63.3	64.0	65.8	67.3	68.5
77.5°	44.3	44.6	44.4	45.2	44.9	45.0	46.5	47.2	47.4	50.2	50.8
80°	33.4	33.8	34.1	34.3	34.5	34.1	35.7	36.5	36.5	38.1	39.3
82.5°	24.0	24.2	24.8	25.1	25.1	25.7	25.8	26.3	26.9	27.6	29.1
85°	12.0	12.7	12.9	12.7	12.9	12.4	13.1	13.4	13.6	13.6	13.6
87.5°	5.8	6.5	6.9	7.7	8.0	8.8	9.0	8.8	9.0	9.7	9.1
90°	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0	26.9	27.8	28.5
92.5°	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2	40.9	41.6	41.8
95°	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3	77.3	78.2	78.7
97.5°	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8	119.9	120.9	121.3
100°	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6	150.2	150.9	151.5
102.5°	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0	185.7	186.3	186.6
105°	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9	237.9	237.9	238.1
107.5°	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2	295.9	296.6	296.8
110°	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5	334.4	335.3	335.5



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7	372.7	373.9	374.4
115°	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9	430.1	430.3	430.3
117.5°	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6	488.6	488.6	488.2
120°	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8	527.6	527.4	526.9
122.5°	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3	566.8	566.2	565.6
125°	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2	625.3	624.4	623.5
127.5°	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4	683.2	681.9	680.8
130°	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0	722.1	721.2	719.9
132.5°	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5	759.5	758.4	757.3
135°	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8	815.9	815.0	814.3
137.5°	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7	870.8	869.8	868.9
140°	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8	907.6	907.4	906.5
142.5°	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7	941.5	941.2	940.5
145°	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5	991.3	991.0	990.5
147.5°	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5	1067.5	1067.5	1066.8
152.5°	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1	1094.4	1094.8	1094.4
155°	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9	1133.8	1134.6	1134.3
157.5°	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2	1167.1	1168.1	1167.9
160°	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7	1187.8	1188.9	1189.0
162.5°	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1	1207.2	1208.3	1208.1
165°	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5	1231.8	1233.1	1233.0
167.5°	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1
170°	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4
172.5°	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7	1271.1	1272.4	1272.4
175°	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9	1280.2	1281.6	1281.4
177.5°	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0	1284.0	1285.2	1285.1
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	464.3	464.1	465.4	464.5	465.4	464.1	464.3	465.6	466.1	466.2	466.2
5°	432.2	432.9	430.5	430.5	430.5	432.9	432.2	433.6	434.7	435.8	437.1
7.5°	403.5	402.5	402.6	401.3	402.6	402.5	403.5	404.7	406.2	408.3	410.2
10°	386.1	384.7	384.2	384.5	384.2	384.7	386.1	388.9	389.8	391.7	393.8
12.5°	371.5	371.3	368.2	368.2	368.2	371.3	371.5	372.3	374.4	378.4	380.8
15°	354.6	350.1	349.6	351.0	349.6	350.1	354.6	354.6	355.5	358.5	359.9
17.5°	337.5	335.1	335.3	334.6	335.3	335.1	337.5	337.8	338.6	341.1	343.0
20°	328.4	327.0	326.8	325.2	326.8	327.0	328.4	328.4	329.4	330.5	332.4
22.5°	320.1	319.7	319.8	318.0	319.8	319.7	320.1	320.7	321.6	322.4	323.8
25°	309.8	311.0	310.0	310.0	310.0	311.0	309.8	310.0	310.3	311.4	312.5
27.5°	302.9	302.9	302.4	302.4	302.4	302.9	302.9	302.4	302.1	301.6	301.4
30°	297.6	297.4	297.8	297.8	297.8	297.4	297.6	296.7	296.2	296.0	295.0
32.5°	292.4	292.7	292.8	293.0	292.8	292.7	292.4	291.2	290.3	289.7	289.0
35°	284.2	284.5	285.2	284.7	285.2	284.5	284.2	282.8	281.9	280.4	279.2
37.5°	273.2	274.3	274.1	274.4	274.1	274.3	273.2	272.8	271.9	270.7	269.3
40°	264.9	265.6	265.4	265.4	265.4	265.6	264.9	264.7	263.8	263.1	261.9
42.5°	256.4	256.9	256.3	256.0	256.3	256.9	256.4	256.0	255.5	254.2	252.8
45°	242.6	242.1	242.8	241.9	242.8	242.1	242.6	241.7	241.4	240.4	239.2
47.5°	227.0	227.5	227.7	228.4	227.7	227.5	227.0	227.1	225.8	225.2	224.9
50°	216.7	218.1	218.1	217.8	218.1	218.1	216.7	216.2	215.3	214.3	214.3
52.5°	206.5	207.1	208.1	208.0	208.1	207.1	206.5	205.7	204.7	203.4	203.0
55°	190.8	191.3	191.8	192.0	191.8	191.3	190.8	188.9	188.2	187.5	186.3
57.5°	174.5	174.3	175.4	175.8	175.4	174.3	174.5	172.8	171.8	169.6	169.3
60°	163.0	163.0	164.9	165.6	164.9	163.0	163.0	161.2	159.6	158.1	157.6
62.5°	150.8	151.6	153.4	152.5	153.4	151.6	150.8	148.8	147.4	145.7	144.4
65°	132.9	134.8	134.6	135.5	134.6	134.8	132.9	131.8	129.2	127.5	126.1
67.5°	114.2	115.4	117.1	117.2	117.1	115.4	114.2	112.4	110.7	109.0	107.2
70°	101.6	102.8	103.7	104.4	103.7	102.8	101.6	99.8	97.9	96.6	94.8
72.5°	89.4	90.0	92.3	91.3	92.3	90.0	89.4	87.2	85.6	84.6	82.6
75°	70.1	71.8	73.2	72.5	73.2	71.8	70.1	68.5	67.3	65.8	64.0
77.5°	51.8	53.5	54.1	53.5	54.1	53.5	51.8	50.8	50.2	47.4	47.2
80°	40.9	40.7	42.1	41.9	42.1	40.7	40.9	39.3	38.1	36.5	36.5
82.5°	30.0	29.8	30.4	30.6	30.4	29.8	30.0	29.1	27.6	26.9	26.3
85°	14.5	15.2	14.3	14.1	14.3	15.2	14.5	13.6	13.6	13.6	13.4
87.5°	9.2	9.3	9.2	9.1	9.2	9.3	9.2	9.1	9.7	9.0	8.8
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0
92.5°	41.5	41.3	41.0	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2
95°	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3
97.5°	121.3	121.2	121.1	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8
100°	151.9	152.3	152.8	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6
102.5°	186.5	186.4	186.4	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0
105°	238.5	239.0	239.4	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9
107.5°	296.6	296.3	296.0	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2
110°	335.0	334.6	334.2	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	374.3	374.2	374.1	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7
115°	430.1	429.9	429.7	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9
117.5°	487.6	487.0	486.4	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6
120°	526.5	526.1	525.6	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8
122.5°	565.0	564.3	563.7	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3
125°	622.7	621.8	620.9	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2
127.5°	679.7	678.6	677.6	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4
130°	718.4	716.8	715.3	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0
132.5°	756.1	754.9	753.7	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5
135°	813.9	813.3	812.9	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8
137.5°	868.1	867.2	866.4	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7
140°	904.9	903.3	901.8	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8
142.5°	939.3	938.1	936.9	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7
145°	989.6	988.7	987.7	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5
147.5°	1036.5	1035.1	1033.8	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5
150°	1065.5	1064.2	1062.8	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5
152.5°	1093.2	1092.1	1090.9	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1
155°	1132.8	1131.1	1129.5	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9
157.5°	1166.7	1165.4	1164.2	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2
160°	1188.2	1187.3	1186.4	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7
162.5°	1206.7	1205.3	1203.9	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1
165°	1231.5	1229.9	1228.4	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5
167.5°	1251.7	1250.3	1249.0	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3
170°	1262.7	1261.2	1259.6	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2
172.5°	1270.8	1269.3	1267.7	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7
175°	1279.9	1278.3	1276.8	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9
177.5°	1283.8	1282.5	1281.3	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	465.6	465.6	469.2	471.5	474.3	476.2	477.5	478.8	481.1	484.0	487.5
5°	439.0	439.9	445.1	450.3	455.2	459.5	463.0	467.3	472.4	478.8	485.8
7.5°	413.2	416.9	422.0	428.4	435.3	441.4	447.7	454.6	462.0	471.3	481.2
10°	396.7	400.6	407.0	415.1	422.3	429.6	437.4	444.8	454.0	465.1	477.9
12.5°	382.1	386.0	392.5	401.2	408.2	416.3	425.2	434.9	445.2	458.5	472.9
15°	362.0	366.6	374.6	378.8	389.4	399.0	407.3	421.3	434.5	448.2	464.8
17.5°	345.6	348.1	354.6	362.4	370.3	381.2	391.9	403.7	416.9	433.5	454.4
20°	334.3	336.4	343.5	351.7	360.2	370.1	379.7	391.5	406.3	423.9	446.6
22.5°	325.9	328.1	332.8	341.5	349.4	357.7	367.3	381.3	397.1	414.3	438.8
25°	313.6	315.0	318.1	325.2	332.1	341.3	349.8	363.0	379.2	399.5	423.9
27.5°	301.9	303.4	305.9	310.9	317.6	325.0	334.3	345.4	361.8	383.8	409.8
30°	295.0	295.3	297.6	302.4	308.0	314.1	322.6	335.3	350.8	373.1	400.4
32.5°	289.0	288.1	289.7	293.3	298.7	304.9	311.8	324.4	339.3	361.2	389.3
35°	278.8	278.3	277.6	280.6	285.4	290.0	296.2	305.6	322.6	343.1	372.4
37.5°	268.4	267.2	266.0	267.4	271.0	276.0	281.2	289.6	304.3	326.8	355.0
40°	260.6	259.7	259.0	258.5	261.9	266.5	270.5	278.5	292.2	313.6	341.3
42.5°	252.2	251.7	250.7	250.0	252.8	256.4	260.5	267.6	281.2	301.3	327.6
45°	238.5	238.1	237.6	237.1	238.8	242.1	245.4	250.5	262.4	281.9	305.6
47.5°	223.4	222.8	223.0	222.2	223.8	226.0	228.3	233.9	245.1	260.9	278.3
50°	212.5	212.2	212.2	212.2	212.7	215.3	217.4	221.7	232.0	247.7	260.2
52.5°	202.1	201.1	201.1	201.5	202.4	204.0	205.3	210.0	218.9	232.0	243.3
55°	185.8	184.0	183.5	184.0	184.7	186.1	187.5	191.3	199.0	208.6	215.3
57.5°	167.8	166.8	166.2	166.3	166.7	167.8	169.0	173.0	179.2	184.2	188.4
60°	155.3	155.7	153.6	154.1	154.1	155.0	156.7	159.3	164.4	167.9	172.2
62.5°	143.4	142.8	142.2	141.5	141.5	141.9	144.1	146.1	150.6	152.4	155.6
65°	124.9	124.9	123.5	124.0	124.2	122.6	123.7	126.1	129.0	129.7	132.7
67.5°	106.2	105.5	104.7	104.0	104.0	103.9	104.5	105.6	107.8	108.1	110.4
70°	93.4	92.9	92.7	92.0	91.1	92.2	91.5	92.7	93.9	94.1	95.5
72.5°	81.0	80.5	80.1	79.4	79.0	78.9	78.9	80.3	81.1	80.8	82.3
75°	63.3	62.8	62.3	61.2	61.2	60.5	60.7	61.6	62.6	61.9	63.3
77.5°	46.5	45.0	44.9	45.2	44.4	44.6	44.3	44.2	44.6	44.6	45.9
80°	35.7	34.1	34.5	34.3	34.1	33.8	33.4	33.6	33.8	34.1	34.8
82.5°	25.8	25.7	25.1	25.1	24.8	24.2	24.0	24.4	24.6	24.5	25.0
85°	13.1	12.4	12.9	12.7	12.9	12.7	12.0	12.0	12.4	12.2	12.7
87.5°	9.0	8.8	8.0	7.7	6.9	6.5	5.8	5.5	5.3	4.7	4.7
90°	25.0	24.2	21.3	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0
92.5°	39.4	38.7	37.1	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4
95°	75.5	74.6	72.8	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5
97.5°	117.8	116.7	115.4	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6
100°	148.9	148.1	147.0	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1
102.5°	184.3	183.7	182.2	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4
105°	237.9	237.9	235.9	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8
107.5°	294.5	293.8	293.0	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9
110°	332.5	331.6	331.2	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	370.6	369.5	369.5	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9
115°	429.7	429.4	429.9	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4
117.5°	488.7	488.7	489.3	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3
120°	528.0	528.3	529.4	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3
122.5°	567.9	568.6	569.2	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7
125°	627.1	628.0	628.4	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0
127.5°	685.6	686.9	687.4	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7
130°	723.9	724.8	725.5	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7
132.5°	761.6	762.7	763.2	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9
135°	817.7	818.5	818.8	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5
137.5°	872.6	873.5	873.0	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0
140°	908.1	908.3	908.1	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2
142.5°	941.9	942.1	941.7	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2
145°	991.7	991.9	991.3	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8
147.5°	1038.5	1038.5	1037.8	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1
150°	1067.5	1067.5	1067.1	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5
152.5°	1093.7	1093.4	1093.1	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3
155°	1132.0	1131.0	1130.8	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1165.3	1164.3	1164.2	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7
160°	1185.6	1184.5	1184.5	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5
162.5°	1205.0	1203.9	1203.7	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9
165°	1229.1	1227.8	1227.8	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8
167.5°	1249.0	1247.6	1247.4	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8
170°	1259.6	1258.1	1258.1	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1
172.5°	1268.3	1266.9	1266.9	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9
175°	1277.6	1276.2	1276.2	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2
177.5°	1281.9	1280.8	1280.8	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	488.6	489.6	492.7	495.0	497.7	499.2	500.6	501.8	503.3	503.6	509.1
5°	490.8	495.4	503.7	509.8	517.4	525.5	531.2	533.8	540.7	546.2	557.5
7.5°	490.2	500.2	512.6	525.5	539.3	552.1	563.2	576.4	585.7	599.9	613.7
10°	489.6	503.0	519.0	535.4	554.7	572.6	588.7	606.5	621.4	640.9	657.5
12.5°	487.9	504.1	526.3	545.8	569.3	593.9	617.6	640.6	653.7	686.2	701.6
15°	483.7	503.0	530.8	560.4	592.6	621.8	651.9	675.9	714.7	743.2	761.3
17.5°	475.7	502.7	535.6	571.4	610.6	649.0	683.2	719.5	760.7	795.2	831.9
20°	471.9	501.6	538.3	577.8	618.5	662.1	700.8	744.6	789.5	823.4	870.5
22.5°	464.9	498.6	538.1	582.1	625.6	670.7	716.1	760.2	812.1	858.8	903.6
25°	453.6	491.2	532.2	581.4	632.4	677.5	732.0	790.5	844.6	904.6	949.3
27.5°	441.6	481.8	522.8	568.6	623.5	677.1	745.5	811.6	877.8	929.6	962.7
30°	432.4	471.5	513.8	560.0	614.3	678.0	754.5	826.7	891.2	935.6	954.2
32.5°	422.4	462.0	499.5	547.9	605.8	677.4	760.1	835.6	891.9	921.5	917.9
35°	406.8	439.9	476.5	523.0	591.2	673.3	763.5	836.4	870.9	864.5	816.6
37.5°	384.2	412.1	448.0	499.0	574.3	664.6	756.8	811.5	809.3	757.6	688.0
40°	370.1	393.8	428.4	482.0	561.1	658.9	746.5	782.0	751.9	679.6	596.4
42.5°	351.6	373.5	408.1	463.2	546.6	647.5	726.7	737.0	678.1	595.0	518.7
45°	323.1	342.3	378.1	435.0	524.8	622.5	678.5	653.3	574.0	488.2	430.1
47.5°	292.3	312.4	346.7	405.3	493.4	584.9	611.6	558.1	476.7	407.0	353.7
50°	272.9	292.2	325.9	384.9	472.2	554.0	565.1	495.9	421.1	359.9	316.2
52.5°	253.4	271.5	304.6	363.9	447.4	518.3	511.5	441.0	372.2	320.0	285.7
55°	224.2	241.4	272.9	328.4	404.5	460.6	436.0	368.7	311.7	271.2	245.1
57.5°	198.1	214.6	241.8	292.0	358.0	396.7	365.3	308.5	263.3	232.1	212.7
60°	180.5	195.0	221.0	267.5	324.9	354.3	323.3	273.2	235.0	210.1	192.7
62.5°	163.7	176.4	200.4	242.7	292.6	317.2	285.8	243.4	211.0	188.8	174.0
65°	138.4	149.9	171.1	204.0	244.9	261.4	234.3	200.0	174.8	158.3	148.5
67.5°	115.2	125.0	143.3	169.2	199.3	211.3	190.7	164.1	145.1	131.9	124.1
70°	99.8	108.3	122.6	144.9	172.2	181.4	162.1	140.2	126.3	115.7	108.5
72.5°	86.7	93.0	106.0	123.3	146.0	153.3	139.9	120.7	107.8	99.8	93.9
75°	66.1	71.3	79.8	93.6	109.4	113.6	103.5	91.5	82.8	77.2	72.7
77.5°	47.7	51.5	57.6	66.1	77.1	80.9	74.5	66.4	60.1	56.4	53.8
80°	36.0	39.1	44.2	51.3	57.9	60.0	56.2	50.1	45.6	43.5	41.4
82.5°	26.6	28.3	31.4	36.3	40.7	43.2	40.1	36.4	33.9	32.0	31.2
85°	13.4	14.3	15.8	17.7	20.5	21.4	20.2	19.3	17.9	16.7	16.7
87.5°	5.6	6.0	7.0	7.9	9.1	10.2	10.6	10.8	11.2	11.2	11.2
90°	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0
92.5°	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2
95°	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3
97.5°	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8
100°	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6
102.5°	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0
105°	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9
107.5°	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2
110°	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7
115°	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9
117.5°	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6
120°	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8
122.5°	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3
125°	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2
127.5°	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4
130°	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0
132.5°	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5
135°	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8
137.5°	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7
140°	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8
142.5°	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7
145°	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5
147.5°	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5
150°	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5
152.5°	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1
155°	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9
157.5°	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2
160°	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7
162.5°	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1
165°	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5
167.5°	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3
170°	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2
172.5°	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7
175°	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9
177.5°	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	511.0	511.2	513.2	514.7	514.0	514.9	515.3
5°	558.3	566.7	571.2	574.5	574.7	575.0	576.8
7.5°	625.3	634.4	641.1	651.2	654.1	657.5	656.6
10°	674.3	687.7	699.2	705.3	712.0	721.5	713.8
12.5°	720.0	743.8	761.3	770.8	777.0	778.9	775.2
15°	795.5	826.5	843.1	842.7	863.8	873.0	858.7
17.5°	864.5	893.2	916.3	928.0	945.6	949.5	947.8
20°	907.0	938.3	956.1	976.3	985.5	993.7	995.1
22.5°	943.4	971.6	990.8	1007.5	1015.2	1019.2	1021.5
25°	981.1	1003.2	1014.7	1020.6	1022.7	1022.2	1019.2
27.5°	978.5	980.2	967.5	955.0	943.8	931.3	927.0
30°	953.0	933.3	898.0	878.0	848.6	825.3	834.8
32.5°	886.3	846.9	807.3	763.6	727.4	717.1	706.7
35°	756.4	687.2	646.7	599.7	580.9	562.1	549.1
37.5°	611.9	558.5	510.4	479.7	460.8	448.9	442.5
40°	529.1	480.9	441.3	416.4	402.0	388.7	386.8
42.5°	463.0	418.2	388.5	368.6	354.9	349.1	345.0
45°	379.2	348.0	328.0	313.9	304.7	301.1	296.4
47.5°	321.0	298.9	283.9	274.3	267.3	264.7	264.4
50°	288.4	270.0	259.0	251.5	246.1	245.1	241.4
52.5°	264.0	248.0	239.4	232.9	228.9	226.3	225.2
55°	229.1	218.5	210.8	207.0	204.0	201.4	201.4
57.5°	200.5	191.7	186.5	183.3	182.4	180.6	179.4
60°	182.8	175.3	171.3	168.4	166.5	166.8	164.7
62.5°	165.5	160.6	156.7	154.0	151.7	151.8	151.9
65°	140.9	137.1	134.3	133.4	132.0	130.4	130.8
67.5°	119.5	115.9	113.7	112.1	111.6	110.7	112.1
70°	104.0	101.4	99.8	98.4	97.9	98.1	99.3
72.5°	89.9	88.1	86.9	86.3	85.2	85.3	86.1
75°	70.6	69.2	68.3	67.6	67.3	67.3	67.3
77.5°	51.8	51.5	51.1	50.1	50.1	50.4	50.4
80°	40.9	40.2	40.0	39.5	38.8	38.4	39.5
82.5°	30.6	29.9	29.7	29.6	28.5	28.4	29.4
85°	16.5	15.8	16.0	15.8	15.8	15.6	15.6
87.5°	11.2	11.2	11.1	11.4	11.3	11.2	11.7
90°	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	334.4	335.3	335.5	335.0	334.6	334.2	333.7



TEST NUMBER: P331893-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)