

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331898-840

Luminaire Tested: **S123DIP-S340D1025U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331898-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5565.2 lumens
Efficiency: N/A
Efficacy: 149.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	84	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	67	60	55	68	60	54	50	47	43	39	35	32	30	23	22	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	21	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	28	24	22	19	17	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	31	25	21	25	20	17	19	16	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5890	5890	5890
5°	5919	5837	5877
10°	5879	5786	5822
15°	5810	5721	5731
20°	5730	5628	5632
25°	5621	5516	5505
30°	5504	5392	5351
35°	5380	5261	5194
40°	5251	5117	5039
45°	5107	4985	4864
50°	4963	4823	4687
55°	4778	4654	4511
60°	4590	4456	4316
65°	4422	4241	4111
70°	4176	3997	3821
75°	3818	3681	3523
80°	3440	3298	3267
85°	3013	2902	2791



TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	0.9
10°-20°	145.6	2.6
20°-30°	215.0	3.9
30°-40°	251.2	4.5
40°-50°	252.5	4.5
50°-60°	221.8	4.0
60°-70°	165.2	3.0
70°-80°	94.1	1.7
80°-90°	30.8	0.6
90°-100°	49.3	0.9
100°-110°	235.1	4.2
110°-120°	564.7	10.1
120°-130°	719.1	12.9
130°-140°	768.3	13.8
140°-150°	718.5	12.9
150°-160°	579.5	10.4
160°-170°	374.0	6.7
170°-180°	128.9	2.3
0°-30°	412.1	7.4
0°-40°	663.3	11.9
0°-60°	1137.6	20.4
0°-90°	1427.8	25.7
90°-120°	849.1	15.3
90°-150°	3055.0	54.9
90°-180°	4137.0	74.3
0°-180°	5565.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	548	545	540	545	544	52
15°	521	519	513	517	514	147
25°	473	470	464	465	464	218
35°	409	406	400	398	395	256
45°	336	333	328	322	320	259
55°	255	254	248	243	240	228
65°	174	171	166	163	161	171
75°	92	90	88	86	85	98
85°	24	24	24	23	23	27
90°	1	11	24	28	30	4
95°	62	23	31	38	38	76
105°	300	306	221	52	44	318
115°	564	570	579	588	593	556
125°	794	802	806	808	810	709
135°	989	995	999	1002	999	761
145°	1141	1148	1150	1152	1152	714
155°	1257	1255	1256	1260	1255	579
165°	1326	1323	1322	1329	1322	374
175°	1357	1352	1353	1359	1352	129
180°	1357	1357	1357	1357	1357	



TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	549.2	548.8	548.5	548.2	547.8	547.1	546.2	545.3	544.4	543.5	544.3
5°	547.8	547.1	546.6	546.1	545.6	544.8	543.6	542.5	541.3	540.2	541.2
7.5°	542.4	541.8	541.3	540.8	540.3	539.4	538.3	537.0	535.8	534.6	535.5
10°	537.9	537.3	536.7	536.2	535.7	534.8	533.4	532.1	530.7	529.4	530.3
12.5°	531.8	531.4	530.9	530.5	530.1	529.2	528.0	526.6	525.3	524.1	524.8
15°	521.4	521.0	520.5	520.1	519.7	518.8	517.5	516.0	514.7	513.4	514.2
17.5°	509.2	508.7	508.2	507.6	507.1	506.1	504.7	503.4	502.0	500.7	501.2
20°	500.2	499.6	499.0	498.3	497.7	496.7	495.3	493.9	492.6	491.3	491.7
22.5°	490.0	489.4	488.8	488.2	487.6	486.6	485.1	483.8	482.4	481.1	481.4
25°	473.3	472.7	472.1	471.5	470.9	469.9	468.5	467.2	465.7	464.4	464.5
27.5°	455.6	454.9	454.3	453.7	453.1	452.1	450.7	449.2	447.8	446.3	446.4
30°	442.8	442.2	441.7	441.2	440.7	439.7	438.3	436.8	435.4	433.8	433.8
32.5°	430.0	429.3	428.6	427.9	427.3	426.3	425.2	424.0	422.9	421.8	421.2
35°	409.4	408.8	408.1	407.5	406.9	405.9	404.6	403.1	401.8	400.4	399.8
37.5°	388.3	387.5	386.7	385.9	385.2	384.1	382.6	381.2	379.9	378.5	377.8
40°	373.7	372.9	372.3	371.7	371.1	370.0	368.6	367.1	365.7	364.2	363.3
42.5°	358.9	358.2	357.5	356.8	356.1	355.0	353.6	352.0	350.6	349.1	348.3
45°	335.5	335.1	334.7	334.3	333.9	333.0	331.5	330.2	328.8	327.5	326.3
47.5°	312.3	311.6	311.0	310.4	309.8	308.9	307.6	306.3	305.1	303.8	302.6
50°	296.4	295.9	295.4	294.9	294.4	293.4	292.1	290.7	289.3	288.0	286.8
52.5°	279.8	279.5	279.1	278.8	278.4	277.5	276.1	274.7	273.3	271.8	270.8
55°	254.6	254.5	254.4	254.3	254.2	253.4	252.1	250.6	249.3	248.0	246.8
57.5°	230.5	230.1	229.7	229.4	229.0	228.3	227.2	226.1	225.1	224.0	223.0
60°	213.2	213.1	213.0	212.9	212.8	212.1	210.8	209.5	208.3	207.0	206.1
62.5°	197.7	197.4	197.2	196.9	196.6	195.9	194.6	193.4	192.1	190.9	190.0
65°	173.6	173.1	172.6	172.1	171.6	170.8	169.8	168.6	167.6	166.5	165.7
67.5°	148.1	147.6	147.2	146.7	146.3	145.6	144.9	144.1	143.3	142.5	141.8
70°	132.7	132.1	131.5	130.8	130.2	129.6	129.0	128.3	127.6	127.0	126.3
72.5°	116.5	116.0	115.6	115.1	114.6	114.1	113.4	112.7	112.0	111.3	110.6
75°	91.8	91.3	90.9	90.5	90.1	89.7	89.4	89.1	88.8	88.5	88.0
77.5°	69.8	69.6	69.4	69.2	68.9	68.6	68.3	67.9	67.5	67.1	66.8
80°	55.5	55.2	54.9	54.6	54.2	54.0	53.8	53.6	53.4	53.2	53.0
82.5°	41.6	41.5	41.5	41.4	41.3	41.3	41.2	41.2	41.2	41.1	40.9
85°	24.4	24.2	24.0	23.8	23.6	23.5	23.5	23.5	23.5	23.5	23.3
87.5°	10.0	10.2	10.4	10.6	10.8	11.1	11.6	12.1	12.6	13.1	13.2
90°	1.0	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0
92.5°	18.8	18.1	17.5	16.9	16.3	17.1	19.2	21.4	23.6	25.9	27.3
95°	61.5	52.3	43.1	33.9	24.7	21.4	23.8	26.4	28.8	31.2	32.8
97.5°	123.6	119.5	115.3	111.2	107.0	96.9	80.9	64.7	48.6	32.4	34.2
100°	170.4	174.8	179.4	183.8	188.2	173.0	138.0	103.1	68.2	33.2	35.0
102.5°	223.6	226.8	230.0	233.3	236.5	219.0	180.9	142.7	104.5	66.3	60.8
105°	300.3	302.9	305.3	307.8	310.2	301.3	281.2	261.1	241.0	220.8	181.1
107.5°	381.4	383.4	385.4	387.4	389.3	391.9	395.1	398.3	401.4	404.7	375.6
110°	435.5	437.3	439.0	440.8	442.6	444.7	447.2	449.7	452.1	454.6	447.2



TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.1	488.7	490.3	491.9	493.5	495.5	498.1	500.5	502.9	505.4	505.5
115°	563.5	564.8	566.1	567.5	568.9	570.6	572.5	574.5	576.5	578.6	580.9
117.5°	637.4	639.1	640.8	642.5	644.1	645.4	646.4	647.5	648.5	649.5	651.4
120°	683.4	685.4	687.4	689.4	691.5	692.9	693.5	694.2	694.9	695.5	697.3
122.5°	730.2	731.8	733.5	735.2	736.8	738.1	738.9	739.8	740.6	741.4	742.8
125°	794.3	796.1	797.9	799.7	801.4	802.8	803.8	804.6	805.5	806.4	806.9
127.5°	856.4	858.2	860.0	861.7	863.5	864.9	866.1	867.2	868.2	869.3	870.0
130°	895.1	896.9	898.7	900.5	902.3	903.6	904.5	905.4	906.3	907.2	908.1
132.5°	932.2	934.0	935.7	937.6	939.4	940.6	941.3	942.0	942.8	943.5	944.4
135°	988.9	990.2	991.5	992.9	994.2	995.3	996.2	997.1	998.0	999.0	999.6
137.5°	1037.2	1038.9	1040.7	1042.4	1044.0	1045.1	1045.6	1046.1	1046.6	1047.1	1048.1
140°	1069.4	1070.9	1072.2	1073.5	1074.9	1075.9	1076.5	1077.2	1077.9	1078.5	1079.4
142.5°	1099.3	1100.7	1102.0	1103.4	1104.7	1105.7	1106.4	1107.0	1107.7	1108.4	1109.1
145°	1141.0	1142.7	1144.2	1145.8	1147.3	1148.3	1148.8	1149.2	1149.6	1150.1	1150.5
147.5°	1180.3	1181.4	1182.5	1183.5	1184.5	1185.2	1185.7	1186.1	1186.6	1187.0	1187.5
150°	1204.6	1205.3	1205.9	1206.6	1207.2	1207.8	1208.2	1208.7	1209.1	1209.6	1210.0
152.5°	1226.3	1226.7	1227.0	1227.3	1227.6	1227.9	1228.1	1228.4	1228.7	1228.9	1229.7
155°	1257.0	1256.5	1256.1	1255.7	1255.2	1255.1	1255.3	1255.5	1255.8	1256.0	1257.1
157.5°	1280.7	1280.7	1280.7	1280.6	1280.6	1280.4	1280.2	1280.0	1279.8	1279.5	1280.9
160°	1295.3	1295.1	1294.8	1294.6	1294.3	1294.1	1293.9	1293.7	1293.4	1293.2	1294.6
162.5°	1309.0	1308.4	1307.8	1307.3	1306.7	1306.3	1306.1	1305.8	1305.6	1305.4	1306.9
165°	1325.5	1324.8	1324.1	1323.5	1322.8	1322.4	1322.1	1321.9	1321.7	1321.5	1323.2
167.5°	1338.4	1337.6	1336.7	1335.7	1334.8	1334.3	1334.3	1334.3	1334.3	1334.3	1336.2
170°	1345.6	1344.7	1343.9	1343.0	1342.1	1341.6	1341.6	1341.6	1341.6	1341.6	1343.4
172.5°	1350.5	1349.5	1348.4	1347.3	1346.3	1345.7	1345.9	1346.2	1346.3	1346.5	1348.3
175°	1356.8	1355.6	1354.5	1353.4	1352.3	1351.8	1352.0	1352.3	1352.5	1352.7	1354.3
177.5°	1358.4	1357.5	1356.6	1355.6	1354.8	1354.4	1354.6	1354.8	1354.9	1355.1	1356.6
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8



TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	547.2	547.2	547.2	547.2	547.2	547.2	547.2	547.2
2.5°	545.1	546.0	546.8	547.2	547.1	547.0	546.9	546.8
5°	542.3	543.3	544.4	544.8	544.6	544.4	544.1	543.9
7.5°	536.5	537.5	538.4	538.8	538.7	538.6	538.5	538.3
10°	531.3	532.2	533.1	533.5	533.3	533.1	532.9	532.7
12.5°	525.4	526.1	526.8	527.1	527.0	526.8	526.7	526.6
15°	515.0	515.8	516.7	516.8	516.1	515.5	514.9	514.3
17.5°	501.8	502.4	503.0	503.2	502.9	502.7	502.5	502.3
20°	492.1	492.5	492.9	493.0	492.6	492.3	492.0	491.7
22.5°	481.7	482.1	482.4	482.4	482.0	481.6	481.2	480.8
25°	464.6	464.7	464.8	464.7	464.4	464.1	463.8	463.5
27.5°	446.5	446.6	446.6	446.5	446.1	445.7	445.2	444.8
30°	433.8	433.8	433.8	433.4	432.7	432.0	431.3	430.5
32.5°	420.6	420.0	419.5	419.0	418.6	418.2	417.8	417.4
35°	399.2	398.6	397.9	397.4	396.9	396.3	395.8	395.3
37.5°	377.0	376.3	375.5	375.0	374.7	374.3	374.0	373.7
40°	362.5	361.7	360.8	360.2	359.8	359.4	359.0	358.6
42.5°	347.5	346.6	345.8	345.2	344.8	344.4	344.0	343.5
45°	325.0	323.8	322.4	321.6	321.0	320.5	320.0	319.5
47.5°	301.3	300.1	298.8	298.0	297.5	297.1	296.6	296.2
50°	285.7	284.5	283.4	282.5	281.9	281.2	280.6	279.9
52.5°	269.8	268.8	267.8	267.0	266.4	265.8	265.2	264.6
55°	245.7	244.5	243.4	242.6	242.1	241.5	241.0	240.4
57.5°	222.0	220.9	219.8	219.0	218.4	217.8	217.2	216.6
60°	205.2	204.2	203.3	202.6	202.0	201.5	201.0	200.5
62.5°	188.9	188.0	187.1	186.4	186.1	185.7	185.4	185.0
65°	164.9	164.1	163.2	162.7	162.4	162.0	161.7	161.4
67.5°	141.0	140.3	139.6	139.0	138.6	138.0	137.6	137.2
70°	125.6	124.8	124.1	123.5	123.0	122.5	121.9	121.4
72.5°	110.0	109.3	108.7	108.2	108.0	107.7	107.3	107.0
75°	87.5	86.8	86.3	85.9	85.6	85.3	85.0	84.7
77.5°	66.3	66.0	65.6	65.5	65.5	65.5	65.5	65.5
80°	52.9	52.8	52.7	52.7	52.7	52.7	52.7	52.7
82.5°	40.8	40.6	40.4	40.2	40.2	40.1	40.0	39.9
85°	23.1	22.9	22.7	22.6	22.6	22.6	22.6	22.6
87.5°	13.3	13.4	13.5	13.6	13.7	13.7	13.8	13.9
90°	26.0	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	28.7	30.1	31.5	32.4	32.6	32.9	33.2	33.4
95°	34.3	36.0	37.6	38.3	38.3	38.3	38.3	38.3
97.5°	36.1	37.9	39.6	40.6	40.9	41.1	41.3	41.5
100°	36.9	38.7	40.4	41.4	41.7	41.9	42.1	42.3
102.5°	55.2	49.7	44.1	41.5	41.9	42.3	42.7	43.1
105°	141.5	101.8	62.2	42.5	43.0	43.4	43.9	44.3
107.5°	346.5	317.4	288.3	258.8	228.9	199.0	169.2	139.3
110°	439.8	432.4	425.1	405.4	373.2	341.2	309.2	277.2



TEST NUMBER: P331898-840

CATALOG NUMBER: S123DIP-S340D1025U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	505.6	505.8	505.9	502.6	495.8	489.1	482.3	475.5
115°	583.1	585.3	587.5	589.2	590.0	590.9	591.8	592.7
117.5°	653.2	654.9	656.7	657.7	657.9	658.0	658.2	658.4
120°	699.1	700.8	702.7	703.6	703.6	703.6	703.6	703.6
122.5°	744.0	745.3	746.5	747.2	747.4	747.6	747.7	747.9
125°	807.3	807.7	808.2	808.6	809.1	809.5	810.0	810.4
127.5°	870.7	871.4	872.1	872.3	871.8	871.4	870.9	870.5
130°	909.0	909.9	910.8	911.0	910.6	910.1	909.7	909.2
132.5°	945.2	946.1	947.1	947.2	946.5	945.9	945.3	944.7
135°	1000.3	1001.0	1001.6	1001.6	1001.0	1000.3	999.6	999.0
137.5°	1049.2	1050.4	1051.4	1051.7	1051.3	1050.9	1050.4	1050.0
140°	1080.4	1081.3	1082.2	1082.4	1081.9	1081.5	1081.1	1080.6
142.5°	1109.8	1110.5	1111.3	1111.3	1110.6	1110.0	1109.4	1108.8
145°	1151.0	1151.4	1152.0	1152.2	1152.2	1152.2	1152.2	1152.2
147.5°	1187.9	1188.3	1188.8	1188.5	1187.5	1186.5	1185.4	1184.4
150°	1210.5	1210.9	1211.4	1211.2	1210.6	1209.9	1209.2	1208.6
152.5°	1230.5	1231.3	1232.1	1232.0	1231.0	1230.0	1229.0	1227.9
155°	1258.2	1259.3	1260.4	1260.3	1259.0	1257.7	1256.3	1255.0
157.5°	1282.2	1283.5	1285.0	1284.8	1282.9	1281.2	1279.5	1277.8
160°	1296.0	1297.3	1298.6	1298.5	1297.0	1295.4	1293.8	1292.2
162.5°	1308.4	1309.9	1311.4	1311.5	1310.1	1308.7	1307.4	1306.0
165°	1325.0	1326.9	1328.7	1328.8	1327.2	1325.6	1324.0	1322.5
167.5°	1338.0	1339.8	1341.5	1341.5	1339.8	1338.0	1336.2	1334.3
170°	1345.2	1347.1	1348.8	1348.8	1347.1	1345.2	1343.4	1341.6
172.5°	1350.1	1351.8	1353.6	1353.5	1351.6	1349.6	1347.7	1345.6
175°	1355.8	1357.5	1359.0	1358.9	1357.1	1355.3	1353.5	1351.7
177.5°	1358.0	1359.5	1360.9	1360.7	1358.9	1357.2	1355.3	1353.5
180°	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8	1356.8

(END OF REPORT)