

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331990

Luminaire Tested: **S123DIP-S775D1025U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331990
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6882.4 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46				
1	97	93	89	85	89	85	82	79	71	69	66	58	57	55	46	45	44	39				
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	41	39	37	32				
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27				
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24	20				
6	62	50	42	36	57	46	39	34	39	34	29	33	28	25	26	23	21	18				
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	19	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14				
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	1.7
10°-20°	323.9	4.7
20°-30°	478.4	7.0
30°-40°	558.9	8.1
40°-50°	561.9	8.2
50°-60°	493.6	7.2
60°-70°	367.7	5.3
70°-80°	209.5	3.0
80°-90°	64.0	0.9
90°-100°	274.4	4.0
100°-110°	777.0	11.3
110°-120°	764.4	11.1
120°-130°	609.7	8.9
130°-140°	480.7	7.0
140°-150°	358.8	5.2
150°-160°	250.1	3.6
160°-170°	146.9	2.1
170°-180°	47.8	0.7
0°-30°	917.1	13.3
0°-40°	1475.9	21.4
0°-60°	2531.4	36.8
0°-90°	3172.5	46.1
90°-120°	1815.8	26.4
90°-150°	3265.1	47.4
90°-180°	3710.0	53.9
0°-180°	6882.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	2	12	25	28	29	5
95°	34	110	592	173	116	37
105°	116	171	802	1403	1270	123
115°	205	255	614	1346	1544	203
125°	284	336	573	1038	1218	252
135°	333	398	565	855	987	258
145°	380	436	558	701	772	238
155°	432	466	540	614	640	199
165°	472	486	517	548	558	133
175°	492	493	496	503	502	47
180°	493	493	493	493	493	



TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	22.2	22.0	21.9	21.9	21.7	21.8	22.2	22.6	23.0	23.4	23.0
90°	2.0	4.0	6.0	9.0	11.0	13.0	16.0	19.0	22.0	25.0	24.0
92.5°	12.4	18.4	26.8	34.5	42.9	57.7	83.8	126.8	168.9	153.5	115.8
95°	33.9	36.9	47.9	64.9	90.8	129.8	214.6	363.3	527.0	591.9	480.1
97.5°	57.9	58.9	67.5	82.2	107.8	149.9	231.0	398.7	671.6	917.3	981.4
100°	73.9	74.9	81.9	95.8	119.8	158.7	228.6	376.3	638.8	945.3	1141.9
102.5°	90.6	92.4	98.6	111.8	133.4	169.1	231.8	357.1	590.9	893.4	1149.9
105°	115.8	118.8	124.8	136.8	155.7	186.7	240.6	343.4	532.0	802.5	1089.0
107.5°	142.5	145.5	151.3	163.1	180.9	209.6	256.9	342.4	494.5	722.3	982.4
110°	161.7	164.7	169.7	180.7	197.6	225.6	270.5	346.4	480.1	676.8	915.3



TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	179.3	182.3	187.3	198.2	215.2	242.4	284.1	354.4	472.1	646.4	857.0
115°	204.6	208.6	214.6	224.6	241.6	268.5	306.4	367.3	469.1	613.9	786.6
117.5°	230.0	234.6	239.6	248.7	267.7	292.7	330.2	384.5	470.9	594.7	744.0
120°	247.5	250.5	255.5	265.5	284.5	309.4	345.4	397.3	474.1	585.9	721.7
122.5°	262.7	265.7	270.7	281.5	299.7	326.2	361.3	409.3	479.7	580.3	703.3
125°	284.5	286.5	292.5	303.4	322.4	349.4	384.3	428.2	488.1	573.0	679.8
127.5°	301.1	304.0	311.4	322.6	343.6	370.5	404.3	443.8	497.7	569.4	659.0
130°	311.4	314.4	323.4	335.4	356.3	383.3	416.2	454.2	504.1	567.0	647.8
132.5°	319.4	323.2	333.0	347.4	368.3	394.5	426.6	463.8	508.9	566.2	637.4
135°	333.4	337.4	348.4	363.3	384.3	411.2	442.2	476.1	516.1	565.0	623.9
137.5°	346.6	350.8	361.5	377.5	398.3	423.2	453.0	485.3	520.8	562.8	612.1
140°	355.4	360.3	370.3	386.3	406.3	431.2	460.2	490.1	524.0	562.0	604.9
142.5°	364.9	369.1	379.9	394.3	414.2	437.6	465.8	494.9	526.4	560.4	598.5
145°	380.3	383.3	392.3	407.3	424.2	447.2	473.1	500.1	528.0	558.0	589.9
147.5°	395.9	397.7	406.5	419.4	435.8	455.4	479.1	503.3	528.0	554.2	581.5
150°	406.3	407.3	415.2	428.2	442.2	460.2	483.1	504.1	528.0	551.0	575.9
152.5°	416.6	416.8	424.8	436.2	448.6	465.8	485.5	505.7	525.6	547.0	569.6
155°	432.2	432.2	438.2	448.2	459.2	473.1	490.1	506.1	523.0	540.0	560.0
157.5°	444.6	445.4	450.2	459.0	468.3	479.1	492.7	507.1	519.7	533.8	549.2
160°	454.2	454.2	458.2	466.1	473.1	483.1	495.1	507.1	518.1	529.0	542.0
162.5°	461.4	461.4	464.6	470.9	477.1	485.5	495.9	506.3	514.9	524.2	534.8
165°	472.1	471.1	473.1	478.1	482.1	489.1	497.1	504.1	510.1	517.1	525.0
167.5°	480.3	479.1	480.1	483.9	486.7	491.1	496.9	502.5	505.3	509.9	515.7
170°	485.1	483.1	484.1	487.1	489.1	491.1	496.1	500.1	502.1	505.1	510.1
172.5°	488.3	487.1	487.3	489.5	490.7	491.9	496.1	499.3	499.7	501.1	504.5
175°	492.1	491.1	490.1	492.1	492.1	493.1	495.1	497.1	496.1	496.1	498.1
177.5°	493.9	493.1	492.3	493.1	493.1	493.1	493.9	495.5	493.9	493.1	493.9
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1



TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	23.0	23.1	23.1	23.4	23.2	23.4	23.6	23.4
90°	25.0	26.0	27.0	28.9	27.9	28.9	29.9	28.9
92.5°	84.0	66.7	58.9	53.7	51.9	48.9	49.9	48.1
95°	359.3	243.6	190.7	154.7	135.8	126.8	119.8	115.8
97.5°	895.8	717.5	588.7	469.3	395.7	350.8	323.8	315.2
100°	1176.9	1096.0	979.2	837.5	736.7	663.8	624.9	625.9
102.5°	1270.3	1267.7	1199.6	1109.8	1031.3	973.6	941.1	918.1
105°	1297.6	1397.5	1416.4	1390.5	1344.5	1306.6	1274.7	1269.7
107.5°	1219.0	1381.1	1468.5	1504.1	1504.9	1492.1	1481.3	1472.1
110°	1143.9	1327.6	1453.3	1523.2	1551.2	1559.2	1557.2	1555.2



TEST NUMBER: P331990

CATALOG NUMBER: S123DIP-S775D1025U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1069.6	1257.3	1398.2	1488.1	1539.2	1563.9	1571.5	1571.9
115°	971.2	1144.9	1291.6	1400.4	1475.3	1519.2	1539.2	1544.2
117.5°	900.0	1049.9	1181.6	1292.0	1370.1	1420.4	1449.2	1455.9
120°	862.4	997.2	1117.0	1217.8	1296.6	1352.5	1376.5	1382.5
122.5°	832.9	954.9	1065.9	1159.5	1229.6	1279.9	1306.2	1313.8
125°	793.6	902.4	998.2	1078.0	1141.9	1185.8	1210.8	1217.8
127.5°	759.2	856.2	942.7	1015.3	1072.2	1109.8	1132.3	1138.7
130°	737.7	827.5	908.3	976.2	1029.1	1065.1	1086.0	1094.0
132.5°	717.7	800.3	875.6	940.3	990.0	1025.9	1044.5	1050.1
135°	690.7	761.6	826.5	883.4	932.3	962.2	980.2	987.2
137.5°	666.2	724.3	780.2	829.5	870.6	901.0	916.1	920.7
140°	651.8	702.7	750.6	793.6	831.5	859.4	875.4	874.4
142.5°	638.2	682.0	723.5	760.8	793.2	817.9	832.3	831.3
145°	621.9	654.8	686.7	715.7	740.6	761.6	769.6	771.6
147.5°	608.5	634.6	660.4	681.0	699.9	714.1	721.7	722.5
150°	598.9	621.9	642.8	661.8	676.8	687.7	693.7	693.7
152.5°	590.1	609.9	628.5	644.2	656.0	666.2	669.8	669.8
155°	576.9	592.9	607.9	619.9	628.9	636.8	638.8	639.8
157.5°	563.0	576.3	587.9	597.3	605.1	611.1	612.7	612.5
160°	555.0	566.0	575.9	582.9	589.9	595.9	595.9	594.9
162.5°	545.4	554.8	564.0	570.2	574.8	579.9	579.9	578.9
165°	533.0	539.0	546.0	551.0	555.0	559.0	558.0	558.0
167.5°	522.2	526.8	530.8	534.4	536.2	539.0	538.0	538.0
170°	515.1	518.1	522.0	524.0	525.0	527.0	526.0	526.0
172.5°	508.7	510.9	514.1	515.3	515.5	517.5	515.7	514.9
175°	500.1	501.1	503.1	503.1	503.1	504.1	503.1	502.1
177.5°	494.7	495.5	496.3	496.3	495.5	496.3	494.7	494.7
180°	493.1	493.1	493.1	493.1	493.1	493.1	493.1	493.1

(END OF REPORT)