

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831617

Luminaire Tested: S123DIP-S775D1195U835-4F0-1E-UDD-G4

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831617
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-17)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1195U835-4F0-1E-UDD-G4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7867.3 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

Luminous Intensity Polar Plot





TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	25				
5	69	58	50	44	63	53	47	42	45	40	36	38	34	31	31	28	26	23				
6	64	52	44	39	58	48	41	36	41	36	32	34	30	27	28	25	23	20				
7	59	47	40	34	54	44	37	32	37	32	28	32	28	25	26	23	21	18				
8	55	43	36	31	50	40	33	29	34	29	25	29	25	22	24	21	19	17				
9	51	40	32	27	47	37	30	26	32	27	23	27	23	20	22	19	17	15				
10	48	36	29	25	44	34	28	24	29	24	21	25	21	18	21	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	23750	23750	23750	23750	23750
5°	30035	28348	23961	19310	17744
10°	30326	31243	23802	15393	13450
15°	22841	29008	23640	13035	11375
20°	15914	23473	23338	11400	10332
25°	12136	18051	22823	10488	9691
30°	10499	14342	22002	9843	9175
35°	9741	12107	21055	9377	8812
40°	9222	10862	19724	8934	8689
45°	8914	10053	18033	8587	8634
50°	8761	9413	16031	8272	8589
55°	8435	8944	14063	7974	8627
60°	8133	8441	12122	7692	8486
65°	7641	7967	10458	7394	8318
70°	7056	7361	8894	6895	7830
75°	6388	6600	7623	6409	7153
80°	5269	5777	6031	5585	6031
85°	4174	4681	4421	4742	4804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 20588 cd/sqm



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.6	2.7
10°-20°	518.9	6.6
20°-30°	614.4	7.8
30°-40°	617.8	7.9
40°-50°	566.8	7.2
50°-60°	467.8	5.9
60°-70°	330.9	4.2
70°-80°	176.7	2.2
80°-90°	48.0	0.6
90°-100°	311.5	4.0
100°-110°	911.8	11.6
110°-120°	890.4	11.3
120°-130°	709.1	9.0
130°-140°	559.5	7.1
140°-150°	417.4	5.3
150°-160°	291.0	3.7
160°-170°	171.0	2.2
170°-180°	55.6	0.7
0°-30°	1341.9	17.1
0°-40°	1959.7	24.9
0°-60°	2994.4	38.1
0°-90°	3549.9	45.1
90°-120°	2113.7	26.9
90°-150°	3799.8	48.3
90°-180°	4317.0	54.9
0°-180°	7867.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2206	2206	2206	2206	2206	
5°	2780	2624	2218	1787	1642	265
15°	2050	2603	2121	1170	1021	566
25°	1022	1520	1922	883	816	482
35°	741	921	1602	714	671	466
45°	586	660	1185	564	567	454
55°	450	477	749	425	460	402
65°	300	313	411	290	327	298
75°	154	159	183	154	172	161
85°	34	38	36	38	39	38
90°	34	29	2	29	34	20
95°	135	689	40	689	135	219
105°	1478	934	135	934	1478	1474
115°	1797	714	238	714	1797	1753
125°	1418	667	331	667	1418	1283
135°	1149	658	388	658	1149	891
145°	898	650	443	650	898	570
155°	745	629	503	629	745	347
165°	650	602	550	602	650	185
175°	584	577	573	577	584	57
180°	574	574	574	574	574	



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2486.9	2484.3	2481.8	2469.0	2456.2	2450.0	2443.9	2425.5	2407.0	2386.5	2366.1
5°	2779.7	2786.9	2794.0	2785.8	2777.7	2752.6	2727.5	2694.2	2660.9	2623.6	2586.2
7.5°	2914.8	2918.9	2923.0	2917.9	2912.8	2906.1	2899.5	2869.8	2840.1	2801.7	2763.3
10°	2774.6	2783.8	2793.0	2813.0	2832.9	2855.5	2878.0	2873.9	2869.8	2858.5	2847.3
12.5°	2466.4	2477.7	2488.9	2528.9	2568.8	2620.0	2671.2	2715.2	2759.2	2789.9	2820.7
15°	2049.7	2080.9	2112.2	2148.5	2184.9	2260.1	2335.4	2428.0	2520.7	2603.1	2685.5
17.5°	1688.3	1700.1	1711.8	1750.7	1789.7	1884.4	1979.1	2086.1	2193.0	2329.7	2466.4
20°	1389.3	1400.1	1410.8	1462.0	1513.2	1587.4	1661.7	1782.0	1902.3	2049.2	2196.1
22.5°	1167.2	1184.1	1201.0	1229.6	1258.3	1329.4	1400.6	1507.6	1614.6	1776.9	1939.1
25°	1021.8	1034.1	1046.4	1063.8	1081.2	1138.0	1194.8	1282.9	1370.9	1519.9	1668.8
27.5°	922.5	927.6	932.7	950.1	967.5	1004.4	1041.2	1117.0	1192.8	1319.2	1445.6
30°	844.7	848.2	851.8	867.2	882.5	907.6	932.7	987.5	1042.3	1153.9	1265.5
32.5°	790.4	793.0	795.5	807.3	819.1	837.0	854.9	894.8	934.8	1026.9	1119.0
35°	741.3	742.8	744.3	753.0	761.7	775.0	788.3	818.6	848.8	921.4	994.1
37.5°	698.3	700.3	702.3	707.5	712.6	724.4	736.1	760.2	784.3	840.1	895.9
40°	656.3	659.9	663.4	667.0	670.6	680.3	690.1	708.5	726.9	773.0	819.1
42.5°	620.4	624.0	627.6	629.1	630.7	636.3	641.9	658.8	675.7	710.0	744.3
45°	585.6	587.2	588.7	590.2	591.8	596.4	601.0	615.8	630.7	660.4	690.1
47.5°	553.9	553.9	553.9	554.9	555.9	560.0	564.1	574.9	585.6	608.7	631.7
50°	523.2	523.2	523.2	521.6	520.1	522.7	525.2	533.4	541.6	562.1	582.6
52.5°	486.3	486.3	486.3	486.8	487.3	487.3	487.3	494.5	501.7	520.1	538.5
55°	449.5	451.5	453.6	452.0	450.5	451.5	452.5	457.1	461.7	476.6	491.4
57.5°	412.6	413.6	414.7	414.1	413.6	414.1	414.7	418.7	422.8	434.1	445.4
60°	377.8	377.8	377.8	376.8	375.7	376.8	377.8	379.8	381.9	392.1	402.4
62.5°	338.9	339.4	339.9	340.4	340.9	339.9	338.9	341.4	344.0	351.7	359.4
65°	300.0	300.5	301.0	302.5	304.1	303.1	302.0	304.6	307.1	312.8	318.4
67.5°	265.2	264.1	263.1	263.6	264.1	265.7	267.2	267.7	268.2	274.4	280.5
70°	224.2	225.2	226.3	225.8	225.2	225.8	226.3	227.8	229.3	233.9	238.6
72.5°	187.4	187.9	188.4	188.4	188.4	189.4	190.4	192.0	193.5	196.1	198.6
75°	153.6	153.6	153.6	154.6	155.6	156.1	156.6	156.6	156.6	158.7	160.7
77.5°	116.7	119.3	121.8	121.3	120.8	121.8	122.9	124.4	125.9	127.0	128.0
80°	85.0	85.0	85.0	85.5	86.0	87.5	89.1	90.1	91.1	93.2	95.2
82.5°	54.3	54.8	55.3	56.8	58.4	59.4	60.4	61.9	63.5	63.5	63.5
85°	33.8	32.8	31.7	32.8	33.8	34.8	35.8	36.3	36.9	37.9	38.9
87.5°	16.4	16.4	16.4	16.4	16.4	16.9	17.4	17.4	17.4	17.4	17.4
90°	33.7	34.9	33.7	32.5	33.7	31.4	30.2	29.0	27.9	29.0	25.6
92.5°	61.6	63.9	62.7	67.4	69.7	77.8	89.5	115.0	161.5	216.1	239.3
95°	134.8	139.4	147.6	158.0	180.1	221.9	283.5	418.3	558.8	689.0	613.5
97.5°	276.5	289.3	317.2	361.3	439.2	571.6	725.0	960.8	1095.6	1059.6	791.2
100°	728.5	727.3	772.6	857.4	974.8	1139.8	1275.7	1369.8	1329.2	1100.3	743.6
102.5°	1153.7	1187.4	1223.4	1286.2	1371.0	1460.4	1525.5	1505.8	1340.8	1024.7	673.9
105°	1477.9	1483.7	1520.9	1565.0	1618.5	1648.7	1626.6	1510.4	1267.6	934.1	619.3
107.5°	1689.3	1702.1	1717.2	1738.1	1745.1	1713.7	1623.1	1440.7	1163.0	854.0	579.8
110°	1810.2	1812.5	1814.8	1805.5	1773.0	1691.7	1545.3	1331.5	1065.4	787.7	558.8



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1834.6	1833.4	1821.8	1788.1	1721.9	1611.5	1443.0	1223.4	980.6	743.6	547.2
115°	1797.4	1791.6	1768.3	1717.2	1630.1	1503.4	1332.6	1130.5	915.5	714.5	546.1
117.5°	1716.0	1707.9	1673.1	1616.1	1525.5	1394.2	1237.4	1058.4	872.5	694.8	547.2
120°	1609.2	1602.2	1574.3	1509.2	1417.5	1300.1	1160.7	1003.8	840.0	682.0	551.9
122.5°	1509.2	1499.9	1468.6	1411.6	1332.6	1225.7	1099.1	960.8	813.3	673.9	560.0
125°	1417.5	1409.3	1380.3	1329.2	1254.8	1161.8	1050.3	923.7	791.2	666.9	568.1
127.5°	1338.4	1331.5	1304.8	1260.6	1193.2	1107.2	1005.0	890.0	770.3	663.4	577.4
130°	1273.4	1264.1	1239.7	1197.9	1136.3	1057.3	963.2	858.6	754.0	659.9	586.7
132.5°	1209.5	1203.7	1182.8	1140.9	1084.0	1009.6	923.7	829.6	738.9	658.8	593.7
135°	1149.1	1140.9	1120.0	1085.2	1028.2	962.0	886.5	804.0	726.2	657.6	600.7
137.5°	1085.2	1078.2	1060.8	1024.7	976.0	916.7	849.3	779.6	714.5	655.3	605.3
140°	1017.8	1018.9	1000.4	967.8	923.7	873.7	817.9	758.7	704.1	654.1	610.0
142.5°	955.0	956.2	939.9	912.1	876.0	834.2	787.7	738.9	694.8	651.8	613.5
145°	898.1	895.8	886.5	862.1	833.0	799.4	762.2	723.8	686.7	649.5	614.6
147.5°	849.3	848.1	838.9	821.4	798.2	773.8	742.4	711.1	678.5	646.0	614.6
150°	807.5	807.5	800.5	787.7	770.3	748.2	723.8	697.1	670.4	641.3	614.6
152.5°	772.6	772.6	769.1	757.5	744.7	727.3	706.4	684.3	661.1	635.5	611.1
155°	744.7	743.6	741.3	732.0	721.5	707.6	690.1	671.5	651.8	628.6	608.8
157.5°	718.0	718.0	715.7	708.7	699.4	687.8	673.9	657.6	641.3	622.8	605.3
160°	692.5	693.6	693.6	686.7	678.5	670.4	658.8	646.0	630.9	615.8	603.0
162.5°	669.2	670.4	670.4	664.6	659.9	653.0	642.5	632.0	620.4	608.8	598.4
165°	649.5	649.5	650.6	646.0	641.3	635.5	627.4	620.4	611.1	601.8	593.7
167.5°	629.7	629.7	630.9	627.4	625.1	620.4	615.8	610.0	601.8	594.9	589.1
170°	612.3	612.3	613.5	611.1	610.0	607.6	603.0	599.5	593.7	587.9	584.4
172.5°	596.0	597.2	599.5	597.2	597.2	596.0	592.5	590.2	585.6	582.1	580.9
175°	584.4	585.6	586.7	585.6	585.6	585.6	583.2	582.1	579.8	577.4	577.4
177.5°	576.3	576.3	578.6	577.4	578.6	578.6	577.4	576.3	575.1	574.0	575.1
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2359.9	2353.8	2331.3	2308.7	2283.1	2257.5	2238.6	2219.7	2191.5	2163.4	2140.3
5°	2557.5	2528.9	2481.3	2433.6	2369.1	2304.6	2261.1	2217.6	2159.3	2100.9	2054.3
7.5°	2714.2	2665.0	2598.5	2531.9	2447.5	2363.0	2283.1	2203.3	2114.2	2025.1	1952.4
10°	2814.0	2780.7	2703.9	2627.1	2514.0	2400.9	2289.3	2177.7	2063.0	1948.3	1852.1
12.5°	2823.7	2826.8	2756.1	2685.5	2557.5	2429.5	2293.9	2158.2	2013.9	1869.5	1757.4
15°	2738.2	2791.0	2752.1	2713.1	2584.1	2455.1	2288.3	2121.4	1955.0	1788.6	1659.1
17.5°	2579.5	2692.7	2698.3	2703.9	2574.9	2445.9	2261.1	2076.3	1887.9	1699.6	1563.4
20°	2363.0	2529.9	2587.2	2644.6	2539.6	2434.7	2236.0	2037.4	1826.5	1615.6	1472.8
22.5°	2141.9	2344.6	2449.5	2554.5	2476.6	2398.8	2187.4	1976.0	1753.3	1530.6	1385.8
25°	1890.0	2111.1	2272.4	2433.6	2386.0	2338.4	2130.1	1921.7	1684.7	1447.7	1299.8
27.5°	1670.4	1895.1	2089.6	2284.2	2273.9	2263.7	2056.9	1850.1	1607.4	1364.8	1221.9
30°	1474.8	1684.2	1901.8	2119.3	2144.4	2169.5	1969.8	1770.2	1527.0	1283.9	1146.2
32.5°	1301.8	1484.6	1718.0	1951.4	2000.6	2049.7	1869.5	1689.3	1448.7	1208.1	1075.5
35°	1160.0	1325.9	1559.3	1792.7	1854.2	1915.6	1758.9	1602.3	1367.8	1133.4	1006.9
37.5°	1034.6	1173.3	1401.1	1628.9	1704.2	1779.4	1639.2	1498.9	1279.3	1059.7	943.5
40°	930.7	1042.3	1251.6	1461.0	1548.0	1635.1	1519.4	1403.7	1195.3	987.0	880.0
42.5°	843.6	942.9	1132.9	1322.8	1406.2	1489.7	1391.9	1294.1	1108.8	923.5	825.7
45°	769.4	848.8	1021.3	1193.8	1273.1	1352.5	1268.5	1184.6	1021.3	858.0	766.8
47.5°	699.8	767.9	915.3	1062.7	1133.4	1204.0	1138.5	1073.0	934.8	796.5	714.1
50°	637.3	692.1	821.1	950.1	1011.5	1073.0	1015.1	957.3	843.6	730.0	658.3
52.5°	583.1	627.6	735.6	843.6	896.4	949.1	899.4	849.8	759.7	669.6	607.1
55°	529.3	567.2	660.9	754.6	790.4	826.2	787.8	749.4	676.8	604.1	551.3
57.5°	479.2	512.9	589.7	666.5	694.2	721.8	687.0	652.2	597.4	542.6	498.6
60°	430.0	457.7	521.6	585.6	602.5	619.4	591.3	563.1	524.7	486.3	446.9
62.5°	384.4	409.5	457.1	504.7	516.0	527.3	505.8	484.3	455.1	425.9	395.2
65°	337.4	356.3	395.2	434.1	441.3	448.4	429.5	410.6	388.5	366.5	344.0
67.5°	293.8	307.1	338.9	370.6	371.1	371.7	356.3	340.9	328.6	316.4	298.4
70°	251.4	264.1	285.1	306.1	306.6	307.1	294.9	282.6	273.4	264.1	250.8
72.5°	207.8	217.1	232.9	248.8	247.8	246.7	239.1	231.4	224.2	217.1	207.3
75°	168.4	176.1	186.8	197.6	194.5	191.5	187.4	183.3	177.1	171.0	164.8
77.5°	132.6	137.2	143.3	149.5	147.4	145.4	141.8	138.2	133.6	129.0	126.4
80°	97.3	99.3	103.4	107.5	106.5	105.5	101.4	97.3	96.2	95.2	91.6
82.5°	66.0	68.6	69.6	70.6	70.1	69.6	66.5	63.5	62.5	61.4	60.9
85°	39.4	39.9	40.4	41.0	39.4	37.9	36.9	35.8	35.8	35.8	35.3
87.5°	17.9	18.4	18.4	18.4	17.9	17.4	16.4	15.4	15.9	16.4	16.4
90°	22.1	18.6	15.1	12.8	10.5	7.0	4.6	2.3	4.6	7.0	10.5
92.5°	178.9	117.3	80.2	59.3	47.6	37.2	25.6	17.4	25.6	37.2	47.6
95°	422.9	249.8	151.0	105.7	75.5	55.8	43.0	39.5	43.0	55.8	75.5
97.5°	470.5	269.5	172.0	122.0	91.8	74.4	63.9	62.7	63.9	74.4	91.8
100°	438.0	266.1	184.7	139.4	111.5	95.3	87.1	86.0	87.1	95.3	111.5
102.5°	410.1	270.7	199.8	159.2	134.8	119.7	112.7	110.4	112.7	119.7	134.8
105°	399.7	280.0	217.3	181.2	159.2	145.2	138.3	134.8	138.3	145.2	159.2
107.5°	397.4	295.1	239.3	205.6	184.7	170.8	163.8	160.3	163.8	170.8	184.7
110°	403.2	314.9	262.6	230.0	210.3	197.5	191.7	188.2	191.7	197.5	210.3



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	414.8	334.6	287.0	255.6	235.9	223.1	217.3	213.8	217.3	223.1	235.9
115°	427.6	356.7	312.5	281.2	261.4	249.8	242.8	238.2	242.8	249.8	261.4
117.5°	443.8	379.9	335.8	306.7	284.7	274.2	268.4	262.6	268.4	274.2	284.7
120°	462.4	402.0	360.2	331.1	309.1	297.4	291.6	288.1	291.6	297.4	309.1
122.5°	479.8	425.2	384.6	353.2	332.3	319.5	313.7	310.2	313.7	319.5	332.3
125°	498.4	447.3	406.6	375.3	353.2	340.4	333.5	331.1	333.5	340.4	353.2
127.5°	513.5	467.1	427.6	396.2	371.8	359.0	350.9	347.4	350.9	359.0	371.8
130°	528.6	484.5	446.1	414.8	390.4	376.4	366.0	362.5	366.0	376.4	390.4
132.5°	542.6	499.6	462.4	432.2	407.8	390.4	378.8	374.1	378.8	390.4	407.8
135°	554.2	514.7	478.7	447.3	422.9	405.5	392.7	388.1	392.7	405.5	422.9
137.5°	563.5	525.2	490.3	461.3	436.9	418.3	405.5	400.8	405.5	418.3	436.9
140°	570.5	535.6	501.9	472.9	449.6	431.0	419.4	413.6	419.4	431.0	449.6
142.5°	577.4	543.7	511.2	484.5	461.3	445.0	432.2	427.6	432.2	445.0	461.3
145°	582.1	550.7	520.5	493.8	474.0	456.6	446.1	442.7	446.1	456.6	474.0
147.5°	585.6	556.5	528.6	505.4	485.7	470.5	460.1	457.8	460.1	470.5	485.7
150°	586.7	562.3	535.6	514.7	498.4	483.3	474.0	472.9	474.0	483.3	498.4
152.5°	589.1	565.8	543.7	524.0	510.1	497.3	488.0	488.0	488.0	497.3	510.1
155°	589.1	570.5	550.7	534.4	521.7	510.1	503.1	503.1	503.1	510.1	521.7
157.5°	590.2	572.8	556.5	543.7	532.1	521.7	515.9	514.7	515.9	521.7	532.1
160°	590.2	576.3	562.3	550.7	542.6	533.3	528.6	528.6	528.6	533.3	542.6
162.5°	589.1	577.4	565.8	556.5	549.6	542.6	539.1	539.1	539.1	542.6	549.6
165°	586.7	578.6	569.3	561.2	556.5	550.7	548.4	549.6	548.4	550.7	556.5
167.5°	585.6	578.6	571.6	565.8	562.3	557.7	556.5	557.7	556.5	557.7	562.3
170°	582.1	577.4	571.6	569.3	567.0	563.5	562.3	564.7	562.3	563.5	567.0
172.5°	580.9	577.4	572.8	571.6	570.5	568.1	568.1	569.3	568.1	568.1	570.5
175°	578.6	576.3	574.0	572.8	572.8	570.5	571.6	572.8	571.6	570.5	572.8
177.5°	577.4	575.1	574.0	574.0	574.0	572.8	574.0	575.1	574.0	572.8	574.0
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2117.3	2097.3	2077.4	2062.0	2046.6	2020.5	1994.4	1988.3	1982.1	1973.4	1964.7
5°	2007.7	1958.6	1909.4	1865.4	1821.4	1787.1	1752.8	1730.3	1707.7	1691.4	1675.0
7.5°	1879.8	1806.0	1732.3	1680.1	1627.9	1578.2	1528.6	1512.7	1496.8	1475.3	1453.8
10°	1755.9	1674.5	1593.1	1525.0	1456.9	1408.3	1359.6	1340.2	1320.7	1293.6	1266.5
12.5°	1645.3	1556.2	1467.1	1398.6	1330.0	1282.9	1235.8	1207.6	1179.5	1164.1	1148.7
15°	1529.6	1434.4	1339.2	1275.7	1212.2	1169.7	1127.2	1102.7	1078.1	1063.2	1048.4
17.5°	1427.2	1333.0	1238.8	1177.9	1117.0	1078.1	1039.2	1017.7	996.2	984.9	973.7
20°	1330.0	1237.8	1145.7	1086.3	1026.9	995.2	963.4	949.6	935.8	926.6	917.4
22.5°	1240.9	1150.3	1059.7	1009.0	958.3	932.7	907.1	897.4	887.7	880.0	872.3
25°	1151.8	1070.9	990.0	947.0	904.0	883.1	862.1	852.3	842.6	834.9	827.3
27.5°	1079.1	1001.8	924.5	887.7	850.8	834.4	818.0	810.4	802.7	795.5	788.3
30°	1008.5	939.4	870.3	838.5	806.8	791.9	777.1	769.4	761.7	755.1	748.4
32.5°	942.9	883.6	824.2	795.0	765.8	753.5	741.3	732.0	722.8	717.7	712.6
35°	880.5	827.3	774.0	750.0	725.9	713.6	701.3	693.6	686.0	681.9	677.8
37.5°	827.3	779.6	732.0	709.0	686.0	674.2	662.4	655.8	649.1	647.6	646.0
40°	773.0	732.0	691.1	668.6	646.0	635.8	625.6	621.5	617.4	616.3	615.3
42.5°	727.9	688.0	648.1	627.6	607.1	598.4	589.7	587.7	585.6	587.2	588.7
45°	675.7	642.5	609.2	590.2	571.3	564.1	557.0	555.4	553.9	557.0	560.0
47.5°	631.7	601.0	570.3	552.4	534.4	529.3	524.2	523.7	523.2	527.3	531.4
50°	586.7	557.0	527.3	512.9	498.6	494.0	489.4	490.9	492.5	499.1	505.8
52.5°	544.7	517.0	489.4	476.1	462.8	459.7	456.6	460.2	463.8	471.0	478.1
55°	498.6	473.5	448.4	438.2	428.0	424.9	421.8	429.0	436.2	442.8	449.5
57.5°	454.6	432.6	410.6	401.3	392.1	391.6	391.1	397.8	404.4	411.6	418.7
60°	407.5	389.1	370.6	363.5	356.3	357.3	358.3	366.0	373.7	379.3	385.0
62.5°	364.5	349.1	333.8	327.1	320.5	323.0	325.6	333.3	340.9	347.6	354.2
65°	321.5	308.7	295.9	291.3	286.7	290.3	293.8	300.5	307.1	311.8	316.4
67.5°	280.5	269.8	259.0	255.4	251.9	255.4	259.0	265.7	272.3	276.9	281.6
70°	237.5	228.8	220.1	217.6	215.0	219.1	223.2	228.8	234.5	239.1	243.7
72.5°	197.6	190.9	184.3	183.8	183.3	186.8	190.4	196.1	201.7	204.8	207.8
75°	158.7	155.1	151.5	151.0	150.5	154.1	157.7	160.7	163.8	166.4	168.9
77.5°	123.9	120.8	117.7	118.3	118.8	121.3	123.9	127.0	130.0	131.6	133.1
80°	88.0	87.0	86.0	87.0	88.0	90.1	92.1	94.2	96.2	97.3	98.3
82.5°	60.4	59.4	58.4	59.9	61.4	63.0	64.5	66.0	67.6	68.1	68.6
85°	34.8	36.3	37.9	37.9	37.9	38.4	38.9	39.4	39.9	39.4	38.9
87.5°	16.4	16.9	17.4	17.4	17.4	17.9	18.4	18.4	18.4	17.9	17.4
90°	12.8	15.1	18.6	22.1	25.6	29.0	27.9	29.0	30.2	31.4	33.7
92.5°	59.3	80.2	117.3	178.9	239.3	216.1	161.5	115.0	89.5	77.8	69.7
95°	105.7	151.0	249.8	422.9	613.5	689.0	558.8	418.3	283.5	221.9	180.1
97.5°	122.0	172.0	269.5	470.5	791.2	1059.6	1095.6	960.8	725.0	571.6	439.2
100°	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2	1369.8	1275.7	1139.8	974.8
102.5°	159.2	199.8	270.7	410.1	673.9	1024.7	1340.8	1505.8	1525.5	1460.4	1371.0
105°	181.2	217.3	280.0	399.7	619.3	934.1	1267.6	1510.4	1626.6	1648.7	1618.5
107.5°	205.6	239.3	295.1	397.4	579.8	854.0	1163.0	1440.7	1623.1	1713.7	1745.1
110°	230.0	262.6	314.9	403.2	558.8	787.7	1065.4	1331.5	1545.3	1691.7	1773.0



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	255.6	287.0	334.6	414.8	547.2	743.6	980.6	1223.4	1443.0	1611.5	1721.9
115°	281.2	312.5	356.7	427.6	546.1	714.5	915.5	1130.5	1332.6	1503.4	1630.1
117.5°	306.7	335.8	379.9	443.8	547.2	694.8	872.5	1058.4	1237.4	1394.2	1525.5
120°	331.1	360.2	402.0	462.4	551.9	682.0	840.0	1003.8	1160.7	1300.1	1417.5
122.5°	353.2	384.6	425.2	479.8	560.0	673.9	813.3	960.8	1099.1	1225.7	1332.6
125°	375.3	406.6	447.3	498.4	568.1	666.9	791.2	923.7	1050.3	1161.8	1254.8
127.5°	396.2	427.6	467.1	513.5	577.4	663.4	770.3	890.0	1005.0	1107.2	1193.2
130°	414.8	446.1	484.5	528.6	586.7	659.9	754.0	858.6	963.2	1057.3	1136.3
132.5°	432.2	462.4	499.6	542.6	593.7	658.8	738.9	829.6	923.7	1009.6	1084.0
135°	447.3	478.7	514.7	554.2	600.7	657.6	726.2	804.0	886.5	962.0	1028.2
137.5°	461.3	490.3	525.2	563.5	605.3	655.3	714.5	779.6	849.3	916.7	976.0
140°	472.9	501.9	535.6	570.5	610.0	654.1	704.1	758.7	817.9	873.7	923.7
142.5°	484.5	511.2	543.7	577.4	613.5	651.8	694.8	738.9	787.7	834.2	876.0
145°	493.8	520.5	550.7	582.1	614.6	649.5	686.7	723.8	762.2	799.4	833.0
147.5°	505.4	528.6	556.5	585.6	614.6	646.0	678.5	711.1	742.4	773.8	798.2
150°	514.7	535.6	562.3	586.7	614.6	641.3	670.4	697.1	723.8	748.2	770.3
152.5°	524.0	543.7	565.8	589.1	611.1	635.5	661.1	684.3	706.4	727.3	744.7
155°	534.4	550.7	570.5	589.1	608.8	628.6	651.8	671.5	690.1	707.6	721.5
157.5°	543.7	556.5	572.8	590.2	605.3	622.8	641.3	657.6	673.9	687.8	699.4
160°	550.7	562.3	576.3	590.2	603.0	615.8	630.9	646.0	658.8	670.4	678.5
162.5°	556.5	565.8	577.4	589.1	598.4	608.8	620.4	632.0	642.5	653.0	659.9
165°	561.2	569.3	578.6	586.7	593.7	601.8	611.1	620.4	627.4	635.5	641.3
167.5°	565.8	571.6	578.6	585.6	589.1	594.9	601.8	610.0	615.8	620.4	625.1
170°	569.3	571.6	577.4	582.1	584.4	587.9	593.7	599.5	603.0	607.6	610.0
172.5°	571.6	572.8	577.4	580.9	580.9	582.1	585.6	590.2	592.5	596.0	597.2
175°	572.8	574.0	576.3	578.6	577.4	577.4	579.8	582.1	583.2	585.6	585.6
177.5°	574.0	574.0	575.1	577.4	575.1	574.0	575.1	576.3	577.4	578.6	578.6
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2206.4	2206.4	2206.4	2206.4
2.5°	1961.1	1957.6	1943.2	1928.9
5°	1662.7	1650.4	1646.3	1642.2
7.5°	1452.8	1451.8	1430.3	1408.8
10°	1268.0	1269.5	1250.1	1230.6
12.5°	1135.9	1123.1	1121.6	1120.1
15°	1036.6	1024.9	1022.8	1020.8
17.5°	966.5	959.3	957.3	955.2
20°	913.3	909.2	905.6	902.0
22.5°	867.2	862.1	859.0	855.9
25°	822.6	818.0	817.0	816.0
27.5°	782.7	777.1	777.1	777.1
30°	744.8	741.3	739.7	738.2
32.5°	709.5	706.4	706.4	706.4
35°	676.2	674.7	672.7	670.6
37.5°	646.0	646.0	645.0	644.0
40°	616.9	618.4	618.4	618.4
42.5°	590.2	591.8	591.8	591.8
45°	562.6	565.2	566.2	567.2
47.5°	535.5	539.6	540.6	541.6
50°	508.8	511.9	512.4	512.9
52.5°	481.7	485.3	487.9	490.4
55°	453.0	456.6	458.2	459.7
57.5°	422.3	425.9	426.4	426.9
60°	388.5	392.1	393.2	394.2
62.5°	356.3	358.3	359.4	360.4
65°	319.4	322.5	324.6	326.6
67.5°	284.1	286.7	286.7	286.7
70°	244.7	245.7	247.3	248.8
72.5°	208.3	208.9	208.9	208.9
75°	170.0	171.0	171.5	172.0
77.5°	133.6	134.1	134.1	134.1
80°	97.8	97.3	97.3	97.3
82.5°	67.1	65.5	65.5	65.5
85°	38.4	37.9	38.4	38.9
87.5°	17.4	17.4	17.4	17.4
90°	32.5	33.7	34.9	33.7
92.5°	67.4	62.7	63.9	61.6
95°	158.0	147.6	139.4	134.8
97.5°	361.3	317.2	289.3	276.5
100°	857.4	772.6	727.3	728.5
102.5°	1286.2	1223.4	1187.4	1153.7
105°	1565.0	1520.9	1483.7	1477.9
107.5°	1738.1	1717.2	1702.1	1689.3
110°	1805.5	1814.8	1812.5	1810.2



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	1788.1	1821.8	1833.4	1834.6
115°	1717.2	1768.3	1791.6	1797.4
117.5°	1616.1	1673.1	1707.9	1716.0
120°	1509.2	1574.3	1602.2	1609.2
122.5°	1411.6	1468.6	1499.9	1509.2
125°	1329.2	1380.3	1409.3	1417.5
127.5°	1260.6	1304.8	1331.5	1338.4
130°	1197.9	1239.7	1264.1	1273.4
132.5°	1140.9	1182.8	1203.7	1209.5
135°	1085.2	1120.0	1140.9	1149.1
137.5°	1024.7	1060.8	1078.2	1085.2
140°	967.8	1000.4	1018.9	1017.8
142.5°	912.1	939.9	956.2	955.0
145°	862.1	886.5	895.8	898.1
147.5°	821.4	838.9	848.1	849.3
150°	787.7	800.5	807.5	807.5
152.5°	757.5	769.1	772.6	772.6
155°	732.0	741.3	743.6	744.7
157.5°	708.7	715.7	718.0	718.0
160°	686.7	693.6	693.6	692.5
162.5°	664.6	670.4	670.4	669.2
165°	646.0	650.6	649.5	649.5
167.5°	627.4	630.9	629.7	629.7
170°	611.1	613.5	612.3	612.3
172.5°	597.2	599.5	597.2	596.0
175°	585.6	586.7	585.6	584.4
177.5°	577.4	578.6	576.3	576.3
180°	574.0	574.0	574.0	574.0



TEST NUMBER: P831617

CATALOG NUMBER: S123DIP-S775D1195U835-4F0-1E-UDD-G4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.10	14.89	15.10	15.90	17.24	16.33	17.12	17.34	18.13	19.47
	3H	15.74	16.45	16.76	17.46	18.83	17.75	18.46	18.77	19.48	20.84
	4H	16.31	16.98	17.34	18.00	19.38	18.20	18.87	19.23	19.89	21.26
	6H	16.68	17.30	17.72	18.32	19.71	18.47	19.09	19.51	20.11	21.50
	8H	16.78	17.36	17.82	18.40	19.78	18.53	19.12	19.58	20.16	21.54
	12H	16.82	17.37	17.87	18.41	19.81	18.55	19.11	19.60	20.14	21.54
4H	2H	14.66	15.33	15.70	16.35	17.73	16.49	17.16	17.52	18.18	19.55
	3H	16.49	17.04	17.53	18.09	19.48	18.10	18.66	19.14	19.71	21.09
	4H	17.18	17.69	18.23	18.73	20.14	18.68	19.19	19.73	20.23	21.64
	6H	17.65	18.09	18.71	19.16	20.56	19.08	19.52	20.14	20.59	21.99
	8H	17.79	18.20	18.85	19.26	20.67	19.19	19.60	20.25	20.66	22.08
	12H	17.85	18.22	18.93	19.29	20.72	19.24	19.60	20.31	20.68	22.10
8H	4H	17.44	17.85	18.50	18.91	20.33	18.78	19.19	19.84	20.25	21.67
	6H	18.03	18.37	19.11	19.47	20.88	19.28	19.62	20.37	20.72	22.13
	8H	18.24	18.53	19.33	19.62	21.05	19.46	19.76	20.55	20.84	22.27
	12H	18.36	18.62	19.45	19.70	21.17	19.56	19.82	20.65	20.90	22.37
12H	4H	17.44	17.81	18.52	18.88	20.30	18.76	19.12	19.83	20.20	21.62
	6H	18.08	18.38	19.17	19.46	20.89	19.30	19.59	20.39	20.68	22.11
	8H	18.31	18.57	19.40	19.65	21.12	19.49	19.75	20.59	20.83	22.31