

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331883-840

Luminaire Tested: **S123DIP-S340D805U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331883-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U840-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4709.2 lumens
Efficiency: N/A
Efficacy: 150.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	52	50	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	35	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	31	27	27	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5226	5226	5226	5226
5°	6232	5249	4652	5249
10°	7802	5223	4203	5223
15°	9569	5180	3911	5180
20°	11399	5116	3725	5116
25°	12105	5035	3682	5035
30°	10376	4977	3701	4977
35°	7215	4893	3741	4893
40°	5435	4796	3729	4796
45°	4512	4652	3682	4652
50°	4042	4357	3647	4357
55°	3780	4040	3603	4040
60°	3546	3707	3565	3707
65°	3331	3380	3451	3380
70°	3125	3006	3286	3006
75°	2799	2633	3015	2633
80°	2448	2157	2597	2157
85°	1927	1568	1741	1568



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.8	1.0
10°-20°	153.4	3.3
20°-30°	257.4	5.5
30°-40°	291.5	6.2
40°-50°	261.4	5.6
50°-60°	210.9	4.5
60°-70°	147.0	3.1
70°-80°	77.3	1.6
80°-90°	21.9	0.5
90°-100°	38.6	0.8
100°-110°	184.1	3.9
110°-120°	442.3	9.4
120°-130°	563.2	12.0
130°-140°	601.8	12.8
140°-150°	562.7	11.9
150°-160°	453.9	9.6
160°-170°	293.0	6.2
170°-180°	101.0	2.1
0°-30°	458.6	9.7
0°-40°	750.1	15.9
0°-60°	1222.4	26.0
0°-90°	1468.6	31.2
90°-120°	665.1	14.1
90°-150°	2392.8	50.8
90°-180°	3241.0	68.8
0°-180°	4709.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	486	486	486	486	486	
5°	577	486	430	486	577	60
15°	859	465	351	465	859	248
25°	1019	424	310	424	1019	447
35°	549	372	285	372	549	357
45°	296	306	242	306	296	235
55°	201	215	192	215	201	181
65°	131	133	136	133	131	130
75°	67	63	72	63	67	72
85°	16	13	14	13	16	19
90°	24	1	24	1	24	12
95°	30	48	30	48	30	25
105°	35	235	35	235	35	79
115°	464	441	464	441	464	429
125°	635	622	635	622	635	567
135°	782	774	782	774	782	603
145°	902	894	902	894	902	563
155°	983	984	983	984	983	453
165°	1036	1038	1036	1038	1036	292
175°	1059	1063	1059	1063	1059	101
180°	1063	1063	1063	1063	1063	



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	515.3	514.9	514.0	514.7	513.2	511.2	511.0	509.1	503.6	503.3	501.8
5°	576.8	575.0	574.7	574.5	571.2	566.7	558.3	557.5	546.2	540.7	533.8
7.5°	656.6	657.5	654.1	651.2	641.1	634.4	625.3	613.7	599.9	585.7	576.4
10°	713.8	721.5	712.0	705.3	699.2	687.7	674.3	657.5	640.9	621.4	606.5
12.5°	775.2	778.9	777.0	770.8	761.3	743.8	720.0	701.6	686.2	653.7	640.6
15°	858.7	873.0	863.8	842.7	843.1	826.5	795.5	761.3	743.2	714.7	675.9
17.5°	947.8	949.5	945.6	928.0	916.3	893.2	864.5	831.9	795.2	760.7	719.5
20°	995.1	993.7	985.5	976.3	956.1	938.3	907.0	870.5	823.4	789.5	744.6
22.5°	1021.5	1019.2	1015.2	1007.5	990.8	971.6	943.4	903.6	858.8	812.1	760.2
25°	1019.2	1022.2	1022.7	1020.6	1014.7	1003.2	981.1	949.3	904.6	844.6	790.5
27.5°	927.0	931.3	943.8	955.0	967.5	980.2	978.5	962.7	929.6	877.8	811.6
30°	834.8	825.3	848.6	878.0	898.0	933.3	953.0	954.2	935.6	891.2	826.7
32.5°	706.7	717.1	727.4	763.6	807.3	846.9	886.3	917.9	921.5	891.9	835.6
35°	549.1	562.1	580.9	599.7	646.7	687.2	756.4	816.6	864.5	870.9	836.4
37.5°	442.5	448.9	460.8	479.7	510.4	558.5	611.9	688.0	757.6	809.3	811.5
40°	386.8	388.7	402.0	416.4	441.3	480.9	529.1	596.4	679.6	751.9	782.0
42.5°	345.0	349.1	354.9	368.6	388.5	418.2	463.0	518.7	595.0	678.1	737.0
45°	296.4	301.1	304.7	313.9	328.0	348.0	379.2	430.1	488.2	574.0	653.3
47.5°	264.4	264.7	267.3	274.3	283.9	298.9	321.0	353.7	407.0	476.7	558.1
50°	241.4	245.1	246.1	251.5	259.0	270.0	288.4	316.2	359.9	421.1	495.9
52.5°	225.2	226.3	228.9	232.9	239.4	248.0	264.0	285.7	320.0	372.2	441.0
55°	201.4	201.4	204.0	207.0	210.8	218.5	229.1	245.1	271.2	311.7	368.7
57.5°	179.4	180.6	182.4	183.3	186.5	191.7	200.5	212.7	232.1	263.3	308.5
60°	164.7	166.8	166.5	168.4	171.3	175.3	182.8	192.7	210.1	235.0	273.2
62.5°	151.9	151.8	151.7	154.0	156.7	160.6	165.5	174.0	188.8	211.0	243.4
65°	130.8	130.4	132.0	133.4	134.3	137.1	140.9	148.5	158.3	174.8	200.0
67.5°	112.1	110.7	111.6	112.1	113.7	115.9	119.5	124.1	131.9	145.1	164.1
70°	99.3	98.1	97.9	98.4	99.8	101.4	104.0	108.5	115.7	126.3	140.2
72.5°	86.1	85.3	85.2	86.3	86.9	88.1	89.9	93.9	99.8	107.8	120.7
75°	67.3	67.3	67.3	67.6	68.3	69.2	70.6	72.7	77.2	82.8	91.5
77.5°	50.4	50.4	50.1	50.1	51.1	51.5	51.8	53.8	56.4	60.1	66.4
80°	39.5	38.4	38.8	39.5	40.0	40.2	40.9	41.4	43.5	45.6	50.1
82.5°	29.4	28.4	28.5	29.6	29.7	29.9	30.6	31.2	32.0	33.9	36.4
85°	15.6	15.6	15.8	15.8	16.0	15.8	16.5	16.7	16.7	17.9	19.3
87.5°	10.4	9.9	10.1	10.2	9.9	10.0	10.0	10.1	10.1	10.2	9.9
90°	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4	19.7	19.0	16.7
92.5°	26.3	26.0	25.8	25.5	25.3	24.7	23.5	22.4	21.3	20.2	18.5
95°	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0	25.8	24.4	22.5
97.5°	32.5	32.3	32.2	32.0	31.8	31.0	29.6	28.3	26.9	25.4	38.1
100°	33.1	33.0	32.8	32.6	32.4	31.7	30.3	28.9	27.5	26.1	53.4
102.5°	33.8	33.4	33.1	32.8	32.5	34.5	38.9	43.2	47.6	51.9	81.8
105°	34.7	34.4	34.0	33.7	33.3	48.7	79.8	110.8	141.9	172.9	188.6
107.5°	109.1	132.5	155.9	179.4	202.7	225.8	248.6	271.4	294.2	316.9	314.4
110°	217.1	242.2	267.3	292.4	317.5	333.0	338.7	344.5	350.3	356.1	354.2



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.5	377.8	383.0	388.4	393.6	396.3	396.2	396.1	396.0	395.9	393.9
115°	464.2	463.5	462.8	462.1	461.4	460.2	458.5	456.7	454.9	453.2	451.6
117.5°	515.7	515.5	515.4	515.3	515.1	514.3	513.0	511.6	510.2	508.8	508.0
120°	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.5	546.1	544.7	544.2
122.5°	585.8	585.7	585.5	585.4	585.2	584.7	583.7	582.7	581.8	580.8	580.1
125°	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3	632.0	631.6	630.9
127.5°	681.9	682.2	682.6	682.9	683.2	683.1	682.6	682.0	681.5	680.9	680.0
130°	712.2	712.5	712.9	713.2	713.6	713.4	712.7	712.0	711.2	710.5	709.8
132.5°	739.9	740.4	740.9	741.4	741.8	741.7	741.0	740.3	739.7	739.0	738.4
135°	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5	782.9	782.4	781.7
137.5°	822.3	822.7	823.0	823.4	823.7	823.5	822.6	821.8	821.0	820.1	819.7
140°	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2	845.5	844.8	844.2
142.5°	868.5	869.0	869.4	869.9	870.4	870.4	869.8	869.3	868.7	868.2	867.6
145°	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5	901.2	900.8	900.5
147.5°	927.7	928.5	929.3	930.1	930.9	931.1	930.8	930.4	930.1	929.7	929.4
150°	946.6	947.2	947.7	948.2	948.8	948.8	948.5	948.1	947.8	947.5	947.1
152.5°	961.8	962.6	963.4	964.2	965.0	965.1	964.4	963.8	963.2	962.6	962.4
155°	982.9	984.0	985.0	986.1	987.1	987.2	986.3	985.5	984.6	983.7	983.5
157.5°	1000.8	1002.2	1003.5	1004.9	1006.2	1006.4	1005.3	1004.3	1003.3	1002.2	1002.4
160°	1012.2	1013.4	1014.6	1015.8	1017.0	1017.1	1016.1	1015.0	1014.0	1012.9	1013.1
162.5°	1022.9	1024.0	1025.0	1026.1	1027.2	1027.1	1026.0	1024.8	1023.6	1022.4	1022.6
165°	1035.8	1037.0	1038.2	1039.6	1040.8	1040.7	1039.3	1037.8	1036.4	1035.0	1035.2
167.5°	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1	1045.1
170°	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9	1050.9
172.5°	1054.0	1055.5	1057.1	1058.6	1060.2	1060.3	1058.8	1057.4	1056.0	1054.6	1054.5
175°	1058.7	1060.2	1061.6	1063.0	1064.3	1064.4	1063.2	1062.0	1060.8	1059.6	1059.3
177.5°	1060.2	1061.6	1063.0	1064.4	1065.8	1065.9	1064.8	1063.7	1062.6	1061.4	1061.3
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	500.6	499.2	497.7	495.0	492.7	489.6	488.6	487.5	484.0	481.1	478.8
5°	531.2	525.5	517.4	509.8	503.7	495.4	490.8	485.8	478.8	472.4	467.3
7.5°	563.2	552.1	539.3	525.5	512.6	500.2	490.2	481.2	471.3	462.0	454.6
10°	588.7	572.6	554.7	535.4	519.0	503.0	489.6	477.9	465.1	454.0	444.8
12.5°	617.6	593.9	569.3	545.8	526.3	504.1	487.9	472.9	458.5	445.2	434.9
15°	651.9	621.8	592.6	560.4	530.8	503.0	483.7	464.8	448.2	434.5	421.3
17.5°	683.2	649.0	610.6	571.4	535.6	502.7	475.7	454.4	433.5	416.9	403.7
20°	700.8	662.1	618.5	577.8	538.3	501.6	471.9	446.6	423.9	406.3	391.5
22.5°	716.1	670.7	625.6	582.1	538.1	498.6	464.9	438.8	414.3	397.1	381.3
25°	732.0	677.5	632.4	581.4	532.2	491.2	453.6	423.9	399.5	379.2	363.0
27.5°	745.5	677.1	623.5	568.6	522.8	481.8	441.6	409.8	383.8	361.8	345.4
30°	754.5	678.0	614.3	560.0	513.8	471.5	432.4	400.4	373.1	350.8	335.3
32.5°	760.1	677.4	605.8	547.9	499.5	462.0	422.4	389.3	361.2	339.3	324.4
35°	763.5	673.3	591.2	523.0	476.5	439.9	406.8	372.4	343.1	322.6	305.6
37.5°	756.8	664.6	574.3	499.0	448.0	412.1	384.2	355.0	326.8	304.3	289.6
40°	746.5	658.9	561.1	482.0	428.4	393.8	370.1	341.3	313.6	292.2	278.5
42.5°	726.7	647.5	546.6	463.2	408.1	373.5	351.6	327.6	301.3	281.2	267.6
45°	678.5	622.5	524.8	435.0	378.1	342.3	323.1	305.6	281.9	262.4	250.5
47.5°	611.6	584.9	493.4	405.3	346.7	312.4	292.3	278.3	260.9	245.1	233.9
50°	565.1	554.0	472.2	384.9	325.9	292.2	272.9	260.2	247.7	232.0	221.7
52.5°	511.5	518.3	447.4	363.9	304.6	271.5	253.4	243.3	232.0	218.9	210.0
55°	436.0	460.6	404.5	328.4	272.9	241.4	224.2	215.3	208.6	199.0	191.3
57.5°	365.3	396.7	358.0	292.0	241.8	214.6	198.1	188.4	184.2	179.2	173.0
60°	323.3	354.3	324.9	267.5	221.0	195.0	180.5	172.2	167.9	164.4	159.3
62.5°	285.8	317.2	292.6	242.7	200.4	176.4	163.7	155.6	152.4	150.6	146.1
65°	234.3	261.4	244.9	204.0	171.1	149.9	138.4	132.7	129.7	129.0	126.1
67.5°	190.7	211.3	199.3	169.2	143.3	125.0	115.2	110.4	108.1	107.8	105.6
70°	162.1	181.4	172.2	144.9	122.6	108.3	99.8	95.5	94.1	93.9	92.7
72.5°	139.9	153.3	146.0	123.3	106.0	93.0	86.7	82.3	80.8	81.1	80.3
75°	103.5	113.6	109.4	93.6	79.8	71.3	66.1	63.3	61.9	62.6	61.6
77.5°	74.5	80.9	77.1	66.1	57.6	51.5	47.7	45.9	44.6	44.6	44.2
80°	56.2	60.0	57.9	51.3	44.2	39.1	36.0	34.8	34.1	33.8	33.6
82.5°	40.1	43.2	40.7	36.3	31.4	28.3	26.6	25.0	24.5	24.6	24.4
85°	20.2	21.4	20.5	17.7	15.8	14.3	13.4	12.7	12.2	12.4	12.0
87.5°	9.8	9.6	8.6	7.4	6.7	5.8	5.4	4.6	4.6	5.0	5.2
90°	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	16.8	15.0	13.3	12.7	13.2	13.7	14.2	14.6	14.2	13.7	13.2
95°	20.6	18.7	16.8	19.4	26.6	33.7	41.0	48.2	41.0	33.7	26.6
97.5°	50.7	63.3	75.9	83.9	87.2	90.4	93.6	96.7	93.6	90.4	87.2
100°	80.8	108.2	135.5	147.4	143.9	140.5	136.9	133.4	136.9	140.5	143.9
102.5°	111.7	141.7	171.6	185.2	182.7	180.2	177.6	175.1	177.6	180.2	182.7
105°	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3	237.2	239.1	241.1
107.5°	311.9	309.4	306.9	304.9	303.4	301.8	300.3	298.7	300.3	301.8	303.4
110°	352.2	350.3	348.3	346.7	345.3	343.9	342.4	341.0	342.4	343.9	345.3



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	392.0	390.1	388.1	386.6	385.3	384.1	382.7	381.5	382.7	384.1	385.3
115°	450.0	448.5	446.9	445.6	444.5	443.4	442.4	441.3	442.4	443.4	444.5
117.5°	507.2	506.3	505.5	504.4	503.2	501.9	500.6	499.3	500.6	501.9	503.2
120°	543.7	543.2	542.7	541.6	540.0	538.5	536.8	535.3	536.8	538.5	540.0
122.5°	579.5	578.8	578.0	577.1	575.8	574.5	573.2	571.9	573.2	574.5	575.8
125°	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.2	623.5	624.9	626.3
127.5°	679.2	678.3	677.5	676.4	675.0	673.6	672.2	670.8	672.2	673.6	675.0
130°	709.1	708.4	707.7	706.7	705.3	703.9	702.5	701.0	702.5	703.9	705.3
132.5°	737.8	737.3	736.7	735.8	734.4	733.0	731.5	730.1	731.5	733.0	734.4
135°	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5	775.6	776.6	777.7
137.5°	819.4	819.0	818.6	817.7	816.4	815.1	813.7	812.4	813.7	815.1	816.4
140°	843.7	843.2	842.6	841.9	840.8	839.8	838.7	837.7	838.7	839.8	840.8
142.5°	867.1	866.6	866.1	865.3	864.2	863.1	862.1	861.0	862.1	863.1	864.2
145°	900.1	899.8	899.4	898.7	897.4	896.2	894.9	893.7	894.9	896.2	897.4
147.5°	929.0	928.7	928.4	927.8	927.0	926.1	925.3	924.5	925.3	926.1	927.0
150°	946.7	946.3	946.0	945.5	945.0	944.5	944.0	943.4	944.0	944.5	945.0
152.5°	962.1	961.9	961.7	961.5	961.3	961.0	960.8	960.5	960.8	961.0	961.3
155°	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5	984.2	983.8	983.5
157.5°	1002.6	1002.7	1002.9	1003.0	1003.0	1003.1	1003.1	1003.1	1003.1	1003.1	1003.0
160°	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5	1014.3	1014.2	1014.0
162.5°	1022.8	1022.9	1023.1	1023.4	1023.9	1024.3	1024.8	1025.2	1024.8	1024.3	1023.9
165°	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.6	1038.2	1037.6	1037.1	1036.6
167.5°	1045.1	1045.1	1045.1	1045.5	1046.2	1046.9	1047.6	1048.3	1047.6	1046.9	1046.2
170°	1050.9	1050.9	1050.9	1051.2	1051.9	1052.6	1053.3	1054.0	1053.3	1052.6	1051.9
172.5°	1054.3	1054.2	1054.1	1054.4	1055.2	1056.1	1056.9	1057.7	1056.9	1056.1	1055.2
175°	1059.1	1058.9	1058.8	1059.1	1060.1	1061.0	1061.8	1062.7	1061.8	1061.0	1060.1
177.5°	1061.2	1061.0	1060.9	1061.2	1061.9	1062.6	1063.3	1063.9	1063.3	1062.6	1061.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	477.5	476.2	474.3	471.5	469.2	465.6	465.6	466.2	466.2	466.1	465.6
5°	463.0	459.5	455.2	450.3	445.1	439.9	439.0	437.1	435.8	434.7	433.6
7.5°	447.7	441.4	435.3	428.4	422.0	416.9	413.2	410.2	408.3	406.2	404.7
10°	437.4	429.6	422.3	415.1	407.0	400.6	396.7	393.8	391.7	389.8	388.9
12.5°	425.2	416.3	408.2	401.2	392.5	386.0	382.1	380.8	378.4	374.4	372.3
15°	407.3	399.0	389.4	378.8	374.6	366.6	362.0	359.9	358.5	355.5	354.6
17.5°	391.9	381.2	370.3	362.4	354.6	348.1	345.6	343.0	341.1	338.6	337.8
20°	379.7	370.1	360.2	351.7	343.5	336.4	334.3	332.4	330.5	329.4	328.4
22.5°	367.3	357.7	349.4	341.5	332.8	328.1	325.9	323.8	322.4	321.6	320.7
25°	349.8	341.3	332.1	325.2	318.1	315.0	313.6	312.5	311.4	310.3	310.0
27.5°	334.3	325.0	317.6	310.9	305.9	303.4	301.9	301.4	301.6	302.1	302.4
30°	322.6	314.1	308.0	302.4	297.6	295.3	295.0	295.0	296.0	296.2	296.7
32.5°	311.8	304.9	298.7	293.3	289.7	288.1	289.0	289.0	289.7	290.3	291.2
35°	296.2	290.0	285.4	280.6	277.6	278.3	278.8	279.2	280.4	281.9	282.8
37.5°	281.2	276.0	271.0	267.4	266.0	267.2	268.4	269.3	270.7	271.9	272.8
40°	270.5	266.5	261.9	258.5	259.0	259.7	260.6	261.9	263.1	263.8	264.7
42.5°	260.5	256.4	252.8	250.0	250.7	251.7	252.2	252.8	254.2	255.5	256.0
45°	245.4	242.1	238.8	237.1	237.6	238.1	238.5	239.2	240.4	241.4	241.7
47.5°	228.3	226.0	223.8	222.2	223.0	222.8	223.4	224.9	225.2	225.8	227.1
50°	217.4	215.3	212.7	212.2	212.2	212.2	212.5	214.3	214.3	215.3	216.2
52.5°	205.3	204.0	202.4	201.5	201.1	201.1	202.1	203.0	203.4	204.7	205.7
55°	187.5	186.1	184.7	184.0	183.5	184.0	185.8	186.3	187.5	188.2	188.9
57.5°	169.0	167.8	166.7	166.3	166.2	166.8	167.8	169.3	169.6	171.8	172.8
60°	156.7	155.0	154.1	154.1	153.6	155.7	155.3	157.6	158.1	159.6	161.2
62.5°	144.1	141.9	141.5	141.5	142.2	142.8	143.4	144.4	145.7	147.4	148.8
65°	123.7	122.6	124.2	124.0	123.5	124.9	124.9	126.1	127.5	129.2	131.8
67.5°	104.5	103.9	104.0	104.0	104.7	105.5	106.2	107.2	109.0	110.7	112.4
70°	91.5	92.2	91.1	92.0	92.7	92.9	93.4	94.8	96.6	97.9	99.8
72.5°	78.9	78.9	79.0	79.4	80.1	80.5	81.0	82.6	84.6	85.6	87.2
75°	60.7	60.5	61.2	61.2	62.3	62.8	63.3	64.0	65.8	67.3	68.5
77.5°	44.3	44.6	44.4	45.2	44.9	45.0	46.5	47.2	47.4	50.2	50.8
80°	33.4	33.8	34.1	34.3	34.5	34.1	35.7	36.5	36.5	38.1	39.3
82.5°	24.0	24.2	24.8	25.1	25.1	25.7	25.8	26.3	26.9	27.6	29.1
85°	12.0	12.7	12.9	12.7	12.9	12.4	13.1	13.4	13.6	13.6	13.6
87.5°	5.4	6.0	6.2	6.9	7.1	7.8	7.9	7.7	7.8	8.5	7.9
90°	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4	21.0	21.7	22.3
92.5°	12.7	13.3	15.0	16.8	18.5	20.2	21.3	22.4	23.5	24.7	25.3
95°	19.4	16.8	18.7	20.6	22.5	24.4	25.8	27.0	28.2	29.4	30.0
97.5°	83.9	75.9	63.3	50.7	38.1	25.4	26.9	28.3	29.6	31.0	31.8
100°	147.4	135.5	108.2	80.8	53.4	26.1	27.5	28.9	30.3	31.7	32.4
102.5°	185.2	171.6	141.7	111.7	81.8	51.9	47.6	43.2	38.9	34.5	32.5
105°	243.0	236.1	220.3	204.5	188.6	172.9	141.9	110.8	79.8	48.7	33.3
107.5°	304.9	306.9	309.4	311.9	314.4	316.9	294.2	271.4	248.6	225.8	202.7
110°	346.7	348.3	350.3	352.2	354.2	356.1	350.3	344.5	338.7	333.0	317.5



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	386.6	388.1	390.1	392.0	393.9	395.9	396.0	396.1	396.2	396.3	393.6
115°	445.6	446.9	448.5	450.0	451.6	453.2	454.9	456.7	458.5	460.2	461.4
117.5°	504.4	505.5	506.3	507.2	508.0	508.8	510.2	511.6	513.0	514.3	515.1
120°	541.6	542.7	543.2	543.7	544.2	544.7	546.1	547.5	549.0	550.4	551.1
122.5°	577.1	578.0	578.8	579.5	580.1	580.8	581.8	582.7	583.7	584.7	585.2
125°	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3	632.7	633.0	633.4
127.5°	676.4	677.5	678.3	679.2	680.0	680.9	681.5	682.0	682.6	683.1	683.2
130°	706.7	707.7	708.4	709.1	709.8	710.5	711.2	712.0	712.7	713.4	713.6
132.5°	735.8	736.7	737.3	737.8	738.4	739.0	739.7	740.3	741.0	741.7	741.8
135°	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5	784.0	784.5	784.5
137.5°	817.7	818.6	819.0	819.4	819.7	820.1	821.0	821.8	822.6	823.5	823.7
140°	841.9	842.6	843.2	843.7	844.2	844.8	845.5	846.2	846.9	847.6	847.8
142.5°	865.3	866.1	866.6	867.1	867.6	868.2	868.7	869.3	869.8	870.4	870.4
145°	898.7	899.4	899.8	900.1	900.5	900.8	901.2	901.5	901.9	902.2	902.4
147.5°	927.8	928.4	928.7	929.0	929.4	929.7	930.1	930.4	930.8	931.1	930.9
150°	945.5	946.0	946.3	946.7	947.1	947.5	947.8	948.1	948.5	948.8	948.8
152.5°	961.5	961.7	961.9	962.1	962.4	962.6	963.2	963.8	964.4	965.1	965.0
155°	983.1	983.0	983.2	983.4	983.5	983.7	984.6	985.5	986.3	987.2	987.1
157.5°	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3	1004.3	1005.3	1006.4	1006.2
160°	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0	1016.1	1017.1	1017.0
162.5°	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6	1024.8	1026.0	1027.1	1027.2
165°	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.8	1039.3	1040.7	1040.8
167.5°	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8
170°	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4
172.5°	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0	1057.4	1058.8	1060.3	1060.2
175°	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8	1062.0	1063.2	1064.4	1064.3
177.5°	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6	1063.7	1064.8	1065.9	1065.8
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	464.3	464.1	465.4	464.5	465.4	464.1	464.3	465.6	466.1	466.2	466.2
5°	432.2	432.9	430.5	430.5	430.5	432.9	432.2	433.6	434.7	435.8	437.1
7.5°	403.5	402.5	402.6	401.3	402.6	402.5	403.5	404.7	406.2	408.3	410.2
10°	386.1	384.7	384.2	384.5	384.2	384.7	386.1	388.9	389.8	391.7	393.8
12.5°	371.5	371.3	368.2	368.2	368.2	371.3	371.5	372.3	374.4	378.4	380.8
15°	354.6	350.1	349.6	351.0	349.6	350.1	354.6	354.6	355.5	358.5	359.9
17.5°	337.5	335.1	335.3	334.6	335.3	335.1	337.5	337.8	338.6	341.1	343.0
20°	328.4	327.0	326.8	325.2	326.8	327.0	328.4	328.4	329.4	330.5	332.4
22.5°	320.1	319.7	319.8	318.0	319.8	319.7	320.1	320.7	321.6	322.4	323.8
25°	309.8	311.0	310.0	310.0	310.0	311.0	309.8	310.0	310.3	311.4	312.5
27.5°	302.9	302.9	302.4	302.4	302.4	302.9	302.9	302.4	302.1	301.6	301.4
30°	297.6	297.4	297.8	297.8	297.8	297.4	297.6	296.7	296.2	296.0	295.0
32.5°	292.4	292.7	292.8	293.0	292.8	292.7	292.4	291.2	290.3	289.7	289.0
35°	284.2	284.5	285.2	284.7	285.2	284.5	284.2	282.8	281.9	280.4	279.2
37.5°	273.2	274.3	274.1	274.4	274.1	274.3	273.2	272.8	271.9	270.7	269.3
40°	264.9	265.6	265.4	265.4	265.4	265.6	264.9	264.7	263.8	263.1	261.9
42.5°	256.4	256.9	256.3	256.0	256.3	256.9	256.4	256.0	255.5	254.2	252.8
45°	242.6	242.1	242.8	241.9	242.8	242.1	242.6	241.7	241.4	240.4	239.2
47.5°	227.0	227.5	227.7	228.4	227.7	227.5	227.0	227.1	225.8	225.2	224.9
50°	216.7	218.1	218.1	217.8	218.1	218.1	216.7	216.2	215.3	214.3	214.3
52.5°	206.5	207.1	208.1	208.0	208.1	207.1	206.5	205.7	204.7	203.4	203.0
55°	190.8	191.3	191.8	192.0	191.8	191.3	190.8	188.9	188.2	187.5	186.3
57.5°	174.5	174.3	175.4	175.8	175.4	174.3	174.5	172.8	171.8	169.6	169.3
60°	163.0	163.0	164.9	165.6	164.9	163.0	163.0	161.2	159.6	158.1	157.6
62.5°	150.8	151.6	153.4	152.5	153.4	151.6	150.8	148.8	147.4	145.7	144.4
65°	132.9	134.8	134.6	135.5	134.6	134.8	132.9	131.8	129.2	127.5	126.1
67.5°	114.2	115.4	117.1	117.2	117.1	115.4	114.2	112.4	110.7	109.0	107.2
70°	101.6	102.8	103.7	104.4	103.7	102.8	101.6	99.8	97.9	96.6	94.8
72.5°	89.4	90.0	92.3	91.3	92.3	90.0	89.4	87.2	85.6	84.6	82.6
75°	70.1	71.8	73.2	72.5	73.2	71.8	70.1	68.5	67.3	65.8	64.0
77.5°	51.8	53.5	54.1	53.5	54.1	53.5	51.8	50.8	50.2	47.4	47.2
80°	40.9	40.7	42.1	41.9	42.1	40.7	40.9	39.3	38.1	36.5	36.5
82.5°	30.0	29.8	30.4	30.6	30.4	29.8	30.0	29.1	27.6	26.9	26.3
85°	14.5	15.2	14.3	14.1	14.3	15.2	14.5	13.6	13.6	13.6	13.4
87.5°	7.9	8.0	7.9	7.8	7.9	8.0	7.9	7.9	8.5	7.8	7.7
90°	22.6	23.0	23.3	23.7	23.3	23.0	22.6	22.3	21.7	21.0	20.4
92.5°	25.5	25.8	26.0	26.3	26.0	25.8	25.5	25.3	24.7	23.5	22.4
95°	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	29.4	28.2	27.0
97.5°	32.0	32.2	32.3	32.5	32.3	32.2	32.0	31.8	31.0	29.6	28.3
100°	32.6	32.8	33.0	33.1	33.0	32.8	32.6	32.4	31.7	30.3	28.9
102.5°	32.8	33.1	33.4	33.8	33.4	33.1	32.8	32.5	34.5	38.9	43.2
105°	33.7	34.0	34.4	34.7	34.4	34.0	33.7	33.3	48.7	79.8	110.8
107.5°	179.4	155.9	132.5	109.1	132.5	155.9	179.4	202.7	225.8	248.6	271.4
110°	292.4	267.3	242.2	217.1	242.2	267.3	292.4	317.5	333.0	338.7	344.5



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	388.4	383.0	377.8	372.5	377.8	383.0	388.4	393.6	396.3	396.2	396.1
115°	462.1	462.8	463.5	464.2	463.5	462.8	462.1	461.4	460.2	458.5	456.7
117.5°	515.3	515.4	515.5	515.7	515.5	515.4	515.3	515.1	514.3	513.0	511.6
120°	551.1	551.1	551.1	551.1	551.1	551.1	551.1	551.1	550.4	549.0	547.5
122.5°	585.4	585.5	585.7	585.8	585.7	585.5	585.4	585.2	584.7	583.7	582.7
125°	633.7	634.1	634.4	634.8	634.4	634.1	633.7	633.4	633.0	632.7	632.3
127.5°	682.9	682.6	682.2	681.9	682.2	682.6	682.9	683.2	683.1	682.6	682.0
130°	713.2	712.9	712.5	712.2	712.5	712.9	713.2	713.6	713.4	712.7	712.0
132.5°	741.4	740.9	740.4	739.9	740.4	740.9	741.4	741.8	741.7	741.0	740.3
135°	784.0	783.5	782.9	782.4	782.9	783.5	784.0	784.5	784.5	784.0	783.5
137.5°	823.4	823.0	822.7	822.3	822.7	823.0	823.4	823.7	823.5	822.6	821.8
140°	847.4	847.1	846.7	846.4	846.7	847.1	847.4	847.8	847.6	846.9	846.2
142.5°	869.9	869.4	869.0	868.5	869.0	869.4	869.9	870.4	870.4	869.8	869.3
145°	902.4	902.4	902.4	902.4	902.4	902.4	902.4	902.4	902.2	901.9	901.5
147.5°	930.1	929.3	928.5	927.7	928.5	929.3	930.1	930.9	931.1	930.8	930.4
150°	948.2	947.7	947.2	946.6	947.2	947.7	948.2	948.8	948.8	948.5	948.1
152.5°	964.2	963.4	962.6	961.8	962.6	963.4	964.2	965.0	965.1	964.4	963.8
155°	986.1	985.0	984.0	982.9	984.0	985.0	986.1	987.1	987.2	986.3	985.5
157.5°	1004.9	1003.5	1002.2	1000.8	1002.2	1003.5	1004.9	1006.2	1006.4	1005.3	1004.3
160°	1015.8	1014.6	1013.4	1012.2	1013.4	1014.6	1015.8	1017.0	1017.1	1016.1	1015.0
162.5°	1026.1	1025.0	1024.0	1022.9	1024.0	1025.0	1026.1	1027.2	1027.1	1026.0	1024.8
165°	1039.6	1038.2	1037.0	1035.8	1037.0	1038.2	1039.6	1040.8	1040.7	1039.3	1037.8
167.5°	1049.4	1047.9	1046.5	1045.1	1046.5	1047.9	1049.4	1050.8	1050.8	1049.4	1047.9
170°	1055.0	1053.6	1052.3	1050.9	1052.3	1053.6	1055.0	1056.4	1056.4	1055.0	1053.6
172.5°	1058.6	1057.1	1055.5	1054.0	1055.5	1057.1	1058.6	1060.2	1060.3	1058.8	1057.4
175°	1063.0	1061.6	1060.2	1058.7	1060.2	1061.6	1063.0	1064.3	1064.4	1063.2	1062.0
177.5°	1064.4	1063.0	1061.6	1060.2	1061.6	1063.0	1064.4	1065.8	1065.9	1064.8	1063.7
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	465.6	465.6	469.2	471.5	474.3	476.2	477.5	478.8	481.1	484.0	487.5
5°	439.0	439.9	445.1	450.3	455.2	459.5	463.0	467.3	472.4	478.8	485.8
7.5°	413.2	416.9	422.0	428.4	435.3	441.4	447.7	454.6	462.0	471.3	481.2
10°	396.7	400.6	407.0	415.1	422.3	429.6	437.4	444.8	454.0	465.1	477.9
12.5°	382.1	386.0	392.5	401.2	408.2	416.3	425.2	434.9	445.2	458.5	472.9
15°	362.0	366.6	374.6	378.8	389.4	399.0	407.3	421.3	434.5	448.2	464.8
17.5°	345.6	348.1	354.6	362.4	370.3	381.2	391.9	403.7	416.9	433.5	454.4
20°	334.3	336.4	343.5	351.7	360.2	370.1	379.7	391.5	406.3	423.9	446.6
22.5°	325.9	328.1	332.8	341.5	349.4	357.7	367.3	381.3	397.1	414.3	438.8
25°	313.6	315.0	318.1	325.2	332.1	341.3	349.8	363.0	379.2	399.5	423.9
27.5°	301.9	303.4	305.9	310.9	317.6	325.0	334.3	345.4	361.8	383.8	409.8
30°	295.0	295.3	297.6	302.4	308.0	314.1	322.6	335.3	350.8	373.1	400.4
32.5°	289.0	288.1	289.7	293.3	298.7	304.9	311.8	324.4	339.3	361.2	389.3
35°	278.8	278.3	277.6	280.6	285.4	290.0	296.2	305.6	322.6	343.1	372.4
37.5°	268.4	267.2	266.0	267.4	271.0	276.0	281.2	289.6	304.3	326.8	355.0
40°	260.6	259.7	259.0	258.5	261.9	266.5	270.5	278.5	292.2	313.6	341.3
42.5°	252.2	251.7	250.7	250.0	252.8	256.4	260.5	267.6	281.2	301.3	327.6
45°	238.5	238.1	237.6	237.1	238.8	242.1	245.4	250.5	262.4	281.9	305.6
47.5°	223.4	222.8	223.0	222.2	223.8	226.0	228.3	233.9	245.1	260.9	278.3
50°	212.5	212.2	212.2	212.2	212.7	215.3	217.4	221.7	232.0	247.7	260.2
52.5°	202.1	201.1	201.1	201.5	202.4	204.0	205.3	210.0	218.9	232.0	243.3
55°	185.8	184.0	183.5	184.0	184.7	186.1	187.5	191.3	199.0	208.6	215.3
57.5°	167.8	166.8	166.2	166.3	166.7	167.8	169.0	173.0	179.2	184.2	188.4
60°	155.3	155.7	153.6	154.1	154.1	155.0	156.7	159.3	164.4	167.9	172.2
62.5°	143.4	142.8	142.2	141.5	141.5	141.9	144.1	146.1	150.6	152.4	155.6
65°	124.9	124.9	123.5	124.0	124.2	122.6	123.7	126.1	129.0	129.7	132.7
67.5°	106.2	105.5	104.7	104.0	104.0	103.9	104.5	105.6	107.8	108.1	110.4
70°	93.4	92.9	92.7	92.0	91.1	92.2	91.5	92.7	93.9	94.1	95.5
72.5°	81.0	80.5	80.1	79.4	79.0	78.9	78.9	80.3	81.1	80.8	82.3
75°	63.3	62.8	62.3	61.2	61.2	60.5	60.7	61.6	62.6	61.9	63.3
77.5°	46.5	45.0	44.9	45.2	44.4	44.6	44.3	44.2	44.6	44.6	45.9
80°	35.7	34.1	34.5	34.3	34.1	33.8	33.4	33.6	33.8	34.1	34.8
82.5°	25.8	25.7	25.1	25.1	24.8	24.2	24.0	24.4	24.6	24.5	25.0
85°	13.1	12.4	12.9	12.7	12.9	12.7	12.0	12.0	12.4	12.2	12.7
87.5°	7.9	7.8	7.1	6.9	6.2	6.0	5.4	5.2	5.0	4.6	4.6
90°	19.7	19.0	16.7	14.3	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	21.3	20.2	18.5	16.8	15.0	13.3	12.7	13.2	13.7	14.2	14.6
95°	25.8	24.4	22.5	20.6	18.7	16.8	19.4	26.6	33.7	41.0	48.2
97.5°	26.9	25.4	38.1	50.7	63.3	75.9	83.9	87.2	90.4	93.6	96.7
100°	27.5	26.1	53.4	80.8	108.2	135.5	147.4	143.9	140.5	136.9	133.4
102.5°	47.6	51.9	81.8	111.7	141.7	171.6	185.2	182.7	180.2	177.6	175.1
105°	141.9	172.9	188.6	204.5	220.3	236.1	243.0	241.1	239.1	237.2	235.3
107.5°	294.2	316.9	314.4	311.9	309.4	306.9	304.9	303.4	301.8	300.3	298.7
110°	350.3	356.1	354.2	352.2	350.3	348.3	346.7	345.3	343.9	342.4	341.0



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	396.0	395.9	393.9	392.0	390.1	388.1	386.6	385.3	384.1	382.7	381.5
115°	454.9	453.2	451.6	450.0	448.5	446.9	445.6	444.5	443.4	442.4	441.3
117.5°	510.2	508.8	508.0	507.2	506.3	505.5	504.4	503.2	501.9	500.6	499.3
120°	546.1	544.7	544.2	543.7	543.2	542.7	541.6	540.0	538.5	536.8	535.3
122.5°	581.8	580.8	580.1	579.5	578.8	578.0	577.1	575.8	574.5	573.2	571.9
125°	632.0	631.6	630.9	630.2	629.5	628.8	627.7	626.3	624.9	623.5	622.2
127.5°	681.5	680.9	680.0	679.2	678.3	677.5	676.4	675.0	673.6	672.2	670.8
130°	711.2	710.5	709.8	709.1	708.4	707.7	706.7	705.3	703.9	702.5	701.0
132.5°	739.7	739.0	738.4	737.8	737.3	736.7	735.8	734.4	733.0	731.5	730.1
135°	782.9	782.4	781.7	781.0	780.3	779.6	778.7	777.7	776.6	775.6	774.5
137.5°	821.0	820.1	819.7	819.4	819.0	818.6	817.7	816.4	815.1	813.7	812.4
140°	845.5	844.8	844.2	843.7	843.2	842.6	841.9	840.8	839.8	838.7	837.7
142.5°	868.7	868.2	867.6	867.1	866.6	866.1	865.3	864.2	863.1	862.1	861.0
145°	901.2	900.8	900.5	900.1	899.8	899.4	898.7	897.4	896.2	894.9	893.7
147.5°	930.1	929.7	929.4	929.0	928.7	928.4	927.8	927.0	926.1	925.3	924.5
150°	947.8	947.5	947.1	946.7	946.3	946.0	945.5	945.0	944.5	944.0	943.4
152.5°	963.2	962.6	962.4	962.1	961.9	961.7	961.5	961.3	961.0	960.8	960.5
155°	984.6	983.7	983.5	983.4	983.2	983.0	983.1	983.5	983.8	984.2	984.5
157.5°	1003.3	1002.2	1002.4	1002.6	1002.7	1002.9	1003.0	1003.0	1003.1	1003.1	1003.1
160°	1014.0	1012.9	1013.1	1013.3	1013.5	1013.6	1013.8	1014.0	1014.2	1014.3	1014.5
162.5°	1023.6	1022.4	1022.6	1022.8	1022.9	1023.1	1023.4	1023.9	1024.3	1024.8	1025.2
165°	1036.4	1035.0	1035.2	1035.4	1035.6	1035.7	1036.1	1036.6	1037.1	1037.6	1038.2
167.5°	1046.5	1045.1	1045.1	1045.1	1045.1	1045.1	1045.5	1046.2	1046.9	1047.6	1048.3
170°	1052.3	1050.9	1050.9	1050.9	1050.9	1050.9	1051.2	1051.9	1052.6	1053.3	1054.0
172.5°	1056.0	1054.6	1054.5	1054.3	1054.2	1054.1	1054.4	1055.2	1056.1	1056.9	1057.7
175°	1060.8	1059.6	1059.3	1059.1	1058.9	1058.8	1059.1	1060.1	1061.0	1061.8	1062.7
177.5°	1062.6	1061.4	1061.3	1061.2	1061.0	1060.9	1061.2	1061.9	1062.6	1063.3	1063.9
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	488.6	489.6	492.7	495.0	497.7	499.2	500.6	501.8	503.3	503.6	509.1
5°	490.8	495.4	503.7	509.8	517.4	525.5	531.2	533.8	540.7	546.2	557.5
7.5°	490.2	500.2	512.6	525.5	539.3	552.1	563.2	576.4	585.7	599.9	613.7
10°	489.6	503.0	519.0	535.4	554.7	572.6	588.7	606.5	621.4	640.9	657.5
12.5°	487.9	504.1	526.3	545.8	569.3	593.9	617.6	640.6	653.7	686.2	701.6
15°	483.7	503.0	530.8	560.4	592.6	621.8	651.9	675.9	714.7	743.2	761.3
17.5°	475.7	502.7	535.6	571.4	610.6	649.0	683.2	719.5	760.7	795.2	831.9
20°	471.9	501.6	538.3	577.8	618.5	662.1	700.8	744.6	789.5	823.4	870.5
22.5°	464.9	498.6	538.1	582.1	625.6	670.7	716.1	760.2	812.1	858.8	903.6
25°	453.6	491.2	532.2	581.4	632.4	677.5	732.0	790.5	844.6	904.6	949.3
27.5°	441.6	481.8	522.8	568.6	623.5	677.1	745.5	811.6	877.8	929.6	962.7
30°	432.4	471.5	513.8	560.0	614.3	678.0	754.5	826.7	891.2	935.6	954.2
32.5°	422.4	462.0	499.5	547.9	605.8	677.4	760.1	835.6	891.9	921.5	917.9
35°	406.8	439.9	476.5	523.0	591.2	673.3	763.5	836.4	870.9	864.5	816.6
37.5°	384.2	412.1	448.0	499.0	574.3	664.6	756.8	811.5	809.3	757.6	688.0
40°	370.1	393.8	428.4	482.0	561.1	658.9	746.5	782.0	751.9	679.6	596.4
42.5°	351.6	373.5	408.1	463.2	546.6	647.5	726.7	737.0	678.1	595.0	518.7
45°	323.1	342.3	378.1	435.0	524.8	622.5	678.5	653.3	574.0	488.2	430.1
47.5°	292.3	312.4	346.7	405.3	493.4	584.9	611.6	558.1	476.7	407.0	353.7
50°	272.9	292.2	325.9	384.9	472.2	554.0	565.1	495.9	421.1	359.9	316.2
52.5°	253.4	271.5	304.6	363.9	447.4	518.3	511.5	441.0	372.2	320.0	285.7
55°	224.2	241.4	272.9	328.4	404.5	460.6	436.0	368.7	311.7	271.2	245.1
57.5°	198.1	214.6	241.8	292.0	358.0	396.7	365.3	308.5	263.3	232.1	212.7
60°	180.5	195.0	221.0	267.5	324.9	354.3	323.3	273.2	235.0	210.1	192.7
62.5°	163.7	176.4	200.4	242.7	292.6	317.2	285.8	243.4	211.0	188.8	174.0
65°	138.4	149.9	171.1	204.0	244.9	261.4	234.3	200.0	174.8	158.3	148.5
67.5°	115.2	125.0	143.3	169.2	199.3	211.3	190.7	164.1	145.1	131.9	124.1
70°	99.8	108.3	122.6	144.9	172.2	181.4	162.1	140.2	126.3	115.7	108.5
72.5°	86.7	93.0	106.0	123.3	146.0	153.3	139.9	120.7	107.8	99.8	93.9
75°	66.1	71.3	79.8	93.6	109.4	113.6	103.5	91.5	82.8	77.2	72.7
77.5°	47.7	51.5	57.6	66.1	77.1	80.9	74.5	66.4	60.1	56.4	53.8
80°	36.0	39.1	44.2	51.3	57.9	60.0	56.2	50.1	45.6	43.5	41.4
82.5°	26.6	28.3	31.4	36.3	40.7	43.2	40.1	36.4	33.9	32.0	31.2
85°	13.4	14.3	15.8	17.7	20.5	21.4	20.2	19.3	17.9	16.7	16.7
87.5°	5.4	5.8	6.7	7.4	8.6	9.6	9.8	9.9	10.2	10.1	10.1
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.3	16.7	19.0	19.7	20.4
92.5°	14.2	13.7	13.2	12.7	13.3	15.0	16.8	18.5	20.2	21.3	22.4
95°	41.0	33.7	26.6	19.4	16.8	18.7	20.6	22.5	24.4	25.8	27.0
97.5°	93.6	90.4	87.2	83.9	75.9	63.3	50.7	38.1	25.4	26.9	28.3
100°	136.9	140.5	143.9	147.4	135.5	108.2	80.8	53.4	26.1	27.5	28.9
102.5°	177.6	180.2	182.7	185.2	171.6	141.7	111.7	81.8	51.9	47.6	43.2
105°	237.2	239.1	241.1	243.0	236.1	220.3	204.5	188.6	172.9	141.9	110.8
107.5°	300.3	301.8	303.4	304.9	306.9	309.4	311.9	314.4	316.9	294.2	271.4
110°	342.4	343.9	345.3	346.7	348.3	350.3	352.2	354.2	356.1	350.3	344.5



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	382.7	384.1	385.3	386.6	388.1	390.1	392.0	393.9	395.9	396.0	396.1
115°	442.4	443.4	444.5	445.6	446.9	448.5	450.0	451.6	453.2	454.9	456.7
117.5°	500.6	501.9	503.2	504.4	505.5	506.3	507.2	508.0	508.8	510.2	511.6
120°	536.8	538.5	540.0	541.6	542.7	543.2	543.7	544.2	544.7	546.1	547.5
122.5°	573.2	574.5	575.8	577.1	578.0	578.8	579.5	580.1	580.8	581.8	582.7
125°	623.5	624.9	626.3	627.7	628.8	629.5	630.2	630.9	631.6	632.0	632.3
127.5°	672.2	673.6	675.0	676.4	677.5	678.3	679.2	680.0	680.9	681.5	682.0
130°	702.5	703.9	705.3	706.7	707.7	708.4	709.1	709.8	710.5	711.2	712.0
132.5°	731.5	733.0	734.4	735.8	736.7	737.3	737.8	738.4	739.0	739.7	740.3
135°	775.6	776.6	777.7	778.7	779.6	780.3	781.0	781.7	782.4	782.9	783.5
137.5°	813.7	815.1	816.4	817.7	818.6	819.0	819.4	819.7	820.1	821.0	821.8
140°	838.7	839.8	840.8	841.9	842.6	843.2	843.7	844.2	844.8	845.5	846.2
142.5°	862.1	863.1	864.2	865.3	866.1	866.6	867.1	867.6	868.2	868.7	869.3
145°	894.9	896.2	897.4	898.7	899.4	899.8	900.1	900.5	900.8	901.2	901.5
147.5°	925.3	926.1	927.0	927.8	928.4	928.7	929.0	929.4	929.7	930.1	930.4
150°	944.0	944.5	945.0	945.5	946.0	946.3	946.7	947.1	947.5	947.8	948.1
152.5°	960.8	961.0	961.3	961.5	961.7	961.9	962.1	962.4	962.6	963.2	963.8
155°	984.2	983.8	983.5	983.1	983.0	983.2	983.4	983.5	983.7	984.6	985.5
157.5°	1003.1	1003.1	1003.0	1003.0	1002.9	1002.7	1002.6	1002.4	1002.2	1003.3	1004.3
160°	1014.3	1014.2	1014.0	1013.8	1013.6	1013.5	1013.3	1013.1	1012.9	1014.0	1015.0
162.5°	1024.8	1024.3	1023.9	1023.4	1023.1	1022.9	1022.8	1022.6	1022.4	1023.6	1024.8
165°	1037.6	1037.1	1036.6	1036.1	1035.7	1035.6	1035.4	1035.2	1035.0	1036.4	1037.8
167.5°	1047.6	1046.9	1046.2	1045.5	1045.1	1045.1	1045.1	1045.1	1045.1	1046.5	1047.9
170°	1053.3	1052.6	1051.9	1051.2	1050.9	1050.9	1050.9	1050.9	1050.9	1052.3	1053.6
172.5°	1056.9	1056.1	1055.2	1054.4	1054.1	1054.2	1054.3	1054.5	1054.6	1056.0	1057.4
175°	1061.8	1061.0	1060.1	1059.1	1058.8	1058.9	1059.1	1059.3	1059.6	1060.8	1062.0
177.5°	1063.3	1062.6	1061.9	1061.2	1060.9	1061.0	1061.2	1061.3	1061.4	1062.6	1063.7
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.5	485.5	485.5	485.5	485.5	485.5	485.5
2.5°	511.0	511.2	513.2	514.7	514.0	514.9	515.3
5°	558.3	566.7	571.2	574.5	574.7	575.0	576.8
7.5°	625.3	634.4	641.1	651.2	654.1	657.5	656.6
10°	674.3	687.7	699.2	705.3	712.0	721.5	713.8
12.5°	720.0	743.8	761.3	770.8	777.0	778.9	775.2
15°	795.5	826.5	843.1	842.7	863.8	873.0	858.7
17.5°	864.5	893.2	916.3	928.0	945.6	949.5	947.8
20°	907.0	938.3	956.1	976.3	985.5	993.7	995.1
22.5°	943.4	971.6	990.8	1007.5	1015.2	1019.2	1021.5
25°	981.1	1003.2	1014.7	1020.6	1022.7	1022.2	1019.2
27.5°	978.5	980.2	967.5	955.0	943.8	931.3	927.0
30°	953.0	933.3	898.0	878.0	848.6	825.3	834.8
32.5°	886.3	846.9	807.3	763.6	727.4	717.1	706.7
35°	756.4	687.2	646.7	599.7	580.9	562.1	549.1
37.5°	611.9	558.5	510.4	479.7	460.8	448.9	442.5
40°	529.1	480.9	441.3	416.4	402.0	388.7	386.8
42.5°	463.0	418.2	388.5	368.6	354.9	349.1	345.0
45°	379.2	348.0	328.0	313.9	304.7	301.1	296.4
47.5°	321.0	298.9	283.9	274.3	267.3	264.7	264.4
50°	288.4	270.0	259.0	251.5	246.1	245.1	241.4
52.5°	264.0	248.0	239.4	232.9	228.9	226.3	225.2
55°	229.1	218.5	210.8	207.0	204.0	201.4	201.4
57.5°	200.5	191.7	186.5	183.3	182.4	180.6	179.4
60°	182.8	175.3	171.3	168.4	166.5	166.8	164.7
62.5°	165.5	160.6	156.7	154.0	151.7	151.8	151.9
65°	140.9	137.1	134.3	133.4	132.0	130.4	130.8
67.5°	119.5	115.9	113.7	112.1	111.6	110.7	112.1
70°	104.0	101.4	99.8	98.4	97.9	98.1	99.3
72.5°	89.9	88.1	86.9	86.3	85.2	85.3	86.1
75°	70.6	69.2	68.3	67.6	67.3	67.3	67.3
77.5°	51.8	51.5	51.1	50.1	50.1	50.4	50.4
80°	40.9	40.2	40.0	39.5	38.8	38.4	39.5
82.5°	30.6	29.9	29.7	29.6	28.5	28.4	29.4
85°	16.5	15.8	16.0	15.8	15.8	15.6	15.6
87.5°	10.0	10.0	9.9	10.2	10.1	9.9	10.4
90°	21.0	21.7	22.3	22.6	23.0	23.3	23.7
92.5°	23.5	24.7	25.3	25.5	25.8	26.0	26.3
95°	28.2	29.4	30.0	30.0	30.0	30.0	30.0
97.5°	29.6	31.0	31.8	32.0	32.2	32.3	32.5
100°	30.3	31.7	32.4	32.6	32.8	33.0	33.1
102.5°	38.9	34.5	32.5	32.8	33.1	33.4	33.8
105°	79.8	48.7	33.3	33.7	34.0	34.4	34.7
107.5°	248.6	225.8	202.7	179.4	155.9	132.5	109.1
110°	338.7	333.0	317.5	292.4	267.3	242.2	217.1



TEST NUMBER: P331883-840

CATALOG NUMBER: S123DIP-S340D805U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	396.2	396.3	393.6	388.4	383.0	377.8	372.5
115°	458.5	460.2	461.4	462.1	462.8	463.5	464.2
117.5°	513.0	514.3	515.1	515.3	515.4	515.5	515.7
120°	549.0	550.4	551.1	551.1	551.1	551.1	551.1
122.5°	583.7	584.7	585.2	585.4	585.5	585.7	585.8
125°	632.7	633.0	633.4	633.7	634.1	634.4	634.8
127.5°	682.6	683.1	683.2	682.9	682.6	682.2	681.9
130°	712.7	713.4	713.6	713.2	712.9	712.5	712.2
132.5°	741.0	741.7	741.8	741.4	740.9	740.4	739.9
135°	784.0	784.5	784.5	784.0	783.5	782.9	782.4
137.5°	822.6	823.5	823.7	823.4	823.0	822.7	822.3
140°	846.9	847.6	847.8	847.4	847.1	846.7	846.4
142.5°	869.8	870.4	870.4	869.9	869.4	869.0	868.5
145°	901.9	902.2	902.4	902.4	902.4	902.4	902.4
147.5°	930.8	931.1	930.9	930.1	929.3	928.5	927.7
150°	948.5	948.8	948.8	948.2	947.7	947.2	946.6
152.5°	964.4	965.1	965.0	964.2	963.4	962.6	961.8
155°	986.3	987.2	987.1	986.1	985.0	984.0	982.9
157.5°	1005.3	1006.4	1006.2	1004.9	1003.5	1002.2	1000.8
160°	1016.1	1017.1	1017.0	1015.8	1014.6	1013.4	1012.2
162.5°	1026.0	1027.1	1027.2	1026.1	1025.0	1024.0	1022.9
165°	1039.3	1040.7	1040.8	1039.6	1038.2	1037.0	1035.8
167.5°	1049.4	1050.8	1050.8	1049.4	1047.9	1046.5	1045.1
170°	1055.0	1056.4	1056.4	1055.0	1053.6	1052.3	1050.9
172.5°	1058.8	1060.3	1060.2	1058.6	1057.1	1055.5	1054.0
175°	1063.2	1064.4	1064.3	1063.0	1061.6	1060.2	1058.7
177.5°	1064.8	1065.9	1065.8	1064.4	1063.0	1061.6	1060.2
180°	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7	1062.7

(END OF REPORT)