

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331972

Luminaire Tested: **S123DIP-S775D585U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331972  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D585U835-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5290.7 lumens  
Efficiency: N/A  
Efficacy: 131.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331972  
CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331972

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	58	56	55	50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	39	36
4	76	65	57	51	71	61	54	48	53	48	43	47	42	38	40	37	34	31
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	30	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	31	27	23	27	24	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	22	19	17
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P331972

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.7	2.2
10°-20°	323.9	6.1
20°-30°	478.4	9.0
30°-40°	558.9	10.6
40°-50°	561.9	10.6
50°-60°	493.6	9.3
60°-70°	367.7	6.9
70°-80°	209.5	4.0
80°-90°	62.3	1.2
90°-100°	156.8	3.0
100°-110°	444.0	8.4
110°-120°	436.8	8.3
120°-130°	348.4	6.6
130°-140°	274.7	5.2
140°-150°	205.0	3.9
150°-160°	142.9	2.7
160°-170°	83.9	1.6
170°-180°	27.3	0.5
0°-30°	917.1	17.3
0°-40°	1475.9	27.9
0°-60°	2531.4	47.8
0°-90°	3170.9	59.9
90°-120°	1037.6	19.6
90°-150°	1865.7	35.3
90°-180°	2120.0	40.1
0°-180°	5290.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	1	7	14	16	16	4
95°	19	63	338	99	66	21
105°	66	98	459	802	726	70
115°	117	146	351	769	882	116
125°	163	192	327	593	696	144
135°	190	227	323	489	564	147
145°	217	249	319	401	441	136
155°	247	266	309	351	366	114
165°	270	278	296	313	319	76
175°	281	282	284	288	287	27
180°	282	282	282	282	282	



TEST NUMBER: P331972

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	22.0	21.7	21.3	21.1	20.8	20.7	20.8	21.0	21.1	21.3	21.0
90°	1.1	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7
92.5°	7.1	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2
95°	19.4	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3
97.5°	33.1	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8
100°	42.2	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5
102.5°	51.8	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1
105°	66.2	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3
107.5°	81.4	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4
110°	92.4	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0



TEST NUMBER: P331972

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	102.4	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7
115°	116.9	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5
117.5°	131.4	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2
120°	141.5	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4
122.5°	150.1	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9
125°	162.6	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4
127.5°	172.0	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6
130°	178.0	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2
132.5°	182.5	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2
135°	190.5	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5
137.5°	198.0	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8
140°	203.1	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6
142.5°	208.5	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0
145°	217.3	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1
147.5°	226.2	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3
150°	232.1	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1
152.5°	238.1	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5
155°	247.0	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0
157.5°	254.0	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8
160°	259.5	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7
162.5°	263.6	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6
165°	269.8	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0
167.5°	274.5	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7
170°	277.2	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5
172.5°	279.0	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3
175°	281.2	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6
177.5°	282.2	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P331972

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	20.9	20.8	20.8	20.9	20.8	20.9	21.0	20.9
90°	14.3	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	48.0	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	205.3	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	511.9	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	672.5	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	725.9	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	741.5	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	696.5	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	653.6	758.6	830.5	870.4	886.4	890.9	889.8	888.6





TEST NUMBER: P331972

CATALOG NUMBER: S123DIP-S775D585U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	611.2	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	555.0	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	514.2	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	492.8	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	475.9	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	453.4	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	433.8	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	421.5	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	410.1	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	394.7	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	380.7	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	372.5	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	364.7	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	355.3	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	347.7	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	342.2	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	337.2	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	329.7	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	321.7	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	317.1	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	311.7	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	304.6	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	298.4	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	294.3	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	290.7	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	285.8	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	282.7	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)