

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331980

Luminaire Tested: **S123DIP-S775D805U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331980
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5929.3 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331980
CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331980

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45				
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38				
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24				
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	24	21				
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P331980

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	1.9
10°-20°	323.9	5.5
20°-30°	478.4	8.1
30°-40°	558.9	9.4
40°-50°	561.9	9.5
50°-60°	493.6	8.3
60°-70°	367.7	6.2
70°-80°	209.5	3.5
80°-90°	63.1	1.1
90°-100°	64.8	1.1
100°-110°	194.1	3.3
110°-120°	330.1	5.6
120°-130°	434.2	7.3
130°-140°	488.0	8.2
140°-150°	479.7	8.1
150°-160°	403.8	6.8
160°-170°	268.8	4.5
170°-180°	94.1	1.6
0°-30°	917.1	15.5
0°-40°	1475.9	24.9
0°-60°	2531.4	42.7
0°-90°	3171.7	53.5
90°-120°	589.0	9.9
90°-150°	1990.8	33.6
90°-180°	2758.0	46.5
0°-180°	5929.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	1	9	19	22	24	6
95°	46	52	58	61	61	52
105°	176	178	184	185	186	188
115°	332	334	333	334	333	329
125°	486	488	487	484	481	434
135°	631	635	635	632	630	486
145°	765	767	769	768	765	478
155°	876	876	877	880	875	403
165°	955	952	952	956	952	269
175°	993	990	990	994	989	94
180°	995	995	995	995	995	



TEST NUMBER: P331980

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	21.9	21.7	21.5	21.3	21.1	21.1	21.4	21.7	21.9	22.2	22.1
90°	0.8	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5
92.5°	18.9	20.1	21.3	22.5	23.6	24.9	26.2	27.5	28.7	30.0	30.6
95°	46.1	47.3	48.6	49.8	51.0	52.3	53.7	55.1	56.5	57.9	58.6
97.5°	81.9	82.8	83.7	84.6	85.6	86.5	87.5	88.5	89.5	90.5	91.3
100°	106.3	107.4	108.4	109.5	110.5	111.5	112.3	113.2	114.1	114.9	115.5
102.5°	134.5	135.1	135.7	136.4	137.0	137.9	139.0	140.2	141.3	142.5	143.0
105°	175.9	176.3	176.6	177.0	177.3	178.3	179.8	181.4	183.0	184.5	184.5
107.5°	224.1	224.3	224.5	224.7	224.9	225.3	226.0	226.6	227.2	227.8	228.4
110°	254.1	254.4	254.8	255.1	255.5	255.8	256.2	256.5	256.9	257.2	257.9



TEST NUMBER: P331980

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	285.4	285.6	285.8	286.0	286.2	286.3	286.4	286.5	286.6	286.6	287.5
115°	332.3	332.8	333.3	333.8	334.4	334.5	334.1	333.8	333.4	333.1	333.2
117.5°	379.5	379.9	380.2	380.5	380.9	380.8	380.4	379.9	379.5	379.0	379.0
120°	408.9	409.9	411.0	412.0	413.1	413.2	412.3	411.4	410.6	409.7	409.5
122.5°	439.6	440.3	441.1	441.8	442.6	442.8	442.3	441.9	441.4	441.0	440.5
125°	486.3	486.8	487.3	487.9	488.4	488.5	488.1	487.8	487.4	487.1	486.4
127.5°	529.5	530.6	531.7	532.8	533.9	534.3	533.9	533.5	533.1	532.7	531.8
130°	558.2	559.6	561.0	562.4	563.8	564.2	563.7	563.2	562.7	562.1	561.4
132.5°	587.0	588.4	589.8	591.2	592.6	593.1	592.7	592.3	591.9	591.5	590.7
135°	630.9	632.0	633.0	634.1	635.1	635.6	635.4	635.2	635.0	634.9	634.2
137.5°	671.6	672.5	673.3	674.2	675.1	675.7	676.2	676.6	677.1	677.5	676.8
140°	699.7	700.6	701.5	702.4	703.2	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	725.4	726.3	727.1	728.0	728.9	729.5	729.8	730.1	730.4	730.7	730.5
145°	765.4	765.8	766.1	766.5	766.8	767.2	767.8	768.3	768.8	769.3	769.2
147.5°	800.5	801.1	801.7	802.3	803.0	803.5	804.0	804.5	805.0	805.5	805.5
150°	824.8	825.2	825.5	825.9	826.2	826.6	826.9	827.3	827.6	828.0	828.0
152.5°	844.9	845.3	845.8	846.3	846.8	847.2	847.4	847.6	847.8	848.0	848.3
155°	876.4	876.4	876.4	876.4	876.4	876.5	876.7	876.9	877.1	877.2	877.9
157.5°	903.3	903.1	902.9	902.7	902.5	902.5	902.6	902.8	902.9	903.0	903.8
160°	920.2	919.9	919.5	919.2	918.8	918.7	918.7	918.7	918.7	918.7	919.5
162.5°	935.2	934.8	934.3	933.8	933.3	933.1	933.3	933.4	933.5	933.7	934.5
165°	954.6	954.1	953.6	953.1	952.5	952.3	952.3	952.3	952.3	952.3	953.3
167.5°	970.1	969.4	968.7	968.0	967.3	967.1	967.2	967.3	967.5	967.6	968.7
170°	978.9	978.2	977.5	976.8	976.1	975.7	975.7	975.7	975.7	975.7	977.0
172.5°	985.7	985.1	984.4	983.7	983.0	982.6	982.6	982.6	982.6	982.6	983.7
175°	992.9	992.2	991.6	990.9	990.2	989.8	989.8	989.8	989.8	989.8	990.9
177.5°	995.9	995.4	994.8	994.2	993.7	993.4	993.4	993.4	993.4	993.4	994.2
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P331980

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	22.1	22.0	22.0	22.0	22.1	22.1	22.2	22.3
90°	20.2	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	31.1	31.7	32.2	32.4	32.2	32.0	31.8	31.6
95°	59.2	59.9	60.6	61.0	61.0	61.0	61.0	61.0
97.5°	92.1	92.9	93.7	94.1	94.0	94.0	93.9	93.8
100°	116.0	116.5	117.0	117.5	117.8	118.1	118.5	118.8
102.5°	143.5	144.0	144.5	144.8	144.7	144.6	144.6	144.5
105°	184.5	184.5	184.5	184.7	185.0	185.4	185.7	186.1
107.5°	228.9	229.5	230.1	230.2	230.0	229.8	229.6	229.4
110°	258.6	259.3	260.0	260.2	259.8	259.5	259.1	258.8



TEST NUMBER: P331980

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	288.3	289.1	290.0	290.3	290.3	290.2	290.1	290.1
115°	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1
117.5°	379.0	378.9	378.9	378.6	378.2	377.7	377.2	376.7
120°	409.3	409.2	409.0	408.7	408.4	408.0	407.7	407.3
122.5°	440.1	439.6	439.2	438.7	438.2	437.7	437.2	436.7
125°	485.7	485.0	484.3	483.6	482.9	482.2	481.5	480.8
127.5°	530.8	529.8	528.9	528.0	527.2	526.4	525.6	524.8
130°	560.8	560.1	559.4	558.4	557.2	556.0	554.8	553.5
132.5°	589.9	589.0	588.2	587.3	586.4	585.4	584.5	583.6
135°	633.5	632.8	632.1	631.6	631.2	630.9	630.5	630.2
137.5°	676.1	675.4	674.6	673.9	673.3	672.6	672.0	671.3
140°	704.1	703.9	703.7	703.1	701.8	700.6	699.4	698.2
142.5°	730.4	730.2	730.0	729.5	728.5	727.6	726.6	725.7
145°	769.0	768.8	768.6	768.2	767.5	766.8	766.1	765.4
147.5°	805.5	805.5	805.5	804.9	803.9	802.8	801.8	800.8
150°	828.0	828.0	828.0	827.5	826.4	825.4	824.3	823.3
152.5°	848.5	848.8	849.1	848.8	847.9	847.0	846.1	845.2
155°	878.6	879.3	880.0	879.7	878.5	877.3	876.1	874.9
157.5°	904.5	905.2	905.9	905.8	904.9	903.9	902.9	901.9
160°	920.4	921.3	922.1	922.2	921.5	920.8	920.1	919.4
162.5°	935.4	936.3	937.2	937.0	935.9	934.8	933.7	932.6
165°	954.4	955.4	956.5	956.4	955.2	953.9	952.7	951.5
167.5°	969.8	970.8	971.9	971.9	970.8	969.8	968.7	967.6
170°	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7
172.5°	984.8	985.9	986.9	986.9	985.6	984.4	983.2	982.0
175°	991.9	992.9	994.0	993.9	992.7	991.5	990.2	989.0
177.5°	995.1	995.9	996.7	996.7	995.7	994.7	993.8	992.8
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3

(END OF REPORT)