

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331918-840

Luminaire Tested: **S123DIP-S560D365U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331918-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D365U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3668.7 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	33
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9684	9684	9684
5°	9729	9596	9662
10°	9664	9512	9571
15°	9551	9404	9423
20°	9419	9251	9260
25°	9242	9069	9049
30°	9047	8866	8797
35°	8843	8650	8539
40°	8630	8413	8283
45°	8397	8196	7995
50°	8162	7927	7708
55°	7854	7651	7418
60°	7543	7326	7093
65°	7272	6976	6757
70°	6864	6571	6279
75°	6276	6047	5793
80°	5659	5424	5368
85°	4965	4780	4594



TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.7	2.3
10°-20°	239.3	6.5
20°-30°	353.5	9.6
30°-40°	412.9	11.3
40°-50°	415.1	11.3
50°-60°	364.6	9.9
60°-70°	271.7	7.4
70°-80°	154.8	4.2
80°-90°	45.8	1.2
90°-100°	98.1	2.7
100°-110°	277.8	7.6
110°-120°	273.3	7.4
120°-130°	218.0	5.9
130°-140°	171.9	4.7
140°-150°	128.3	3.5
150°-160°	89.4	2.4
160°-170°	52.5	1.4
170°-180°	17.1	0.5
0°-30°	677.5	18.5
0°-40°	1090.4	29.7
0°-60°	1870.2	51.0
0°-90°	2342.4	63.8
90°-120°	649.2	17.7
90°-150°	1167.3	31.8
90°-180°	1326.0	36.1
0°-180°	3668.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	900	900	900	900	900	
5°	900	896	888	895	894	85
15°	857	854	844	850	846	242
25°	778	773	764	764	762	358
35°	673	668	658	654	650	421
45°	552	548	538	529	525	426
55°	418	417	408	399	395	375
65°	286	281	274	268	265	282
75°	151	148	145	142	139	161
85°	40	39	39	37	37	44
90°	1	4	9	10	10	3
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	219	481	552	72
125°	102	120	205	371	435	90
135°	119	142	202	306	353	92
145°	136	156	199	251	276	85
155°	154	167	193	219	229	71
165°	169	174	185	196	199	48
175°	176	176	177	180	180	17
180°	176	176	176	176	176	



TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	902.7	902.2	901.7	901.1	900.6	899.5	898.0	896.5	895.0	893.5	894.8
5°	900.4	899.6	898.7	897.9	897.0	895.6	893.7	891.8	890.0	888.1	889.8
7.5°	891.6	890.8	889.9	889.1	888.2	886.8	884.8	882.8	880.9	879.0	880.5
10°	884.2	883.3	882.5	881.6	880.8	879.2	877.0	874.7	872.5	870.3	871.8
12.5°	874.3	873.5	872.8	872.1	871.4	870.0	867.9	865.8	863.7	861.6	862.7
15°	857.1	856.5	855.8	855.1	854.3	852.9	850.7	848.5	846.2	843.9	845.4
17.5°	837.2	836.3	835.4	834.5	833.5	832.0	829.8	827.6	825.4	823.0	824.0
20°	822.3	821.3	820.2	819.2	818.2	816.6	814.4	812.1	809.8	807.6	808.3
22.5°	805.6	804.6	803.5	802.5	801.4	799.8	797.6	795.4	793.1	790.9	791.4
25°	778.2	777.2	776.2	775.2	774.1	772.4	770.2	768.0	765.8	763.6	763.7
27.5°	749.0	748.0	747.0	746.0	745.0	743.3	740.8	738.5	736.1	733.7	733.8
30°	727.9	727.1	726.2	725.4	724.5	722.9	720.4	718.0	715.7	713.3	713.3
32.5°	706.9	705.8	704.6	703.5	702.4	700.8	699.0	697.1	695.3	693.5	692.5
35°	673.0	672.0	671.0	669.9	668.9	667.2	665.0	662.8	660.6	658.3	657.3
37.5°	638.3	637.0	635.7	634.4	633.1	631.4	629.0	626.8	624.5	622.3	621.1
40°	614.2	613.2	612.2	611.2	610.1	608.3	605.9	603.6	601.2	598.7	597.3
42.5°	590.1	589.0	587.7	586.5	585.4	583.6	581.2	578.9	576.4	574.0	572.6
45°	551.6	550.9	550.2	549.5	548.8	547.3	545.1	542.9	540.7	538.4	536.3
47.5°	513.3	512.3	511.4	510.4	509.4	507.8	505.7	503.6	501.5	499.4	497.4
50°	487.4	486.5	485.6	484.7	483.9	482.4	480.1	477.9	475.6	473.4	471.5
52.5°	460.1	459.5	459.0	458.4	457.8	456.3	453.9	451.6	449.2	446.9	445.2
55°	418.5	418.3	418.2	418.0	417.8	416.6	414.3	412.1	409.9	407.7	405.8
57.5°	378.9	378.3	377.7	377.2	376.6	375.4	373.5	371.8	370.0	368.2	366.6
60°	350.4	350.2	350.1	349.9	349.7	348.6	346.6	344.5	342.4	340.3	338.8
62.5°	325.1	324.6	324.2	323.8	323.3	322.0	319.9	317.9	315.8	313.8	312.3
65°	285.5	284.6	283.8	282.9	282.1	280.7	279.0	277.3	275.6	273.9	272.5
67.5°	243.5	242.8	242.0	241.3	240.4	239.4	238.1	236.8	235.5	234.3	233.1
70°	218.1	217.1	216.1	215.1	214.0	213.0	212.0	211.0	209.8	208.8	207.6
72.5°	191.6	190.8	190.1	189.2	188.5	187.5	186.4	185.2	184.0	182.9	181.8
75°	150.9	150.2	149.5	148.8	148.1	147.5	146.9	146.4	145.9	145.4	144.6
77.5°	114.8	114.4	114.0	113.7	113.3	112.8	112.2	111.6	110.9	110.3	109.8
80°	91.3	90.8	90.3	89.8	89.2	88.8	88.5	88.1	87.8	87.5	87.3
82.5°	68.4	68.3	68.2	68.1	68.0	67.9	67.9	67.8	67.7	67.7	67.3
85°	40.2	39.9	39.6	39.2	38.9	38.7	38.7	38.7	38.7	38.7	38.4
87.5°	16.3	16.0	15.7	15.5	15.2	15.0	15.1	15.2	15.3	15.3	15.1
90°	0.7	1.4	2.1	3.2	3.9	4.6	5.8	6.8	7.9	8.9	8.6
92.5°	4.4	6.6	9.6	12.3	15.3	20.6	30.0	45.3	60.4	54.8	41.4
95°	12.1	13.2	17.2	23.2	32.5	46.4	76.7	129.9	188.4	211.7	171.7
97.5°	20.7	21.0	24.1	29.4	38.6	53.6	82.6	142.5	240.1	328.0	350.8
100°	26.5	26.8	29.3	34.2	42.8	56.8	81.7	134.5	228.4	338.0	408.3
102.5°	32.4	33.0	35.2	40.0	47.7	60.5	82.9	127.6	211.3	319.4	411.1
105°	41.4	42.5	44.6	48.9	55.6	66.8	86.0	122.8	190.3	286.9	389.3
107.5°	51.0	52.0	54.1	58.3	64.6	74.9	91.9	122.4	176.8	258.2	351.2
110°	57.8	58.9	60.7	64.6	70.7	80.7	96.7	123.8	171.7	242.0	327.3



TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	64.1	65.1	67.0	70.9	77.0	86.6	101.6	126.7	168.7	231.1	306.4
115°	73.1	74.6	76.7	80.3	86.3	96.0	109.6	131.3	167.7	219.4	281.2
117.5°	82.2	83.8	85.6	89.0	95.7	104.6	118.1	137.4	168.3	212.6	266.0
120°	88.5	89.6	91.4	94.9	101.7	110.6	123.5	142.0	169.6	209.4	258.0
122.5°	93.9	95.0	96.7	100.7	107.1	116.6	129.2	146.3	171.5	207.5	251.5
125°	101.7	102.4	104.5	108.5	115.2	124.9	137.4	153.1	174.5	204.8	243.1
127.5°	107.7	108.7	111.4	115.3	122.8	132.5	144.5	158.6	177.9	203.6	235.6
130°	111.4	112.4	115.6	119.9	127.4	137.0	148.9	162.4	180.3	202.7	231.6
132.5°	114.2	115.5	119.1	124.2	131.7	141.1	152.5	165.8	182.0	202.4	227.9
135°	119.2	120.6	124.5	129.9	137.4	147.0	158.0	170.3	184.5	202.0	223.1
137.5°	123.9	125.4	129.3	134.9	142.4	151.3	162.0	173.5	186.2	201.2	218.8
140°	127.0	128.9	132.4	138.1	145.2	154.2	164.5	175.2	187.3	201.0	216.2
142.5°	130.5	132.0	135.8	141.0	148.1	156.4	166.5	176.9	188.2	200.4	214.0
145°	135.9	137.0	140.3	145.6	151.7	159.9	169.2	178.7	188.7	199.4	210.9
147.5°	141.6	142.2	145.3	150.0	155.8	162.8	171.3	180.0	188.7	198.1	207.9
150°	145.2	145.6	148.5	153.1	158.0	164.5	172.7	180.3	188.7	197.0	205.9
152.5°	149.0	149.1	151.9	155.9	160.4	166.5	173.6	180.8	187.9	195.6	203.6
155°	154.5	154.5	156.6	160.3	164.2	169.2	175.2	181.0	187.0	193.1	200.2
157.5°	159.0	159.3	161.0	164.1	167.4	171.3	176.1	181.3	185.8	190.9	196.3
160°	162.4	162.4	163.8	166.6	169.2	172.7	177.0	181.3	185.2	189.1	193.8
162.5°	164.9	164.9	166.1	168.3	170.6	173.6	177.3	181.0	184.1	187.4	191.2
165°	168.7	168.4	169.2	171.0	172.4	174.9	177.7	180.3	182.4	184.9	187.7
167.5°	171.7	171.3	171.7	173.0	174.0	175.6	177.6	179.7	180.7	182.3	184.4
170°	173.4	172.7	173.1	174.1	174.9	175.6	177.3	178.7	179.6	180.6	182.4
172.5°	174.6	174.1	174.2	175.0	175.4	175.8	177.3	178.5	178.6	179.2	180.4
175°	175.9	175.6	175.2	175.9	175.9	176.3	177.0	177.7	177.3	177.3	178.0
177.5°	176.6	176.3	176.0	176.3	176.3	176.3	176.6	177.1	176.6	176.3	176.6
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3



TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	899.7	899.7	899.7	899.7	899.7	899.7	899.7	899.7
2.5°	896.3	897.6	899.0	899.6	899.5	899.3	899.2	899.1
5°	891.5	893.2	894.9	895.6	895.2	894.9	894.6	894.2
7.5°	882.0	883.5	885.1	885.8	885.6	885.3	885.1	884.9
10°	873.3	874.9	876.5	877.1	876.8	876.4	876.1	875.7
12.5°	863.8	865.1	866.2	866.6	866.4	866.2	866.0	865.8
15°	846.8	848.1	849.5	849.6	848.6	847.6	846.6	845.6
17.5°	825.1	826.0	827.0	827.2	826.9	826.5	826.1	825.7
20°	809.0	809.7	810.3	810.4	809.9	809.4	808.9	808.4
22.5°	792.0	792.5	793.1	793.0	792.4	791.7	791.1	790.4
25°	763.9	764.1	764.2	764.1	763.6	763.1	762.4	761.9
27.5°	734.0	734.1	734.2	734.0	733.3	732.7	732.0	731.3
30°	713.3	713.3	713.3	712.7	711.4	710.2	709.0	707.8
32.5°	691.6	690.5	689.5	688.7	688.1	687.5	686.8	686.2
35°	656.2	655.2	654.2	653.3	652.4	651.6	650.7	649.8
37.5°	619.8	618.5	617.3	616.4	615.9	615.3	614.8	614.2
40°	596.0	594.6	593.3	592.2	591.5	590.9	590.2	589.5
42.5°	571.3	569.9	568.5	567.4	566.7	566.1	565.4	564.7
45°	534.3	532.2	530.2	528.7	527.9	526.9	526.1	525.2
47.5°	495.3	493.3	491.3	489.9	489.2	488.4	487.7	486.9
50°	469.7	467.8	465.9	464.4	463.3	462.3	461.3	460.3
52.5°	443.6	442.0	440.4	439.0	438.0	437.0	436.0	434.9
55°	403.8	402.0	400.1	398.7	397.9	397.0	396.2	395.3
57.5°	364.9	363.1	361.5	360.1	359.1	358.2	357.2	356.2
60°	337.3	335.8	334.2	333.0	332.1	331.2	330.4	329.5
62.5°	310.6	309.1	307.6	306.5	305.9	305.4	304.8	304.2
65°	271.0	269.7	268.3	267.4	266.9	266.4	265.9	265.3
67.5°	231.9	230.7	229.4	228.4	227.7	227.0	226.3	225.6
70°	206.4	205.3	204.1	203.0	202.2	201.3	200.5	199.5
72.5°	180.8	179.7	178.6	177.8	177.4	176.9	176.5	176.0
75°	143.7	142.9	142.0	141.3	140.8	140.3	139.8	139.3
77.5°	109.2	108.6	108.0	107.7	107.7	107.7	107.7	107.7
80°	87.1	86.8	86.7	86.6	86.6	86.6	86.6	86.6
82.5°	67.0	66.7	66.3	66.1	66.0	65.8	65.7	65.6
85°	38.0	37.7	37.3	37.2	37.2	37.2	37.2	37.2
87.5°	15.1	15.0	14.9	15.0	14.9	15.0	15.1	15.0
90°	8.9	9.3	9.6	10.3	10.0	10.3	10.7	10.3
92.5°	30.1	23.8	21.0	19.2	18.6	17.5	17.9	17.2
95°	128.5	87.1	68.2	55.3	48.6	45.3	42.8	41.4
97.5°	320.2	256.5	210.5	167.8	141.5	125.4	115.7	112.7
100°	420.7	391.8	350.1	299.4	263.4	237.3	223.4	223.8
102.5°	454.1	453.2	428.9	396.8	368.7	348.1	336.5	328.2
105°	463.9	499.6	506.3	497.2	480.7	467.2	455.8	453.9
107.5°	435.8	493.7	525.0	537.8	538.1	533.4	529.6	526.3
110°	409.0	474.6	519.6	544.6	554.6	557.4	556.7	556.0



TEST NUMBER: P331918-840

CATALOG NUMBER: S123DIP-S560D365U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	382.4	449.5	499.9	532.0	550.3	559.2	561.9	562.0
115°	347.2	409.3	461.8	500.7	527.5	543.1	550.3	552.1
117.5°	321.7	375.4	422.4	461.9	489.9	507.9	518.1	520.5
120°	308.3	356.5	399.3	435.4	463.5	483.5	492.1	494.2
122.5°	297.8	341.3	381.0	414.5	439.6	457.6	467.0	469.7
125°	283.7	322.7	356.9	385.5	408.3	423.9	432.9	435.4
127.5°	271.5	306.1	337.0	363.0	383.3	396.8	404.9	407.1
130°	263.7	295.9	324.8	349.0	367.9	380.8	388.3	391.1
132.5°	256.6	286.1	313.1	336.2	354.0	366.8	373.4	375.5
135°	246.9	272.3	295.5	315.8	333.4	344.1	350.4	352.9
137.5°	238.1	258.9	278.9	296.6	311.2	322.1	327.5	329.2
140°	233.1	251.3	268.3	283.7	297.3	307.3	313.0	312.7
142.5°	228.2	243.8	258.6	272.0	283.6	292.5	297.5	297.2
145°	222.4	234.1	245.5	255.9	264.8	272.3	275.2	275.9
147.5°	217.5	226.9	236.1	243.5	250.2	255.3	258.0	258.3
150°	214.1	222.4	229.8	236.6	242.0	245.9	248.0	248.0
152.5°	211.0	218.0	224.7	230.4	234.5	238.1	239.4	239.4
155°	206.3	212.0	217.3	221.6	224.8	227.7	228.4	228.7
157.5°	201.3	206.0	210.2	213.6	216.3	218.4	219.0	218.9
160°	198.4	202.4	205.9	208.4	210.9	213.1	213.1	212.7
162.5°	195.0	198.3	201.7	203.9	205.5	207.3	207.3	207.0
165°	190.6	192.7	195.2	197.0	198.4	199.9	199.4	199.4
167.5°	186.7	188.3	189.8	191.1	191.7	192.7	192.4	192.4
170°	184.1	185.2	186.6	187.3	187.7	188.4	188.0	188.0
172.5°	181.9	182.7	183.8	184.2	184.3	185.0	184.4	184.1
175°	178.7	179.2	179.9	179.9	179.9	180.3	179.9	179.6
177.5°	176.8	177.1	177.4	177.4	177.1	177.4	176.8	176.8
180°	176.3	176.3	176.3	176.3	176.3	176.3	176.3	176.3

(END OF REPORT)