

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P831697

Luminaire Tested: S123DIP-S775D805U835-4F0-1E-UDD-G1

Issue Date: 05/03/2024

Test Information

Test Method: LM-79-2019
Report Number: P831697
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2301-905-1, G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 05/03/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U835-4F0-1E-UDD-G1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, GRAZE OPTIC
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6306.6 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 1.19 / 0.89
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 46.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

Luminous Intensity Polar Plot





TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				56
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	54	53				49	
2	91	84	78	73	85	79	74	69	68	64	61	59	56	53	50	48	46				42	
3	84	75	68	62	78	70	64	59	61	56	52	52	49	46	45	42	40				36	
4	77	67	59	53	72	62	56	50	55	49	45	47	43	40	40	38	35				32	
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31				28	
6	66	54	46	41	61	51	44	39	45	39	35	39	35	31	34	30	28				25	
7	61	49	42	36	57	46	39	34	41	35	31	36	32	28	31	28	25				23	
8	57	45	37	32	53	43	36	31	38	32	28	33	29	26	29	25	23				21	
9	53	41	34	29	50	39	33	28	35	29	26	31	26	23	27	24	21				19	
10	50	38	31	26	47	36	30	25	32	27	23	29	24	21	25	22	19				17	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	23750	23750	23750	23750	23750
5°	30035	28348	23961	19310	17744
10°	30326	31243	23802	15393	13450
15°	22841	29008	23640	13035	11375
20°	15914	23473	23338	11400	10332
25°	12136	18051	22823	10488	9691
30°	10499	14342	22002	9843	9175
35°	9741	12107	21055	9377	8812
40°	9222	10862	19724	8934	8689
45°	8914	10053	18033	8587	8634
50°	8761	9413	16031	8272	8589
55°	8435	8944	14063	7974	8627
60°	8133	8441	12122	7692	8486
65°	7641	7967	10458	7394	8318
70°	7056	7361	8894	6895	7830
75°	6388	6600	7623	6409	7153
80°	5269	5777	6031	5585	6031
85°	4174	4681	4421	4742	4804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 80°
 Vertical Angle: 45°
 Luminance: 20588 cd/sqm



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.6	3.3
10°-20°	518.9	8.2
20°-30°	614.4	9.7
30°-40°	617.8	9.8
40°-50°	566.8	9.0
50°-60°	467.8	7.4
60°-70°	330.9	5.2
70°-80°	176.7	2.8
80°-90°	46.9	0.7
90°-100°	64.1	1.0
100°-110°	193.9	3.1
110°-120°	330.1	5.2
120°-130°	434.3	6.9
130°-140°	488.2	7.7
140°-150°	479.9	7.6
150°-160°	404.0	6.4
160°-170°	269.0	4.3
170°-180°	94.2	1.5
0°-30°	1341.9	21.3
0°-40°	1959.7	31.1
0°-60°	2994.4	47.5
0°-90°	3548.9	56.3
90°-120°	588.1	9.3
90°-150°	1990.5	31.6
90°-180°	2758.0	43.7
0°-180°	6306.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2206	2206	2206	2206	2206	
5°	2780	2624	2218	1787	1642	265
15°	2050	2603	2121	1170	1021	566
25°	1022	1520	1922	883	816	482
35°	741	921	1602	714	671	466
45°	586	660	1185	564	567	454
55°	450	477	749	425	460	402
65°	300	313	411	290	327	298
75°	154	159	183	154	172	161
85°	34	38	36	38	39	38
90°	24	19	1	19	24	13
95°	61	58	46	58	61	61
105°	186	184	176	184	186	197
115°	333	333	332	333	333	330
125°	481	487	486	487	481	430
135°	630	635	631	635	630	485
145°	765	769	765	769	765	478
155°	875	877	876	877	875	403
165°	952	952	955	952	952	269
175°	989	990	993	990	989	94
180°	995	995	995	995	995	



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2486.9	2484.3	2481.8	2469.0	2456.2	2450.0	2443.9	2425.5	2407.0	2386.5	2366.1
5°	2779.7	2786.9	2794.0	2785.8	2777.7	2752.6	2727.5	2694.2	2660.9	2623.6	2586.2
7.5°	2914.8	2918.9	2923.0	2917.9	2912.8	2906.1	2899.5	2869.8	2840.1	2801.7	2763.3
10°	2774.6	2783.8	2793.0	2813.0	2832.9	2855.5	2878.0	2873.9	2869.8	2858.5	2847.3
12.5°	2466.4	2477.7	2488.9	2528.9	2568.8	2620.0	2671.2	2715.2	2759.2	2789.9	2820.7
15°	2049.7	2080.9	2112.2	2148.5	2184.9	2260.1	2335.4	2428.0	2520.7	2603.1	2685.5
17.5°	1688.3	1700.1	1711.8	1750.7	1789.7	1884.4	1979.1	2086.1	2193.0	2329.7	2466.4
20°	1389.3	1400.1	1410.8	1462.0	1513.2	1587.4	1661.7	1782.0	1902.3	2049.2	2196.1
22.5°	1167.2	1184.1	1201.0	1229.6	1258.3	1329.4	1400.6	1507.6	1614.6	1776.9	1939.1
25°	1021.8	1034.1	1046.4	1063.8	1081.2	1138.0	1194.8	1282.9	1370.9	1519.9	1668.8
27.5°	922.5	927.6	932.7	950.1	967.5	1004.4	1041.2	1117.0	1192.8	1319.2	1445.6
30°	844.7	848.2	851.8	867.2	882.5	907.6	932.7	987.5	1042.3	1153.9	1265.5
32.5°	790.4	793.0	795.5	807.3	819.1	837.0	854.9	894.8	934.8	1026.9	1119.0
35°	741.3	742.8	744.3	753.0	761.7	775.0	788.3	818.6	848.8	921.4	994.1
37.5°	698.3	700.3	702.3	707.5	712.6	724.4	736.1	760.2	784.3	840.1	895.9
40°	656.3	659.9	663.4	667.0	670.6	680.3	690.1	708.5	726.9	773.0	819.1
42.5°	620.4	624.0	627.6	629.1	630.7	636.3	641.9	658.8	675.7	710.0	744.3
45°	585.6	587.2	588.7	590.2	591.8	596.4	601.0	615.8	630.7	660.4	690.1
47.5°	553.9	553.9	553.9	554.9	555.9	560.0	564.1	574.9	585.6	608.7	631.7
50°	523.2	523.2	523.2	521.6	520.1	522.7	525.2	533.4	541.6	562.1	582.6
52.5°	486.3	486.3	486.3	486.8	487.3	487.3	487.3	494.5	501.7	520.1	538.5
55°	449.5	451.5	453.6	452.0	450.5	451.5	452.5	457.1	461.7	476.6	491.4
57.5°	412.6	413.6	414.7	414.1	413.6	414.1	414.7	418.7	422.8	434.1	445.4
60°	377.8	377.8	377.8	376.8	375.7	376.8	377.8	379.8	381.9	392.1	402.4
62.5°	338.9	339.4	339.9	340.4	340.9	339.9	338.9	341.4	344.0	351.7	359.4
65°	300.0	300.5	301.0	302.5	304.1	303.1	302.0	304.6	307.1	312.8	318.4
67.5°	265.2	264.1	263.1	263.6	264.1	265.7	267.2	267.7	268.2	274.4	280.5
70°	224.2	225.2	226.3	225.8	225.2	225.8	226.3	227.8	229.3	233.9	238.6
72.5°	187.4	187.9	188.4	188.4	188.4	189.4	190.4	192.0	193.5	196.1	198.6
75°	153.6	153.6	153.6	154.6	155.6	156.1	156.6	156.6	156.6	158.7	160.7
77.5°	116.7	119.3	121.8	121.3	120.8	121.8	122.9	124.4	125.9	127.0	128.0
80°	85.0	85.0	85.0	85.5	86.0	87.5	89.1	90.1	91.1	93.2	95.2
82.5°	54.3	54.8	55.3	56.8	58.4	59.4	60.4	61.9	63.5	63.5	63.5
85°	33.8	32.8	31.7	32.8	33.8	34.8	35.8	36.3	36.9	37.9	38.9
87.5°	16.4	16.4	16.4	16.4	16.4	16.9	17.4	17.4	17.4	17.4	17.4
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	33.6	34.0	34.3	34.7	35.0	34.9	34.4	33.9	33.4	32.8	31.8
95°	61.0	61.0	61.0	61.0	61.0	60.6	59.9	59.2	58.6	57.9	56.5
97.5°	87.6	87.7	87.9	88.1	88.3	87.9	87.0	86.2	85.3	84.4	83.4
100°	118.8	118.5	118.1	117.8	117.5	117.0	116.5	116.0	115.5	114.9	114.1
102.5°	150.9	151.1	151.2	151.4	151.6	151.4	150.9	150.4	149.9	149.3	148.1
105°	186.1	185.7	185.4	185.0	184.7	184.5	184.5	184.5	184.5	184.5	183.0
107.5°	222.0	222.2	222.4	222.6	222.7	222.6	222.0	221.5	221.0	220.5	219.8
110°	258.8	259.1	259.5	259.8	260.2	260.0	259.3	258.6	257.9	257.2	256.9



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.9	297.9	297.9	297.9	297.9	297.4	296.6	295.7	294.8	294.0	294.0
115°	333.1	333.2	333.4	333.6	333.8	333.8	333.6	333.4	333.2	333.1	333.4
117.5°	369.0	369.6	370.1	370.6	371.1	371.4	371.4	371.4	371.4	371.4	371.7
120°	407.3	407.7	408.0	408.4	408.7	409.0	409.2	409.3	409.5	409.7	410.6
122.5°	444.1	444.6	445.1	445.7	446.2	446.7	447.2	447.7	448.3	448.8	449.1
125°	480.8	481.5	482.2	482.9	483.6	484.3	485.0	485.7	486.4	487.1	487.4
127.5°	517.6	518.3	519.0	519.7	520.4	521.2	522.3	523.3	524.4	525.4	525.7
130°	553.5	554.8	556.0	557.2	558.4	559.4	560.1	560.8	561.4	562.1	562.7
132.5°	591.1	591.9	592.8	593.7	594.5	595.4	596.3	597.2	598.0	598.9	599.2
135°	630.2	630.5	630.9	631.2	631.6	632.1	632.8	633.5	634.2	634.9	635.0
137.5°	664.6	665.1	665.6	666.1	666.7	667.3	668.2	669.1	670.0	670.8	670.3
140°	698.2	699.4	700.6	701.8	703.1	703.7	703.9	704.1	704.3	704.4	704.3
142.5°	732.6	733.5	734.3	735.2	736.1	736.6	736.8	736.9	737.1	737.3	736.9
145°	765.4	766.1	766.8	767.5	768.2	768.6	768.8	769.0	769.2	769.3	768.8
147.5°	795.1	796.2	797.2	798.3	799.3	799.8	799.8	799.8	799.8	799.8	799.3
150°	823.3	824.3	825.4	826.4	827.5	828.0	828.0	828.0	828.0	828.0	827.6
152.5°	850.6	851.5	852.4	853.3	854.1	854.4	854.0	853.7	853.3	853.0	852.8
155°	874.9	876.1	877.3	878.5	879.7	880.0	879.3	878.6	877.9	877.2	877.1
157.5°	897.6	898.6	899.6	900.7	901.7	901.9	901.2	900.5	899.8	899.1	898.9
160°	919.4	920.1	920.8	921.5	922.2	922.1	921.3	920.4	919.5	918.7	918.7
162.5°	935.9	937.1	938.3	939.5	940.7	940.9	940.0	939.2	938.3	937.4	937.3
165°	951.5	952.7	953.9	955.2	956.4	956.5	955.4	954.4	953.3	952.3	952.3
167.5°	965.6	966.6	967.7	968.7	969.7	969.7	968.7	967.7	966.6	965.6	965.4
170°	975.7	977.0	978.2	979.4	980.6	980.6	979.4	978.2	977.0	975.7	975.7
172.5°	983.6	984.8	986.0	987.2	988.4	988.5	987.5	986.4	985.4	984.3	984.3
175°	989.0	990.2	991.5	992.7	993.9	994.0	992.9	991.9	990.9	989.8	989.8
177.5°	992.2	993.4	994.6	995.8	997.0	997.1	996.1	995.0	994.0	992.9	992.9
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2359.9	2353.8	2331.3	2308.7	2283.1	2257.5	2238.6	2219.7	2191.5	2163.4	2140.3
5°	2557.5	2528.9	2481.3	2433.6	2369.1	2304.6	2261.1	2217.6	2159.3	2100.9	2054.3
7.5°	2714.2	2665.0	2598.5	2531.9	2447.5	2363.0	2283.1	2203.3	2114.2	2025.1	1952.4
10°	2814.0	2780.7	2703.9	2627.1	2514.0	2400.9	2289.3	2177.7	2063.0	1948.3	1852.1
12.5°	2823.7	2826.8	2756.1	2685.5	2557.5	2429.5	2293.9	2158.2	2013.9	1869.5	1757.4
15°	2738.2	2791.0	2752.1	2713.1	2584.1	2455.1	2288.3	2121.4	1955.0	1788.6	1659.1
17.5°	2579.5	2692.7	2698.3	2703.9	2574.9	2445.9	2261.1	2076.3	1887.9	1699.6	1563.4
20°	2363.0	2529.9	2587.2	2644.6	2539.6	2434.7	2236.0	2037.4	1826.5	1615.6	1472.8
22.5°	2141.9	2344.6	2449.5	2554.5	2476.6	2398.8	2187.4	1976.0	1753.3	1530.6	1385.8
25°	1890.0	2111.1	2272.4	2433.6	2386.0	2338.4	2130.1	1921.7	1684.7	1447.7	1299.8
27.5°	1670.4	1895.1	2089.6	2284.2	2273.9	2263.7	2056.9	1850.1	1607.4	1364.8	1221.9
30°	1474.8	1684.2	1901.8	2119.3	2144.4	2169.5	1969.8	1770.2	1527.0	1283.9	1146.2
32.5°	1301.8	1484.6	1718.0	1951.4	2000.6	2049.7	1869.5	1689.3	1448.7	1208.1	1075.5
35°	1160.0	1325.9	1559.3	1792.7	1854.2	1915.6	1758.9	1602.3	1367.8	1133.4	1006.9
37.5°	1034.6	1173.3	1401.1	1628.9	1704.2	1779.4	1639.2	1498.9	1279.3	1059.7	943.5
40°	930.7	1042.3	1251.6	1461.0	1548.0	1635.1	1519.4	1403.7	1195.3	987.0	880.0
42.5°	843.6	942.9	1132.9	1322.8	1406.2	1489.7	1391.9	1294.1	1108.8	923.5	825.7
45°	769.4	848.8	1021.3	1193.8	1273.1	1352.5	1268.5	1184.6	1021.3	858.0	766.8
47.5°	699.8	767.9	915.3	1062.7	1133.4	1204.0	1138.5	1073.0	934.8	796.5	714.1
50°	637.3	692.1	821.1	950.1	1011.5	1073.0	1015.1	957.3	843.6	730.0	658.3
52.5°	583.1	627.6	735.6	843.6	896.4	949.1	899.4	849.8	759.7	669.6	607.1
55°	529.3	567.2	660.9	754.6	790.4	826.2	787.8	749.4	676.8	604.1	551.3
57.5°	479.2	512.9	589.7	666.5	694.2	721.8	687.0	652.2	597.4	542.6	498.6
60°	430.0	457.7	521.6	585.6	602.5	619.4	591.3	563.1	524.7	486.3	446.9
62.5°	384.4	409.5	457.1	504.7	516.0	527.3	505.8	484.3	455.1	425.9	395.2
65°	337.4	356.3	395.2	434.1	441.3	448.4	429.5	410.6	388.5	366.5	344.0
67.5°	293.8	307.1	338.9	370.6	371.1	371.7	356.3	340.9	328.6	316.4	298.4
70°	251.4	264.1	285.1	306.1	306.6	307.1	294.9	282.6	273.4	264.1	250.8
72.5°	207.8	217.1	232.9	248.8	247.8	246.7	239.1	231.4	224.2	217.1	207.3
75°	168.4	176.1	186.8	197.6	194.5	191.5	187.4	183.3	177.1	171.0	164.8
77.5°	132.6	137.2	143.3	149.5	147.4	145.4	141.8	138.2	133.6	129.0	126.4
80°	97.3	99.3	103.4	107.5	106.5	105.5	101.4	97.3	96.2	95.2	91.6
82.5°	66.0	68.6	69.6	70.6	70.1	69.6	66.5	63.5	62.5	61.4	60.9
85°	39.4	39.9	40.4	41.0	39.4	37.9	36.9	35.8	35.8	35.8	35.3
87.5°	17.9	18.4	18.4	18.4	17.9	17.4	16.4	15.4	15.9	16.4	16.4
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	30.8	29.7	28.7	27.6	26.6	25.5	24.5	23.5	24.5	25.5	26.6
95°	55.1	53.7	52.3	51.0	49.8	48.6	47.3	46.1	47.3	48.6	49.8
97.5°	82.4	81.3	80.3	79.3	78.4	77.6	76.7	75.8	76.7	77.6	78.4
100°	113.2	112.3	111.5	110.5	109.5	108.4	107.4	106.3	107.4	108.4	109.5
102.5°	146.9	145.7	144.5	143.6	143.1	142.6	142.0	141.5	142.0	142.6	143.1
105°	181.4	179.8	178.3	177.3	177.0	176.6	176.3	175.9	176.3	176.6	177.0
107.5°	219.1	218.4	217.7	217.3	217.1	216.9	216.7	216.6	216.7	216.9	217.1
110°	256.5	256.2	255.8	255.5	255.1	254.8	254.4	254.1	254.4	254.8	255.1



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	294.0	294.0	294.0	293.9	293.7	293.5	293.4	293.2	293.4	293.5	293.7
115°	333.8	334.1	334.5	334.4	333.8	333.3	332.8	332.3	332.8	333.3	333.8
117.5°	372.1	372.4	372.8	372.9	372.7	372.5	372.3	372.2	372.3	372.5	372.7
120°	411.4	412.3	413.2	413.1	412.0	411.0	409.9	408.9	409.9	411.0	412.0
122.5°	449.5	449.8	450.2	450.0	449.3	448.6	447.9	447.2	447.9	448.6	449.3
125°	487.8	488.1	488.5	488.4	487.9	487.3	486.8	486.3	486.8	487.3	487.9
127.5°	526.1	526.4	526.8	526.4	525.4	524.4	523.3	522.3	523.3	524.4	525.4
130°	563.2	563.7	564.2	563.8	562.4	561.0	559.6	558.2	559.6	561.0	562.4
132.5°	599.6	599.9	600.3	599.8	598.4	597.0	595.6	594.2	595.6	597.0	598.4
135°	635.2	635.4	635.6	635.1	634.1	633.0	632.0	630.9	632.0	633.0	634.1
137.5°	669.8	669.3	668.7	668.0	667.2	666.3	665.4	664.6	665.4	666.3	667.2
140°	704.1	703.9	703.7	703.2	702.4	701.5	700.6	699.7	700.6	701.5	702.4
142.5°	736.6	736.2	735.9	735.3	734.4	733.5	732.7	731.8	732.7	733.5	734.4
145°	768.3	767.8	767.2	766.8	766.5	766.1	765.8	765.4	765.8	766.1	766.5
147.5°	798.8	798.3	797.7	797.1	796.4	795.7	795.0	794.4	795.0	795.7	796.4
150°	827.3	826.9	826.6	826.2	825.9	825.5	825.2	824.8	825.2	825.5	825.9
152.5°	852.6	852.5	852.3	851.9	851.4	850.9	850.4	849.9	850.4	850.9	851.4
155°	876.9	876.7	876.5	876.4	876.4	876.4	876.4	876.4	876.4	876.4	876.4
157.5°	898.8	898.6	898.4	898.4	898.6	898.8	898.9	899.1	898.9	898.8	898.6
160°	918.7	918.7	918.7	918.8	919.2	919.5	919.9	920.2	919.9	919.5	919.2
162.5°	937.1	936.9	936.7	936.9	937.4	938.0	938.5	939.0	938.5	938.0	937.4
165°	952.3	952.3	952.3	952.5	953.1	953.6	954.1	954.6	954.1	953.6	953.1
167.5°	965.2	965.1	964.9	965.1	965.8	966.5	967.2	967.9	967.2	966.5	965.8
170°	975.7	975.7	975.7	976.1	976.8	977.5	978.2	978.9	978.2	977.5	976.8
172.5°	984.3	984.3	984.3	984.7	985.4	986.1	986.8	987.5	986.8	986.1	985.4
175°	989.8	989.8	989.8	990.2	990.9	991.6	992.2	992.9	992.2	991.6	990.9
177.5°	992.9	992.9	992.9	993.3	994.0	994.7	995.4	996.1	995.4	994.7	994.0
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4	2206.4
2.5°	2117.3	2097.3	2077.4	2062.0	2046.6	2020.5	1994.4	1988.3	1982.1	1973.4	1964.7
5°	2007.7	1958.6	1909.4	1865.4	1821.4	1787.1	1752.8	1730.3	1707.7	1691.4	1675.0
7.5°	1879.8	1806.0	1732.3	1680.1	1627.9	1578.2	1528.6	1512.7	1496.8	1475.3	1453.8
10°	1755.9	1674.5	1593.1	1525.0	1456.9	1408.3	1359.6	1340.2	1320.7	1293.6	1266.5
12.5°	1645.3	1556.2	1467.1	1398.6	1330.0	1282.9	1235.8	1207.6	1179.5	1164.1	1148.7
15°	1529.6	1434.4	1339.2	1275.7	1212.2	1169.7	1127.2	1102.7	1078.1	1063.2	1048.4
17.5°	1427.2	1333.0	1238.8	1177.9	1117.0	1078.1	1039.2	1017.7	996.2	984.9	973.7
20°	1330.0	1237.8	1145.7	1086.3	1026.9	995.2	963.4	949.6	935.8	926.6	917.4
22.5°	1240.9	1150.3	1059.7	1009.0	958.3	932.7	907.1	897.4	887.7	880.0	872.3
25°	1151.8	1070.9	990.0	947.0	904.0	883.1	862.1	852.3	842.6	834.9	827.3
27.5°	1079.1	1001.8	924.5	887.7	850.8	834.4	818.0	810.4	802.7	795.5	788.3
30°	1008.5	939.4	870.3	838.5	806.8	791.9	777.1	769.4	761.7	755.1	748.4
32.5°	942.9	883.6	824.2	795.0	765.8	753.5	741.3	732.0	722.8	717.7	712.6
35°	880.5	827.3	774.0	750.0	725.9	713.6	701.3	693.6	686.0	681.9	677.8
37.5°	827.3	779.6	732.0	709.0	686.0	674.2	662.4	655.8	649.1	647.6	646.0
40°	773.0	732.0	691.1	668.6	646.0	635.8	625.6	621.5	617.4	616.3	615.3
42.5°	727.9	688.0	648.1	627.6	607.1	598.4	589.7	587.7	585.6	587.2	588.7
45°	675.7	642.5	609.2	590.2	571.3	564.1	557.0	555.4	553.9	557.0	560.0
47.5°	631.7	601.0	570.3	552.4	534.4	529.3	524.2	523.7	523.2	527.3	531.4
50°	586.7	557.0	527.3	512.9	498.6	494.0	489.4	490.9	492.5	499.1	505.8
52.5°	544.7	517.0	489.4	476.1	462.8	459.7	456.6	460.2	463.8	471.0	478.1
55°	498.6	473.5	448.4	438.2	428.0	424.9	421.8	429.0	436.2	442.8	449.5
57.5°	454.6	432.6	410.6	401.3	392.1	391.6	391.1	397.8	404.4	411.6	418.7
60°	407.5	389.1	370.6	363.5	356.3	357.3	358.3	366.0	373.7	379.3	385.0
62.5°	364.5	349.1	333.8	327.1	320.5	323.0	325.6	333.3	340.9	347.6	354.2
65°	321.5	308.7	295.9	291.3	286.7	290.3	293.8	300.5	307.1	311.8	316.4
67.5°	280.5	269.8	259.0	255.4	251.9	255.4	259.0	265.7	272.3	276.9	281.6
70°	237.5	228.8	220.1	217.6	215.0	219.1	223.2	228.8	234.5	239.1	243.7
72.5°	197.6	190.9	184.3	183.8	183.3	186.8	190.4	196.1	201.7	204.8	207.8
75°	158.7	155.1	151.5	151.0	150.5	154.1	157.7	160.7	163.8	166.4	168.9
77.5°	123.9	120.8	117.7	118.3	118.8	121.3	123.9	127.0	130.0	131.6	133.1
80°	88.0	87.0	86.0	87.0	88.0	90.1	92.1	94.2	96.2	97.3	98.3
82.5°	60.4	59.4	58.4	59.9	61.4	63.0	64.5	66.0	67.6	68.1	68.6
85°	34.8	36.3	37.9	37.9	37.9	38.4	38.9	39.4	39.9	39.4	38.9
87.5°	16.4	16.9	17.4	17.4	17.4	17.9	18.4	18.4	18.4	17.9	17.4
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	27.6	28.7	29.7	30.8	31.8	32.8	33.4	33.9	34.4	34.9	35.0
95°	51.0	52.3	53.7	55.1	56.5	57.9	58.6	59.2	59.9	60.6	61.0
97.5°	79.3	80.3	81.3	82.4	83.4	84.4	85.3	86.2	87.0	87.9	88.3
100°	110.5	111.5	112.3	113.2	114.1	114.9	115.5	116.0	116.5	117.0	117.5
102.5°	143.6	144.5	145.7	146.9	148.1	149.3	149.9	150.4	150.9	151.4	151.6
105°	177.3	178.3	179.8	181.4	183.0	184.5	184.5	184.5	184.5	184.5	184.7
107.5°	217.3	217.7	218.4	219.1	219.8	220.5	221.0	221.5	222.0	222.6	222.7
110°	255.5	255.8	256.2	256.5	256.9	257.2	257.9	258.6	259.3	260.0	260.2



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	293.9	294.0	294.0	294.0	294.0	294.0	294.8	295.7	296.6	297.4	297.9
115°	334.4	334.5	334.1	333.8	333.4	333.1	333.2	333.4	333.6	333.8	333.8
117.5°	372.9	372.8	372.4	372.1	371.7	371.4	371.4	371.4	371.4	371.4	371.1
120°	413.1	413.2	412.3	411.4	410.6	409.7	409.5	409.3	409.2	409.0	408.7
122.5°	450.0	450.2	449.8	449.5	449.1	448.8	448.3	447.7	447.2	446.7	446.2
125°	488.4	488.5	488.1	487.8	487.4	487.1	486.4	485.7	485.0	484.3	483.6
127.5°	526.4	526.8	526.4	526.1	525.7	525.4	524.4	523.3	522.3	521.2	520.4
130°	563.8	564.2	563.7	563.2	562.7	562.1	561.4	560.8	560.1	559.4	558.4
132.5°	599.8	600.3	599.9	599.6	599.2	598.9	598.0	597.2	596.3	595.4	594.5
135°	635.1	635.6	635.4	635.2	635.0	634.9	634.2	633.5	632.8	632.1	631.6
137.5°	668.0	668.7	669.3	669.8	670.3	670.8	670.0	669.1	668.2	667.3	666.7
140°	703.2	703.7	703.9	704.1	704.3	704.4	704.3	704.1	703.9	703.7	703.1
142.5°	735.3	735.9	736.2	736.6	736.9	737.3	737.1	736.9	736.8	736.6	736.1
145°	766.8	767.2	767.8	768.3	768.8	769.3	769.2	769.0	768.8	768.6	768.2
147.5°	797.1	797.7	798.3	798.8	799.3	799.8	799.8	799.8	799.8	799.8	799.3
150°	826.2	826.6	826.9	827.3	827.6	828.0	828.0	828.0	828.0	828.0	827.5
152.5°	851.9	852.3	852.5	852.6	852.8	853.0	853.3	853.7	854.0	854.4	854.1
155°	876.4	876.5	876.7	876.9	877.1	877.2	877.9	878.6	879.3	880.0	879.7
157.5°	898.4	898.4	898.6	898.8	898.9	899.1	899.8	900.5	901.2	901.9	901.7
160°	918.8	918.7	918.7	918.7	918.7	918.7	919.5	920.4	921.3	922.1	922.2
162.5°	936.9	936.7	936.9	937.1	937.3	937.4	938.3	939.2	940.0	940.9	940.7
165°	952.5	952.3	952.3	952.3	952.3	952.3	953.3	954.4	955.4	956.5	956.4
167.5°	965.1	964.9	965.1	965.2	965.4	965.6	966.6	967.7	968.7	969.7	969.7
170°	976.1	975.7	975.7	975.7	975.7	975.7	977.0	978.2	979.4	980.6	980.6
172.5°	984.7	984.3	984.3	984.3	984.3	984.3	985.4	986.4	987.5	988.5	988.4
175°	990.2	989.8	989.8	989.8	989.8	989.8	990.9	991.9	992.9	994.0	993.9
177.5°	993.3	992.9	992.9	992.9	992.9	992.9	994.0	995.0	996.1	997.1	997.0
180°	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3	995.3



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2206.4	2206.4	2206.4	2206.4
2.5°	1961.1	1957.6	1943.2	1928.9
5°	1662.7	1650.4	1646.3	1642.2
7.5°	1452.8	1451.8	1430.3	1408.8
10°	1268.0	1269.5	1250.1	1230.6
12.5°	1135.9	1123.1	1121.6	1120.1
15°	1036.6	1024.9	1022.8	1020.8
17.5°	966.5	959.3	957.3	955.2
20°	913.3	909.2	905.6	902.0
22.5°	867.2	862.1	859.0	855.9
25°	822.6	818.0	817.0	816.0
27.5°	782.7	777.1	777.1	777.1
30°	744.8	741.3	739.7	738.2
32.5°	709.5	706.4	706.4	706.4
35°	676.2	674.7	672.7	670.6
37.5°	646.0	646.0	645.0	644.0
40°	616.9	618.4	618.4	618.4
42.5°	590.2	591.8	591.8	591.8
45°	562.6	565.2	566.2	567.2
47.5°	535.5	539.6	540.6	541.6
50°	508.8	511.9	512.4	512.9
52.5°	481.7	485.3	487.9	490.4
55°	453.0	456.6	458.2	459.7
57.5°	422.3	425.9	426.4	426.9
60°	388.5	392.1	393.2	394.2
62.5°	356.3	358.3	359.4	360.4
65°	319.4	322.5	324.6	326.6
67.5°	284.1	286.7	286.7	286.7
70°	244.7	245.7	247.3	248.8
72.5°	208.3	208.9	208.9	208.9
75°	170.0	171.0	171.5	172.0
77.5°	133.6	134.1	134.1	134.1
80°	97.8	97.3	97.3	97.3
82.5°	67.1	65.5	65.5	65.5
85°	38.4	37.9	38.4	38.9
87.5°	17.4	17.4	17.4	17.4
90°	22.4	22.8	23.1	23.5
92.5°	34.7	34.3	34.0	33.6
95°	61.0	61.0	61.0	61.0
97.5°	88.1	87.9	87.7	87.6
100°	117.8	118.1	118.5	118.8
102.5°	151.4	151.2	151.1	150.9
105°	185.0	185.4	185.7	186.1
107.5°	222.6	222.4	222.2	222.0
110°	259.8	259.5	259.1	258.8



TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
112.5°	297.9	297.9	297.9	297.9
115°	333.6	333.4	333.2	333.1
117.5°	370.6	370.1	369.6	369.0
120°	408.4	408.0	407.7	407.3
122.5°	445.7	445.1	444.6	444.1
125°	482.9	482.2	481.5	480.8
127.5°	519.7	519.0	518.3	517.6
130°	557.2	556.0	554.8	553.5
132.5°	593.7	592.8	591.9	591.1
135°	631.2	630.9	630.5	630.2
137.5°	666.1	665.6	665.1	664.6
140°	701.8	700.6	699.4	698.2
142.5°	735.2	734.3	733.5	732.6
145°	767.5	766.8	766.1	765.4
147.5°	798.3	797.2	796.2	795.1
150°	826.4	825.4	824.3	823.3
152.5°	853.3	852.4	851.5	850.6
155°	878.5	877.3	876.1	874.9
157.5°	900.7	899.6	898.6	897.6
160°	921.5	920.8	920.1	919.4
162.5°	939.5	938.3	937.1	935.9
165°	955.2	953.9	952.7	951.5
167.5°	968.7	967.7	966.6	965.6
170°	979.4	978.2	977.0	975.7
172.5°	987.2	986.0	984.8	983.6
175°	992.7	991.5	990.2	989.0
177.5°	995.8	994.6	993.4	992.2
180°	995.3	995.3	995.3	995.3

TEST NUMBER: P831697

CATALOG NUMBER: S123DIP-S775D805U835-4F0-1E-UDD-G1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.14	16.02	16.05	16.94	18.12	17.38	18.26	18.29	19.18	20.36
	3H	16.79	17.58	17.71	18.51	19.71	18.80	19.59	19.72	20.52	21.73
	4H	17.37	18.11	18.30	19.05	20.26	19.25	20.00	20.19	20.93	22.15
	6H	17.74	18.42	18.69	19.37	20.59	19.53	20.21	20.48	21.16	22.39
	8H	17.84	18.49	18.79	19.45	20.67	19.59	20.24	20.55	21.20	22.43
	12H	17.88	18.50	18.84	19.45	20.71	19.61	20.23	20.57	21.19	22.44
4H	2H	15.72	16.46	16.66	17.40	18.61	17.54	18.29	18.48	19.22	20.44
	3H	17.55	18.17	18.50	19.13	20.36	19.16	19.78	20.11	20.75	21.98
	4H	18.25	18.81	19.21	19.77	21.03	19.75	20.31	20.71	21.27	22.53
	6H	18.72	19.21	19.70	20.19	21.45	20.15	20.64	21.13	21.62	22.88
	8H	18.86	19.31	19.83	20.29	21.56	20.26	20.72	21.24	21.70	22.97
	12H	18.93	19.34	19.92	20.33	21.61	20.31	20.72	21.30	21.71	22.99
8H	4H	18.51	18.97	19.49	19.95	21.21	19.85	20.31	20.83	21.29	22.55
	6H	19.10	19.48	20.10	20.50	21.77	20.36	20.73	21.36	21.75	23.02
	8H	19.31	19.64	20.32	20.65	21.94	20.54	20.87	21.55	21.88	23.16
	12H	19.44	19.73	20.45	20.73	22.06	20.64	20.93	21.65	21.93	23.26
12H	4H	18.52	18.92	19.51	19.92	21.19	19.83	20.24	20.82	21.23	22.51
	6H	19.15	19.48	20.16	20.49	21.78	20.37	20.70	21.38	21.71	23.00
	8H	19.39	19.68	20.40	20.68	22.01	20.57	20.86	21.58	21.86	23.20