

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332359

Luminaire Tested: **S123RDIP-S1000D1195U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332359
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8113.7 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47						47														
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40						40														
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34						34														
3	81	72	65	59	74	67	60	55	56	52	48	46	43	40	38	35	33	29						29														
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25						25														
5	68	57	49	43	63	53	46	41	45	40	35	37	33	30	31	28	25	22						22														
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	22	20						20														
7	58	46	39	33	54	43	36	31	37	31	27	31	27	24	25	22	20	17						17														
8	54	42	34	29	50	39	32	28	34	28	24	28	24	21	23	20	18	16						16														
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16	14						14														
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15	13						13														

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	1.9
10°-20°	438.5	5.4
20°-30°	631.4	7.8
30°-40°	711.2	8.8
40°-50°	680.4	8.4
50°-60°	557.2	6.9
60°-70°	375.9	4.6
70°-80°	189.1	2.3
80°-90°	54.5	0.7
90°-100°	319.4	3.9
100°-110°	904.4	11.1
110°-120°	889.7	11.0
120°-130°	709.7	8.7
130°-140°	559.5	6.9
140°-150°	417.6	5.1
150°-160°	291.1	3.6
160°-170°	171.0	2.1
170°-180°	55.6	0.7
0°-30°	1227.4	15.1
0°-40°	1938.6	23.9
0°-60°	3176.1	39.1
0°-90°	3795.6	46.8
90°-120°	2113.6	26.0
90°-150°	3800.4	46.8
90°-180°	4318.0	53.2
0°-180°	8113.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	2	14	29	33	34	6
95°	40	128	689	201	135	43
105°	135	199	934	1634	1478	143
115°	238	297	714	1567	1797	236
125°	331	391	667	1208	1418	294
135°	388	463	658	995	1149	300
145°	443	507	650	816	898	277
155°	503	543	629	715	745	231
165°	550	565	602	638	650	155
175°	573	573	577	586	584	54
180°	574	574	574	574	574	



TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.6	24.4	22.2	20.2	18.0	17.2	17.9	18.6	19.3	20.0	19.5
90°	2.3	4.6	7.0	10.5	12.8	15.1	18.6	22.1	25.6	29.0	27.9
92.5°	14.4	21.4	31.1	40.2	50.0	67.2	97.6	147.6	196.6	178.7	134.8
95°	39.5	43.0	55.8	75.5	105.7	151.0	249.8	422.9	613.5	689.0	558.8
97.5°	67.4	68.5	78.5	95.7	125.5	174.5	268.9	464.0	781.7	1067.7	1142.3
100°	86.0	87.1	95.3	111.5	139.4	184.7	266.1	438.0	743.6	1100.3	1329.2
102.5°	105.5	107.6	114.8	130.1	155.2	196.8	269.8	415.7	687.8	1039.9	1338.4
105°	134.8	138.3	145.2	159.2	181.2	217.3	280.0	399.7	619.3	934.1	1267.6
107.5°	165.9	169.4	176.1	189.8	210.5	244.0	299.1	398.5	575.6	840.7	1143.5
110°	188.2	191.7	197.5	210.3	230.0	262.6	314.9	403.2	558.8	787.7	1065.4



TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	208.7	212.2	218.0	230.7	250.5	282.1	330.7	412.5	549.6	752.4	997.6
115°	238.2	242.8	249.8	261.4	281.2	312.5	356.7	427.6	546.1	714.5	915.5
117.5°	267.7	273.0	278.8	289.5	311.6	340.7	384.3	447.5	548.2	692.2	866.0
120°	288.1	291.6	297.4	309.1	331.1	360.2	402.0	462.4	551.9	682.0	840.0
122.5°	305.8	309.3	315.1	327.6	348.8	379.7	420.6	476.4	558.4	675.5	818.6
125°	331.1	333.5	340.4	353.2	375.3	406.6	447.3	498.4	568.1	666.9	791.2
127.5°	350.4	353.9	362.5	375.5	399.9	431.3	470.5	516.6	579.3	662.7	767.1
130°	362.5	366.0	376.4	390.4	414.8	446.1	484.5	528.6	586.7	659.9	754.0
132.5°	371.8	376.2	387.6	404.3	428.7	459.2	496.6	539.8	592.3	659.0	742.0
135°	388.1	392.7	405.5	422.9	447.3	478.7	514.7	554.2	600.7	657.6	726.2
137.5°	403.4	408.3	420.8	439.4	463.6	492.6	527.2	564.9	606.3	655.0	712.4
140°	413.6	419.4	431.0	449.6	472.9	501.9	535.6	570.5	610.0	654.1	704.1
142.5°	424.8	429.7	442.2	458.9	482.2	509.4	542.1	576.0	612.8	652.3	696.6
145°	442.7	446.1	456.6	474.0	493.8	520.5	550.7	582.1	614.6	649.5	686.7
147.5°	460.8	462.9	473.1	488.2	507.3	530.0	557.7	585.8	614.6	645.1	676.9
150°	472.9	474.0	483.3	498.4	514.7	535.6	562.3	586.7	614.6	641.3	670.4
152.5°	485.0	485.2	494.5	507.7	522.1	542.1	565.1	588.6	611.8	636.7	663.0
155°	503.1	503.1	510.1	521.7	534.4	550.7	570.5	589.1	608.8	628.6	651.8
157.5°	517.5	518.4	524.0	534.2	545.1	557.7	573.5	590.2	604.9	621.4	639.2
160°	528.6	528.6	533.3	542.6	550.7	562.3	576.3	590.2	603.0	615.8	630.9
162.5°	537.0	537.0	540.7	548.2	555.4	565.1	577.2	589.3	599.3	610.2	622.5
165°	549.6	548.4	550.7	556.5	561.2	569.3	578.6	586.7	593.7	601.8	611.1
167.5°	559.1	557.7	558.8	563.3	566.5	571.6	578.4	584.9	588.1	593.5	600.2
170°	564.7	562.3	563.5	567.0	569.3	571.6	577.4	582.1	584.4	587.9	593.7
172.5°	568.4	567.0	567.2	569.8	571.2	572.6	577.4	581.2	581.6	583.2	587.2
175°	572.8	571.6	570.5	572.8	572.8	574.0	576.3	578.6	577.4	577.4	579.8
177.5°	574.9	574.0	573.0	574.0	574.0	574.0	574.9	576.7	574.9	574.0	574.9
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0



TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	19.5	19.5	19.5	19.7	19.2	19.2	19.2	18.7
90°	29.0	30.2	31.4	33.7	32.5	33.7	34.9	33.7
92.5°	97.8	77.6	68.5	62.5	60.4	56.9	58.1	56.0
95°	418.3	283.5	221.9	180.1	158.0	147.6	139.4	134.8
97.5°	1042.6	835.1	685.3	546.3	460.6	408.3	376.9	366.9
100°	1369.8	1275.7	1139.8	974.8	857.4	772.6	727.3	728.5
102.5°	1478.6	1475.5	1396.3	1291.7	1200.4	1133.3	1095.4	1068.7
105°	1510.4	1626.6	1648.7	1618.5	1565.0	1520.9	1483.7	1477.9
107.5°	1418.8	1607.5	1709.3	1750.7	1751.6	1736.7	1724.2	1713.5
110°	1331.5	1545.3	1691.7	1773.0	1805.5	1814.8	1812.5	1810.2



TEST NUMBER: P332359

CATALOG NUMBER: S123RDIP-S1000D1195U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1245.0	1463.5	1627.5	1732.1	1791.6	1820.4	1829.2	1829.7
115°	1130.5	1332.6	1503.4	1630.1	1717.2	1768.3	1791.6	1797.4
117.5°	1047.5	1222.0	1375.4	1503.9	1594.8	1653.3	1686.8	1694.7
120°	1003.8	1160.7	1300.1	1417.5	1509.2	1574.3	1602.2	1609.2
122.5°	969.4	1111.4	1240.6	1349.6	1431.2	1489.7	1520.4	1529.2
125°	923.7	1050.3	1161.8	1254.8	1329.2	1380.3	1409.3	1417.5
127.5°	883.7	996.6	1097.2	1181.8	1248.1	1291.7	1318.0	1325.4
130°	858.6	963.2	1057.3	1136.3	1197.9	1239.7	1264.1	1273.4
132.5°	835.4	931.6	1019.2	1094.5	1152.3	1194.1	1215.8	1222.3
135°	804.0	886.5	962.0	1028.2	1085.2	1120.0	1140.9	1149.1
137.5°	775.4	843.0	908.1	965.5	1013.4	1048.7	1066.3	1071.7
140°	758.7	817.9	873.7	923.7	967.8	1000.4	1018.9	1017.8
142.5°	742.9	793.8	842.1	885.6	923.2	952.0	968.7	967.6
145°	723.8	762.2	799.4	833.0	862.1	886.5	895.8	898.1
147.5°	708.3	738.7	768.7	792.6	814.7	831.2	840.0	840.9
150°	697.1	723.8	748.2	770.3	787.7	800.5	807.5	807.5
152.5°	686.9	709.9	731.5	749.9	763.6	775.4	779.6	779.6
155°	671.5	690.1	707.6	721.5	732.0	741.3	743.6	744.7
157.5°	655.3	670.9	684.3	695.2	704.3	711.3	713.1	712.9
160°	646.0	658.8	670.4	678.5	686.7	693.6	693.6	692.5
162.5°	634.8	645.8	656.4	663.6	669.0	675.0	675.0	673.9
165°	620.4	627.4	635.5	641.3	646.0	650.6	649.5	649.5
167.5°	607.9	613.2	617.9	622.1	624.1	627.4	626.2	626.2
170°	599.5	603.0	607.6	610.0	611.1	613.5	612.3	612.3
172.5°	592.1	594.6	598.4	599.7	600.0	602.3	600.2	599.3
175°	582.1	583.2	585.6	585.6	585.6	586.7	585.6	584.4
177.5°	575.8	576.7	577.7	577.7	576.7	577.7	575.8	575.8
180°	574.0	574.0	574.0	574.0	574.0	574.0	574.0	574.0

(END OF REPORT)