

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332338

Luminaire Tested: **S123RDIP-S1000D585U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332338
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U835-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6080.2 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61	56
2	93	86	80	75	88	82	76	72	72	68	65	64	61	59	56	54	52	48
3	86	77	69	64	80	72	66	61	65	60	56	57	54	50	51	48	45	42
4	79	68	61	55	74	65	58	52	58	52	48	52	47	44	46	42	40	37
5	73	61	53	47	68	58	51	46	52	46	42	47	42	39	42	38	35	32
6	67	55	47	42	63	53	45	40	47	42	37	43	38	34	38	34	31	29
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17111	17111	17111	17111
5°	20398	17184	15132	17184
10°	25468	17086	13671	17086
15°	29895	16912	12467	16912
20°	33364	16651	11443	16651
25°	32831	16376	10815	16376
30°	23599	16122	10167	16122
35°	15757	15792	9747	15792
40°	11609	15396	9313	15396
45°	9738	14700	8888	14700
50°	8592	13788	8296	13788
55°	7535	12746	7484	12746
60°	6710	11750	6857	11750
65°	5894	10677	6378	10677
70°	4626	9725	5825	9725
75°	4076	8492	5319	8492
80°	3546	7215	5232	7215
85°	2853	5805	5545	5805



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	2.6
10°-20°	488.4	8.0
20°-30°	767.3	12.6
30°-40°	800.5	13.2
40°-50°	685.1	11.3
50°-60°	522.2	8.6
60°-70°	334.7	5.5
70°-80°	161.0	2.6
80°-90°	44.8	0.7
90°-100°	156.8	2.6
100°-110°	444.0	7.3
110°-120°	436.8	7.2
120°-130°	348.4	5.7
130°-140°	274.7	4.5
140°-150°	205.0	3.4
150°-160°	142.9	2.4
160°-170°	83.9	1.4
170°-180°	27.3	0.4
0°-30°	1412.0	23.2
0°-40°	2212.6	36.4
0°-60°	3419.8	56.2
0°-90°	3960.3	65.1
90°-120°	1037.6	17.1
90°-150°	1865.7	30.7
90°-180°	2120.0	34.9
0°-180°	6080.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1888	1590	1400	1590	1888	195
15°	2683	1518	1119	1518	2683	761
25°	2764	1379	911	1379	2764	1188
35°	1199	1202	742	1202	1199	786
45°	640	966	584	966	640	503
55°	402	679	399	679	402	363
65°	231	419	250	419	231	228
75°	98	204	128	204	98	105
85°	23	47	45	47	23	27
90°	16	1	16	1	16	9
95°	66	19	66	19	66	119
105°	726	66	726	66	726	716
115°	882	117	882	117	882	857
125°	696	163	696	163	696	631
135°	564	190	564	190	564	438
145°	441	217	441	217	441	280
155°	366	247	366	247	366	171
165°	319	270	319	270	319	91
175°	287	281	287	281	287	28
180°	282	282	282	282	282	



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1693.2	1695.3	1688.3	1687.2	1679.0	1676.8	1676.8	1665.4	1658.3	1649.1	1643.6
5°	1887.8	1898.7	1893.2	1881.0	1860.6	1855.8	1842.9	1822.5	1799.3	1770.7	1757.1
7.5°	2130.9	2145.7	2140.0	2121.1	2099.7	2082.4	2046.0	2012.1	1964.6	1922.9	1887.3
10°	2330.1	2314.5	2302.2	2283.9	2264.1	2232.1	2194.0	2141.6	2081.1	2033.4	1980.4
12.5°	2479.3	2476.7	2461.2	2442.3	2414.4	2384.0	2337.2	2273.4	2203.0	2134.2	2073.4
15°	2682.7	2686.7	2676.5	2656.8	2617.3	2563.6	2492.8	2466.3	2365.5	2290.7	2215.8
17.5°	2823.4	2822.6	2821.2	2793.9	2753.6	2715.3	2649.7	2579.9	2488.7	2383.2	2282.4
20°	2912.7	2905.9	2907.2	2876.6	2846.7	2802.4	2738.5	2637.1	2562.2	2440.4	2336.3
22.5°	2910.5	2909.1	2914.3	2903.8	2882.1	2848.2	2797.8	2712.2	2616.6	2493.7	2376.6
25°	2764.3	2758.9	2790.9	2799.7	2834.4	2840.5	2825.6	2778.6	2688.1	2561.5	2416.6
27.5°	2313.5	2310.5	2369.9	2444.2	2538.4	2611.6	2682.4	2716.6	2688.1	2597.5	2452.2
30°	1898.7	1962.7	1992.6	2100.1	2219.9	2362.8	2488.0	2607.1	2636.4	2596.9	2477.8
32.5°	1576.4	1632.2	1657.2	1749.5	1861.1	2028.5	2216.4	2385.0	2504.1	2534.3	2462.6
35°	1199.1	1199.8	1256.9	1297.8	1401.2	1573.4	1755.8	1981.7	2206.3	2376.4	2394.1
37.5°	956.8	960.2	994.8	1035.5	1113.1	1204.1	1364.7	1552.6	1812.0	2073.2	2226.3
40°	826.2	832.3	858.2	898.3	954.1	1022.8	1148.1	1325.0	1541.4	1832.0	2069.5
42.5°	742.3	752.3	765.6	796.5	831.1	895.4	996.7	1133.4	1330.2	1605.0	1879.0
45°	639.7	645.1	655.4	669.6	700.9	745.9	813.9	905.8	1069.1	1290.3	1564.5
47.5°	564.3	561.4	572.2	583.8	604.6	635.2	680.8	755.8	872.3	1049.8	1282.4
50°	513.1	512.4	519.9	528.8	548.5	571.0	608.4	664.9	757.4	904.4	1117.4
52.5°	465.2	467.8	473.1	484.1	498.4	516.5	550.1	590.8	670.3	797.2	974.8
55°	401.5	403.6	411.0	417.2	427.4	445.7	466.8	500.9	555.3	643.8	790.1
57.5°	347.6	346.7	353.9	355.4	366.9	381.9	398.2	424.7	464.1	529.9	628.4
60°	311.7	309.6	315.8	320.5	326.7	338.9	352.5	378.4	409.7	458.0	542.4
62.5°	279.0	278.1	282.6	287.3	292.4	303.5	315.0	334.8	359.6	400.3	467.3
65°	231.4	233.4	235.5	237.5	240.2	247.0	257.9	271.5	288.5	317.1	365.4
67.5°	181.8	183.9	184.6	188.8	194.6	198.9	205.5	217.6	229.5	253.6	281.1
70°	147.0	146.3	147.0	149.0	156.5	164.0	172.9	181.7	189.2	206.2	229.3
72.5°	126.3	125.1	126.9	127.3	130.9	133.0	138.6	146.9	156.5	168.1	184.7
75°	98.0	98.0	98.0	98.0	100.7	102.1	104.1	106.2	109.6	115.0	127.3
77.5°	72.4	72.5	73.5	74.2	74.7	75.5	76.8	78.8	80.0	82.9	88.2
80°	57.2	57.8	57.2	57.8	57.8	59.2	59.9	61.9	62.6	66.0	68.1
82.5°	43.0	42.6	43.0	43.7	43.7	45.1	45.2	46.7	46.8	48.6	50.6
85°	23.1	21.8	23.1	22.5	23.8	22.5	23.1	24.5	24.5	25.2	27.9
87.5°	8.8	10.0	8.8	9.2	9.3	9.6	9.5	9.4	10.4	9.9	10.1
90°	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3	13.7	14.3	12.5
92.5°	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0	66.2	87.7	96.5
95°	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3	274.3	338.2	301.2
97.5°	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9	560.8	524.2	383.7
100°	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5	652.5	540.1	365.0
102.5°	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9	657.1	510.5	337.7
105°	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5	622.3	458.6	304.0
107.5°	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5	561.4	412.7	282.6
110°	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6	523.0	386.7	274.3



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2	489.7	369.4	269.8
115°	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0	449.5	350.8	268.1
117.5°	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2	425.2	339.8	269.1
120°	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8	412.4	334.8	270.9
122.5°	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9	401.9	331.6	274.1
125°	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4	388.4	327.4	278.9
127.5°	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8	376.6	325.3	284.4
130°	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5	370.2	324.0	288.0
132.5°	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1	364.2	323.5	290.8
135°	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7	356.5	322.8	294.9
137.5°	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7	349.8	321.6	297.6
140°	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5	345.6	321.1	299.4
142.5°	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7	342.0	320.2	300.8
145°	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3	337.1	318.8	301.7
147.5°	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7	332.3	316.7	301.7
150°	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2	329.1	314.8	301.7
152.5°	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2	325.5	312.6	300.4
155°	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7	320.0	308.6	298.9
157.5°	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7	313.8	305.0	296.9
160°	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1	309.7	302.3	296.0
162.5°	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7	305.6	299.6	294.2
165°	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6	300.0	295.5	291.5
167.5°	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4	294.7	291.3	288.7
170°	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3	291.5	288.6	286.9
172.5°	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7	288.3	286.3	285.5
175°	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8	284.6	283.5	283.5
177.5°	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7	282.2	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1641.4	1639.8	1632.2	1623.5	1612.0	1604.4	1598.4	1595.2	1585.4	1573.4	1565.2
5°	1742.8	1722.4	1700.7	1674.1	1649.6	1624.4	1608.8	1590.4	1567.9	1542.8	1525.1
7.5°	1851.5	1811.4	1768.3	1723.8	1679.8	1640.4	1605.5	1575.7	1539.9	1503.8	1478.5
10°	1934.8	1876.2	1815.7	1753.7	1697.2	1644.2	1603.3	1563.2	1520.3	1478.8	1447.5
12.5°	2010.4	1933.4	1863.6	1787.5	1715.2	1651.8	1593.0	1545.8	1494.2	1449.9	1414.3
15°	2106.2	2027.3	1942.9	1827.2	1731.3	1651.0	1579.5	1517.6	1455.0	1400.5	1365.8
17.5°	2195.8	2077.0	1963.6	1867.1	1742.4	1642.1	1554.9	1480.8	1412.1	1354.4	1311.7
20°	2232.8	2117.8	1994.6	1871.5	1749.0	1636.7	1535.3	1453.6	1382.2	1316.8	1277.4
22.5°	2255.1	2124.9	1995.2	1862.8	1732.6	1616.0	1515.7	1425.9	1348.4	1286.3	1237.6
25°	2281.1	2126.0	1983.1	1852.4	1719.7	1593.1	1474.0	1378.8	1295.1	1229.0	1177.3
27.5°	2298.3	2115.8	1946.9	1801.6	1667.0	1541.0	1431.8	1330.8	1245.9	1176.1	1120.6
30°	2301.6	2107.6	1919.1	1761.9	1625.1	1509.4	1393.7	1297.1	1207.3	1133.1	1081.4
32.5°	2305.9	2087.5	1881.5	1714.5	1574.5	1459.9	1355.1	1262.8	1170.8	1097.7	1044.9
35°	2288.0	2076.3	1824.5	1632.6	1492.4	1381.5	1286.9	1201.8	1111.3	1040.5	986.8
37.5°	2210.6	2032.1	1765.4	1540.3	1393.7	1291.0	1213.9	1139.8	1056.7	980.4	929.7
40°	2132.8	1988.5	1719.7	1484.2	1331.1	1225.6	1156.2	1095.7	1015.4	943.9	889.5
42.5°	2016.8	1929.2	1676.2	1425.4	1260.3	1158.7	1100.1	1043.4	972.9	900.3	849.2
45°	1804.1	1815.7	1587.0	1331.8	1162.3	1060.3	1005.1	965.7	903.1	843.2	790.8
47.5°	1537.3	1645.5	1482.3	1232.0	1059.0	963.2	915.0	880.6	838.4	779.6	731.8
50°	1363.1	1517.6	1398.5	1165.1	994.3	899.0	851.3	823.4	786.7	740.4	694.8
52.5°	1202.5	1368.4	1297.2	1090.5	924.0	836.9	790.4	767.4	738.2	694.7	653.4
55°	980.6	1148.7	1132.4	977.9	818.7	740.4	705.0	679.2	659.4	626.8	594.1
57.5°	793.2	952.6	961.0	852.7	725.9	648.5	618.1	598.6	585.7	561.0	530.8
60°	675.1	821.4	850.0	768.3	659.4	591.4	561.4	545.8	535.6	515.8	492.7
62.5°	577.1	701.6	734.0	675.2	595.7	532.0	508.6	493.5	486.6	469.6	449.2
65°	441.7	545.1	576.4	543.7	502.2	451.2	432.1	419.2	413.1	403.6	388.6
67.5°	332.1	407.5	441.8	418.8	403.8	371.6	359.5	352.5	347.1	340.5	328.0
70°	266.8	322.6	358.0	351.8	339.6	322.6	313.7	309.0	303.5	298.1	287.2
72.5°	214.5	252.9	286.1	289.2	279.2	275.8	268.0	266.0	262.7	256.2	250.2
75°	142.2	168.8	191.9	200.8	204.8	208.2	204.8	204.2	203.5	198.0	194.6
77.5°	93.2	107.5	122.1	137.2	143.6	148.2	149.3	151.8	150.0	147.1	145.5
80°	71.5	74.9	85.1	98.0	108.2	112.3	115.0	116.4	115.7	115.0	112.3
82.5°	51.9	54.7	59.5	68.6	77.2	84.0	85.6	85.3	86.8	87.2	85.1
85°	27.9	28.6	29.9	31.3	36.1	43.6	45.6	47.0	48.3	48.3	44.2
87.5°	10.9	10.0	10.7	10.5	11.9	12.1	15.2	17.6	18.4	16.5	16.8
90°	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1	2.3	3.4	5.1
92.5°	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1	10.5	15.3	19.7
95°	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4	21.1	27.4	37.1
97.5°	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1	33.7	38.6	47.0
100°	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2	42.8	46.8	54.8
102.5°	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8	52.8	56.4	63.9
105°	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2	67.9	71.3	78.1
107.5°	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4	83.2	86.5	93.2
110°	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4	94.1	97.0	103.2



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4	104.2	107.0	113.3
115°	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9	119.2	122.6	128.3
117.5°	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4	134.0	136.9	142.1
120°	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5	143.2	146.0	151.7
122.5°	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1	151.8	154.7	160.8
125°	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6	163.7	167.1	173.4
127.5°	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0	173.7	178.0	184.3
130°	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0	179.7	184.8	191.6
132.5°	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5	184.7	190.3	198.5
135°	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5	192.8	199.1	207.6
137.5°	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0	200.4	206.6	215.7
140°	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1	205.9	211.6	220.7
142.5°	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5	210.9	217.1	225.3
145°	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3	219.0	224.2	232.7
147.5°	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2	227.2	232.3	239.7
150°	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1	232.7	237.3	244.7
152.5°	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1	238.2	242.8	249.3
155°	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0	247.0	250.4	256.1
157.5°	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0	254.5	257.2	262.3
160°	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5	259.5	261.8	266.4
162.5°	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6	263.6	265.5	269.1
165°	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8	269.2	270.4	273.2
167.5°	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5	273.8	274.3	276.5
170°	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2	276.1	276.6	278.3
172.5°	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0	278.3	278.5	279.7
175°	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2	280.6	280.1	281.2
177.5°	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2	281.8	281.3	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1562.5	1555.4	1550.5	1539.6	1532.6	1524.9	1517.3	1522.2	1521.7	1521.1	1521.1
5°	1510.1	1494.4	1480.2	1461.8	1450.2	1435.9	1425.0	1423.7	1426.4	1416.9	1411.4
7.5°	1458.1	1436.7	1416.5	1396.2	1374.7	1357.5	1346.8	1341.7	1334.8	1328.9	1322.8
10°	1421.6	1396.5	1376.7	1351.5	1328.4	1308.0	1295.1	1286.2	1281.4	1276.7	1267.8
12.5°	1384.1	1359.4	1334.3	1305.8	1283.8	1260.1	1250.4	1240.5	1231.4	1226.0	1213.9
15°	1329.1	1297.1	1270.6	1240.6	1216.1	1193.0	1179.4	1159.6	1156.9	1150.1	1137.9
17.5°	1274.0	1239.2	1202.6	1180.5	1152.8	1128.7	1108.0	1101.4	1081.9	1074.6	1063.9
20°	1230.4	1198.4	1170.5	1141.3	1101.1	1078.6	1062.3	1053.5	1037.8	1028.3	1021.5
22.5°	1192.8	1160.3	1128.1	1093.9	1060.8	1035.6	1023.7	1009.9	1001.3	988.0	980.6
25°	1139.2	1103.8	1065.0	1028.3	1004.5	985.4	966.4	954.1	941.9	935.7	922.1
27.5°	1076.9	1039.9	1003.6	975.7	946.5	927.7	910.4	899.5	884.8	874.5	867.0
30°	1042.6	999.0	967.7	942.5	905.1	887.4	874.5	860.9	850.0	839.1	831.6
32.5°	1002.8	963.1	933.4	902.3	873.5	854.2	837.5	825.5	816.2	805.9	798.4
35°	940.5	907.2	876.5	845.2	824.1	804.4	784.7	774.4	765.6	756.1	749.3
37.5°	884.1	853.0	823.9	794.2	768.0	752.0	736.1	728.3	716.3	709.9	703.0
40°	849.3	818.7	787.4	758.8	731.6	719.3	705.0	693.5	682.6	677.8	670.3
42.5°	811.2	780.6	754.2	723.4	701.1	684.5	671.3	658.6	650.5	643.5	639.3
45°	754.7	727.5	701.6	671.0	649.9	635.6	620.6	609.1	601.6	596.8	589.3
47.5°	699.9	672.6	646.4	619.7	599.3	582.9	568.0	559.9	550.0	544.2	539.1
50°	660.1	635.6	607.7	583.2	562.8	546.5	534.2	524.0	515.2	507.7	504.3
52.5°	623.6	597.5	573.4	550.6	529.0	510.5	499.4	488.6	482.0	473.4	469.4
55°	563.5	538.3	517.9	495.4	474.3	458.7	445.1	435.5	428.7	419.2	413.8
57.5°	507.0	484.4	460.0	440.6	418.8	405.6	394.3	381.4	373.1	365.6	360.3
60°	468.9	443.0	421.9	403.6	384.5	367.5	357.3	347.1	338.2	330.7	326.0
62.5°	429.1	406.6	386.5	366.5	349.1	334.3	322.4	313.9	306.1	301.3	296.6
65°	368.2	350.5	330.1	313.7	297.4	286.5	277.0	269.5	264.0	260.6	256.6
67.5°	312.1	294.9	277.1	261.1	250.2	241.9	235.6	229.2	226.5	222.1	219.4
70°	275.6	257.9	242.3	230.0	219.1	213.0	208.9	204.2	201.4	196.0	193.3
72.5°	235.9	223.1	211.8	201.7	193.0	187.4	182.2	176.4	172.0	166.0	163.3
75°	185.8	174.2	165.4	158.6	153.1	145.6	138.1	132.0	130.0	127.9	127.3
77.5°	137.6	130.3	123.9	118.1	111.3	105.9	104.3	102.9	102.5	101.4	101.4
80°	108.2	101.4	96.6	89.8	85.7	85.7	85.7	84.4	85.1	85.1	85.1
82.5°	80.4	74.2	71.6	69.1	68.3	68.9	68.9	69.1	68.7	69.8	69.3
85°	41.5	42.2	43.6	42.9	43.6	43.6	44.9	44.2	44.9	43.6	44.9
87.5°	16.5	18.4	19.2	20.1	21.0	20.8	21.2	21.4	22.0	22.1	22.4
90°	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3	14.8	15.4	16.5
92.5°	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0	38.1	33.7	30.7
95°	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3	139.2	108.9	88.4
97.5°	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9	410.0	336.4	268.2
100°	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5	626.3	559.5	478.5
102.5°	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9	724.4	685.5	634.1
105°	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5	798.5	809.4	794.5
107.5°	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5	789.2	839.1	859.4
110°	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6	758.6	830.5	870.4



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2	718.4	799.0	850.3
115°	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0	654.2	738.1	800.2
117.5°	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2	599.9	675.2	738.3
120°	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8	569.8	638.2	695.9
122.5°	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9	545.6	609.0	662.5
125°	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4	515.6	570.4	616.0
127.5°	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8	489.3	538.7	580.2
130°	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5	472.8	519.0	557.8
132.5°	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1	457.3	500.3	537.3
135°	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7	435.2	472.3	504.8
137.5°	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7	413.9	445.8	474.0
140°	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5	401.5	428.9	453.4
142.5°	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7	389.7	413.4	434.7
145°	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3	374.2	392.4	409.0
147.5°	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7	362.6	377.4	389.1
150°	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2	355.3	367.3	378.2
152.5°	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2	348.5	359.1	368.1
155°	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7	338.8	347.4	354.2
157.5°	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7	329.3	336.0	341.3
160°	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1	323.4	329.1	333.1
162.5°	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7	317.0	322.3	325.8
165°	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6	308.0	312.0	314.8
167.5°	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4	301.0	303.3	305.4
170°	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3	296.0	298.3	299.4
172.5°	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7	291.9	293.7	294.4
175°	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8	286.3	287.5	287.5
177.5°	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7	283.1	283.6	283.6
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1514.6	1514.0	1514.6	1512.4	1514.6	1514.0	1514.6	1521.1	1521.1	1521.7	1522.2
5°	1409.4	1408.7	1406.7	1400.5	1406.7	1408.7	1409.4	1411.4	1416.9	1426.4	1423.7
7.5°	1317.5	1316.6	1310.6	1310.7	1310.6	1316.6	1317.5	1322.8	1328.9	1334.8	1341.7
10°	1263.1	1263.7	1255.6	1250.8	1255.6	1263.7	1263.1	1267.8	1276.7	1281.4	1286.2
12.5°	1210.3	1207.1	1200.6	1195.3	1200.6	1207.1	1210.3	1213.9	1226.0	1231.4	1240.5
15°	1140.6	1133.8	1117.4	1118.8	1117.4	1133.8	1140.6	1137.9	1150.1	1156.9	1159.6
17.5°	1058.5	1053.5	1053.2	1043.7	1053.2	1053.5	1058.5	1063.9	1074.6	1081.9	1101.4
20°	1010.6	1007.2	1008.5	999.0	1008.5	1007.2	1010.6	1021.5	1028.3	1037.8	1053.5
22.5°	973.0	969.6	963.9	960.9	963.9	969.6	973.0	980.6	988.0	1001.3	1009.9
25°	918.0	912.6	907.2	910.6	907.2	912.6	918.0	922.1	935.7	941.9	954.1
27.5°	863.1	859.0	853.5	852.8	853.5	859.0	863.1	867.0	874.5	884.8	899.5
30°	828.2	824.1	821.4	818.0	821.4	824.1	828.2	831.6	839.1	850.0	860.9
32.5°	792.8	792.0	787.1	786.4	787.1	792.0	792.8	798.4	805.9	816.2	825.5
35°	746.5	742.5	741.1	741.8	741.1	742.5	746.5	749.3	756.1	765.6	774.4
37.5°	702.6	697.1	694.7	692.2	694.7	697.1	702.6	703.0	709.9	716.3	728.3
40°	671.0	665.6	664.2	662.8	664.2	665.6	671.0	670.3	677.8	682.6	693.5
42.5°	635.6	633.4	632.6	630.2	632.6	633.4	635.6	639.3	643.5	650.5	658.6
45°	587.3	586.6	582.5	583.9	582.5	586.6	587.3	589.3	596.8	601.6	609.1
47.5°	536.4	533.4	530.5	532.4	530.5	533.4	536.4	539.1	544.2	550.0	559.9
50°	501.6	500.2	494.1	495.4	494.1	500.2	501.6	504.3	507.7	515.2	524.0
52.5°	466.7	461.5	459.2	458.4	459.2	461.5	466.7	469.4	473.4	482.0	488.6
55°	409.0	402.9	400.2	398.8	400.2	402.9	409.0	413.8	419.2	428.7	435.5
57.5°	352.4	350.7	348.6	350.1	348.6	350.7	352.4	360.3	365.6	373.1	381.4
60°	319.2	319.2	319.2	318.5	319.2	319.2	319.2	326.0	330.7	338.2	347.1
62.5°	293.6	291.9	291.4	292.4	291.4	291.9	293.6	296.6	301.3	306.1	313.9
65°	254.5	253.8	251.1	250.4	251.1	253.8	254.5	256.6	260.6	264.0	269.5
67.5°	217.6	215.2	214.4	213.4	214.4	215.2	217.6	219.4	222.1	226.5	229.2
70°	189.9	188.5	184.4	185.1	184.4	188.5	189.9	193.3	196.0	201.4	204.2
72.5°	159.9	158.6	157.7	156.8	157.7	158.6	159.9	163.3	166.0	172.0	176.4
75°	126.6	125.9	125.2	127.9	125.2	125.9	126.6	127.3	127.9	130.0	132.0
77.5°	101.4	101.4	101.8	100.7	101.8	101.4	101.4	101.4	101.4	102.5	102.9
80°	85.1	85.1	84.4	84.4	84.4	85.1	85.1	85.1	85.1	85.1	84.4
82.5°	68.2	68.7	69.1	68.1	69.1	68.7	68.2	69.3	69.8	68.7	69.1
85°	44.9	44.2	45.6	44.9	45.6	44.2	44.9	44.9	43.6	44.9	44.2
87.5°	23.3	22.4	22.5	22.9	22.5	22.4	23.3	22.4	22.1	22.0	21.4
90°	16.0	16.5	17.1	16.5	17.1	16.5	16.0	16.5	15.4	14.8	14.3
92.5°	29.7	27.9	28.5	27.5	28.5	27.9	29.7	30.7	33.7	38.1	48.0
95°	77.6	72.4	68.4	66.2	68.4	72.4	77.6	88.4	108.9	139.2	205.3
97.5°	226.1	200.4	185.0	180.1	185.0	200.4	226.1	268.2	336.4	410.0	511.9
100°	420.9	379.3	357.1	357.6	357.1	379.3	420.9	478.5	559.5	626.3	672.5
102.5°	589.3	556.3	537.7	524.6	537.7	556.3	589.3	634.1	685.5	724.4	725.9
105°	768.3	746.6	728.4	725.5	728.4	746.6	768.3	794.5	809.4	798.5	741.5
107.5°	859.9	852.6	846.4	841.2	846.4	852.6	859.9	859.4	839.1	789.2	696.5
110°	886.4	890.9	889.8	888.6	889.8	890.9	886.4	870.4	830.5	758.6	653.6



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	879.5	893.7	898.0	898.2	898.0	893.7	879.5	850.3	799.0	718.4	611.2
115°	843.0	868.1	879.5	882.4	879.5	868.1	843.0	800.2	738.1	654.2	555.0
117.5°	782.9	811.6	828.1	831.9	828.1	811.6	782.9	738.3	675.2	599.9	514.2
120°	740.9	772.9	786.5	790.0	786.5	772.9	740.9	695.9	638.2	569.8	492.8
122.5°	702.6	731.3	746.4	750.7	746.4	731.3	702.6	662.5	609.0	545.6	475.9
125°	652.5	677.6	691.9	695.9	691.9	677.6	652.5	616.0	570.4	515.6	453.4
127.5°	612.7	634.1	647.0	650.7	647.0	634.1	612.7	580.2	538.7	489.3	433.8
130°	588.1	608.6	620.6	625.1	620.6	608.6	588.1	557.8	519.0	472.8	421.5
132.5°	565.7	586.2	596.8	600.0	596.8	586.2	565.7	537.3	500.3	457.3	410.1
135°	532.7	549.8	560.1	564.1	560.1	549.8	532.7	504.8	472.3	435.2	394.7
137.5°	497.5	514.8	523.5	526.1	523.5	514.8	497.5	474.0	445.8	413.9	380.7
140°	475.1	491.1	500.2	499.6	500.2	491.1	475.1	453.4	428.9	401.5	372.5
142.5°	453.2	467.4	475.6	475.0	475.6	467.4	453.2	434.7	413.4	389.7	364.7
145°	423.2	435.2	439.8	440.9	439.8	435.2	423.2	409.0	392.4	374.2	355.3
147.5°	399.9	408.0	412.4	412.8	412.4	408.0	399.9	389.1	377.4	362.6	347.7
150°	386.7	393.0	396.4	396.4	396.4	393.0	386.7	378.2	367.3	355.3	342.2
152.5°	374.8	380.7	382.7	382.7	382.7	380.7	374.8	368.1	359.1	348.5	337.2
155°	359.3	363.9	365.0	365.6	365.0	363.9	359.3	354.2	347.4	338.8	329.7
157.5°	345.8	349.2	350.1	350.0	350.1	349.2	345.8	341.3	336.0	329.3	321.7
160°	337.1	340.5	340.5	339.9	340.5	340.5	337.1	333.1	329.1	323.4	317.1
162.5°	328.4	331.4	331.4	330.8	331.4	331.4	328.4	325.8	322.3	317.0	311.7
165°	317.1	319.4	318.8	318.8	318.8	319.4	317.1	314.8	312.0	308.0	304.6
167.5°	306.4	308.0	307.4	307.4	307.4	308.0	306.4	305.4	303.3	301.0	298.4
170°	300.0	301.2	300.6	300.6	300.6	301.2	300.0	299.4	298.3	296.0	294.3
172.5°	294.5	295.7	294.7	294.2	294.7	295.7	294.5	294.4	293.7	291.9	290.7
175°	287.5	288.0	287.5	286.9	287.5	288.0	287.5	287.5	287.5	286.3	285.8
177.5°	283.1	283.6	282.7	282.7	282.7	283.6	283.1	283.6	283.6	283.1	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1517.3	1524.9	1532.6	1539.6	1550.5	1555.4	1562.5	1565.2	1573.4	1585.4	1595.2
5°	1425.0	1435.9	1450.2	1461.8	1480.2	1494.4	1510.1	1525.1	1542.8	1567.9	1590.4
7.5°	1346.8	1357.5	1374.7	1396.2	1416.5	1436.7	1458.1	1478.5	1503.8	1539.9	1575.7
10°	1295.1	1308.0	1328.4	1351.5	1376.7	1396.5	1421.6	1447.5	1478.8	1520.3	1563.2
12.5°	1250.4	1260.1	1283.8	1305.8	1334.3	1359.4	1384.1	1414.3	1449.9	1494.2	1545.8
15°	1179.4	1193.0	1216.1	1240.6	1270.6	1297.1	1329.1	1365.8	1400.5	1455.0	1517.6
17.5°	1108.0	1128.7	1152.8	1180.5	1202.6	1239.2	1274.0	1311.7	1354.4	1412.1	1480.8
20°	1062.3	1078.6	1101.1	1141.3	1170.5	1198.4	1230.4	1277.4	1316.8	1382.2	1453.6
22.5°	1023.7	1035.6	1060.8	1093.9	1128.1	1160.3	1192.8	1237.6	1286.3	1348.4	1425.9
25°	966.4	985.4	1004.5	1028.3	1065.0	1103.8	1139.2	1177.3	1229.0	1295.1	1378.8
27.5°	910.4	927.7	946.5	975.7	1003.6	1039.9	1076.9	1120.6	1176.1	1245.9	1330.8
30°	874.5	887.4	905.1	942.5	967.7	999.0	1042.6	1081.4	1133.1	1207.3	1297.1
32.5°	837.5	854.2	873.5	902.3	933.4	963.1	1002.8	1044.9	1097.7	1170.8	1262.8
35°	784.7	804.4	824.1	845.2	876.5	907.2	940.5	986.8	1040.5	1111.3	1201.8
37.5°	736.1	752.0	768.0	794.2	823.9	853.0	884.1	929.7	980.4	1056.7	1139.8
40°	705.0	719.3	731.6	758.8	787.4	818.7	849.3	889.5	943.9	1015.4	1095.7
42.5°	671.3	684.5	701.1	723.4	754.2	780.6	811.2	849.2	900.3	972.9	1043.4
45°	620.6	635.6	649.9	671.0	701.6	727.5	754.7	790.8	843.2	903.1	965.7
47.5°	568.0	582.9	599.3	619.7	646.4	672.6	699.9	731.8	779.6	838.4	880.6
50°	534.2	546.5	562.8	583.2	607.7	635.6	660.1	694.8	740.4	786.7	823.4
52.5°	499.4	510.5	529.0	550.6	573.4	597.5	623.6	653.4	694.7	738.2	767.4
55°	445.1	458.7	474.3	495.4	517.9	538.3	563.5	594.1	626.8	659.4	679.2
57.5°	394.3	405.6	418.8	440.6	460.0	484.4	507.0	530.8	561.0	585.7	598.6
60°	357.3	367.5	384.5	403.6	421.9	443.0	468.9	492.7	515.8	535.6	545.8
62.5°	322.4	334.3	349.1	366.5	386.5	406.6	429.1	449.2	469.6	486.6	493.5
65°	277.0	286.5	297.4	313.7	330.1	350.5	368.2	388.6	403.6	413.1	419.2
67.5°	235.6	241.9	250.2	261.1	277.1	294.9	312.1	328.0	340.5	347.1	352.5
70°	208.9	213.0	219.1	230.0	242.3	257.9	275.6	287.2	298.1	303.5	309.0
72.5°	182.2	187.4	193.0	201.7	211.8	223.1	235.9	250.2	256.2	262.7	266.0
75°	138.1	145.6	153.1	158.6	165.4	174.2	185.8	194.6	198.0	203.5	204.2
77.5°	104.3	105.9	111.3	118.1	123.9	130.3	137.6	145.5	147.1	150.0	151.8
80°	85.7	85.7	85.7	89.8	96.6	101.4	108.2	112.3	115.0	115.7	116.4
82.5°	68.9	68.9	68.3	69.1	71.6	74.2	80.4	85.1	87.2	86.8	85.3
85°	44.9	43.6	43.6	42.9	43.6	42.2	41.5	44.2	48.3	48.3	47.0
87.5°	21.2	20.8	21.0	20.1	19.2	18.4	16.5	16.8	16.5	18.4	17.6
90°	13.7	14.3	12.5	10.8	9.1	7.4	6.3	5.1	3.4	2.3	1.1
92.5°	66.2	87.7	96.5	72.4	47.9	33.0	24.5	19.7	15.3	10.5	7.1
95°	274.3	338.2	301.2	207.6	122.6	74.1	51.9	37.1	27.4	21.1	19.4
97.5°	560.8	524.2	383.7	227.8	132.0	85.7	61.6	47.0	38.6	33.7	33.1
100°	652.5	540.1	365.0	215.0	130.6	90.7	68.4	54.8	46.8	42.8	42.2
102.5°	657.1	510.5	337.7	204.1	132.4	96.6	76.2	63.9	56.4	52.8	51.8
105°	622.3	458.6	304.0	196.2	137.5	106.7	89.0	78.1	71.3	67.9	66.2
107.5°	561.4	412.7	282.6	195.6	146.8	119.8	103.4	93.2	86.5	83.2	81.4
110°	523.0	386.7	274.3	197.9	154.6	128.9	112.9	103.2	97.0	94.1	92.4



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	489.7	369.4	269.8	202.5	162.3	138.5	123.0	113.3	107.0	104.2	102.4
115°	449.5	350.8	268.1	209.9	175.1	153.4	138.0	128.3	122.6	119.2	116.9
117.5°	425.2	339.8	269.1	219.7	188.7	167.2	153.0	142.1	136.9	134.0	131.4
120°	412.4	334.8	270.9	227.0	197.3	176.8	162.6	151.7	146.0	143.2	141.5
122.5°	401.9	331.6	274.1	233.9	206.5	186.4	171.2	160.8	154.7	151.8	150.1
125°	388.4	327.4	278.9	244.7	219.6	199.6	184.2	173.4	167.1	163.7	162.6
127.5°	376.6	325.3	284.4	253.6	231.0	211.7	196.3	184.3	178.0	173.7	172.0
130°	370.2	324.0	288.0	259.5	237.8	219.0	203.6	191.6	184.8	179.7	178.0
132.5°	364.2	323.5	290.8	265.0	243.8	225.4	210.5	198.5	190.3	184.7	182.5
135°	356.5	322.8	294.9	272.1	252.7	235.0	219.6	207.6	199.1	192.8	190.5
137.5°	349.8	321.6	297.6	277.3	258.8	241.8	227.6	215.7	206.6	200.4	198.0
140°	345.6	321.1	299.4	280.1	262.9	246.4	232.1	220.7	211.6	205.9	203.1
142.5°	342.0	320.2	300.8	282.8	266.1	250.1	236.7	225.3	217.1	210.9	208.5
145°	337.1	318.8	301.7	285.8	270.4	255.5	242.4	232.7	224.2	219.0	217.3
147.5°	332.3	316.7	301.7	287.6	273.8	260.2	249.0	239.7	232.3	227.2	226.2
150°	329.1	314.8	301.7	288.0	276.1	262.9	252.7	244.7	237.3	232.7	232.1
152.5°	325.5	312.6	300.4	289.0	277.4	266.1	256.3	249.3	242.8	238.2	238.1
155°	320.0	308.6	298.9	289.2	280.1	270.4	262.4	256.1	250.4	247.0	247.0
157.5°	313.8	305.0	296.9	289.8	281.5	273.8	267.6	262.3	257.2	254.5	254.0
160°	309.7	302.3	296.0	289.8	282.9	276.1	270.4	266.4	261.8	259.5	259.5
162.5°	305.6	299.6	294.2	289.3	283.4	277.4	272.6	269.1	265.5	263.6	263.6
165°	300.0	295.5	291.5	288.0	284.0	279.5	275.5	273.2	270.4	269.2	269.8
167.5°	294.7	291.3	288.7	287.1	283.9	280.6	278.1	276.5	274.3	273.8	274.5
170°	291.5	288.6	286.9	285.8	283.5	280.6	279.5	278.3	276.6	276.1	277.2
172.5°	288.3	286.3	285.5	285.3	283.5	281.1	280.4	279.7	278.5	278.3	279.0
175°	284.6	283.5	283.5	284.0	282.9	281.8	281.2	281.2	280.1	280.6	281.2
177.5°	282.2	281.8	282.2	283.1	282.2	281.8	281.8	281.8	281.3	281.8	282.2
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1598.4	1604.4	1612.0	1623.5	1632.2	1639.8	1641.4	1643.6	1649.1	1658.3	1665.4
5°	1608.8	1624.4	1649.6	1674.1	1700.7	1722.4	1742.8	1757.1	1770.7	1799.3	1822.5
7.5°	1605.5	1640.4	1679.8	1723.8	1768.3	1811.4	1851.5	1887.3	1922.9	1964.6	2012.1
10°	1603.3	1644.2	1697.2	1753.7	1815.7	1876.2	1934.8	1980.4	2033.4	2081.1	2141.6
12.5°	1593.0	1651.8	1715.2	1787.5	1863.6	1933.4	2010.4	2073.4	2134.2	2203.0	2273.4
15°	1579.5	1651.0	1731.3	1827.2	1942.9	2027.3	2106.2	2215.8	2290.7	2365.5	2466.3
17.5°	1554.9	1642.1	1742.4	1867.1	1963.6	2077.0	2195.8	2282.4	2383.2	2488.7	2579.9
20°	1535.3	1636.7	1749.0	1871.5	1994.6	2117.8	2232.8	2336.3	2440.4	2562.2	2637.1
22.5°	1515.7	1616.0	1732.6	1862.8	1995.2	2124.9	2255.1	2376.6	2493.7	2616.6	2712.2
25°	1474.0	1593.1	1719.7	1852.4	1983.1	2126.0	2281.1	2416.6	2561.5	2688.1	2778.6
27.5°	1431.8	1541.0	1667.0	1801.6	1946.9	2115.8	2298.3	2452.2	2597.5	2688.1	2716.6
30°	1393.7	1509.4	1625.1	1761.9	1919.1	2107.6	2301.6	2477.8	2596.9	2636.4	2607.1
32.5°	1355.1	1459.9	1574.5	1714.5	1881.5	2087.5	2305.9	2462.6	2534.3	2504.1	2385.0
35°	1286.9	1381.5	1492.4	1632.6	1824.5	2076.3	2288.0	2394.1	2376.4	2206.3	1981.7
37.5°	1213.9	1291.0	1393.7	1540.3	1765.4	2032.1	2210.6	2226.3	2073.2	1812.0	1552.6
40°	1156.2	1225.6	1331.1	1484.2	1719.7	1988.5	2132.8	2069.5	1832.0	1541.4	1325.0
42.5°	1100.1	1158.7	1260.3	1425.4	1676.2	1929.2	2016.8	1879.0	1605.0	1330.2	1133.4
45°	1005.1	1060.3	1162.3	1331.8	1587.0	1815.7	1804.1	1564.5	1290.3	1069.1	905.8
47.5°	915.0	963.2	1059.0	1232.0	1482.3	1645.5	1537.3	1282.4	1049.8	872.3	755.8
50°	851.3	899.0	994.3	1165.1	1398.5	1517.6	1363.1	1117.4	904.4	757.4	664.9
52.5°	790.4	836.9	924.0	1090.5	1297.2	1368.4	1202.5	974.8	797.2	670.3	590.8
55°	705.0	740.4	818.7	977.9	1132.4	1148.7	980.6	790.1	643.8	555.3	500.9
57.5°	618.1	648.5	725.9	852.7	961.0	952.6	793.2	628.4	529.9	464.1	424.7
60°	561.4	591.4	659.4	768.3	850.0	821.4	675.1	542.4	458.0	409.7	378.4
62.5°	508.6	532.0	595.7	675.2	734.0	701.6	577.1	467.3	400.3	359.6	334.8
65°	432.1	451.2	502.2	543.7	576.4	545.1	441.7	365.4	317.1	288.5	271.5
67.5°	359.5	371.6	403.8	418.8	441.8	407.5	332.1	281.1	253.6	229.5	217.6
70°	313.7	322.6	339.6	351.8	358.0	322.6	266.8	229.3	206.2	189.2	181.7
72.5°	268.0	275.8	279.2	289.2	286.1	252.9	214.5	184.7	168.1	156.5	146.9
75°	204.8	208.2	204.8	200.8	191.9	168.8	142.2	127.3	115.0	109.6	106.2
77.5°	149.3	148.2	143.6	137.2	122.1	107.5	93.2	88.2	82.9	80.0	78.8
80°	115.0	112.3	108.2	98.0	85.1	74.9	71.5	68.1	66.0	62.6	61.9
82.5°	85.6	84.0	77.2	68.6	59.5	54.7	51.9	50.6	48.6	46.8	46.7
85°	45.6	43.6	36.1	31.3	29.9	28.6	27.9	27.9	25.2	24.5	24.5
87.5°	15.2	12.1	11.9	10.5	10.7	10.0	10.9	10.1	9.9	10.4	9.4
90°	2.3	3.4	5.1	6.3	7.4	9.1	10.8	12.5	14.3	13.7	14.3
92.5°	10.5	15.3	19.7	24.5	33.0	47.9	72.4	96.5	87.7	66.2	48.0
95°	21.1	27.4	37.1	51.9	74.1	122.6	207.6	301.2	338.2	274.3	205.3
97.5°	33.7	38.6	47.0	61.6	85.7	132.0	227.8	383.7	524.2	560.8	511.9
100°	42.8	46.8	54.8	68.4	90.7	130.6	215.0	365.0	540.1	652.5	672.5
102.5°	52.8	56.4	63.9	76.2	96.6	132.4	204.1	337.7	510.5	657.1	725.9
105°	67.9	71.3	78.1	89.0	106.7	137.5	196.2	304.0	458.6	622.3	741.5
107.5°	83.2	86.5	93.2	103.4	119.8	146.8	195.6	282.6	412.7	561.4	696.5
110°	94.1	97.0	103.2	112.9	128.9	154.6	197.9	274.3	386.7	523.0	653.6



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	104.2	107.0	113.3	123.0	138.5	162.3	202.5	269.8	369.4	489.7	611.2
115°	119.2	122.6	128.3	138.0	153.4	175.1	209.9	268.1	350.8	449.5	555.0
117.5°	134.0	136.9	142.1	153.0	167.2	188.7	219.7	269.1	339.8	425.2	514.2
120°	143.2	146.0	151.7	162.6	176.8	197.3	227.0	270.9	334.8	412.4	492.8
122.5°	151.8	154.7	160.8	171.2	186.4	206.5	233.9	274.1	331.6	401.9	475.9
125°	163.7	167.1	173.4	184.2	199.6	219.6	244.7	278.9	327.4	388.4	453.4
127.5°	173.7	178.0	184.3	196.3	211.7	231.0	253.6	284.4	325.3	376.6	433.8
130°	179.7	184.8	191.6	203.6	219.0	237.8	259.5	288.0	324.0	370.2	421.5
132.5°	184.7	190.3	198.5	210.5	225.4	243.8	265.0	290.8	323.5	364.2	410.1
135°	192.8	199.1	207.6	219.6	235.0	252.7	272.1	294.9	322.8	356.5	394.7
137.5°	200.4	206.6	215.7	227.6	241.8	258.8	277.3	297.6	321.6	349.8	380.7
140°	205.9	211.6	220.7	232.1	246.4	262.9	280.1	299.4	321.1	345.6	372.5
142.5°	210.9	217.1	225.3	236.7	250.1	266.1	282.8	300.8	320.2	342.0	364.7
145°	219.0	224.2	232.7	242.4	255.5	270.4	285.8	301.7	318.8	337.1	355.3
147.5°	227.2	232.3	239.7	249.0	260.2	273.8	287.6	301.7	316.7	332.3	347.7
150°	232.7	237.3	244.7	252.7	262.9	276.1	288.0	301.7	314.8	329.1	342.2
152.5°	238.2	242.8	249.3	256.3	266.1	277.4	289.0	300.4	312.6	325.5	337.2
155°	247.0	250.4	256.1	262.4	270.4	280.1	289.2	298.9	308.6	320.0	329.7
157.5°	254.5	257.2	262.3	267.6	273.8	281.5	289.8	296.9	305.0	313.8	321.7
160°	259.5	261.8	266.4	270.4	276.1	282.9	289.8	296.0	302.3	309.7	317.1
162.5°	263.6	265.5	269.1	272.6	277.4	283.4	289.3	294.2	299.6	305.6	311.7
165°	269.2	270.4	273.2	275.5	279.5	284.0	288.0	291.5	295.5	300.0	304.6
167.5°	273.8	274.3	276.5	278.1	280.6	283.9	287.1	288.7	291.3	294.7	298.4
170°	276.1	276.6	278.3	279.5	280.6	283.5	285.8	286.9	288.6	291.5	294.3
172.5°	278.3	278.5	279.7	280.4	281.1	283.5	285.3	285.5	286.3	288.3	290.7
175°	280.6	280.1	281.2	281.2	281.8	282.9	284.0	283.5	283.5	284.6	285.8
177.5°	281.8	281.3	281.8	281.8	281.8	282.2	283.1	282.2	281.8	282.2	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1676.8	1676.8	1679.0	1687.2	1688.3	1695.3	1693.2
5°	1842.9	1855.8	1860.6	1881.0	1893.2	1898.7	1887.8
7.5°	2046.0	2082.4	2099.7	2121.1	2140.0	2145.7	2130.9
10°	2194.0	2232.1	2264.1	2283.9	2302.2	2314.5	2330.1
12.5°	2337.2	2384.0	2414.4	2442.3	2461.2	2476.7	2479.3
15°	2492.8	2563.6	2617.3	2656.8	2676.5	2686.7	2682.7
17.5°	2649.7	2715.3	2753.6	2793.9	2821.2	2822.6	2823.4
20°	2738.5	2802.4	2846.7	2876.6	2907.2	2905.9	2912.7
22.5°	2797.8	2848.2	2882.1	2903.8	2914.3	2909.1	2910.5
25°	2825.6	2840.5	2834.4	2799.7	2790.9	2758.9	2764.3
27.5°	2682.4	2611.6	2538.4	2444.2	2369.9	2310.5	2313.5
30°	2488.0	2362.8	2219.9	2100.1	1992.6	1962.7	1898.7
32.5°	2216.4	2028.5	1861.1	1749.5	1657.2	1632.2	1576.4
35°	1755.8	1573.4	1401.2	1297.8	1256.9	1199.8	1199.1
37.5°	1364.7	1204.1	1113.1	1035.5	994.8	960.2	956.8
40°	1148.1	1022.8	954.1	898.3	858.2	832.3	826.2
42.5°	996.7	895.4	831.1	796.5	765.6	752.3	742.3
45°	813.9	745.9	700.9	669.6	655.4	645.1	639.7
47.5°	680.8	635.2	604.6	583.8	572.2	561.4	564.3
50°	608.4	571.0	548.5	528.8	519.9	512.4	513.1
52.5°	550.1	516.5	498.4	484.1	473.1	467.8	465.2
55°	466.8	445.7	427.4	417.2	411.0	403.6	401.5
57.5°	398.2	381.9	366.9	355.4	353.9	346.7	347.6
60°	352.5	338.9	326.7	320.5	315.8	309.6	311.7
62.5°	315.0	303.5	292.4	287.3	282.6	278.1	279.0
65°	257.9	247.0	240.2	237.5	235.5	233.4	231.4
67.5°	205.5	198.9	194.6	188.8	184.6	183.9	181.8
70°	172.9	164.0	156.5	149.0	147.0	146.3	147.0
72.5°	138.6	133.0	130.9	127.3	126.9	125.1	126.3
75°	104.1	102.1	100.7	98.0	98.0	98.0	98.0
77.5°	76.8	75.5	74.7	74.2	73.5	72.5	72.4
80°	59.9	59.2	57.8	57.8	57.2	57.8	57.2
82.5°	45.2	45.1	43.7	43.7	43.0	42.6	43.0
85°	23.1	22.5	23.8	22.5	23.1	21.8	23.1
87.5°	9.5	9.6	9.3	9.2	8.8	10.0	8.8
90°	14.8	15.4	16.5	16.0	16.5	17.1	16.5
92.5°	38.1	33.7	30.7	29.7	27.9	28.5	27.5
95°	139.2	108.9	88.4	77.6	72.4	68.4	66.2
97.5°	410.0	336.4	268.2	226.1	200.4	185.0	180.1
100°	626.3	559.5	478.5	420.9	379.3	357.1	357.6
102.5°	724.4	685.5	634.1	589.3	556.3	537.7	524.6
105°	798.5	809.4	794.5	768.3	746.6	728.4	725.5
107.5°	789.2	839.1	859.4	859.9	852.6	846.4	841.2
110°	758.6	830.5	870.4	886.4	890.9	889.8	888.6



TEST NUMBER: P332338

CATALOG NUMBER: S123RDIP-S1000D585U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	718.4	799.0	850.3	879.5	893.7	898.0	898.2
115°	654.2	738.1	800.2	843.0	868.1	879.5	882.4
117.5°	599.9	675.2	738.3	782.9	811.6	828.1	831.9
120°	569.8	638.2	695.9	740.9	772.9	786.5	790.0
122.5°	545.6	609.0	662.5	702.6	731.3	746.4	750.7
125°	515.6	570.4	616.0	652.5	677.6	691.9	695.9
127.5°	489.3	538.7	580.2	612.7	634.1	647.0	650.7
130°	472.8	519.0	557.8	588.1	608.6	620.6	625.1
132.5°	457.3	500.3	537.3	565.7	586.2	596.8	600.0
135°	435.2	472.3	504.8	532.7	549.8	560.1	564.1
137.5°	413.9	445.8	474.0	497.5	514.8	523.5	526.1
140°	401.5	428.9	453.4	475.1	491.1	500.2	499.6
142.5°	389.7	413.4	434.7	453.2	467.4	475.6	475.0
145°	374.2	392.4	409.0	423.2	435.2	439.8	440.9
147.5°	362.6	377.4	389.1	399.9	408.0	412.4	412.8
150°	355.3	367.3	378.2	386.7	393.0	396.4	396.4
152.5°	348.5	359.1	368.1	374.8	380.7	382.7	382.7
155°	338.8	347.4	354.2	359.3	363.9	365.0	365.6
157.5°	329.3	336.0	341.3	345.8	349.2	350.1	350.0
160°	323.4	329.1	333.1	337.1	340.5	340.5	339.9
162.5°	317.0	322.3	325.8	328.4	331.4	331.4	330.8
165°	308.0	312.0	314.8	317.1	319.4	318.8	318.8
167.5°	301.0	303.3	305.4	306.4	308.0	307.4	307.4
170°	296.0	298.3	299.4	300.0	301.2	300.6	300.6
172.5°	291.9	293.7	294.4	294.5	295.7	294.7	294.2
175°	286.3	287.5	287.5	287.5	288.0	287.5	286.9
177.5°	283.1	283.6	283.6	283.1	283.6	282.7	282.7
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8

(END OF REPORT)