

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331983-840

Luminaire Tested: **S123DIP-S775D1025U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331983-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6852.7 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	48	47	46	41	41	41	41	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26	26	26	26	
5	68	57	49	43	63	53	46	41	45	40	35	38	34	31	31	28	26	22	22	22	22	
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20	20	20	20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16	16	16	16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11746	11746	11746	11746
5°	14008	11797	10454	11797
10°	17533	11737	9441	11737
15°	21504	11642	8790	11642
20°	25616	11494	8369	11494
25°	27201	11315	8276	11315
30°	23313	11184	8319	11184
35°	16215	10997	8406	10997
40°	12213	10779	8379	10779
45°	10140	10455	8273	10455
50°	9083	9791	8199	9791
55°	8492	9077	8096	9077
60°	7967	8331	8013	8331
65°	7488	7595	7755	7595
70°	7021	6754	7386	6754
75°	6288	5914	6771	5914
80°	5511	4854	5833	4854
85°	4310	3532	3915	3532



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	1.6
10°-20°	344.7	5.0
20°-30°	578.5	8.4
30°-40°	655.0	9.6
40°-50°	587.4	8.6
50°-60°	474.0	6.9
60°-70°	330.3	4.8
70°-80°	173.6	2.5
80°-90°	46.3	0.7
90°-100°	83.6	1.2
100°-110°	250.2	3.7
110°-120°	425.6	6.2
120°-130°	559.8	8.2
130°-140°	629.2	9.2
140°-150°	618.5	9.0
150°-160°	520.7	7.6
160°-170°	346.6	5.1
170°-180°	121.4	1.8
0°-30°	1030.6	15.0
0°-40°	1685.7	24.6
0°-60°	2747.1	40.1
0°-90°	3297.3	48.1
90°-120°	759.4	11.1
90°-150°	2566.9	37.5
90°-180°	3555.0	51.9
0°-180°	6852.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1091	1091	1091	1091	1091	
5°	1296	1092	968	1092	1296	134
15°	1930	1045	789	1045	1930	557
25°	2290	953	697	953	2290	1004
35°	1234	837	640	837	1234	802
45°	666	687	544	687	666	527
55°	452	484	431	484	452	406
65°	294	298	304	298	294	293
75°	151	142	163	142	151	162
85°	35	29	32	29	35	42
90°	30	1	30	1	30	16
95°	79	60	79	60	79	81
105°	240	227	240	227	240	255
115°	429	428	429	428	429	425
125°	620	627	620	627	620	554
135°	812	814	812	814	812	625
145°	987	987	987	987	987	616
155°	1128	1130	1128	1130	1128	519
165°	1227	1231	1227	1231	1227	346
175°	1275	1280	1275	1280	1275	121
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1158.0	1157.2	1155.1	1156.8	1153.4	1148.7	1148.3	1144.1	1131.8	1130.9	1127.6
5°	1296.4	1292.1	1291.6	1291.0	1283.6	1273.6	1254.6	1252.9	1227.6	1214.9	1199.6
7.5°	1475.4	1477.6	1470.0	1463.2	1440.6	1425.6	1405.2	1379.1	1348.0	1316.4	1295.3
10°	1604.1	1621.4	1599.8	1585.0	1571.2	1545.3	1515.2	1477.6	1440.2	1396.2	1362.9
12.5°	1741.9	1750.5	1746.2	1732.2	1710.8	1671.4	1618.0	1576.6	1542.1	1468.9	1439.5
15°	1929.7	1962.0	1941.4	1893.7	1894.8	1857.2	1787.5	1710.8	1670.1	1606.1	1518.9
17.5°	2129.7	2133.7	2125.0	2085.4	2058.9	2007.3	1942.9	1869.5	1787.0	1709.5	1617.0
20°	2236.3	2233.1	2214.6	2194.0	2148.6	2108.4	2038.1	1956.1	1850.4	1774.2	1673.2
22.5°	2295.5	2290.3	2281.5	2264.2	2226.3	2183.2	2120.1	2030.5	1930.0	1825.0	1708.4
25°	2290.3	2297.1	2298.1	2293.4	2280.2	2254.3	2204.6	2133.2	2032.8	1897.9	1776.4
27.5°	2083.0	2092.7	2121.0	2146.1	2174.0	2202.6	2198.8	2163.3	2089.0	1972.7	1823.9
30°	1875.7	1854.6	1906.9	1973.1	2018.0	2097.3	2141.7	2144.3	2102.5	2002.7	1857.7
32.5°	1588.1	1611.4	1634.6	1715.9	1814.1	1903.2	1991.6	2062.8	2070.8	2004.4	1877.6
35°	1234.0	1263.0	1305.4	1347.6	1453.4	1544.3	1699.7	1835.0	1942.9	1957.2	1879.5
37.5°	994.3	1008.8	1035.5	1077.8	1147.0	1254.9	1375.1	1546.2	1702.4	1818.7	1823.7
40°	869.2	873.4	903.5	935.7	991.8	1080.7	1189.0	1340.2	1527.3	1689.7	1757.4
42.5°	775.3	784.6	797.4	828.3	872.9	939.8	1040.6	1165.5	1337.1	1523.9	1656.3
45°	666.1	676.7	684.7	705.3	737.0	781.9	852.2	966.4	1097.0	1290.0	1468.1
47.5°	594.0	594.9	600.8	616.3	637.9	671.7	721.3	794.8	914.6	1071.1	1254.1
50°	542.4	550.9	553.0	565.1	582.1	606.9	648.1	710.5	808.9	946.3	1114.5
52.5°	506.0	508.6	514.5	523.3	538.1	557.4	593.2	642.1	719.2	836.4	991.0
55°	452.5	452.5	458.4	465.2	473.7	491.1	514.9	550.9	609.6	700.5	828.5
57.5°	403.0	405.7	409.8	411.9	419.1	430.7	450.5	477.9	521.6	591.6	693.3
60°	370.1	374.9	374.4	378.5	384.9	393.8	410.8	433.0	472.1	528.2	613.8
62.5°	341.3	341.0	340.9	346.0	352.3	360.9	371.8	391.1	424.3	474.0	546.9
65°	294.0	292.9	296.6	299.7	301.8	308.2	316.7	333.6	355.8	392.8	449.4
67.5°	251.9	248.8	250.9	251.9	255.5	260.4	268.3	278.8	296.5	326.2	368.8
70°	223.1	220.5	219.9	221.0	224.2	227.8	233.7	243.7	260.1	283.9	315.1
72.5°	193.5	191.7	191.6	193.9	195.4	197.8	202.0	211.2	224.2	242.1	271.1
75°	151.2	151.2	151.2	151.7	153.3	155.4	158.6	163.4	173.4	186.1	205.6
77.5°	113.3	113.2	112.6	112.5	114.8	115.8	116.5	121.0	126.5	135.1	149.4
80°	88.9	86.1	87.3	88.9	89.9	90.4	92.0	93.0	97.9	102.6	112.6
82.5°	65.9	63.7	63.9	66.4	66.7	67.2	68.8	70.2	72.0	76.3	81.7
85°	34.9	34.9	35.4	35.4	36.0	35.4	37.0	37.6	37.6	40.2	43.3
87.5°	18.8	17.8	18.2	18.5	18.0	18.3	18.5	18.7	19.0	19.2	19.1
90°	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0	25.0	24.2	21.3
92.5°	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2	39.4	38.7	37.1
95°	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3	75.5	74.6	72.8
97.5°	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8	117.8	116.7	115.4
100°	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6	148.9	148.1	147.0
102.5°	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0	184.3	183.7	182.2
105°	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9	237.9	237.9	235.9
107.5°	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2	294.5	293.8	293.0
110°	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5	332.5	331.6	331.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7	370.6	369.5	369.5
115°	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4	429.9
117.5°	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6	488.7	488.7	489.3
120°	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8	528.0	528.3	529.4
122.5°	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3	567.9	568.6	569.2
125°	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2	627.1	628.0	628.4
127.5°	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4	685.6	686.9	687.4
130°	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0	723.9	724.8	725.5
132.5°	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5	761.6	762.7	763.2
135°	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8	817.7	818.5	818.8
137.5°	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7	872.6	873.5	873.0
140°	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7	941.9	942.1	941.7
145°	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5	991.7	991.9	991.3
147.5°	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5	1067.5	1067.5	1067.1
152.5°	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1	1093.7	1093.4	1093.1
155°	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9	1132.0	1131.0	1130.8
157.5°	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2	1165.3	1164.3	1164.2
160°	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7	1185.6	1184.5	1184.5
162.5°	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1	1205.0	1203.9	1203.7
165°	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5	1229.1	1227.8	1227.8
167.5°	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6	1247.4
170°	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1	1258.1
172.5°	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7	1268.3	1266.9	1266.9
175°	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9	1277.6	1276.2	1276.2
177.5°	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0	1281.9	1280.8	1280.8
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1125.0	1121.7	1118.2	1112.4	1107.3	1100.0	1097.9	1095.4	1087.8	1081.1	1076.0
5°	1193.8	1181.0	1162.6	1145.7	1132.0	1113.4	1102.9	1091.8	1075.9	1061.6	1050.0
7.5°	1265.7	1240.7	1211.9	1180.8	1151.9	1124.0	1101.5	1081.4	1059.1	1038.1	1021.8
10°	1322.7	1286.8	1246.7	1203.3	1166.3	1130.3	1100.1	1073.8	1045.2	1020.4	999.8
12.5°	1387.9	1334.6	1279.2	1226.6	1182.8	1132.9	1096.4	1062.8	1030.4	1000.5	977.3
15°	1465.0	1397.4	1331.7	1259.3	1192.8	1130.3	1087.0	1044.7	1007.1	976.4	946.8
17.5°	1535.2	1458.5	1372.1	1284.0	1203.7	1129.7	1069.0	1021.2	974.2	936.8	907.3
20°	1575.0	1487.7	1389.9	1298.5	1209.6	1127.1	1060.6	1003.4	952.7	913.0	879.7
22.5°	1609.2	1507.1	1405.9	1308.2	1209.2	1120.3	1044.9	986.1	931.1	892.3	856.9
25°	1644.8	1522.6	1421.1	1306.4	1195.9	1103.9	1019.3	952.7	897.7	852.2	815.8
27.5°	1675.2	1521.6	1401.1	1277.7	1175.0	1082.8	992.4	921.0	862.6	813.2	776.2
30°	1695.5	1523.7	1380.4	1258.3	1154.7	1059.4	971.7	899.8	838.5	788.3	753.4
32.5°	1708.2	1522.4	1361.4	1231.2	1122.5	1038.3	949.3	874.8	811.8	762.4	728.8
35°	1715.6	1513.1	1328.6	1175.3	1070.6	988.7	914.1	836.9	770.8	724.8	686.8
37.5°	1700.8	1493.5	1290.5	1121.4	1006.7	926.0	863.3	797.6	734.4	683.7	651.0
40°	1677.5	1480.9	1260.9	1083.3	962.7	885.0	831.6	767.1	704.7	656.6	625.9
42.5°	1633.1	1455.0	1228.3	1041.0	917.1	839.3	790.2	736.3	677.2	632.1	601.5
45°	1524.7	1398.9	1179.5	977.5	849.6	769.2	725.9	686.8	633.4	589.5	563.0
47.5°	1374.3	1314.4	1108.8	910.6	779.2	701.9	656.8	625.3	586.3	550.9	525.5
50°	1269.9	1245.1	1061.1	864.9	732.3	656.6	613.3	584.7	556.7	521.3	498.1
52.5°	1149.3	1164.7	1005.2	817.6	684.4	610.1	569.3	546.6	521.2	492.1	471.8
55°	979.7	1035.1	908.8	738.0	613.3	542.4	503.8	483.7	469.0	447.3	429.8
57.5°	820.7	891.4	804.6	656.1	543.4	482.3	445.2	423.3	413.8	402.5	388.8
60°	726.4	796.2	730.1	601.1	496.4	438.3	405.5	387.0	377.5	369.5	357.9
62.5°	642.3	712.9	657.3	545.3	450.3	396.4	367.9	349.8	342.3	338.2	328.3
65°	526.5	587.3	550.4	458.4	384.4	336.8	310.8	298.2	291.3	289.7	283.4
67.5°	428.6	474.8	447.9	380.2	321.9	280.8	258.8	248.0	242.8	242.3	237.5
70°	364.3	407.6	387.0	325.7	275.5	243.2	224.2	214.6	211.5	211.0	208.3
72.5°	314.4	344.6	328.2	277.0	238.2	208.9	195.0	185.0	181.5	182.2	180.4
75°	232.6	255.4	245.8	210.5	179.3	160.2	148.6	142.2	139.1	140.7	138.6
77.5°	167.3	181.8	173.2	148.7	129.5	115.6	107.1	103.2	100.4	100.3	99.3
80°	126.3	134.8	130.1	115.2	99.4	87.8	80.9	78.3	76.6	76.1	75.6
82.5°	90.0	97.1	91.6	81.4	70.6	63.6	59.8	56.2	55.1	55.4	54.8
85°	45.4	48.1	45.9	39.7	35.4	32.2	30.1	28.6	27.5	28.0	27.0
87.5°	19.3	19.2	17.3	15.1	13.8	12.1	11.6	10.4	10.0	10.4	10.4
90°	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4	26.0	27.5	29.0
95°	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5	61.0	62.6	64.2
97.5°	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6	106.8	108.0	109.2
100°	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1	138.5	139.8	141.1
102.5°	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4	174.2	175.0	175.8
105°	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8	227.2	227.7	228.1
107.5°	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9	289.2	289.4	289.7
110°	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6	328.1	328.5	328.9



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9	368.2	368.5	368.7
115°	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4	429.1	429.8	430.4
117.5°	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3	489.8	490.2	490.7
120°	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3	528.6	529.9	531.3
122.5°	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7	567.7	568.7	569.7
125°	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0	627.7	628.3	629.0
127.5°	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7	684.1	685.5	686.9
130°	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7	721.5	723.4	725.1
132.5°	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9	758.6	760.4	762.2
135°	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5	814.9	816.2	817.5
137.5°	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0	867.1	868.2	869.3
140°	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2	903.3	904.4	905.5
142.5°	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2	936.3	937.6	938.7
145°	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8	987.3	987.7	988.3
147.5°	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1	1032.9	1033.7	1034.5
150°	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5	1064.0	1064.4	1064.8
152.5°	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3	1089.9	1090.6	1091.2
155°	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7	1164.5	1164.2	1163.9
160°	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5	1186.0	1185.6	1185.2
162.5°	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9	1205.2	1204.6	1204.0
165°	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8	1230.1	1229.5	1228.8
167.5°	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8	1249.9	1249.0	1248.1
170°	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1	1261.2	1260.3	1259.4
172.5°	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9	1270.1	1269.2	1268.3
175°	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2	1279.3	1278.4	1277.6
177.5°	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0	1283.3	1282.6	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1073.0	1070.1	1065.8	1059.4	1054.4	1046.3	1046.3	1047.6	1047.6	1047.2	1046.3
5°	1040.5	1032.5	1023.0	1011.9	1000.3	988.7	986.5	982.3	979.2	977.0	974.3
7.5°	1006.1	992.0	978.2	962.6	948.5	936.8	928.6	921.8	917.5	912.8	909.5
10°	982.8	965.3	949.0	932.6	914.6	900.4	891.4	885.0	880.3	876.1	873.9
12.5°	955.3	935.3	917.3	901.7	882.0	867.4	858.8	855.9	850.2	841.3	836.7
15°	915.1	896.7	874.9	851.2	841.6	823.6	813.6	808.9	805.7	798.8	796.7
17.5°	880.8	856.6	832.2	814.5	796.8	782.2	776.6	770.7	766.5	760.8	759.2
20°	853.3	831.6	809.4	790.4	771.8	756.0	751.2	747.0	742.8	740.1	738.0
22.5°	825.4	803.8	785.3	767.5	747.8	737.4	732.3	727.6	724.6	722.9	720.7
25°	786.2	767.1	746.5	730.6	714.8	707.9	704.7	702.1	699.9	697.3	696.8
27.5°	751.0	730.3	713.6	698.8	687.4	681.7	678.6	677.3	677.8	678.7	679.3
30°	724.8	705.8	692.1	679.3	668.8	663.5	663.0	663.0	665.1	665.6	666.7
32.5°	700.7	685.1	671.4	659.0	651.1	647.4	649.4	649.4	651.2	652.5	654.4
35°	665.6	651.9	641.3	630.8	623.9	625.4	626.5	627.5	630.2	633.4	635.5
37.5°	632.1	620.2	609.2	600.9	597.7	600.6	603.1	605.3	608.4	610.9	613.0
40°	607.9	599.0	588.4	581.0	582.1	583.7	585.8	588.4	591.1	592.7	594.8
42.5°	585.5	576.1	568.2	562.0	563.5	565.5	566.7	568.2	571.2	574.0	575.3
45°	551.4	544.0	536.6	532.9	534.0	535.0	536.0	537.7	540.3	542.4	543.0
47.5°	513.0	507.9	502.9	499.3	501.0	500.6	501.9	505.3	506.1	507.5	510.4
50°	488.5	483.7	478.0	476.9	476.9	476.9	477.4	481.6	481.6	483.7	485.8
52.5°	461.4	458.4	454.6	452.7	451.9	451.9	454.1	456.3	457.1	460.1	462.2
55°	421.3	418.2	415.1	413.4	412.3	413.4	417.7	418.7	421.3	422.9	424.5
57.5°	379.6	377.2	374.7	373.8	373.5	375.0	377.3	380.4	381.1	386.0	388.4
60°	352.1	348.4	346.3	346.3	345.3	350.0	348.9	354.3	355.3	358.4	362.1
62.5°	323.8	318.8	317.9	317.9	319.4	320.8	322.2	324.6	327.4	331.3	334.3
65°	278.1	275.5	279.1	278.6	277.5	280.7	280.7	283.4	286.5	290.2	296.1
67.5°	234.8	233.5	233.8	233.8	235.4	237.2	238.6	241.0	244.8	248.7	252.5
70°	205.6	207.2	204.6	206.7	208.3	208.8	209.8	213.1	217.3	219.9	224.2
72.5°	177.3	177.2	177.5	178.3	180.0	180.9	182.0	185.6	190.3	192.5	195.8
75°	136.4	135.8	137.4	137.4	140.1	141.2	142.2	143.8	148.0	151.2	153.8
77.5°	99.6	100.3	99.9	101.7	101.0	101.2	104.4	106.0	106.4	112.7	114.1
80°	75.0	76.1	76.6	77.2	77.8	76.6	80.4	81.9	81.9	85.6	88.3
82.5°	53.9	54.5	55.9	56.5	56.6	57.7	58.0	59.1	60.4	62.0	65.4
85°	27.0	28.6	29.1	28.6	29.1	28.0	29.6	30.1	30.7	30.7	30.7
87.5°	10.5	11.4	11.5	12.5	12.7	13.7	13.9	13.2	13.4	14.8	13.3
90°	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0	26.9	27.8	28.5
92.5°	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2	40.9	41.6	41.8
95°	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3	77.3	78.2	78.7
97.5°	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8	119.9	120.9	121.3
100°	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6	150.2	150.9	151.5
102.5°	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0	185.7	186.3	186.6
105°	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9	237.9	237.9	238.1
107.5°	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2	295.9	296.6	296.8
110°	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5	334.4	335.3	335.5



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7	372.7	373.9	374.4
115°	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9	430.1	430.3	430.3
117.5°	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6	488.6	488.6	488.2
120°	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8	527.6	527.4	526.9
122.5°	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3	566.8	566.2	565.6
125°	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2	625.3	624.4	623.5
127.5°	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4	683.2	681.9	680.8
130°	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0	722.1	721.2	719.9
132.5°	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5	759.5	758.4	757.3
135°	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8	815.9	815.0	814.3
137.5°	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7	870.8	869.8	868.9
140°	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8	907.6	907.4	906.5
142.5°	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7	941.5	941.2	940.5
145°	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5	991.3	991.0	990.5
147.5°	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5	1067.5	1067.5	1066.8
152.5°	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1	1094.4	1094.8	1094.4
155°	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9	1133.8	1134.6	1134.3
157.5°	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2	1167.1	1168.1	1167.9
160°	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7	1187.8	1188.9	1189.0
162.5°	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1	1207.2	1208.3	1208.1
165°	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5	1231.8	1233.1	1233.0
167.5°	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1
170°	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4
172.5°	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7	1271.1	1272.4	1272.4
175°	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9	1280.2	1281.6	1281.4
177.5°	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0	1284.0	1285.2	1285.1
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1043.4	1043.0	1045.9	1043.8	1045.9	1043.0	1043.4	1046.3	1047.2	1047.6	1047.6
5°	971.2	972.8	967.5	967.5	967.5	972.8	971.2	974.3	977.0	979.2	982.3
7.5°	906.9	904.5	904.7	901.9	904.7	904.5	906.9	909.5	912.8	917.5	921.8
10°	867.6	864.4	863.3	863.8	863.3	864.4	867.6	873.9	876.1	880.3	885.0
12.5°	835.0	834.4	827.4	827.5	827.4	834.4	835.0	836.7	841.3	850.2	855.9
15°	796.7	786.7	785.6	788.8	785.6	786.7	796.7	796.7	798.8	805.7	808.9
17.5°	758.3	753.1	753.4	751.7	753.4	753.1	758.3	759.2	760.8	766.5	770.7
20°	738.0	734.9	734.4	730.6	734.4	734.9	738.0	738.0	740.1	742.8	747.0
22.5°	719.4	718.4	718.7	714.6	718.7	718.4	719.4	720.7	722.9	724.6	727.6
25°	696.3	698.9	696.8	696.8	696.8	698.9	696.3	696.8	697.3	699.9	702.1
27.5°	680.6	680.5	679.4	679.4	679.4	680.5	680.6	679.3	678.7	677.8	677.3
30°	668.8	668.2	669.3	669.3	669.3	668.2	668.8	666.7	665.6	665.1	663.0
32.5°	656.9	657.7	657.9	658.3	657.9	657.7	656.9	654.4	652.5	651.2	649.4
35°	638.6	639.1	640.8	639.7	640.8	639.1	638.6	635.5	633.4	630.2	627.5
37.5°	613.9	616.3	615.8	616.6	615.8	616.3	613.9	613.0	610.9	608.4	605.3
40°	595.3	596.9	596.3	596.3	596.3	596.9	595.3	594.8	592.7	591.1	588.4
42.5°	576.2	577.4	576.0	575.2	576.0	577.4	576.2	575.3	574.0	571.2	568.2
45°	545.0	544.0	545.6	543.5	545.6	544.0	545.0	543.0	542.4	540.3	537.7
47.5°	510.2	511.2	511.7	513.2	511.7	511.2	510.2	510.4	507.5	506.1	505.3
50°	487.0	490.1	490.1	489.6	490.1	490.1	487.0	485.8	483.7	481.6	481.6
52.5°	464.0	465.5	467.7	467.6	467.7	465.5	464.0	462.2	460.1	457.1	456.3
55°	428.8	429.8	430.9	431.4	430.9	429.8	428.8	424.5	422.9	421.3	418.7
57.5°	392.1	391.7	394.3	395.1	394.3	391.7	392.1	388.4	386.0	381.1	380.4
60°	366.4	366.4	370.6	372.2	370.6	366.4	366.4	362.1	358.4	355.3	354.3
62.5°	338.9	340.6	344.8	342.5	344.8	340.6	338.9	334.3	331.3	327.4	324.6
65°	298.7	303.0	302.5	304.5	302.5	303.0	298.7	296.1	290.2	286.5	283.4
67.5°	256.7	259.3	263.2	263.5	263.2	259.3	256.7	252.5	248.7	244.8	241.0
70°	228.4	231.1	233.2	234.7	233.2	231.1	228.4	224.2	219.9	217.3	213.1
72.5°	200.9	202.3	207.3	205.1	207.3	202.3	200.9	195.8	192.5	190.3	185.6
75°	157.5	161.3	164.4	162.8	164.4	161.3	157.5	153.8	151.2	148.0	143.8
77.5°	116.5	120.2	121.7	120.4	121.7	120.2	116.5	114.1	112.7	106.4	106.0
80°	92.0	91.5	94.6	94.1	94.6	91.5	92.0	88.3	85.6	81.9	81.9
82.5°	67.5	67.0	68.4	68.8	68.4	67.0	67.5	65.4	62.0	60.4	59.1
85°	32.8	34.3	32.2	31.7	32.2	34.3	32.8	30.7	30.7	30.7	30.1
87.5°	13.4	13.5	13.1	12.8	13.1	13.5	13.4	13.3	14.8	13.4	13.2
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0
92.5°	41.5	41.3	41.0	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2
95°	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3
97.5°	121.3	121.2	121.1	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8
100°	151.9	152.3	152.8	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6
102.5°	186.5	186.4	186.4	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0
105°	238.5	239.0	239.4	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9
107.5°	296.6	296.3	296.0	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2
110°	335.0	334.6	334.2	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	374.3	374.2	374.1	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7
115°	430.1	429.9	429.7	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9
117.5°	487.6	487.0	486.4	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6
120°	526.5	526.1	525.6	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8
122.5°	565.0	564.3	563.7	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3
125°	622.7	621.8	620.9	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2
127.5°	679.7	678.6	677.6	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4
130°	718.4	716.8	715.3	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0
132.5°	756.1	754.9	753.7	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5
135°	813.9	813.3	812.9	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8
137.5°	868.1	867.2	866.4	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7
140°	904.9	903.3	901.8	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8
142.5°	939.3	938.1	936.9	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7
145°	989.6	988.7	987.7	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5
147.5°	1036.5	1035.1	1033.8	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5
150°	1065.5	1064.2	1062.8	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5
152.5°	1093.2	1092.1	1090.9	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1
155°	1132.8	1131.1	1129.5	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9
157.5°	1166.7	1165.4	1164.2	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2
160°	1188.2	1187.3	1186.4	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7
162.5°	1206.7	1205.3	1203.9	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1
165°	1231.5	1229.9	1228.4	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5
167.5°	1251.7	1250.3	1249.0	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3
170°	1262.7	1261.2	1259.6	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2
172.5°	1270.8	1269.3	1267.7	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7
175°	1279.9	1278.3	1276.8	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9
177.5°	1283.8	1282.5	1281.3	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1046.3	1046.3	1054.4	1059.4	1065.8	1070.1	1073.0	1076.0	1081.1	1087.8	1095.4
5°	986.5	988.7	1000.3	1011.9	1023.0	1032.5	1040.5	1050.0	1061.6	1075.9	1091.8
7.5°	928.6	936.8	948.5	962.6	978.2	992.0	1006.1	1021.8	1038.1	1059.1	1081.4
10°	891.4	900.4	914.6	932.6	949.0	965.3	982.8	999.8	1020.4	1045.2	1073.8
12.5°	858.8	867.4	882.0	901.7	917.3	935.3	955.3	977.3	1000.5	1030.4	1062.8
15°	813.6	823.6	841.6	851.2	874.9	896.7	915.1	946.8	976.4	1007.1	1044.7
17.5°	776.6	782.2	796.8	814.5	832.2	856.6	880.8	907.3	936.8	974.2	1021.2
20°	751.2	756.0	771.8	790.4	809.4	831.6	853.3	879.7	913.0	952.7	1003.4
22.5°	732.3	737.4	747.8	767.5	785.3	803.8	825.4	856.9	892.3	931.1	986.1
25°	704.7	707.9	714.8	730.6	746.5	767.1	786.2	815.8	852.2	897.7	952.7
27.5°	678.6	681.7	687.4	698.8	713.6	730.3	751.0	776.2	813.2	862.6	921.0
30°	663.0	663.5	668.8	679.3	692.1	705.8	724.8	753.4	788.3	838.5	899.8
32.5°	649.4	647.4	651.1	659.0	671.4	685.1	700.7	728.8	762.4	811.8	874.8
35°	626.5	625.4	623.9	630.8	641.3	651.9	665.6	686.8	724.8	770.8	836.9
37.5°	603.1	600.6	597.7	600.9	609.2	620.2	632.1	651.0	683.7	734.4	797.6
40°	585.8	583.7	582.1	581.0	588.4	599.0	607.9	625.9	656.6	704.7	767.1
42.5°	566.7	565.5	563.5	562.0	568.2	576.1	585.5	601.5	632.1	677.2	736.3
45°	536.0	535.0	534.0	532.9	536.6	544.0	551.4	563.0	589.5	633.4	686.8
47.5°	501.9	500.6	501.0	499.3	502.9	507.9	513.0	525.5	550.9	586.3	625.3
50°	477.4	476.9	476.9	476.9	478.0	483.7	488.5	498.1	521.3	556.7	584.7
52.5°	454.1	451.9	451.9	452.7	454.6	458.4	461.4	471.8	492.1	521.2	546.6
55°	417.7	413.4	412.3	413.4	415.1	418.2	421.3	429.8	447.3	469.0	483.7
57.5°	377.3	375.0	373.5	373.8	374.7	377.2	379.6	388.8	402.5	413.8	423.3
60°	348.9	350.0	345.3	346.3	346.3	348.4	352.1	357.9	369.5	377.5	387.0
62.5°	322.2	320.8	319.4	317.9	317.9	318.8	323.8	328.3	338.2	342.3	349.8
65°	280.7	280.7	277.5	278.6	279.1	275.5	278.1	283.4	289.7	291.3	298.2
67.5°	238.6	237.2	235.4	233.8	233.8	233.5	234.8	237.5	242.3	242.8	248.0
70°	209.8	208.8	208.3	206.7	204.6	207.2	205.6	208.3	211.0	211.5	214.6
72.5°	182.0	180.9	180.0	178.3	177.5	177.2	177.3	180.4	182.2	181.5	185.0
75°	142.2	141.2	140.1	137.4	137.4	135.8	136.4	138.6	140.7	139.1	142.2
77.5°	104.4	101.2	101.0	101.7	99.9	100.3	99.6	99.3	100.3	100.4	103.2
80°	80.4	76.6	77.8	77.2	76.6	76.1	75.0	75.6	76.1	76.6	78.3
82.5°	58.0	57.7	56.6	56.5	55.9	54.5	53.9	54.8	55.4	55.1	56.2
85°	29.6	28.0	29.1	28.6	29.1	28.6	27.0	27.0	28.0	27.5	28.6
87.5°	13.9	13.7	12.7	12.5	11.5	11.4	10.5	10.4	10.4	10.0	10.4
90°	25.0	24.2	21.3	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0
92.5°	39.4	38.7	37.1	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4
95°	75.5	74.6	72.8	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5
97.5°	117.8	116.7	115.4	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6
100°	148.9	148.1	147.0	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1
102.5°	184.3	183.7	182.2	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4
105°	237.9	237.9	235.9	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8
107.5°	294.5	293.8	293.0	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9
110°	332.5	331.6	331.2	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	370.6	369.5	369.5	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9
115°	429.7	429.4	429.9	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4
117.5°	488.7	488.7	489.3	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3
120°	528.0	528.3	529.4	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3
122.5°	567.9	568.6	569.2	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7
125°	627.1	628.0	628.4	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0
127.5°	685.6	686.9	687.4	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7
130°	723.9	724.8	725.5	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7
132.5°	761.6	762.7	763.2	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9
135°	817.7	818.5	818.8	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5
137.5°	872.6	873.5	873.0	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0
140°	908.1	908.3	908.1	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2
142.5°	941.9	942.1	941.7	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2
145°	991.7	991.9	991.3	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8
147.5°	1038.5	1038.5	1037.8	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1
150°	1067.5	1067.5	1067.1	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5
152.5°	1093.7	1093.4	1093.1	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3
155°	1132.0	1131.0	1130.8	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1165.3	1164.3	1164.2	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7
160°	1185.6	1184.5	1184.5	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5
162.5°	1205.0	1203.9	1203.7	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9
165°	1229.1	1227.8	1227.8	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8
167.5°	1249.0	1247.6	1247.4	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8
170°	1259.6	1258.1	1258.1	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1
172.5°	1268.3	1266.9	1266.9	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9
175°	1277.6	1276.2	1276.2	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2
177.5°	1281.9	1280.8	1280.8	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1097.9	1100.0	1107.3	1112.4	1118.2	1121.7	1125.0	1127.6	1130.9	1131.8	1144.1
5°	1102.9	1113.4	1132.0	1145.7	1162.6	1181.0	1193.8	1199.6	1214.9	1227.6	1252.9
7.5°	1101.5	1124.0	1151.9	1180.8	1211.9	1240.7	1265.7	1295.3	1316.4	1348.0	1379.1
10°	1100.1	1130.3	1166.3	1203.3	1246.7	1286.8	1322.7	1362.9	1396.2	1440.2	1477.6
12.5°	1096.4	1132.9	1182.8	1226.6	1279.2	1334.6	1387.9	1439.5	1468.9	1542.1	1576.6
15°	1087.0	1130.3	1192.8	1259.3	1331.7	1397.4	1465.0	1518.9	1606.1	1670.1	1710.8
17.5°	1069.0	1129.7	1203.7	1284.0	1372.1	1458.5	1535.2	1617.0	1709.5	1787.0	1869.5
20°	1060.6	1127.1	1209.6	1298.5	1389.9	1487.7	1575.0	1673.2	1774.2	1850.4	1956.1
22.5°	1044.9	1120.3	1209.2	1308.2	1405.9	1507.1	1609.2	1708.4	1825.0	1930.0	2030.5
25°	1019.3	1103.9	1195.9	1306.4	1421.1	1522.6	1644.8	1776.4	1897.9	2032.8	2133.2
27.5°	992.4	1082.8	1175.0	1277.7	1401.1	1521.6	1675.2	1823.9	1972.7	2089.0	2163.3
30°	971.7	1059.4	1154.7	1258.3	1380.4	1523.7	1695.5	1857.7	2002.7	2102.5	2144.3
32.5°	949.3	1038.3	1122.5	1231.2	1361.4	1522.4	1708.2	1877.6	2004.4	2070.8	2062.8
35°	914.1	988.7	1070.6	1175.3	1328.6	1513.1	1715.6	1879.5	1957.2	1942.9	1835.0
37.5°	863.3	926.0	1006.7	1121.4	1290.5	1493.5	1700.8	1823.7	1818.7	1702.4	1546.2
40°	831.6	885.0	962.7	1083.3	1260.9	1480.9	1677.5	1757.4	1689.7	1527.3	1340.2
42.5°	790.2	839.3	917.1	1041.0	1228.3	1455.0	1633.1	1656.3	1523.9	1337.1	1165.5
45°	725.9	769.2	849.6	977.5	1179.5	1398.9	1524.7	1468.1	1290.0	1097.0	966.4
47.5°	656.8	701.9	779.2	910.6	1108.8	1314.4	1374.3	1254.1	1071.1	914.6	794.8
50°	613.3	656.6	732.3	864.9	1061.1	1245.1	1269.9	1114.5	946.3	808.9	710.5
52.5°	569.3	610.1	684.4	817.6	1005.2	1164.7	1149.3	991.0	836.4	719.2	642.1
55°	503.8	542.4	613.3	738.0	908.8	1035.1	979.7	828.5	700.5	609.6	550.9
57.5°	445.2	482.3	543.4	656.1	804.6	891.4	820.7	693.3	591.6	521.6	477.9
60°	405.5	438.3	496.4	601.1	730.1	796.2	726.4	613.8	528.2	472.1	433.0
62.5°	367.9	396.4	450.3	545.3	657.3	712.9	642.3	546.9	474.0	424.3	391.1
65°	310.8	336.8	384.4	458.4	550.4	587.3	526.5	449.4	392.8	355.8	333.6
67.5°	258.8	280.8	321.9	380.2	447.9	474.8	428.6	368.8	326.2	296.5	278.8
70°	224.2	243.2	275.5	325.7	387.0	407.6	364.3	315.1	283.9	260.1	243.7
72.5°	195.0	208.9	238.2	277.0	328.2	344.6	314.4	271.1	242.1	224.2	211.2
75°	148.6	160.2	179.3	210.5	245.8	255.4	232.6	205.6	186.1	173.4	163.4
77.5°	107.1	115.6	129.5	148.7	173.2	181.8	167.3	149.4	135.1	126.5	121.0
80°	80.9	87.8	99.4	115.2	130.1	134.8	126.3	112.6	102.6	97.9	93.0
82.5°	59.8	63.6	70.6	81.4	91.6	97.1	90.0	81.7	76.3	72.0	70.2
85°	30.1	32.2	35.4	39.7	45.9	48.1	45.4	43.3	40.2	37.6	37.6
87.5°	11.6	12.1	13.8	15.1	17.3	19.2	19.3	19.1	19.2	19.0	18.7
90°	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0
92.5°	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2
95°	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3
97.5°	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8
100°	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6
102.5°	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0
105°	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9
107.5°	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2
110°	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7
115°	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9
117.5°	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6
120°	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8
122.5°	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3
125°	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2
127.5°	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4
130°	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0
132.5°	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5
135°	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8
137.5°	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7
140°	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8
142.5°	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7
145°	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5
147.5°	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5
150°	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5
152.5°	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1
155°	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9
157.5°	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2
160°	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7
162.5°	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1
165°	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5
167.5°	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3
170°	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2
172.5°	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7
175°	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9
177.5°	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2	1091.2
2.5°	1148.3	1148.7	1153.4	1156.8	1155.1	1157.2	1158.0
5°	1254.6	1273.6	1283.6	1291.0	1291.6	1292.1	1296.4
7.5°	1405.2	1425.6	1440.6	1463.2	1470.0	1477.6	1475.4
10°	1515.2	1545.3	1571.2	1585.0	1599.8	1621.4	1604.1
12.5°	1618.0	1671.4	1710.8	1732.2	1746.2	1750.5	1741.9
15°	1787.5	1857.2	1894.8	1893.7	1941.4	1962.0	1929.7
17.5°	1942.9	2007.3	2058.9	2085.4	2125.0	2133.7	2129.7
20°	2038.1	2108.4	2148.6	2194.0	2214.6	2233.1	2236.3
22.5°	2120.1	2183.2	2226.3	2264.2	2281.5	2290.3	2295.5
25°	2204.6	2254.3	2280.2	2293.4	2298.1	2297.1	2290.3
27.5°	2198.8	2202.6	2174.0	2146.1	2121.0	2092.7	2083.0
30°	2141.7	2097.3	2018.0	1973.1	1906.9	1854.6	1875.7
32.5°	1991.6	1903.2	1814.1	1715.9	1634.6	1611.4	1588.1
35°	1699.7	1544.3	1453.4	1347.6	1305.4	1263.0	1234.0
37.5°	1375.1	1254.9	1147.0	1077.8	1035.5	1008.8	994.3
40°	1189.0	1080.7	991.8	935.7	903.5	873.4	869.2
42.5°	1040.6	939.8	872.9	828.3	797.4	784.6	775.3
45°	852.2	781.9	737.0	705.3	684.7	676.7	666.1
47.5°	721.3	671.7	637.9	616.3	600.8	594.9	594.0
50°	648.1	606.9	582.1	565.1	553.0	550.9	542.4
52.5°	593.2	557.4	538.1	523.3	514.5	508.6	506.0
55°	514.9	491.1	473.7	465.2	458.4	452.5	452.5
57.5°	450.5	430.7	419.1	411.9	409.8	405.7	403.0
60°	410.8	393.8	384.9	378.5	374.4	374.9	370.1
62.5°	371.8	360.9	352.3	346.0	340.9	341.0	341.3
65°	316.7	308.2	301.8	299.7	296.6	292.9	294.0
67.5°	268.3	260.4	255.5	251.9	250.9	248.8	251.9
70°	233.7	227.8	224.2	221.0	219.9	220.5	223.1
72.5°	202.0	197.8	195.4	193.9	191.6	191.7	193.5
75°	158.6	155.4	153.3	151.7	151.2	151.2	151.2
77.5°	116.5	115.8	114.8	112.5	112.6	113.2	113.3
80°	92.0	90.4	89.9	88.9	87.3	86.1	88.9
82.5°	68.8	67.2	66.7	66.4	63.9	63.7	65.9
85°	37.0	35.4	36.0	35.4	35.4	34.9	34.9
87.5°	18.5	18.3	18.0	18.5	18.2	17.8	18.8
90°	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	334.4	335.3	335.5	335.0	334.6	334.2	333.7



TEST NUMBER: P331983-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)