

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331990-840

Luminaire Tested: **S123DIP-S775D1025U840-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331990-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D1025U840-4F0-1E-UDD-F4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6950.3 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53	46				46
1	97	93	89	85	89	85	82	79	71	69	66	58	57	55	46	45	44	39				39
2	88	81	75	69	81	74	69	65	62	58	55	51	48	46	41	39	37	32				32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32	27				27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23				23
5	67	56	48	42	62	52	44	39	44	38	34	36	32	29	29	26	24	20				20
6	62	50	42	36	57	46	39	34	39	34	29	33	28	25	26	23	21	18				18
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	19	16				16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14				14
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13				13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	1.7
10°-20°	327.1	4.7
20°-30°	483.2	7.0
30°-40°	564.4	8.1
40°-50°	567.4	8.2
50°-60°	498.4	7.2
60°-70°	371.3	5.3
70°-80°	211.6	3.0
80°-90°	64.6	0.9
90°-100°	277.1	4.0
100°-110°	784.7	11.3
110°-120°	771.9	11.1
120°-130°	615.7	8.9
130°-140°	485.5	7.0
140°-150°	362.3	5.2
150°-160°	252.5	3.6
160°-170°	148.4	2.1
170°-180°	48.3	0.7
0°-30°	926.1	13.3
0°-40°	1490.5	21.4
0°-60°	2556.3	36.8
0°-90°	3203.8	46.1
90°-120°	1833.8	26.4
90°-150°	3297.3	47.4
90°-180°	3746.0	53.9
0°-180°	6950.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	2	12	25	28	29	5
95°	34	111	598	174	117	37
105°	117	173	810	1417	1282	124
115°	207	258	620	1359	1559	205
125°	287	339	579	1048	1230	255
135°	337	402	571	863	997	260
145°	384	440	564	708	779	241
155°	436	471	545	620	646	201
165°	477	490	522	554	564	134
175°	497	498	501	508	507	47
180°	498	498	498	498	498	



TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.4	22.2	22.1	22.1	21.9	22.0	22.4	22.8	23.2	23.6	23.2
90°	2.0	4.0	6.1	9.1	11.1	13.1	16.2	19.2	22.2	25.2	24.2
92.5°	12.5	18.6	27.1	34.8	43.3	58.3	84.6	128.1	170.6	155.0	116.9
95°	34.2	37.3	48.4	65.5	91.7	131.1	216.7	366.9	532.2	597.7	484.8
97.5°	58.5	59.5	68.2	83.0	108.9	151.4	233.3	402.6	678.2	926.3	991.1
100°	74.6	75.6	82.7	96.7	121.0	160.3	230.9	380.0	645.1	954.6	1153.2
102.5°	91.5	93.3	99.6	112.9	134.7	170.8	234.1	360.6	596.7	902.2	1161.2
105°	116.9	120.0	126.0	138.1	157.2	188.5	243.0	346.8	537.2	810.4	1099.7
107.5°	143.9	146.9	152.8	164.7	182.7	211.7	259.4	345.8	499.4	729.4	992.1
110°	163.3	166.3	171.4	182.5	199.5	227.8	273.2	349.8	484.8	683.5	924.3



TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.1	184.1	189.1	200.2	217.3	244.8	286.9	357.9	476.8	652.8	865.5
115°	206.6	210.7	216.7	226.8	244.0	271.1	309.4	370.9	473.7	620.0	794.4
117.5°	232.3	236.9	242.0	251.2	270.3	295.6	333.5	388.3	475.5	600.6	751.3
120°	249.9	253.0	258.0	268.1	287.3	312.5	348.8	401.2	478.8	591.7	728.8
122.5°	265.3	268.3	273.4	284.3	302.7	329.4	364.9	413.3	484.4	586.0	710.2
125°	287.3	289.3	295.4	306.4	325.6	352.8	388.1	432.4	492.9	578.7	686.5
127.5°	304.1	307.0	314.5	325.8	347.0	374.2	408.3	448.2	502.6	575.0	665.5
130°	314.5	317.5	326.6	338.7	359.8	387.1	420.3	458.7	509.1	572.6	654.2
132.5°	322.6	326.4	336.3	350.8	371.9	398.4	430.8	468.4	513.9	571.8	643.7
135°	336.7	340.7	351.8	366.9	388.1	415.3	446.6	480.8	521.2	570.6	630.1
137.5°	350.0	354.3	365.1	381.2	402.2	427.4	457.5	490.1	525.9	568.4	618.1
140°	358.9	363.9	374.0	390.1	410.3	435.5	464.7	494.9	529.2	567.5	610.9
142.5°	368.5	372.7	383.6	398.2	418.3	441.9	470.4	499.8	531.6	565.9	604.4
145°	384.1	387.1	396.2	411.3	428.4	451.6	477.8	505.0	533.2	563.5	595.7
147.5°	399.8	401.6	410.5	423.5	440.1	459.9	483.8	508.3	533.2	559.7	587.2
150°	410.3	411.3	419.3	432.4	446.6	464.7	487.9	509.1	533.2	556.4	581.6
152.5°	420.7	420.9	429.0	440.5	453.0	470.4	490.3	510.7	530.8	552.4	575.2
155°	436.5	436.5	442.5	452.6	463.7	477.8	494.9	511.1	528.2	545.3	565.5
157.5°	449.0	449.8	454.6	463.5	472.9	483.8	497.6	512.1	524.8	539.1	554.6
160°	458.7	458.7	462.7	470.7	477.8	487.9	500.0	512.1	523.2	534.2	547.3
162.5°	466.0	466.0	469.2	475.5	481.8	490.3	500.8	511.3	520.0	529.4	540.1
165°	476.8	475.7	477.8	482.8	486.9	493.9	502.0	509.1	515.1	522.2	530.2
167.5°	485.0	483.8	484.8	488.7	491.5	495.9	501.8	507.5	510.3	514.9	520.8
170°	489.9	487.9	488.9	491.9	493.9	495.9	501.0	505.0	507.1	510.1	515.1
172.5°	493.1	491.9	492.1	494.3	495.5	496.8	501.0	504.2	504.6	506.0	509.5
175°	497.0	495.9	494.9	497.0	497.0	498.0	500.0	502.0	501.0	501.0	503.0
177.5°	498.8	498.0	497.2	498.0	498.0	498.0	498.8	500.4	498.8	498.0	498.8
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0



TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	23.2	23.3	23.3	23.6	23.4	23.6	23.8	23.6
90°	25.2	26.3	27.3	29.2	28.2	29.2	30.2	29.2
92.5°	84.8	67.4	59.5	54.2	52.4	49.4	50.4	48.6
95°	362.8	246.0	192.6	156.2	137.1	128.1	121.0	116.9
97.5°	904.6	724.6	594.5	473.9	399.6	354.3	327.0	318.3
100°	1188.5	1106.8	988.9	845.8	744.0	670.3	631.1	632.1
102.5°	1282.8	1280.2	1211.4	1120.7	1041.5	983.2	950.4	927.2
105°	1310.4	1411.3	1430.4	1404.2	1357.8	1319.5	1287.3	1282.2
107.5°	1231.0	1394.7	1483.0	1518.9	1519.7	1506.8	1495.9	1486.6
110°	1155.2	1340.7	1467.6	1538.2	1566.5	1574.6	1572.6	1570.5



TEST NUMBER: P331990-840

CATALOG NUMBER: S123DIP-S775D1025U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1080.2	1269.7	1412.0	1502.8	1554.4	1579.3	1587.0	1587.4
115°	980.8	1156.2	1304.3	1414.2	1489.9	1534.2	1554.4	1559.4
117.5°	908.9	1060.3	1193.3	1304.7	1383.6	1434.4	1463.5	1470.3
120°	870.9	1007.0	1128.0	1229.8	1309.4	1365.8	1390.1	1396.1
122.5°	841.1	964.3	1076.4	1170.9	1241.7	1292.5	1319.1	1326.8
125°	801.4	911.3	1008.0	1088.6	1153.2	1197.5	1222.7	1229.8
127.5°	766.7	864.6	952.0	1025.3	1082.8	1120.7	1143.5	1149.9
130°	745.0	835.7	917.3	985.8	1039.3	1075.6	1096.7	1104.8
132.5°	724.8	808.2	884.2	949.6	999.8	1036.0	1054.8	1060.5
135°	697.5	769.1	834.7	892.1	941.5	971.7	989.9	996.9
137.5°	672.8	731.4	787.9	837.7	879.2	909.9	925.1	929.8
140°	658.2	709.6	758.0	801.4	839.7	867.9	884.0	883.0
142.5°	644.5	688.7	730.6	768.3	801.0	826.0	840.5	839.5
145°	628.0	661.3	693.5	722.8	747.9	769.1	777.2	779.2
147.5°	614.5	640.9	666.9	687.7	706.8	721.1	728.8	729.6
150°	604.8	628.0	649.1	668.3	683.5	694.5	700.5	700.5
152.5°	595.9	615.9	634.7	650.6	662.5	672.8	676.4	676.4
155°	582.6	598.7	613.9	626.0	635.1	643.1	645.1	646.1
157.5°	568.6	582.0	593.7	603.2	611.1	617.1	618.7	618.5
160°	560.5	571.6	581.6	588.7	595.7	601.8	601.8	600.8
162.5°	550.8	560.3	569.6	575.8	580.5	585.6	585.6	584.6
165°	538.3	544.3	551.4	556.4	560.5	564.5	563.5	563.5
167.5°	527.4	532.0	536.0	539.7	541.5	544.3	543.3	543.3
170°	520.2	523.2	527.1	529.2	530.2	532.2	531.2	531.2
172.5°	513.7	515.9	519.2	520.4	520.6	522.6	520.8	520.0
175°	505.0	506.0	508.1	508.1	508.1	509.1	508.1	507.1
177.5°	499.6	500.4	501.2	501.2	500.4	501.2	499.6	499.6
180°	498.0	498.0	498.0	498.0	498.0	498.0	498.0	498.0

(END OF REPORT)