

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332342

Luminaire Tested: **S123RDIP-S1000D805U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332342
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D805U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7170.1 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	84	75	67	62	78	70	63	58	60	56	52	52	48	46	44	42	39	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	34	31
5	71	59	52	46	66	56	49	44	49	43	39	42	38	35	36	33	30	27
6	65	54	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27	24
7	61	49	41	35	56	46	39	34	40	35	31	35	31	27	30	27	24	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	24	22	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17111	17111	17111	17111
5°	20398	17184	15132	17184
10°	25468	17086	13671	17086
15°	29895	16912	12467	16912
20°	33364	16651	11443	16651
25°	32831	16376	10815	16376
30°	23599	16122	10167	16122
35°	15757	15792	9747	15792
40°	11609	15396	9313	15396
45°	9738	14700	8888	14700
50°	8592	13788	8296	13788
55°	7535	12746	7484	12746
60°	6710	11750	6857	11750
65°	5894	10677	6378	10677
70°	4626	9725	5825	9725
75°	4076	8492	5319	8492
80°	3546	7215	5232	7215
85°	2853	5805	5545	5805



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.3	2.2
10°-20°	488.4	6.8
20°-30°	767.3	10.7
30°-40°	800.5	11.2
40°-50°	685.1	9.6
50°-60°	522.2	7.3
60°-70°	334.7	4.7
70°-80°	161.0	2.2
80°-90°	45.6	0.6
90°-100°	38.3	0.5
100°-110°	182.3	2.5
110°-120°	438.0	6.1
120°-130°	557.7	7.8
130°-140°	595.9	8.3
140°-150°	557.2	7.8
150°-160°	449.5	6.3
160°-170°	290.1	4.0
170°-180°	100.0	1.4
0°-30°	1412.0	19.7
0°-40°	2212.6	30.9
0°-60°	3419.8	47.7
0°-90°	3961.1	55.2
90°-120°	658.6	9.2
90°-150°	2369.4	33.0
90°-180°	3209.0	44.8
0°-180°	7170.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1888	1590	1400	1590	1888	195
15°	2683	1518	1119	1518	2683	761
25°	2764	1379	911	1379	2764	1188
35°	1199	1202	742	1202	1199	786
45°	640	966	584	966	640	503
55°	402	679	399	679	402	363
65°	231	419	250	419	231	228
75°	98	204	128	204	98	105
85°	23	47	45	47	23	27
90°	24	1	24	1	24	11
95°	30	48	30	48	30	25
105°	34	233	34	233	34	79
115°	460	437	460	437	460	425
125°	629	616	629	616	629	561
135°	775	767	775	767	775	597
145°	894	885	894	885	894	558
155°	973	975	973	975	973	449
165°	1026	1028	1026	1028	1026	290
175°	1048	1052	1048	1052	1048	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1693.2	1695.3	1688.3	1687.2	1679.0	1676.8	1676.8	1665.4	1658.3	1649.1	1643.6
5°	1887.8	1898.7	1893.2	1881.0	1860.6	1855.8	1842.9	1822.5	1799.3	1770.7	1757.1
7.5°	2130.9	2145.7	2140.0	2121.1	2099.7	2082.4	2046.0	2012.1	1964.6	1922.9	1887.3
10°	2330.1	2314.5	2302.2	2283.9	2264.1	2232.1	2194.0	2141.6	2081.1	2033.4	1980.4
12.5°	2479.3	2476.7	2461.2	2442.3	2414.4	2384.0	2337.2	2273.4	2203.0	2134.2	2073.4
15°	2682.7	2686.7	2676.5	2656.8	2617.3	2563.6	2492.8	2466.3	2365.5	2290.7	2215.8
17.5°	2823.4	2822.6	2821.2	2793.9	2753.6	2715.3	2649.7	2579.9	2488.7	2383.2	2282.4
20°	2912.7	2905.9	2907.2	2876.6	2846.7	2802.4	2738.5	2637.1	2562.2	2440.4	2336.3
22.5°	2910.5	2909.1	2914.3	2903.8	2882.1	2848.2	2797.8	2712.2	2616.6	2493.7	2376.6
25°	2764.3	2758.9	2790.9	2799.7	2834.4	2840.5	2825.6	2778.6	2688.1	2561.5	2416.6
27.5°	2313.5	2310.5	2369.9	2444.2	2538.4	2611.6	2682.4	2716.6	2688.1	2597.5	2452.2
30°	1898.7	1962.7	1992.6	2100.1	2219.9	2362.8	2488.0	2607.1	2636.4	2596.9	2477.8
32.5°	1576.4	1632.2	1657.2	1749.5	1861.1	2028.5	2216.4	2385.0	2504.1	2534.3	2462.6
35°	1199.1	1199.8	1256.9	1297.8	1401.2	1573.4	1755.8	1981.7	2206.3	2376.4	2394.1
37.5°	956.8	960.2	994.8	1035.5	1113.1	1204.1	1364.7	1552.6	1812.0	2073.2	2226.3
40°	826.2	832.3	858.2	898.3	954.1	1022.8	1148.1	1325.0	1541.4	1832.0	2069.5
42.5°	742.3	752.3	765.6	796.5	831.1	895.4	996.7	1133.4	1330.2	1605.0	1879.0
45°	639.7	645.1	655.4	669.6	700.9	745.9	813.9	905.8	1069.1	1290.3	1564.5
47.5°	564.3	561.4	572.2	583.8	604.6	635.2	680.8	755.8	872.3	1049.8	1282.4
50°	513.1	512.4	519.9	528.8	548.5	571.0	608.4	664.9	757.4	904.4	1117.4
52.5°	465.2	467.8	473.1	484.1	498.4	516.5	550.1	590.8	670.3	797.2	974.8
55°	401.5	403.6	411.0	417.2	427.4	445.7	466.8	500.9	555.3	643.8	790.1
57.5°	347.6	346.7	353.9	355.4	366.9	381.9	398.2	424.7	464.1	529.9	628.4
60°	311.7	309.6	315.8	320.5	326.7	338.9	352.5	378.4	409.7	458.0	542.4
62.5°	279.0	278.1	282.6	287.3	292.4	303.5	315.0	334.8	359.6	400.3	467.3
65°	231.4	233.4	235.5	237.5	240.2	247.0	257.9	271.5	288.5	317.1	365.4
67.5°	181.8	183.9	184.6	188.8	194.6	198.9	205.5	217.6	229.5	253.6	281.1
70°	147.0	146.3	147.0	149.0	156.5	164.0	172.9	181.7	189.2	206.2	229.3
72.5°	126.3	125.1	126.9	127.3	130.9	133.0	138.6	146.9	156.5	168.1	184.7
75°	98.0	98.0	98.0	98.0	100.7	102.1	104.1	106.2	109.6	115.0	127.3
77.5°	72.4	72.5	73.5	74.2	74.7	75.5	76.8	78.8	80.0	82.9	88.2
80°	57.2	57.8	57.2	57.8	57.8	59.2	59.9	61.9	62.6	66.0	68.1
82.5°	43.0	42.6	43.0	43.7	43.7	45.1	45.2	46.7	46.8	48.6	50.6
85°	23.1	21.8	23.1	22.5	23.8	22.5	23.1	24.5	24.5	25.2	27.9
87.5°	10.1	11.2	10.0	10.5	10.4	10.8	10.7	10.6	11.5	10.8	10.9
90°	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2	19.5	18.8	16.5
92.5°	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2	21.1	20.0	18.3
95°	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7	25.5	24.2	22.3
97.5°	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0	26.6	25.2	37.7
100°	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6	27.2	25.8	52.9
102.5°	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8	47.1	51.4	81.0
105°	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7	140.5	171.2	186.8
107.5°	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7	291.3	313.8	311.3
110°	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1	346.9	352.6	350.7



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2	392.1	392.0	390.1
115°	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2	450.5	448.8	447.2
117.5°	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6	505.2	503.8	503.0
120°	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2	540.8	539.4	538.9
122.5°	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0	576.1	575.1	574.4
125°	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1	625.8	625.4	624.7
127.5°	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3	674.8	674.2	673.4
130°	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0	704.3	703.6	702.9
132.5°	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1	732.5	731.8	731.2
135°	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8	775.3	774.8	774.1
137.5°	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8	813.0	812.1	811.7
140°	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9	837.2	836.5	836.0
142.5°	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8	860.2	859.7	859.1
145°	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7	892.4	892.0	891.7
147.5°	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3	921.0	920.6	920.3
150°	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8	938.5	938.2	937.8
152.5°	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4	953.8	953.2	953.0
155°	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9	975.0	974.1	973.9
157.5°	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5	993.5	992.4	992.6
160°	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1	1004.1	1003.0	1003.2
162.5°	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8	1013.6	1012.4	1012.6
165°	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7	1026.3	1024.9	1025.1
167.5°	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9	1034.9
170°	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6	1040.6
172.5°	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1	1045.7	1044.3	1044.2
175°	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6	1050.4	1049.2	1049.0
177.5°	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3	1052.2	1051.0	1050.9
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1641.4	1639.8	1632.2	1623.5	1612.0	1604.4	1598.4	1595.2	1585.4	1573.4	1565.2
5°	1742.8	1722.4	1700.7	1674.1	1649.6	1624.4	1608.8	1590.4	1567.9	1542.8	1525.1
7.5°	1851.5	1811.4	1768.3	1723.8	1679.8	1640.4	1605.5	1575.7	1539.9	1503.8	1478.5
10°	1934.8	1876.2	1815.7	1753.7	1697.2	1644.2	1603.3	1563.2	1520.3	1478.8	1447.5
12.5°	2010.4	1933.4	1863.6	1787.5	1715.2	1651.8	1593.0	1545.8	1494.2	1449.9	1414.3
15°	2106.2	2027.3	1942.9	1827.2	1731.3	1651.0	1579.5	1517.6	1455.0	1400.5	1365.8
17.5°	2195.8	2077.0	1963.6	1867.1	1742.4	1642.1	1554.9	1480.8	1412.1	1354.4	1311.7
20°	2232.8	2117.8	1994.6	1871.5	1749.0	1636.7	1535.3	1453.6	1382.2	1316.8	1277.4
22.5°	2255.1	2124.9	1995.2	1862.8	1732.6	1616.0	1515.7	1425.9	1348.4	1286.3	1237.6
25°	2281.1	2126.0	1983.1	1852.4	1719.7	1593.1	1474.0	1378.8	1295.1	1229.0	1177.3
27.5°	2298.3	2115.8	1946.9	1801.6	1667.0	1541.0	1431.8	1330.8	1245.9	1176.1	1120.6
30°	2301.6	2107.6	1919.1	1761.9	1625.1	1509.4	1393.7	1297.1	1207.3	1133.1	1081.4
32.5°	2305.9	2087.5	1881.5	1714.5	1574.5	1459.9	1355.1	1262.8	1170.8	1097.7	1044.9
35°	2288.0	2076.3	1824.5	1632.6	1492.4	1381.5	1286.9	1201.8	1111.3	1040.5	986.8
37.5°	2210.6	2032.1	1765.4	1540.3	1393.7	1291.0	1213.9	1139.8	1056.7	980.4	929.7
40°	2132.8	1988.5	1719.7	1484.2	1331.1	1225.6	1156.2	1095.7	1015.4	943.9	889.5
42.5°	2016.8	1929.2	1676.2	1425.4	1260.3	1158.7	1100.1	1043.4	972.9	900.3	849.2
45°	1804.1	1815.7	1587.0	1331.8	1162.3	1060.3	1005.1	965.7	903.1	843.2	790.8
47.5°	1537.3	1645.5	1482.3	1232.0	1059.0	963.2	915.0	880.6	838.4	779.6	731.8
50°	1363.1	1517.6	1398.5	1165.1	994.3	899.0	851.3	823.4	786.7	740.4	694.8
52.5°	1202.5	1368.4	1297.2	1090.5	924.0	836.9	790.4	767.4	738.2	694.7	653.4
55°	980.6	1148.7	1132.4	977.9	818.7	740.4	705.0	679.2	659.4	626.8	594.1
57.5°	793.2	952.6	961.0	852.7	725.9	648.5	618.1	598.6	585.7	561.0	530.8
60°	675.1	821.4	850.0	768.3	659.4	591.4	561.4	545.8	535.6	515.8	492.7
62.5°	577.1	701.6	734.0	675.2	595.7	532.0	508.6	493.5	486.6	469.6	449.2
65°	441.7	545.1	576.4	543.7	502.2	451.2	432.1	419.2	413.1	403.6	388.6
67.5°	332.1	407.5	441.8	418.8	403.8	371.6	359.5	352.5	347.1	340.5	328.0
70°	266.8	322.6	358.0	351.8	339.6	322.6	313.7	309.0	303.5	298.1	287.2
72.5°	214.5	252.9	286.1	289.2	279.2	275.8	268.0	266.0	262.7	256.2	250.2
75°	142.2	168.8	191.9	200.8	204.8	208.2	204.8	204.2	203.5	198.0	194.6
77.5°	93.2	107.5	122.1	137.2	143.6	148.2	149.3	151.8	150.0	147.1	145.5
80°	71.5	74.9	85.1	98.0	108.2	112.3	115.0	116.4	115.7	115.0	112.3
82.5°	51.9	54.7	59.5	68.6	77.2	84.0	85.6	85.3	86.8	87.2	85.1
85°	27.9	28.6	29.9	31.3	36.1	43.6	45.6	47.0	48.3	48.3	44.2
87.5°	11.6	10.6	11.2	10.8	12.1	12.3	15.2	17.6	18.5	16.6	17.0
90°	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8	2.5	4.3	6.0
92.5°	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5	14.1	13.6	13.1
95°	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7	40.6	33.4	26.3
97.5°	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8	92.7	89.5	86.3
100°	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1	135.6	139.1	142.5
102.5°	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4	175.9	178.4	180.9
105°	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0	234.9	236.8	238.7
107.5°	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8	297.4	298.9	300.4
110°	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7	339.1	340.5	341.9



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8	379.0	380.3	381.5
115°	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0	438.1	439.1	440.2
117.5°	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4	495.7	497.0	498.3
120°	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1	531.6	533.2	534.7
122.5°	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3	567.6	568.9	570.2
125°	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1	617.4	618.8	620.2
127.5°	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2	665.6	667.0	668.4
130°	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2	695.6	697.0	698.4
132.5°	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0	724.4	725.8	727.2
135°	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9	768.0	769.0	770.1
137.5°	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5	805.8	807.1	808.4
140°	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5	830.5	831.6	832.6
142.5°	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6	853.7	854.7	855.8
145°	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0	886.2	887.4	888.6
147.5°	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5	916.3	917.1	917.9
150°	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2	934.8	935.3	935.8
152.5°	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1	951.4	951.6	951.9
155°	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9	974.6	974.2	973.9
157.5°	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3	993.3	993.3	993.2
160°	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6	1004.4	1004.3	1004.1
162.5°	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2	1014.8	1014.3	1013.9
165°	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1	1027.5	1027.0	1026.5
167.5°	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1	1037.4	1036.7	1036.0
170°	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7	1043.0	1042.3	1041.6
172.5°	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4	1046.6	1045.8	1044.9
175°	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3	1051.4	1050.6	1049.7
177.5°	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5	1052.9	1052.2	1051.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1562.5	1555.4	1550.5	1539.6	1532.6	1524.9	1517.3	1522.2	1521.7	1521.1	1521.1
5°	1510.1	1494.4	1480.2	1461.8	1450.2	1435.9	1425.0	1423.7	1426.4	1416.9	1411.4
7.5°	1458.1	1436.7	1416.5	1396.2	1374.7	1357.5	1346.8	1341.7	1334.8	1328.9	1322.8
10°	1421.6	1396.5	1376.7	1351.5	1328.4	1308.0	1295.1	1286.2	1281.4	1276.7	1267.8
12.5°	1384.1	1359.4	1334.3	1305.8	1283.8	1260.1	1250.4	1240.5	1231.4	1226.0	1213.9
15°	1329.1	1297.1	1270.6	1240.6	1216.1	1193.0	1179.4	1159.6	1156.9	1150.1	1137.9
17.5°	1274.0	1239.2	1202.6	1180.5	1152.8	1128.7	1108.0	1101.4	1081.9	1074.6	1063.9
20°	1230.4	1198.4	1170.5	1141.3	1101.1	1078.6	1062.3	1053.5	1037.8	1028.3	1021.5
22.5°	1192.8	1160.3	1128.1	1093.9	1060.8	1035.6	1023.7	1009.9	1001.3	988.0	980.6
25°	1139.2	1103.8	1065.0	1028.3	1004.5	985.4	966.4	954.1	941.9	935.7	922.1
27.5°	1076.9	1039.9	1003.6	975.7	946.5	927.7	910.4	899.5	884.8	874.5	867.0
30°	1042.6	999.0	967.7	942.5	905.1	887.4	874.5	860.9	850.0	839.1	831.6
32.5°	1002.8	963.1	933.4	902.3	873.5	854.2	837.5	825.5	816.2	805.9	798.4
35°	940.5	907.2	876.5	845.2	824.1	804.4	784.7	774.4	765.6	756.1	749.3
37.5°	884.1	853.0	823.9	794.2	768.0	752.0	736.1	728.3	716.3	709.9	703.0
40°	849.3	818.7	787.4	758.8	731.6	719.3	705.0	693.5	682.6	677.8	670.3
42.5°	811.2	780.6	754.2	723.4	701.1	684.5	671.3	658.6	650.5	643.5	639.3
45°	754.7	727.5	701.6	671.0	649.9	635.6	620.6	609.1	601.6	596.8	589.3
47.5°	699.9	672.6	646.4	619.7	599.3	582.9	568.0	559.9	550.0	544.2	539.1
50°	660.1	635.6	607.7	583.2	562.8	546.5	534.2	524.0	515.2	507.7	504.3
52.5°	623.6	597.5	573.4	550.6	529.0	510.5	499.4	488.6	482.0	473.4	469.4
55°	563.5	538.3	517.9	495.4	474.3	458.7	445.1	435.5	428.7	419.2	413.8
57.5°	507.0	484.4	460.0	440.6	418.8	405.6	394.3	381.4	373.1	365.6	360.3
60°	468.9	443.0	421.9	403.6	384.5	367.5	357.3	347.1	338.2	330.7	326.0
62.5°	429.1	406.6	386.5	366.5	349.1	334.3	322.4	313.9	306.1	301.3	296.6
65°	368.2	350.5	330.1	313.7	297.4	286.5	277.0	269.5	264.0	260.6	256.6
67.5°	312.1	294.9	277.1	261.1	250.2	241.9	235.6	229.2	226.5	222.1	219.4
70°	275.6	257.9	242.3	230.0	219.1	213.0	208.9	204.2	201.4	196.0	193.3
72.5°	235.9	223.1	211.8	201.7	193.0	187.4	182.2	176.4	172.0	166.0	163.3
75°	185.8	174.2	165.4	158.6	153.1	145.6	138.1	132.0	130.0	127.9	127.3
77.5°	137.6	130.3	123.9	118.1	111.3	105.9	104.3	102.9	102.5	101.4	101.4
80°	108.2	101.4	96.6	89.8	85.7	85.7	85.7	84.4	85.1	85.1	85.1
82.5°	80.4	74.2	71.6	69.1	68.3	68.9	68.9	69.1	68.7	69.8	69.3
85°	41.5	42.2	43.6	42.9	43.6	43.6	44.9	44.2	44.9	43.6	44.9
87.5°	16.8	18.8	19.8	20.8	21.8	21.7	22.4	22.5	23.2	23.4	23.5
90°	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2	20.8	21.5	22.1
92.5°	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2	23.3	24.5	25.1
95°	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7	27.9	29.1	29.7
97.5°	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0	29.3	30.7	31.5
100°	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6	30.0	31.4	32.1
102.5°	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8	38.5	34.2	32.2
105°	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7	79.0	48.2	33.0
107.5°	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7	246.2	223.6	200.7
110°	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1	335.4	329.7	314.4



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2	392.3	392.4	389.8
115°	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2	454.0	455.7	456.9
117.5°	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6	508.0	509.3	510.1
120°	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2	543.6	545.0	545.7
122.5°	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0	578.0	579.0	579.5
125°	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1	626.5	626.8	627.2
127.5°	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3	675.9	676.4	676.5
130°	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0	705.7	706.4	706.6
132.5°	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1	733.8	734.5	734.6
135°	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8	776.3	776.8	776.8
137.5°	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8	814.6	815.5	815.7
140°	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9	838.6	839.3	839.5
142.5°	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8	861.3	861.9	861.9
145°	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7	893.1	893.4	893.6
147.5°	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3	921.7	922.0	921.8
150°	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8	939.2	939.5	939.5
152.5°	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4	955.0	955.7	955.6
155°	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9	976.7	977.6	977.5
157.5°	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5	995.5	996.6	996.4
160°	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1	1006.2	1007.2	1007.1
162.5°	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8	1016.0	1017.1	1017.2
165°	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7	1029.1	1030.5	1030.6
167.5°	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5
170°	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1
172.5°	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1	1048.5	1049.9	1049.8
175°	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6	1052.8	1054.0	1053.9
177.5°	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3	1054.4	1055.5	1055.4
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1514.6	1514.0	1514.6	1512.4	1514.6	1514.0	1514.6	1521.1	1521.1	1521.7	1522.2
5°	1409.4	1408.7	1406.7	1400.5	1406.7	1408.7	1409.4	1411.4	1416.9	1426.4	1423.7
7.5°	1317.5	1316.6	1310.6	1310.7	1310.6	1316.6	1317.5	1322.8	1328.9	1334.8	1341.7
10°	1263.1	1263.7	1255.6	1250.8	1255.6	1263.7	1263.1	1267.8	1276.7	1281.4	1286.2
12.5°	1210.3	1207.1	1200.6	1195.3	1200.6	1207.1	1210.3	1213.9	1226.0	1231.4	1240.5
15°	1140.6	1133.8	1117.4	1118.8	1117.4	1133.8	1140.6	1137.9	1150.1	1156.9	1159.6
17.5°	1058.5	1053.5	1053.2	1043.7	1053.2	1053.5	1058.5	1063.9	1074.6	1081.9	1101.4
20°	1010.6	1007.2	1008.5	999.0	1008.5	1007.2	1010.6	1021.5	1028.3	1037.8	1053.5
22.5°	973.0	969.6	963.9	960.9	963.9	969.6	973.0	980.6	988.0	1001.3	1009.9
25°	918.0	912.6	907.2	910.6	907.2	912.6	918.0	922.1	935.7	941.9	954.1
27.5°	863.1	859.0	853.5	852.8	853.5	859.0	863.1	867.0	874.5	884.8	899.5
30°	828.2	824.1	821.4	818.0	821.4	824.1	828.2	831.6	839.1	850.0	860.9
32.5°	792.8	792.0	787.1	786.4	787.1	792.0	792.8	798.4	805.9	816.2	825.5
35°	746.5	742.5	741.1	741.8	741.1	742.5	746.5	749.3	756.1	765.6	774.4
37.5°	702.6	697.1	694.7	692.2	694.7	697.1	702.6	703.0	709.9	716.3	728.3
40°	671.0	665.6	664.2	662.8	664.2	665.6	671.0	670.3	677.8	682.6	693.5
42.5°	635.6	633.4	632.6	630.2	632.6	633.4	635.6	639.3	643.5	650.5	658.6
45°	587.3	586.6	582.5	583.9	582.5	586.6	587.3	589.3	596.8	601.6	609.1
47.5°	536.4	533.4	530.5	532.4	530.5	533.4	536.4	539.1	544.2	550.0	559.9
50°	501.6	500.2	494.1	495.4	494.1	500.2	501.6	504.3	507.7	515.2	524.0
52.5°	466.7	461.5	459.2	458.4	459.2	461.5	466.7	469.4	473.4	482.0	488.6
55°	409.0	402.9	400.2	398.8	400.2	402.9	409.0	413.8	419.2	428.7	435.5
57.5°	352.4	350.7	348.6	350.1	348.6	350.7	352.4	360.3	365.6	373.1	381.4
60°	319.2	319.2	319.2	318.5	319.2	319.2	319.2	326.0	330.7	338.2	347.1
62.5°	293.6	291.9	291.4	292.4	291.4	291.9	293.6	296.6	301.3	306.1	313.9
65°	254.5	253.8	251.1	250.4	251.1	253.8	254.5	256.6	260.6	264.0	269.5
67.5°	217.6	215.2	214.4	213.4	214.4	215.2	217.6	219.4	222.1	226.5	229.2
70°	189.9	188.5	184.4	185.1	184.4	188.5	189.9	193.3	196.0	201.4	204.2
72.5°	159.9	158.6	157.7	156.8	157.7	158.6	159.9	163.3	166.0	172.0	176.4
75°	126.6	125.9	125.2	127.9	125.2	125.9	126.6	127.3	127.9	130.0	132.0
77.5°	101.4	101.4	101.8	100.7	101.8	101.4	101.4	101.4	101.4	102.5	102.9
80°	85.1	85.1	84.4	84.4	84.4	85.1	85.1	85.1	85.1	85.1	84.4
82.5°	68.2	68.7	69.1	68.1	69.1	68.7	68.2	69.3	69.8	68.7	69.1
85°	44.9	44.2	45.6	44.9	45.6	44.2	44.9	44.9	43.6	44.9	44.2
87.5°	24.6	23.6	23.7	24.3	23.7	23.6	24.6	23.5	23.4	23.2	22.5
90°	22.4	22.8	23.1	23.5	23.1	22.8	22.4	22.1	21.5	20.8	20.2
92.5°	25.3	25.5	25.7	26.0	25.7	25.5	25.3	25.1	24.5	23.3	22.2
95°	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.7	29.1	27.9	26.7
97.5°	31.7	31.9	32.0	32.2	32.0	31.9	31.7	31.5	30.7	29.3	28.0
100°	32.3	32.5	32.7	32.8	32.7	32.5	32.3	32.1	31.4	30.0	28.6
102.5°	32.5	32.8	33.1	33.5	33.1	32.8	32.5	32.2	34.2	38.5	42.8
105°	33.4	33.7	34.1	34.4	34.1	33.7	33.4	33.0	48.2	79.0	109.7
107.5°	177.6	154.4	131.2	108.0	131.2	154.4	177.6	200.7	223.6	246.2	268.7
110°	289.5	264.7	239.8	215.0	239.8	264.7	289.5	314.4	329.7	335.4	341.1



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	384.6	379.3	374.1	368.9	374.1	379.3	384.6	389.8	392.4	392.3	392.2
115°	457.6	458.3	459.0	459.7	459.0	458.3	457.6	456.9	455.7	454.0	452.2
117.5°	510.3	510.4	510.5	510.7	510.5	510.4	510.3	510.1	509.3	508.0	506.6
120°	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.7	545.0	543.6	542.2
122.5°	579.7	579.8	580.0	580.1	580.0	579.8	579.7	579.5	579.0	578.0	577.0
125°	627.5	627.9	628.2	628.6	628.2	627.9	627.5	627.2	626.8	626.5	626.1
127.5°	676.2	675.9	675.5	675.2	675.5	675.9	676.2	676.5	676.4	675.9	675.3
130°	706.2	705.9	705.5	705.2	705.5	705.9	706.2	706.6	706.4	705.7	705.0
132.5°	734.2	733.7	733.2	732.7	733.2	733.7	734.2	734.6	734.5	733.8	733.1
135°	776.3	775.8	775.3	774.8	775.3	775.8	776.3	776.8	776.8	776.3	775.8
137.5°	815.4	815.0	814.7	814.3	814.7	815.0	815.4	815.7	815.5	814.6	813.8
140°	839.1	838.8	838.4	838.1	838.4	838.8	839.1	839.5	839.3	838.6	837.9
142.5°	861.4	860.9	860.5	860.0	860.5	860.9	861.4	861.9	861.9	861.3	860.8
145°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.4	893.1	892.7
147.5°	921.0	920.2	919.4	918.6	919.4	920.2	921.0	921.8	922.0	921.7	921.3
150°	938.9	938.4	937.9	937.4	937.9	938.4	938.9	939.5	939.5	939.2	938.8
152.5°	954.8	954.0	953.2	952.4	953.2	954.0	954.8	955.6	955.7	955.0	954.4
155°	976.5	975.4	974.4	973.3	974.4	975.4	976.5	977.5	977.6	976.7	975.9
157.5°	995.1	993.7	992.4	991.0	992.4	993.7	995.1	996.4	996.6	995.5	994.5
160°	1005.9	1004.7	1003.5	1002.3	1003.5	1004.7	1005.9	1007.1	1007.2	1006.2	1005.1
162.5°	1016.1	1015.0	1014.0	1012.9	1014.0	1015.0	1016.1	1017.2	1017.1	1016.0	1014.8
165°	1029.4	1028.1	1026.9	1025.7	1026.9	1028.1	1029.4	1030.6	1030.5	1029.1	1027.7
167.5°	1039.1	1037.7	1036.3	1034.9	1036.3	1037.7	1039.1	1040.5	1040.5	1039.1	1037.7
170°	1044.7	1043.3	1042.0	1040.6	1042.0	1043.3	1044.7	1046.1	1046.1	1044.7	1043.3
172.5°	1048.3	1046.8	1045.2	1043.7	1045.2	1046.8	1048.3	1049.8	1049.9	1048.5	1047.1
175°	1052.6	1051.2	1049.8	1048.4	1049.8	1051.2	1052.6	1053.9	1054.0	1052.8	1051.6
177.5°	1054.0	1052.6	1051.2	1049.8	1051.2	1052.6	1054.0	1055.4	1055.5	1054.4	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1517.3	1524.9	1532.6	1539.6	1550.5	1555.4	1562.5	1565.2	1573.4	1585.4	1595.2
5°	1425.0	1435.9	1450.2	1461.8	1480.2	1494.4	1510.1	1525.1	1542.8	1567.9	1590.4
7.5°	1346.8	1357.5	1374.7	1396.2	1416.5	1436.7	1458.1	1478.5	1503.8	1539.9	1575.7
10°	1295.1	1308.0	1328.4	1351.5	1376.7	1396.5	1421.6	1447.5	1478.8	1520.3	1563.2
12.5°	1250.4	1260.1	1283.8	1305.8	1334.3	1359.4	1384.1	1414.3	1449.9	1494.2	1545.8
15°	1179.4	1193.0	1216.1	1240.6	1270.6	1297.1	1329.1	1365.8	1400.5	1455.0	1517.6
17.5°	1108.0	1128.7	1152.8	1180.5	1202.6	1239.2	1274.0	1311.7	1354.4	1412.1	1480.8
20°	1062.3	1078.6	1101.1	1141.3	1170.5	1198.4	1230.4	1277.4	1316.8	1382.2	1453.6
22.5°	1023.7	1035.6	1060.8	1093.9	1128.1	1160.3	1192.8	1237.6	1286.3	1348.4	1425.9
25°	966.4	985.4	1004.5	1028.3	1065.0	1103.8	1139.2	1177.3	1229.0	1295.1	1378.8
27.5°	910.4	927.7	946.5	975.7	1003.6	1039.9	1076.9	1120.6	1176.1	1245.9	1330.8
30°	874.5	887.4	905.1	942.5	967.7	999.0	1042.6	1081.4	1133.1	1207.3	1297.1
32.5°	837.5	854.2	873.5	902.3	933.4	963.1	1002.8	1044.9	1097.7	1170.8	1262.8
35°	784.7	804.4	824.1	845.2	876.5	907.2	940.5	986.8	1040.5	1111.3	1201.8
37.5°	736.1	752.0	768.0	794.2	823.9	853.0	884.1	929.7	980.4	1056.7	1139.8
40°	705.0	719.3	731.6	758.8	787.4	818.7	849.3	889.5	943.9	1015.4	1095.7
42.5°	671.3	684.5	701.1	723.4	754.2	780.6	811.2	849.2	900.3	972.9	1043.4
45°	620.6	635.6	649.9	671.0	701.6	727.5	754.7	790.8	843.2	903.1	965.7
47.5°	568.0	582.9	599.3	619.7	646.4	672.6	699.9	731.8	779.6	838.4	880.6
50°	534.2	546.5	562.8	583.2	607.7	635.6	660.1	694.8	740.4	786.7	823.4
52.5°	499.4	510.5	529.0	550.6	573.4	597.5	623.6	653.4	694.7	738.2	767.4
55°	445.1	458.7	474.3	495.4	517.9	538.3	563.5	594.1	626.8	659.4	679.2
57.5°	394.3	405.6	418.8	440.6	460.0	484.4	507.0	530.8	561.0	585.7	598.6
60°	357.3	367.5	384.5	403.6	421.9	443.0	468.9	492.7	515.8	535.6	545.8
62.5°	322.4	334.3	349.1	366.5	386.5	406.6	429.1	449.2	469.6	486.6	493.5
65°	277.0	286.5	297.4	313.7	330.1	350.5	368.2	388.6	403.6	413.1	419.2
67.5°	235.6	241.9	250.2	261.1	277.1	294.9	312.1	328.0	340.5	347.1	352.5
70°	208.9	213.0	219.1	230.0	242.3	257.9	275.6	287.2	298.1	303.5	309.0
72.5°	182.2	187.4	193.0	201.7	211.8	223.1	235.9	250.2	256.2	262.7	266.0
75°	138.1	145.6	153.1	158.6	165.4	174.2	185.8	194.6	198.0	203.5	204.2
77.5°	104.3	105.9	111.3	118.1	123.9	130.3	137.6	145.5	147.1	150.0	151.8
80°	85.7	85.7	85.7	89.8	96.6	101.4	108.2	112.3	115.0	115.7	116.4
82.5°	68.9	68.9	68.3	69.1	71.6	74.2	80.4	85.1	87.2	86.8	85.3
85°	44.9	43.6	43.6	42.9	43.6	42.2	41.5	44.2	48.3	48.3	47.0
87.5°	22.4	21.7	21.8	20.8	19.8	18.8	16.8	17.0	16.6	18.5	17.6
90°	19.5	18.8	16.5	14.2	12.0	9.7	7.7	6.0	4.3	2.5	0.8
92.5°	21.1	20.0	18.3	16.6	14.9	13.2	12.6	13.1	13.6	14.1	14.5
95°	25.5	24.2	22.3	20.4	18.5	16.6	19.2	26.3	33.4	40.6	47.7
97.5°	26.6	25.2	37.7	50.2	62.7	75.2	83.1	86.3	89.5	92.7	95.8
100°	27.2	25.8	52.9	80.0	107.1	134.2	146.0	142.5	139.1	135.6	132.1
102.5°	47.1	51.4	81.0	110.6	140.3	169.9	183.4	180.9	178.4	175.9	173.4
105°	140.5	171.2	186.8	202.5	218.1	233.8	240.6	238.7	236.8	234.9	233.0
107.5°	291.3	313.8	311.3	308.9	306.4	303.9	301.9	300.4	298.9	297.4	295.8
110°	346.9	352.6	350.7	348.8	346.9	344.9	343.3	341.9	340.5	339.1	337.7



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	392.1	392.0	390.1	388.2	386.3	384.3	382.8	381.5	380.3	379.0	377.8
115°	450.5	448.8	447.2	445.6	444.1	442.5	441.2	440.2	439.1	438.1	437.0
117.5°	505.2	503.8	503.0	502.2	501.4	500.6	499.5	498.3	497.0	495.7	494.4
120°	540.8	539.4	538.9	538.4	537.9	537.4	536.3	534.7	533.2	531.6	530.1
122.5°	576.1	575.1	574.4	573.8	573.1	572.4	571.5	570.2	568.9	567.6	566.3
125°	625.8	625.4	624.7	624.0	623.4	622.7	621.6	620.2	618.8	617.4	616.1
127.5°	674.8	674.2	673.4	672.6	671.7	670.9	669.8	668.4	667.0	665.6	664.2
130°	704.3	703.6	702.9	702.2	701.5	700.8	699.8	698.4	697.0	695.6	694.2
132.5°	732.5	731.8	731.2	730.6	730.1	729.5	728.6	727.2	725.8	724.4	723.0
135°	775.3	774.8	774.1	773.4	772.7	772.0	771.1	770.1	769.0	768.0	766.9
137.5°	813.0	812.1	811.7	811.4	811.0	810.6	809.7	808.4	807.1	805.8	804.5
140°	837.2	836.5	836.0	835.5	835.0	834.4	833.7	832.6	831.6	830.5	829.5
142.5°	860.2	859.7	859.1	858.6	858.1	857.6	856.8	855.8	854.7	853.7	852.6
145°	892.4	892.0	891.7	891.3	891.0	890.6	889.9	888.6	887.4	886.2	885.0
147.5°	921.0	920.6	920.3	919.9	919.6	919.3	918.7	917.9	917.1	916.3	915.5
150°	938.5	938.2	937.8	937.5	937.1	936.8	936.3	935.8	935.3	934.8	934.2
152.5°	953.8	953.2	953.0	952.7	952.5	952.3	952.1	951.9	951.6	951.4	951.1
155°	975.0	974.1	973.9	973.8	973.6	973.4	973.5	973.9	974.2	974.6	974.9
157.5°	993.5	992.4	992.6	992.8	992.9	993.1	993.2	993.2	993.3	993.3	993.3
160°	1004.1	1003.0	1003.2	1003.4	1003.6	1003.7	1003.9	1004.1	1004.3	1004.4	1004.6
162.5°	1013.6	1012.4	1012.6	1012.8	1012.9	1013.1	1013.4	1013.9	1014.3	1014.8	1015.2
165°	1026.3	1024.9	1025.1	1025.3	1025.5	1025.6	1026.0	1026.5	1027.0	1027.5	1028.1
167.5°	1036.3	1034.9	1034.9	1034.9	1034.9	1034.9	1035.3	1036.0	1036.7	1037.4	1038.1
170°	1042.0	1040.6	1040.6	1040.6	1040.6	1040.6	1040.9	1041.6	1042.3	1043.0	1043.7
172.5°	1045.7	1044.3	1044.2	1044.0	1043.9	1043.8	1044.1	1044.9	1045.8	1046.6	1047.4
175°	1050.4	1049.2	1049.0	1048.8	1048.6	1048.5	1048.8	1049.7	1050.6	1051.4	1052.3
177.5°	1052.2	1051.0	1050.9	1050.8	1050.6	1050.5	1050.8	1051.5	1052.2	1052.9	1053.5
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1598.4	1604.4	1612.0	1623.5	1632.2	1639.8	1641.4	1643.6	1649.1	1658.3	1665.4
5°	1608.8	1624.4	1649.6	1674.1	1700.7	1722.4	1742.8	1757.1	1770.7	1799.3	1822.5
7.5°	1605.5	1640.4	1679.8	1723.8	1768.3	1811.4	1851.5	1887.3	1922.9	1964.6	2012.1
10°	1603.3	1644.2	1697.2	1753.7	1815.7	1876.2	1934.8	1980.4	2033.4	2081.1	2141.6
12.5°	1593.0	1651.8	1715.2	1787.5	1863.6	1933.4	2010.4	2073.4	2134.2	2203.0	2273.4
15°	1579.5	1651.0	1731.3	1827.2	1942.9	2027.3	2106.2	2215.8	2290.7	2365.5	2466.3
17.5°	1554.9	1642.1	1742.4	1867.1	1963.6	2077.0	2195.8	2282.4	2383.2	2488.7	2579.9
20°	1535.3	1636.7	1749.0	1871.5	1994.6	2117.8	2232.8	2336.3	2440.4	2562.2	2637.1
22.5°	1515.7	1616.0	1732.6	1862.8	1995.2	2124.9	2255.1	2376.6	2493.7	2616.6	2712.2
25°	1474.0	1593.1	1719.7	1852.4	1983.1	2126.0	2281.1	2416.6	2561.5	2688.1	2778.6
27.5°	1431.8	1541.0	1667.0	1801.6	1946.9	2115.8	2298.3	2452.2	2597.5	2688.1	2716.6
30°	1393.7	1509.4	1625.1	1761.9	1919.1	2107.6	2301.6	2477.8	2596.9	2636.4	2607.1
32.5°	1355.1	1459.9	1574.5	1714.5	1881.5	2087.5	2305.9	2462.6	2534.3	2504.1	2385.0
35°	1286.9	1381.5	1492.4	1632.6	1824.5	2076.3	2288.0	2394.1	2376.4	2206.3	1981.7
37.5°	1213.9	1291.0	1393.7	1540.3	1765.4	2032.1	2210.6	2226.3	2073.2	1812.0	1552.6
40°	1156.2	1225.6	1331.1	1484.2	1719.7	1988.5	2132.8	2069.5	1832.0	1541.4	1325.0
42.5°	1100.1	1158.7	1260.3	1425.4	1676.2	1929.2	2016.8	1879.0	1605.0	1330.2	1133.4
45°	1005.1	1060.3	1162.3	1331.8	1587.0	1815.7	1804.1	1564.5	1290.3	1069.1	905.8
47.5°	915.0	963.2	1059.0	1232.0	1482.3	1645.5	1537.3	1282.4	1049.8	872.3	755.8
50°	851.3	899.0	994.3	1165.1	1398.5	1517.6	1363.1	1117.4	904.4	757.4	664.9
52.5°	790.4	836.9	924.0	1090.5	1297.2	1368.4	1202.5	974.8	797.2	670.3	590.8
55°	705.0	740.4	818.7	977.9	1132.4	1148.7	980.6	790.1	643.8	555.3	500.9
57.5°	618.1	648.5	725.9	852.7	961.0	952.6	793.2	628.4	529.9	464.1	424.7
60°	561.4	591.4	659.4	768.3	850.0	821.4	675.1	542.4	458.0	409.7	378.4
62.5°	508.6	532.0	595.7	675.2	734.0	701.6	577.1	467.3	400.3	359.6	334.8
65°	432.1	451.2	502.2	543.7	576.4	545.1	441.7	365.4	317.1	288.5	271.5
67.5°	359.5	371.6	403.8	418.8	441.8	407.5	332.1	281.1	253.6	229.5	217.6
70°	313.7	322.6	339.6	351.8	358.0	322.6	266.8	229.3	206.2	189.2	181.7
72.5°	268.0	275.8	279.2	289.2	286.1	252.9	214.5	184.7	168.1	156.5	146.9
75°	204.8	208.2	204.8	200.8	191.9	168.8	142.2	127.3	115.0	109.6	106.2
77.5°	149.3	148.2	143.6	137.2	122.1	107.5	93.2	88.2	82.9	80.0	78.8
80°	115.0	112.3	108.2	98.0	85.1	74.9	71.5	68.1	66.0	62.6	61.9
82.5°	85.6	84.0	77.2	68.6	59.5	54.7	51.9	50.6	48.6	46.8	46.7
85°	45.6	43.6	36.1	31.3	29.9	28.6	27.9	27.9	25.2	24.5	24.5
87.5°	15.2	12.3	12.1	10.8	11.2	10.6	11.6	10.9	10.8	11.5	10.6
90°	2.5	4.3	6.0	7.7	9.7	12.0	14.2	16.5	18.8	19.5	20.2
92.5°	14.1	13.6	13.1	12.6	13.2	14.9	16.6	18.3	20.0	21.1	22.2
95°	40.6	33.4	26.3	19.2	16.6	18.5	20.4	22.3	24.2	25.5	26.7
97.5°	92.7	89.5	86.3	83.1	75.2	62.7	50.2	37.7	25.2	26.6	28.0
100°	135.6	139.1	142.5	146.0	134.2	107.1	80.0	52.9	25.8	27.2	28.6
102.5°	175.9	178.4	180.9	183.4	169.9	140.3	110.6	81.0	51.4	47.1	42.8
105°	234.9	236.8	238.7	240.6	233.8	218.1	202.5	186.8	171.2	140.5	109.7
107.5°	297.4	298.9	300.4	301.9	303.9	306.4	308.9	311.3	313.8	291.3	268.7
110°	339.1	340.5	341.9	343.3	344.9	346.9	348.8	350.7	352.6	346.9	341.1



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	379.0	380.3	381.5	382.8	384.3	386.3	388.2	390.1	392.0	392.1	392.2
115°	438.1	439.1	440.2	441.2	442.5	444.1	445.6	447.2	448.8	450.5	452.2
117.5°	495.7	497.0	498.3	499.5	500.6	501.4	502.2	503.0	503.8	505.2	506.6
120°	531.6	533.2	534.7	536.3	537.4	537.9	538.4	538.9	539.4	540.8	542.2
122.5°	567.6	568.9	570.2	571.5	572.4	573.1	573.8	574.4	575.1	576.1	577.0
125°	617.4	618.8	620.2	621.6	622.7	623.4	624.0	624.7	625.4	625.8	626.1
127.5°	665.6	667.0	668.4	669.8	670.9	671.7	672.6	673.4	674.2	674.8	675.3
130°	695.6	697.0	698.4	699.8	700.8	701.5	702.2	702.9	703.6	704.3	705.0
132.5°	724.4	725.8	727.2	728.6	729.5	730.1	730.6	731.2	731.8	732.5	733.1
135°	768.0	769.0	770.1	771.1	772.0	772.7	773.4	774.1	774.8	775.3	775.8
137.5°	805.8	807.1	808.4	809.7	810.6	811.0	811.4	811.7	812.1	813.0	813.8
140°	830.5	831.6	832.6	833.7	834.4	835.0	835.5	836.0	836.5	837.2	837.9
142.5°	853.7	854.7	855.8	856.8	857.6	858.1	858.6	859.1	859.7	860.2	860.8
145°	886.2	887.4	888.6	889.9	890.6	891.0	891.3	891.7	892.0	892.4	892.7
147.5°	916.3	917.1	917.9	918.7	919.3	919.6	919.9	920.3	920.6	921.0	921.3
150°	934.8	935.3	935.8	936.3	936.8	937.1	937.5	937.8	938.2	938.5	938.8
152.5°	951.4	951.6	951.9	952.1	952.3	952.5	952.7	953.0	953.2	953.8	954.4
155°	974.6	974.2	973.9	973.5	973.4	973.6	973.8	973.9	974.1	975.0	975.9
157.5°	993.3	993.3	993.2	993.2	993.1	992.9	992.8	992.6	992.4	993.5	994.5
160°	1004.4	1004.3	1004.1	1003.9	1003.7	1003.6	1003.4	1003.2	1003.0	1004.1	1005.1
162.5°	1014.8	1014.3	1013.9	1013.4	1013.1	1012.9	1012.8	1012.6	1012.4	1013.6	1014.8
165°	1027.5	1027.0	1026.5	1026.0	1025.6	1025.5	1025.3	1025.1	1024.9	1026.3	1027.7
167.5°	1037.4	1036.7	1036.0	1035.3	1034.9	1034.9	1034.9	1034.9	1034.9	1036.3	1037.7
170°	1043.0	1042.3	1041.6	1040.9	1040.6	1040.6	1040.6	1040.6	1040.6	1042.0	1043.3
172.5°	1046.6	1045.8	1044.9	1044.1	1043.8	1043.9	1044.0	1044.2	1044.3	1045.7	1047.1
175°	1051.4	1050.6	1049.7	1048.8	1048.5	1048.6	1048.8	1049.0	1049.2	1050.4	1051.6
177.5°	1052.9	1052.2	1051.5	1050.8	1050.5	1050.6	1050.8	1050.9	1051.0	1052.2	1053.3
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7	1589.7
2.5°	1676.8	1676.8	1679.0	1687.2	1688.3	1695.3	1693.2
5°	1842.9	1855.8	1860.6	1881.0	1893.2	1898.7	1887.8
7.5°	2046.0	2082.4	2099.7	2121.1	2140.0	2145.7	2130.9
10°	2194.0	2232.1	2264.1	2283.9	2302.2	2314.5	2330.1
12.5°	2337.2	2384.0	2414.4	2442.3	2461.2	2476.7	2479.3
15°	2492.8	2563.6	2617.3	2656.8	2676.5	2686.7	2682.7
17.5°	2649.7	2715.3	2753.6	2793.9	2821.2	2822.6	2823.4
20°	2738.5	2802.4	2846.7	2876.6	2907.2	2905.9	2912.7
22.5°	2797.8	2848.2	2882.1	2903.8	2914.3	2909.1	2910.5
25°	2825.6	2840.5	2834.4	2799.7	2790.9	2758.9	2764.3
27.5°	2682.4	2611.6	2538.4	2444.2	2369.9	2310.5	2313.5
30°	2488.0	2362.8	2219.9	2100.1	1992.6	1962.7	1898.7
32.5°	2216.4	2028.5	1861.1	1749.5	1657.2	1632.2	1576.4
35°	1755.8	1573.4	1401.2	1297.8	1256.9	1199.8	1199.1
37.5°	1364.7	1204.1	1113.1	1035.5	994.8	960.2	956.8
40°	1148.1	1022.8	954.1	898.3	858.2	832.3	826.2
42.5°	996.7	895.4	831.1	796.5	765.6	752.3	742.3
45°	813.9	745.9	700.9	669.6	655.4	645.1	639.7
47.5°	680.8	635.2	604.6	583.8	572.2	561.4	564.3
50°	608.4	571.0	548.5	528.8	519.9	512.4	513.1
52.5°	550.1	516.5	498.4	484.1	473.1	467.8	465.2
55°	466.8	445.7	427.4	417.2	411.0	403.6	401.5
57.5°	398.2	381.9	366.9	355.4	353.9	346.7	347.6
60°	352.5	338.9	326.7	320.5	315.8	309.6	311.7
62.5°	315.0	303.5	292.4	287.3	282.6	278.1	279.0
65°	257.9	247.0	240.2	237.5	235.5	233.4	231.4
67.5°	205.5	198.9	194.6	188.8	184.6	183.9	181.8
70°	172.9	164.0	156.5	149.0	147.0	146.3	147.0
72.5°	138.6	133.0	130.9	127.3	126.9	125.1	126.3
75°	104.1	102.1	100.7	98.0	98.0	98.0	98.0
77.5°	76.8	75.5	74.7	74.2	73.5	72.5	72.4
80°	59.9	59.2	57.8	57.8	57.2	57.8	57.2
82.5°	45.2	45.1	43.7	43.7	43.0	42.6	43.0
85°	23.1	22.5	23.8	22.5	23.1	21.8	23.1
87.5°	10.7	10.8	10.4	10.5	10.0	11.2	10.1
90°	20.8	21.5	22.1	22.4	22.8	23.1	23.5
92.5°	23.3	24.5	25.1	25.3	25.5	25.7	26.0
95°	27.9	29.1	29.7	29.7	29.7	29.7	29.7
97.5°	29.3	30.7	31.5	31.7	31.9	32.0	32.2
100°	30.0	31.4	32.1	32.3	32.5	32.7	32.8
102.5°	38.5	34.2	32.2	32.5	32.8	33.1	33.5
105°	79.0	48.2	33.0	33.4	33.7	34.1	34.4
107.5°	246.2	223.6	200.7	177.6	154.4	131.2	108.0
110°	335.4	329.7	314.4	289.5	264.7	239.8	215.0



TEST NUMBER: P332342

CATALOG NUMBER: S123RDIP-S1000D805U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	392.3	392.4	389.8	384.6	379.3	374.1	368.9
115°	454.0	455.7	456.9	457.6	458.3	459.0	459.7
117.5°	508.0	509.3	510.1	510.3	510.4	510.5	510.7
120°	543.6	545.0	545.7	545.7	545.7	545.7	545.7
122.5°	578.0	579.0	579.5	579.7	579.8	580.0	580.1
125°	626.5	626.8	627.2	627.5	627.9	628.2	628.6
127.5°	675.9	676.4	676.5	676.2	675.9	675.5	675.2
130°	705.7	706.4	706.6	706.2	705.9	705.5	705.2
132.5°	733.8	734.5	734.6	734.2	733.7	733.2	732.7
135°	776.3	776.8	776.8	776.3	775.8	775.3	774.8
137.5°	814.6	815.5	815.7	815.4	815.0	814.7	814.3
140°	838.6	839.3	839.5	839.1	838.8	838.4	838.1
142.5°	861.3	861.9	861.9	861.4	860.9	860.5	860.0
145°	893.1	893.4	893.6	893.6	893.6	893.6	893.6
147.5°	921.7	922.0	921.8	921.0	920.2	919.4	918.6
150°	939.2	939.5	939.5	938.9	938.4	937.9	937.4
152.5°	955.0	955.7	955.6	954.8	954.0	953.2	952.4
155°	976.7	977.6	977.5	976.5	975.4	974.4	973.3
157.5°	995.5	996.6	996.4	995.1	993.7	992.4	991.0
160°	1006.2	1007.2	1007.1	1005.9	1004.7	1003.5	1002.3
162.5°	1016.0	1017.1	1017.2	1016.1	1015.0	1014.0	1012.9
165°	1029.1	1030.5	1030.6	1029.4	1028.1	1026.9	1025.7
167.5°	1039.1	1040.5	1040.5	1039.1	1037.7	1036.3	1034.9
170°	1044.7	1046.1	1046.1	1044.7	1043.3	1042.0	1040.6
172.5°	1048.5	1049.9	1049.8	1048.3	1046.8	1045.2	1043.7
175°	1052.8	1054.0	1053.9	1052.6	1051.2	1049.8	1048.4
177.5°	1054.4	1055.5	1055.4	1054.0	1052.6	1051.2	1049.8
180°	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3	1052.3

(END OF REPORT)