

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331961-840

Luminaire Tested: **S123DIP-S775D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331961-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D365U840-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4666.1 lumens
Efficiency: N/A
Efficacy: 133.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	97	93	90	96	92	89	85	82	79	77	73	71	69	65	63	62	58
2	93	85	79	73	87	80	75	70	72	68	64	64	61	58	57	54	52	48
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44	41
4	77	66	58	52	73	63	55	50	56	50	46	51	46	42	45	41	38	35
5	71	59	51	44	67	56	49	43	51	44	39	45	40	36	41	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	34	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21	19
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13237	13237	13237
5°	13299	13116	13207
10°	13210	13002	13083
15°	13056	12856	12880
20°	12875	12645	12657
25°	12634	12396	12371
30°	12367	12117	12026
35°	12089	11825	11671
40°	11797	11500	11323
45°	11478	11204	10930
50°	11156	10836	10535
55°	10736	10457	10141
60°	10312	10015	9698
65°	9938	9536	9235
70°	9385	8985	8585
75°	8576	8268	7918
80°	7736	7407	7345
85°	6780	6533	6274



TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	2.5
10°-20°	327.1	7.0
20°-30°	483.2	10.4
30°-40°	564.4	12.1
40°-50°	567.4	12.2
50°-60°	498.4	10.7
60°-70°	371.3	8.0
70°-80°	211.6	4.5
80°-90°	62.1	1.3
90°-100°	17.5	0.4
100°-110°	83.2	1.8
110°-120°	199.9	4.3
120°-130°	254.6	5.5
130°-140°	272.0	5.8
140°-150°	254.4	5.5
150°-160°	205.2	4.4
160°-170°	132.4	2.8
170°-180°	45.6	1.0
0°-30°	926.1	19.8
0°-40°	1490.5	31.9
0°-60°	2556.3	54.8
0°-90°	3201.3	68.6
90°-120°	300.6	6.4
90°-150°	1081.5	23.2
90°-180°	1465.0	31.4
0°-180°	4666.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1230	1230	1230	1230	1230	
5°	1231	1225	1214	1224	1222	117
15°	1172	1167	1154	1161	1156	330
25°	1064	1057	1044	1044	1042	490
35°	920	913	900	894	888	575
45°	754	749	736	724	718	582
55°	572	570	557	546	540	512
65°	390	385	374	366	363	385
75°	206	202	199	194	190	221
85°	55	53	53	51	51	60
90°	0	4	9	10	11	4
95°	22	8	11	13	14	27
105°	106	108	78	18	16	113
115°	199	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	269
145°	404	406	407	408	408	253
155°	445	444	445	446	444	205
165°	469	468	468	470	468	133
175°	480	479	479	481	479	46
180°	480	480	480	480	480	



TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1234.0	1233.2	1232.5	1231.7	1231.0	1229.6	1227.5	1225.5	1223.4	1221.3	1223.1
5°	1230.8	1229.6	1228.5	1227.3	1226.1	1224.3	1221.6	1219.1	1216.5	1213.9	1216.3
7.5°	1218.8	1217.6	1216.4	1215.3	1214.1	1212.1	1209.4	1206.8	1204.1	1201.4	1203.6
10°	1208.6	1207.4	1206.3	1205.1	1204.0	1201.8	1198.7	1195.7	1192.7	1189.6	1191.7
12.5°	1195.1	1194.1	1193.2	1192.1	1191.1	1189.2	1186.4	1183.5	1180.6	1177.7	1179.3
15°	1171.6	1170.6	1169.7	1168.8	1167.8	1165.9	1162.8	1159.7	1156.7	1153.7	1155.5
17.5°	1144.3	1143.1	1141.9	1140.6	1139.4	1137.3	1134.3	1131.1	1128.1	1125.1	1126.4
20°	1124.0	1122.6	1121.3	1119.8	1118.4	1116.1	1113.1	1110.0	1107.0	1103.9	1104.9
22.5°	1101.2	1099.7	1098.3	1096.9	1095.5	1093.3	1090.3	1087.2	1084.2	1081.1	1081.9
25°	1063.8	1062.4	1061.0	1059.6	1058.1	1055.9	1052.8	1049.8	1046.7	1043.7	1043.9
27.5°	1023.8	1022.4	1021.1	1019.7	1018.3	1016.0	1012.7	1009.5	1006.1	1002.8	1003.0
30°	995.0	993.8	992.7	991.5	990.3	988.1	984.8	981.5	978.3	974.9	974.9
32.5°	966.2	964.7	963.1	961.6	960.1	958.1	955.4	952.9	950.4	947.9	946.5
35°	920.0	918.6	917.2	915.7	914.3	912.1	909.0	905.9	902.9	899.9	898.5
37.5°	872.5	870.8	869.0	867.2	865.5	863.0	859.9	856.8	853.6	850.6	848.9
40°	839.6	838.2	836.8	835.4	833.9	831.6	828.3	825.1	821.7	818.4	816.6
42.5°	806.6	805.0	803.3	801.8	800.2	797.8	794.5	791.1	787.9	784.6	782.7
45°	754.0	753.0	752.0	751.1	750.1	748.2	745.1	742.0	739.0	736.0	733.2
47.5°	701.7	700.3	698.9	697.6	696.2	694.1	691.3	688.4	685.5	682.7	679.8
50°	666.2	665.0	663.8	662.7	661.5	659.3	656.3	653.3	650.2	647.1	644.6
52.5°	628.9	628.1	627.3	626.5	625.7	623.7	620.5	617.2	614.0	610.8	608.5
55°	572.1	571.8	571.6	571.4	571.1	569.5	566.4	563.4	560.3	557.2	554.7
57.5°	518.0	517.2	516.3	515.5	514.7	513.1	510.7	508.2	505.7	503.3	501.0
60°	479.0	478.8	478.6	478.3	478.1	476.6	473.7	470.9	468.1	465.2	463.1
62.5°	444.3	443.7	443.1	442.5	441.9	440.2	437.4	434.5	431.7	428.9	426.8
65°	390.2	389.0	387.8	386.7	385.5	383.7	381.3	379.0	376.7	374.4	372.4
67.5°	332.9	331.8	330.8	329.7	328.7	327.3	325.6	323.8	321.9	320.2	318.5
70°	298.2	296.8	295.4	294.0	292.6	291.1	289.7	288.3	286.9	285.5	283.9
72.5°	261.9	260.7	259.7	258.7	257.7	256.4	254.8	253.2	251.6	249.9	248.5
75°	206.2	205.2	204.3	203.4	202.5	201.6	200.9	200.2	199.4	198.8	197.6
77.5°	156.9	156.4	155.9	155.4	154.8	154.2	153.3	152.5	151.7	150.8	150.0
80°	124.8	124.1	123.4	122.7	122.0	121.4	120.9	120.5	120.0	119.5	119.3
82.5°	93.5	93.3	93.2	93.0	92.9	92.8	92.7	92.6	92.5	92.4	92.0
85°	54.9	54.5	54.0	53.6	53.1	52.9	52.9	52.9	52.9	52.9	52.4
87.5°	22.0	21.6	21.2	20.8	20.4	20.3	20.3	20.3	20.3	20.3	20.2
90°	0.4	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.6	8.6	8.9
92.5°	6.7	6.5	6.2	6.0	5.8	6.1	6.8	7.6	8.4	9.1	9.6
95°	21.8	18.5	15.2	12.0	8.8	7.6	8.5	9.3	10.2	11.1	11.6
97.5°	43.7	42.3	40.8	39.4	37.9	34.3	28.6	22.9	17.2	11.5	12.1
100°	60.3	61.9	63.5	65.0	66.7	61.3	48.9	36.6	24.1	11.8	12.4
102.5°	79.2	80.3	81.4	82.6	83.7	77.6	64.0	50.5	37.0	23.5	21.5
105°	106.3	107.2	108.1	109.0	109.9	106.7	99.6	92.4	85.3	78.2	64.1
107.5°	135.0	135.7	136.4	137.1	137.8	138.8	139.9	141.0	142.1	143.2	132.9
110°	154.2	154.8	155.4	156.0	156.7	157.4	158.3	159.2	160.1	161.0	158.3



TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.4	173.0	173.6	174.1	174.7	175.4	176.3	177.2	178.0	178.9	178.9
115°	199.4	200.0	200.5	200.9	201.4	202.0	202.7	203.4	204.1	204.8	205.6
117.5°	225.7	226.3	226.8	227.4	228.0	228.5	228.8	229.2	229.6	229.9	230.6
120°	242.0	242.7	243.4	244.1	244.8	245.3	245.5	245.8	246.0	246.2	246.9
122.5°	258.5	259.1	259.6	260.2	260.8	261.3	261.6	261.9	262.2	262.5	263.0
125°	281.2	281.9	282.5	283.1	283.8	284.2	284.6	284.9	285.2	285.5	285.7
127.5°	303.2	303.9	304.5	305.1	305.7	306.2	306.6	307.0	307.4	307.7	308.0
130°	316.9	317.5	318.1	318.8	319.4	319.9	320.2	320.5	320.8	321.1	321.4
132.5°	330.0	330.6	331.3	331.9	332.5	333.0	333.3	333.6	333.8	334.1	334.4
135°	350.1	350.5	351.0	351.5	351.9	352.3	352.6	353.0	353.4	353.7	353.9
137.5°	367.2	367.8	368.4	369.0	369.6	370.0	370.2	370.3	370.5	370.7	371.1
140°	378.6	379.1	379.6	380.0	380.5	380.9	381.1	381.3	381.6	381.8	382.1
142.5°	389.2	389.7	390.1	390.6	391.1	391.4	391.7	391.9	392.1	392.4	392.6
145°	403.9	404.6	405.1	405.7	406.2	406.6	406.7	406.9	407.0	407.2	407.4
147.5°	417.9	418.3	418.6	419.0	419.3	419.6	419.8	419.9	420.1	420.2	420.4
150°	426.5	426.7	426.9	427.2	427.4	427.6	427.8	427.9	428.1	428.2	428.4
152.5°	434.1	434.2	434.3	434.4	434.5	434.7	434.7	434.8	434.9	435.0	435.4
155°	445.0	444.8	444.6	444.5	444.3	444.3	444.4	444.4	444.5	444.6	445.0
157.5°	453.4	453.4	453.4	453.3	453.3	453.3	453.2	453.1	453.0	453.0	453.4
160°	458.6	458.5	458.4	458.3	458.3	458.2	458.1	458.0	458.0	457.9	458.3
162.5°	463.4	463.2	463.0	462.8	462.6	462.4	462.3	462.3	462.2	462.1	462.6
165°	469.3	469.0	468.8	468.6	468.3	468.2	468.1	468.0	467.9	467.9	468.5
167.5°	473.8	473.5	473.2	472.9	472.5	472.4	472.4	472.4	472.4	472.4	473.0
170°	476.4	476.1	475.7	475.4	475.1	474.9	474.9	474.9	474.9	474.9	475.6
172.5°	478.1	477.8	477.4	477.0	476.6	476.5	476.5	476.6	476.7	476.7	477.4
175°	480.3	479.9	479.5	479.2	478.8	478.6	478.7	478.8	478.8	478.9	479.5
177.5°	480.9	480.6	480.3	480.0	479.6	479.5	479.6	479.6	479.7	479.8	480.3
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3



TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8	1229.8
2.5°	1225.1	1227.0	1228.8	1229.7	1229.5	1229.3	1229.1	1228.9
5°	1218.6	1220.9	1223.4	1224.3	1223.8	1223.4	1222.8	1222.3
7.5°	1205.7	1207.8	1209.9	1210.8	1210.5	1210.2	1209.9	1209.7
10°	1193.9	1195.9	1198.0	1198.9	1198.4	1197.9	1197.5	1197.0
12.5°	1180.8	1182.3	1184.0	1184.6	1184.3	1184.0	1183.8	1183.5
15°	1157.4	1159.2	1161.1	1161.3	1159.9	1158.5	1157.2	1155.8
17.5°	1127.7	1129.0	1130.3	1130.7	1130.2	1129.7	1129.2	1128.7
20°	1105.8	1106.7	1107.7	1107.8	1107.1	1106.4	1105.7	1105.0
22.5°	1082.6	1083.4	1084.1	1084.0	1083.2	1082.3	1081.4	1080.5
25°	1044.1	1044.4	1044.6	1044.4	1043.7	1043.0	1042.3	1041.6
27.5°	1003.2	1003.4	1003.6	1003.2	1002.4	1001.5	1000.6	999.7
30°	974.9	974.9	974.9	974.1	972.5	970.8	969.2	967.6
32.5°	945.2	943.9	942.6	941.5	940.6	939.7	938.8	938.0
35°	897.1	895.6	894.2	892.9	891.7	890.6	889.4	888.2
37.5°	847.2	845.5	843.8	842.6	841.8	841.1	840.3	839.6
40°	814.7	812.8	810.9	809.5	808.6	807.6	806.7	805.8
42.5°	780.8	778.9	777.1	775.7	774.8	773.8	772.8	771.9
45°	730.3	727.5	724.7	722.7	721.5	720.3	719.1	718.0
47.5°	677.1	674.4	671.6	669.6	668.6	667.6	666.6	665.5
50°	642.0	639.3	636.8	634.8	633.4	632.0	630.6	629.1
52.5°	606.3	604.1	601.9	600.2	598.7	597.3	595.9	594.5
55°	552.1	549.5	546.9	545.0	543.8	542.7	541.5	540.4
57.5°	498.7	496.4	494.1	492.3	490.9	489.6	488.2	486.9
60°	461.0	458.9	456.8	455.1	453.9	452.8	451.6	450.5
62.5°	424.6	422.5	420.4	419.0	418.2	417.4	416.6	415.8
65°	370.5	368.7	366.8	365.5	364.8	364.1	363.3	362.6
67.5°	316.9	315.3	313.6	312.3	311.3	310.3	309.3	308.3
70°	282.3	280.5	278.9	277.5	276.3	275.2	274.0	272.8
72.5°	247.0	245.6	244.2	243.1	242.5	241.9	241.3	240.7
75°	196.4	195.3	194.1	193.2	192.5	191.8	191.1	190.4
77.5°	149.2	148.3	147.5	147.2	147.2	147.2	147.2	147.2
80°	119.1	118.8	118.6	118.5	118.5	118.5	118.5	118.5
82.5°	91.6	91.2	90.7	90.4	90.3	90.1	89.9	89.7
85°	51.9	51.5	51.0	50.8	50.8	50.8	50.8	50.8
87.5°	20.1	20.0	19.8	19.8	19.8	19.8	19.9	19.9
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.2	10.7	11.2	11.5	11.5	11.6	11.7	11.8
95°	12.2	12.7	13.3	13.5	13.5	13.5	13.5	13.5
97.5°	12.7	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.6	14.7	14.8	14.9	14.9
102.5°	19.6	17.6	15.7	14.7	14.8	14.9	15.1	15.2
105°	50.1	36.1	22.0	15.0	15.2	15.3	15.6	15.7
107.5°	122.7	112.4	102.1	91.6	81.1	70.5	59.9	49.3
110°	155.7	153.1	150.5	143.5	132.2	120.8	109.5	98.2



TEST NUMBER: P331961-840

CATALOG NUMBER: S123DIP-S775D365U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	179.0	179.0	179.2	177.9	175.5	173.2	170.8	168.3
115°	206.4	207.2	208.0	208.5	208.8	209.2	209.5	209.8
117.5°	231.3	231.9	232.5	232.9	232.9	233.0	233.1	233.1
120°	247.5	248.1	248.7	249.1	249.1	249.1	249.1	249.1
122.5°	263.4	263.9	264.3	264.5	264.6	264.7	264.7	264.8
125°	285.8	286.0	286.1	286.3	286.4	286.6	286.8	286.9
127.5°	308.2	308.5	308.8	308.8	308.6	308.5	308.3	308.2
130°	321.8	322.1	322.4	322.6	322.3	322.2	322.0	321.8
132.5°	334.7	335.0	335.3	335.4	335.1	334.9	334.7	334.5
135°	354.2	354.4	354.6	354.6	354.4	354.2	353.9	353.7
137.5°	371.4	371.8	372.2	372.3	372.1	372.0	371.8	371.7
140°	382.4	382.7	383.1	383.1	383.0	382.8	382.7	382.5
142.5°	392.9	393.1	393.4	393.4	393.2	392.9	392.7	392.5
145°	407.5	407.7	407.8	407.9	407.9	407.9	407.9	407.9
147.5°	420.5	420.7	420.9	420.8	420.4	420.0	419.7	419.3
150°	428.6	428.7	428.9	428.8	428.6	428.4	428.1	427.9
152.5°	435.7	436.0	436.3	436.2	435.9	435.5	435.0	434.7
155°	445.5	445.9	446.3	446.2	445.8	445.2	444.7	444.2
157.5°	453.9	454.4	454.9	454.8	454.2	453.6	452.9	452.3
160°	458.8	459.3	459.8	459.7	459.2	458.6	458.1	457.5
162.5°	463.2	463.7	464.2	464.3	463.8	463.3	462.8	462.3
165°	469.1	469.8	470.4	470.4	469.9	469.3	468.8	468.2
167.5°	473.6	474.3	474.9	474.9	474.3	473.6	473.0	472.4
170°	476.3	476.9	477.5	477.5	476.9	476.3	475.6	474.9
172.5°	478.0	478.6	479.2	479.2	478.5	477.8	477.1	476.4
175°	480.0	480.6	481.1	481.1	480.5	479.8	479.2	478.6
177.5°	480.8	481.3	481.8	481.7	481.1	480.5	479.8	479.2
180°	480.3	480.3	480.3	480.3	480.3	480.3	480.3	480.3

(END OF REPORT)